

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332306-830

Luminaire Tested: **S123RDIP-S775D585U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332306-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D585U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5078.8 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	92	84	79	74	85	79	74	69	69	65	61	59	56	54	50	48	46	42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36
4	77	67	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	30	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	57	45	37	32	53	42	35	30	37	32	28	33	28	25	28	25	22	20
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	26	23	20	18
10	49	38	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12408	12408	12408	12408
5°	14791	12460	10974	12460
10°	18467	12389	9913	12389
15°	21677	12262	9040	12262
20°	24192	12073	8298	12073
25°	23807	11874	7842	11874
30°	17112	11691	7372	11691
35°	11426	11452	7068	11452
40°	8418	11164	6753	11164
45°	7060	10659	6445	10659
50°	6231	9999	6015	9999
55°	5465	9242	5427	9242
60°	4865	8521	4971	8521
65°	4274	7743	4625	7743
70°	3355	7050	4223	7050
75°	2957	6159	3855	6159
80°	2572	5232	3794	5232
85°	2075	4199	4026	4199



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.4	2.2
10°-20°	354.2	7.0
20°-30°	556.4	11.0
30°-40°	580.5	11.4
40°-50°	496.8	9.8
50°-60°	378.6	7.5
60°-70°	242.7	4.8
70°-80°	116.7	2.3
80°-90°	32.9	0.6
90°-100°	26.3	0.5
100°-110°	125.4	2.5
110°-120°	301.2	5.9
120°-130°	383.5	7.6
130°-140°	409.8	8.1
140°-150°	383.2	7.5
150°-160°	309.1	6.1
160°-170°	199.5	3.9
170°-180°	68.7	1.4
0°-30°	1023.9	20.2
0°-40°	1604.4	31.6
0°-60°	2479.8	48.8
0°-90°	2872.2	56.6
90°-120°	452.8	8.9
90°-150°	1629.3	32.1
90°-180°	2207.0	43.5
0°-180°	5078.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1153	1153	1153	1153	1153	
5°	1369	1153	1016	1153	1369	141
15°	1945	1100	811	1100	1945	552
25°	2004	1000	660	1000	2004	862
35°	870	872	538	872	870	570
45°	464	700	423	700	464	365
55°	291	492	289	492	291	263
65°	168	304	182	304	168	165
75°	71	148	93	148	71	76
85°	17	34	33	34	17	20
90°	16	1	16	1	16	8
95°	20	33	20	33	20	17
105°	24	160	24	160	24	54
115°	316	300	316	300	316	292
125°	432	424	432	424	432	386
135°	533	527	533	527	533	411
145°	614	608	614	608	614	384
155°	669	670	669	670	669	309
165°	705	707	705	707	705	199
175°	721	724	721	724	721	69
180°	724	724	724	724	724	



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1227.8	1229.4	1224.2	1223.4	1217.5	1215.9	1215.9	1207.6	1202.5	1195.8	1191.8
5°	1368.9	1376.8	1372.8	1364.0	1349.2	1345.7	1336.3	1321.5	1304.8	1284.0	1274.1
7.5°	1545.1	1555.9	1551.8	1538.0	1522.6	1510.0	1483.6	1459.0	1424.6	1394.3	1368.5
10°	1689.6	1678.3	1669.4	1656.0	1641.8	1618.5	1590.9	1552.9	1509.0	1474.5	1436.0
12.5°	1797.8	1795.9	1784.7	1770.9	1750.8	1728.7	1694.8	1648.5	1597.4	1547.6	1503.5
15°	1945.2	1948.2	1940.8	1926.5	1897.9	1858.9	1807.6	1788.3	1715.3	1661.0	1606.8
17.5°	2047.3	2046.7	2045.7	2025.9	1996.7	1969.0	1921.4	1870.8	1804.6	1728.2	1655.0
20°	2112.0	2107.1	2108.1	2085.8	2064.2	2032.1	1985.7	1912.2	1857.9	1769.6	1694.0
22.5°	2110.4	2109.5	2113.3	2105.6	2089.8	2065.3	2028.7	1966.7	1897.4	1808.3	1723.3
25°	2004.5	2000.5	2023.7	2030.1	2055.3	2059.7	2048.9	2014.9	1949.2	1857.4	1752.3
27.5°	1677.6	1675.5	1718.4	1772.4	1840.6	1893.8	1945.0	1969.8	1949.2	1883.5	1778.2
30°	1376.8	1423.1	1444.9	1522.9	1609.7	1713.4	1804.1	1890.5	1911.7	1883.1	1796.7
32.5°	1143.1	1183.6	1201.6	1268.6	1349.5	1470.9	1607.1	1729.4	1815.8	1837.7	1785.6
35°	869.5	870.0	911.4	941.0	1016.1	1140.9	1273.2	1437.0	1599.8	1723.2	1736.0
37.5°	693.8	696.3	721.3	750.8	807.1	873.2	989.6	1125.8	1313.9	1503.3	1614.3
40°	599.1	603.5	622.3	651.4	691.8	741.7	832.5	960.8	1117.7	1328.4	1500.6
42.5°	538.3	545.4	555.2	577.6	602.7	649.3	722.7	821.8	964.5	1163.8	1362.4
45°	463.8	467.8	475.2	485.6	508.3	540.8	590.2	656.8	775.2	935.7	1134.4
47.5°	409.2	407.1	414.9	423.3	438.4	460.6	493.7	548.1	632.5	761.2	929.9
50°	372.1	371.6	377.0	383.4	397.8	414.1	441.2	482.1	549.2	655.8	810.3
52.5°	337.3	339.2	343.1	351.1	361.4	374.6	398.9	428.4	486.1	578.1	706.8
55°	291.2	292.7	298.0	302.5	309.9	323.2	338.6	363.2	402.7	466.8	572.9
57.5°	252.0	251.4	256.6	257.7	266.1	276.9	288.8	307.9	336.6	384.2	455.6
60°	226.0	224.5	228.9	232.4	236.9	245.7	255.6	274.4	297.1	332.1	393.3
62.5°	202.4	201.6	204.9	208.3	212.0	220.1	228.4	242.8	260.7	290.3	338.8
65°	167.8	169.3	170.7	172.2	174.2	179.1	187.0	196.9	209.2	230.0	264.9
67.5°	131.9	133.4	133.8	136.9	141.1	144.2	149.0	157.8	166.4	183.9	203.8
70°	106.6	106.1	106.6	108.1	113.5	118.9	125.4	131.8	137.1	149.5	166.3
72.5°	91.6	90.7	92.0	92.3	94.9	96.4	100.5	106.5	113.5	121.9	133.9
75°	71.1	71.1	71.1	71.1	73.0	74.0	75.5	77.0	79.5	83.4	92.3
77.5°	52.5	52.6	53.3	53.8	54.2	54.8	55.7	57.1	58.1	60.1	64.0
80°	41.5	41.9	41.5	41.9	41.9	42.9	43.5	44.9	45.4	47.9	49.4
82.5°	31.2	30.9	31.2	31.7	31.7	32.7	32.8	33.8	33.9	35.3	36.8
85°	16.8	15.8	16.8	16.3	17.2	16.3	16.8	17.7	17.7	18.3	20.3
87.5°	7.2	7.9	7.1	7.4	7.4	7.7	7.6	7.5	8.2	7.7	7.8
90°	16.1	15.9	15.6	15.5	15.2	14.8	14.3	13.9	13.4	12.9	11.3
92.5°	17.8	17.7	17.5	17.4	17.2	16.8	16.0	15.3	14.5	13.8	12.6
95°	20.5	20.5	20.5	20.5	20.5	20.0	19.1	18.4	17.5	16.7	15.4
97.5°	22.1	22.1	21.9	21.8	21.7	21.1	20.2	19.2	18.3	17.3	25.9
100°	22.6	22.4	22.3	22.2	22.1	21.6	20.6	19.6	18.7	17.7	36.4
102.5°	23.0	22.8	22.6	22.3	22.1	23.6	26.5	29.4	32.4	35.3	55.7
105°	23.7	23.4	23.2	22.9	22.7	33.2	54.3	75.4	96.6	117.7	128.5
107.5°	74.3	90.2	106.1	122.1	138.1	153.7	169.3	184.7	200.3	215.7	214.1
110°	147.8	164.9	182.0	199.1	216.1	226.7	230.6	234.6	238.5	242.4	241.1



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	253.6	257.2	260.8	264.5	268.1	269.8	269.8	269.7	269.7	269.6	268.2
115°	316.1	315.7	315.2	314.6	314.1	313.4	312.2	310.9	309.8	308.6	307.5
117.5°	351.2	351.1	351.0	350.9	350.8	350.2	349.3	348.4	347.4	346.4	345.9
120°	375.2	375.2	375.2	375.2	375.2	374.8	373.8	372.9	371.9	370.9	370.6
122.5°	398.9	398.8	398.7	398.6	398.5	398.1	397.5	396.8	396.2	395.5	395.0
125°	432.3	432.0	431.8	431.5	431.3	431.0	430.7	430.6	430.3	430.1	429.6
127.5°	464.3	464.5	464.8	465.0	465.2	465.1	464.8	464.4	464.0	463.6	463.1
130°	484.9	485.1	485.4	485.6	485.9	485.7	485.2	484.7	484.3	483.8	483.3
132.5°	503.8	504.2	504.4	504.8	505.2	505.1	504.6	504.2	503.7	503.2	502.8
135°	532.7	533.1	533.5	533.9	534.1	534.1	533.9	533.5	533.1	532.7	532.3
137.5°	560.0	560.2	560.4	560.6	560.9	560.7	560.2	559.6	559.0	558.5	558.2
140°	576.3	576.6	576.7	577.0	577.2	577.1	576.6	576.2	575.7	575.2	574.9
142.5°	591.4	591.6	592.0	592.4	592.7	592.7	592.3	591.9	591.5	591.2	590.8
145°	614.4	614.4	614.4	614.4	614.4	614.3	614.1	613.9	613.6	613.4	613.1
147.5°	631.7	632.3	632.7	633.3	633.9	634.0	633.8	633.6	633.3	633.1	632.8
150°	644.6	644.9	645.3	645.6	646.0	646.0	645.8	645.5	645.4	645.1	644.9
152.5°	654.9	655.4	656.0	656.6	657.0	657.1	656.7	656.3	655.8	655.4	655.3
155°	669.3	670.1	670.7	671.5	672.1	672.2	671.7	671.0	670.4	669.9	669.7
157.5°	681.5	682.4	683.3	684.2	685.1	685.3	684.6	683.8	683.2	682.4	682.5
160°	689.2	690.0	690.9	691.7	692.5	692.6	691.8	691.2	690.4	689.8	689.8
162.5°	696.5	697.2	698.0	698.7	699.5	699.5	698.6	697.8	697.0	696.2	696.3
165°	705.3	706.2	707.0	707.8	708.7	708.6	707.7	706.7	705.8	704.7	704.9
167.5°	711.6	712.7	713.6	714.5	715.5	715.5	714.5	713.6	712.7	711.6	711.6
170°	715.5	716.5	717.5	718.4	719.3	719.3	718.4	717.5	716.5	715.5	715.5
172.5°	717.7	718.7	719.8	720.9	721.9	721.9	721.0	720.0	719.1	718.1	718.0
175°	720.9	721.9	722.8	723.8	724.7	724.8	724.0	723.1	722.3	721.4	721.3
177.5°	721.9	722.8	723.8	724.7	725.7	725.8	725.0	724.2	723.5	722.7	722.6
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1190.2	1189.0	1183.6	1177.2	1168.9	1163.4	1159.0	1156.7	1149.6	1140.9	1135.0
5°	1263.8	1249.0	1233.2	1213.9	1196.2	1177.9	1166.6	1153.2	1137.0	1118.7	1105.9
7.5°	1342.6	1313.5	1282.2	1250.0	1218.0	1189.5	1164.2	1142.6	1116.6	1090.4	1072.1
10°	1403.0	1360.5	1316.5	1271.7	1230.7	1192.2	1162.6	1133.5	1102.4	1072.3	1049.6
12.5°	1457.8	1401.9	1351.3	1296.2	1243.8	1197.8	1155.1	1120.9	1083.5	1051.4	1025.5
15°	1527.3	1470.1	1408.8	1324.9	1255.4	1197.1	1145.4	1100.4	1055.1	1015.6	990.4
17.5°	1592.2	1506.1	1423.9	1353.9	1263.5	1190.7	1127.5	1073.7	1024.0	982.1	951.1
20°	1619.1	1535.7	1446.3	1357.1	1268.2	1186.8	1113.2	1054.0	1002.2	954.9	926.2
22.5°	1635.2	1540.8	1446.7	1350.8	1256.4	1171.8	1099.1	1033.9	977.8	932.7	897.4
25°	1654.1	1541.6	1437.9	1343.2	1247.0	1155.2	1068.8	999.8	939.1	891.2	853.7
27.5°	1666.5	1534.2	1411.7	1306.4	1208.8	1117.4	1038.2	965.1	903.4	852.8	812.6
30°	1668.9	1528.2	1391.6	1277.6	1178.4	1094.5	1010.6	940.6	875.4	821.6	784.1
32.5°	1672.1	1513.6	1364.3	1243.2	1141.7	1058.6	982.6	915.7	848.9	796.0	757.7
35°	1659.1	1505.6	1323.0	1183.8	1082.1	1001.7	933.1	871.5	805.9	754.5	715.5
37.5°	1603.0	1473.5	1280.2	1116.9	1010.6	936.1	880.2	826.4	766.3	710.9	674.2
40°	1546.5	1441.9	1247.0	1076.3	965.3	888.7	838.4	794.5	736.2	684.5	645.0
42.5°	1462.4	1398.9	1215.4	1033.6	913.9	840.2	797.8	756.6	705.5	652.9	615.8
45°	1308.2	1316.5	1150.8	965.7	842.8	768.8	728.9	700.2	654.9	611.4	573.4
47.5°	1114.7	1193.2	1074.9	893.3	767.9	698.4	663.5	638.6	607.9	565.3	530.7
50°	988.4	1100.4	1014.1	844.8	721.0	651.9	617.4	597.1	570.4	536.9	503.8
52.5°	871.9	992.3	940.7	790.7	670.1	606.9	573.2	556.5	535.3	503.7	473.8
55°	711.1	833.0	821.1	709.1	593.6	536.9	511.2	492.5	478.2	454.5	430.8
57.5°	575.2	690.8	696.9	618.3	526.3	470.2	448.2	434.0	424.7	406.8	384.9
60°	489.6	595.6	616.3	557.1	478.2	428.9	407.1	395.8	388.3	374.1	357.3
62.5°	418.5	508.8	532.3	489.7	432.0	385.8	368.8	357.9	352.8	340.4	325.6
65°	320.3	395.3	417.9	394.3	364.2	327.2	313.4	304.0	299.5	292.7	281.7
67.5°	240.8	295.5	320.4	303.7	292.8	269.5	260.6	255.6	251.7	246.9	237.9
70°	193.4	233.9	259.6	255.1	246.3	233.9	227.5	224.0	220.1	216.1	208.2
72.5°	155.5	183.4	207.5	209.7	202.5	199.9	194.4	192.8	190.5	185.8	181.4
75°	103.1	122.3	139.1	145.5	148.5	151.0	148.5	148.1	147.5	143.6	141.1
77.5°	67.6	77.9	88.5	99.4	104.2	107.4	108.3	110.1	108.8	106.7	105.5
80°	51.8	54.3	61.6	71.1	78.4	81.4	83.4	84.4	83.9	83.4	81.4
82.5°	37.6	39.7	43.2	49.8	56.0	60.9	62.1	61.9	63.0	63.2	61.6
85°	20.3	20.7	21.7	22.7	26.1	31.6	33.1	34.0	35.1	35.1	32.0
87.5°	8.3	7.5	8.0	7.7	8.8	8.9	11.0	12.7	13.4	12.1	12.3
90°	9.8	8.2	6.7	5.3	4.1	2.9	1.7	0.6	1.7	2.9	4.1
92.5°	11.4	10.3	9.0	8.7	9.0	9.3	9.7	10.0	9.7	9.3	9.0
95°	14.0	12.7	11.4	13.2	18.1	23.0	27.9	32.8	27.9	23.0	18.1
97.5°	34.5	43.1	51.7	57.1	59.3	61.5	63.7	65.9	63.7	61.5	59.3
100°	55.0	73.6	92.3	100.4	98.0	95.7	93.2	90.9	93.2	95.7	98.0
102.5°	76.1	96.4	116.8	126.1	124.4	122.7	120.9	119.2	120.9	122.7	124.4
105°	139.2	150.0	160.7	165.4	164.1	162.9	161.6	160.2	161.6	162.9	164.1
107.5°	212.4	210.7	209.0	207.6	206.6	205.6	204.4	203.4	204.4	205.6	206.6
110°	239.8	238.5	237.2	236.0	235.1	234.1	233.2	232.2	233.2	234.1	235.1



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	266.9	265.6	264.3	263.2	262.3	261.5	260.6	259.8	260.6	261.5	262.3
115°	306.4	305.4	304.3	303.4	302.7	301.9	301.2	300.5	301.2	301.9	302.7
117.5°	345.3	344.8	344.2	343.5	342.6	341.8	340.8	340.0	340.8	341.8	342.6
120°	370.2	369.9	369.5	368.8	367.7	366.6	365.5	364.5	365.5	366.6	367.7
122.5°	394.5	394.1	393.6	392.9	392.1	391.2	390.3	389.5	390.3	391.2	392.1
125°	429.1	428.7	428.2	427.4	426.5	425.6	424.6	423.6	424.6	425.6	426.5
127.5°	462.5	461.8	461.3	460.5	459.6	458.6	457.7	456.8	457.7	458.6	459.6
130°	482.9	482.4	481.9	481.2	480.2	479.3	478.3	477.4	478.3	479.3	480.2
132.5°	502.4	502.0	501.6	501.0	500.0	499.1	498.1	497.2	498.1	499.1	500.0
135°	531.8	531.3	530.8	530.3	529.5	528.8	528.1	527.4	528.1	528.8	529.5
137.5°	557.9	557.6	557.4	556.8	555.9	555.0	554.1	553.2	554.1	555.0	555.9
140°	574.5	574.1	573.8	573.3	572.5	571.8	571.1	570.3	571.1	571.8	572.5
142.5°	590.4	590.0	589.7	589.2	588.4	587.8	587.0	586.3	587.0	587.8	588.4
145°	612.9	612.7	612.5	611.9	611.1	610.2	609.4	608.5	609.4	610.2	611.1
147.5°	632.5	632.4	632.1	631.7	631.1	630.7	630.1	629.5	630.1	630.7	631.1
150°	644.6	644.4	644.1	643.9	643.5	643.1	642.8	642.4	642.8	643.1	643.5
152.5°	655.2	655.0	654.9	654.7	654.5	654.3	654.2	654.0	654.2	654.3	654.5
155°	669.6	669.5	669.4	669.4	669.7	669.9	670.1	670.3	670.1	669.9	669.7
157.5°	682.7	682.8	682.9	683.0	683.0	683.0	683.1	683.1	683.1	683.0	683.0
160°	689.9	690.0	690.2	690.3	690.4	690.6	690.7	690.8	690.7	690.6	690.4
162.5°	696.4	696.5	696.6	696.8	697.2	697.5	697.8	698.1	697.8	697.5	697.2
165°	705.0	705.1	705.2	705.5	705.9	706.2	706.5	706.9	706.5	706.2	705.9
167.5°	711.6	711.6	711.6	711.9	712.4	712.8	713.3	713.8	713.3	712.8	712.4
170°	715.5	715.5	715.5	715.8	716.2	716.7	717.2	717.7	717.2	716.7	716.2
172.5°	717.9	717.8	717.7	717.9	718.5	719.1	719.7	720.3	719.7	719.1	718.5
175°	721.2	721.0	721.0	721.2	721.8	722.4	723.0	723.6	723.0	722.4	721.8
177.5°	722.6	722.5	722.4	722.6	723.0	723.5	724.0	724.4	724.0	723.5	723.0
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1133.0	1127.8	1124.4	1116.4	1111.3	1105.8	1100.2	1103.8	1103.4	1103.0	1103.0
5°	1095.0	1083.6	1073.3	1060.0	1051.6	1041.2	1033.3	1032.4	1034.3	1027.4	1023.4
7.5°	1057.3	1041.8	1027.1	1012.4	996.8	984.4	976.6	972.9	967.9	963.7	959.2
10°	1030.9	1012.6	998.2	980.1	963.3	948.5	939.1	932.6	929.2	925.8	919.4
12.5°	1003.6	985.7	967.5	946.9	930.9	913.7	906.7	899.5	892.9	889.0	880.2
15°	963.7	940.6	921.3	899.6	881.8	865.1	855.2	840.8	838.9	834.0	825.1
17.5°	923.8	898.6	872.0	856.0	835.9	818.5	803.4	798.6	784.5	779.2	771.5
20°	892.2	869.0	848.8	827.6	798.4	782.1	770.3	763.9	752.5	745.6	740.6
22.5°	865.0	841.4	817.9	793.2	769.2	750.9	742.3	732.3	726.1	716.4	711.1
25°	826.0	800.4	772.3	745.6	728.4	714.5	700.7	691.8	683.0	678.5	668.6
27.5°	780.9	754.0	727.7	707.6	686.4	672.7	660.2	652.2	641.6	634.1	628.7
30°	756.0	724.4	701.7	683.4	656.3	643.5	634.1	624.2	616.3	608.4	603.0
32.5°	727.2	698.3	676.8	654.2	633.4	619.4	607.3	598.6	591.8	584.4	578.9
35°	681.9	657.8	635.6	612.8	597.6	583.2	569.0	561.6	555.2	548.3	543.3
37.5°	641.1	618.5	597.4	575.9	556.9	545.3	533.8	528.1	519.4	514.8	509.7
40°	615.9	593.6	570.9	550.3	530.5	521.6	511.2	502.8	494.9	491.5	486.1
42.5°	588.2	566.0	546.9	524.5	508.4	496.3	486.7	477.6	471.6	466.7	463.5
45°	547.2	527.5	508.8	486.5	471.3	460.9	450.1	441.7	436.2	432.8	427.3
47.5°	507.5	487.8	468.7	449.3	434.5	422.7	411.9	406.0	398.8	394.5	391.0
50°	478.6	460.9	440.6	422.9	408.1	396.2	387.4	379.9	373.5	368.2	365.7
52.5°	452.2	433.3	415.8	399.3	383.6	370.2	362.1	354.3	349.5	343.3	340.4
55°	408.6	390.3	375.5	359.2	343.9	332.6	322.7	315.8	310.9	304.0	300.0
57.5°	367.6	351.3	333.6	319.4	303.7	294.1	285.9	276.5	270.5	265.1	261.3
60°	340.0	321.2	305.9	292.7	278.8	266.5	259.1	251.7	245.2	239.8	236.4
62.5°	311.2	294.8	280.3	265.8	253.2	242.4	233.8	227.6	222.0	218.5	215.1
65°	266.9	254.1	239.3	227.5	215.7	207.7	200.9	195.4	191.4	189.0	186.1
67.5°	226.3	213.9	201.0	189.3	181.4	175.4	170.9	166.2	164.2	161.1	159.1
70°	199.8	187.0	175.7	166.8	158.9	154.5	151.5	148.1	146.1	142.1	140.2
72.5°	171.1	161.7	153.5	146.3	140.0	135.9	132.1	127.9	124.8	120.4	118.5
75°	134.7	126.3	119.9	115.0	111.0	105.6	100.2	95.8	94.3	92.7	92.3
77.5°	99.8	94.4	89.8	85.7	80.8	76.8	75.6	74.6	74.3	73.5	73.5
80°	78.4	73.5	70.0	65.1	62.2	62.2	62.2	61.2	61.6	61.6	61.6
82.5°	58.3	53.8	51.9	50.1	49.6	50.0	50.0	50.1	49.9	50.6	50.2
85°	30.1	30.6	31.6	31.1	31.6	31.6	32.6	32.0	32.6	31.6	32.6
87.5°	12.2	13.6	14.3	15.0	15.6	15.6	16.1	16.2	16.7	16.8	16.9
90°	5.3	6.7	8.2	9.8	11.3	12.9	13.4	13.9	14.3	14.8	15.2
92.5°	8.7	9.0	10.3	11.4	12.6	13.8	14.5	15.3	16.0	16.8	17.2
95°	13.2	11.4	12.7	14.0	15.4	16.7	17.5	18.4	19.1	20.0	20.5
97.5°	57.1	51.7	43.1	34.5	25.9	17.3	18.3	19.2	20.2	21.1	21.7
100°	100.4	92.3	73.6	55.0	36.4	17.7	18.7	19.6	20.6	21.6	22.1
102.5°	126.1	116.8	96.4	76.1	55.7	35.3	32.4	29.4	26.5	23.6	22.1
105°	165.4	160.7	150.0	139.2	128.5	117.7	96.6	75.4	54.3	33.2	22.7
107.5°	207.6	209.0	210.7	212.4	214.1	215.7	200.3	184.7	169.3	153.7	138.1
110°	236.0	237.2	238.5	239.8	241.1	242.4	238.5	234.6	230.6	226.7	216.1



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	263.2	264.3	265.6	266.9	268.2	269.6	269.7	269.7	269.8	269.8	268.1
115°	303.4	304.3	305.4	306.4	307.5	308.6	309.8	310.9	312.2	313.4	314.1
117.5°	343.5	344.2	344.8	345.3	345.9	346.4	347.4	348.4	349.3	350.2	350.8
120°	368.8	369.5	369.9	370.2	370.6	370.9	371.9	372.9	373.8	374.8	375.2
122.5°	392.9	393.6	394.1	394.5	395.0	395.5	396.2	396.8	397.5	398.1	398.5
125°	427.4	428.2	428.7	429.1	429.6	430.1	430.3	430.6	430.7	431.0	431.3
127.5°	460.5	461.3	461.8	462.5	463.1	463.6	464.0	464.4	464.8	465.1	465.2
130°	481.2	481.9	482.4	482.9	483.3	483.8	484.3	484.7	485.2	485.7	485.9
132.5°	501.0	501.6	502.0	502.4	502.8	503.2	503.7	504.2	504.6	505.1	505.2
135°	530.3	530.8	531.3	531.8	532.3	532.7	533.1	533.5	533.9	534.1	534.1
137.5°	556.8	557.4	557.6	557.9	558.2	558.5	559.0	559.6	560.2	560.7	560.9
140°	573.3	573.8	574.1	574.5	574.9	575.2	575.7	576.2	576.6	577.1	577.2
142.5°	589.2	589.7	590.0	590.4	590.8	591.2	591.5	591.9	592.3	592.7	592.7
145°	611.9	612.5	612.7	612.9	613.1	613.4	613.6	613.9	614.1	614.3	614.4
147.5°	631.7	632.1	632.4	632.5	632.8	633.1	633.3	633.6	633.8	634.0	633.9
150°	643.9	644.1	644.4	644.6	644.9	645.1	645.4	645.5	645.8	646.0	646.0
152.5°	654.7	654.9	655.0	655.2	655.3	655.4	655.8	656.3	656.7	657.1	657.0
155°	669.4	669.4	669.5	669.6	669.7	669.9	670.4	671.0	671.7	672.2	672.1
157.5°	683.0	682.9	682.8	682.7	682.5	682.4	683.2	683.8	684.6	685.3	685.1
160°	690.3	690.2	690.0	689.9	689.8	689.8	690.4	691.2	691.8	692.6	692.5
162.5°	696.8	696.6	696.5	696.4	696.3	696.2	697.0	697.8	698.6	699.5	699.5
165°	705.5	705.2	705.1	705.0	704.9	704.7	705.8	706.7	707.7	708.6	708.7
167.5°	711.9	711.6	711.6	711.6	711.6	711.6	712.7	713.6	714.5	715.5	715.5
170°	715.8	715.5	715.5	715.5	715.5	715.5	716.5	717.5	718.4	719.3	719.3
172.5°	717.9	717.7	717.8	717.9	718.0	718.1	719.1	720.0	721.0	721.9	721.9
175°	721.2	721.0	721.0	721.2	721.3	721.4	722.3	723.1	724.0	724.8	724.7
177.5°	722.6	722.4	722.5	722.6	722.6	722.7	723.5	724.2	725.0	725.8	725.7
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1098.3	1097.9	1098.3	1096.6	1098.3	1097.9	1098.3	1103.0	1103.0	1103.4	1103.8
5°	1022.0	1021.4	1020.0	1015.6	1020.0	1021.4	1022.0	1023.4	1027.4	1034.3	1032.4
7.5°	955.4	954.7	950.4	950.5	950.4	954.7	955.4	959.2	963.7	967.9	972.9
10°	915.9	916.3	910.5	907.0	910.5	916.3	915.9	919.4	925.8	929.2	932.6
12.5°	877.6	875.3	870.5	866.8	870.5	875.3	877.6	880.2	889.0	892.9	899.5
15°	827.1	822.1	810.3	811.2	810.3	822.1	827.1	825.1	834.0	838.9	840.8
17.5°	767.5	763.9	763.6	756.8	763.6	763.9	767.5	771.5	779.2	784.5	798.6
20°	732.8	730.4	731.3	724.4	731.3	730.4	732.8	740.6	745.6	752.5	763.9
22.5°	705.6	703.1	699.0	696.8	699.0	703.1	705.6	711.1	716.4	726.1	732.3
25°	665.7	661.8	657.8	660.3	657.8	661.8	665.7	668.6	678.5	683.0	691.8
27.5°	625.8	622.8	618.9	618.4	618.9	622.8	625.8	628.7	634.1	641.6	652.2
30°	600.6	597.6	595.6	593.1	595.6	597.6	600.6	603.0	608.4	616.3	624.2
32.5°	574.9	574.3	570.7	570.2	570.7	574.3	574.9	578.9	584.4	591.8	598.6
35°	541.3	538.4	537.3	537.9	537.3	538.4	541.3	543.3	548.3	555.2	561.6
37.5°	509.4	505.5	503.7	502.0	503.7	505.5	509.4	509.7	514.8	519.4	528.1
40°	486.5	482.6	481.6	480.6	481.6	482.6	486.5	486.1	491.5	494.9	502.8
42.5°	460.9	459.3	458.7	456.9	458.7	459.3	460.9	463.5	466.7	471.6	477.6
45°	425.8	425.4	422.4	423.4	422.4	425.4	425.8	427.3	432.8	436.2	441.7
47.5°	389.0	386.8	384.7	386.1	384.7	386.8	389.0	391.0	394.5	398.8	406.0
50°	363.7	362.7	358.3	359.2	358.3	362.7	363.7	365.7	368.2	373.5	379.9
52.5°	338.5	334.7	333.0	332.4	333.0	334.7	338.5	340.4	343.3	349.5	354.3
55°	296.6	292.1	290.1	289.2	290.1	292.1	296.6	300.0	304.0	310.9	315.8
57.5°	255.5	254.3	252.8	253.8	252.8	254.3	255.5	261.3	265.1	270.5	276.5
60°	231.4	231.4	231.4	230.9	231.4	231.4	231.4	236.4	239.8	245.2	251.7
62.5°	212.9	211.7	211.3	212.0	211.3	211.7	212.9	215.1	218.5	222.0	227.6
65°	184.5	184.1	182.1	181.6	182.1	184.1	184.5	186.1	189.0	191.4	195.4
67.5°	157.8	156.0	155.4	154.8	155.4	156.0	157.8	159.1	161.1	164.2	166.2
70°	137.7	136.7	133.7	134.2	133.7	136.7	137.7	140.2	142.1	146.1	148.1
72.5°	115.9	115.0	114.4	113.7	114.4	115.0	115.9	118.5	120.4	124.8	127.9
75°	91.8	91.3	90.8	92.7	90.8	91.3	91.8	92.3	92.7	94.3	95.8
77.5°	73.5	73.5	73.8	73.0	73.8	73.5	73.5	73.5	73.5	74.3	74.6
80°	61.6	61.6	61.2	61.2	61.2	61.6	61.6	61.6	61.6	61.6	61.2
82.5°	49.5	49.9	50.1	49.4	50.1	49.9	49.5	50.2	50.6	49.9	50.1
85°	32.6	32.0	33.1	32.6	33.1	32.0	32.6	32.6	31.6	32.6	32.0
87.5°	17.7	17.0	17.0	17.4	17.0	17.0	17.7	16.9	16.8	16.7	16.2
90°	15.5	15.6	15.9	16.1	15.9	15.6	15.5	15.2	14.8	14.3	13.9
92.5°	17.4	17.5	17.7	17.8	17.7	17.5	17.4	17.2	16.8	16.0	15.3
95°	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.0	19.1	18.4
97.5°	21.8	21.9	22.1	22.1	22.1	21.9	21.8	21.7	21.1	20.2	19.2
100°	22.2	22.3	22.4	22.6	22.4	22.3	22.2	22.1	21.6	20.6	19.6
102.5°	22.3	22.6	22.8	23.0	22.8	22.6	22.3	22.1	23.6	26.5	29.4
105°	22.9	23.2	23.4	23.7	23.4	23.2	22.9	22.7	33.2	54.3	75.4
107.5°	122.1	106.1	90.2	74.3	90.2	106.1	122.1	138.1	153.7	169.3	184.7
110°	199.1	182.0	164.9	147.8	164.9	182.0	199.1	216.1	226.7	230.6	234.6



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	264.5	260.8	257.2	253.6	257.2	260.8	264.5	268.1	269.8	269.8	269.7
115°	314.6	315.2	315.7	316.1	315.7	315.2	314.6	314.1	313.4	312.2	310.9
117.5°	350.9	351.0	351.1	351.2	351.1	351.0	350.9	350.8	350.2	349.3	348.4
120°	375.2	375.2	375.2	375.2	375.2	375.2	375.2	375.2	374.8	373.8	372.9
122.5°	398.6	398.7	398.8	398.9	398.8	398.7	398.6	398.5	398.1	397.5	396.8
125°	431.5	431.8	432.0	432.3	432.0	431.8	431.5	431.3	431.0	430.7	430.6
127.5°	465.0	464.8	464.5	464.3	464.5	464.8	465.0	465.2	465.1	464.8	464.4
130°	485.6	485.4	485.1	484.9	485.1	485.4	485.6	485.9	485.7	485.2	484.7
132.5°	504.8	504.4	504.2	503.8	504.2	504.4	504.8	505.2	505.1	504.6	504.2
135°	533.9	533.5	533.1	532.7	533.1	533.5	533.9	534.1	534.1	533.9	533.5
137.5°	560.6	560.4	560.2	560.0	560.2	560.4	560.6	560.9	560.7	560.2	559.6
140°	577.0	576.7	576.6	576.3	576.6	576.7	577.0	577.2	577.1	576.6	576.2
142.5°	592.4	592.0	591.6	591.4	591.6	592.0	592.4	592.7	592.7	592.3	591.9
145°	614.4	614.4	614.4	614.4	614.4	614.4	614.4	614.4	614.3	614.1	613.9
147.5°	633.3	632.7	632.3	631.7	632.3	632.7	633.3	633.9	634.0	633.8	633.6
150°	645.6	645.3	644.9	644.6	644.9	645.3	645.6	646.0	646.0	645.8	645.5
152.5°	656.6	656.0	655.4	654.9	655.4	656.0	656.6	657.0	657.1	656.7	656.3
155°	671.5	670.7	670.1	669.3	670.1	670.7	671.5	672.1	672.2	671.7	671.0
157.5°	684.2	683.3	682.4	681.5	682.4	683.3	684.2	685.1	685.3	684.6	683.8
160°	691.7	690.9	690.0	689.2	690.0	690.9	691.7	692.5	692.6	691.8	691.2
162.5°	698.7	698.0	697.2	696.5	697.2	698.0	698.7	699.5	699.5	698.6	697.8
165°	707.8	707.0	706.2	705.3	706.2	707.0	707.8	708.7	708.6	707.7	706.7
167.5°	714.5	713.6	712.7	711.6	712.7	713.6	714.5	715.5	715.5	714.5	713.6
170°	718.4	717.5	716.5	715.5	716.5	717.5	718.4	719.3	719.3	718.4	717.5
172.5°	720.9	719.8	718.7	717.7	718.7	719.8	720.9	721.9	721.9	721.0	720.0
175°	723.8	722.8	721.9	720.9	721.9	722.8	723.8	724.7	724.8	724.0	723.1
177.5°	724.7	723.8	722.8	721.9	722.8	723.8	724.7	725.7	725.8	725.0	724.2
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1100.2	1105.8	1111.3	1116.4	1124.4	1127.8	1133.0	1135.0	1140.9	1149.6	1156.7
5°	1033.3	1041.2	1051.6	1060.0	1073.3	1083.6	1095.0	1105.9	1118.7	1137.0	1153.2
7.5°	976.6	984.4	996.8	1012.4	1027.1	1041.8	1057.3	1072.1	1090.4	1116.6	1142.6
10°	939.1	948.5	963.3	980.1	998.2	1012.6	1030.9	1049.6	1072.3	1102.4	1133.5
12.5°	906.7	913.7	930.9	946.9	967.5	985.7	1003.6	1025.5	1051.4	1083.5	1120.9
15°	855.2	865.1	881.8	899.6	921.3	940.6	963.7	990.4	1015.6	1055.1	1100.4
17.5°	803.4	818.5	835.9	856.0	872.0	898.6	923.8	951.1	982.1	1024.0	1073.7
20°	770.3	782.1	798.4	827.6	848.8	869.0	892.2	926.2	954.9	1002.2	1054.0
22.5°	742.3	750.9	769.2	793.2	817.9	841.4	865.0	897.4	932.7	977.8	1033.9
25°	700.7	714.5	728.4	745.6	772.3	800.4	826.0	853.7	891.2	939.1	999.8
27.5°	660.2	672.7	686.4	707.6	727.7	754.0	780.9	812.6	852.8	903.4	965.1
30°	634.1	643.5	656.3	683.4	701.7	724.4	756.0	784.1	821.6	875.4	940.6
32.5°	607.3	619.4	633.4	654.2	676.8	698.3	727.2	757.7	796.0	848.9	915.7
35°	569.0	583.2	597.6	612.8	635.6	657.8	681.9	715.5	754.5	805.9	871.5
37.5°	533.8	545.3	556.9	575.9	597.4	618.5	641.1	674.2	710.9	766.3	826.4
40°	511.2	521.6	530.5	550.3	570.9	593.6	615.9	645.0	684.5	736.2	794.5
42.5°	486.7	496.3	508.4	524.5	546.9	566.0	588.2	615.8	652.9	705.5	756.6
45°	450.1	460.9	471.3	486.5	508.8	527.5	547.2	573.4	611.4	654.9	700.2
47.5°	411.9	422.7	434.5	449.3	468.7	487.8	507.5	530.7	565.3	607.9	638.6
50°	387.4	396.2	408.1	422.9	440.6	460.9	478.6	503.8	536.9	570.4	597.1
52.5°	362.1	370.2	383.6	399.3	415.8	433.3	452.2	473.8	503.7	535.3	556.5
55°	322.7	332.6	343.9	359.2	375.5	390.3	408.6	430.8	454.5	478.2	492.5
57.5°	285.9	294.1	303.7	319.4	333.6	351.3	367.6	384.9	406.8	424.7	434.0
60°	259.1	266.5	278.8	292.7	305.9	321.2	340.0	357.3	374.1	388.3	395.8
62.5°	233.8	242.4	253.2	265.8	280.3	294.8	311.2	325.6	340.4	352.8	357.9
65°	200.9	207.7	215.7	227.5	239.3	254.1	266.9	281.7	292.7	299.5	304.0
67.5°	170.9	175.4	181.4	189.3	201.0	213.9	226.3	237.9	246.9	251.7	255.6
70°	151.5	154.5	158.9	166.8	175.7	187.0	199.8	208.2	216.1	220.1	224.0
72.5°	132.1	135.9	140.0	146.3	153.5	161.7	171.1	181.4	185.8	190.5	192.8
75°	100.2	105.6	111.0	115.0	119.9	126.3	134.7	141.1	143.6	147.5	148.1
77.5°	75.6	76.8	80.8	85.7	89.8	94.4	99.8	105.5	106.7	108.8	110.1
80°	62.2	62.2	62.2	65.1	70.0	73.5	78.4	81.4	83.4	83.9	84.4
82.5°	50.0	50.0	49.6	50.1	51.9	53.8	58.3	61.6	63.2	63.0	61.9
85°	32.6	31.6	31.6	31.1	31.6	30.6	30.1	32.0	35.1	35.1	34.0
87.5°	16.1	15.6	15.6	15.0	14.3	13.6	12.2	12.3	12.1	13.4	12.7
90°	13.4	12.9	11.3	9.8	8.2	6.7	5.3	4.1	2.9	1.7	0.6
92.5°	14.5	13.8	12.6	11.4	10.3	9.0	8.7	9.0	9.3	9.7	10.0
95°	17.5	16.7	15.4	14.0	12.7	11.4	13.2	18.1	23.0	27.9	32.8
97.5°	18.3	17.3	25.9	34.5	43.1	51.7	57.1	59.3	61.5	63.7	65.9
100°	18.7	17.7	36.4	55.0	73.6	92.3	100.4	98.0	95.7	93.2	90.9
102.5°	32.4	35.3	55.7	76.1	96.4	116.8	126.1	124.4	122.7	120.9	119.2
105°	96.6	117.7	128.5	139.2	150.0	160.7	165.4	164.1	162.9	161.6	160.2
107.5°	200.3	215.7	214.1	212.4	210.7	209.0	207.6	206.6	205.6	204.4	203.4
110°	238.5	242.4	241.1	239.8	238.5	237.2	236.0	235.1	234.1	233.2	232.2



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	269.7	269.6	268.2	266.9	265.6	264.3	263.2	262.3	261.5	260.6	259.8
115°	309.8	308.6	307.5	306.4	305.4	304.3	303.4	302.7	301.9	301.2	300.5
117.5°	347.4	346.4	345.9	345.3	344.8	344.2	343.5	342.6	341.8	340.8	340.0
120°	371.9	370.9	370.6	370.2	369.9	369.5	368.8	367.7	366.6	365.5	364.5
122.5°	396.2	395.5	395.0	394.5	394.1	393.6	392.9	392.1	391.2	390.3	389.5
125°	430.3	430.1	429.6	429.1	428.7	428.2	427.4	426.5	425.6	424.6	423.6
127.5°	464.0	463.6	463.1	462.5	461.8	461.3	460.5	459.6	458.6	457.7	456.8
130°	484.3	483.8	483.3	482.9	482.4	481.9	481.2	480.2	479.3	478.3	477.4
132.5°	503.7	503.2	502.8	502.4	502.0	501.6	501.0	500.0	499.1	498.1	497.2
135°	533.1	532.7	532.3	531.8	531.3	530.8	530.3	529.5	528.8	528.1	527.4
137.5°	559.0	558.5	558.2	557.9	557.6	557.4	556.8	555.9	555.0	554.1	553.2
140°	575.7	575.2	574.9	574.5	574.1	573.8	573.3	572.5	571.8	571.1	570.3
142.5°	591.5	591.2	590.8	590.4	590.0	589.7	589.2	588.4	587.8	587.0	586.3
145°	613.6	613.4	613.1	612.9	612.7	612.5	611.9	611.1	610.2	609.4	608.5
147.5°	633.3	633.1	632.8	632.5	632.4	632.1	631.7	631.1	630.7	630.1	629.5
150°	645.4	645.1	644.9	644.6	644.4	644.1	643.9	643.5	643.1	642.8	642.4
152.5°	655.8	655.4	655.3	655.2	655.0	654.9	654.7	654.5	654.3	654.2	654.0
155°	670.4	669.9	669.7	669.6	669.5	669.4	669.4	669.7	669.9	670.1	670.3
157.5°	683.2	682.4	682.5	682.7	682.8	682.9	683.0	683.0	683.0	683.1	683.1
160°	690.4	689.8	689.8	689.9	690.0	690.2	690.3	690.4	690.6	690.7	690.8
162.5°	697.0	696.2	696.3	696.4	696.5	696.6	696.8	697.2	697.5	697.8	698.1
165°	705.8	704.7	704.9	705.0	705.1	705.2	705.5	705.9	706.2	706.5	706.9
167.5°	712.7	711.6	711.6	711.6	711.6	711.6	711.9	712.4	712.8	713.3	713.8
170°	716.5	715.5	715.5	715.5	715.5	715.5	715.8	716.2	716.7	717.2	717.7
172.5°	719.1	718.1	718.0	717.9	717.8	717.7	717.9	718.5	719.1	719.7	720.3
175°	722.3	721.4	721.3	721.2	721.0	721.0	721.2	721.8	722.4	723.0	723.6
177.5°	723.5	722.7	722.6	722.6	722.5	722.4	722.6	723.0	723.5	724.0	724.4
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1159.0	1163.4	1168.9	1177.2	1183.6	1189.0	1190.2	1191.8	1195.8	1202.5	1207.6
5°	1166.6	1177.9	1196.2	1213.9	1233.2	1249.0	1263.8	1274.1	1284.0	1304.8	1321.5
7.5°	1164.2	1189.5	1218.0	1250.0	1282.2	1313.5	1342.6	1368.5	1394.3	1424.6	1459.0
10°	1162.6	1192.2	1230.7	1271.7	1316.5	1360.5	1403.0	1436.0	1474.5	1509.0	1552.9
12.5°	1155.1	1197.8	1243.8	1296.2	1351.3	1401.9	1457.8	1503.5	1547.6	1597.4	1648.5
15°	1145.4	1197.1	1255.4	1324.9	1408.8	1470.1	1527.3	1606.8	1661.0	1715.3	1788.3
17.5°	1127.5	1190.7	1263.5	1353.9	1423.9	1506.1	1592.2	1655.0	1728.2	1804.6	1870.8
20°	1113.2	1186.8	1268.2	1357.1	1446.3	1535.7	1619.1	1694.0	1769.6	1857.9	1912.2
22.5°	1099.1	1171.8	1256.4	1350.8	1446.7	1540.8	1635.2	1723.3	1808.3	1897.4	1966.7
25°	1068.8	1155.2	1247.0	1343.2	1437.9	1541.6	1654.1	1752.3	1857.4	1949.2	2014.9
27.5°	1038.2	1117.4	1208.8	1306.4	1411.7	1534.2	1666.5	1778.2	1883.5	1949.2	1969.8
30°	1010.6	1094.5	1178.4	1277.6	1391.6	1528.2	1668.9	1796.7	1883.1	1911.7	1890.5
32.5°	982.6	1058.6	1141.7	1243.2	1364.3	1513.6	1672.1	1785.6	1837.7	1815.8	1729.4
35°	933.1	1001.7	1082.1	1183.8	1323.0	1505.6	1659.1	1736.0	1723.2	1599.8	1437.0
37.5°	880.2	936.1	1010.6	1116.9	1280.2	1473.5	1603.0	1614.3	1503.3	1313.9	1125.8
40°	838.4	888.7	965.3	1076.3	1247.0	1441.9	1546.5	1500.6	1328.4	1117.7	960.8
42.5°	797.8	840.2	913.9	1033.6	1215.4	1398.9	1462.4	1362.4	1163.8	964.5	821.8
45°	728.9	768.8	842.8	965.7	1150.8	1316.5	1308.2	1134.4	935.7	775.2	656.8
47.5°	663.5	698.4	767.9	893.3	1074.9	1193.2	1114.7	929.9	761.2	632.5	548.1
50°	617.4	651.9	721.0	844.8	1014.1	1100.4	988.4	810.3	655.8	549.2	482.1
52.5°	573.2	606.9	670.1	790.7	940.7	992.3	871.9	706.8	578.1	486.1	428.4
55°	511.2	536.9	593.6	709.1	821.1	833.0	711.1	572.9	466.8	402.7	363.2
57.5°	448.2	470.2	526.3	618.3	696.9	690.8	575.2	455.6	384.2	336.6	307.9
60°	407.1	428.9	478.2	557.1	616.3	595.6	489.6	393.3	332.1	297.1	274.4
62.5°	368.8	385.8	432.0	489.7	532.3	508.8	418.5	338.8	290.3	260.7	242.8
65°	313.4	327.2	364.2	394.3	417.9	395.3	320.3	264.9	230.0	209.2	196.9
67.5°	260.6	269.5	292.8	303.7	320.4	295.5	240.8	203.8	183.9	166.4	157.8
70°	227.5	233.9	246.3	255.1	259.6	233.9	193.4	166.3	149.5	137.1	131.8
72.5°	194.4	199.9	202.5	209.7	207.5	183.4	155.5	133.9	121.9	113.5	106.5
75°	148.5	151.0	148.5	145.5	139.1	122.3	103.1	92.3	83.4	79.5	77.0
77.5°	108.3	107.4	104.2	99.4	88.5	77.9	67.6	64.0	60.1	58.1	57.1
80°	83.4	81.4	78.4	71.1	61.6	54.3	51.8	49.4	47.9	45.4	44.9
82.5°	62.1	60.9	56.0	49.8	43.2	39.7	37.6	36.8	35.3	33.9	33.8
85°	33.1	31.6	26.1	22.7	21.7	20.7	20.3	20.3	18.3	17.7	17.7
87.5°	11.0	8.9	8.8	7.7	8.0	7.5	8.3	7.8	7.7	8.2	7.5
90°	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4	13.9
92.5°	9.7	9.3	9.0	8.7	9.0	10.3	11.4	12.6	13.8	14.5	15.3
95°	27.9	23.0	18.1	13.2	11.4	12.7	14.0	15.4	16.7	17.5	18.4
97.5°	63.7	61.5	59.3	57.1	51.7	43.1	34.5	25.9	17.3	18.3	19.2
100°	93.2	95.7	98.0	100.4	92.3	73.6	55.0	36.4	17.7	18.7	19.6
102.5°	120.9	122.7	124.4	126.1	116.8	96.4	76.1	55.7	35.3	32.4	29.4
105°	161.6	162.9	164.1	165.4	160.7	150.0	139.2	128.5	117.7	96.6	75.4
107.5°	204.4	205.6	206.6	207.6	209.0	210.7	212.4	214.1	215.7	200.3	184.7
110°	233.2	234.1	235.1	236.0	237.2	238.5	239.8	241.1	242.4	238.5	234.6



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	260.6	261.5	262.3	263.2	264.3	265.6	266.9	268.2	269.6	269.7	269.7
115°	301.2	301.9	302.7	303.4	304.3	305.4	306.4	307.5	308.6	309.8	310.9
117.5°	340.8	341.8	342.6	343.5	344.2	344.8	345.3	345.9	346.4	347.4	348.4
120°	365.5	366.6	367.7	368.8	369.5	369.9	370.2	370.6	370.9	371.9	372.9
122.5°	390.3	391.2	392.1	392.9	393.6	394.1	394.5	395.0	395.5	396.2	396.8
125°	424.6	425.6	426.5	427.4	428.2	428.7	429.1	429.6	430.1	430.3	430.6
127.5°	457.7	458.6	459.6	460.5	461.3	461.8	462.5	463.1	463.6	464.0	464.4
130°	478.3	479.3	480.2	481.2	481.9	482.4	482.9	483.3	483.8	484.3	484.7
132.5°	498.1	499.1	500.0	501.0	501.6	502.0	502.4	502.8	503.2	503.7	504.2
135°	528.1	528.8	529.5	530.3	530.8	531.3	531.8	532.3	532.7	533.1	533.5
137.5°	554.1	555.0	555.9	556.8	557.4	557.6	557.9	558.2	558.5	559.0	559.6
140°	571.1	571.8	572.5	573.3	573.8	574.1	574.5	574.9	575.2	575.7	576.2
142.5°	587.0	587.8	588.4	589.2	589.7	590.0	590.4	590.8	591.2	591.5	591.9
145°	609.4	610.2	611.1	611.9	612.5	612.7	612.9	613.1	613.4	613.6	613.9
147.5°	630.1	630.7	631.1	631.7	632.1	632.4	632.5	632.8	633.1	633.3	633.6
150°	642.8	643.1	643.5	643.9	644.1	644.4	644.6	644.9	645.1	645.4	645.5
152.5°	654.2	654.3	654.5	654.7	654.9	655.0	655.2	655.3	655.4	655.8	656.3
155°	670.1	669.9	669.7	669.4	669.4	669.5	669.6	669.7	669.9	670.4	671.0
157.5°	683.1	683.0	683.0	683.0	682.9	682.8	682.7	682.5	682.4	683.2	683.8
160°	690.7	690.6	690.4	690.3	690.2	690.0	689.9	689.8	689.8	690.4	691.2
162.5°	697.8	697.5	697.2	696.8	696.6	696.5	696.4	696.3	696.2	697.0	697.8
165°	706.5	706.2	705.9	705.5	705.2	705.1	705.0	704.9	704.7	705.8	706.7
167.5°	713.3	712.8	712.4	711.9	711.6	711.6	711.6	711.6	711.6	712.7	713.6
170°	717.2	716.7	716.2	715.8	715.5	715.5	715.5	715.5	715.5	716.5	717.5
172.5°	719.7	719.1	718.5	717.9	717.7	717.8	717.9	718.0	718.1	719.1	720.0
175°	723.0	722.4	721.8	721.2	721.0	721.0	721.2	721.3	721.4	722.3	723.1
177.5°	724.0	723.5	723.0	722.6	722.4	722.5	722.6	722.6	722.7	723.5	724.2
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1215.9	1215.9	1217.5	1223.4	1224.2	1229.4	1227.8
5°	1336.3	1345.7	1349.2	1364.0	1372.8	1376.8	1368.9
7.5°	1483.6	1510.0	1522.6	1538.0	1551.8	1555.9	1545.1
10°	1590.9	1618.5	1641.8	1656.0	1669.4	1678.3	1689.6
12.5°	1694.8	1728.7	1750.8	1770.9	1784.7	1795.9	1797.8
15°	1807.6	1858.9	1897.9	1926.5	1940.8	1948.2	1945.2
17.5°	1921.4	1969.0	1996.7	2025.9	2045.7	2046.7	2047.3
20°	1985.7	2032.1	2064.2	2085.8	2108.1	2107.1	2112.0
22.5°	2028.7	2065.3	2089.8	2105.6	2113.3	2109.5	2110.4
25°	2048.9	2059.7	2055.3	2030.1	2023.7	2000.5	2004.5
27.5°	1945.0	1893.8	1840.6	1772.4	1718.4	1675.5	1677.6
30°	1804.1	1713.4	1609.7	1522.9	1444.9	1423.1	1376.8
32.5°	1607.1	1470.9	1349.5	1268.6	1201.6	1183.6	1143.1
35°	1273.2	1140.9	1016.1	941.0	911.4	870.0	869.5
37.5°	989.6	873.2	807.1	750.8	721.3	696.3	693.8
40°	832.5	741.7	691.8	651.4	622.3	603.5	599.1
42.5°	722.7	649.3	602.7	577.6	555.2	545.4	538.3
45°	590.2	540.8	508.3	485.6	475.2	467.8	463.8
47.5°	493.7	460.6	438.4	423.3	414.9	407.1	409.2
50°	441.2	414.1	397.8	383.4	377.0	371.6	372.1
52.5°	398.9	374.6	361.4	351.1	343.1	339.2	337.3
55°	338.6	323.2	309.9	302.5	298.0	292.7	291.2
57.5°	288.8	276.9	266.1	257.7	256.6	251.4	252.0
60°	255.6	245.7	236.9	232.4	228.9	224.5	226.0
62.5°	228.4	220.1	212.0	208.3	204.9	201.6	202.4
65°	187.0	179.1	174.2	172.2	170.7	169.3	167.8
67.5°	149.0	144.2	141.1	136.9	133.8	133.4	131.9
70°	125.4	118.9	113.5	108.1	106.6	106.1	106.6
72.5°	100.5	96.4	94.9	92.3	92.0	90.7	91.6
75°	75.5	74.0	73.0	71.1	71.1	71.1	71.1
77.5°	55.7	54.8	54.2	53.8	53.3	52.6	52.5
80°	43.5	42.9	41.9	41.9	41.5	41.9	41.5
82.5°	32.8	32.7	31.7	31.7	31.2	30.9	31.2
85°	16.8	16.3	17.2	16.3	16.8	15.8	16.8
87.5°	7.6	7.7	7.4	7.4	7.1	7.9	7.2
90°	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	16.0	16.8	17.2	17.4	17.5	17.7	17.8
95°	19.1	20.0	20.5	20.5	20.5	20.5	20.5
97.5°	20.2	21.1	21.7	21.8	21.9	22.1	22.1
100°	20.6	21.6	22.1	22.2	22.3	22.4	22.6
102.5°	26.5	23.6	22.1	22.3	22.6	22.8	23.0
105°	54.3	33.2	22.7	22.9	23.2	23.4	23.7
107.5°	169.3	153.7	138.1	122.1	106.1	90.2	74.3
110°	230.6	226.7	216.1	199.1	182.0	164.9	147.8



TEST NUMBER: P332306-830

CATALOG NUMBER: S123RDIP-S775D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	269.8	269.8	268.1	264.5	260.8	257.2	253.6
115°	312.2	313.4	314.1	314.6	315.2	315.7	316.1
117.5°	349.3	350.2	350.8	350.9	351.0	351.1	351.2
120°	373.8	374.8	375.2	375.2	375.2	375.2	375.2
122.5°	397.5	398.1	398.5	398.6	398.7	398.8	398.9
125°	430.7	431.0	431.3	431.5	431.8	432.0	432.3
127.5°	464.8	465.1	465.2	465.0	464.8	464.5	464.3
130°	485.2	485.7	485.9	485.6	485.4	485.1	484.9
132.5°	504.6	505.1	505.2	504.8	504.4	504.2	503.8
135°	533.9	534.1	534.1	533.9	533.5	533.1	532.7
137.5°	560.2	560.7	560.9	560.6	560.4	560.2	560.0
140°	576.6	577.1	577.2	577.0	576.7	576.6	576.3
142.5°	592.3	592.7	592.7	592.4	592.0	591.6	591.4
145°	614.1	614.3	614.4	614.4	614.4	614.4	614.4
147.5°	633.8	634.0	633.9	633.3	632.7	632.3	631.7
150°	645.8	646.0	646.0	645.6	645.3	644.9	644.6
152.5°	656.7	657.1	657.0	656.6	656.0	655.4	654.9
155°	671.7	672.2	672.1	671.5	670.7	670.1	669.3
157.5°	684.6	685.3	685.1	684.2	683.3	682.4	681.5
160°	691.8	692.6	692.5	691.7	690.9	690.0	689.2
162.5°	698.6	699.5	699.5	698.7	698.0	697.2	696.5
165°	707.7	708.6	708.7	707.8	707.0	706.2	705.3
167.5°	714.5	715.5	715.5	714.5	713.6	712.7	711.6
170°	718.4	719.3	719.3	718.4	717.5	716.5	715.5
172.5°	721.0	721.9	721.9	720.9	719.8	718.7	717.7
175°	724.0	724.8	724.7	723.8	722.8	721.9	720.9
177.5°	725.0	725.8	725.7	724.7	723.8	722.8	721.9
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6

(END OF REPORT)