

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331696-940

Luminaire Tested: **S122RDIP-S675D925U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331696-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S675D925U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5369.9 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331696-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331696-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	70	79	73	68	64	60	56	53	48	45	43	36	35	34	28
3	80	71	64	58	72	65	59	54	53	49	45	42	40	37	33	31	29	25
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21
5	67	56	48	43	61	51	45	40	43	38	34	34	31	28	27	24	22	19
6	62	50	43	37	56	46	39	35	38	33	30	31	27	25	24	22	20	17
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	20	18	16	13
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16239	16239	16239
5°	16302	16037	16126
10°	16179	15775	15641
15°	15992	15308	14867
20°	15735	14639	13904
25°	15471	13881	12975
30°	15105	13103	11779
35°	14747	12254	10730
40°	14389	11377	9516
45°	13967	10392	8416
50°	13536	9399	7340
55°	13095	8329	6303
60°	12581	7201	5231
65°	12000	6052	4768
70°	11301	4985	4381
75°	10449	4548	4086
80°	9224	4063	3719
85°	7243	3205	3205



TEST NUMBER: P331696-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	1.8
10°-20°	258.5	4.8
20°-30°	363.0	6.8
30°-40°	395.9	7.4
40°-50°	364.0	6.8
50°-60°	285.9	5.3
60°-70°	186.4	3.5
70°-80°	96.1	1.8
80°-90°	27.7	0.5
90°-100°	37.5	0.7
100°-110°	137.7	2.6
110°-120°	368.0	6.9
120°-130°	607.5	11.3
130°-140°	646.1	12.0
140°-150°	600.5	11.2
150°-160°	482.8	9.0
160°-170°	311.1	5.8
170°-180°	107.1	2.0
0°-30°	715.7	13.3
0°-40°	1111.6	20.7
0°-60°	1761.4	32.8
0°-90°	2071.6	38.6
90°-120°	543.2	10.1
90°-150°	2397.3	44.6
90°-180°	3298.0	61.4
0°-180°	5369.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1006	1001	990	997	995	95
15°	957	946	916	899	889	269
25°	868	838	779	743	728	399
35°	748	700	622	566	544	468
45°	612	549	455	393	369	472
55°	465	393	296	243	224	416
65°	314	240	158	129	125	311
75°	168	106	73	67	66	177
85°	39	21	17	17	17	46
90°	1	10	16	20	22	4
95°	53	28	32	36	35	65
105°	248	258	50	58	62	265
115°	468	482	502	143	67	461
125°	662	673	688	694	696	590
135°	819	832	840	847	846	633
145°	950	950	963	969	965	594
155°	1046	1040	1049	1053	1047	482
165°	1103	1098	1100	1105	1100	311
175°	1128	1123	1124	1129	1121	107
180°	1126	1126	1126	1126	1126	



TEST NUMBER: P331696-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1009.5	1008.7	1007.9	1007.1	1006.3	1005.0	1003.2	1001.4	999.7	997.9	999.5
5°	1005.8	1004.9	1003.9	1002.8	1001.8	1000.1	997.4	994.8	992.1	989.5	991.3
7.5°	995.5	994.3	993.0	991.8	990.5	988.3	985.3	982.2	979.1	976.1	976.5
10°	986.8	985.3	983.9	982.5	981.1	978.4	974.3	970.3	966.3	962.2	961.6
12.5°	975.8	974.1	972.3	970.6	968.8	965.5	960.3	955.1	949.9	944.7	943.6
15°	956.7	954.5	952.3	950.0	947.8	943.3	936.4	929.5	922.7	915.8	912.0
17.5°	933.3	929.9	926.5	923.0	919.6	913.6	904.7	895.9	887.1	878.2	873.7
20°	915.8	911.7	907.7	903.7	899.6	892.5	882.3	872.3	862.2	852.0	846.9
22.5°	896.8	892.3	887.8	883.2	878.7	870.8	859.3	847.9	836.5	825.1	818.6
25°	868.4	861.9	855.5	849.0	842.6	832.6	819.3	805.9	792.6	779.2	770.9
27.5°	834.2	827.2	820.1	813.1	806.0	795.0	780.0	764.9	749.8	734.8	725.1
30°	810.2	802.5	794.8	787.1	779.4	767.5	751.3	735.1	718.9	702.8	692.4
32.5°	786.8	777.8	768.9	759.9	750.9	738.2	721.7	705.2	688.7	672.2	660.4
35°	748.2	738.0	727.6	717.3	707.0	692.9	675.1	657.4	639.5	621.7	608.9
37.5°	709.7	698.3	687.0	675.6	664.3	649.2	630.3	611.3	592.3	573.3	559.3
40°	682.7	670.6	658.4	646.3	634.2	618.3	598.7	579.1	559.5	539.8	525.5
42.5°	655.1	642.3	629.5	616.7	604.0	587.4	567.1	546.9	526.6	506.3	491.4
45°	611.7	598.2	584.6	571.1	557.5	540.1	518.9	497.7	476.4	455.1	440.8
47.5°	569.4	555.1	540.7	526.4	512.0	493.9	472.0	450.0	428.1	406.2	391.9
50°	538.9	524.5	510.1	495.8	481.4	463.2	440.9	418.7	396.4	374.2	360.2
52.5°	509.1	494.0	479.0	464.0	449.0	430.6	408.8	387.1	365.3	343.6	330.1
55°	465.2	449.4	433.6	417.9	402.1	383.3	361.4	339.6	317.7	295.9	283.7
57.5°	420.2	404.0	387.8	371.7	355.4	336.9	315.8	294.9	273.8	252.9	241.7
60°	389.6	373.4	357.2	341.1	324.9	306.4	285.5	264.7	243.9	223.0	212.7
62.5°	359.7	343.6	327.3	311.2	295.0	277.0	257.2	237.3	217.4	197.5	187.7
65°	314.1	297.7	281.2	264.9	248.5	231.2	213.0	194.8	176.6	158.4	151.5
67.5°	270.0	253.7	237.5	221.2	204.9	188.6	172.2	155.9	139.5	123.1	119.9
70°	239.4	223.6	207.9	192.1	176.3	161.4	147.5	133.5	119.6	105.6	103.5
72.5°	210.3	195.1	180.0	164.9	149.7	136.6	125.4	114.1	103.0	91.8	90.1
75°	167.5	153.4	139.2	125.0	110.8	100.3	93.5	86.6	79.7	72.9	71.4
77.5°	125.5	113.0	100.6	88.2	75.8	67.9	64.6	61.3	58.0	54.7	53.8
80°	99.2	88.9	78.6	68.3	58.0	51.8	49.8	47.7	45.7	43.7	42.9
82.5°	75.2	67.1	59.1	51.0	43.0	38.3	36.9	35.5	34.2	32.8	32.3
85°	39.1	34.9	30.7	26.4	22.1	19.7	19.1	18.5	17.9	17.3	17.3
87.5°	11.8	10.9	10.0	9.1	8.2	7.9	8.2	8.5	8.8	9.1	9.1
90°	0.8	2.8	4.8	6.8	8.7	10.5	11.9	13.4	14.8	16.3	17.2
92.5°	16.4	16.2	16.1	15.9	15.7	16.0	16.8	17.5	18.2	18.9	19.4
95°	53.0	47.0	41.0	35.0	29.1	26.7	28.0	29.2	30.5	31.7	32.6
97.5°	105.0	88.2	71.4	54.6	37.7	30.8	33.7	36.6	39.6	42.5	43.2
100°	144.2	119.3	94.5	69.7	44.9	34.2	37.2	40.3	43.3	46.5	47.9
102.5°	187.2	181.9	176.6	171.4	166.1	150.7	124.9	99.2	73.5	47.7	49.6
105°	247.5	253.0	258.4	263.9	269.3	247.3	197.9	148.5	99.1	49.7	51.6
107.5°	316.5	320.8	325.2	329.6	334.0	306.6	247.3	188.1	128.8	69.6	67.5
110°	360.8	364.6	368.4	372.2	375.9	351.7	299.4	247.1	194.8	142.5	124.4



TEST NUMBER: P331696-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	402.4	405.8	409.2	412.6	415.9	411.2	398.2	385.3	372.4	359.4	293.5
115°	468.2	471.4	474.4	477.5	480.5	484.4	488.9	493.5	497.9	502.5	418.7
117.5°	527.1	530.5	534.0	537.4	540.8	544.1	547.2	550.4	553.5	556.5	536.3
120°	570.1	572.7	575.5	578.2	580.9	583.9	587.2	590.4	593.7	596.9	599.1
122.5°	606.5	609.4	612.2	615.1	618.0	621.2	624.7	628.3	631.9	635.4	636.7
125°	662.1	664.4	666.8	669.1	671.5	674.4	677.9	681.3	684.7	688.1	689.5
127.5°	712.4	715.1	717.6	720.2	722.8	725.4	728.0	730.6	733.2	735.8	737.5
130°	744.4	747.3	750.1	753.0	755.9	758.4	760.4	762.3	764.4	766.3	768.3
132.5°	776.9	779.4	781.9	784.3	786.8	789.0	791.0	793.0	795.0	796.9	798.7
135°	819.3	822.2	825.1	828.0	830.9	833.1	834.7	836.4	838.0	839.6	841.4
137.5°	862.1	864.2	866.2	868.2	870.2	872.2	874.0	875.8	877.7	879.6	881.3
140°	890.1	891.6	893.0	894.5	895.9	897.7	899.6	901.6	903.7	905.6	907.2
142.5°	913.6	914.9	916.2	917.5	918.8	920.6	922.8	925.1	927.5	929.7	931.2
145°	950.4	950.2	950.0	949.9	949.7	951.1	954.2	957.3	960.4	963.4	964.7
147.5°	982.5	981.8	981.1	980.4	979.7	980.9	983.9	987.0	990.1	993.1	994.0
150°	1003.4	1002.1	1000.8	999.5	998.3	999.1	1002.0	1004.9	1007.8	1010.7	1011.7
152.5°	1020.9	1019.5	1018.1	1016.7	1015.3	1015.9	1018.7	1021.5	1024.2	1027.0	1028.1
155°	1046.5	1044.9	1043.2	1041.6	1040.0	1040.3	1042.4	1044.6	1046.8	1048.9	1050.0
157.5°	1066.5	1065.1	1063.8	1062.4	1061.0	1061.1	1062.7	1064.2	1065.7	1067.2	1068.4
160°	1078.3	1077.2	1076.1	1075.0	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3	1079.3
162.5°	1088.7	1087.6	1086.5	1085.4	1084.3	1084.2	1085.2	1086.1	1087.1	1088.1	1089.2
165°	1102.7	1101.6	1100.5	1099.4	1098.3	1098.1	1098.6	1099.1	1099.7	1100.3	1101.5
167.5°	1113.1	1112.1	1111.0	1109.8	1108.8	1108.5	1109.0	1109.5	1110.0	1110.5	1111.8
170°	1119.0	1117.8	1116.8	1115.7	1114.6	1114.3	1114.6	1115.0	1115.4	1115.7	1117.0
172.5°	1122.8	1121.8	1120.7	1119.6	1118.6	1118.2	1118.6	1118.9	1119.3	1119.6	1120.9
175°	1127.9	1126.7	1125.4	1124.1	1122.8	1122.4	1122.8	1123.1	1123.5	1123.8	1125.2
177.5°	1128.7	1127.7	1126.8	1125.7	1124.7	1124.3	1124.4	1124.5	1124.7	1124.8	1125.9
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331696-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1001.1	1002.7	1004.3	1005.0	1004.7	1004.3	1004.1	1003.7
5°	993.1	995.0	996.8	997.4	996.8	996.1	995.6	995.0
7.5°	977.0	977.6	978.1	977.9	976.8	975.8	974.7	973.7
10°	961.0	960.4	959.7	958.9	957.6	956.4	955.2	954.0
12.5°	942.5	941.5	940.3	938.8	936.7	934.8	932.7	930.7
15°	908.1	904.2	900.4	897.4	895.5	893.4	891.4	889.4
17.5°	869.2	864.5	860.0	856.0	852.5	849.0	845.5	842.0
20°	842.0	836.9	831.8	827.1	822.6	818.1	813.7	809.2
22.5°	812.1	805.6	799.1	794.2	790.8	787.5	784.2	780.9
25°	762.6	754.3	746.0	740.4	737.4	734.3	731.3	728.3
27.5°	715.4	705.8	696.2	688.8	684.0	679.2	674.4	669.6
30°	682.2	671.8	661.5	653.6	648.1	642.7	637.2	631.8
32.5°	648.6	636.9	625.1	616.6	611.4	606.4	601.2	596.1
35°	596.3	583.5	570.8	562.1	557.7	553.2	548.8	544.4
37.5°	545.2	531.2	517.2	507.6	502.5	497.4	492.3	487.2
40°	511.0	496.7	482.3	472.5	467.3	462.0	456.7	451.5
42.5°	476.6	461.7	446.9	436.9	431.9	426.8	421.7	416.5
45°	426.4	412.1	397.7	388.1	383.3	378.4	373.5	368.6
47.5°	377.6	363.4	349.0	339.7	335.3	330.9	326.5	322.1
50°	346.3	332.3	318.3	309.2	305.0	300.7	296.5	292.2
52.5°	316.6	303.1	289.6	281.0	277.1	273.1	269.2	265.3
55°	271.6	259.4	247.3	239.3	235.5	231.6	227.7	223.9
57.5°	230.6	219.5	208.4	201.2	198.0	194.7	191.5	188.2
60°	202.4	192.1	181.7	175.0	171.7	168.5	165.2	162.0
62.5°	177.9	168.0	158.2	152.3	150.3	148.5	146.5	144.5
65°	144.6	137.8	130.9	127.2	126.5	125.9	125.3	124.8
67.5°	116.7	113.6	110.5	108.5	107.9	107.3	106.6	105.9
70°	101.6	99.5	97.5	96.1	95.2	94.4	93.6	92.8
72.5°	88.4	86.7	85.0	83.9	83.4	82.9	82.4	81.9
75°	70.0	68.6	67.1	66.3	66.2	66.0	65.7	65.5
77.5°	53.0	52.2	51.4	50.8	50.5	50.2	49.8	49.5
80°	42.1	41.3	40.5	40.0	40.0	40.0	40.0	40.0
82.5°	31.8	31.3	30.9	30.6	30.6	30.6	30.6	30.6
85°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	9.1	9.2	9.2	9.2	9.3	9.4	9.5	9.5
90°	18.1	19.0	19.9	20.5	20.9	21.2	21.7	22.0
92.5°	19.8	20.3	20.8	21.1	21.3	21.6	21.8	22.0
95°	33.5	34.5	35.4	35.8	35.6	35.4	35.2	35.0
97.5°	44.0	44.7	45.4	45.8	46.1	46.3	46.5	46.7
100°	49.3	50.7	52.3	53.1	53.5	53.9	54.2	54.6
102.5°	51.5	53.4	55.3	56.4	57.0	57.4	58.0	58.5
105°	53.7	55.6	57.6	59.0	59.7	60.5	61.2	61.9
107.5°	65.5	63.5	61.4	60.8	61.5	62.2	63.0	63.7
110°	106.3	88.2	70.1	61.4	62.2	62.9	63.6	64.4



TEST NUMBER: P331696-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	227.5	161.4	95.4	62.7	63.2	63.8	64.4	65.0
115°	334.9	251.1	167.3	118.9	105.8	92.8	79.8	66.8
117.5°	516.0	495.8	475.5	443.9	401.1	358.3	315.5	272.7
120°	601.3	603.5	605.6	594.5	570.1	545.6	521.2	496.8
122.5°	638.0	639.3	640.6	638.9	634.2	629.4	624.6	619.9
125°	690.7	692.0	693.2	694.1	694.6	695.2	695.8	696.3
127.5°	739.4	741.3	743.2	744.0	744.2	744.3	744.4	744.5
130°	770.3	772.3	774.3	775.3	775.1	774.8	774.6	774.5
132.5°	800.4	802.1	803.8	804.5	804.3	804.1	804.0	803.8
135°	843.3	845.1	846.9	847.6	847.2	846.9	846.5	846.1
137.5°	883.1	884.8	886.6	887.3	886.6	886.0	885.4	884.8
140°	908.8	910.5	912.1	912.5	911.6	910.7	909.8	908.8
142.5°	932.6	934.2	935.7	935.9	935.0	934.2	933.3	932.3
145°	966.0	967.2	968.5	968.7	967.8	966.9	966.0	965.1
147.5°	995.0	995.9	996.8	996.9	996.1	995.4	994.6	993.9
150°	1012.8	1014.0	1015.0	1015.1	1014.2	1013.3	1012.4	1011.5
152.5°	1029.1	1030.2	1031.3	1031.3	1030.0	1028.9	1027.7	1026.4
155°	1051.1	1052.2	1053.3	1053.1	1051.7	1050.2	1048.7	1047.3
157.5°	1069.6	1070.9	1072.1	1072.0	1070.6	1069.2	1067.7	1066.4
160°	1080.4	1081.6	1082.6	1082.5	1081.2	1080.0	1078.7	1077.5
162.5°	1090.5	1091.7	1093.0	1092.8	1091.3	1089.7	1088.2	1086.5
165°	1102.8	1104.0	1105.3	1105.3	1104.0	1102.8	1101.5	1100.3
167.5°	1113.0	1114.3	1115.6	1115.4	1113.7	1112.1	1110.5	1108.8
170°	1118.3	1119.5	1120.8	1120.6	1119.0	1117.3	1115.7	1114.1
172.5°	1122.1	1123.5	1124.7	1124.5	1122.8	1121.2	1119.6	1118.0
175°	1126.4	1127.7	1128.9	1128.6	1126.9	1125.1	1123.2	1121.4
177.5°	1126.9	1127.9	1128.9	1128.7	1127.5	1126.1	1124.8	1123.6
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5

(END OF REPORT)