

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331732-940

Luminaire Tested: **S122RDIP-S865D1080U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331732-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D1080U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6531.5 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331732-940

CATALOG NUMBER: S122RDIP-S865D1080U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331732-940

CATALOG NUMBER: S122RDIP-S865D1080U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41																				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35																				
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30																				
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26																				
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23																				
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	23	20																				
6	63	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18																				
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19	16																				
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14																				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13																				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21111	21111	21111
5°	21191	20846	20960
10°	21028	20505	20330
15°	20787	19896	19323
20°	20452	19029	18076
25°	20110	18045	16864
30°	19634	17031	15310
35°	19170	15930	13947
40°	18704	14790	12370
45°	18155	13511	10942
50°	17595	12215	9540
55°	17022	10826	8194
60°	16353	9361	6801
65°	15595	7866	6193
70°	14691	6477	5693
75°	13587	5908	5315
80°	11985	5281	4844
85°	9429	4168	4168



TEST NUMBER: P331732-940

CATALOG NUMBER: S122RDIP-S865D1080U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	1.9
10°-20°	336.0	5.1
20°-30°	471.9	7.2
30°-40°	514.6	7.9
40°-50°	473.1	7.2
50°-60°	371.6	5.7
60°-70°	242.3	3.7
70°-80°	124.9	1.9
80°-90°	35.6	0.5
90°-100°	43.7	0.7
100°-110°	160.2	2.5
110°-120°	428.4	6.6
120°-130°	707.1	10.8
130°-140°	752.0	11.5
140°-150°	699.0	10.7
150°-160°	562.0	8.6
160°-170°	362.1	5.5
170°-180°	124.6	1.9
0°-30°	930.3	14.2
0°-40°	1444.9	22.1
0°-60°	2289.6	35.1
0°-90°	2692.4	41.2
90°-120°	632.3	9.7
90°-150°	2790.4	42.7
90°-180°	3839.0	58.8
0°-180°	6531.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1308	1301	1286	1296	1293	124
15°	1244	1229	1190	1168	1156	350
25°	1129	1089	1013	966	947	519
35°	973	910	808	736	708	608
45°	795	713	592	511	479	614
55°	605	510	385	316	291	540
65°	408	312	206	168	162	405
75°	218	137	95	87	85	230
85°	51	27	22	22	22	60
90°	1	11	19	24	26	5
95°	62	32	37	41	41	75
105°	288	301	58	68	72	308
115°	545	562	585	167	78	537
125°	771	783	801	807	810	687
135°	954	968	977	986	985	736
145°	1106	1106	1121	1127	1123	692
155°	1218	1211	1221	1226	1219	561
165°	1284	1278	1281	1287	1281	362
175°	1313	1307	1308	1314	1305	125
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P331732-940

CATALOG NUMBER: S122RDIP-S865D1080U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1312.2	1311.2	1310.1	1309.0	1308.1	1306.4	1304.0	1301.7	1299.4	1297.1	1299.2
5°	1307.5	1306.2	1304.8	1303.5	1302.3	1299.8	1296.5	1293.1	1289.6	1286.2	1288.5
7.5°	1294.0	1292.4	1290.8	1289.1	1287.5	1284.7	1280.7	1276.7	1272.6	1268.6	1269.4
10°	1282.6	1280.8	1279.0	1277.1	1275.2	1271.8	1266.5	1261.2	1256.0	1250.7	1249.9
12.5°	1268.5	1266.1	1263.9	1261.7	1259.4	1254.9	1248.1	1241.4	1234.7	1228.0	1226.5
15°	1243.6	1240.7	1237.8	1234.9	1232.0	1226.1	1217.2	1208.3	1199.3	1190.3	1185.4
17.5°	1213.1	1208.6	1204.3	1199.8	1195.4	1187.5	1176.0	1164.5	1153.1	1141.6	1135.7
20°	1190.3	1185.1	1179.8	1174.6	1169.3	1160.1	1146.9	1133.8	1120.7	1107.5	1100.9
22.5°	1165.7	1159.8	1154.0	1148.1	1142.2	1131.8	1117.0	1102.2	1087.4	1072.5	1064.0
25°	1128.8	1120.4	1112.0	1103.6	1095.2	1082.3	1064.9	1047.6	1030.2	1012.9	1002.1
27.5°	1084.3	1075.1	1066.0	1056.9	1047.8	1033.4	1013.8	994.3	974.6	955.1	942.5
30°	1053.1	1043.1	1033.1	1023.1	1013.2	997.6	976.6	955.6	934.5	913.5	900.1
32.5°	1022.8	1011.1	999.4	987.7	976.1	959.6	938.1	916.6	895.2	873.7	858.4
35°	972.6	959.2	945.8	932.4	919.0	900.7	877.5	854.4	831.3	808.2	791.6
37.5°	922.5	907.8	893.0	878.2	863.5	843.8	819.2	794.5	769.9	745.2	726.9
40°	887.4	871.6	855.9	840.1	824.3	803.7	778.2	752.7	727.2	701.7	683.0
42.5°	851.5	834.8	818.2	801.6	785.0	763.5	737.2	710.8	684.5	658.1	638.8
45°	795.1	777.5	759.9	742.3	724.7	702.0	674.5	646.8	619.2	591.7	572.9
47.5°	740.2	721.6	702.9	684.2	665.6	641.9	613.5	585.0	556.4	528.0	509.4
50°	700.5	681.8	663.2	644.4	625.8	602.0	573.1	544.1	515.2	486.3	468.1
52.5°	661.6	642.1	622.7	603.2	583.6	559.7	531.5	503.1	474.8	446.6	429.0
55°	604.7	584.2	563.7	543.1	522.6	498.1	469.8	441.3	413.0	384.6	368.8
57.5°	546.2	525.1	504.1	483.0	462.1	437.9	410.5	383.3	356.0	328.7	314.2
60°	506.4	485.4	464.4	443.4	422.3	398.2	371.1	344.0	317.0	289.9	276.5
62.5°	467.6	446.6	425.5	404.5	383.4	360.1	334.2	308.4	282.6	256.7	244.0
65°	408.2	386.9	365.6	344.3	323.1	300.5	276.9	253.2	229.5	205.9	197.0
67.5°	351.0	329.8	308.7	287.5	266.4	245.1	223.9	202.6	181.3	160.0	155.9
70°	311.2	290.7	270.2	249.7	229.2	209.8	191.7	173.5	155.4	137.2	134.6
72.5°	273.3	253.7	234.0	214.4	194.7	177.5	163.0	148.4	133.8	119.3	117.1
75°	217.8	199.3	180.9	162.5	144.1	130.5	121.5	112.5	103.6	94.7	92.8
77.5°	163.1	146.9	130.7	114.6	98.4	88.3	83.9	79.6	75.3	71.0	69.9
80°	128.9	115.6	102.2	88.7	75.3	67.3	64.6	62.1	59.4	56.8	55.7
82.5°	97.7	87.3	76.8	66.3	55.9	49.8	48.0	46.2	44.4	42.6	42.0
85°	50.9	45.4	39.9	34.3	28.8	25.7	24.9	24.1	23.3	22.5	22.5
87.5°	15.3	14.1	12.9	11.7	10.4	10.0	10.3	10.7	11.1	11.3	11.3
90°	1.0	3.3	5.6	7.9	10.3	12.2	13.9	15.6	17.3	19.0	20.0
92.5°	19.2	18.9	18.7	18.5	18.3	18.6	19.4	20.3	21.1	22.0	22.6
95°	61.6	54.7	47.7	40.8	33.8	31.0	32.5	34.1	35.5	37.0	38.0
97.5°	122.3	102.7	83.1	63.5	44.0	35.8	39.2	42.6	46.1	49.5	50.3
100°	167.8	138.9	110.0	81.2	52.3	39.7	43.2	46.9	50.5	54.0	55.7
102.5°	217.8	211.7	205.6	199.5	193.4	175.4	145.4	115.5	85.5	55.6	57.8
105°	288.2	294.5	300.8	307.1	313.4	287.8	230.3	172.8	115.3	57.8	60.1
107.5°	368.4	373.4	378.5	383.6	388.8	356.9	287.8	218.9	149.9	81.0	78.6
110°	419.9	424.4	428.8	433.2	437.7	409.4	348.5	287.7	226.8	165.9	144.8



TEST NUMBER: P331732-940

CATALOG NUMBER: S122RDIP-S865D1080U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	468.5	472.4	476.3	480.2	484.1	478.6	463.5	448.5	433.5	418.4	341.6
115°	545.1	548.7	552.2	555.8	559.4	563.8	569.1	574.4	579.6	584.9	487.3
117.5°	613.5	617.5	621.5	625.5	629.5	633.3	636.9	640.6	644.2	647.8	624.2
120°	663.5	666.7	669.9	673.1	676.2	679.7	683.5	687.2	691.1	694.8	697.3
122.5°	706.1	709.4	712.7	716.0	719.3	723.1	727.2	731.3	735.5	739.6	741.1
125°	770.7	773.4	776.1	778.9	781.6	785.0	789.0	793.0	797.0	801.0	802.5
127.5°	829.3	832.3	835.4	838.4	841.4	844.4	847.4	850.3	853.4	856.4	858.5
130°	866.4	869.8	873.2	876.6	879.9	882.7	885.0	887.3	889.7	892.0	894.3
132.5°	904.3	907.2	910.1	912.9	915.8	918.4	920.7	923.0	925.3	927.6	929.6
135°	953.6	957.0	960.4	963.8	967.1	969.7	971.6	973.5	975.4	977.3	979.5
137.5°	1003.4	1005.8	1008.2	1010.6	1012.9	1015.1	1017.4	1019.5	1021.6	1023.8	1025.8
140°	1036.1	1037.8	1039.5	1041.2	1042.9	1044.8	1047.1	1049.5	1051.8	1054.1	1056.0
142.5°	1063.4	1064.9	1066.4	1067.9	1069.4	1071.6	1074.2	1076.8	1079.5	1082.2	1083.9
145°	1106.3	1106.0	1105.8	1105.6	1105.4	1107.1	1110.6	1114.2	1117.8	1121.4	1122.8
147.5°	1143.6	1142.8	1142.0	1141.2	1140.4	1141.7	1145.3	1148.8	1152.4	1155.9	1157.0
150°	1167.9	1166.4	1164.9	1163.4	1162.0	1162.9	1166.3	1169.7	1173.0	1176.3	1177.7
152.5°	1188.3	1186.7	1185.0	1183.4	1181.8	1182.5	1185.7	1188.9	1192.1	1195.3	1196.6
155°	1218.1	1216.2	1214.3	1212.4	1210.5	1210.9	1213.4	1215.8	1218.4	1220.9	1222.2
157.5°	1241.4	1239.8	1238.2	1236.6	1235.0	1235.1	1236.9	1238.6	1240.4	1242.2	1243.6
160°	1255.1	1253.8	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1256.3
162.5°	1267.2	1266.0	1264.6	1263.4	1262.1	1262.0	1263.1	1264.3	1265.3	1266.4	1267.8
165°	1283.5	1282.2	1280.9	1279.7	1278.4	1278.1	1278.7	1279.4	1280.1	1280.7	1282.1
167.5°	1295.7	1294.4	1293.1	1291.8	1290.6	1290.2	1290.8	1291.4	1292.0	1292.6	1294.1
170°	1302.4	1301.2	1299.9	1298.7	1297.4	1297.0	1297.4	1297.8	1298.2	1298.7	1300.1
172.5°	1307.0	1305.7	1304.5	1303.2	1302.0	1301.5	1302.0	1302.3	1302.8	1303.2	1304.7
175°	1312.9	1311.4	1309.9	1308.5	1307.0	1306.4	1306.9	1307.3	1307.7	1308.1	1309.7
177.5°	1313.8	1312.7	1311.4	1310.3	1309.1	1308.6	1308.8	1308.9	1309.1	1309.3	1310.5
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331732-940

CATALOG NUMBER: S122RDIP-S865D1080U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1301.3	1303.4	1305.5	1306.4	1305.9	1305.5	1305.1	1304.7
5°	1290.9	1293.2	1295.7	1296.5	1295.7	1294.9	1294.1	1293.2
7.5°	1270.1	1270.7	1271.4	1271.0	1269.7	1268.4	1266.9	1265.6
10°	1249.1	1248.3	1247.5	1246.3	1244.7	1243.2	1241.6	1240.0
12.5°	1225.1	1223.7	1222.3	1220.3	1217.6	1215.0	1212.4	1209.8
15°	1180.4	1175.4	1170.4	1166.5	1164.0	1161.3	1158.7	1156.0
17.5°	1129.7	1123.7	1117.8	1112.6	1108.0	1103.6	1099.0	1094.5
20°	1094.4	1087.8	1081.2	1075.0	1069.3	1063.5	1057.7	1052.0
22.5°	1055.6	1047.1	1038.7	1032.2	1028.0	1023.6	1019.3	1015.0
25°	991.3	980.5	969.7	962.3	958.4	954.5	950.6	946.6
27.5°	930.0	917.4	904.8	895.5	889.2	882.9	876.6	870.4
30°	886.6	873.3	859.8	849.5	842.5	835.4	828.3	821.2
32.5°	843.1	827.8	812.5	801.5	794.9	788.2	781.5	774.8
35°	775.0	758.5	741.9	730.8	725.0	719.2	713.4	707.6
37.5°	708.7	690.5	672.3	659.8	653.2	646.5	639.9	633.3
40°	664.3	645.7	627.0	614.2	607.4	600.6	593.7	586.9
42.5°	619.6	600.2	580.9	567.9	561.3	554.7	548.0	541.4
45°	554.3	535.7	516.9	504.4	498.1	491.9	485.5	479.2
47.5°	490.8	472.3	453.7	441.6	435.9	430.1	424.4	418.7
50°	450.0	431.9	413.8	401.9	396.4	390.8	385.3	379.8
52.5°	411.5	394.0	376.5	365.2	360.1	355.0	349.9	344.8
55°	353.0	337.2	321.5	311.0	306.0	301.0	296.0	291.1
57.5°	299.8	285.3	270.9	261.5	257.3	253.1	248.9	244.7
60°	263.1	249.7	236.2	227.5	223.2	219.0	214.8	210.6
62.5°	231.2	218.5	205.6	198.0	195.5	193.0	190.4	187.9
65°	188.0	179.1	170.1	165.2	164.4	163.7	162.9	162.1
67.5°	151.8	147.7	143.6	141.1	140.3	139.4	138.6	137.8
70°	132.0	129.4	126.7	124.9	123.9	122.8	121.7	120.6
72.5°	114.9	112.6	110.4	109.1	108.3	107.7	107.1	106.5
75°	91.0	89.2	87.3	86.2	86.0	85.7	85.4	85.2
77.5°	68.9	67.9	66.8	66.1	65.6	65.2	64.8	64.4
80°	54.7	53.7	52.6	52.1	52.1	52.1	52.1	52.1
82.5°	41.4	40.7	40.0	39.8	39.8	39.8	39.8	39.8
85°	22.5	22.5	22.5	22.5	22.5	22.5	22.5	22.5
87.5°	11.3	11.3	11.3	11.4	11.5	11.6	11.7	11.8
90°	21.0	22.1	23.2	23.9	24.3	24.8	25.1	25.6
92.5°	23.1	23.6	24.2	24.6	24.9	25.1	25.3	25.6
95°	39.1	40.1	41.2	41.6	41.4	41.2	40.9	40.8
97.5°	51.2	52.0	52.9	53.4	53.7	53.9	54.1	54.4
100°	57.4	59.1	60.8	61.8	62.2	62.7	63.1	63.5
102.5°	59.9	62.2	64.3	65.7	66.3	66.9	67.5	68.0
105°	62.4	64.7	67.1	68.7	69.6	70.4	71.2	72.1
107.5°	76.2	73.8	71.5	70.8	71.6	72.4	73.3	74.1
110°	123.8	102.7	81.6	71.5	72.3	73.2	74.0	74.9



TEST NUMBER: P331732-940

CATALOG NUMBER: S122RDIP-S865D1080U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	264.7	187.9	111.0	72.9	73.7	74.3	75.0	75.6
115°	389.8	292.3	194.7	138.4	123.2	108.1	92.9	77.8
117.5°	600.7	577.0	553.5	516.7	466.9	417.1	367.2	317.4
120°	699.9	702.4	705.0	692.0	663.5	635.1	606.6	578.3
122.5°	742.6	744.1	745.6	743.6	738.2	732.6	727.1	721.6
125°	804.0	805.4	806.9	808.0	808.6	809.2	809.9	810.5
127.5°	860.7	862.8	865.0	866.1	866.2	866.4	866.5	866.6
130°	896.6	898.9	901.3	902.3	902.1	901.9	901.7	901.5
132.5°	931.6	933.6	935.6	936.5	936.2	936.0	935.9	935.6
135°	981.5	983.6	985.7	986.6	986.1	985.7	985.3	984.9
137.5°	1027.9	1029.9	1032.0	1032.7	1032.0	1031.3	1030.6	1029.8
140°	1057.9	1059.8	1061.7	1062.1	1061.0	1060.0	1058.9	1057.9
142.5°	1085.6	1087.4	1089.0	1089.4	1088.3	1087.3	1086.3	1085.2
145°	1124.4	1125.8	1127.3	1127.5	1126.5	1125.4	1124.4	1123.3
147.5°	1158.1	1159.2	1160.3	1160.4	1159.5	1158.6	1157.7	1156.8
150°	1178.9	1180.2	1181.4	1181.5	1180.4	1179.5	1178.4	1177.3
152.5°	1197.8	1199.2	1200.4	1200.3	1198.9	1197.6	1196.1	1194.8
155°	1223.4	1224.8	1226.0	1225.7	1224.1	1222.4	1220.8	1219.1
157.5°	1245.0	1246.4	1247.9	1247.8	1246.2	1244.5	1242.9	1241.2
160°	1257.6	1258.8	1260.1	1260.0	1258.6	1257.0	1255.6	1254.1
162.5°	1269.3	1270.7	1272.2	1271.9	1270.2	1268.4	1266.5	1264.7
165°	1283.6	1285.0	1286.6	1286.6	1285.0	1283.6	1282.1	1280.7
167.5°	1295.6	1297.0	1298.5	1298.2	1296.4	1294.5	1292.6	1290.7
170°	1301.6	1303.1	1304.6	1304.3	1302.4	1300.6	1298.7	1296.7
172.5°	1306.2	1307.6	1309.1	1308.9	1307.0	1305.1	1303.2	1301.3
175°	1311.1	1312.6	1314.0	1313.8	1311.6	1309.5	1307.4	1305.3
177.5°	1311.6	1312.8	1314.0	1313.8	1312.3	1310.8	1309.3	1307.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0

(END OF REPORT)