

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332034-930

Luminaire Tested: **S123DIP-S1000D1025U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332034-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D1025U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6231.6 lumens  
Efficiency: N/A  
Efficacy: 103.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332034-930

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332034-930

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54				
1	99	94	90	87	91	87	84	81	75	72	70	63	62	60	53	51	50	45				
2	90	82	76	71	83	76	71	66	66	62	58	56	53	50	46	44	42	38				
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36	32				
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24				
6	63	51	43	37	59	48	40	35	41	36	31	36	31	27	30	26	24	21				
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19				
8	54	42	34	29	50	39	32	27	34	29	24	30	25	22	25	22	19	17				
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15				
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332034-930

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.6	2.0
10°-20°	343.3	5.5
20°-30°	507.0	8.1
30°-40°	592.3	9.5
40°-50°	595.5	9.6
50°-60°	523.1	8.4
60°-70°	389.7	6.3
70°-80°	222.0	3.6
80°-90°	66.8	1.1
90°-100°	67.5	1.1
100°-110°	202.0	3.2
110°-120°	343.6	5.5
120°-130°	451.9	7.3
130°-140°	508.0	8.2
140°-150°	499.3	8.0
150°-160°	420.4	6.7
160°-170°	279.8	4.5
170°-180°	98.0	1.6
0°-30°	971.9	15.6
0°-40°	1564.1	25.1
0°-60°	2682.6	43.0
0°-90°	3361.1	53.9
90°-120°	613.1	9.8
90°-150°	2072.3	33.3
90°-180°	2870.0	46.1
0°-180°	6231.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	1	9	20	23	24	6
95°	48	54	60	63	64	54
105°	183	185	192	192	194	196
115°	346	348	347	347	347	342
125°	506	508	507	504	500	451
135°	657	661	661	658	656	506
145°	797	798	801	800	797	497
155°	912	912	913	916	911	420
165°	994	991	991	996	990	280
175°	1034	1030	1030	1035	1030	98
180°	1036	1036	1036	1036	1036	



TEST NUMBER: P332034-930

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.2	23.0	22.7	22.6	22.3	22.3	22.6	22.9	23.2	23.4	23.4
90°	0.8	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2
92.5°	19.7	21.0	22.2	23.4	24.6	25.9	27.2	28.5	29.9	31.2	31.8
95°	48.0	49.2	50.5	51.9	53.1	54.5	55.8	57.3	58.8	60.3	61.0
97.5°	85.3	86.3	87.2	88.1	89.0	90.0	91.1	92.1	93.2	94.2	95.1
100°	110.7	111.8	112.8	113.9	115.0	116.0	116.9	117.8	118.7	119.6	120.2
102.5°	140.0	140.6	141.3	141.9	142.6	143.5	144.7	145.9	147.1	148.3	148.8
105°	183.1	183.4	183.8	184.2	184.6	185.6	187.2	188.8	190.5	192.1	192.1
107.5°	233.3	233.5	233.7	233.9	234.2	234.6	235.2	235.9	236.5	237.2	237.7
110°	264.5	264.9	265.2	265.5	266.0	266.3	266.7	267.0	267.4	267.7	268.5



TEST NUMBER: P332034-930

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	297.0	297.3	297.5	297.7	297.9	298.1	298.2	298.2	298.3	298.3	299.2
115°	345.8	346.4	347.0	347.5	348.1	348.1	347.8	347.4	347.1	346.7	346.9
117.5°	395.0	395.4	395.7	396.2	396.5	396.4	396.0	395.5	395.0	394.5	394.5
120°	425.7	426.7	427.8	428.9	430.0	430.1	429.2	428.3	427.4	426.5	426.2
122.5°	457.5	458.4	459.1	459.9	460.7	460.9	460.4	459.9	459.5	459.0	458.5
125°	506.2	506.8	507.3	507.8	508.3	508.5	508.1	507.8	507.4	507.0	506.3
127.5°	551.1	552.3	553.4	554.6	555.8	556.1	555.7	555.4	555.0	554.6	553.5
130°	581.1	582.5	584.0	585.4	586.9	587.3	586.8	586.2	585.7	585.1	584.4
132.5°	611.1	612.5	613.9	615.4	616.9	617.3	616.9	616.5	616.1	615.7	614.9
135°	656.8	657.9	658.9	660.0	661.1	661.5	661.4	661.2	661.0	660.8	660.1
137.5°	699.1	700.0	700.9	701.8	702.7	703.4	703.8	704.3	704.8	705.2	704.5
140°	728.4	729.3	730.2	731.1	732.0	732.5	732.7	732.9	733.1	733.3	733.1
142.5°	755.0	755.9	756.9	757.8	758.7	759.3	759.6	759.9	760.3	760.6	760.4
145°	796.7	797.1	797.4	797.9	798.2	798.7	799.2	799.7	800.3	800.8	800.6
147.5°	833.2	833.9	834.5	835.2	835.8	836.4	836.9	837.4	837.9	838.5	838.5
150°	858.6	859.0	859.3	859.7	860.1	860.4	860.8	861.1	861.5	861.9	861.9
152.5°	879.5	880.0	880.4	880.9	881.4	881.8	882.1	882.2	882.5	882.7	883.0
155°	912.3	912.3	912.3	912.3	912.3	912.4	912.6	912.7	913.0	913.1	913.9
157.5°	940.3	940.1	939.9	939.6	939.5	939.4	939.6	939.7	939.9	940.0	940.8
160°	957.9	957.5	957.2	956.8	956.4	956.3	956.3	956.3	956.3	956.3	957.2
162.5°	973.5	973.0	972.5	972.0	971.5	971.3	971.4	971.6	971.8	971.9	972.8
165°	993.7	993.1	992.6	992.1	991.6	991.2	991.2	991.2	991.2	991.2	992.3
167.5°	1009.8	1009.1	1008.4	1007.6	1006.9	1006.7	1006.8	1006.9	1007.1	1007.2	1008.4
170°	1019.0	1018.2	1017.5	1016.8	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9
172.5°	1026.1	1025.4	1024.7	1023.9	1023.2	1022.8	1022.8	1022.8	1022.8	1022.8	1023.9
175°	1033.6	1032.8	1032.1	1031.4	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4
177.5°	1036.7	1036.1	1035.5	1034.9	1034.4	1034.0	1034.0	1034.0	1034.0	1034.0	1034.9
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332034-930

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	23.3	23.3	23.2	23.2	23.3	23.4	23.5	23.6
90°	21.0	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	32.4	33.0	33.6	33.8	33.5	33.3	33.1	32.9
95°	61.6	62.4	63.1	63.5	63.5	63.5	63.5	63.5
97.5°	95.9	96.8	97.6	97.9	97.9	97.8	97.8	97.7
100°	120.7	121.2	121.8	122.3	122.6	122.9	123.4	123.7
102.5°	149.4	149.9	150.4	150.7	150.6	150.5	150.5	150.4
105°	192.1	192.1	192.1	192.2	192.6	193.0	193.3	193.7
107.5°	238.3	238.9	239.5	239.6	239.5	239.2	239.0	238.8
110°	269.2	269.9	270.7	270.8	270.4	270.1	269.8	269.4





TEST NUMBER: P332034-930

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	300.1	300.9	301.8	302.2	302.1	302.1	302.0	301.9
115°	347.1	347.2	347.4	347.4	347.2	347.1	346.9	346.7
117.5°	394.4	394.4	394.4	394.1	393.6	393.1	392.6	392.1
120°	426.1	425.9	425.7	425.4	425.1	424.8	424.4	424.0
122.5°	458.0	457.6	457.1	456.6	456.2	455.6	455.1	454.6
125°	505.6	504.8	504.1	503.4	502.7	502.0	501.2	500.5
127.5°	552.5	551.5	550.5	549.6	548.8	547.9	547.1	546.3
130°	583.7	582.9	582.3	581.2	580.0	578.7	577.5	576.2
132.5°	614.0	613.2	612.3	611.4	610.4	609.4	608.5	607.5
135°	659.4	658.7	657.9	657.4	657.0	656.6	656.3	656.0
137.5°	703.8	703.0	702.2	701.5	700.8	700.1	699.4	698.8
140°	732.9	732.7	732.5	731.8	730.6	729.3	728.1	726.8
142.5°	760.3	760.1	759.9	759.3	758.3	757.3	756.4	755.4
145°	800.5	800.3	800.1	799.6	798.9	798.2	797.4	796.7
147.5°	838.5	838.5	838.5	837.9	836.8	835.7	834.6	833.6
150°	861.9	861.9	861.9	861.3	860.2	859.2	858.0	857.0
152.5°	883.3	883.5	883.9	883.5	882.6	881.7	880.7	879.8
155°	914.6	915.3	916.0	915.7	914.5	913.2	911.9	910.7
157.5°	941.5	942.2	943.1	942.9	941.9	940.9	939.9	938.8
160°	958.1	959.0	959.9	959.9	959.3	958.5	957.8	957.1
162.5°	973.7	974.6	975.5	975.3	974.2	973.1	971.9	970.8
165°	993.4	994.5	995.6	995.5	994.3	993.0	991.7	990.4
167.5°	1009.4	1010.6	1011.7	1011.7	1010.6	1009.4	1008.4	1007.2
170°	1018.2	1019.5	1020.8	1020.8	1019.5	1018.2	1016.9	1015.7
172.5°	1025.1	1026.2	1027.3	1027.3	1026.0	1024.7	1023.4	1022.1
175°	1032.5	1033.6	1034.7	1034.5	1033.3	1032.0	1030.8	1029.5
177.5°	1035.8	1036.7	1037.5	1037.5	1036.5	1035.4	1034.5	1033.4
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0

(END OF REPORT)