

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831061

Luminaire Tested: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831061
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U930-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6631.5 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 61
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57				
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	56	55	54	49				
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46	42				
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36				
4	77	67	59	53	72	63	56	51	55	50	45	47	43	40	41	38	35	32				
5	71	60	52	46	66	56	49	44	49	44	40	43	39	35	37	34	31	28				
6	66	54	46	41	61	51	44	39	45	39	35	39	35	32	34	31	28	25				
7	61	49	42	36	57	46	40	35	41	36	31	36	32	28	31	28	25	23				
8	57	45	38	32	53	43	36	31	38	32	28	33	29	26	29	26	23	21				
9	53	41	34	29	50	39	33	28	35	30	26	31	27	23	27	24	21	19				
10	50	38	31	27	47	36	30	26	32	27	23	29	25	21	25	22	19	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	25168	25168	25168	25168	25168
5°	31829	30041	25393	20464	18805
10°	32138	33111	25224	16312	14255
15°	24206	30741	25052	13814	12055
20°	16866	24876	24733	12080	10950
25°	12860	19130	24188	11114	10271
30°	11125	15198	23317	10432	9723
35°	10322	12832	22312	9938	9339
40°	9773	11511	20903	9468	9208
45°	9447	10653	19110	9100	9150
50°	9284	9975	16988	8766	9103
55°	8938	9479	14904	8450	9143
60°	8620	8947	12848	8153	8992
65°	8097	8443	11082	7834	8815
70°	7478	7802	9426	7308	8299
75°	6771	6995	8077	6791	7582
80°	5585	6118	6391	5920	6391
85°	4421	4952	4693	5027	5088

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 21818 cd/sqm



TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	3.3
10°-20°	549.9	8.3
20°-30°	651.1	9.8
30°-40°	654.7	9.9
40°-50°	600.7	9.1
50°-60°	495.8	7.5
60°-70°	350.7	5.3
70°-80°	187.2	2.8
80°-90°	49.7	0.7
90°-100°	66.7	1.0
100°-110°	201.9	3.0
110°-120°	343.6	5.2
120°-130°	452.1	6.8
130°-140°	508.1	7.7
140°-150°	499.6	7.5
150°-160°	420.6	6.3
160°-170°	280.0	4.2
170°-180°	98.0	1.5
0°-30°	1422.1	21.4
0°-40°	2076.8	31.3
0°-60°	3173.3	47.9
0°-90°	3760.9	56.7
90°-120°	612.2	9.2
90°-150°	2072.0	31.2
90°-180°	2871.0	43.3
0°-180°	6631.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2338	2338	2338	2338	2338	
5°	2946	2780	2350	1894	1740	281
15°	2172	2759	2248	1240	1082	600
25°	1083	1611	2037	936	865	511
35°	786	976	1698	756	711	494
45°	621	700	1255	598	601	481
55°	476	505	794	450	487	426
65°	318	332	435	308	346	316
75°	163	168	194	163	182	171
85°	36	40	38	41	41	40
90°	24	20	1	20	24	14
95°	64	60	48	60	64	64
105°	194	192	183	192	194	205
115°	347	347	346	347	347	343
125°	500	507	506	507	500	448
135°	656	661	657	661	656	505
145°	797	801	797	801	797	498
155°	911	913	912	913	911	420
165°	990	991	994	991	990	279
175°	1030	1030	1034	1030	1030	98
180°	1036	1036	1036	1036	1036	



TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2
2.5°	2635.5	2632.8	2630.1	2616.5	2602.9	2596.4	2589.9	2570.4	2550.9	2529.2	2507.5
5°	2945.8	2953.4	2961.0	2952.3	2943.6	2917.1	2890.5	2855.2	2819.9	2780.3	2740.7
7.5°	3089.0	3093.4	3097.7	3092.3	3086.9	3079.8	3072.8	3041.3	3009.8	2969.1	2928.5
10°	2940.4	2950.2	2959.9	2981.1	3002.2	3026.1	3050.0	3045.6	3041.3	3029.4	3017.4
12.5°	2613.8	2625.7	2637.7	2680.0	2722.3	2776.5	2830.8	2877.5	2924.1	2956.7	2989.2
15°	2172.2	2205.3	2238.4	2276.9	2315.4	2395.2	2474.9	2573.1	2671.3	2758.6	2846.0
17.5°	1789.2	1801.7	1814.1	1855.4	1896.6	1997.0	2097.3	2210.7	2324.1	2468.9	2613.8
20°	1472.4	1483.8	1495.1	1549.4	1603.6	1682.3	1761.0	1888.5	2016.0	2171.7	2327.4
22.5°	1236.9	1254.8	1272.7	1303.1	1333.5	1408.9	1484.3	1597.7	1711.1	1883.0	2055.0
25°	1082.8	1095.9	1108.9	1127.3	1145.8	1206.0	1266.2	1359.5	1452.8	1610.7	1768.6
27.5°	977.6	983.0	988.4	1006.9	1025.3	1064.4	1103.5	1183.7	1264.0	1398.0	1532.0
30°	895.1	898.9	902.7	919.0	935.3	961.9	988.4	1046.5	1104.5	1222.8	1341.1
32.5°	837.6	840.3	843.1	855.5	868.0	887.0	906.0	948.3	990.6	1088.3	1185.9
35°	785.5	787.2	788.8	798.0	807.2	821.4	835.5	867.5	899.5	976.5	1053.5
37.5°	740.0	742.1	744.3	749.7	755.2	767.6	780.1	805.6	831.1	890.3	949.4
40°	695.5	699.3	703.1	706.9	710.7	721.0	731.3	750.8	770.4	819.2	868.0
42.5°	657.5	661.3	665.1	666.7	668.4	674.3	680.3	698.2	716.1	752.5	788.8
45°	620.6	622.3	623.9	625.5	627.1	632.0	636.9	652.6	668.4	699.8	731.3
47.5°	587.0	587.0	587.0	588.1	589.2	593.5	597.8	609.2	620.6	645.0	669.5
50°	554.4	554.4	554.4	552.8	551.2	553.9	556.6	565.3	574.0	595.7	617.4
52.5°	515.4	515.4	515.4	515.9	516.5	516.5	516.5	524.1	531.7	551.2	570.7
55°	476.3	478.5	480.7	479.0	477.4	478.5	479.6	484.5	489.3	505.1	520.8
57.5°	437.3	438.3	439.4	438.9	438.3	438.9	439.4	443.8	448.1	460.0	472.0
60°	400.4	400.4	400.4	399.3	398.2	399.3	400.4	402.5	404.7	415.6	426.4
62.5°	359.1	359.7	360.2	360.8	361.3	360.2	359.1	361.9	364.6	372.7	380.8
65°	317.9	318.5	319.0	320.6	322.2	321.2	320.1	322.8	325.5	331.5	337.4
67.5°	281.0	279.9	278.8	279.4	279.9	281.6	283.2	283.7	284.3	290.8	297.3
70°	237.6	238.7	239.8	239.2	238.7	239.2	239.8	241.4	243.0	247.9	252.8
72.5°	198.6	199.1	199.6	199.6	199.6	200.7	201.8	203.4	205.1	207.8	210.5
75°	162.8	162.8	162.8	163.8	164.9	165.5	166.0	166.0	166.0	168.2	170.3
77.5°	123.7	126.4	129.1	128.6	128.0	129.1	130.2	131.8	133.5	134.5	135.6
80°	90.1	90.1	90.1	90.6	91.1	92.8	94.4	95.5	96.6	98.7	100.9
82.5°	57.5	58.0	58.6	60.2	61.8	62.9	64.0	65.6	67.3	67.3	67.3
85°	35.8	34.7	33.6	34.7	35.8	36.9	38.0	38.5	39.1	40.1	41.2
87.5°	17.4	17.4	17.4	17.4	17.4	17.9	18.4	18.4	18.4	18.4	18.4
90°	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0	20.3	19.5	17.2
92.5°	35.0	35.4	35.7	36.1	36.4	36.4	35.8	35.3	34.7	34.2	33.1
95°	63.5	63.5	63.5	63.5	63.5	63.1	62.4	61.7	60.9	60.2	58.8
97.5°	91.1	91.3	91.5	91.7	91.9	91.5	90.6	89.7	88.8	87.9	86.8
100°	123.7	123.3	123.0	122.6	122.3	121.8	121.3	120.7	120.2	119.6	118.7
102.5°	157.1	157.3	157.4	157.6	157.8	157.6	157.1	156.5	156.0	155.4	154.2
105°	193.7	193.3	193.0	192.6	192.2	192.1	192.1	192.1	192.1	192.1	190.4
107.5°	231.1	231.3	231.5	231.7	231.9	231.7	231.1	230.6	230.0	229.5	228.8
110°	269.4	269.7	270.1	270.5	270.8	270.6	269.9	269.2	268.5	267.8	267.4



TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	310.1	310.1	310.1	310.1	310.1	309.6	308.7	307.8	306.9	306.0	306.0
115°	346.7	346.9	347.1	347.2	347.4	347.4	347.2	347.1	346.9	346.7	347.1
117.5°	384.1	384.7	385.2	385.8	386.3	386.6	386.6	386.6	386.6	386.6	386.9
120°	424.0	424.4	424.7	425.1	425.5	425.7	425.9	426.1	426.3	426.5	427.4
122.5°	462.3	462.8	463.3	463.9	464.4	465.0	465.5	466.1	466.6	467.1	467.5
125°	500.5	501.2	502.0	502.7	503.4	504.1	504.9	505.6	506.3	507.0	507.4
127.5°	538.8	539.5	540.2	540.9	541.7	542.6	543.6	544.7	545.8	546.9	547.3
130°	576.2	577.5	578.7	580.0	581.3	582.3	583.0	583.7	584.4	585.1	585.7
132.5°	615.3	616.2	617.1	618.0	618.9	619.8	620.7	621.6	622.5	623.4	623.8
135°	656.0	656.3	656.7	657.0	657.4	657.9	658.7	659.4	660.1	660.8	661.0
137.5°	691.8	692.3	692.8	693.4	693.9	694.7	695.6	696.5	697.4	698.3	697.7
140°	726.8	728.0	729.3	730.6	731.8	732.5	732.7	732.9	733.1	733.3	733.1
142.5°	762.6	763.5	764.4	765.3	766.2	766.7	766.9	767.1	767.3	767.4	767.1
145°	796.7	797.5	798.2	798.9	799.6	800.1	800.3	800.5	800.6	800.8	800.3
147.5°	827.7	828.8	829.8	830.9	832.0	832.6	832.6	832.6	832.6	832.6	832.0
150°	857.0	858.1	859.1	860.2	861.3	861.9	861.9	861.9	861.9	861.9	861.5
152.5°	885.5	886.4	887.3	888.2	889.1	889.3	889.0	888.6	888.3	887.9	887.7
155°	910.7	912.0	913.2	914.5	915.7	916.0	915.3	914.6	913.8	913.1	912.9
157.5°	934.3	935.4	936.5	937.5	938.6	938.8	938.1	937.4	936.6	935.9	935.7
160°	957.1	957.8	958.5	959.2	960.0	959.9	959.0	958.1	957.2	956.3	956.3
162.5°	974.2	975.4	976.7	978.0	979.2	979.4	978.5	977.6	976.7	975.8	975.6
165°	990.4	991.7	993.0	994.2	995.5	995.6	994.5	993.4	992.3	991.3	991.3
167.5°	1005.1	1006.2	1007.3	1008.3	1009.4	1009.4	1008.3	1007.3	1006.2	1005.1	1004.9
170°	1015.7	1016.9	1018.2	1019.5	1020.7	1020.7	1019.5	1018.2	1016.9	1015.7	1015.7
172.5°	1023.8	1025.1	1026.3	1027.6	1028.9	1029.0	1027.9	1026.8	1025.7	1024.6	1024.6
175°	1029.5	1030.8	1032.0	1033.3	1034.6	1034.7	1033.6	1032.5	1031.4	1030.3	1030.3
177.5°	1032.8	1034.0	1035.3	1036.6	1037.8	1037.9	1036.8	1035.7	1034.7	1033.6	1033.6
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2
2.5°	2501.0	2494.4	2470.6	2446.7	2419.6	2392.5	2372.4	2352.3	2322.5	2292.6	2268.2
5°	2710.4	2680.0	2629.5	2579.1	2510.7	2442.4	2396.3	2350.1	2288.3	2226.4	2177.1
7.5°	2876.4	2824.3	2753.8	2683.2	2593.7	2504.2	2419.6	2334.9	2240.6	2146.2	2069.1
10°	2982.2	2946.9	2865.5	2784.1	2664.2	2544.4	2426.1	2307.8	2186.3	2064.8	1962.8
12.5°	2992.5	2995.7	2920.9	2846.0	2710.4	2574.7	2431.0	2287.2	2134.2	1981.2	1862.4
15°	2901.9	2957.7	2916.5	2875.3	2738.6	2601.9	2425.0	2248.1	2071.8	1895.5	1758.3
17.5°	2733.7	2853.6	2859.6	2865.5	2728.8	2592.1	2396.3	2200.4	2000.8	1801.1	1656.8
20°	2504.2	2681.1	2741.8	2802.6	2691.4	2580.2	2369.7	2159.2	1935.7	1712.2	1560.8
22.5°	2269.8	2484.7	2595.9	2707.1	2624.6	2542.2	2318.1	2094.1	1858.1	1622.1	1468.6
25°	2002.9	2237.3	2408.2	2579.1	2528.6	2478.2	2257.4	2036.6	1785.4	1534.2	1377.4
27.5°	1770.2	2008.4	2214.5	2420.7	2409.8	2399.0	2179.8	1960.6	1703.5	1446.3	1295.0
30°	1563.0	1784.8	2015.4	2246.0	2272.6	2299.1	2087.6	1876.0	1618.3	1360.6	1214.7
32.5°	1379.6	1573.3	1820.7	2068.0	2120.1	2172.2	1981.2	1790.3	1535.3	1280.3	1139.8
35°	1229.3	1405.1	1652.5	1899.9	1965.0	2030.1	1864.1	1698.0	1449.6	1201.1	1067.1
37.5°	1096.4	1243.4	1484.8	1726.3	1806.0	1885.8	1737.1	1588.5	1355.7	1123.0	999.8
40°	986.3	1104.5	1326.4	1548.3	1640.5	1732.8	1610.2	1487.6	1266.8	1046.0	932.6
42.5°	894.1	999.3	1200.6	1401.8	1490.3	1578.7	1475.1	1371.5	1175.1	978.7	875.1
45°	815.4	899.5	1082.3	1265.1	1349.2	1433.3	1344.3	1255.4	1082.3	909.2	812.7
47.5°	741.6	813.8	970.0	1126.2	1201.1	1276.0	1206.5	1137.1	990.6	844.1	756.8
50°	675.4	733.5	870.2	1006.9	1072.0	1137.1	1075.8	1014.5	894.1	773.6	697.7
52.5°	617.9	665.1	779.6	894.1	949.9	1005.8	953.2	900.6	805.1	709.6	643.4
55°	561.0	601.1	700.4	799.7	837.6	875.6	834.9	794.2	717.2	640.2	584.3
57.5°	507.8	543.6	625.0	706.3	735.6	764.9	728.0	691.2	633.1	575.1	528.4
60°	455.7	485.0	552.8	620.6	638.5	656.4	626.6	596.8	556.1	515.4	473.6
62.5°	407.4	434.0	484.5	534.9	546.8	558.8	536.0	513.2	482.3	451.4	418.8
65°	357.5	377.6	418.8	460.0	467.6	475.2	455.2	435.1	411.8	388.4	364.6
67.5°	311.4	325.5	359.1	392.8	393.3	393.9	377.6	361.3	348.3	335.3	316.3
70°	266.4	279.9	302.2	324.4	325.0	325.5	312.5	299.5	289.7	279.9	265.8
72.5°	220.3	230.0	246.8	263.7	262.6	261.5	253.4	245.2	237.6	230.0	219.7
75°	178.5	186.6	198.0	209.4	206.2	202.9	198.6	194.2	187.7	181.2	174.7
77.5°	140.5	145.4	151.9	158.4	156.2	154.1	150.3	146.5	141.6	136.7	134.0
80°	103.1	105.2	109.6	113.9	112.8	111.8	107.4	103.1	102.0	100.9	97.1
82.5°	70.0	72.7	73.8	74.9	74.3	73.8	70.5	67.3	66.2	65.1	64.6
85°	41.8	42.3	42.9	43.4	41.8	40.1	39.1	38.0	38.0	38.0	37.4
87.5°	19.0	19.5	19.5	19.5	19.0	18.4	17.4	16.3	16.8	17.4	17.4
90°	14.8	12.5	10.1	8.0	6.2	4.4	2.6	0.8	2.6	4.4	6.2
92.5°	32.0	30.9	29.8	28.8	27.7	26.6	25.5	24.4	25.5	26.6	27.7
95°	57.3	55.9	54.4	53.1	51.8	50.5	49.3	48.0	49.3	50.5	51.8
97.5°	85.7	84.6	83.6	82.6	81.7	80.8	79.8	78.9	79.8	80.8	81.7
100°	117.8	116.9	116.0	115.0	113.9	112.9	111.8	110.7	111.8	112.9	113.9
102.5°	152.9	151.6	150.4	149.5	148.9	148.4	147.8	147.3	147.8	148.4	148.9
105°	188.8	187.2	185.6	184.6	184.2	183.8	183.5	183.1	183.5	183.8	184.2
107.5°	228.1	227.3	226.6	226.2	226.0	225.8	225.6	225.4	225.6	225.8	226.0
110°	267.0	266.7	266.3	265.9	265.6	265.2	264.9	264.5	264.9	265.2	265.6



TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	306.0	306.0	306.0	305.9	305.7	305.6	305.4	305.2	305.4	305.6	305.7
115°	347.4	347.8	348.1	348.1	347.5	347.0	346.4	345.9	346.4	347.0	347.5
117.5°	387.3	387.7	388.0	388.1	387.9	387.7	387.6	387.4	387.6	387.7	387.9
120°	428.3	429.2	430.1	430.0	428.9	427.8	426.7	425.6	426.7	427.8	428.9
122.5°	467.9	468.2	468.6	468.4	467.7	467.0	466.2	465.5	466.2	467.0	467.7
125°	507.7	508.1	508.5	508.4	507.8	507.3	506.7	506.2	506.7	507.3	507.8
127.5°	547.6	548.0	548.3	548.0	546.9	545.8	544.7	543.6	544.7	545.8	546.9
130°	586.2	586.8	587.3	586.9	585.4	584.0	582.5	581.1	582.5	584.0	585.4
132.5°	624.1	624.5	624.8	624.3	622.9	621.4	620.0	618.5	620.0	621.4	622.9
135°	661.2	661.4	661.6	661.1	660.0	658.9	657.9	656.8	657.9	658.9	660.0
137.5°	697.2	696.6	696.1	695.4	694.5	693.6	692.7	691.8	692.7	693.6	694.5
140°	732.9	732.7	732.5	732.0	731.1	730.2	729.3	728.4	729.3	730.2	731.1
142.5°	766.7	766.4	766.0	765.4	764.5	763.6	762.7	761.8	762.7	763.6	764.5
145°	799.7	799.2	798.6	798.2	797.8	797.5	797.1	796.7	797.1	797.5	797.8
147.5°	831.5	830.9	830.4	829.8	829.0	828.3	827.6	826.9	827.6	828.3	829.0
150°	861.1	860.8	860.4	860.0	859.7	859.3	859.0	858.6	859.0	859.3	859.7
152.5°	887.5	887.4	887.2	886.8	886.3	885.7	885.2	884.6	885.2	885.7	886.3
155°	912.8	912.6	912.4	912.3	912.3	912.3	912.3	912.3	912.3	912.3	912.3
157.5°	935.6	935.4	935.2	935.2	935.4	935.6	935.7	935.9	935.7	935.6	935.4
160°	956.3	956.3	956.3	956.4	956.8	957.2	957.5	957.9	957.5	957.2	956.8
162.5°	975.4	975.2	975.1	975.2	975.8	976.3	976.9	977.4	976.9	976.3	975.8
165°	991.3	991.3	991.3	991.5	992.1	992.6	993.2	993.7	993.2	992.6	992.1
167.5°	1004.7	1004.5	1004.4	1004.6	1005.4	1006.1	1006.8	1007.5	1006.8	1006.1	1005.4
170°	1015.7	1015.7	1015.7	1016.0	1016.8	1017.5	1018.2	1018.9	1018.2	1017.5	1016.8
172.5°	1024.6	1024.6	1024.6	1025.0	1025.7	1026.4	1027.2	1027.9	1027.2	1026.4	1025.7
175°	1030.3	1030.3	1030.3	1030.7	1031.4	1032.1	1032.9	1033.6	1032.9	1032.1	1031.4
177.5°	1033.6	1033.6	1033.6	1033.9	1034.7	1035.4	1036.1	1036.8	1036.1	1035.4	1034.7
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2
2.5°	2243.8	2222.6	2201.5	2185.2	2168.9	2141.3	2113.6	2107.1	2100.6	2091.4	2082.1
5°	2127.7	2075.6	2023.5	1976.9	1930.2	1893.9	1857.5	1833.7	1809.8	1792.4	1775.1
7.5°	1992.1	1914.0	1835.8	1780.5	1725.2	1672.5	1619.9	1603.1	1586.3	1563.5	1540.7
10°	1860.8	1774.5	1688.3	1616.1	1544.0	1492.4	1440.9	1420.3	1399.7	1370.9	1342.2
12.5°	1743.6	1649.2	1554.8	1482.1	1409.4	1359.5	1309.6	1279.8	1249.9	1233.7	1217.4
15°	1621.0	1520.1	1419.2	1351.9	1284.7	1239.6	1194.6	1168.6	1142.5	1126.8	1111.1
17.5°	1512.5	1412.7	1312.9	1248.3	1183.7	1142.5	1101.3	1078.5	1055.7	1043.8	1031.8
20°	1409.4	1311.8	1214.1	1151.2	1088.3	1054.6	1021.0	1006.3	991.7	981.9	972.2
22.5°	1315.0	1219.0	1123.0	1069.3	1015.6	988.4	961.3	951.0	940.7	932.6	924.4
25°	1220.6	1134.9	1049.2	1003.6	958.1	935.8	913.6	903.3	893.0	884.8	876.7
27.5°	1143.6	1061.7	979.8	940.7	901.6	884.3	866.9	858.8	850.7	843.1	835.5
30°	1068.7	995.5	922.3	888.6	855.0	839.3	823.5	815.4	807.2	800.2	793.1
32.5°	999.3	936.4	873.4	842.5	811.6	798.6	785.5	775.8	766.0	760.6	755.2
35°	933.1	876.7	820.3	794.8	769.3	756.3	743.2	735.1	727.0	722.6	718.3
37.5°	876.7	826.2	775.8	751.4	727.0	714.5	702.0	695.0	687.9	686.3	684.6
40°	819.2	775.8	732.4	708.5	684.6	673.8	662.9	658.6	654.3	653.2	652.1
42.5°	771.4	729.1	686.8	665.1	643.4	634.2	625.0	622.8	620.6	622.3	623.9
45°	716.1	680.8	645.6	625.5	605.4	597.8	590.2	588.6	587.0	590.2	593.5
47.5°	669.5	636.9	604.4	585.4	566.4	561.0	555.5	555.0	554.4	558.8	563.1
50°	621.7	590.2	558.8	543.6	528.4	523.5	518.6	520.3	521.9	528.9	536.0
52.5°	577.2	547.9	518.6	504.5	490.4	487.2	483.9	487.7	491.5	499.1	506.7
55°	528.4	501.8	475.2	464.4	453.5	450.3	447.0	454.6	462.2	469.3	476.3
57.5°	481.7	458.4	435.1	425.3	415.6	415.0	414.5	421.5	428.6	436.2	443.8
60°	431.8	412.3	392.8	385.2	377.6	378.7	379.8	387.9	396.0	402.0	408.0
62.5°	386.3	370.0	353.7	346.7	339.6	342.3	345.0	353.2	361.3	368.4	375.4
65°	340.7	327.1	313.6	308.7	303.8	307.6	311.4	318.5	325.5	330.4	335.3
67.5°	297.3	285.9	274.5	270.7	266.9	270.7	274.5	281.6	288.6	293.5	298.4
70°	251.7	242.5	233.3	230.6	227.9	232.2	236.5	242.5	248.5	253.4	258.2
72.5°	209.4	202.4	195.3	194.8	194.2	198.0	201.8	207.8	213.7	217.0	220.3
75°	168.2	164.4	160.6	160.0	159.5	163.3	167.1	170.3	173.6	176.3	179.0
77.5°	131.3	128.0	124.8	125.3	125.9	128.6	131.3	134.5	137.8	139.4	141.1
80°	93.3	92.2	91.1	92.2	93.3	95.5	97.7	99.8	102.0	103.1	104.2
82.5°	64.0	62.9	61.8	63.5	65.1	66.7	68.4	70.0	71.6	72.2	72.7
85°	36.9	38.5	40.1	40.1	40.1	40.7	41.2	41.8	42.3	41.8	41.2
87.5°	17.4	17.9	18.4	18.4	18.4	19.0	19.5	19.5	19.5	19.0	18.4
90°	8.0	10.1	12.5	14.8	17.2	19.5	20.3	21.0	21.7	22.4	23.0
92.5°	28.8	29.8	30.9	32.0	33.1	34.2	34.7	35.3	35.8	36.4	36.4
95°	53.1	54.4	55.9	57.3	58.8	60.2	60.9	61.7	62.4	63.1	63.5
97.5°	82.6	83.6	84.6	85.7	86.8	87.9	88.8	89.7	90.6	91.5	91.9
100°	115.0	116.0	116.9	117.8	118.7	119.6	120.2	120.7	121.3	121.8	122.3
102.5°	149.5	150.4	151.6	152.9	154.2	155.4	156.0	156.5	157.1	157.6	157.8
105°	184.6	185.6	187.2	188.8	190.4	192.1	192.1	192.1	192.1	192.1	192.2
107.5°	226.2	226.6	227.3	228.1	228.8	229.5	230.0	230.6	231.1	231.7	231.9
110°	265.9	266.3	266.7	267.0	267.4	267.8	268.5	269.2	269.9	270.6	270.8



TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	305.9	306.0	306.0	306.0	306.0	306.0	306.9	307.8	308.7	309.6	310.1
115°	348.1	348.1	347.8	347.4	347.1	346.7	346.9	347.1	347.2	347.4	347.4
117.5°	388.1	388.0	387.7	387.3	386.9	386.6	386.6	386.6	386.6	386.6	386.3
120°	430.0	430.1	429.2	428.3	427.4	426.5	426.3	426.1	425.9	425.7	425.5
122.5°	468.4	468.6	468.2	467.9	467.5	467.1	466.6	466.1	465.5	465.0	464.4
125°	508.4	508.5	508.1	507.7	507.4	507.0	506.3	505.6	504.9	504.1	503.4
127.5°	548.0	548.3	548.0	547.6	547.3	546.9	545.8	544.7	543.6	542.6	541.7
130°	586.9	587.3	586.8	586.2	585.7	585.1	584.4	583.7	583.0	582.3	581.3
132.5°	624.3	624.8	624.5	624.1	623.8	623.4	622.5	621.6	620.7	619.8	618.9
135°	661.1	661.6	661.4	661.2	661.0	660.8	660.1	659.4	658.7	657.9	657.4
137.5°	695.4	696.1	696.6	697.2	697.7	698.3	697.4	696.5	695.6	694.7	693.9
140°	732.0	732.5	732.7	732.9	733.1	733.3	733.1	732.9	732.7	732.5	731.8
142.5°	765.4	766.0	766.4	766.7	767.1	767.4	767.3	767.1	766.9	766.7	766.2
145°	798.2	798.6	799.2	799.7	800.3	800.8	800.6	800.5	800.3	800.1	799.6
147.5°	829.8	830.4	830.9	831.5	832.0	832.6	832.6	832.6	832.6	832.6	832.0
150°	860.0	860.4	860.8	861.1	861.5	861.9	861.9	861.9	861.9	861.9	861.3
152.5°	886.8	887.2	887.4	887.5	887.7	887.9	888.3	888.6	889.0	889.3	889.1
155°	912.3	912.4	912.6	912.8	912.9	913.1	913.8	914.6	915.3	916.0	915.7
157.5°	935.2	935.2	935.4	935.6	935.7	935.9	936.6	937.4	938.1	938.8	938.6
160°	956.4	956.3	956.3	956.3	956.3	956.3	957.2	958.1	959.0	959.9	960.0
162.5°	975.2	975.1	975.2	975.4	975.6	975.8	976.7	977.6	978.5	979.4	979.2
165°	991.5	991.3	991.3	991.3	991.3	991.3	992.3	993.4	994.5	995.6	995.5
167.5°	1004.6	1004.4	1004.5	1004.7	1004.9	1005.1	1006.2	1007.3	1008.3	1009.4	1009.4
170°	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9	1018.2	1019.5	1020.7	1020.7
172.5°	1025.0	1024.6	1024.6	1024.6	1024.6	1024.6	1025.7	1026.8	1027.9	1029.0	1028.9
175°	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4	1032.5	1033.6	1034.7	1034.6
177.5°	1033.9	1033.6	1033.6	1033.6	1033.6	1033.6	1034.7	1035.7	1036.8	1037.9	1037.8
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2338.2	2338.2	2338.2	2338.2
2.5°	2078.3	2074.5	2059.4	2044.2
5°	1762.1	1749.0	1744.7	1740.4
7.5°	1539.6	1538.5	1515.8	1493.0
10°	1343.8	1345.4	1324.8	1304.2
12.5°	1203.8	1190.3	1188.6	1187.0
15°	1098.6	1086.1	1083.9	1081.8
17.5°	1024.3	1016.7	1014.5	1012.3
20°	967.8	963.5	959.7	955.9
22.5°	919.0	913.6	910.3	907.1
25°	871.8	866.9	865.8	864.8
27.5°	829.5	823.5	823.5	823.5
30°	789.3	785.5	783.9	782.3
32.5°	751.9	748.7	748.7	748.7
35°	716.7	715.0	712.9	710.7
37.5°	684.6	684.6	683.6	682.5
40°	653.7	655.3	655.3	655.3
42.5°	625.5	627.1	627.1	627.1
45°	596.2	598.9	600.0	601.1
47.5°	567.5	571.8	572.9	574.0
50°	539.3	542.5	543.0	543.6
52.5°	510.5	514.3	517.0	519.7
55°	480.1	483.9	485.5	487.2
57.5°	447.6	451.4	451.9	452.5
60°	411.8	415.6	416.6	417.7
62.5°	377.6	379.8	380.8	381.9
65°	338.5	341.8	343.9	346.1
67.5°	301.1	303.8	303.8	303.8
70°	259.3	260.4	262.0	263.7
72.5°	220.8	221.3	221.3	221.3
75°	180.1	181.2	181.7	182.3
77.5°	141.6	142.1	142.1	142.1
80°	103.6	103.1	103.1	103.1
82.5°	71.1	69.4	69.4	69.4
85°	40.7	40.1	40.7	41.2
87.5°	18.4	18.4	18.4	18.4
90°	23.3	23.7	24.1	24.4
92.5°	36.1	35.7	35.4	35.0
95°	63.5	63.5	63.5	63.5
97.5°	91.7	91.5	91.3	91.1
100°	122.6	123.0	123.3	123.7
102.5°	157.6	157.4	157.3	157.1
105°	192.6	193.0	193.3	193.7
107.5°	231.7	231.5	231.3	231.1
110°	270.5	270.1	269.7	269.4



TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	310.1	310.1	310.1	310.1
115°	347.2	347.1	346.9	346.7
117.5°	385.8	385.2	384.7	384.1
120°	425.1	424.7	424.4	424.0
122.5°	463.9	463.3	462.8	462.3
125°	502.7	502.0	501.2	500.5
127.5°	540.9	540.2	539.5	538.8
130°	580.0	578.7	577.5	576.2
132.5°	618.0	617.1	616.2	615.3
135°	657.0	656.7	656.3	656.0
137.5°	693.4	692.8	692.3	691.8
140°	730.6	729.3	728.0	726.8
142.5°	765.3	764.4	763.5	762.6
145°	798.9	798.2	797.5	796.7
147.5°	830.9	829.8	828.8	827.7
150°	860.2	859.1	858.1	857.0
152.5°	888.2	887.3	886.4	885.5
155°	914.5	913.2	912.0	910.7
157.5°	937.5	936.5	935.4	934.3
160°	959.2	958.5	957.8	957.1
162.5°	978.0	976.7	975.4	974.2
165°	994.2	993.0	991.7	990.4
167.5°	1008.3	1007.3	1006.2	1005.1
170°	1019.5	1018.2	1016.9	1015.7
172.5°	1027.6	1026.3	1025.1	1023.8
175°	1033.3	1032.0	1030.8	1029.5
177.5°	1036.6	1035.3	1034.0	1032.8
180°	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P831061

CATALOG NUMBER: S123DIP-S1000D1025U930-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.38	16.26	16.29	17.18	18.36	17.62	18.50	18.52	19.42	20.59
	3H	17.03	17.82	17.95	18.75	19.95	19.04	19.83	19.96	20.76	21.96
	4H	17.61	18.35	18.54	19.29	20.50	19.49	20.24	20.43	21.17	22.38
	6H	17.98	18.67	18.92	19.61	20.83	19.77	20.46	20.71	21.40	22.62
	8H	18.08	18.73	19.03	19.69	20.91	19.83	20.49	20.79	21.44	22.66
	12H	18.12	18.74	19.08	19.69	20.94	19.85	20.48	20.81	21.43	22.67
4H	2H	15.96	16.70	16.90	17.64	18.85	17.78	18.53	18.72	19.46	20.67
	3H	17.79	18.41	18.74	19.37	20.60	19.40	20.03	20.35	20.99	22.21
	4H	18.49	19.05	19.44	20.01	21.26	19.99	20.56	20.95	21.51	22.76
	6H	18.96	19.45	19.93	20.43	21.68	20.39	20.88	21.36	21.86	23.11
	8H	19.10	19.56	20.07	20.53	21.79	20.51	20.96	21.48	21.94	23.20
	12H	19.17	19.58	20.16	20.57	21.84	20.55	20.96	21.54	21.95	23.22
8H	4H	18.75	19.21	19.73	20.19	21.45	20.10	20.55	21.07	21.53	22.79
	6H	19.34	19.72	20.34	20.74	22.00	20.60	20.97	21.60	21.99	23.25
	8H	19.55	19.88	20.56	20.89	22.17	20.78	21.11	21.78	22.12	23.39
	12H	19.68	19.97	20.69	20.97	22.29	20.88	21.17	21.89	22.17	23.50
12H	4H	18.76	19.17	19.75	20.16	21.43	20.07	20.48	21.06	21.47	22.74
	6H	19.40	19.73	20.40	20.73	22.01	20.61	20.94	21.62	21.95	23.23
	8H	19.63	19.92	20.64	20.92	22.25	20.81	21.11	21.82	22.10	23.43