

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332007-930

Luminaire Tested: **S123DIP-S1000D365U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332007-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D365U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4375.4 lumens  
Efficiency: N/A  
Efficacy: 100.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332007-930  
CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332007-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	70	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57	54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49	46
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	50	45	42	39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	41	36	32	30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	32	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	32	26	22	29	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332007-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.6	2.8
10°-20°	343.3	7.8
20°-30°	507.0	11.6
30°-40°	592.3	13.5
40°-50°	595.5	13.6
50°-60°	523.1	12.0
60°-70°	389.7	8.9
70°-80°	222.0	5.1
80°-90°	64.8	1.5
90°-100°	23.9	0.5
100°-110°	71.5	1.6
110°-120°	121.6	2.8
120°-130°	160.0	3.7
130°-140°	179.8	4.1
140°-150°	176.8	4.0
150°-160°	148.8	3.4
160°-170°	99.1	2.3
170°-180°	34.7	0.8
0°-30°	971.9	22.2
0°-40°	1564.1	35.7
0°-60°	2682.6	61.3
0°-90°	3359.2	76.8
90°-120°	217.1	5.0
90°-150°	733.7	16.8
90°-180°	1016.0	23.2
0°-180°	4375.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	0	3	7	8	9	4
95°	17	19	21	22	22	19
105°	65	66	68	68	69	69
115°	122	123	123	123	123	121
125°	179	180	180	178	177	160
135°	232	234	234	233	232	179
145°	282	283	284	283	282	176
155°	323	323	323	324	322	149
165°	352	351	351	352	351	99
175°	366	365	365	366	364	35
180°	367	367	367	367	367	



TEST NUMBER: P332007-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.2	22.7	22.2	21.8	21.3	21.0	21.0	21.0	21.0	21.0	20.8
90°	0.3	0.9	1.5	2.2	2.9	3.6	4.4	5.2	6.1	6.9	7.2
92.5°	7.0	7.4	7.8	8.3	8.7	9.1	9.6	10.1	10.6	11.1	11.3
95°	17.0	17.4	17.9	18.3	18.8	19.2	19.8	20.3	20.8	21.4	21.6
97.5°	30.2	30.5	30.9	31.2	31.6	31.9	32.3	32.6	33.0	33.3	33.7
100°	39.2	39.5	39.9	40.4	40.7	41.1	41.4	41.7	42.1	42.3	42.6
102.5°	49.6	49.8	50.0	50.2	50.5	50.8	51.2	51.7	52.1	52.5	52.7
105°	64.8	65.0	65.1	65.2	65.3	65.7	66.3	66.9	67.4	68.0	68.0
107.5°	82.6	82.7	82.8	82.8	82.9	83.0	83.2	83.5	83.7	84.0	84.1
110°	93.7	93.8	93.9	94.0	94.2	94.2	94.4	94.6	94.7	94.8	95.1



TEST NUMBER: P332007-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	105.2	105.3	105.3	105.4	105.5	105.5	105.6	105.6	105.6	105.7	105.9
115°	122.5	122.6	122.9	123.0	123.2	123.3	123.1	123.0	122.9	122.7	122.8
117.5°	139.8	140.0	140.1	140.2	140.4	140.3	140.1	140.0	139.8	139.7	139.7
120°	150.7	151.1	151.5	151.8	152.2	152.2	152.0	151.6	151.3	151.0	150.9
122.5°	162.0	162.2	162.6	162.8	163.1	163.1	163.0	162.8	162.7	162.5	162.3
125°	179.2	179.4	179.6	179.8	180.0	180.0	179.9	179.8	179.6	179.5	179.2
127.5°	195.1	195.5	195.9	196.3	196.7	196.9	196.7	196.6	196.5	196.3	196.0
130°	205.7	206.2	206.8	207.2	207.7	207.9	207.7	207.6	207.3	207.2	206.9
132.5°	216.3	216.9	217.4	217.8	218.3	218.6	218.4	218.3	218.1	218.0	217.7
135°	232.5	232.9	233.3	233.7	234.1	234.2	234.2	234.1	234.0	234.0	233.7
137.5°	247.5	247.9	248.1	248.4	248.7	249.0	249.2	249.3	249.5	249.6	249.4
140°	257.9	258.2	258.5	258.9	259.2	259.3	259.4	259.4	259.5	259.6	259.5
142.5°	267.3	267.7	268.0	268.3	268.6	268.8	269.0	269.0	269.1	269.3	269.2
145°	282.1	282.2	282.3	282.4	282.6	282.7	282.9	283.2	283.3	283.5	283.5
147.5°	295.0	295.2	295.5	295.7	295.9	296.1	296.3	296.4	296.6	296.9	296.9
150°	303.9	304.1	304.2	304.4	304.5	304.6	304.8	304.8	305.0	305.1	305.1
152.5°	311.4	311.5	311.7	311.9	312.1	312.2	312.3	312.3	312.4	312.5	312.6
155°	323.0	323.0	323.0	323.0	323.0	323.0	323.1	323.1	323.2	323.3	323.5
157.5°	332.9	332.8	332.7	332.6	332.6	332.6	332.6	332.6	332.7	332.8	333.0
160°	339.1	339.0	338.8	338.8	338.6	338.5	338.5	338.5	338.5	338.5	338.8
162.5°	344.6	344.5	344.3	344.1	343.9	343.9	343.9	344.0	344.1	344.1	344.4
165°	351.8	351.6	351.4	351.2	351.0	350.9	350.9	350.9	350.9	350.9	351.3
167.5°	357.5	357.3	357.0	356.7	356.4	356.4	356.4	356.4	356.5	356.6	356.9
170°	360.7	360.4	360.2	360.0	359.7	359.5	359.5	359.5	359.5	359.5	360.0
172.5°	363.3	363.0	362.7	362.5	362.2	362.1	362.1	362.1	362.1	362.1	362.5
175°	365.9	365.7	365.4	365.2	364.9	364.8	364.8	364.8	364.8	364.8	365.2
177.5°	367.0	366.8	366.6	366.4	366.2	366.1	366.1	366.1	366.1	366.1	366.4
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8



TEST NUMBER: P332007-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	20.6	20.5	20.3	20.3	20.3	20.3	20.4	20.4
90°	7.4	7.7	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	11.5	11.7	11.9	12.0	11.9	11.8	11.7	11.7
95°	21.9	22.1	22.3	22.5	22.5	22.5	22.5	22.5
97.5°	33.9	34.2	34.6	34.7	34.7	34.7	34.6	34.6
100°	42.7	43.0	43.1	43.3	43.4	43.5	43.7	43.8
102.5°	52.9	53.1	53.2	53.3	53.3	53.3	53.2	53.2
105°	68.0	68.0	68.0	68.1	68.2	68.3	68.5	68.6
107.5°	84.4	84.5	84.8	84.9	84.8	84.7	84.6	84.5
110°	95.3	95.6	95.8	95.9	95.7	95.6	95.5	95.4





TEST NUMBER: P332007-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	106.2	106.6	106.9	107.0	107.0	107.0	106.9	106.9
115°	122.9	122.9	123.0	123.0	122.9	122.9	122.8	122.7
117.5°	139.7	139.7	139.7	139.5	139.3	139.2	139.0	138.8
120°	150.8	150.7	150.7	150.6	150.5	150.3	150.3	150.1
122.5°	162.2	162.0	161.8	161.7	161.5	161.3	161.1	160.9
125°	179.0	178.7	178.5	178.2	178.0	177.7	177.4	177.2
127.5°	195.6	195.3	194.9	194.5	194.3	194.0	193.7	193.4
130°	206.7	206.4	206.1	205.8	205.4	204.9	204.5	204.0
132.5°	217.4	217.0	216.8	216.5	216.1	215.7	215.4	215.1
135°	233.4	233.2	232.9	232.8	232.6	232.4	232.4	232.2
137.5°	249.2	248.9	248.6	248.3	248.1	247.9	247.6	247.4
140°	259.4	259.4	259.3	259.1	258.6	258.2	257.7	257.3
142.5°	269.1	269.0	269.0	268.8	268.5	268.2	267.7	267.4
145°	283.4	283.3	283.2	283.1	282.8	282.6	282.3	282.1
147.5°	296.9	296.9	296.9	296.6	296.3	295.9	295.5	295.1
150°	305.1	305.1	305.1	304.9	304.5	304.2	303.8	303.4
152.5°	312.7	312.8	312.9	312.7	312.4	312.1	311.8	311.4
155°	323.8	324.0	324.3	324.2	323.8	323.3	322.9	322.4
157.5°	333.3	333.6	333.9	333.8	333.5	333.1	332.7	332.4
160°	339.2	339.5	339.8	339.8	339.6	339.3	339.1	338.8
162.5°	344.7	345.0	345.4	345.3	344.9	344.5	344.1	343.6
165°	351.7	352.0	352.5	352.5	352.0	351.6	351.1	350.7
167.5°	357.3	357.8	358.2	358.2	357.8	357.3	356.9	356.6
170°	360.4	360.9	361.3	361.3	360.9	360.4	360.0	359.5
172.5°	362.9	363.3	363.7	363.7	363.2	362.8	362.3	361.9
175°	365.5	365.9	366.3	366.2	365.8	365.3	364.9	364.4
177.5°	366.7	367.0	367.3	367.3	367.0	366.6	366.2	365.8
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8

(END OF REPORT)