

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332008-930

Luminaire Tested: **S123DIP-S1000D365U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332008-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D365U930-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4430.0 lumens  
Efficiency: N/A  
Efficacy: 101.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332008-930  
CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332008-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	76
1	103	99	95	91	98	94	91	87	86	83	80	78	76	74	70	69	67	64
2	94	86	80	74	89	82	77	72	75	70	66	68	65	61	62	59	57	53
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	45
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	42	39
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	34
6	67	54	46	39	63	52	44	38	48	41	36	44	38	34	40	36	32	29
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28	26
8	58	45	37	31	55	43	35	30	40	33	29	37	31	27	34	29	25	23
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	21
10	50	38	30	25	48	36	29	24	34	28	23	31	26	22	29	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332008-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.6	2.7
10°-20°	343.3	7.7
20°-30°	507.0	11.4
30°-40°	592.3	13.4
40°-50°	595.5	13.4
50°-60°	523.1	11.8
60°-70°	389.7	8.8
70°-80°	222.0	5.0
80°-90°	64.8	1.5
90°-100°	79.2	1.8
100°-110°	224.3	5.1
110°-120°	220.6	5.0
120°-130°	176.0	4.0
130°-140°	138.8	3.1
140°-150°	103.6	2.3
150°-160°	72.2	1.6
160°-170°	42.4	1.0
170°-180°	13.8	0.3
0°-30°	971.9	21.9
0°-40°	1564.1	35.3
0°-60°	2682.6	60.6
0°-90°	3359.2	75.8
90°-120°	524.1	11.8
90°-150°	942.4	21.3
90°-180°	1071.0	24.2
0°-180°	4430.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	1	4	7	8	8	4
95°	10	32	171	50	33	11
105°	33	49	232	405	366	36
115°	59	74	177	388	446	58
125°	82	97	165	300	352	73
135°	96	115	163	247	285	74
145°	110	126	161	202	223	69
155°	125	135	156	177	185	57
165°	136	140	149	158	161	38
175°	142	142	143	145	145	13
180°	142	142	142	142	142	



TEST NUMBER: P332008-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.2	22.7	22.3	21.9	21.4	21.0	21.0	21.0	21.0	21.0	20.7
90°	0.6	1.1	1.7	2.6	3.2	3.8	4.6	5.5	6.4	7.2	6.9
92.5°	3.6	5.3	7.7	9.9	12.4	16.6	24.2	36.6	48.8	44.3	33.4
95°	9.8	10.7	13.9	18.8	26.3	37.4	62.0	104.8	152.1	170.9	138.6
97.5°	16.7	17.0	19.5	23.7	31.1	43.3	66.7	115.0	193.9	264.8	283.2
100°	21.4	21.6	23.6	27.6	34.6	45.8	66.0	108.6	184.4	272.9	329.6
102.5°	26.2	26.7	28.5	32.3	38.5	48.8	66.9	103.1	170.6	257.9	331.9
105°	33.4	34.3	36.0	39.5	44.9	53.9	69.5	99.1	153.6	231.6	314.3
107.5°	41.2	42.0	43.7	47.0	52.2	60.5	74.2	98.8	142.8	208.5	283.6
110°	46.6	47.5	49.0	52.2	57.1	65.1	78.1	100.0	138.6	195.3	264.2



TEST NUMBER: P332008-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	51.8	52.6	54.1	57.2	62.1	70.0	82.0	102.3	136.2	186.5	247.4
115°	59.0	60.3	62.0	64.8	69.7	77.5	88.5	106.0	135.4	177.2	227.1
117.5°	66.4	67.7	69.1	71.8	77.3	84.5	95.3	111.0	135.9	171.6	214.7
120°	71.4	72.3	73.8	76.6	82.1	89.3	99.7	114.6	136.9	169.1	208.3
122.5°	75.8	76.7	78.1	81.3	86.5	94.2	104.3	118.1	138.4	167.5	203.0
125°	82.1	82.7	84.4	87.6	93.0	100.9	111.0	123.6	140.9	165.3	196.2
127.5°	86.9	87.7	89.9	93.1	99.1	107.0	116.7	128.1	143.7	164.4	190.2
130°	89.9	90.7	93.4	96.8	102.9	110.6	120.2	131.1	145.5	163.6	186.9
132.5°	92.2	93.3	96.1	100.3	106.3	113.9	123.1	133.9	146.9	163.4	184.0
135°	96.2	97.3	100.5	104.8	111.0	118.7	127.6	137.5	149.0	163.1	180.1
137.5°	100.0	101.3	104.4	108.9	115.0	122.1	130.8	140.1	150.3	162.4	176.7
140°	102.6	104.0	106.9	111.5	117.2	124.5	132.8	141.5	151.2	162.2	174.6
142.5°	105.3	106.6	109.7	113.8	119.6	126.3	134.4	142.8	152.0	161.8	172.8
145°	109.7	110.6	113.2	117.6	122.5	129.1	136.6	144.3	152.4	161.0	170.2
147.5°	114.3	114.8	117.3	121.1	125.8	131.4	138.3	145.3	152.4	160.0	167.9
150°	117.2	117.6	119.8	123.6	127.6	132.8	139.4	145.5	152.4	159.1	166.2
152.5°	120.3	120.3	122.6	125.9	129.5	134.4	140.1	145.9	151.7	157.9	164.4
155°	124.7	124.7	126.5	129.4	132.6	136.6	141.5	146.1	151.0	155.9	161.6
157.5°	128.3	128.6	130.0	132.5	135.2	138.3	142.2	146.3	150.0	154.1	158.5
160°	131.1	131.1	132.2	134.5	136.6	139.4	142.9	146.3	149.5	152.7	156.5
162.5°	133.1	133.1	134.1	135.9	137.7	140.1	143.2	146.1	148.6	151.3	154.3
165°	136.2	136.0	136.6	138.0	139.2	141.2	143.5	145.5	147.2	149.3	151.6
167.5°	138.6	138.3	138.6	139.7	140.5	141.8	143.4	145.0	145.9	147.2	148.9
170°	140.0	139.4	139.7	140.6	141.2	141.8	143.2	144.3	145.0	145.8	147.2
172.5°	141.0	140.6	140.6	141.3	141.6	141.9	143.2	144.1	144.2	144.6	145.6
175°	142.0	141.8	141.5	142.0	142.0	142.4	142.9	143.5	143.2	143.2	143.7
177.5°	142.6	142.4	142.1	142.4	142.4	142.4	142.6	143.0	142.6	142.4	142.6
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332008-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	20.5	20.5	20.3	20.3	20.2	20.3	20.4	20.3
90°	7.2	7.5	7.7	8.3	8.1	8.3	8.6	8.3
92.5°	24.3	19.2	17.0	15.5	15.0	14.1	14.4	13.9
95°	103.7	70.3	55.0	44.7	39.2	36.6	34.6	33.4
97.5°	258.5	207.1	169.9	135.5	114.2	101.3	93.4	91.0
100°	339.7	316.3	282.7	241.7	212.6	191.6	180.3	180.7
102.5°	366.6	365.9	346.3	320.3	297.7	281.0	271.7	265.0
105°	374.5	403.3	408.8	401.4	388.1	377.2	367.9	366.5
107.5°	351.8	398.6	423.9	434.1	434.4	430.6	427.5	424.9
110°	330.2	383.2	419.5	439.7	447.8	450.0	449.5	448.9





TEST NUMBER: P332008-930

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	308.8	362.9	403.6	429.5	444.3	451.4	453.6	453.7
115°	280.3	330.4	372.8	404.2	425.8	438.5	444.3	445.7
117.5°	259.8	303.0	341.0	372.9	395.5	410.0	418.2	420.2
120°	248.9	287.8	322.4	351.5	374.2	390.4	397.3	399.0
122.5°	240.4	275.6	307.6	334.7	354.9	369.4	377.0	379.2
125°	229.0	260.5	288.1	311.2	329.6	342.3	349.5	351.5
127.5°	219.2	247.1	272.1	293.1	309.5	320.3	326.9	328.6
130°	212.9	238.9	262.2	281.8	297.0	307.4	313.5	315.8
132.5°	207.2	231.0	252.7	271.4	285.8	296.1	301.5	303.1
135°	199.3	219.8	238.6	254.9	269.1	277.8	282.9	284.9
137.5°	192.2	209.0	225.2	239.5	251.3	260.1	264.4	265.8
140°	188.2	202.8	216.6	229.0	240.0	248.1	252.7	252.4
142.5°	184.3	196.8	208.8	219.6	228.9	236.1	240.2	239.9
145°	179.5	189.0	198.2	206.6	213.8	219.8	222.2	222.7
147.5°	175.6	183.2	190.6	196.6	202.0	206.1	208.3	208.6
150°	172.8	179.5	185.6	191.0	195.3	198.5	200.2	200.2
152.5°	170.3	176.0	181.4	186.0	189.3	192.2	193.3	193.3
155°	166.6	171.1	175.5	178.9	181.5	183.8	184.4	184.7
157.5°	162.5	166.3	169.7	172.4	174.6	176.3	176.8	176.8
160°	160.2	163.4	166.2	168.3	170.2	172.0	172.0	171.7
162.5°	157.4	160.1	162.8	164.6	165.9	167.4	167.4	167.1
165°	153.8	155.6	157.6	159.1	160.2	161.3	161.0	161.0
167.5°	150.7	152.1	153.2	154.3	154.7	155.6	155.3	155.3
170°	148.6	149.5	150.7	151.2	151.6	152.1	151.8	151.8
172.5°	146.8	147.5	148.4	148.7	148.8	149.4	148.9	148.6
175°	144.3	144.6	145.2	145.2	145.2	145.5	145.2	145.0
177.5°	142.8	143.0	143.2	143.2	143.0	143.2	142.8	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4

(END OF REPORT)