

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332018-930

Luminaire Tested: **S123DIP-S1000D805U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332018-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6074.9 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332018-930
CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR	0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57																											
	1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	53	49																											
	2	91	84	78	72	84	78	73	68	68	64	60	58	55	53	49	47	45	41																											
	3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35																											
	4	76	65	58	52	71	61	54	49	54	48	44	46	42	39	39	36	34	30																											
	5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	27																											
	6	65	53	44	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23																											
	7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23	21																											
	8	56	43	35	30	52	41	34	29	36	30	26	31	27	23	27	24	21	19																											
	9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17																											
	10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15																											

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12326	12326	12326	12326
5°	14699	12379	10970	12379
10°	18398	12316	9908	12316
15°	22566	12217	9225	12217
20°	26882	12062	8782	12062
25°	28544	11873	8684	11873
30°	24467	11737	8730	11737
35°	17015	11540	8821	11540
40°	12816	11311	8793	11311
45°	10641	10971	8681	10971
50°	9532	10275	8602	10275
55°	8912	9526	8496	9526
60°	8359	8742	8409	8742
65°	7857	7969	8140	7969
70°	7371	7091	7751	7091
75°	6600	6209	7107	6209
80°	5777	5089	6118	5089
85°	4520	3693	4113	3693



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	1.9
10°-20°	361.7	6.0
20°-30°	607.1	10.0
30°-40°	687.4	11.3
40°-50°	616.4	10.1
50°-60°	497.4	8.2
60°-70°	346.6	5.7
70°-80°	182.2	3.0
80°-90°	47.0	0.8
90°-100°	31.2	0.5
100°-110°	148.7	2.4
110°-120°	357.1	5.9
120°-130°	454.7	7.5
130°-140°	485.8	8.0
140°-150°	454.3	7.5
150°-160°	366.5	6.0
160°-170°	236.5	3.9
170°-180°	81.5	1.3
0°-30°	1081.6	17.8
0°-40°	1768.9	29.1
0°-60°	2882.8	47.5
0°-90°	3458.6	56.9
90°-120°	536.9	8.8
90°-150°	1931.8	31.8
90°-180°	2616.0	43.1
0°-180°	6074.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1145	1145	1145	1145	1145	
5°	1360	1146	1015	1146	1360	141
15°	2025	1096	828	1096	2025	585
25°	2403	1000	731	1000	2403	1054
35°	1295	878	671	878	1295	841
45°	699	721	570	721	699	553
55°	475	508	453	508	475	426
65°	308	313	320	313	308	307
75°	159	149	171	149	159	170
85°	37	30	33	30	37	44
90°	19	1	19	1	19	11
95°	24	39	24	39	24	20
105°	28	190	28	190	28	64
115°	375	356	375	356	375	346
125°	512	502	512	502	512	458
135°	632	625	632	625	632	487
145°	729	722	729	722	729	455
155°	794	795	794	795	794	366
165°	836	838	836	838	836	236
175°	855	858	855	858	855	81
180°	858	858	858	858	858	



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1215.2	1214.4	1212.1	1213.9	1210.4	1205.5	1205.0	1200.6	1187.7	1186.8	1183.3
5°	1360.4	1355.9	1355.4	1354.9	1347.0	1336.5	1316.5	1314.9	1288.3	1275.0	1258.8
7.5°	1548.3	1550.7	1542.5	1535.5	1511.7	1496.1	1474.6	1447.2	1414.5	1381.4	1359.3
10°	1683.3	1701.6	1678.9	1663.3	1648.9	1621.7	1590.1	1550.7	1511.3	1465.3	1430.3
12.5°	1828.0	1837.0	1832.4	1817.8	1795.4	1754.0	1697.9	1654.6	1618.3	1541.6	1510.6
15°	2025.0	2058.9	2037.3	1987.3	1988.4	1949.1	1875.8	1795.4	1752.6	1685.5	1594.0
17.5°	2235.0	2239.2	2230.0	2188.3	2160.6	2106.5	2038.9	1961.8	1875.3	1794.0	1697.0
20°	2346.8	2343.5	2324.1	2302.4	2254.7	2212.6	2138.8	2052.8	1941.8	1861.9	1756.0
22.5°	2409.0	2403.4	2394.2	2376.1	2336.4	2291.2	2224.9	2130.9	2025.3	1915.2	1792.8
25°	2403.4	2410.6	2411.7	2406.8	2392.9	2365.7	2313.5	2238.6	2133.2	1991.8	1864.2
27.5°	2185.9	2196.2	2225.8	2252.1	2281.5	2311.5	2307.5	2270.3	2192.3	2070.0	1914.1
30°	1968.5	1946.3	2001.2	2070.5	2117.7	2200.9	2247.5	2250.3	2206.4	2101.6	1949.5
32.5°	1666.6	1691.0	1715.3	1800.7	1903.7	1997.2	2089.9	2164.6	2173.2	2103.4	1970.4
35°	1294.9	1325.4	1369.8	1414.2	1525.2	1620.6	1783.7	1925.7	2038.9	2053.9	1972.3
37.5°	1043.5	1058.6	1086.6	1131.1	1203.7	1316.9	1443.1	1622.6	1786.6	1908.5	1913.8
40°	912.1	916.6	948.2	982.0	1040.8	1134.0	1247.7	1406.4	1602.8	1773.2	1844.2
42.5°	813.6	823.3	836.7	869.3	916.1	986.2	1091.9	1223.1	1403.1	1599.1	1738.1
45°	699.0	710.1	718.4	740.1	773.4	820.5	894.4	1014.2	1151.2	1353.7	1540.7
47.5°	623.4	624.3	630.5	646.8	669.4	704.8	757.0	834.0	959.8	1124.1	1316.0
50°	569.2	578.1	580.3	593.0	610.8	636.9	680.2	745.7	848.9	993.1	1169.5
52.5°	531.1	533.7	540.0	549.2	564.7	585.0	622.5	673.8	754.7	877.7	1039.9
55°	474.9	474.9	481.0	488.2	497.1	515.4	540.4	578.1	639.7	735.2	869.4
57.5°	423.0	425.7	430.1	432.3	439.9	451.9	472.8	501.4	547.4	620.9	727.6
60°	388.3	393.4	392.8	397.2	403.9	413.4	431.0	454.4	495.5	554.2	644.2
62.5°	358.2	357.8	357.8	363.1	369.7	378.7	390.3	410.4	445.3	497.4	574.0
65°	308.5	307.4	311.3	314.5	316.8	323.4	332.3	350.1	373.4	412.2	471.6
67.5°	264.3	261.1	263.2	264.3	268.1	273.3	281.6	292.6	311.1	342.3	387.0
70°	234.2	231.4	230.8	231.9	235.2	239.1	245.2	255.8	273.0	297.9	330.7
72.5°	203.1	201.1	201.1	203.5	205.0	207.6	211.9	221.6	235.2	254.0	284.5
75°	158.7	158.7	158.7	159.2	160.9	163.1	166.4	171.5	182.0	195.3	215.8
77.5°	119.0	118.9	118.1	118.1	120.5	121.5	122.3	126.9	132.8	141.8	156.8
80°	93.2	90.4	91.6	93.2	94.3	94.9	96.5	97.7	102.6	107.6	118.1
82.5°	69.2	66.9	67.1	69.7	69.9	70.4	72.2	73.7	75.6	80.1	85.8
85°	36.6	36.6	37.2	37.2	37.7	37.2	38.8	39.4	39.4	42.2	45.5
87.5°	17.1	16.2	16.6	17.0	16.5	16.8	17.1	17.5	17.9	18.2	18.3
90°	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5	15.9	15.3	13.5
92.5°	21.2	21.0	20.8	20.6	20.5	20.0	19.0	18.1	17.2	16.3	14.9
95°	24.2	24.2	24.2	24.2	24.2	23.7	22.7	21.8	20.8	19.7	18.2
97.5°	26.3	26.1	26.0	25.8	25.7	25.0	23.9	22.8	21.7	20.5	30.7
100°	26.7	26.7	26.5	26.3	26.2	25.6	24.5	23.3	22.2	21.0	43.1
102.5°	27.3	27.0	26.7	26.5	26.3	27.9	31.4	34.9	38.4	41.9	66.0
105°	28.0	27.8	27.5	27.2	26.9	39.3	64.4	89.4	114.5	139.6	152.3
107.5°	88.1	107.0	125.9	144.8	163.6	182.3	200.7	219.1	237.5	255.8	253.8
110°	175.3	195.5	215.8	236.0	256.3	268.8	273.5	278.1	282.8	287.5	285.9



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	300.8	305.0	309.2	313.6	317.8	319.9	319.8	319.8	319.7	319.6	318.0
115°	374.8	374.2	373.7	373.1	372.5	371.5	370.1	368.7	367.3	365.9	364.6
117.5°	416.4	416.2	416.1	416.0	415.9	415.2	414.2	413.0	411.9	410.7	410.1
120°	444.9	444.9	444.9	444.9	444.9	444.3	443.2	442.1	440.9	439.8	439.4
122.5°	473.0	472.9	472.7	472.6	472.5	472.1	471.2	470.4	469.7	468.9	468.3
125°	512.5	512.2	511.9	511.6	511.4	511.0	510.8	510.5	510.2	509.9	509.3
127.5°	550.5	550.7	551.1	551.3	551.5	551.5	551.1	550.6	550.2	549.7	549.0
130°	574.9	575.2	575.5	575.8	576.1	575.9	575.4	574.8	574.2	573.6	573.1
132.5°	597.4	597.8	598.2	598.6	598.9	598.8	598.3	597.7	597.2	596.6	596.1
135°	631.7	632.1	632.5	632.9	633.3	633.3	632.9	632.5	632.1	631.7	631.1
137.5°	663.9	664.2	664.5	664.8	665.0	664.9	664.1	663.5	662.8	662.1	661.8
140°	683.3	683.5	683.9	684.1	684.4	684.3	683.7	683.1	682.6	682.0	681.6
142.5°	701.2	701.6	701.9	702.3	702.7	702.7	702.2	701.8	701.3	700.9	700.4
145°	728.6	728.6	728.6	728.6	728.6	728.4	728.1	727.8	727.6	727.2	727.0
147.5°	748.9	749.6	750.2	750.9	751.5	751.7	751.5	751.1	750.9	750.6	750.3
150°	764.3	764.7	765.1	765.5	766.0	766.0	765.7	765.4	765.2	764.9	764.6
152.5°	776.5	777.1	777.8	778.4	779.1	779.2	778.6	778.1	777.6	777.1	777.0
155°	793.5	794.4	795.2	796.1	797.0	797.0	796.3	795.7	794.9	794.2	794.0
157.5°	808.0	809.1	810.2	811.3	812.4	812.5	811.6	810.8	810.0	809.1	809.3
160°	817.2	818.2	819.1	820.1	821.1	821.2	820.4	819.5	818.6	817.7	817.9
162.5°	825.8	826.7	827.5	828.4	829.3	829.2	828.3	827.4	826.4	825.4	825.6
165°	836.3	837.2	838.2	839.3	840.2	840.2	839.0	837.9	836.7	835.6	835.8
167.5°	843.8	844.9	846.0	847.2	848.3	848.3	847.2	846.0	844.9	843.8	843.8
170°	848.4	849.5	850.6	851.7	852.9	852.9	851.7	850.6	849.5	848.4	848.4
172.5°	850.9	852.2	853.5	854.7	855.9	856.0	854.8	853.7	852.6	851.4	851.3
175°	854.8	855.9	857.0	858.2	859.2	859.3	858.3	857.4	856.4	855.4	855.2
177.5°	855.9	857.0	858.2	859.3	860.5	860.5	859.7	858.8	857.9	856.9	856.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1180.6	1177.0	1173.5	1167.3	1162.0	1154.5	1152.2	1149.6	1141.6	1134.5	1129.1
5°	1252.7	1239.4	1220.0	1202.2	1187.8	1168.4	1157.3	1145.7	1129.0	1114.0	1101.9
7.5°	1328.2	1302.0	1271.9	1239.2	1208.8	1179.5	1155.8	1134.8	1111.5	1089.4	1072.2
10°	1388.1	1350.4	1308.2	1262.7	1223.9	1186.2	1154.5	1126.8	1096.8	1070.7	1049.1
12.5°	1456.5	1400.5	1342.4	1287.1	1241.2	1188.9	1150.6	1115.2	1081.3	1049.9	1025.6
15°	1537.3	1466.3	1397.6	1321.5	1251.6	1186.2	1140.7	1096.3	1056.9	1024.7	993.7
17.5°	1611.0	1530.6	1439.9	1347.5	1263.1	1185.5	1121.9	1071.6	1022.4	983.0	952.0
20°	1652.8	1561.2	1458.6	1362.6	1269.4	1182.8	1113.0	1053.0	999.7	958.1	923.2
22.5°	1688.7	1581.6	1475.4	1372.8	1268.9	1175.7	1096.5	1034.9	977.1	936.4	899.2
25°	1726.0	1597.8	1491.3	1370.9	1255.0	1158.5	1069.7	999.7	942.1	894.4	856.1
27.5°	1757.9	1596.8	1470.3	1340.8	1233.0	1136.2	1041.5	966.5	905.2	853.4	814.6
30°	1779.2	1599.0	1448.6	1320.5	1211.7	1111.8	1019.7	944.3	880.0	827.2	790.6
32.5°	1792.6	1597.6	1428.6	1292.0	1177.9	1089.6	996.2	918.1	852.0	800.1	764.8
35°	1800.3	1587.9	1394.2	1233.3	1123.5	1037.5	959.3	878.2	808.9	760.7	720.7
37.5°	1784.8	1567.3	1354.3	1176.7	1056.5	971.8	906.0	837.0	770.6	717.5	683.1
40°	1760.4	1554.0	1323.2	1136.8	1010.3	928.7	872.7	805.0	739.6	689.1	656.9
42.5°	1713.8	1526.9	1289.1	1092.4	962.4	880.8	829.2	772.7	710.7	663.3	631.1
45°	1600.0	1468.0	1237.8	1025.8	891.5	807.2	761.7	720.7	664.6	618.6	590.8
47.5°	1442.3	1379.3	1163.7	955.6	817.7	736.5	689.3	656.2	615.3	578.1	551.5
50°	1332.6	1306.6	1113.5	907.7	768.4	689.1	643.6	613.6	584.2	547.1	522.6
52.5°	1206.2	1222.2	1054.9	857.9	718.3	640.3	597.5	573.6	546.9	516.4	495.1
55°	1028.1	1086.3	953.7	774.5	643.6	569.2	528.7	507.6	492.1	469.4	451.0
57.5°	861.3	935.4	844.3	688.5	570.2	506.1	467.2	444.3	434.3	422.4	408.0
60°	762.3	835.5	766.2	630.8	521.0	459.9	425.5	406.1	396.2	387.8	375.6
62.5°	674.0	748.1	689.8	572.3	472.5	416.0	386.0	367.0	359.3	355.0	344.5
65°	552.6	616.4	577.6	481.0	403.3	353.4	326.2	312.9	305.7	304.0	297.3
67.5°	449.7	498.3	470.0	399.0	337.9	294.7	271.7	260.3	254.8	254.2	249.2
70°	382.3	427.8	406.1	341.8	289.0	255.2	235.2	225.3	221.9	221.4	218.6
72.5°	329.9	361.6	344.4	290.7	250.0	219.2	204.6	194.2	190.4	191.2	189.3
75°	244.1	268.0	258.0	220.8	188.1	168.1	155.9	149.3	145.9	147.6	145.4
77.5°	175.6	190.8	181.7	156.0	135.8	121.4	112.4	108.3	105.3	105.2	104.2
80°	132.6	141.5	136.5	120.9	104.3	92.1	84.9	82.1	80.5	79.9	79.3
82.5°	94.4	102.0	96.1	85.4	74.1	66.8	62.7	59.0	57.8	58.1	57.6
85°	47.7	50.5	48.3	41.6	37.2	33.8	31.6	29.9	28.9	29.4	28.3
87.5°	18.8	18.8	17.1	15.0	13.9	12.2	12.0	10.8	10.2	10.4	10.3
90°	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7	2.0	3.5	4.9
92.5°	13.5	12.1	10.8	10.3	10.7	11.1	11.5	11.8	11.5	11.1	10.7
95°	16.6	15.1	13.5	15.7	21.4	27.2	33.1	38.9	33.1	27.2	21.4
97.5°	40.9	51.1	61.3	67.8	70.4	73.0	75.6	78.1	75.6	73.0	70.4
100°	65.2	87.3	109.4	119.0	116.2	113.4	110.6	107.7	110.6	113.4	116.2
102.5°	90.2	114.4	138.5	149.5	147.5	145.4	143.4	141.4	143.4	145.4	147.5
105°	165.1	177.8	190.6	196.2	194.6	193.1	191.5	190.0	191.5	193.1	194.6
107.5°	251.8	249.8	247.8	246.1	244.9	243.7	242.5	241.2	242.5	243.7	244.9
110°	284.4	282.8	281.2	279.9	278.8	277.6	276.5	275.3	276.5	277.6	278.8



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.5	315.0	313.3	312.1	311.0	310.1	309.0	308.0	309.0	310.1	311.0
115°	363.3	362.1	360.8	359.7	358.9	358.0	357.2	356.3	357.2	358.0	358.9
117.5°	409.4	408.8	408.1	407.2	406.3	405.2	404.1	403.1	404.1	405.2	406.3
120°	439.0	438.5	438.1	437.2	435.9	434.7	433.4	432.2	433.4	434.7	435.9
122.5°	467.8	467.2	466.7	465.9	464.9	463.8	462.8	461.7	462.8	463.8	464.9
125°	508.7	508.3	507.7	506.8	505.6	504.5	503.4	502.3	503.4	504.5	505.6
127.5°	548.4	547.6	547.0	546.1	544.9	543.8	542.7	541.5	542.7	543.8	544.9
130°	572.5	571.9	571.4	570.5	569.4	568.3	567.1	566.0	567.1	568.3	569.4
132.5°	595.7	595.3	594.8	594.0	592.9	591.7	590.6	589.5	590.6	591.7	592.9
135°	630.6	630.0	629.4	628.7	627.9	627.0	626.1	625.3	626.1	627.0	627.9
137.5°	661.5	661.2	660.9	660.1	659.1	658.0	657.0	655.9	657.0	658.0	659.1
140°	681.2	680.8	680.3	679.7	678.8	678.0	677.1	676.3	677.1	678.0	678.8
142.5°	700.0	699.6	699.2	698.5	697.7	696.8	696.0	695.1	696.0	696.8	697.7
145°	726.7	726.4	726.1	725.5	724.5	723.5	722.5	721.5	722.5	723.5	724.5
147.5°	750.0	749.7	749.5	749.0	748.4	747.7	747.1	746.4	747.1	747.7	748.4
150°	764.3	764.0	763.8	763.4	763.0	762.5	762.1	761.7	762.1	762.5	763.0
152.5°	776.7	776.6	776.4	776.2	776.1	775.8	775.7	775.4	775.7	775.8	776.1
155°	793.9	793.8	793.6	793.7	794.0	794.3	794.6	794.8	794.6	794.3	794.0
157.5°	809.4	809.5	809.7	809.8	809.8	809.8	809.8	809.8	809.8	809.8	809.8
160°	818.1	818.2	818.3	818.5	818.6	818.8	818.9	819.0	818.9	818.8	818.6
162.5°	825.7	825.8	826.0	826.2	826.6	827.0	827.4	827.7	827.4	827.0	826.6
165°	835.9	836.1	836.2	836.5	836.9	837.3	837.7	838.2	837.7	837.3	836.9
167.5°	843.8	843.8	843.8	844.1	844.7	845.2	845.8	846.4	845.8	845.2	844.7
170°	848.4	848.4	848.4	848.6	849.2	849.8	850.4	850.9	850.4	849.8	849.2
172.5°	851.2	851.1	851.0	851.3	851.9	852.6	853.3	853.9	853.3	852.6	851.9
175°	855.1	854.9	854.8	855.1	855.8	856.6	857.2	857.9	857.2	856.6	855.8
177.5°	856.7	856.6	856.5	856.7	857.3	857.9	858.4	858.9	858.4	857.9	857.3
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1126.0	1122.9	1118.5	1111.8	1106.5	1098.0	1098.0	1099.4	1099.4	1098.9	1098.0
5°	1091.8	1083.5	1073.6	1061.9	1049.7	1037.5	1035.3	1030.9	1027.5	1025.2	1022.5
7.5°	1055.8	1041.1	1026.5	1010.2	995.3	983.0	974.4	967.4	962.8	957.9	954.4
10°	1031.4	1013.1	995.9	978.7	959.8	944.9	935.4	928.7	923.7	919.3	917.1
12.5°	1002.5	981.5	962.6	946.2	925.6	910.2	901.2	898.1	892.3	882.9	878.0
15°	960.3	940.9	918.2	893.2	883.2	864.4	853.9	848.9	845.5	838.3	836.1
17.5°	924.3	898.9	873.3	854.8	836.2	820.9	815.0	808.8	804.4	798.5	796.7
20°	895.4	872.7	849.4	829.4	810.0	793.4	788.4	783.9	779.5	776.7	774.5
22.5°	866.2	843.4	824.1	805.4	784.7	773.8	768.4	763.5	760.4	758.6	756.3
25°	825.0	805.0	783.4	766.7	750.1	742.9	739.6	736.8	734.6	731.8	731.2
27.5°	788.1	766.4	748.9	733.4	721.4	715.3	712.2	710.8	711.3	712.2	712.9
30°	760.7	740.7	726.3	712.9	701.8	696.3	695.7	695.7	698.0	698.5	699.6
32.5°	735.3	718.9	704.5	691.6	683.2	679.4	681.5	681.5	683.3	684.8	686.7
35°	698.5	684.0	672.9	661.9	654.7	656.3	657.5	658.5	661.3	664.6	666.9
37.5°	663.3	650.8	639.3	630.6	627.3	630.2	632.9	635.3	638.5	641.0	643.3
40°	638.1	628.6	617.5	609.8	610.8	612.5	614.7	617.5	620.3	621.9	624.2
42.5°	614.5	604.6	596.2	589.8	591.3	593.5	594.8	596.2	599.4	602.4	603.7
45°	578.7	570.9	563.1	559.2	560.4	561.5	562.6	564.3	567.0	569.2	569.8
47.5°	538.3	533.0	527.7	524.0	525.7	525.3	526.8	530.3	531.2	532.5	535.6
50°	512.7	507.6	501.6	500.4	500.4	500.4	501.0	505.4	505.4	507.6	509.9
52.5°	484.2	481.0	477.1	475.2	474.3	474.3	476.5	478.8	479.7	482.8	485.0
55°	442.2	438.9	435.5	433.8	432.8	433.8	438.3	439.4	442.2	443.8	445.5
57.5°	398.4	395.8	393.1	392.2	392.0	393.5	395.9	399.3	399.9	405.0	407.6
60°	369.5	365.6	363.4	363.4	362.3	367.3	366.2	371.7	372.8	376.2	380.0
62.5°	339.7	334.5	333.6	333.6	335.3	336.6	338.2	340.6	343.6	347.7	350.7
65°	291.8	289.0	292.9	292.4	291.3	294.6	294.6	297.3	300.7	304.6	310.7
67.5°	246.5	245.0	245.3	245.3	247.0	248.9	250.5	252.9	256.9	261.0	265.0
70°	215.8	217.5	214.7	217.0	218.6	219.2	220.3	223.6	228.0	230.8	235.2
72.5°	186.1	186.0	186.3	187.2	188.8	189.9	190.9	194.8	199.6	201.9	205.5
75°	143.2	142.6	144.2	144.2	147.0	148.1	149.3	150.9	155.3	158.7	161.4
77.5°	104.5	105.2	104.8	106.7	106.0	106.2	109.7	111.3	111.8	118.3	119.8
80°	78.8	79.9	80.5	81.0	81.5	80.5	84.3	86.0	86.0	89.8	92.6
82.5°	56.6	57.2	58.7	59.3	59.4	60.5	60.8	62.0	63.3	65.1	68.6
85°	28.3	29.9	30.5	29.9	30.5	29.4	31.1	31.6	32.2	32.2	32.2
87.5°	10.1	10.9	10.8	11.7	11.6	12.4	12.5	11.7	11.8	13.3	11.6
90°	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5	17.0	17.5	18.0
92.5°	10.3	10.8	12.1	13.5	14.9	16.3	17.2	18.1	19.0	20.0	20.5
95°	15.7	13.5	15.1	16.6	18.2	19.7	20.8	21.8	22.7	23.7	24.2
97.5°	67.8	61.3	51.1	40.9	30.7	20.5	21.7	22.8	23.9	25.0	25.7
100°	119.0	109.4	87.3	65.2	43.1	21.0	22.2	23.3	24.5	25.6	26.2
102.5°	149.5	138.5	114.4	90.2	66.0	41.9	38.4	34.9	31.4	27.9	26.3
105°	196.2	190.6	177.8	165.1	152.3	139.6	114.5	89.4	64.4	39.3	26.9
107.5°	246.1	247.8	249.8	251.8	253.8	255.8	237.5	219.1	200.7	182.3	163.6
110°	279.9	281.2	282.8	284.4	285.9	287.5	282.8	278.1	273.5	268.8	256.3



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	312.1	313.3	315.0	316.5	318.0	319.6	319.7	319.8	319.8	319.9	317.8
115°	359.7	360.8	362.1	363.3	364.6	365.9	367.3	368.7	370.1	371.5	372.5
117.5°	407.2	408.1	408.8	409.4	410.1	410.7	411.9	413.0	414.2	415.2	415.9
120°	437.2	438.1	438.5	439.0	439.4	439.8	440.9	442.1	443.2	444.3	444.9
122.5°	465.9	466.7	467.2	467.8	468.3	468.9	469.7	470.4	471.2	472.1	472.5
125°	506.8	507.7	508.3	508.7	509.3	509.9	510.2	510.5	510.8	511.0	511.4
127.5°	546.1	547.0	547.6	548.4	549.0	549.7	550.2	550.6	551.1	551.5	551.5
130°	570.5	571.4	571.9	572.5	573.1	573.6	574.2	574.8	575.4	575.9	576.1
132.5°	594.0	594.8	595.3	595.7	596.1	596.6	597.2	597.7	598.3	598.8	598.9
135°	628.7	629.4	630.0	630.6	631.1	631.7	632.1	632.5	632.9	633.3	633.3
137.5°	660.1	660.9	661.2	661.5	661.8	662.1	662.8	663.5	664.1	664.9	665.0
140°	679.7	680.3	680.8	681.2	681.6	682.0	682.6	683.1	683.7	684.3	684.4
142.5°	698.5	699.2	699.6	700.0	700.4	700.9	701.3	701.8	702.2	702.7	702.7
145°	725.5	726.1	726.4	726.7	727.0	727.2	727.6	727.8	728.1	728.4	728.6
147.5°	749.0	749.5	749.7	750.0	750.3	750.6	750.9	751.1	751.5	751.7	751.5
150°	763.4	763.8	764.0	764.3	764.6	764.9	765.2	765.4	765.7	766.0	766.0
152.5°	776.2	776.4	776.6	776.7	777.0	777.1	777.6	778.1	778.6	779.2	779.1
155°	793.7	793.6	793.8	793.9	794.0	794.2	794.9	795.7	796.3	797.0	797.0
157.5°	809.8	809.7	809.5	809.4	809.3	809.1	810.0	810.8	811.6	812.5	812.4
160°	818.5	818.3	818.2	818.1	817.9	817.7	818.6	819.5	820.4	821.2	821.1
162.5°	826.2	826.0	825.8	825.7	825.6	825.4	826.4	827.4	828.3	829.2	829.3
165°	836.5	836.2	836.1	835.9	835.8	835.6	836.7	837.9	839.0	840.2	840.2
167.5°	844.1	843.8	843.8	843.8	843.8	843.8	844.9	846.0	847.2	848.3	848.3
170°	848.6	848.4	848.4	848.4	848.4	848.4	849.5	850.6	851.7	852.9	852.9
172.5°	851.3	851.0	851.1	851.2	851.3	851.4	852.6	853.7	854.8	856.0	855.9
175°	855.1	854.8	854.9	855.1	855.2	855.4	856.4	857.4	858.3	859.3	859.2
177.5°	856.7	856.5	856.6	856.7	856.8	856.9	857.9	858.8	859.7	860.5	860.5
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1094.9	1094.5	1097.6	1095.4	1097.6	1094.5	1094.9	1098.0	1098.9	1099.4	1099.4
5°	1019.2	1020.8	1015.3	1015.3	1015.3	1020.8	1019.2	1022.5	1025.2	1027.5	1030.9
7.5°	951.7	949.3	949.5	946.5	949.5	949.3	951.7	954.4	957.9	962.8	967.4
10°	910.4	907.1	906.0	906.5	906.0	907.1	910.4	917.1	919.3	923.7	928.7
12.5°	876.3	875.6	868.3	868.4	868.3	875.6	876.3	878.0	882.9	892.3	898.1
15°	836.1	825.6	824.4	827.8	824.4	825.6	836.1	836.1	838.3	845.5	848.9
17.5°	795.8	790.3	790.6	789.0	790.6	790.3	795.8	796.7	798.5	804.4	808.8
20°	774.5	771.2	770.6	766.7	770.6	771.2	774.5	774.5	776.7	779.5	783.9
22.5°	755.0	753.9	754.2	749.9	754.2	753.9	755.0	756.3	758.6	760.4	763.5
25°	730.7	733.4	731.2	731.2	731.2	733.4	730.7	731.2	731.8	734.6	736.8
27.5°	714.3	714.1	713.1	713.1	713.1	714.1	714.3	712.9	712.2	711.3	710.8
30°	701.8	701.2	702.4	702.4	702.4	701.2	701.8	699.6	698.5	698.0	695.7
32.5°	689.4	690.2	690.4	690.8	690.4	690.2	689.4	686.7	684.8	683.3	681.5
35°	670.2	670.7	672.5	671.3	672.5	670.7	670.2	666.9	664.6	661.3	658.5
37.5°	644.2	646.8	646.2	647.1	646.2	646.8	644.2	643.3	641.0	638.5	635.3
40°	624.7	626.4	625.8	625.8	625.8	626.4	624.7	624.2	621.9	620.3	617.5
42.5°	604.7	605.9	604.5	603.6	604.5	605.9	604.7	603.7	602.4	599.4	596.2
45°	572.0	570.9	572.6	570.3	572.6	570.9	572.0	569.8	569.2	567.0	564.3
47.5°	535.4	536.5	537.0	538.6	537.0	536.5	535.4	535.6	532.5	531.2	530.3
50°	510.9	514.3	514.3	513.7	514.3	514.3	510.9	509.9	507.6	505.4	505.4
52.5°	487.0	488.5	490.8	490.6	490.8	488.5	487.0	485.0	482.8	479.7	478.8
55°	450.0	451.0	452.2	452.7	452.2	451.0	450.0	445.5	443.8	442.2	439.4
57.5°	411.6	411.1	413.8	414.6	413.8	411.1	411.6	407.6	405.0	399.9	399.3
60°	384.5	384.5	388.9	390.6	388.9	384.5	384.5	380.0	376.2	372.8	371.7
62.5°	355.6	357.4	361.8	359.5	361.8	357.4	355.6	350.7	347.7	343.6	340.6
65°	313.5	317.9	317.3	319.6	317.3	317.9	313.5	310.7	304.6	300.7	297.3
67.5°	269.4	272.1	276.1	276.5	276.1	272.1	269.4	265.0	261.0	256.9	252.9
70°	239.7	242.5	244.7	246.3	244.7	242.5	239.7	235.2	230.8	228.0	223.6
72.5°	210.8	212.3	217.6	215.2	217.6	212.3	210.8	205.5	201.9	199.6	194.8
75°	165.3	169.2	172.5	170.9	172.5	169.2	165.3	161.4	158.7	155.3	150.9
77.5°	122.3	126.1	127.7	126.3	127.7	126.1	122.3	119.8	118.3	111.8	111.3
80°	96.5	96.0	99.3	98.7	99.3	96.0	96.5	92.6	89.8	86.0	86.0
82.5°	70.8	70.3	71.8	72.2	71.8	70.3	70.8	68.6	65.1	63.3	62.0
85°	34.4	36.0	33.8	33.3	33.8	36.0	34.4	32.2	32.2	32.2	31.6
87.5°	11.7	11.7	11.3	10.9	11.3	11.7	11.7	11.6	13.3	11.8	11.7
90°	18.3	18.6	18.8	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5
92.5°	20.6	20.8	21.0	21.2	21.0	20.8	20.6	20.5	20.0	19.0	18.1
95°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	23.7	22.7	21.8
97.5°	25.8	26.0	26.1	26.3	26.1	26.0	25.8	25.7	25.0	23.9	22.8
100°	26.3	26.5	26.7	26.7	26.7	26.5	26.3	26.2	25.6	24.5	23.3
102.5°	26.5	26.7	27.0	27.3	27.0	26.7	26.5	26.3	27.9	31.4	34.9
105°	27.2	27.5	27.8	28.0	27.8	27.5	27.2	26.9	39.3	64.4	89.4
107.5°	144.8	125.9	107.0	88.1	107.0	125.9	144.8	163.6	182.3	200.7	219.1
110°	236.0	215.8	195.5	175.3	195.5	215.8	236.0	256.3	268.8	273.5	278.1



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	313.6	309.2	305.0	300.8	305.0	309.2	313.6	317.8	319.9	319.8	319.8
115°	373.1	373.7	374.2	374.8	374.2	373.7	373.1	372.5	371.5	370.1	368.7
117.5°	416.0	416.1	416.2	416.4	416.2	416.1	416.0	415.9	415.2	414.2	413.0
120°	444.9	444.9	444.9	444.9	444.9	444.9	444.9	444.9	444.3	443.2	442.1
122.5°	472.6	472.7	472.9	473.0	472.9	472.7	472.6	472.5	472.1	471.2	470.4
125°	511.6	511.9	512.2	512.5	512.2	511.9	511.6	511.4	511.0	510.8	510.5
127.5°	551.3	551.1	550.7	550.5	550.7	551.1	551.3	551.5	551.5	551.1	550.6
130°	575.8	575.5	575.2	574.9	575.2	575.5	575.8	576.1	575.9	575.4	574.8
132.5°	598.6	598.2	597.8	597.4	597.8	598.2	598.6	598.9	598.8	598.3	597.7
135°	632.9	632.5	632.1	631.7	632.1	632.5	632.9	633.3	633.3	632.9	632.5
137.5°	664.8	664.5	664.2	663.9	664.2	664.5	664.8	665.0	664.9	664.1	663.5
140°	684.1	683.9	683.5	683.3	683.5	683.9	684.1	684.4	684.3	683.7	683.1
142.5°	702.3	701.9	701.6	701.2	701.6	701.9	702.3	702.7	702.7	702.2	701.8
145°	728.6	728.6	728.6	728.6	728.6	728.6	728.6	728.6	728.4	728.1	727.8
147.5°	750.9	750.2	749.6	748.9	749.6	750.2	750.9	751.5	751.7	751.5	751.1
150°	765.5	765.1	764.7	764.3	764.7	765.1	765.5	766.0	766.0	765.7	765.4
152.5°	778.4	777.8	777.1	776.5	777.1	777.8	778.4	779.1	779.2	778.6	778.1
155°	796.1	795.2	794.4	793.5	794.4	795.2	796.1	797.0	797.0	796.3	795.7
157.5°	811.3	810.2	809.1	808.0	809.1	810.2	811.3	812.4	812.5	811.6	810.8
160°	820.1	819.1	818.2	817.2	818.2	819.1	820.1	821.1	821.2	820.4	819.5
162.5°	828.4	827.5	826.7	825.8	826.7	827.5	828.4	829.3	829.2	828.3	827.4
165°	839.3	838.2	837.2	836.3	837.2	838.2	839.3	840.2	840.2	839.0	837.9
167.5°	847.2	846.0	844.9	843.8	844.9	846.0	847.2	848.3	848.3	847.2	846.0
170°	851.7	850.6	849.5	848.4	849.5	850.6	851.7	852.9	852.9	851.7	850.6
172.5°	854.7	853.5	852.2	850.9	852.2	853.5	854.7	855.9	856.0	854.8	853.7
175°	858.2	857.0	855.9	854.8	855.9	857.0	858.2	859.2	859.3	858.3	857.4
177.5°	859.3	858.2	857.0	855.9	857.0	858.2	859.3	860.5	860.5	859.7	858.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1098.0	1098.0	1106.5	1111.8	1118.5	1122.9	1126.0	1129.1	1134.5	1141.6	1149.6
5°	1035.3	1037.5	1049.7	1061.9	1073.6	1083.5	1091.8	1101.9	1114.0	1129.0	1145.7
7.5°	974.4	983.0	995.3	1010.2	1026.5	1041.1	1055.8	1072.2	1089.4	1111.5	1134.8
10°	935.4	944.9	959.8	978.7	995.9	1013.1	1031.4	1049.1	1070.7	1096.8	1126.8
12.5°	901.2	910.2	925.6	946.2	962.6	981.5	1002.5	1025.6	1049.9	1081.3	1115.2
15°	853.9	864.4	883.2	893.2	918.2	940.9	960.3	993.7	1024.7	1056.9	1096.3
17.5°	815.0	820.9	836.2	854.8	873.3	898.9	924.3	952.0	983.0	1022.4	1071.6
20°	788.4	793.4	810.0	829.4	849.4	872.7	895.4	923.2	958.1	999.7	1053.0
22.5°	768.4	773.8	784.7	805.4	824.1	843.4	866.2	899.2	936.4	977.1	1034.9
25°	739.6	742.9	750.1	766.7	783.4	805.0	825.0	856.1	894.4	942.1	999.7
27.5°	712.2	715.3	721.4	733.4	748.9	766.4	788.1	814.6	853.4	905.2	966.5
30°	695.7	696.3	701.8	712.9	726.3	740.7	760.7	790.6	827.2	880.0	944.3
32.5°	681.5	679.4	683.2	691.6	704.5	718.9	735.3	764.8	800.1	852.0	918.1
35°	657.5	656.3	654.7	661.9	672.9	684.0	698.5	720.7	760.7	808.9	878.2
37.5°	632.9	630.2	627.3	630.6	639.3	650.8	663.3	683.1	717.5	770.6	837.0
40°	614.7	612.5	610.8	609.8	617.5	628.6	638.1	656.9	689.1	739.6	805.0
42.5°	594.8	593.5	591.3	589.8	596.2	604.6	614.5	631.1	663.3	710.7	772.7
45°	562.6	561.5	560.4	559.2	563.1	570.9	578.7	590.8	618.6	664.6	720.7
47.5°	526.8	525.3	525.7	524.0	527.7	533.0	538.3	551.5	578.1	615.3	656.2
50°	501.0	500.4	500.4	500.4	501.6	507.6	512.7	522.6	547.1	584.2	613.6
52.5°	476.5	474.3	474.3	475.2	477.1	481.0	484.2	495.1	516.4	546.9	573.6
55°	438.3	433.8	432.8	433.8	435.5	438.9	442.2	451.0	469.4	492.1	507.6
57.5°	395.9	393.5	392.0	392.2	393.1	395.8	398.4	408.0	422.4	434.3	444.3
60°	366.2	367.3	362.3	363.4	363.4	365.6	369.5	375.6	387.8	396.2	406.1
62.5°	338.2	336.6	335.3	333.6	333.6	334.5	339.7	344.5	355.0	359.3	367.0
65°	294.6	294.6	291.3	292.4	292.9	289.0	291.8	297.3	304.0	305.7	312.9
67.5°	250.5	248.9	247.0	245.3	245.3	245.0	246.5	249.2	254.2	254.8	260.3
70°	220.3	219.2	218.6	217.0	214.7	217.5	215.8	218.6	221.4	221.9	225.3
72.5°	190.9	189.9	188.8	187.2	186.3	186.0	186.1	189.3	191.2	190.4	194.2
75°	149.3	148.1	147.0	144.2	144.2	142.6	143.2	145.4	147.6	145.9	149.3
77.5°	109.7	106.2	106.0	106.7	104.8	105.2	104.5	104.2	105.2	105.3	108.3
80°	84.3	80.5	81.5	81.0	80.5	79.9	78.8	79.3	79.9	80.5	82.1
82.5°	60.8	60.5	59.4	59.3	58.7	57.2	56.6	57.6	58.1	57.8	59.0
85°	31.1	29.4	30.5	29.9	30.5	29.9	28.3	28.3	29.4	28.9	29.9
87.5°	12.5	12.4	11.6	11.7	10.8	10.9	10.1	10.3	10.4	10.2	10.8
90°	15.9	15.3	13.5	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7
92.5°	17.2	16.3	14.9	13.5	12.1	10.8	10.3	10.7	11.1	11.5	11.8
95°	20.8	19.7	18.2	16.6	15.1	13.5	15.7	21.4	27.2	33.1	38.9
97.5°	21.7	20.5	30.7	40.9	51.1	61.3	67.8	70.4	73.0	75.6	78.1
100°	22.2	21.0	43.1	65.2	87.3	109.4	119.0	116.2	113.4	110.6	107.7
102.5°	38.4	41.9	66.0	90.2	114.4	138.5	149.5	147.5	145.4	143.4	141.4
105°	114.5	139.6	152.3	165.1	177.8	190.6	196.2	194.6	193.1	191.5	190.0
107.5°	237.5	255.8	253.8	251.8	249.8	247.8	246.1	244.9	243.7	242.5	241.2
110°	282.8	287.5	285.9	284.4	282.8	281.2	279.9	278.8	277.6	276.5	275.3



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	319.7	319.6	318.0	316.5	315.0	313.3	312.1	311.0	310.1	309.0	308.0
115°	367.3	365.9	364.6	363.3	362.1	360.8	359.7	358.9	358.0	357.2	356.3
117.5°	411.9	410.7	410.1	409.4	408.8	408.1	407.2	406.3	405.2	404.1	403.1
120°	440.9	439.8	439.4	439.0	438.5	438.1	437.2	435.9	434.7	433.4	432.2
122.5°	469.7	468.9	468.3	467.8	467.2	466.7	465.9	464.9	463.8	462.8	461.7
125°	510.2	509.9	509.3	508.7	508.3	507.7	506.8	505.6	504.5	503.4	502.3
127.5°	550.2	549.7	549.0	548.4	547.6	547.0	546.1	544.9	543.8	542.7	541.5
130°	574.2	573.6	573.1	572.5	571.9	571.4	570.5	569.4	568.3	567.1	566.0
132.5°	597.2	596.6	596.1	595.7	595.3	594.8	594.0	592.9	591.7	590.6	589.5
135°	632.1	631.7	631.1	630.6	630.0	629.4	628.7	627.9	627.0	626.1	625.3
137.5°	662.8	662.1	661.8	661.5	661.2	660.9	660.1	659.1	658.0	657.0	655.9
140°	682.6	682.0	681.6	681.2	680.8	680.3	679.7	678.8	678.0	677.1	676.3
142.5°	701.3	700.9	700.4	700.0	699.6	699.2	698.5	697.7	696.8	696.0	695.1
145°	727.6	727.2	727.0	726.7	726.4	726.1	725.5	724.5	723.5	722.5	721.5
147.5°	750.9	750.6	750.3	750.0	749.7	749.5	749.0	748.4	747.7	747.1	746.4
150°	765.2	764.9	764.6	764.3	764.0	763.8	763.4	763.0	762.5	762.1	761.7
152.5°	777.6	777.1	777.0	776.7	776.6	776.4	776.2	776.1	775.8	775.7	775.4
155°	794.9	794.2	794.0	793.9	793.8	793.6	793.7	794.0	794.3	794.6	794.8
157.5°	810.0	809.1	809.3	809.4	809.5	809.7	809.8	809.8	809.8	809.8	809.8
160°	818.6	817.7	817.9	818.1	818.2	818.3	818.5	818.6	818.8	818.9	819.0
162.5°	826.4	825.4	825.6	825.7	825.8	826.0	826.2	826.6	827.0	827.4	827.7
165°	836.7	835.6	835.8	835.9	836.1	836.2	836.5	836.9	837.3	837.7	838.2
167.5°	844.9	843.8	843.8	843.8	843.8	843.8	844.1	844.7	845.2	845.8	846.4
170°	849.5	848.4	848.4	848.4	848.4	848.4	848.6	849.2	849.8	850.4	850.9
172.5°	852.6	851.4	851.3	851.2	851.1	851.0	851.3	851.9	852.6	853.3	853.9
175°	856.4	855.4	855.2	855.1	854.9	854.8	855.1	855.8	856.6	857.2	857.9
177.5°	857.9	856.9	856.8	856.7	856.6	856.5	856.7	857.3	857.9	858.4	858.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1152.2	1154.5	1162.0	1167.3	1173.5	1177.0	1180.6	1183.3	1186.8	1187.7	1200.6
5°	1157.3	1168.4	1187.8	1202.2	1220.0	1239.4	1252.7	1258.8	1275.0	1288.3	1314.9
7.5°	1155.8	1179.5	1208.8	1239.2	1271.9	1302.0	1328.2	1359.3	1381.4	1414.5	1447.2
10°	1154.5	1186.2	1223.9	1262.7	1308.2	1350.4	1388.1	1430.3	1465.3	1511.3	1550.7
12.5°	1150.6	1188.9	1241.2	1287.1	1342.4	1400.5	1456.5	1510.6	1541.6	1618.3	1654.6
15°	1140.7	1186.2	1251.6	1321.5	1397.6	1466.3	1537.3	1594.0	1685.5	1752.6	1795.4
17.5°	1121.9	1185.5	1263.1	1347.5	1439.9	1530.6	1611.0	1697.0	1794.0	1875.3	1961.8
20°	1113.0	1182.8	1269.4	1362.6	1458.6	1561.2	1652.8	1756.0	1861.9	1941.8	2052.8
22.5°	1096.5	1175.7	1268.9	1372.8	1475.4	1581.6	1688.7	1792.8	1915.2	2025.3	2130.9
25°	1069.7	1158.5	1255.0	1370.9	1491.3	1597.8	1726.0	1864.2	1991.8	2133.2	2238.6
27.5°	1041.5	1136.2	1233.0	1340.8	1470.3	1596.8	1757.9	1914.1	2070.0	2192.3	2270.3
30°	1019.7	1111.8	1211.7	1320.5	1448.6	1599.0	1779.2	1949.5	2101.6	2206.4	2250.3
32.5°	996.2	1089.6	1177.9	1292.0	1428.6	1597.6	1792.6	1970.4	2103.4	2173.2	2164.6
35°	959.3	1037.5	1123.5	1233.3	1394.2	1587.9	1800.3	1972.3	2053.9	2038.9	1925.7
37.5°	906.0	971.8	1056.5	1176.7	1354.3	1567.3	1784.8	1913.8	1908.5	1786.6	1622.6
40°	872.7	928.7	1010.3	1136.8	1323.2	1554.0	1760.4	1844.2	1773.2	1602.8	1406.4
42.5°	829.2	880.8	962.4	1092.4	1289.1	1526.9	1713.8	1738.1	1599.1	1403.1	1223.1
45°	761.7	807.2	891.5	1025.8	1237.8	1468.0	1600.0	1540.7	1353.7	1151.2	1014.2
47.5°	689.3	736.5	817.7	955.6	1163.7	1379.3	1442.3	1316.0	1124.1	959.8	834.0
50°	643.6	689.1	768.4	907.7	1113.5	1306.6	1332.6	1169.5	993.1	848.9	745.7
52.5°	597.5	640.3	718.3	857.9	1054.9	1222.2	1206.2	1039.9	877.7	754.7	673.8
55°	528.7	569.2	643.6	774.5	953.7	1086.3	1028.1	869.4	735.2	639.7	578.1
57.5°	467.2	506.1	570.2	688.5	844.3	935.4	861.3	727.6	620.9	547.4	501.4
60°	425.5	459.9	521.0	630.8	766.2	835.5	762.3	644.2	554.2	495.5	454.4
62.5°	386.0	416.0	472.5	572.3	689.8	748.1	674.0	574.0	497.4	445.3	410.4
65°	326.2	353.4	403.3	481.0	577.6	616.4	552.6	471.6	412.2	373.4	350.1
67.5°	271.7	294.7	337.9	399.0	470.0	498.3	449.7	387.0	342.3	311.1	292.6
70°	235.2	255.2	289.0	341.8	406.1	427.8	382.3	330.7	297.9	273.0	255.8
72.5°	204.6	219.2	250.0	290.7	344.4	361.6	329.9	284.5	254.0	235.2	221.6
75°	155.9	168.1	188.1	220.8	258.0	268.0	244.1	215.8	195.3	182.0	171.5
77.5°	112.4	121.4	135.8	156.0	181.7	190.8	175.6	156.8	141.8	132.8	126.9
80°	84.9	92.1	104.3	120.9	136.5	141.5	132.6	118.1	107.6	102.6	97.7
82.5°	62.7	66.8	74.1	85.4	96.1	102.0	94.4	85.8	80.1	75.6	73.7
85°	31.6	33.8	37.2	41.6	48.3	50.5	47.7	45.5	42.2	39.4	39.4
87.5°	12.0	12.2	13.9	15.0	17.1	18.8	18.8	18.3	18.2	17.9	17.5
90°	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5
92.5°	11.5	11.1	10.7	10.3	10.8	12.1	13.5	14.9	16.3	17.2	18.1
95°	33.1	27.2	21.4	15.7	13.5	15.1	16.6	18.2	19.7	20.8	21.8
97.5°	75.6	73.0	70.4	67.8	61.3	51.1	40.9	30.7	20.5	21.7	22.8
100°	110.6	113.4	116.2	119.0	109.4	87.3	65.2	43.1	21.0	22.2	23.3
102.5°	143.4	145.4	147.5	149.5	138.5	114.4	90.2	66.0	41.9	38.4	34.9
105°	191.5	193.1	194.6	196.2	190.6	177.8	165.1	152.3	139.6	114.5	89.4
107.5°	242.5	243.7	244.9	246.1	247.8	249.8	251.8	253.8	255.8	237.5	219.1
110°	276.5	277.6	278.8	279.9	281.2	282.8	284.4	285.9	287.5	282.8	278.1



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	309.0	310.1	311.0	312.1	313.3	315.0	316.5	318.0	319.6	319.7	319.8
115°	357.2	358.0	358.9	359.7	360.8	362.1	363.3	364.6	365.9	367.3	368.7
117.5°	404.1	405.2	406.3	407.2	408.1	408.8	409.4	410.1	410.7	411.9	413.0
120°	433.4	434.7	435.9	437.2	438.1	438.5	439.0	439.4	439.8	440.9	442.1
122.5°	462.8	463.8	464.9	465.9	466.7	467.2	467.8	468.3	468.9	469.7	470.4
125°	503.4	504.5	505.6	506.8	507.7	508.3	508.7	509.3	509.9	510.2	510.5
127.5°	542.7	543.8	544.9	546.1	547.0	547.6	548.4	549.0	549.7	550.2	550.6
130°	567.1	568.3	569.4	570.5	571.4	571.9	572.5	573.1	573.6	574.2	574.8
132.5°	590.6	591.7	592.9	594.0	594.8	595.3	595.7	596.1	596.6	597.2	597.7
135°	626.1	627.0	627.9	628.7	629.4	630.0	630.6	631.1	631.7	632.1	632.5
137.5°	657.0	658.0	659.1	660.1	660.9	661.2	661.5	661.8	662.1	662.8	663.5
140°	677.1	678.0	678.8	679.7	680.3	680.8	681.2	681.6	682.0	682.6	683.1
142.5°	696.0	696.8	697.7	698.5	699.2	699.6	700.0	700.4	700.9	701.3	701.8
145°	722.5	723.5	724.5	725.5	726.1	726.4	726.7	727.0	727.2	727.6	727.8
147.5°	747.1	747.7	748.4	749.0	749.5	749.7	750.0	750.3	750.6	750.9	751.1
150°	762.1	762.5	763.0	763.4	763.8	764.0	764.3	764.6	764.9	765.2	765.4
152.5°	775.7	775.8	776.1	776.2	776.4	776.6	776.7	777.0	777.1	777.6	778.1
155°	794.6	794.3	794.0	793.7	793.6	793.8	793.9	794.0	794.2	794.9	795.7
157.5°	809.8	809.8	809.8	809.8	809.7	809.5	809.4	809.3	809.1	810.0	810.8
160°	818.9	818.8	818.6	818.5	818.3	818.2	818.1	817.9	817.7	818.6	819.5
162.5°	827.4	827.0	826.6	826.2	826.0	825.8	825.7	825.6	825.4	826.4	827.4
165°	837.7	837.3	836.9	836.5	836.2	836.1	835.9	835.8	835.6	836.7	837.9
167.5°	845.8	845.2	844.7	844.1	843.8	843.8	843.8	843.8	843.8	844.9	846.0
170°	850.4	849.8	849.2	848.6	848.4	848.4	848.4	848.4	848.4	849.5	850.6
172.5°	853.3	852.6	851.9	851.3	851.0	851.1	851.2	851.3	851.4	852.6	853.7
175°	857.2	856.6	855.8	855.1	854.8	854.9	855.1	855.2	855.4	856.4	857.4
177.5°	858.4	857.9	857.3	856.7	856.5	856.6	856.7	856.8	856.9	857.9	858.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332018-930
 CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1205.0	1205.5	1210.4	1213.9	1212.1	1214.4	1215.2
5°	1316.5	1336.5	1347.0	1354.9	1355.4	1355.9	1360.4
7.5°	1474.6	1496.1	1511.7	1535.5	1542.5	1550.7	1548.3
10°	1590.1	1621.7	1648.9	1663.3	1678.9	1701.6	1683.3
12.5°	1697.9	1754.0	1795.4	1817.8	1832.4	1837.0	1828.0
15°	1875.8	1949.1	1988.4	1987.3	2037.3	2058.9	2025.0
17.5°	2038.9	2106.5	2160.6	2188.3	2230.0	2239.2	2235.0
20°	2138.8	2212.6	2254.7	2302.4	2324.1	2343.5	2346.8
22.5°	2224.9	2291.2	2336.4	2376.1	2394.2	2403.4	2409.0
25°	2313.5	2365.7	2392.9	2406.8	2411.7	2410.6	2403.4
27.5°	2307.5	2311.5	2281.5	2252.1	2225.8	2196.2	2185.9
30°	2247.5	2200.9	2117.7	2070.5	2001.2	1946.3	1968.5
32.5°	2089.9	1997.2	1903.7	1800.7	1715.3	1691.0	1666.6
35°	1783.7	1620.6	1525.2	1414.2	1369.8	1325.4	1294.9
37.5°	1443.1	1316.9	1203.7	1131.1	1086.6	1058.6	1043.5
40°	1247.7	1134.0	1040.8	982.0	948.2	916.6	912.1
42.5°	1091.9	986.2	916.1	869.3	836.7	823.3	813.6
45°	894.4	820.5	773.4	740.1	718.4	710.1	699.0
47.5°	757.0	704.8	669.4	646.8	630.5	624.3	623.4
50°	680.2	636.9	610.8	593.0	580.3	578.1	569.2
52.5°	622.5	585.0	564.7	549.2	540.0	533.7	531.1
55°	540.4	515.4	497.1	488.2	481.0	474.9	474.9
57.5°	472.8	451.9	439.9	432.3	430.1	425.7	423.0
60°	431.0	413.4	403.9	397.2	392.8	393.4	388.3
62.5°	390.3	378.7	369.7	363.1	357.8	357.8	358.2
65°	332.3	323.4	316.8	314.5	311.3	307.4	308.5
67.5°	281.6	273.3	268.1	264.3	263.2	261.1	264.3
70°	245.2	239.1	235.2	231.9	230.8	231.4	234.2
72.5°	211.9	207.6	205.0	203.5	201.1	201.1	203.1
75°	166.4	163.1	160.9	159.2	158.7	158.7	158.7
77.5°	122.3	121.5	120.5	118.1	118.1	118.9	119.0
80°	96.5	94.9	94.3	93.2	91.6	90.4	93.2
82.5°	72.2	70.4	69.9	69.7	67.1	66.9	69.2
85°	38.8	37.2	37.7	37.2	37.2	36.6	36.6
87.5°	17.1	16.8	16.5	17.0	16.6	16.2	17.1
90°	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	19.0	20.0	20.5	20.6	20.8	21.0	21.2
95°	22.7	23.7	24.2	24.2	24.2	24.2	24.2
97.5°	23.9	25.0	25.7	25.8	26.0	26.1	26.3
100°	24.5	25.6	26.2	26.3	26.5	26.7	26.7
102.5°	31.4	27.9	26.3	26.5	26.7	27.0	27.3
105°	64.4	39.3	26.9	27.2	27.5	27.8	28.0
107.5°	200.7	182.3	163.6	144.8	125.9	107.0	88.1
110°	273.5	268.8	256.3	236.0	215.8	195.5	175.3



TEST NUMBER: P332018-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	319.8	319.9	317.8	313.6	309.2	305.0	300.8
115°	370.1	371.5	372.5	373.1	373.7	374.2	374.8
117.5°	414.2	415.2	415.9	416.0	416.1	416.2	416.4
120°	443.2	444.3	444.9	444.9	444.9	444.9	444.9
122.5°	471.2	472.1	472.5	472.6	472.7	472.9	473.0
125°	510.8	511.0	511.4	511.6	511.9	512.2	512.5
127.5°	551.1	551.5	551.5	551.3	551.1	550.7	550.5
130°	575.4	575.9	576.1	575.8	575.5	575.2	574.9
132.5°	598.3	598.8	598.9	598.6	598.2	597.8	597.4
135°	632.9	633.3	633.3	632.9	632.5	632.1	631.7
137.5°	664.1	664.9	665.0	664.8	664.5	664.2	663.9
140°	683.7	684.3	684.4	684.1	683.9	683.5	683.3
142.5°	702.2	702.7	702.7	702.3	701.9	701.6	701.2
145°	728.1	728.4	728.6	728.6	728.6	728.6	728.6
147.5°	751.5	751.7	751.5	750.9	750.2	749.6	748.9
150°	765.7	766.0	766.0	765.5	765.1	764.7	764.3
152.5°	778.6	779.2	779.1	778.4	777.8	777.1	776.5
155°	796.3	797.0	797.0	796.1	795.2	794.4	793.5
157.5°	811.6	812.5	812.4	811.3	810.2	809.1	808.0
160°	820.4	821.2	821.1	820.1	819.1	818.2	817.2
162.5°	828.3	829.2	829.3	828.4	827.5	826.7	825.8
165°	839.0	840.2	840.2	839.3	838.2	837.2	836.3
167.5°	847.2	848.3	848.3	847.2	846.0	844.9	843.8
170°	851.7	852.9	852.9	851.7	850.6	849.5	848.4
172.5°	854.8	856.0	855.9	854.7	853.5	852.2	850.9
175°	858.3	859.3	859.2	858.2	857.0	855.9	854.8
177.5°	859.7	860.5	860.5	859.3	858.2	857.0	855.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9

(END OF REPORT)