

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332035-927

Luminaire Tested: **S123DIP-S1000D1025U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332035-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6204.7 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332035-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332035-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85		71	71	71		59	59	59	53
1	98	94	90	86	91	87	84	81	74	72	70		62	61	59		52	50	49	44
2	89	82	76	71	83	76	71	66	65	61	58		55	52	49		45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48		48	45	42		40	38	35	31
4	75	64	56	50	69	59	52	47	51	45	41		43	39	36		36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	35		39	34	31		32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31		35	31	27		29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27		32	27	24		27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24		29	25	21		25	21	19	16
9	50	38	31	26	47	36	29	24	31	26	22		27	22	19		23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20		25	20	17		21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332035-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.1	1.9
10°-20°	333.5	5.4
20°-30°	492.7	7.9
30°-40°	575.5	9.3
40°-50°	578.6	9.3
50°-60°	508.2	8.2
60°-70°	378.6	6.1
70°-80°	215.7	3.5
80°-90°	64.9	1.0
90°-100°	217.4	3.5
100°-110°	615.6	9.9
110°-120°	605.5	9.8
120°-130°	483.0	7.8
130°-140°	380.8	6.1
140°-150°	284.2	4.6
150°-160°	198.1	3.2
160°-170°	116.4	1.9
170°-180°	37.9	0.6
0°-30°	944.3	15.2
0°-40°	1519.8	24.5
0°-60°	2606.6	42.0
0°-90°	3265.9	52.6
90°-120°	1438.5	23.2
90°-150°	2586.5	41.7
90°-180°	2939.0	47.4
0°-180°	6204.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	2	10	20	22	23	5
95°	27	87	469	137	92	29
105°	92	136	636	1112	1006	97
115°	162	202	486	1066	1223	160
125°	225	266	454	822	965	200
135°	264	315	448	677	782	204
145°	301	345	442	556	611	189
155°	342	369	428	486	507	157
165°	374	385	410	434	442	105
175°	390	390	393	398	398	37
180°	391	391	391	391	391	



TEST NUMBER: P332035-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.7	22.5	22.3	22.1	21.9	21.8	22.1	22.3	22.7	22.9	22.6
90°	1.6	3.2	4.8	7.1	8.7	10.3	12.7	15.1	17.4	19.8	19.0
92.5°	9.8	14.6	21.2	27.3	34.0	45.7	66.4	100.4	133.8	121.6	91.7
95°	26.9	29.2	37.9	51.4	71.9	102.8	170.0	287.8	417.5	468.9	380.3
97.5°	45.9	46.7	53.5	65.1	85.4	118.7	183.0	315.8	532.0	726.7	777.4
100°	58.5	59.3	64.9	75.9	94.9	125.7	181.1	298.1	506.0	748.8	904.6
102.5°	71.8	73.2	78.1	88.6	105.7	134.0	183.6	282.9	468.1	707.7	910.9
105°	91.7	94.1	98.9	108.4	123.3	147.9	190.6	272.0	421.4	635.7	862.7
107.5°	112.9	115.3	119.9	129.2	143.3	166.0	203.5	271.2	391.7	572.2	778.2
110°	128.1	130.5	134.4	143.1	156.5	178.7	214.3	274.4	380.3	536.1	725.1



TEST NUMBER: P332035-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.0	144.4	148.4	157.0	170.5	192.0	225.1	280.7	374.0	512.1	678.9
115°	162.1	165.2	170.0	177.9	191.4	212.7	242.7	291.0	371.6	486.3	623.1
117.5°	182.2	185.8	189.8	197.0	212.1	231.9	261.6	304.6	373.0	471.1	589.4
120°	196.1	198.4	202.4	210.3	225.4	245.1	273.6	314.7	375.6	464.1	571.7
122.5°	208.1	210.5	214.4	223.0	237.4	258.4	286.2	324.2	380.0	459.7	557.1
125°	225.4	227.0	231.7	240.3	255.4	276.8	304.4	339.2	386.7	453.9	538.5
127.5°	238.5	240.8	246.7	255.6	272.2	293.5	320.3	351.6	394.3	451.1	522.0
130°	246.7	249.1	256.2	265.7	282.3	303.6	329.7	359.8	399.3	449.2	513.2
132.5°	253.0	256.0	263.8	275.2	291.8	312.5	337.9	367.4	403.1	448.5	504.9
135°	264.1	267.3	276.0	287.8	304.4	325.7	350.3	377.2	408.8	447.6	494.2
137.5°	274.6	277.9	286.4	299.0	315.5	335.3	358.9	384.4	412.6	445.8	484.9
140°	281.5	285.4	293.3	306.0	321.9	341.6	364.6	388.2	415.1	445.2	479.2
142.5°	289.1	292.4	301.0	312.4	328.1	346.7	369.0	392.1	417.0	443.9	474.1
145°	301.3	303.6	310.8	322.7	336.0	354.3	374.8	396.2	418.3	442.0	467.3
147.5°	313.6	315.1	322.0	332.2	345.2	360.8	379.5	398.7	418.3	439.0	460.7
150°	321.9	322.7	328.9	339.2	350.3	364.6	382.7	399.3	418.3	436.5	456.2
152.5°	330.0	330.2	336.5	345.5	355.4	369.0	384.6	400.6	416.4	433.3	451.2
155°	342.4	342.4	347.1	355.1	363.8	374.8	388.2	400.9	414.3	427.8	443.6
157.5°	352.2	352.8	356.6	363.6	371.0	379.5	390.3	401.7	411.7	422.9	435.1
160°	359.8	359.8	363.0	369.2	374.8	382.7	392.2	401.7	410.4	419.1	429.4
162.5°	365.5	365.5	368.0	373.0	378.0	384.6	392.8	401.1	407.9	415.3	423.7
165°	374.0	373.2	374.8	378.7	381.9	387.5	393.8	399.3	404.1	409.6	415.9
167.5°	380.5	379.5	380.3	383.3	385.6	389.0	393.6	398.1	400.3	403.9	408.5
170°	384.3	382.7	383.5	385.9	387.5	389.0	393.0	396.2	397.8	400.1	404.1
172.5°	386.8	385.9	386.0	387.8	388.7	389.7	393.0	395.5	395.9	397.0	399.7
175°	389.8	389.0	388.2	389.8	389.8	390.6	392.2	393.8	393.0	393.0	394.6
177.5°	391.3	390.6	390.0	390.6	390.6	390.6	391.3	392.5	391.3	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P332035-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	22.6	22.5	22.5	22.7	22.6	22.7	22.9	22.7
90°	19.8	20.6	21.4	22.9	22.1	22.9	23.7	22.9
92.5°	66.5	52.8	46.7	42.5	41.1	38.7	39.5	38.1
95°	284.6	193.0	151.1	122.6	107.6	100.4	94.9	91.7
97.5°	709.6	568.4	466.4	371.8	313.5	277.9	256.5	249.7
100°	932.3	868.2	775.7	663.5	583.6	525.9	495.0	495.8
102.5°	1006.3	1004.2	950.3	879.2	817.0	771.3	745.5	727.3
105°	1027.9	1107.1	1122.0	1101.5	1065.1	1035.1	1009.8	1005.8
107.5°	965.7	1094.1	1163.3	1191.5	1192.2	1182.0	1173.5	1166.2
110°	906.2	1051.7	1151.3	1206.7	1228.8	1235.2	1233.6	1232.0



TEST NUMBER: P332035-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	847.3	996.0	1107.6	1178.8	1219.3	1238.9	1244.9	1245.2
115°	769.4	907.0	1023.2	1109.4	1168.7	1203.5	1219.3	1223.3
117.5°	713.0	831.7	936.0	1023.5	1085.4	1125.2	1148.0	1153.3
120°	683.2	790.0	884.9	964.7	1027.1	1071.4	1090.4	1095.2
122.5°	659.8	756.5	844.4	918.5	974.1	1013.9	1034.7	1040.8
125°	628.7	714.9	790.8	854.0	904.6	939.4	959.2	964.7
127.5°	601.4	678.3	746.8	804.3	849.4	879.2	897.0	902.1
130°	584.4	655.5	719.5	773.3	815.2	843.8	860.3	866.6
132.5°	568.5	634.0	693.6	744.9	784.3	812.7	827.4	831.9
135°	547.2	603.3	654.7	699.8	738.6	762.2	776.5	782.0
137.5°	527.8	573.8	618.1	657.1	689.7	713.8	725.7	729.4
140°	516.3	556.7	594.6	628.7	658.7	680.8	693.5	692.7
142.5°	505.6	540.3	573.1	602.7	628.4	647.9	659.3	658.5
145°	492.7	518.7	544.0	567.0	586.7	603.3	609.7	611.2
147.5°	482.0	502.7	523.2	539.5	554.4	565.7	571.7	572.4
150°	474.4	492.7	509.2	524.3	536.1	544.8	549.5	549.5
152.5°	467.5	483.2	497.9	510.3	519.7	527.8	530.6	530.6
155°	457.0	469.7	481.6	491.1	498.2	504.5	506.0	506.8
157.5°	446.0	456.5	465.7	473.2	479.3	484.1	485.4	485.2
160°	439.7	448.4	456.2	461.8	467.3	472.1	472.1	471.3
162.5°	432.1	439.5	446.8	451.7	455.3	459.4	459.4	458.6
165°	422.2	427.0	432.5	436.5	439.7	442.8	442.0	442.0
167.5°	413.7	417.3	420.5	423.3	424.8	427.0	426.2	426.2
170°	408.1	410.4	413.5	415.1	415.9	417.5	416.7	416.7
172.5°	403.0	404.7	407.3	408.2	408.4	410.0	408.5	407.9
175°	396.2	397.0	398.5	398.5	398.5	399.3	398.5	397.8
177.5°	391.9	392.5	393.2	393.2	392.5	393.2	391.9	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

(END OF REPORT)