

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831057

Luminaire Tested: S123DIP-S1000D1025U927-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831057
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U927-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6898.7 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 61
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53				
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46				
2	91	84	78	73	84	78	73	68	67	63	60	57	54	51	47	45	44	39				
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34				
4	76	66	58	53	71	62	55	50	53	48	44	46	42	39	38	36	33	30				
5	70	59	51	46	65	55	48	43	48	43	39	41	37	34	35	32	30	26				
6	65	54	46	40	60	50	43	38	44	38	34	38	34	30	32	29	26	24				
7	61	49	41	36	56	46	39	34	40	34	30	35	30	27	30	26	24	21				
8	56	44	37	32	52	42	35	30	37	31	27	32	28	25	27	24	22	19				
9	53	41	34	29	49	38	32	27	34	29	25	30	25	22	26	22	20	18				
10	49	38	31	26	46	36	29	25	31	26	23	28	23	20	24	21	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	24455	24455	24455	24455	24455
5°	30927	29190	24673	19883	18271
10°	31227	32172	24509	15850	13850
15°	23520	29869	24342	13422	11713
20°	16387	24171	24032	11738	10639
25°	12495	18587	23502	10799	9979
30°	10811	14767	22656	10136	9447
35°	10030	12468	21680	9656	9073
40°	9496	11185	20310	9199	8948
45°	9179	10351	18568	8843	8891
50°	9021	9692	16506	8519	8845
55°	8685	9211	14482	8210	8884
60°	8374	8693	12482	7920	8738
65°	7868	8204	10769	7613	8565
70°	7267	7582	9158	7100	8063
75°	6575	6796	7848	6600	7365
80°	5424	5945	6211	5752	6211
85°	4298	4817	4557	4878	4952

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 21200 cd/sqm



TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	3.1
10°-20°	534.3	7.7
20°-30°	632.7	9.2
30°-40°	636.1	9.2
40°-50°	583.6	8.5
50°-60°	481.7	7.0
60°-70°	340.8	4.9
70°-80°	181.9	2.6
80°-90°	48.3	0.7
90°-100°	37.5	0.5
100°-110°	181.4	2.6
110°-120°	444.6	6.4
120°-130°	564.5	8.2
130°-140°	603.0	8.7
140°-150°	563.9	8.2
150°-160°	454.8	6.6
160°-170°	293.5	4.3
170°-180°	101.2	1.5
0°-30°	1381.8	20.0
0°-40°	2018.0	29.3
0°-60°	3083.3	44.7
0°-90°	3654.3	53.0
90°-120°	663.5	9.6
90°-150°	2394.9	34.7
90°-180°	3244.0	47.0
0°-180°	6898.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2272	2272	2272	2272	2272	
5°	2862	2702	2284	1840	1691	273
15°	2111	2680	2184	1204	1051	583
25°	1052	1565	1979	909	840	497
35°	763	949	1650	735	690	480
45°	603	680	1220	581	584	467
55°	463	491	772	438	473	414
65°	309	322	423	299	336	307
75°	158	163	189	159	177	166
85°	35	39	37	40	40	39
90°	24	19	1	19	24	12
95°	30	24	48	24	30	25
105°	35	173	236	173	35	72
115°	465	454	442	454	465	437
125°	636	633	623	633	636	568
135°	784	784	776	784	784	604
145°	904	902	895	902	904	564
155°	984	985	986	985	984	454
165°	1037	1037	1040	1037	1037	293
175°	1060	1061	1064	1061	1060	101
180°	1064	1064	1064	1064	1064	



TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9
2.5°	2560.8	2558.1	2555.5	2542.3	2529.1	2522.8	2516.5	2497.5	2478.5	2457.5	2436.4
5°	2862.3	2869.7	2877.0	2868.6	2860.2	2834.3	2808.5	2774.3	2740.0	2701.5	2663.0
7.5°	3001.4	3005.7	3009.9	3004.6	2999.3	2992.5	2985.6	2955.1	2924.5	2885.0	2845.4
10°	2857.0	2866.5	2876.0	2896.5	2917.1	2940.3	2963.5	2959.3	2955.1	2943.5	2931.9
12.5°	2539.7	2551.3	2562.9	2604.0	2645.1	2697.8	2750.5	2795.9	2841.2	2872.8	2904.5
15°	2110.6	2142.8	2174.9	2212.3	2249.8	2327.3	2404.7	2500.2	2595.6	2680.4	2765.3
17.5°	1738.5	1750.6	1762.7	1802.8	1842.8	1940.3	2037.9	2148.0	2258.2	2398.9	2539.7
20°	1430.6	1441.7	1452.8	1505.5	1558.2	1634.6	1711.0	1834.9	1958.8	2110.1	2261.4
22.5°	1201.8	1219.2	1236.6	1266.2	1295.7	1368.9	1442.2	1552.4	1662.5	1829.6	1996.7
25°	1052.1	1064.8	1077.4	1095.4	1113.3	1171.8	1230.3	1321.0	1411.6	1565.0	1718.4
27.5°	949.9	955.1	960.4	978.3	996.3	1034.2	1072.2	1150.2	1228.2	1358.4	1488.6
30°	869.8	873.4	877.1	892.9	908.8	934.6	960.4	1016.8	1073.2	1188.1	1303.1
32.5°	813.9	816.5	819.2	831.3	843.4	861.8	880.3	921.4	962.5	1057.4	1152.3
35°	763.3	764.9	766.4	775.4	784.4	798.1	811.8	842.9	874.0	948.8	1023.7
37.5°	719.0	721.1	723.2	728.5	733.8	745.9	758.0	782.8	807.6	865.0	922.5
40°	675.8	679.5	683.2	686.8	690.5	700.5	710.6	729.5	748.5	796.0	843.4
42.5°	638.9	642.6	646.3	647.8	649.4	655.2	661.0	678.4	695.8	731.1	766.4
45°	603.0	604.6	606.2	607.8	609.4	614.1	618.8	634.1	649.4	680.0	710.6
47.5°	570.3	570.3	570.3	571.4	572.5	576.7	580.9	592.0	603.0	626.8	650.5
50°	538.7	538.7	538.7	537.1	535.6	538.2	540.8	549.3	557.7	578.8	599.9
52.5°	500.8	500.8	500.8	501.3	501.8	501.8	501.8	509.2	516.6	535.6	554.5
55°	462.8	464.9	467.0	465.5	463.9	464.9	466.0	470.7	475.5	490.8	506.0
57.5°	424.9	425.9	427.0	426.4	425.9	426.4	427.0	431.2	435.4	447.0	458.6
60°	389.0	389.0	389.0	388.0	386.9	388.0	389.0	391.1	393.2	403.8	414.3
62.5°	349.0	349.5	350.0	350.5	351.1	350.0	349.0	351.6	354.2	362.1	370.0
65°	308.9	309.4	309.9	311.5	313.1	312.1	311.0	313.6	316.3	322.1	327.9
67.5°	273.1	272.0	270.9	271.5	272.0	273.6	275.2	275.7	276.2	282.5	288.9
70°	230.9	231.9	233.0	232.5	231.9	232.5	233.0	234.6	236.2	240.9	245.6
72.5°	192.9	193.5	194.0	194.0	194.0	195.0	196.1	197.7	199.3	201.9	204.5
75°	158.1	158.1	158.1	159.2	160.2	160.8	161.3	161.3	161.3	163.4	165.5
77.5°	120.2	122.8	125.5	124.9	124.4	125.5	126.5	128.1	129.7	130.7	131.8
80°	87.5	87.5	87.5	88.0	88.6	90.1	91.7	92.8	93.8	95.9	98.0
82.5°	55.9	56.4	56.9	58.5	60.1	61.1	62.2	63.8	65.4	65.4	65.4
85°	34.8	33.7	32.7	33.7	34.8	35.8	36.9	37.4	38.0	39.0	40.1
87.5°	16.9	16.9	16.9	16.9	16.9	17.4	17.9	17.9	17.9	17.9	17.9
90°	23.7	23.4	23.0	22.7	22.3	21.8	21.1	20.4	19.7	19.0	16.7
92.5°	26.9	26.7	26.5	26.4	26.2	25.5	24.2	23.0	21.8	20.6	19.0
95°	30.0	30.0	30.0	30.0	30.0	29.4	28.2	27.0	25.7	24.5	22.6
97.5°	32.4	32.2	32.1	31.9	31.7	30.9	29.5	28.1	26.7	25.3	34.3
100°	33.2	33.0	32.9	32.7	32.5	31.7	30.3	28.9	27.5	26.1	53.5
102.5°	34.0	33.6	33.3	32.9	32.6	35.3	41.1	46.9	52.7	58.5	89.1
105°	34.8	34.4	34.1	33.7	33.4	48.8	79.9	111.0	142.1	173.2	189.0
107.5°	82.2	105.3	128.3	151.3	174.3	199.3	226.4	253.5	280.5	307.6	305.0
110°	217.4	242.6	267.7	292.8	318.0	333.4	339.2	345.0	350.8	356.6	354.7



TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	412.0	412.3	412.7	413.0	413.4	412.8	411.2	409.6	408.0	406.4	404.5
115°	464.9	464.2	463.5	462.8	462.1	460.9	459.1	457.4	455.6	453.9	452.3
117.5°	507.6	507.5	507.3	507.1	506.9	506.1	504.7	503.3	501.9	500.5	499.6
120°	551.9	551.9	551.9	551.9	551.9	551.2	549.8	548.4	547.0	545.6	545.1
122.5°	595.4	595.2	595.1	594.9	594.7	594.2	593.3	592.4	591.5	590.7	590.0
125°	635.7	635.4	635.0	634.7	634.3	634.0	633.6	633.3	632.9	632.6	631.9
127.5°	675.3	675.6	676.0	676.3	676.7	676.6	676.1	675.5	675.0	674.5	673.6
130°	713.2	713.6	713.9	714.3	714.6	714.5	713.8	713.0	712.3	711.6	710.9
132.5°	748.0	748.5	749.1	749.6	750.1	750.0	749.3	748.6	747.9	747.2	746.7
135°	783.6	784.1	784.7	785.2	785.7	785.7	785.2	784.7	784.1	783.6	782.9
137.5°	817.6	817.9	818.3	818.7	819.0	818.7	817.9	817.0	816.1	815.2	814.9
140°	847.6	848.0	848.3	848.7	849.1	848.9	848.2	847.5	846.8	846.1	845.5
142.5°	875.3	875.8	876.4	876.9	877.4	877.4	876.9	876.4	875.8	875.3	874.8
145°	903.8	903.8	903.8	903.8	903.8	903.6	903.3	902.9	902.6	902.2	901.9
147.5°	924.3	925.2	926.1	927.0	927.9	928.1	927.8	927.4	927.1	926.7	926.4
150°	948.1	948.6	949.1	949.6	950.2	950.3	949.9	949.6	949.2	948.9	948.5
152.5°	967.0	967.9	968.8	969.7	970.6	970.6	969.9	969.2	968.5	967.8	967.7
155°	984.4	985.5	986.5	987.6	988.7	988.7	987.9	987.0	986.1	985.2	985.1
157.5°	999.5	1000.9	1002.3	1003.7	1005.1	1005.3	1004.2	1003.2	1002.1	1001.0	1001.2
160°	1013.7	1014.9	1016.2	1017.4	1018.6	1018.7	1017.6	1016.6	1015.5	1014.5	1014.7
162.5°	1027.1	1028.2	1029.2	1030.3	1031.4	1031.3	1030.0	1028.8	1027.6	1026.3	1026.5
165°	1037.4	1038.6	1039.9	1041.1	1042.3	1042.2	1040.8	1039.4	1038.0	1036.6	1036.8
167.5°	1045.3	1046.7	1048.1	1049.5	1050.9	1050.9	1049.5	1048.1	1046.7	1045.3	1045.3
170°	1052.4	1053.8	1055.3	1056.7	1058.1	1058.1	1056.7	1055.3	1053.8	1052.4	1052.4
172.5°	1056.4	1058.0	1059.6	1061.1	1062.7	1062.8	1061.4	1060.0	1058.6	1057.2	1057.0
175°	1060.3	1061.8	1063.2	1064.6	1066.0	1066.1	1064.8	1063.6	1062.4	1061.1	1061.0
177.5°	1061.1	1062.9	1064.7	1066.4	1068.2	1068.3	1066.9	1065.5	1064.1	1062.7	1062.5
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9
2.5°	2430.0	2423.7	2400.5	2377.3	2351.0	2324.6	2305.1	2285.6	2256.6	2227.6	2203.9
5°	2633.5	2604.0	2555.0	2505.9	2439.5	2373.1	2328.3	2283.5	2223.4	2163.3	2115.3
7.5°	2794.8	2744.2	2675.7	2607.2	2520.2	2433.2	2351.0	2268.7	2177.0	2085.3	2010.5
10°	2897.6	2863.3	2784.3	2705.2	2588.7	2472.2	2357.3	2242.4	2124.3	2006.2	1907.1
12.5°	2907.6	2910.8	2838.0	2765.3	2633.5	2501.7	2362.0	2222.4	2073.7	1925.1	1809.6
15°	2819.6	2873.9	2833.8	2793.8	2660.9	2528.1	2356.2	2184.4	2013.1	1841.8	1708.4
17.5°	2656.2	2772.7	2778.5	2784.3	2651.4	2518.6	2328.3	2138.0	1944.0	1750.1	1609.8
20°	2433.2	2605.0	2664.1	2723.1	2615.1	2507.0	2302.5	2098.0	1880.8	1663.6	1516.5
22.5°	2205.5	2414.2	2522.3	2630.3	2550.2	2470.1	2252.4	2034.7	1805.4	1576.1	1426.9
25°	1946.1	2173.9	2339.9	2505.9	2456.9	2407.9	2193.4	1978.8	1734.8	1490.7	1338.4
27.5°	1720.0	1951.4	2151.7	2352.0	2341.5	2330.9	2118.0	1905.0	1655.2	1405.3	1258.2
30°	1518.6	1734.2	1958.3	2182.3	2208.1	2234.0	2028.4	1822.8	1572.4	1322.0	1180.2
32.5°	1340.5	1528.7	1769.0	2009.4	2060.0	2110.6	1925.1	1739.5	1491.8	1244.0	1107.5
35°	1194.5	1365.3	1605.6	1846.0	1909.2	1972.5	1811.2	1649.9	1408.5	1167.1	1036.9
37.5°	1065.3	1208.2	1442.7	1677.3	1754.8	1832.3	1687.9	1543.4	1317.3	1091.1	971.5
40°	958.3	1073.2	1288.8	1504.4	1594.0	1683.6	1564.5	1445.4	1230.8	1016.3	906.1
42.5°	868.7	971.0	1166.5	1362.1	1448.0	1533.9	1433.3	1332.6	1141.8	950.9	850.3
45°	792.3	874.0	1051.6	1229.3	1311.0	1392.7	1306.2	1219.8	1051.6	883.5	789.6
47.5°	720.6	790.7	942.5	1094.3	1167.1	1239.8	1172.3	1104.9	962.5	820.2	735.3
50°	656.3	712.7	845.5	978.3	1041.6	1104.9	1045.3	985.7	868.7	751.7	677.9
52.5°	600.4	646.3	757.5	868.7	923.0	977.3	926.2	875.0	782.3	689.5	625.2
55°	545.0	584.1	680.5	777.0	813.9	850.8	811.2	771.7	696.9	622.0	567.7
57.5°	493.4	528.2	607.2	686.3	714.8	743.2	707.4	671.6	615.2	558.8	513.4
60°	442.8	471.2	537.1	603.0	620.4	637.8	608.8	579.8	540.3	500.8	460.2
62.5°	395.9	421.7	470.7	519.7	531.3	542.9	520.8	498.7	468.6	438.6	406.9
65°	347.4	366.9	406.9	447.0	454.4	461.8	442.3	422.8	400.1	377.4	354.2
67.5°	302.6	316.3	349.0	381.6	382.2	382.7	366.9	351.1	338.4	325.8	307.3
70°	258.8	272.0	293.6	315.2	315.7	316.3	303.6	291.0	281.5	272.0	258.3
72.5°	214.0	223.5	239.8	256.2	255.1	254.1	246.2	238.3	230.9	223.5	213.5
75°	173.4	181.3	192.4	203.5	200.3	197.1	192.9	188.7	182.4	176.1	169.7
77.5°	136.5	141.3	147.6	153.9	151.8	149.7	146.0	142.3	137.6	132.8	130.2
80°	100.2	102.3	106.5	110.7	109.6	108.6	104.4	100.2	99.1	98.0	94.4
82.5°	68.0	70.6	71.7	72.7	72.2	71.7	68.5	65.4	64.3	63.3	62.7
85°	40.6	41.1	41.6	42.2	40.6	39.0	38.0	36.9	36.9	36.9	36.4
87.5°	18.4	19.0	19.0	19.0	18.4	17.9	16.9	15.8	16.3	16.9	16.9
90°	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	17.4	15.8	14.2	14.0	15.0	16.1	17.1	18.2	17.1	16.1	15.0
95°	20.6	18.7	16.8	19.4	26.6	33.8	41.0	48.2	41.0	33.8	26.6
97.5°	43.2	52.2	61.1	68.1	73.0	77.9	82.8	87.8	82.8	77.9	73.0
100°	80.9	108.3	135.7	147.7	144.2	140.7	137.1	133.6	137.1	140.7	144.2
102.5°	119.7	150.2	180.8	195.0	192.7	190.4	188.1	185.8	188.1	190.4	192.7
105°	204.8	220.6	236.4	243.4	241.4	239.5	237.6	235.6	237.6	239.5	241.4
107.5°	302.3	299.7	297.0	294.9	293.4	291.8	290.2	288.6	290.2	291.8	293.4
110°	352.7	350.8	348.9	347.2	345.8	344.4	343.0	341.6	343.0	344.4	345.8



TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	402.6	400.6	398.7	397.1	395.9	394.7	393.4	392.2	393.4	394.7	395.9
115°	450.7	449.1	447.5	446.2	445.2	444.1	443.1	442.0	443.1	444.1	445.2
117.5°	498.8	497.9	497.0	496.0	494.7	493.5	492.3	491.0	492.3	493.5	494.7
120°	544.5	544.0	543.5	542.4	540.8	539.3	537.7	536.1	537.7	539.3	540.8
122.5°	589.3	588.6	587.9	586.9	585.7	584.4	583.2	582.0	583.2	584.4	585.7
125°	631.2	630.5	629.8	628.7	627.3	625.9	624.5	623.1	624.5	625.9	627.3
127.5°	672.7	671.8	671.0	669.8	668.4	667.0	665.6	664.2	665.6	667.0	668.4
130°	710.2	709.5	708.8	707.8	706.4	705.0	703.6	702.2	703.6	705.0	706.4
132.5°	746.2	745.6	745.1	744.1	742.7	741.3	739.9	738.5	739.9	741.3	742.7
135°	782.2	781.5	780.8	779.9	778.9	777.8	776.7	775.7	776.7	777.8	778.9
137.5°	814.5	814.2	813.8	812.9	811.5	810.1	808.7	807.3	808.7	810.1	811.5
140°	845.0	844.5	844.0	843.2	842.1	841.1	840.0	838.9	840.0	841.1	842.1
142.5°	874.3	873.7	873.2	872.4	871.4	870.3	869.3	868.2	869.3	870.3	871.4
145°	901.5	901.1	900.8	900.0	898.8	897.5	896.3	895.1	896.3	897.5	898.8
147.5°	926.0	925.7	925.3	924.7	923.8	922.9	922.1	921.2	922.1	922.9	923.8
150°	948.2	947.8	947.4	947.0	946.5	946.0	945.4	944.9	945.4	946.0	946.5
152.5°	967.5	967.3	967.1	967.0	966.8	966.6	966.4	966.3	966.4	966.6	966.8
155°	984.9	984.7	984.5	984.6	985.0	985.3	985.7	986.0	985.7	985.3	985.0
157.5°	1001.4	1001.6	1001.7	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8
160°	1014.8	1015.0	1015.2	1015.4	1015.5	1015.7	1015.9	1016.1	1015.9	1015.7	1015.5
162.5°	1026.7	1026.9	1027.0	1027.4	1027.9	1028.5	1029.0	1029.5	1029.0	1028.5	1027.9
165°	1037.0	1037.2	1037.3	1037.7	1038.2	1038.7	1039.3	1039.8	1039.3	1038.7	1038.2
167.5°	1045.3	1045.3	1045.3	1045.7	1046.4	1047.1	1047.8	1048.5	1047.8	1047.1	1046.4
170°	1052.4	1052.4	1052.4	1052.8	1053.5	1054.2	1054.9	1055.6	1054.9	1054.2	1053.5
172.5°	1056.8	1056.7	1056.5	1056.8	1057.7	1058.6	1059.5	1060.3	1059.5	1058.6	1057.7
175°	1060.8	1060.6	1060.4	1060.8	1061.7	1062.5	1063.4	1064.3	1063.4	1062.5	1061.7
177.5°	1062.4	1062.2	1062.0	1062.4	1063.2	1064.1	1065.0	1065.9	1065.0	1064.1	1063.2
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9
2.5°	2180.2	2159.6	2139.1	2123.3	2107.4	2080.6	2053.7	2047.4	2041.0	2032.1	2023.1
5°	2067.4	2016.8	1966.2	1920.8	1875.5	1840.2	1804.9	1781.7	1758.5	1741.6	1724.8
7.5°	1935.6	1859.7	1783.8	1730.0	1676.3	1625.1	1574.0	1557.7	1541.3	1519.2	1497.0
10°	1808.0	1724.2	1640.4	1570.3	1500.2	1450.1	1400.0	1380.0	1360.0	1332.0	1304.1
12.5°	1694.2	1602.5	1510.7	1440.1	1369.5	1321.0	1272.5	1243.5	1214.5	1198.7	1182.9
15°	1575.0	1477.0	1379.0	1313.6	1248.2	1204.5	1160.7	1135.4	1110.1	1094.8	1079.6
17.5°	1469.6	1372.6	1275.6	1212.9	1150.2	1110.1	1070.1	1047.9	1025.8	1014.2	1002.6
20°	1369.5	1274.6	1179.7	1118.6	1057.4	1024.7	992.0	977.8	963.6	954.1	944.6
22.5°	1277.7	1184.4	1091.1	1039.0	986.8	960.4	934.1	924.0	914.0	906.1	898.2
25°	1186.0	1102.7	1019.5	975.2	930.9	909.3	887.7	877.7	867.6	859.7	851.8
27.5°	1111.2	1031.6	952.0	914.0	876.1	859.2	842.3	834.4	826.5	819.2	811.8
30°	1038.4	967.3	896.1	863.4	830.7	815.5	800.2	792.3	784.4	777.5	770.7
32.5°	971.0	909.8	848.7	818.6	788.6	775.9	763.3	753.8	744.3	739.0	733.8
35°	906.7	851.8	797.0	772.2	747.5	734.8	722.2	714.3	706.3	702.1	697.9
37.5°	851.8	802.8	753.8	730.1	706.3	694.2	682.1	675.2	668.4	666.8	665.2
40°	796.0	753.8	711.6	688.4	665.2	654.7	644.1	639.9	635.7	634.7	633.6
42.5°	749.6	708.5	667.3	646.3	625.2	616.2	607.2	605.1	603.0	604.6	606.2
45°	695.8	661.5	627.3	607.8	588.3	580.9	573.5	571.9	570.3	573.5	576.7
47.5°	650.5	618.8	587.2	568.8	550.3	545.0	539.8	539.2	538.7	542.9	547.2
50°	604.1	573.5	542.9	528.2	513.4	508.7	503.9	505.5	507.1	513.9	520.8
52.5°	560.9	532.4	503.9	490.2	476.5	473.4	470.2	473.9	477.6	485.0	492.3
55°	513.4	487.6	461.8	451.2	440.7	437.5	434.4	441.7	449.1	456.0	462.8
57.5°	468.1	445.4	422.8	413.3	403.8	403.3	402.7	409.6	416.4	423.8	431.2
60°	419.6	400.6	381.6	374.3	366.9	367.9	369.0	376.9	384.8	390.6	396.4
62.5°	375.3	359.5	343.7	336.8	330.0	332.6	335.3	343.2	351.1	357.9	364.8
65°	331.0	317.9	304.7	299.9	295.2	298.9	302.6	309.4	316.3	321.0	325.8
67.5°	288.9	277.8	266.7	263.0	259.3	263.0	266.7	273.6	280.4	285.2	289.9
70°	244.6	235.6	226.7	224.0	221.4	225.6	229.8	235.6	241.4	246.2	250.9
72.5°	203.5	196.6	189.8	189.2	188.7	192.4	196.1	201.9	207.7	210.8	214.0
75°	163.4	159.7	156.0	155.5	155.0	158.7	162.4	165.5	168.7	171.3	174.0
77.5°	127.6	124.4	121.2	121.8	122.3	124.9	127.6	130.7	133.9	135.5	137.1
80°	90.7	89.6	88.6	89.6	90.7	92.8	94.9	97.0	99.1	100.2	101.2
82.5°	62.2	61.1	60.1	61.7	63.3	64.8	66.4	68.0	69.6	70.1	70.6
85°	35.8	37.4	39.0	39.0	39.0	39.5	40.1	40.6	41.1	40.6	40.1
87.5°	16.9	17.4	17.9	17.9	17.9	18.4	19.0	19.0	19.0	18.4	17.9
90°	7.8	9.8	12.1	14.4	16.7	19.0	19.7	20.4	21.1	21.8	22.3
92.5°	14.0	14.2	15.8	17.4	19.0	20.6	21.8	23.0	24.2	25.5	26.2
95°	19.4	16.8	18.7	20.6	22.6	24.5	25.7	27.0	28.2	29.4	30.0
97.5°	68.1	61.1	52.2	43.2	34.3	25.3	26.7	28.1	29.5	30.9	31.7
100°	147.7	135.7	108.3	80.9	53.5	26.1	27.5	28.9	30.3	31.7	32.5
102.5°	195.0	180.8	150.2	119.7	89.1	58.5	52.7	46.9	41.1	35.3	32.6
105°	243.4	236.4	220.6	204.8	189.0	173.2	142.1	111.0	79.9	48.8	33.4
107.5°	294.9	297.0	299.7	302.3	305.0	307.6	280.5	253.5	226.4	199.3	174.3
110°	347.2	348.9	350.8	352.7	354.7	356.6	350.8	345.0	339.2	333.4	318.0



TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	397.1	398.7	400.6	402.6	404.5	406.4	408.0	409.6	411.2	412.8	413.4
115°	446.2	447.5	449.1	450.7	452.3	453.9	455.6	457.4	459.1	460.9	462.1
117.5°	496.0	497.0	497.9	498.8	499.6	500.5	501.9	503.3	504.7	506.1	506.9
120°	542.4	543.5	544.0	544.5	545.1	545.6	547.0	548.4	549.8	551.2	551.9
122.5°	586.9	587.9	588.6	589.3	590.0	590.7	591.5	592.4	593.3	594.2	594.7
125°	628.7	629.8	630.5	631.2	631.9	632.6	632.9	633.3	633.6	634.0	634.3
127.5°	669.8	671.0	671.8	672.7	673.6	674.5	675.0	675.5	676.1	676.6	676.7
130°	707.8	708.8	709.5	710.2	710.9	711.6	712.3	713.0	713.8	714.5	714.6
132.5°	744.1	745.1	745.6	746.2	746.7	747.2	747.9	748.6	749.3	750.0	750.1
135°	779.9	780.8	781.5	782.2	782.9	783.6	784.1	784.7	785.2	785.7	785.7
137.5°	812.9	813.8	814.2	814.5	814.9	815.2	816.1	817.0	817.9	818.7	819.0
140°	843.2	844.0	844.5	845.0	845.5	846.1	846.8	847.5	848.2	848.9	849.1
142.5°	872.4	873.2	873.7	874.3	874.8	875.3	875.8	876.4	876.9	877.4	877.4
145°	900.0	900.8	901.1	901.5	901.9	902.2	902.6	902.9	903.3	903.6	903.8
147.5°	924.7	925.3	925.7	926.0	926.4	926.7	927.1	927.4	927.8	928.1	927.9
150°	947.0	947.4	947.8	948.2	948.5	948.9	949.2	949.6	949.9	950.3	950.2
152.5°	967.0	967.1	967.3	967.5	967.7	967.8	968.5	969.2	969.9	970.6	970.6
155°	984.6	984.5	984.7	984.9	985.1	985.2	986.1	987.0	987.9	988.7	988.7
157.5°	1001.8	1001.7	1001.6	1001.4	1001.2	1001.0	1002.1	1003.2	1004.2	1005.3	1005.1
160°	1015.4	1015.2	1015.0	1014.8	1014.7	1014.5	1015.5	1016.6	1017.6	1018.7	1018.6
162.5°	1027.4	1027.0	1026.9	1026.7	1026.5	1026.3	1027.6	1028.8	1030.0	1031.3	1031.4
165°	1037.7	1037.3	1037.2	1037.0	1036.8	1036.6	1038.0	1039.4	1040.8	1042.2	1042.3
167.5°	1045.7	1045.3	1045.3	1045.3	1045.3	1045.3	1046.7	1048.1	1049.5	1050.9	1050.9
170°	1052.8	1052.4	1052.4	1052.4	1052.4	1052.4	1053.8	1055.3	1056.7	1058.1	1058.1
172.5°	1056.8	1056.5	1056.7	1056.8	1057.0	1057.2	1058.6	1060.0	1061.4	1062.8	1062.7
175°	1060.8	1060.4	1060.6	1060.8	1061.0	1061.1	1062.4	1063.6	1064.8	1066.1	1066.0
177.5°	1062.4	1062.0	1062.2	1062.4	1062.5	1062.7	1064.1	1065.5	1066.9	1068.3	1068.2
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2271.9	2271.9	2271.9	2271.9
2.5°	2019.4	2015.7	2001.0	1986.2
5°	1712.1	1699.4	1695.2	1691.0
7.5°	1496.0	1494.9	1472.8	1450.6
10°	1305.7	1307.3	1287.2	1267.2
12.5°	1169.7	1156.5	1154.9	1153.3
15°	1067.4	1055.3	1053.2	1051.1
17.5°	995.2	987.8	985.7	983.6
20°	940.4	936.2	932.5	928.8
22.5°	892.9	887.7	884.5	881.4
25°	847.1	842.3	841.3	840.2
27.5°	806.0	800.2	800.2	800.2
30°	767.0	763.3	761.7	760.1
32.5°	730.6	727.4	727.4	727.4
35°	696.3	694.7	692.6	690.5
37.5°	665.2	665.2	664.2	663.1
40°	635.2	636.8	636.8	636.8
42.5°	607.8	609.4	609.4	609.4
45°	579.3	581.9	583.0	584.1
47.5°	551.4	555.6	556.6	557.7
50°	524.0	527.1	527.7	528.2
52.5°	496.0	499.7	502.3	505.0
55°	466.5	470.2	471.8	473.4
57.5°	434.9	438.6	439.1	439.6
60°	400.1	403.8	404.8	405.9
62.5°	366.9	369.0	370.0	371.1
65°	328.9	332.1	334.2	336.3
67.5°	292.6	295.2	295.2	295.2
70°	252.0	253.0	254.6	256.2
72.5°	214.5	215.1	215.1	215.1
75°	175.0	176.1	176.6	177.1
77.5°	137.6	138.1	138.1	138.1
80°	100.7	100.2	100.2	100.2
82.5°	69.1	67.5	67.5	67.5
85°	39.5	39.0	39.5	40.1
87.5°	17.9	17.9	17.9	17.9
90°	22.7	23.0	23.4	23.7
92.5°	26.4	26.5	26.7	26.9
95°	30.0	30.0	30.0	30.0
97.5°	31.9	32.1	32.2	32.4
100°	32.7	32.9	33.0	33.2
102.5°	32.9	33.3	33.6	34.0
105°	33.7	34.1	34.4	34.8
107.5°	151.3	128.3	105.3	82.2
110°	292.8	267.7	242.6	217.4



TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	413.0	412.7	412.3	412.0
115°	462.8	463.5	464.2	464.9
117.5°	507.1	507.3	507.5	507.6
120°	551.9	551.9	551.9	551.9
122.5°	594.9	595.1	595.2	595.4
125°	634.7	635.0	635.4	635.7
127.5°	676.3	676.0	675.6	675.3
130°	714.3	713.9	713.6	713.2
132.5°	749.6	749.1	748.5	748.0
135°	785.2	784.7	784.1	783.6
137.5°	818.7	818.3	817.9	817.6
140°	848.7	848.3	848.0	847.6
142.5°	876.9	876.4	875.8	875.3
145°	903.8	903.8	903.8	903.8
147.5°	927.0	926.1	925.2	924.3
150°	949.6	949.1	948.6	948.1
152.5°	969.7	968.8	967.9	967.0
155°	987.6	986.5	985.5	984.4
157.5°	1003.7	1002.3	1000.9	999.5
160°	1017.4	1016.2	1014.9	1013.7
162.5°	1030.3	1029.2	1028.2	1027.1
165°	1041.1	1039.9	1038.6	1037.4
167.5°	1049.5	1048.1	1046.7	1045.3
170°	1056.7	1055.3	1053.8	1052.4
172.5°	1061.1	1059.6	1058.0	1056.4
175°	1064.6	1063.2	1061.8	1060.3
177.5°	1066.4	1064.7	1062.9	1061.1
180°	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P831057

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.95	15.80	15.89	16.75	17.98	17.18	18.03	18.12	18.99	20.22
	3H	16.60	17.36	17.55	18.32	19.57	18.61	19.37	19.56	20.33	21.58
	4H	17.17	17.89	18.14	18.86	20.12	19.06	19.78	20.02	20.74	22.01
	6H	17.54	18.20	18.52	19.17	20.45	19.33	20.00	20.31	20.97	22.24
	8H	17.64	18.27	18.62	19.25	20.53	19.40	20.03	20.38	21.01	22.29
	12H	17.68	18.28	18.67	19.26	20.56	19.42	20.01	20.40	20.99	22.29
4H	2H	15.52	16.24	16.49	17.21	18.47	17.35	18.07	18.32	19.03	20.29
	3H	17.35	17.95	18.33	18.94	20.22	18.97	19.56	19.94	20.56	21.84
	4H	18.05	18.60	19.04	19.58	20.88	19.55	20.10	20.54	21.08	22.38
	6H	18.52	18.99	19.52	20.00	21.30	19.95	20.42	20.95	21.43	22.73
	8H	18.66	19.10	19.66	20.10	21.42	20.06	20.50	21.07	21.51	22.82
	12H	18.73	19.12	19.74	20.14	21.46	20.11	20.50	21.13	21.52	22.84
8H	4H	18.31	18.75	19.31	19.76	21.07	19.65	20.09	20.65	21.10	22.41
	6H	18.90	19.26	19.93	20.31	21.62	20.16	20.52	21.18	21.56	22.88
	8H	19.11	19.43	20.14	20.46	21.79	20.34	20.65	21.37	21.69	23.02
	12H	19.23	19.51	20.27	20.54	21.91	20.44	20.72	21.47	21.74	23.12
12H	4H	18.31	18.71	19.33	19.73	21.05	19.63	20.02	20.65	21.04	22.36
	6H	18.95	19.27	19.99	20.30	21.63	20.17	20.49	21.20	21.52	22.85
	8H	19.19	19.47	20.22	20.49	21.87	20.37	20.65	21.41	21.68	23.05