

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332073-930

Luminaire Tested: **S123DIP-S1165D1025U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332073-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1025U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6865.2 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332073-930
CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58				58
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	56	54	50				50
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42				42
3	83	74	67	61	78	69	63	58	61	56	51	52	49	45	45	42	40	36				36
4	76	66	58	52	71	62	55	49	54	48	44	47	43	39	40	37	34	31				31
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27				27
6	65	53	45	39	60	50	42	37	44	38	33	38	34	30	33	29	27	24				24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21				21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19				19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17				17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16				16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14235	14235	14235	14235
5°	16977	14296	12670	14296
10°	21249	14224	11444	14224
15°	26063	14110	10653	14110
20°	31047	13931	10143	13931
25°	32967	13713	10030	13713
30°	28256	13554	10082	13554
35°	19651	13328	10188	13328
40°	14802	13065	10156	13065
45°	12291	12670	10027	12670
50°	11010	11868	9937	11868
55°	10293	11003	9813	11003
60°	9655	10097	9711	10097
65°	9075	9205	9401	9205
70°	8510	8189	8954	8189
75°	7623	7170	8210	7170
80°	6670	5876	7073	5876
85°	5224	4273	4755	4273



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	1.9
10°-20°	417.7	6.1
20°-30°	701.1	10.2
30°-40°	793.9	11.6
40°-50°	711.9	10.4
50°-60°	574.5	8.4
60°-70°	400.3	5.8
70°-80°	210.4	3.1
80°-90°	54.5	0.8
90°-100°	67.5	1.0
100°-110°	202.0	2.9
110°-120°	343.6	5.0
120°-130°	451.9	6.6
130°-140°	508.0	7.4
140°-150°	499.3	7.3
150°-160°	420.4	6.1
160°-170°	279.8	4.1
170°-180°	98.0	1.4
0°-30°	1249.1	18.2
0°-40°	2043.0	29.8
0°-60°	3329.4	48.5
0°-90°	3994.7	58.2
90°-120°	613.1	8.9
90°-150°	2072.3	30.2
90°-180°	2870.0	41.8
0°-180°	6865.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1322	1322	1322	1322	1322	
5°	1571	1323	1173	1323	1571	163
15°	2339	1266	956	1266	2339	675
25°	2776	1155	844	1155	2776	1217
35°	1496	1014	775	1014	1496	972
45°	807	832	659	832	807	639
55°	548	586	523	586	548	492
65°	356	361	369	361	356	355
75°	183	172	197	172	183	196
85°	42	35	38	35	42	51
90°	24	1	24	1	24	14
95°	64	48	64	48	64	65
105°	194	183	194	183	194	206
115°	347	346	347	346	347	343
125°	500	506	500	506	500	448
135°	656	657	656	657	656	504
145°	797	797	797	797	797	497
155°	911	912	911	912	911	419
165°	990	994	990	994	990	279
175°	1030	1034	1030	1034	1030	98
180°	1036	1036	1036	1036	1036	



TEST NUMBER: P332073-930
 CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1403.5	1402.5	1400.0	1402.0	1397.9	1392.2	1391.7	1386.6	1371.7	1370.7	1366.6
5°	1571.2	1566.0	1565.4	1564.7	1555.8	1543.6	1520.5	1518.6	1487.8	1472.4	1453.9
7.5°	1788.2	1790.9	1781.6	1773.4	1746.0	1727.9	1703.2	1671.5	1633.7	1595.4	1569.9
10°	1944.1	1965.2	1938.9	1921.0	1904.4	1872.9	1836.5	1790.9	1745.4	1692.2	1651.9
12.5°	2111.2	2121.6	2116.3	2099.4	2073.5	2025.7	1961.0	1910.9	1869.0	1780.5	1744.7
15°	2338.8	2377.9	2352.9	2295.2	2296.5	2251.0	2166.4	2073.5	2024.1	1946.6	1840.9
17.5°	2581.2	2586.1	2575.4	2527.4	2495.4	2432.9	2354.8	2265.7	2165.8	2072.0	1959.8
20°	2710.4	2706.5	2684.1	2659.2	2604.1	2555.4	2470.1	2370.8	2242.6	2150.4	2028.0
22.5°	2782.2	2775.8	2765.2	2744.2	2698.4	2646.1	2569.6	2461.1	2339.0	2211.9	2070.5
25°	2775.8	2784.1	2785.4	2779.6	2763.6	2732.2	2672.0	2585.5	2463.8	2300.4	2153.0
27.5°	2524.6	2536.4	2570.6	2601.0	2635.0	2669.5	2664.9	2622.0	2531.9	2390.8	2210.6
30°	2273.4	2247.8	2311.2	2391.4	2445.8	2541.9	2595.7	2598.9	2548.3	2427.2	2251.6
32.5°	1924.8	1953.0	1981.1	2079.7	2198.7	2306.6	2413.8	2500.0	2509.9	2429.3	2275.7
35°	1495.5	1530.8	1582.0	1633.3	1761.5	1871.7	2060.0	2224.1	2354.8	2372.1	2277.9
37.5°	1205.2	1222.5	1255.0	1306.4	1390.2	1520.9	1666.6	1874.0	2063.4	2204.2	2210.4
40°	1053.4	1058.5	1095.0	1134.2	1202.1	1309.7	1441.0	1624.3	1851.1	2047.9	2129.9
42.5°	939.6	950.9	966.4	1004.0	1058.0	1139.1	1261.2	1412.6	1620.5	1846.9	2007.3
45°	807.4	820.2	829.8	854.8	893.2	947.7	1032.9	1171.3	1329.6	1563.4	1779.4
47.5°	720.0	721.0	728.1	747.0	773.1	814.0	874.2	963.2	1108.5	1298.2	1519.9
50°	657.5	667.6	670.3	684.9	705.5	735.6	785.5	861.2	980.4	1147.0	1350.7
52.5°	613.3	616.4	623.6	634.2	652.2	675.6	718.9	778.1	871.7	1013.7	1201.0
55°	548.5	548.5	555.5	563.9	574.1	595.3	624.1	667.6	738.8	849.0	1004.0
57.5°	488.5	491.7	496.7	499.3	508.0	522.0	546.1	579.1	632.2	717.0	840.3
60°	448.5	454.3	453.6	458.8	466.5	477.4	497.9	524.8	572.2	640.1	744.0
62.5°	413.7	413.3	413.2	419.3	427.0	437.4	450.7	474.0	514.3	574.5	662.9
65°	356.3	355.0	359.5	363.3	365.9	373.6	383.8	404.3	431.2	476.1	544.6
67.5°	305.2	301.6	303.9	305.2	309.7	315.6	325.2	337.9	359.3	395.3	447.0
70°	270.4	267.2	266.5	267.8	271.7	276.1	283.2	295.4	315.3	344.1	381.9
72.5°	234.5	232.4	232.2	235.1	236.8	239.8	244.8	255.9	271.7	293.3	328.6
75°	183.3	183.3	183.3	183.9	185.8	188.4	192.2	198.0	210.2	225.5	249.2
77.5°	137.4	137.2	136.5	136.3	139.2	140.3	141.2	146.6	153.4	163.8	181.1
80°	107.6	104.4	105.7	107.6	108.9	109.6	111.5	112.8	118.5	124.3	136.5
82.5°	80.0	77.3	77.5	80.5	80.7	81.4	83.3	85.1	87.2	92.5	99.1
85°	42.3	42.3	43.0	43.0	43.5	43.0	44.8	45.5	45.5	48.7	52.5
87.5°	20.3	19.2	19.6	20.1	19.5	19.9	20.2	20.6	21.0	21.4	21.4
90°	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0	20.2	19.6	17.2
92.5°	32.9	33.1	33.3	33.5	33.8	33.6	33.0	32.4	31.8	31.2	29.9
95°	63.5	63.5	63.5	63.5	63.5	63.1	62.4	61.6	61.0	60.3	58.8
97.5°	97.7	97.8	97.8	97.9	97.9	97.6	96.8	95.9	95.1	94.2	93.2
100°	123.7	123.4	122.9	122.6	122.3	121.8	121.2	120.7	120.2	119.6	118.7
102.5°	150.4	150.5	150.5	150.6	150.7	150.4	149.9	149.4	148.8	148.3	147.1
105°	193.7	193.3	193.0	192.6	192.2	192.1	192.1	192.1	192.1	192.1	190.5
107.5°	238.8	239.0	239.2	239.5	239.6	239.5	238.9	238.3	237.7	237.2	236.5
110°	269.4	269.8	270.1	270.4	270.8	270.7	269.9	269.2	268.5	267.7	267.4



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	301.9	302.0	302.1	302.1	302.2	301.8	300.9	300.1	299.2	298.3	298.3
115°	346.7	346.9	347.1	347.2	347.4	347.4	347.2	347.1	346.9	346.7	347.1
117.5°	392.1	392.6	393.1	393.6	394.1	394.4	394.4	394.4	394.5	394.5	395.0
120°	424.0	424.4	424.8	425.1	425.4	425.7	425.9	426.1	426.2	426.5	427.4
122.5°	454.6	455.1	455.6	456.2	456.6	457.1	457.6	458.0	458.5	459.0	459.5
125°	500.5	501.2	502.0	502.7	503.4	504.1	504.8	505.6	506.3	507.0	507.4
127.5°	546.3	547.1	547.9	548.8	549.6	550.5	551.5	552.5	553.5	554.6	555.0
130°	576.2	577.5	578.7	580.0	581.2	582.3	582.9	583.7	584.4	585.1	585.7
132.5°	607.5	608.5	609.4	610.4	611.4	612.3	613.2	614.0	614.9	615.7	616.1
135°	656.0	656.3	656.6	657.0	657.4	657.9	658.7	659.4	660.1	660.8	661.0
137.5°	698.8	699.4	700.1	700.8	701.5	702.2	703.0	703.8	704.5	705.2	704.8
140°	726.8	728.1	729.3	730.6	731.8	732.5	732.7	732.9	733.1	733.3	733.1
142.5°	755.4	756.4	757.3	758.3	759.3	759.9	760.1	760.3	760.4	760.6	760.3
145°	796.7	797.4	798.2	798.9	799.6	800.1	800.3	800.5	800.6	800.8	800.3
147.5°	833.6	834.6	835.7	836.8	837.9	838.5	838.5	838.5	838.5	838.5	837.9
150°	857.0	858.0	859.2	860.2	861.3	861.9	861.9	861.9	861.9	861.9	861.5
152.5°	879.8	880.7	881.7	882.6	883.5	883.9	883.5	883.3	883.0	882.7	882.5
155°	910.7	911.9	913.2	914.5	915.7	916.0	915.3	914.6	913.9	913.1	913.0
157.5°	938.8	939.9	940.9	941.9	942.9	943.1	942.2	941.5	940.8	940.0	939.9
160°	957.1	957.8	958.5	959.3	959.9	959.9	959.0	958.1	957.2	956.3	956.3
162.5°	970.8	971.9	973.1	974.2	975.3	975.5	974.6	973.7	972.8	971.9	971.8
165°	990.4	991.7	993.0	994.3	995.5	995.6	994.5	993.4	992.3	991.2	991.2
167.5°	1007.2	1008.4	1009.4	1010.6	1011.7	1011.7	1010.6	1009.4	1008.4	1007.2	1007.1
170°	1015.7	1016.9	1018.2	1019.5	1020.8	1020.8	1019.5	1018.2	1016.9	1015.7	1015.7
172.5°	1022.1	1023.4	1024.7	1026.0	1027.3	1027.3	1026.2	1025.1	1023.9	1022.8	1022.8
175°	1029.5	1030.8	1032.0	1033.3	1034.5	1034.7	1033.6	1032.5	1031.4	1030.3	1030.3
177.5°	1033.4	1034.5	1035.4	1036.5	1037.5	1037.5	1036.7	1035.8	1034.9	1034.0	1034.0
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1363.5	1359.4	1355.4	1348.2	1342.0	1333.3	1330.7	1327.6	1318.4	1310.3	1304.1
5°	1446.8	1431.4	1409.0	1388.5	1371.9	1349.5	1336.6	1323.1	1303.9	1286.6	1272.5
7.5°	1534.0	1503.7	1468.8	1431.2	1396.1	1362.3	1335.0	1310.6	1283.7	1258.2	1238.4
10°	1603.2	1559.6	1510.9	1458.4	1413.5	1369.9	1333.4	1301.4	1266.8	1236.6	1211.7
12.5°	1682.1	1617.6	1550.4	1486.5	1433.5	1373.0	1328.8	1288.1	1248.9	1212.6	1184.5
15°	1775.6	1693.5	1614.0	1526.3	1445.5	1369.9	1317.4	1266.2	1220.7	1183.5	1147.6
17.5°	1860.7	1767.7	1663.0	1556.2	1458.9	1369.2	1295.6	1237.7	1180.8	1135.3	1099.5
20°	1908.9	1803.1	1684.6	1573.7	1466.1	1366.1	1285.4	1216.2	1154.6	1106.6	1066.2
22.5°	1950.4	1826.7	1704.1	1585.5	1465.6	1357.9	1266.4	1195.1	1128.5	1081.5	1038.5
25°	1993.4	1845.4	1722.4	1583.3	1449.4	1337.9	1235.4	1154.6	1088.0	1032.9	988.7
27.5°	2030.3	1844.1	1698.1	1548.6	1424.0	1312.3	1202.8	1116.2	1045.5	985.6	940.8
30°	2054.9	1846.7	1673.0	1525.0	1399.5	1284.1	1177.7	1090.5	1016.3	955.4	913.1
32.5°	2070.3	1845.1	1649.9	1492.2	1360.5	1258.4	1150.6	1060.3	984.0	924.1	883.4
35°	2079.3	1833.9	1610.2	1424.4	1297.5	1198.2	1107.9	1014.3	934.3	878.5	832.3
37.5°	2061.3	1810.1	1564.1	1359.0	1220.2	1122.3	1046.4	966.6	890.0	828.7	788.9
40°	2033.1	1794.8	1528.2	1313.0	1166.9	1072.6	1008.0	929.8	854.1	795.8	758.6
42.5°	1979.3	1763.5	1488.7	1261.7	1111.5	1017.2	957.7	892.3	820.8	766.1	729.0
45°	1848.0	1695.4	1429.5	1184.8	1029.7	932.3	879.8	832.3	767.6	714.4	682.4
47.5°	1665.7	1593.1	1343.9	1103.7	944.4	850.7	796.1	757.9	710.6	667.6	636.9
50°	1539.1	1509.0	1286.0	1048.3	887.5	795.8	743.3	708.7	674.7	631.8	603.6
52.5°	1393.0	1411.6	1218.4	990.8	829.6	739.5	690.0	662.5	631.7	596.4	571.9
55°	1187.3	1254.6	1101.5	894.5	743.3	657.5	610.7	586.3	568.3	542.1	521.0
57.5°	994.7	1080.4	975.1	795.2	658.6	584.5	539.6	513.1	501.6	487.9	471.2
60°	880.4	965.0	884.9	728.6	601.7	531.2	491.5	469.0	457.5	447.9	433.8
62.5°	778.4	864.0	796.7	660.9	545.8	480.5	445.8	424.0	415.0	409.9	397.9
65°	638.2	711.9	667.0	555.5	465.9	408.1	376.7	361.4	353.0	351.1	343.5
67.5°	519.4	575.5	542.8	460.8	390.2	340.4	313.7	300.7	294.2	293.6	287.8
70°	441.5	494.0	469.0	394.7	333.9	294.7	271.7	260.2	256.3	255.7	252.5
72.5°	381.0	417.7	397.8	335.7	288.7	253.2	236.3	224.3	219.9	220.8	218.7
75°	281.9	309.5	298.0	255.0	217.2	194.1	180.0	172.4	168.5	170.5	167.9
77.5°	202.8	220.3	209.9	180.2	156.9	140.2	129.8	125.1	121.6	121.5	120.3
80°	153.1	163.4	157.6	139.7	120.5	106.4	98.0	94.8	92.9	92.3	91.6
82.5°	109.1	117.8	111.0	98.7	85.6	77.1	72.4	68.2	66.8	67.2	66.5
85°	55.1	58.3	55.8	48.0	43.0	39.1	36.5	34.6	33.3	34.0	32.7
87.5°	21.9	22.0	20.0	17.5	16.1	14.2	13.9	12.5	11.8	12.1	12.0
90°	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8	2.6	4.4	6.3
92.5°	28.5	27.2	25.9	24.6	23.4	22.2	21.0	19.7	21.0	22.2	23.4
95°	57.3	55.8	54.5	53.1	51.9	50.5	49.2	48.0	49.2	50.5	51.9
97.5°	92.1	91.1	90.0	89.0	88.1	87.2	86.3	85.3	86.3	87.2	88.1
100°	117.8	116.9	116.0	115.0	113.9	112.8	111.8	110.7	111.8	112.8	113.9
102.5°	145.9	144.7	143.5	142.6	141.9	141.3	140.6	140.0	140.6	141.3	141.9
105°	188.8	187.2	185.6	184.6	184.2	183.8	183.4	183.1	183.4	183.8	184.2
107.5°	235.9	235.2	234.6	234.2	233.9	233.7	233.5	233.3	233.5	233.7	233.9
110°	267.0	266.7	266.3	266.0	265.5	265.2	264.9	264.5	264.9	265.2	265.5



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	298.2	298.2	298.1	297.9	297.7	297.5	297.3	297.0	297.3	297.5	297.7
115°	347.4	347.8	348.1	348.1	347.5	347.0	346.4	345.8	346.4	347.0	347.5
117.5°	395.5	396.0	396.4	396.5	396.2	395.7	395.4	395.0	395.4	395.7	396.2
120°	428.3	429.2	430.1	430.0	428.9	427.8	426.7	425.7	426.7	427.8	428.9
122.5°	459.9	460.4	460.9	460.7	459.9	459.1	458.4	457.5	458.4	459.1	459.9
125°	507.8	508.1	508.5	508.3	507.8	507.3	506.8	506.2	506.8	507.3	507.8
127.5°	555.4	555.7	556.1	555.8	554.6	553.4	552.3	551.1	552.3	553.4	554.6
130°	586.2	586.8	587.3	586.9	585.4	584.0	582.5	581.1	582.5	584.0	585.4
132.5°	616.5	616.9	617.3	616.9	615.4	613.9	612.5	611.1	612.5	613.9	615.4
135°	661.2	661.4	661.5	661.1	660.0	658.9	657.9	656.8	657.9	658.9	660.0
137.5°	704.3	703.8	703.4	702.7	701.8	700.9	700.0	699.1	700.0	700.9	701.8
140°	732.9	732.7	732.5	732.0	731.1	730.2	729.3	728.4	729.3	730.2	731.1
142.5°	759.9	759.6	759.3	758.7	757.8	756.9	755.9	755.0	755.9	756.9	757.8
145°	799.7	799.2	798.7	798.2	797.9	797.4	797.1	796.7	797.1	797.4	797.9
147.5°	837.4	836.9	836.4	835.8	835.2	834.5	833.9	833.2	833.9	834.5	835.2
150°	861.1	860.8	860.4	860.1	859.7	859.3	859.0	858.6	859.0	859.3	859.7
152.5°	882.2	882.1	881.8	881.4	880.9	880.4	880.0	879.5	880.0	880.4	880.9
155°	912.7	912.6	912.4	912.3	912.3	912.3	912.3	912.3	912.3	912.3	912.3
157.5°	939.7	939.6	939.4	939.5	939.6	939.9	940.1	940.3	940.1	939.9	939.6
160°	956.3	956.3	956.3	956.4	956.8	957.2	957.5	957.9	957.5	957.2	956.8
162.5°	971.6	971.4	971.3	971.5	972.0	972.5	973.0	973.5	973.0	972.5	972.0
165°	991.2	991.2	991.2	991.6	992.1	992.6	993.1	993.7	993.1	992.6	992.1
167.5°	1006.9	1006.8	1006.7	1006.9	1007.6	1008.4	1009.1	1009.8	1009.1	1008.4	1007.6
170°	1015.7	1015.7	1015.7	1016.0	1016.8	1017.5	1018.2	1019.0	1018.2	1017.5	1016.8
172.5°	1022.8	1022.8	1022.8	1023.2	1023.9	1024.7	1025.4	1026.1	1025.4	1024.7	1023.9
175°	1030.3	1030.3	1030.3	1030.7	1031.4	1032.1	1032.8	1033.6	1032.8	1032.1	1031.4
177.5°	1034.0	1034.0	1034.0	1034.4	1034.9	1035.5	1036.1	1036.7	1036.1	1035.5	1034.9
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1300.5	1296.9	1291.8	1284.1	1277.9	1268.2	1268.2	1269.7	1269.7	1269.3	1268.2
5°	1261.0	1251.4	1239.9	1226.5	1212.4	1198.2	1195.6	1190.5	1186.7	1184.1	1181.0
7.5°	1219.4	1202.3	1185.5	1166.7	1149.5	1135.3	1125.4	1117.2	1112.0	1106.4	1102.2
10°	1191.2	1170.0	1150.1	1130.3	1108.5	1091.2	1080.4	1072.6	1066.9	1061.8	1059.2
12.5°	1157.9	1133.7	1111.7	1092.9	1069.0	1051.2	1040.9	1037.2	1030.5	1019.7	1014.1
15°	1109.1	1086.7	1060.5	1031.6	1020.1	998.3	986.1	980.4	976.5	968.2	965.6
17.5°	1067.5	1038.1	1008.7	987.2	965.7	948.0	941.3	934.1	929.0	922.2	920.1
20°	1034.2	1008.0	981.0	958.0	935.5	916.3	910.5	905.4	900.3	897.1	894.5
22.5°	1000.4	974.1	951.8	930.3	906.3	893.7	887.5	881.8	878.2	876.0	873.5
25°	952.8	929.8	904.7	885.5	866.3	857.9	854.1	850.9	848.4	845.1	844.5
27.5°	910.3	885.2	864.9	846.9	833.2	826.2	822.5	820.9	821.5	822.6	823.4
30°	878.5	855.4	838.8	823.4	810.6	804.1	803.5	803.5	806.1	806.7	808.0
32.5°	849.3	830.3	813.7	798.7	789.0	784.6	787.1	787.1	789.1	790.8	793.1
35°	806.7	790.0	777.2	764.4	756.1	758.0	759.3	760.6	763.8	767.6	770.2
37.5°	766.1	751.6	738.3	728.3	724.5	727.9	731.0	733.7	737.4	740.4	742.9
40°	736.9	725.9	713.1	704.2	705.5	707.4	710.0	713.1	716.4	718.3	720.9
42.5°	709.7	698.3	688.6	681.1	682.9	685.3	686.9	688.6	692.3	695.8	697.2
45°	668.3	659.3	650.4	645.9	647.2	648.5	649.7	651.7	654.8	657.5	658.0
47.5°	621.8	615.6	609.5	605.1	607.2	606.7	608.4	612.5	613.4	615.0	618.6
50°	592.1	586.3	579.3	578.0	578.0	578.0	578.6	583.8	583.8	586.3	588.9
52.5°	559.3	555.5	551.1	548.8	547.7	547.7	550.4	553.0	554.0	557.6	560.2
55°	510.7	506.9	503.0	501.1	499.8	501.1	506.2	507.4	510.7	512.6	514.5
57.5°	460.1	457.1	454.0	453.0	452.7	454.4	457.2	461.1	461.9	467.7	470.7
60°	426.7	422.2	419.7	419.7	418.4	424.2	422.9	429.3	430.6	434.5	439.0
62.5°	392.4	386.4	385.4	385.4	387.2	388.8	390.6	393.5	396.7	401.6	405.1
65°	337.0	333.9	338.3	337.7	336.4	340.2	340.2	343.5	347.3	351.8	358.8
67.5°	284.6	283.0	283.3	283.3	285.3	287.5	289.3	292.0	296.7	301.4	306.1
70°	249.2	251.2	248.0	250.5	252.5	253.1	254.4	258.2	263.3	266.5	271.7
72.5°	214.9	214.7	215.2	216.2	218.1	219.2	220.5	224.9	230.6	233.3	237.3
75°	165.3	164.7	166.6	166.6	169.8	171.0	172.4	174.3	179.4	183.3	186.5
77.5°	120.7	121.5	121.1	123.3	122.4	122.6	126.6	128.6	129.1	136.6	138.3
80°	91.0	92.3	92.9	93.5	94.2	92.9	97.4	99.3	99.3	103.8	107.0
82.5°	65.4	66.1	67.8	68.4	68.6	69.9	70.2	71.7	73.2	75.1	79.3
85°	32.7	34.6	35.2	34.6	35.2	34.0	35.9	36.5	37.2	37.2	37.2
87.5°	11.8	12.8	12.7	13.7	13.7	14.7	14.8	13.9	14.1	15.7	13.9
90°	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0	21.7	22.4	23.0
92.5°	24.6	25.9	27.2	28.5	29.9	31.2	31.8	32.4	33.0	33.6	33.8
95°	53.1	54.5	55.8	57.3	58.8	60.3	61.0	61.6	62.4	63.1	63.5
97.5°	89.0	90.0	91.1	92.1	93.2	94.2	95.1	95.9	96.8	97.6	97.9
100°	115.0	116.0	116.9	117.8	118.7	119.6	120.2	120.7	121.2	121.8	122.3
102.5°	142.6	143.5	144.7	145.9	147.1	148.3	148.8	149.4	149.9	150.4	150.7
105°	184.6	185.6	187.2	188.8	190.5	192.1	192.1	192.1	192.1	192.1	192.2
107.5°	234.2	234.6	235.2	235.9	236.5	237.2	237.7	238.3	238.9	239.5	239.6
110°	266.0	266.3	266.7	267.0	267.4	267.7	268.5	269.2	269.9	270.7	270.8



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	297.9	298.1	298.2	298.2	298.3	298.3	299.2	300.1	300.9	301.8	302.2
115°	348.1	348.1	347.8	347.4	347.1	346.7	346.9	347.1	347.2	347.4	347.4
117.5°	396.5	396.4	396.0	395.5	395.0	394.5	394.5	394.4	394.4	394.4	394.1
120°	430.0	430.1	429.2	428.3	427.4	426.5	426.2	426.1	425.9	425.7	425.4
122.5°	460.7	460.9	460.4	459.9	459.5	459.0	458.5	458.0	457.6	457.1	456.6
125°	508.3	508.5	508.1	507.8	507.4	507.0	506.3	505.6	504.8	504.1	503.4
127.5°	555.8	556.1	555.7	555.4	555.0	554.6	553.5	552.5	551.5	550.5	549.6
130°	586.9	587.3	586.8	586.2	585.7	585.1	584.4	583.7	582.9	582.3	581.2
132.5°	616.9	617.3	616.9	616.5	616.1	615.7	614.9	614.0	613.2	612.3	611.4
135°	661.1	661.5	661.4	661.2	661.0	660.8	660.1	659.4	658.7	657.9	657.4
137.5°	702.7	703.4	703.8	704.3	704.8	705.2	704.5	703.8	703.0	702.2	701.5
140°	732.0	732.5	732.7	732.9	733.1	733.3	733.1	732.9	732.7	732.5	731.8
142.5°	758.7	759.3	759.6	759.9	760.3	760.6	760.4	760.3	760.1	759.9	759.3
145°	798.2	798.7	799.2	799.7	800.3	800.8	800.6	800.5	800.3	800.1	799.6
147.5°	835.8	836.4	836.9	837.4	837.9	838.5	838.5	838.5	838.5	838.5	837.9
150°	860.1	860.4	860.8	861.1	861.5	861.9	861.9	861.9	861.9	861.9	861.3
152.5°	881.4	881.8	882.1	882.2	882.5	882.7	883.0	883.3	883.5	883.9	883.5
155°	912.3	912.4	912.6	912.7	913.0	913.1	913.9	914.6	915.3	916.0	915.7
157.5°	939.5	939.4	939.6	939.7	939.9	940.0	940.8	941.5	942.2	943.1	942.9
160°	956.4	956.3	956.3	956.3	956.3	956.3	957.2	958.1	959.0	959.9	959.9
162.5°	971.5	971.3	971.4	971.6	971.8	971.9	972.8	973.7	974.6	975.5	975.3
165°	991.6	991.2	991.2	991.2	991.2	991.2	992.3	993.4	994.5	995.6	995.5
167.5°	1006.9	1006.7	1006.8	1006.9	1007.1	1007.2	1008.4	1009.4	1010.6	1011.7	1011.7
170°	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9	1018.2	1019.5	1020.8	1020.8
172.5°	1023.2	1022.8	1022.8	1022.8	1022.8	1022.8	1023.9	1025.1	1026.2	1027.3	1027.3
175°	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4	1032.5	1033.6	1034.7	1034.5
177.5°	1034.4	1034.0	1034.0	1034.0	1034.0	1034.0	1034.9	1035.8	1036.7	1037.5	1037.5
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1264.6	1264.1	1267.7	1265.1	1267.7	1264.1	1264.6	1268.2	1269.3	1269.7	1269.7
5°	1177.0	1179.0	1172.6	1172.6	1172.6	1179.0	1177.0	1181.0	1184.1	1186.7	1190.5
7.5°	1099.2	1096.3	1096.6	1093.2	1096.6	1096.3	1099.2	1102.2	1106.4	1112.0	1117.2
10°	1051.5	1047.7	1046.4	1047.0	1046.4	1047.7	1051.5	1059.2	1061.8	1066.9	1072.6
12.5°	1012.0	1011.2	1002.8	1002.9	1002.8	1011.2	1012.0	1014.1	1019.7	1030.5	1037.2
15°	965.6	953.5	952.2	956.0	952.2	953.5	965.6	965.6	968.2	976.5	980.4
17.5°	919.1	912.7	913.1	911.2	913.1	912.7	919.1	920.1	922.2	929.0	934.1
20°	894.5	890.6	890.0	885.5	890.0	890.6	894.5	894.5	897.1	900.3	905.4
22.5°	872.0	870.7	871.1	866.1	871.1	870.7	872.0	873.5	876.0	878.2	881.8
25°	843.9	847.1	844.5	844.5	844.5	847.1	843.9	844.5	845.1	848.4	850.9
27.5°	824.9	824.8	823.5	823.5	823.5	824.8	824.9	823.4	822.6	821.5	820.9
30°	810.6	809.9	811.2	811.2	811.2	809.9	810.6	808.0	806.7	806.1	803.5
32.5°	796.2	797.1	797.4	797.9	797.4	797.1	796.2	793.1	790.8	789.1	787.1
35°	774.0	774.7	776.6	775.3	776.6	774.7	774.0	770.2	767.6	763.8	760.6
37.5°	744.0	747.0	746.3	747.4	746.3	747.0	744.0	742.9	740.4	737.4	733.7
40°	721.5	723.4	722.8	722.8	722.8	723.4	721.5	720.9	718.3	716.4	713.1
42.5°	698.5	699.9	698.1	697.2	698.1	699.9	698.5	697.2	695.8	692.3	688.6
45°	660.6	659.3	661.3	658.7	661.3	659.3	660.6	658.0	657.5	654.8	651.7
47.5°	618.3	619.6	620.1	622.1	620.1	619.6	618.3	618.6	615.0	613.4	612.5
50°	590.1	593.9	593.9	593.4	593.9	593.9	590.1	588.9	586.3	583.8	583.8
52.5°	562.5	564.3	566.8	566.7	566.8	564.3	562.5	560.2	557.6	554.0	553.0
55°	519.7	521.0	522.2	522.9	522.2	521.0	519.7	514.5	512.6	510.7	507.4
57.5°	475.3	474.8	477.8	478.7	477.8	474.8	475.3	470.7	467.7	461.9	461.1
60°	444.0	444.0	449.1	451.1	449.1	444.0	444.0	439.0	434.5	430.6	429.3
62.5°	410.7	412.8	417.9	415.2	417.9	412.8	410.7	405.1	401.6	396.7	393.5
65°	362.0	367.1	366.5	369.1	366.5	367.1	362.0	358.8	351.8	347.3	343.5
67.5°	311.1	314.4	318.9	319.4	318.9	314.4	311.1	306.1	301.4	296.7	292.0
70°	276.8	280.0	282.6	284.5	282.6	280.0	276.8	271.7	266.5	263.3	258.2
72.5°	243.5	245.2	251.3	248.6	251.3	245.2	243.5	237.3	233.3	230.6	224.9
75°	190.9	195.4	199.3	197.4	199.3	195.4	190.9	186.5	183.3	179.4	174.3
77.5°	141.2	145.7	147.5	145.9	147.5	145.7	141.2	138.3	136.6	129.1	128.6
80°	111.5	110.9	114.7	114.1	114.7	110.9	111.5	107.0	103.8	99.3	99.3
82.5°	81.8	81.1	82.9	83.3	82.9	81.1	81.8	79.3	75.1	73.2	71.7
85°	39.7	41.7	39.1	38.5	39.1	41.7	39.7	37.2	37.2	37.2	36.5
87.5°	13.9	13.9	13.5	13.0	13.5	13.9	13.9	13.9	15.7	14.1	13.9
90°	23.3	23.7	24.1	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0
92.5°	33.5	33.3	33.1	32.9	33.1	33.3	33.5	33.8	33.6	33.0	32.4
95°	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.1	62.4	61.6
97.5°	97.9	97.8	97.8	97.7	97.8	97.8	97.9	97.9	97.6	96.8	95.9
100°	122.6	122.9	123.4	123.7	123.4	122.9	122.6	122.3	121.8	121.2	120.7
102.5°	150.6	150.5	150.5	150.4	150.5	150.5	150.6	150.7	150.4	149.9	149.4
105°	192.6	193.0	193.3	193.7	193.3	193.0	192.6	192.2	192.1	192.1	192.1
107.5°	239.5	239.2	239.0	238.8	239.0	239.2	239.5	239.6	239.5	238.9	238.3
110°	270.4	270.1	269.8	269.4	269.8	270.1	270.4	270.8	270.7	269.9	269.2



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	302.1	302.1	302.0	301.9	302.0	302.1	302.1	302.2	301.8	300.9	300.1
115°	347.2	347.1	346.9	346.7	346.9	347.1	347.2	347.4	347.4	347.2	347.1
117.5°	393.6	393.1	392.6	392.1	392.6	393.1	393.6	394.1	394.4	394.4	394.4
120°	425.1	424.8	424.4	424.0	424.4	424.8	425.1	425.4	425.7	425.9	426.1
122.5°	456.2	455.6	455.1	454.6	455.1	455.6	456.2	456.6	457.1	457.6	458.0
125°	502.7	502.0	501.2	500.5	501.2	502.0	502.7	503.4	504.1	504.8	505.6
127.5°	548.8	547.9	547.1	546.3	547.1	547.9	548.8	549.6	550.5	551.5	552.5
130°	580.0	578.7	577.5	576.2	577.5	578.7	580.0	581.2	582.3	582.9	583.7
132.5°	610.4	609.4	608.5	607.5	608.5	609.4	610.4	611.4	612.3	613.2	614.0
135°	657.0	656.6	656.3	656.0	656.3	656.6	657.0	657.4	657.9	658.7	659.4
137.5°	700.8	700.1	699.4	698.8	699.4	700.1	700.8	701.5	702.2	703.0	703.8
140°	730.6	729.3	728.1	726.8	728.1	729.3	730.6	731.8	732.5	732.7	732.9
142.5°	758.3	757.3	756.4	755.4	756.4	757.3	758.3	759.3	759.9	760.1	760.3
145°	798.9	798.2	797.4	796.7	797.4	798.2	798.9	799.6	800.1	800.3	800.5
147.5°	836.8	835.7	834.6	833.6	834.6	835.7	836.8	837.9	838.5	838.5	838.5
150°	860.2	859.2	858.0	857.0	858.0	859.2	860.2	861.3	861.9	861.9	861.9
152.5°	882.6	881.7	880.7	879.8	880.7	881.7	882.6	883.5	883.9	883.5	883.3
155°	914.5	913.2	911.9	910.7	911.9	913.2	914.5	915.7	916.0	915.3	914.6
157.5°	941.9	940.9	939.9	938.8	939.9	940.9	941.9	942.9	943.1	942.2	941.5
160°	959.3	958.5	957.8	957.1	957.8	958.5	959.3	959.9	959.9	959.0	958.1
162.5°	974.2	973.1	971.9	970.8	971.9	973.1	974.2	975.3	975.5	974.6	973.7
165°	994.3	993.0	991.7	990.4	991.7	993.0	994.3	995.5	995.6	994.5	993.4
167.5°	1010.6	1009.4	1008.4	1007.2	1008.4	1009.4	1010.6	1011.7	1011.7	1010.6	1009.4
170°	1019.5	1018.2	1016.9	1015.7	1016.9	1018.2	1019.5	1020.8	1020.8	1019.5	1018.2
172.5°	1026.0	1024.7	1023.4	1022.1	1023.4	1024.7	1026.0	1027.3	1027.3	1026.2	1025.1
175°	1033.3	1032.0	1030.8	1029.5	1030.8	1032.0	1033.3	1034.5	1034.7	1033.6	1032.5
177.5°	1036.5	1035.4	1034.5	1033.4	1034.5	1035.4	1036.5	1037.5	1037.5	1036.7	1035.8
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1268.2	1268.2	1277.9	1284.1	1291.8	1296.9	1300.5	1304.1	1310.3	1318.4	1327.6
5°	1195.6	1198.2	1212.4	1226.5	1239.9	1251.4	1261.0	1272.5	1286.6	1303.9	1323.1
7.5°	1125.4	1135.3	1149.5	1166.7	1185.5	1202.3	1219.4	1238.4	1258.2	1283.7	1310.6
10°	1080.4	1091.2	1108.5	1130.3	1150.1	1170.0	1191.2	1211.7	1236.6	1266.8	1301.4
12.5°	1040.9	1051.2	1069.0	1092.9	1111.7	1133.7	1157.9	1184.5	1212.6	1248.9	1288.1
15°	986.1	998.3	1020.1	1031.6	1060.5	1086.7	1109.1	1147.6	1183.5	1220.7	1266.2
17.5°	941.3	948.0	965.7	987.2	1008.7	1038.1	1067.5	1099.5	1135.3	1180.8	1237.7
20°	910.5	916.3	935.5	958.0	981.0	1008.0	1034.2	1066.2	1106.6	1154.6	1216.2
22.5°	887.5	893.7	906.3	930.3	951.8	974.1	1000.4	1038.5	1081.5	1128.5	1195.1
25°	854.1	857.9	866.3	885.5	904.7	929.8	952.8	988.7	1032.9	1088.0	1154.6
27.5°	822.5	826.2	833.2	846.9	864.9	885.2	910.3	940.8	985.6	1045.5	1116.2
30°	803.5	804.1	810.6	823.4	838.8	855.4	878.5	913.1	955.4	1016.3	1090.5
32.5°	787.1	784.6	789.0	798.7	813.7	830.3	849.3	883.4	924.1	984.0	1060.3
35°	759.3	758.0	756.1	764.4	777.2	790.0	806.7	832.3	878.5	934.3	1014.3
37.5°	731.0	727.9	724.5	728.3	738.3	751.6	766.1	788.9	828.7	890.0	966.6
40°	710.0	707.4	705.5	704.2	713.1	725.9	736.9	758.6	795.8	854.1	929.8
42.5°	686.9	685.3	682.9	681.1	688.6	698.3	709.7	729.0	766.1	820.8	892.3
45°	649.7	648.5	647.2	645.9	650.4	659.3	668.3	682.4	714.4	767.6	832.3
47.5°	608.4	606.7	607.2	605.1	609.5	615.6	621.8	636.9	667.6	710.6	757.9
50°	578.6	578.0	578.0	578.0	579.3	586.3	592.1	603.6	631.8	674.7	708.7
52.5°	550.4	547.7	547.7	548.8	551.1	555.5	559.3	571.9	596.4	631.7	662.5
55°	506.2	501.1	499.8	501.1	503.0	506.9	510.7	521.0	542.1	568.3	586.3
57.5°	457.2	454.4	452.7	453.0	454.0	457.1	460.1	471.2	487.9	501.6	513.1
60°	422.9	424.2	418.4	419.7	419.7	422.2	426.7	433.8	447.9	457.5	469.0
62.5°	390.6	388.8	387.2	385.4	385.4	386.4	392.4	397.9	409.9	415.0	424.0
65°	340.2	340.2	336.4	337.7	338.3	333.9	337.0	343.5	351.1	353.0	361.4
67.5°	289.3	287.5	285.3	283.3	283.3	283.0	284.6	287.8	293.6	294.2	300.7
70°	254.4	253.1	252.5	250.5	248.0	251.2	249.2	252.5	255.7	256.3	260.2
72.5°	220.5	219.2	218.1	216.2	215.2	214.7	214.9	218.7	220.8	219.9	224.3
75°	172.4	171.0	169.8	166.6	166.6	164.7	165.3	167.9	170.5	168.5	172.4
77.5°	126.6	122.6	122.4	123.3	121.1	121.5	120.7	120.3	121.5	121.6	125.1
80°	97.4	92.9	94.2	93.5	92.9	92.3	91.0	91.6	92.3	92.9	94.8
82.5°	70.2	69.9	68.6	68.4	67.8	66.1	65.4	66.5	67.2	66.8	68.2
85°	35.9	34.0	35.2	34.6	35.2	34.6	32.7	32.7	34.0	33.3	34.6
87.5°	14.8	14.7	13.7	13.7	12.7	12.8	11.8	12.0	12.1	11.8	12.5
90°	20.2	19.6	17.2	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8
92.5°	31.8	31.2	29.9	28.5	27.2	25.9	24.6	23.4	22.2	21.0	19.7
95°	61.0	60.3	58.8	57.3	55.8	54.5	53.1	51.9	50.5	49.2	48.0
97.5°	95.1	94.2	93.2	92.1	91.1	90.0	89.0	88.1	87.2	86.3	85.3
100°	120.2	119.6	118.7	117.8	116.9	116.0	115.0	113.9	112.8	111.8	110.7
102.5°	148.8	148.3	147.1	145.9	144.7	143.5	142.6	141.9	141.3	140.6	140.0
105°	192.1	192.1	190.5	188.8	187.2	185.6	184.6	184.2	183.8	183.4	183.1
107.5°	237.7	237.2	236.5	235.9	235.2	234.6	234.2	233.9	233.7	233.5	233.3
110°	268.5	267.7	267.4	267.0	266.7	266.3	266.0	265.5	265.2	264.9	264.5



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	299.2	298.3	298.3	298.2	298.2	298.1	297.9	297.7	297.5	297.3	297.0
115°	346.9	346.7	347.1	347.4	347.8	348.1	348.1	347.5	347.0	346.4	345.8
117.5°	394.5	394.5	395.0	395.5	396.0	396.4	396.5	396.2	395.7	395.4	395.0
120°	426.2	426.5	427.4	428.3	429.2	430.1	430.0	428.9	427.8	426.7	425.7
122.5°	458.5	459.0	459.5	459.9	460.4	460.9	460.7	459.9	459.1	458.4	457.5
125°	506.3	507.0	507.4	507.8	508.1	508.5	508.3	507.8	507.3	506.8	506.2
127.5°	553.5	554.6	555.0	555.4	555.7	556.1	555.8	554.6	553.4	552.3	551.1
130°	584.4	585.1	585.7	586.2	586.8	587.3	586.9	585.4	584.0	582.5	581.1
132.5°	614.9	615.7	616.1	616.5	616.9	617.3	616.9	615.4	613.9	612.5	611.1
135°	660.1	660.8	661.0	661.2	661.4	661.5	661.1	660.0	658.9	657.9	656.8
137.5°	704.5	705.2	704.8	704.3	703.8	703.4	702.7	701.8	700.9	700.0	699.1
140°	733.1	733.3	733.1	732.9	732.7	732.5	732.0	731.1	730.2	729.3	728.4
142.5°	760.4	760.6	760.3	759.9	759.6	759.3	758.7	757.8	756.9	755.9	755.0
145°	800.6	800.8	800.3	799.7	799.2	798.7	798.2	797.9	797.4	797.1	796.7
147.5°	838.5	838.5	837.9	837.4	836.9	836.4	835.8	835.2	834.5	833.9	833.2
150°	861.9	861.9	861.5	861.1	860.8	860.4	860.1	859.7	859.3	859.0	858.6
152.5°	883.0	882.7	882.5	882.2	882.1	881.8	881.4	880.9	880.4	880.0	879.5
155°	913.9	913.1	913.0	912.7	912.6	912.4	912.3	912.3	912.3	912.3	912.3
157.5°	940.8	940.0	939.9	939.7	939.6	939.4	939.5	939.6	939.9	940.1	940.3
160°	957.2	956.3	956.3	956.3	956.3	956.3	956.4	956.8	957.2	957.5	957.9
162.5°	972.8	971.9	971.8	971.6	971.4	971.3	971.5	972.0	972.5	973.0	973.5
165°	992.3	991.2	991.2	991.2	991.2	991.2	991.6	992.1	992.6	993.1	993.7
167.5°	1008.4	1007.2	1007.1	1006.9	1006.8	1006.7	1006.9	1007.6	1008.4	1009.1	1009.8
170°	1016.9	1015.7	1015.7	1015.7	1015.7	1015.7	1016.0	1016.8	1017.5	1018.2	1019.0
172.5°	1023.9	1022.8	1022.8	1022.8	1022.8	1022.8	1023.2	1023.9	1024.7	1025.4	1026.1
175°	1031.4	1030.3	1030.3	1030.3	1030.3	1030.3	1030.7	1031.4	1032.1	1032.8	1033.6
177.5°	1034.9	1034.0	1034.0	1034.0	1034.0	1034.0	1034.4	1034.9	1035.5	1036.1	1036.7
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332073-930
 CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1330.7	1333.3	1342.0	1348.2	1355.4	1359.4	1363.5	1366.6	1370.7	1371.7	1386.6
5°	1336.6	1349.5	1371.9	1388.5	1409.0	1431.4	1446.8	1453.9	1472.4	1487.8	1518.6
7.5°	1335.0	1362.3	1396.1	1431.2	1468.8	1503.7	1534.0	1569.9	1595.4	1633.7	1671.5
10°	1333.4	1369.9	1413.5	1458.4	1510.9	1559.6	1603.2	1651.9	1692.2	1745.4	1790.9
12.5°	1328.8	1373.0	1433.5	1486.5	1550.4	1617.6	1682.1	1744.7	1780.5	1869.0	1910.9
15°	1317.4	1369.9	1445.5	1526.3	1614.0	1693.5	1775.6	1840.9	1946.6	2024.1	2073.5
17.5°	1295.6	1369.2	1458.9	1556.2	1663.0	1767.7	1860.7	1959.8	2072.0	2165.8	2265.7
20°	1285.4	1366.1	1466.1	1573.7	1684.6	1803.1	1908.9	2028.0	2150.4	2242.6	2370.8
22.5°	1266.4	1357.9	1465.6	1585.5	1704.1	1826.7	1950.4	2070.5	2211.9	2339.0	2461.1
25°	1235.4	1337.9	1449.4	1583.3	1722.4	1845.4	1993.4	2153.0	2300.4	2463.8	2585.5
27.5°	1202.8	1312.3	1424.0	1548.6	1698.1	1844.1	2030.3	2210.6	2390.8	2531.9	2622.0
30°	1177.7	1284.1	1399.5	1525.0	1673.0	1846.7	2054.9	2251.6	2427.2	2548.3	2598.9
32.5°	1150.6	1258.4	1360.5	1492.2	1649.9	1845.1	2070.3	2275.7	2429.3	2509.9	2500.0
35°	1107.9	1198.2	1297.5	1424.4	1610.2	1833.9	2079.3	2277.9	2372.1	2354.8	2224.1
37.5°	1046.4	1122.3	1220.2	1359.0	1564.1	1810.1	2061.3	2210.4	2204.2	2063.4	1874.0
40°	1008.0	1072.6	1166.9	1313.0	1528.2	1794.8	2033.1	2129.9	2047.9	1851.1	1624.3
42.5°	957.7	1017.2	1111.5	1261.7	1488.7	1763.5	1979.3	2007.3	1846.9	1620.5	1412.6
45°	879.8	932.3	1029.7	1184.8	1429.5	1695.4	1848.0	1779.4	1563.4	1329.6	1171.3
47.5°	796.1	850.7	944.4	1103.7	1343.9	1593.1	1665.7	1519.9	1298.2	1108.5	963.2
50°	743.3	795.8	887.5	1048.3	1286.0	1509.0	1539.1	1350.7	1147.0	980.4	861.2
52.5°	690.0	739.5	829.6	990.8	1218.4	1411.6	1393.0	1201.0	1013.7	871.7	778.1
55°	610.7	657.5	743.3	894.5	1101.5	1254.6	1187.3	1004.0	849.0	738.8	667.6
57.5°	539.6	584.5	658.6	795.2	975.1	1080.4	994.7	840.3	717.0	632.2	579.1
60°	491.5	531.2	601.7	728.6	884.9	965.0	880.4	744.0	640.1	572.2	524.8
62.5°	445.8	480.5	545.8	660.9	796.7	864.0	778.4	662.9	574.5	514.3	474.0
65°	376.7	408.1	465.9	555.5	667.0	711.9	638.2	544.6	476.1	431.2	404.3
67.5°	313.7	340.4	390.2	460.8	542.8	575.5	519.4	447.0	395.3	359.3	337.9
70°	271.7	294.7	333.9	394.7	469.0	494.0	441.5	381.9	344.1	315.3	295.4
72.5°	236.3	253.2	288.7	335.7	397.8	417.7	381.0	328.6	293.3	271.7	255.9
75°	180.0	194.1	217.2	255.0	298.0	309.5	281.9	249.2	225.5	210.2	198.0
77.5°	129.8	140.2	156.9	180.2	209.9	220.3	202.8	181.1	163.8	153.4	146.6
80°	98.0	106.4	120.5	139.7	157.6	163.4	153.1	136.5	124.3	118.5	112.8
82.5°	72.4	77.1	85.6	98.7	111.0	117.8	109.1	99.1	92.5	87.2	85.1
85°	36.5	39.1	43.0	48.0	55.8	58.3	55.1	52.5	48.7	45.5	45.5
87.5°	13.9	14.2	16.1	17.5	20.0	22.0	21.9	21.4	21.4	21.0	20.6
90°	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0
92.5°	21.0	22.2	23.4	24.6	25.9	27.2	28.5	29.9	31.2	31.8	32.4
95°	49.2	50.5	51.9	53.1	54.5	55.8	57.3	58.8	60.3	61.0	61.6
97.5°	86.3	87.2	88.1	89.0	90.0	91.1	92.1	93.2	94.2	95.1	95.9
100°	111.8	112.8	113.9	115.0	116.0	116.9	117.8	118.7	119.6	120.2	120.7
102.5°	140.6	141.3	141.9	142.6	143.5	144.7	145.9	147.1	148.3	148.8	149.4
105°	183.4	183.8	184.2	184.6	185.6	187.2	188.8	190.5	192.1	192.1	192.1
107.5°	233.5	233.7	233.9	234.2	234.6	235.2	235.9	236.5	237.2	237.7	238.3
110°	264.9	265.2	265.5	266.0	266.3	266.7	267.0	267.4	267.7	268.5	269.2



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	297.3	297.5	297.7	297.9	298.1	298.2	298.2	298.3	298.3	299.2	300.1
115°	346.4	347.0	347.5	348.1	348.1	347.8	347.4	347.1	346.7	346.9	347.1
117.5°	395.4	395.7	396.2	396.5	396.4	396.0	395.5	395.0	394.5	394.5	394.4
120°	426.7	427.8	428.9	430.0	430.1	429.2	428.3	427.4	426.5	426.2	426.1
122.5°	458.4	459.1	459.9	460.7	460.9	460.4	459.9	459.5	459.0	458.5	458.0
125°	506.8	507.3	507.8	508.3	508.5	508.1	507.8	507.4	507.0	506.3	505.6
127.5°	552.3	553.4	554.6	555.8	556.1	555.7	555.4	555.0	554.6	553.5	552.5
130°	582.5	584.0	585.4	586.9	587.3	586.8	586.2	585.7	585.1	584.4	583.7
132.5°	612.5	613.9	615.4	616.9	617.3	616.9	616.5	616.1	615.7	614.9	614.0
135°	657.9	658.9	660.0	661.1	661.5	661.4	661.2	661.0	660.8	660.1	659.4
137.5°	700.0	700.9	701.8	702.7	703.4	703.8	704.3	704.8	705.2	704.5	703.8
140°	729.3	730.2	731.1	732.0	732.5	732.7	732.9	733.1	733.3	733.1	732.9
142.5°	755.9	756.9	757.8	758.7	759.3	759.6	759.9	760.3	760.6	760.4	760.3
145°	797.1	797.4	797.9	798.2	798.7	799.2	799.7	800.3	800.8	800.6	800.5
147.5°	833.9	834.5	835.2	835.8	836.4	836.9	837.4	837.9	838.5	838.5	838.5
150°	859.0	859.3	859.7	860.1	860.4	860.8	861.1	861.5	861.9	861.9	861.9
152.5°	880.0	880.4	880.9	881.4	881.8	882.1	882.2	882.5	882.7	883.0	883.3
155°	912.3	912.3	912.3	912.3	912.4	912.6	912.7	913.0	913.1	913.9	914.6
157.5°	940.1	939.9	939.6	939.5	939.4	939.6	939.7	939.9	940.0	940.8	941.5
160°	957.5	957.2	956.8	956.4	956.3	956.3	956.3	956.3	956.3	957.2	958.1
162.5°	973.0	972.5	972.0	971.5	971.3	971.4	971.6	971.8	971.9	972.8	973.7
165°	993.1	992.6	992.1	991.6	991.2	991.2	991.2	991.2	991.2	992.3	993.4
167.5°	1009.1	1008.4	1007.6	1006.9	1006.7	1006.8	1006.9	1007.1	1007.2	1008.4	1009.4
170°	1018.2	1017.5	1016.8	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9	1018.2
172.5°	1025.4	1024.7	1023.9	1023.2	1022.8	1022.8	1022.8	1022.8	1022.8	1023.9	1025.1
175°	1032.8	1032.1	1031.4	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4	1032.5
177.5°	1036.1	1035.5	1034.9	1034.4	1034.0	1034.0	1034.0	1034.0	1034.0	1034.9	1035.8
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332073-930
 CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1391.7	1392.2	1397.9	1402.0	1400.0	1402.5	1403.5
5°	1520.5	1543.6	1555.8	1564.7	1565.4	1566.0	1571.2
7.5°	1703.2	1727.9	1746.0	1773.4	1781.6	1790.9	1788.2
10°	1836.5	1872.9	1904.4	1921.0	1938.9	1965.2	1944.1
12.5°	1961.0	2025.7	2073.5	2099.4	2116.3	2121.6	2111.2
15°	2166.4	2251.0	2296.5	2295.2	2352.9	2377.9	2338.8
17.5°	2354.8	2432.9	2495.4	2527.4	2575.4	2586.1	2581.2
20°	2470.1	2555.4	2604.1	2659.2	2684.1	2706.5	2710.4
22.5°	2569.6	2646.1	2698.4	2744.2	2765.2	2775.8	2782.2
25°	2672.0	2732.2	2763.6	2779.6	2785.4	2784.1	2775.8
27.5°	2664.9	2669.5	2635.0	2601.0	2570.6	2536.4	2524.6
30°	2595.7	2541.9	2445.8	2391.4	2311.2	2247.8	2273.4
32.5°	2413.8	2306.6	2198.7	2079.7	1981.1	1953.0	1924.8
35°	2060.0	1871.7	1761.5	1633.3	1582.0	1530.8	1495.5
37.5°	1666.6	1520.9	1390.2	1306.4	1255.0	1222.5	1205.2
40°	1441.0	1309.7	1202.1	1134.2	1095.0	1058.5	1053.4
42.5°	1261.2	1139.1	1058.0	1004.0	966.4	950.9	939.6
45°	1032.9	947.7	893.2	854.8	829.8	820.2	807.4
47.5°	874.2	814.0	773.1	747.0	728.1	721.0	720.0
50°	785.5	735.6	705.5	684.9	670.3	667.6	657.5
52.5°	718.9	675.6	652.2	634.2	623.6	616.4	613.3
55°	624.1	595.3	574.1	563.9	555.5	548.5	548.5
57.5°	546.1	522.0	508.0	499.3	496.7	491.7	488.5
60°	497.9	477.4	466.5	458.8	453.6	454.3	448.5
62.5°	450.7	437.4	427.0	419.3	413.2	413.3	413.7
65°	383.8	373.6	365.9	363.3	359.5	355.0	356.3
67.5°	325.2	315.6	309.7	305.2	303.9	301.6	305.2
70°	283.2	276.1	271.7	267.8	266.5	267.2	270.4
72.5°	244.8	239.8	236.8	235.1	232.2	232.4	234.5
75°	192.2	188.4	185.8	183.9	183.3	183.3	183.3
77.5°	141.2	140.3	139.2	136.3	136.5	137.2	137.4
80°	111.5	109.6	108.9	107.6	105.7	104.4	107.6
82.5°	83.3	81.4	80.7	80.5	77.5	77.3	80.0
85°	44.8	43.0	43.5	43.0	43.0	42.3	42.3
87.5°	20.2	19.9	19.5	20.1	19.6	19.2	20.3
90°	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	33.0	33.6	33.8	33.5	33.3	33.1	32.9
95°	62.4	63.1	63.5	63.5	63.5	63.5	63.5
97.5°	96.8	97.6	97.9	97.9	97.8	97.8	97.7
100°	121.2	121.8	122.3	122.6	122.9	123.4	123.7
102.5°	149.9	150.4	150.7	150.6	150.5	150.5	150.4
105°	192.1	192.1	192.2	192.6	193.0	193.3	193.7
107.5°	238.9	239.5	239.6	239.5	239.2	239.0	238.8
110°	269.9	270.7	270.8	270.4	270.1	269.8	269.4



TEST NUMBER: P332073-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	300.9	301.8	302.2	302.1	302.1	302.0	301.9
115°	347.2	347.4	347.4	347.2	347.1	346.9	346.7
117.5°	394.4	394.4	394.1	393.6	393.1	392.6	392.1
120°	425.9	425.7	425.4	425.1	424.8	424.4	424.0
122.5°	457.6	457.1	456.6	456.2	455.6	455.1	454.6
125°	504.8	504.1	503.4	502.7	502.0	501.2	500.5
127.5°	551.5	550.5	549.6	548.8	547.9	547.1	546.3
130°	582.9	582.3	581.2	580.0	578.7	577.5	576.2
132.5°	613.2	612.3	611.4	610.4	609.4	608.5	607.5
135°	658.7	657.9	657.4	657.0	656.6	656.3	656.0
137.5°	703.0	702.2	701.5	700.8	700.1	699.4	698.8
140°	732.7	732.5	731.8	730.6	729.3	728.1	726.8
142.5°	760.1	759.9	759.3	758.3	757.3	756.4	755.4
145°	800.3	800.1	799.6	798.9	798.2	797.4	796.7
147.5°	838.5	838.5	837.9	836.8	835.7	834.6	833.6
150°	861.9	861.9	861.3	860.2	859.2	858.0	857.0
152.5°	883.5	883.9	883.5	882.6	881.7	880.7	879.8
155°	915.3	916.0	915.7	914.5	913.2	911.9	910.7
157.5°	942.2	943.1	942.9	941.9	940.9	939.9	938.8
160°	959.0	959.9	959.9	959.3	958.5	957.8	957.1
162.5°	974.6	975.5	975.3	974.2	973.1	971.9	970.8
165°	994.5	995.6	995.5	994.3	993.0	991.7	990.4
167.5°	1010.6	1011.7	1011.7	1010.6	1009.4	1008.4	1007.2
170°	1019.5	1020.8	1020.8	1019.5	1018.2	1016.9	1015.7
172.5°	1026.2	1027.3	1027.3	1026.0	1024.7	1023.4	1022.1
175°	1033.6	1034.7	1034.5	1033.3	1032.0	1030.8	1029.5
177.5°	1036.7	1037.5	1037.5	1036.5	1035.4	1034.5	1033.4
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0

(END OF REPORT)