

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332080-930

Luminaire Tested: **S123DIP-S1165D1025U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332080-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1025U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6906.1 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332080-930
CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332080-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	55	53	52	47				
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44	39				
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	40	37	33				
4	75	64	56	50	70	60	53	47	52	47	42	45	41	37	38	35	32	29				
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25				
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	25	22				
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16043	16043	16043
5°	16119	15896	16008
10°	16010	15759	15856
15°	15824	15581	15610
20°	15605	15326	15340
25°	15311	15023	14992
30°	14989	14686	14574
35°	14651	14331	14146
40°	14299	13939	13722
45°	13910	13577	13247
50°	13520	13134	12769
55°	13011	12675	12288
60°	12499	12140	11752
65°	12045	11556	11196
70°	11374	10889	10408
75°	10393	10019	9590
80°	9372	8976	8901
85°	8225	7916	7608



TEST NUMBER: P332080-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	2.0
10°-20°	396.4	5.7
20°-30°	585.6	8.5
30°-40°	684.0	9.9
40°-50°	687.7	10.0
50°-60°	604.1	8.7
60°-70°	450.0	6.5
70°-80°	256.4	3.7
80°-90°	76.7	1.1
90°-100°	223.7	3.2
100°-110°	633.5	9.2
110°-120°	623.2	9.0
120°-130°	497.1	7.2
130°-140°	391.9	5.7
140°-150°	292.5	4.2
150°-160°	203.9	3.0
160°-170°	119.8	1.7
170°-180°	39.0	0.6
0°-30°	1122.4	16.3
0°-40°	1806.5	26.2
0°-60°	3098.3	44.9
0°-90°	3881.5	56.2
90°-120°	1480.5	21.4
90°-150°	2662.0	38.5
90°-180°	3025.0	43.8
0°-180°	6906.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1492	1485	1471	1483	1482	141
15°	1420	1414	1398	1407	1401	400
25°	1289	1281	1265	1266	1262	594
35°	1115	1107	1091	1083	1076	697
45°	914	908	892	877	870	705
55°	693	691	675	662	655	621
65°	473	466	454	444	440	466
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	2	10	20	23	24	6
95°	28	90	483	141	94	30
105°	94	140	654	1144	1035	100
115°	167	208	500	1097	1259	165
125°	232	274	467	846	993	206
135°	272	324	461	697	805	210
145°	310	355	455	572	629	194
155°	352	380	440	500	522	162
165°	385	396	422	447	455	108
175°	401	402	404	410	409	38
180°	402	402	402	402	402	



TEST NUMBER: P332080-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1495.6	1494.7	1493.8	1492.9	1491.9	1490.2	1487.8	1485.2	1482.7	1480.2	1482.5
5°	1491.8	1490.4	1488.9	1487.5	1486.0	1483.8	1480.7	1477.5	1474.4	1471.2	1474.1
7.5°	1477.2	1475.7	1474.3	1472.8	1471.5	1469.1	1465.8	1462.6	1459.4	1456.1	1458.7
10°	1464.8	1463.4	1462.0	1460.5	1459.1	1456.6	1452.9	1449.2	1445.4	1441.8	1444.3
12.5°	1448.5	1447.2	1446.0	1444.9	1443.7	1441.3	1437.9	1434.4	1430.9	1427.4	1429.3
15°	1420.0	1418.9	1417.7	1416.6	1415.4	1413.0	1409.3	1405.6	1401.9	1398.2	1400.4
17.5°	1386.9	1385.4	1384.0	1382.5	1381.0	1378.4	1374.7	1371.0	1367.3	1363.6	1365.2
20°	1362.3	1360.6	1358.9	1357.1	1355.5	1352.7	1349.1	1345.4	1341.7	1338.0	1339.1
22.5°	1334.6	1332.9	1331.2	1329.5	1327.8	1325.1	1321.4	1317.7	1314.0	1310.3	1311.2
25°	1289.2	1287.5	1285.8	1284.1	1282.5	1279.7	1276.0	1272.4	1268.6	1264.9	1265.2
27.5°	1240.8	1239.2	1237.5	1235.8	1234.2	1231.4	1227.4	1223.4	1219.4	1215.4	1215.7
30°	1206.0	1204.5	1203.1	1201.7	1200.3	1197.6	1193.6	1189.6	1185.6	1181.6	1181.6
32.5°	1171.1	1169.2	1167.3	1165.5	1163.6	1161.1	1158.1	1155.0	1151.9	1148.8	1147.2
35°	1115.0	1113.3	1111.6	1109.9	1108.2	1105.5	1101.7	1098.0	1094.3	1090.6	1088.9
37.5°	1057.5	1055.4	1053.2	1051.1	1048.9	1045.9	1042.2	1038.4	1034.7	1030.9	1028.8
40°	1017.6	1015.9	1014.2	1012.4	1010.7	1007.9	1003.9	999.9	995.9	992.0	989.7
42.5°	977.5	975.7	973.7	971.8	969.8	966.9	962.9	958.9	954.9	951.0	948.7
45°	913.8	912.6	911.5	910.4	909.2	906.8	903.1	899.4	895.7	891.9	888.6
47.5°	850.4	848.8	847.2	845.5	843.8	841.3	837.8	834.3	830.9	827.4	824.0
50°	807.4	806.0	804.5	803.2	801.7	799.2	795.4	791.7	788.0	784.3	781.2
52.5°	762.3	761.3	760.3	759.4	758.4	755.9	752.0	748.1	744.2	740.2	737.5
55°	693.3	693.1	692.8	692.5	692.2	690.2	686.5	682.8	679.1	675.4	672.3
57.5°	627.7	626.7	625.7	624.8	623.9	621.9	618.9	616.0	613.0	610.0	607.2
60°	580.6	580.2	580.0	579.7	579.4	577.6	574.1	570.7	567.3	563.9	561.3
62.5°	538.5	537.8	537.0	536.3	535.6	533.5	530.0	526.6	523.3	519.8	517.2
65°	472.9	471.5	470.0	468.6	467.2	465.0	462.2	459.3	456.5	453.7	451.4
67.5°	403.4	402.2	401.0	399.7	398.4	396.7	394.5	392.4	390.2	388.1	386.0
70°	361.4	359.7	358.0	356.3	354.6	352.9	351.1	349.4	347.7	346.0	344.1
72.5°	317.3	316.1	314.8	313.6	312.3	310.7	308.8	306.8	304.9	303.0	301.2
75°	249.9	248.7	247.6	246.5	245.3	244.3	243.5	242.6	241.8	240.9	239.5
77.5°	190.2	189.6	188.9	188.3	187.7	186.9	185.8	184.8	183.8	182.8	181.8
80°	151.2	150.3	149.5	148.6	147.8	147.1	146.5	145.9	145.4	144.8	144.6
82.5°	113.3	113.1	112.9	112.8	112.6	112.4	112.3	112.3	112.1	112.0	111.5
85°	66.6	66.0	65.5	64.9	64.3	64.1	64.1	64.1	64.1	64.1	63.5
87.5°	27.0	26.7	26.3	26.1	25.7	25.6	25.8	26.1	26.3	26.7	26.3
90°	1.6	3.3	4.9	7.3	9.0	10.6	13.0	15.5	17.9	20.4	19.6
92.5°	10.1	15.0	21.9	28.1	35.0	47.0	68.3	103.4	137.7	125.1	94.4
95°	27.6	30.1	39.1	52.9	74.0	105.8	175.0	296.2	429.7	482.6	391.4
97.5°	47.2	48.0	55.0	67.0	87.9	122.2	188.3	325.1	547.6	747.9	800.1
100°	60.3	61.1	66.8	78.1	97.7	129.4	186.4	306.8	520.8	770.7	931.0
102.5°	73.9	75.3	80.4	91.2	108.8	137.9	189.0	291.1	481.8	728.4	937.5
105°	94.4	96.9	101.7	111.5	126.9	152.2	196.2	280.0	433.7	654.3	887.9
107.5°	116.2	118.6	123.4	133.0	147.5	170.9	209.5	279.2	403.2	588.9	801.0
110°	131.8	134.3	138.4	147.3	161.1	183.9	220.5	282.4	391.4	551.8	746.2



TEST NUMBER: P332080-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.2	148.6	152.7	161.6	175.5	197.6	231.6	288.9	384.9	527.0	698.7
115°	166.8	170.1	175.0	183.1	197.0	218.9	249.8	299.5	382.5	500.5	641.3
117.5°	187.5	191.3	195.3	202.8	218.3	238.6	269.2	313.5	383.9	484.9	606.6
120°	201.8	204.2	208.3	216.5	232.0	252.3	281.6	323.9	386.5	477.7	588.4
122.5°	214.2	216.6	220.7	229.5	244.3	266.0	294.6	333.7	391.1	473.1	573.4
125°	232.0	233.6	238.5	247.4	262.9	284.9	313.3	349.1	397.9	467.2	554.2
127.5°	245.5	247.9	253.9	263.0	280.1	302.1	329.6	361.8	405.8	464.2	537.3
130°	253.9	256.3	263.7	273.5	290.5	312.5	339.3	370.3	411.0	462.3	528.2
132.5°	260.4	263.5	271.5	283.2	300.3	321.6	347.8	378.1	414.9	461.6	519.7
135°	271.8	275.1	284.1	296.2	313.3	335.3	360.5	388.2	420.8	460.6	508.7
137.5°	282.6	286.0	294.7	307.8	324.7	345.0	369.3	395.7	424.6	458.9	499.0
140°	289.8	293.8	301.9	315.0	331.3	351.6	375.2	399.6	427.2	458.2	493.2
142.5°	297.5	300.9	309.7	321.5	337.7	356.8	379.8	403.5	429.2	456.9	488.0
145°	310.1	312.5	319.8	332.1	345.8	364.6	385.7	407.7	430.5	454.9	480.9
147.5°	322.8	324.2	331.4	341.9	355.3	371.3	390.6	410.3	430.5	451.8	474.1
150°	331.3	332.1	338.5	349.1	360.5	375.2	393.9	411.0	430.5	449.2	469.5
152.5°	339.7	339.8	346.3	355.6	365.7	379.8	395.8	412.3	428.5	446.0	464.4
155°	352.4	352.4	357.3	365.4	374.4	385.7	399.6	412.6	426.4	440.3	456.6
157.5°	362.5	363.1	367.0	374.2	381.8	390.6	401.7	413.4	423.7	435.2	447.8
160°	370.3	370.3	373.6	380.0	385.7	393.9	403.7	413.4	422.4	431.3	441.9
162.5°	376.2	376.2	378.8	383.9	389.0	395.8	404.3	412.8	419.8	427.4	436.0
165°	384.9	384.1	385.7	389.8	393.1	398.8	405.3	411.0	415.9	421.6	428.0
167.5°	391.6	390.6	391.4	394.5	396.8	400.4	405.1	409.7	412.0	415.7	420.4
170°	395.5	393.9	394.7	397.1	398.8	400.4	404.5	407.7	409.4	411.8	415.9
172.5°	398.1	397.1	397.3	399.1	400.1	401.0	404.5	407.1	407.4	408.5	411.3
175°	401.2	400.4	399.6	401.2	401.2	402.0	403.7	405.3	404.5	404.5	406.1
177.5°	402.7	402.0	401.4	402.0	402.0	402.0	402.7	404.0	402.7	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332080-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1484.7	1487.0	1489.3	1490.4	1490.1	1489.9	1489.6	1489.5
5°	1476.9	1479.8	1482.6	1483.8	1483.2	1482.6	1482.1	1481.5
7.5°	1461.3	1463.8	1466.4	1467.5	1467.1	1466.8	1466.5	1466.2
10°	1446.9	1449.4	1452.0	1453.0	1452.5	1451.9	1451.3	1450.7
12.5°	1431.2	1433.1	1434.9	1435.7	1435.3	1435.0	1434.7	1434.4
15°	1402.7	1405.0	1407.3	1407.6	1405.9	1404.2	1402.5	1400.8
17.5°	1366.8	1368.4	1369.9	1370.4	1369.9	1369.2	1368.6	1368.0
20°	1340.3	1341.4	1342.6	1342.6	1341.8	1340.9	1340.1	1339.2
22.5°	1312.1	1313.0	1313.9	1313.9	1312.8	1311.7	1310.6	1309.5
25°	1265.5	1265.8	1266.1	1265.8	1264.9	1264.0	1263.2	1262.3
27.5°	1215.9	1216.1	1216.3	1215.9	1214.9	1213.7	1212.7	1211.6
30°	1181.6	1181.6	1181.6	1180.6	1178.6	1176.6	1174.6	1172.6
32.5°	1145.6	1144.0	1142.4	1141.1	1140.0	1138.9	1137.8	1136.8
35°	1087.2	1085.5	1083.8	1082.2	1080.8	1079.4	1077.9	1076.5
37.5°	1026.8	1024.7	1022.7	1021.2	1020.3	1019.4	1018.5	1017.6
40°	987.4	985.1	982.8	981.1	980.0	978.8	977.7	976.6
42.5°	946.4	944.1	941.8	940.1	939.0	937.8	936.7	935.6
45°	885.2	881.7	878.3	875.9	874.5	873.0	871.6	870.2
47.5°	820.7	817.3	813.9	811.6	810.4	809.1	807.9	806.7
50°	778.0	774.9	771.8	769.4	767.7	766.0	764.3	762.5
52.5°	734.9	732.2	729.5	727.3	725.6	723.9	722.2	720.5
55°	669.1	666.0	662.8	660.6	659.2	657.7	656.3	654.8
57.5°	604.5	601.7	598.8	596.6	595.0	593.4	591.7	590.0
60°	558.8	556.2	553.7	551.6	550.2	548.8	547.4	545.9
62.5°	514.7	512.1	509.6	507.8	506.8	505.8	504.9	503.9
65°	449.1	446.9	444.6	443.0	442.1	441.3	440.4	439.6
67.5°	384.1	382.0	380.1	378.5	377.3	376.1	374.9	373.7
70°	342.0	340.1	338.0	336.3	334.9	333.5	332.1	330.7
72.5°	299.5	297.7	295.9	294.6	293.9	293.2	292.4	291.7
75°	238.1	236.7	235.2	234.1	233.3	232.4	231.5	230.6
77.5°	180.8	179.9	178.9	178.4	178.4	178.4	178.4	178.4
80°	144.2	144.0	143.7	143.6	143.6	143.6	143.6	143.6
82.5°	111.0	110.5	110.0	109.6	109.3	109.2	108.9	108.7
85°	62.9	62.4	61.8	61.6	61.6	61.6	61.6	61.6
87.5°	26.2	26.1	26.0	26.3	26.1	26.3	26.4	26.3
90°	20.4	21.2	22.0	23.6	22.7	23.6	24.4	23.6
92.5°	68.5	54.4	48.0	43.8	42.3	39.9	40.7	39.2
95°	292.9	198.6	155.5	126.1	110.7	103.4	97.7	94.4
97.5°	730.3	585.0	480.0	382.6	322.6	286.0	264.0	257.0
100°	959.5	893.6	798.3	682.8	600.6	541.2	509.5	510.3
102.5°	1035.7	1033.6	978.0	904.8	840.8	793.8	767.3	748.5
105°	1057.9	1139.4	1154.8	1133.7	1096.2	1065.3	1039.3	1035.2
107.5°	993.8	1126.0	1197.3	1226.3	1226.9	1216.5	1207.7	1200.2
110°	932.6	1082.4	1184.9	1241.9	1264.7	1271.2	1269.6	1268.0



TEST NUMBER: P332080-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	872.0	1025.1	1140.0	1213.2	1254.9	1275.0	1281.2	1281.6
115°	791.8	933.4	1053.0	1141.7	1202.8	1238.6	1254.9	1259.0
117.5°	733.8	856.0	963.4	1053.4	1117.0	1158.1	1181.5	1187.0
120°	703.1	813.0	910.7	992.9	1057.1	1102.7	1122.3	1127.2
122.5°	679.1	778.5	869.0	945.3	1002.5	1043.5	1064.9	1071.1
125°	647.0	735.7	813.8	878.9	931.0	966.8	987.2	992.9
127.5°	619.0	698.1	768.6	827.8	874.2	904.8	923.2	928.4
130°	601.4	674.7	740.5	795.9	839.0	868.4	885.4	891.9
132.5°	585.1	652.5	713.9	766.6	807.1	836.4	851.6	856.1
135°	563.1	620.9	673.8	720.2	760.1	784.5	799.2	804.9
137.5°	543.2	590.5	636.1	676.3	709.8	734.6	746.9	750.6
140°	531.4	572.9	612.0	647.0	677.9	700.7	713.7	712.9
142.5°	520.3	556.0	589.9	620.3	646.7	666.8	678.6	677.8
145°	507.0	533.9	559.9	583.5	603.8	620.9	627.5	629.1
147.5°	496.1	517.4	538.4	555.2	570.6	582.2	588.4	589.1
150°	488.3	507.0	524.1	539.6	551.8	560.7	565.6	565.6
152.5°	481.1	497.3	512.4	525.2	534.8	543.2	546.1	546.1
155°	470.3	483.4	495.6	505.4	512.7	519.2	520.8	521.6
157.5°	459.0	469.9	479.3	487.0	493.3	498.2	499.5	499.4
160°	452.5	461.5	469.5	475.2	480.9	485.8	485.8	485.0
162.5°	444.7	452.3	459.8	464.9	468.6	472.8	472.8	472.0
165°	434.6	439.4	445.2	449.2	452.5	455.8	454.9	454.9
167.5°	425.7	429.5	432.8	435.7	437.2	439.4	438.6	438.6
170°	420.0	422.4	425.6	427.2	428.0	429.7	428.8	428.8
172.5°	414.7	416.5	419.1	420.1	420.3	421.9	420.4	419.8
175°	407.7	408.5	410.2	410.2	410.2	411.0	410.2	409.4
177.5°	403.3	404.0	404.6	404.6	404.0	404.6	403.3	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0

(END OF REPORT)