

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332087-930

Luminaire Tested: **S123DIP-S1165D1195U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332087-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7769.9 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332087-930
CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332087-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	93	89	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42				
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	40	35				
3	81	72	64	58	75	66	60	55	56	51	47	47	43	40	39	36	34	30				
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25				
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22				
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19				
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17				
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	15				
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14				
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16043	16043	16043
5°	16119	15896	16008
10°	16010	15759	15856
15°	15824	15581	15610
20°	15605	15326	15340
25°	15311	15023	14992
30°	14989	14686	14574
35°	14651	14331	14146
40°	14299	13939	13722
45°	13910	13577	13247
50°	13520	13134	12769
55°	13011	12675	12288
60°	12499	12140	11752
65°	12045	11556	11196
70°	11374	10889	10408
75°	10393	10019	9590
80°	9372	8976	8901
85°	8225	7916	7608



TEST NUMBER: P332087-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	1.8
10°-20°	396.4	5.1
20°-30°	585.6	7.5
30°-40°	684.0	8.8
40°-50°	687.7	8.9
50°-60°	604.1	7.8
60°-70°	450.0	5.8
70°-80°	256.4	3.3
80°-90°	77.2	1.0
90°-100°	46.4	0.6
100°-110°	220.9	2.8
110°-120°	530.6	6.8
120°-130°	675.7	8.7
130°-140°	722.0	9.3
140°-150°	675.1	8.7
150°-160°	544.6	7.0
160°-170°	351.5	4.5
170°-180°	121.1	1.6
0°-30°	1122.4	14.4
0°-40°	1806.5	23.2
0°-60°	3098.3	39.9
0°-90°	3881.9	50.0
90°-120°	797.9	10.3
90°-150°	2870.8	36.9
90°-180°	3888.0	50.0
0°-180°	7769.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1492	1485	1471	1483	1482	141
15°	1420	1414	1398	1407	1401	400
25°	1289	1281	1265	1266	1262	594
35°	1115	1107	1091	1083	1076	697
45°	914	908	892	877	870	705
55°	693	691	675	662	655	621
65°	473	466	454	444	440	466
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	11	23	26	28	6
95°	58	22	29	36	36	71
105°	282	287	207	49	42	299
115°	530	535	544	553	557	522
125°	746	754	758	760	762	666
135°	929	935	939	941	939	715
145°	1072	1079	1081	1083	1083	671
155°	1181	1179	1180	1184	1179	544
165°	1246	1243	1242	1249	1243	352
175°	1275	1270	1271	1277	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P332087-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1495.6	1494.7	1493.8	1492.9	1491.9	1490.2	1487.8	1485.2	1482.7	1480.2	1482.5
5°	1491.8	1490.4	1488.9	1487.5	1486.0	1483.8	1480.7	1477.5	1474.4	1471.2	1474.1
7.5°	1477.2	1475.7	1474.3	1472.8	1471.5	1469.1	1465.8	1462.6	1459.4	1456.1	1458.7
10°	1464.8	1463.4	1462.0	1460.5	1459.1	1456.6	1452.9	1449.2	1445.4	1441.8	1444.3
12.5°	1448.5	1447.2	1446.0	1444.9	1443.7	1441.3	1437.9	1434.4	1430.9	1427.4	1429.3
15°	1420.0	1418.9	1417.7	1416.6	1415.4	1413.0	1409.3	1405.6	1401.9	1398.2	1400.4
17.5°	1386.9	1385.4	1384.0	1382.5	1381.0	1378.4	1374.7	1371.0	1367.3	1363.6	1365.2
20°	1362.3	1360.6	1358.9	1357.1	1355.5	1352.7	1349.1	1345.4	1341.7	1338.0	1339.1
22.5°	1334.6	1332.9	1331.2	1329.5	1327.8	1325.1	1321.4	1317.7	1314.0	1310.3	1311.2
25°	1289.2	1287.5	1285.8	1284.1	1282.5	1279.7	1276.0	1272.4	1268.6	1264.9	1265.2
27.5°	1240.8	1239.2	1237.5	1235.8	1234.2	1231.4	1227.4	1223.4	1219.4	1215.4	1215.7
30°	1206.0	1204.5	1203.1	1201.7	1200.3	1197.6	1193.6	1189.6	1185.6	1181.6	1181.6
32.5°	1171.1	1169.2	1167.3	1165.5	1163.6	1161.1	1158.1	1155.0	1151.9	1148.8	1147.2
35°	1115.0	1113.3	1111.6	1109.9	1108.2	1105.5	1101.7	1098.0	1094.3	1090.6	1088.9
37.5°	1057.5	1055.4	1053.2	1051.1	1048.9	1045.9	1042.2	1038.4	1034.7	1030.9	1028.8
40°	1017.6	1015.9	1014.2	1012.4	1010.7	1007.9	1003.9	999.9	995.9	992.0	989.7
42.5°	977.5	975.7	973.7	971.8	969.8	966.9	962.9	958.9	954.9	951.0	948.7
45°	913.8	912.6	911.5	910.4	909.2	906.8	903.1	899.4	895.7	891.9	888.6
47.5°	850.4	848.8	847.2	845.5	843.8	841.3	837.8	834.3	830.9	827.4	824.0
50°	807.4	806.0	804.5	803.2	801.7	799.2	795.4	791.7	788.0	784.3	781.2
52.5°	762.3	761.3	760.3	759.4	758.4	755.9	752.0	748.1	744.2	740.2	737.5
55°	693.3	693.1	692.8	692.5	692.2	690.2	686.5	682.8	679.1	675.4	672.3
57.5°	627.7	626.7	625.7	624.8	623.9	621.9	618.9	616.0	613.0	610.0	607.2
60°	580.6	580.2	580.0	579.7	579.4	577.6	574.1	570.7	567.3	563.9	561.3
62.5°	538.5	537.8	537.0	536.3	535.6	533.5	530.0	526.6	523.3	519.8	517.2
65°	472.9	471.5	470.0	468.6	467.2	465.0	462.2	459.3	456.5	453.7	451.4
67.5°	403.4	402.2	401.0	399.7	398.4	396.7	394.5	392.4	390.2	388.1	386.0
70°	361.4	359.7	358.0	356.3	354.6	352.9	351.1	349.4	347.7	346.0	344.1
72.5°	317.3	316.1	314.8	313.6	312.3	310.7	308.8	306.8	304.9	303.0	301.2
75°	249.9	248.7	247.6	246.5	245.3	244.3	243.5	242.6	241.8	240.9	239.5
77.5°	190.2	189.6	188.9	188.3	187.7	186.9	185.8	184.8	183.8	182.8	181.8
80°	151.2	150.3	149.5	148.6	147.8	147.1	146.5	145.9	145.4	144.8	144.6
82.5°	113.3	113.1	112.9	112.8	112.6	112.4	112.3	112.3	112.1	112.0	111.5
85°	66.6	66.0	65.5	64.9	64.3	64.1	64.1	64.1	64.1	64.1	63.5
87.5°	26.8	26.6	26.3	26.1	25.8	25.8	26.2	26.5	26.8	27.1	27.1
90°	1.0	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6
92.5°	17.6	17.0	16.5	15.8	15.2	16.0	18.1	20.1	22.2	24.2	25.6
95°	57.8	49.2	40.5	31.9	23.2	20.1	22.4	24.7	27.1	29.4	30.8
97.5°	116.1	112.3	108.4	104.5	100.6	91.2	76.0	60.8	45.7	30.5	32.2
100°	160.0	164.3	168.5	172.7	176.9	162.6	129.8	96.9	64.1	31.2	32.9
102.5°	210.1	213.1	216.1	219.2	222.3	205.8	169.9	134.0	98.2	62.3	57.1
105°	282.3	284.6	286.9	289.2	291.6	283.2	264.2	245.3	226.4	207.4	170.2
107.5°	358.4	360.3	362.2	363.9	365.8	368.3	371.3	374.2	377.2	380.3	352.9
110°	409.2	410.9	412.5	414.3	416.0	417.9	420.3	422.6	424.9	427.2	420.3



TEST NUMBER: P332087-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.7	459.2	460.7	462.3	463.7	465.7	468.0	470.3	472.6	474.9	475.1
115°	529.5	530.8	532.0	533.3	534.5	536.1	538.0	539.9	541.8	543.7	545.8
117.5°	599.0	600.5	602.1	603.7	605.3	606.5	607.5	608.5	609.4	610.4	612.0
120°	642.2	644.1	646.0	647.9	649.8	651.1	651.7	652.3	653.0	653.5	655.3
122.5°	686.2	687.7	689.3	690.8	692.4	693.6	694.4	695.2	695.9	696.8	698.0
125°	746.4	748.1	749.7	751.5	753.2	754.4	755.2	756.1	756.9	757.7	758.2
127.5°	804.8	806.4	808.1	809.8	811.5	812.9	813.8	814.9	815.9	816.8	817.6
130°	841.1	842.9	844.5	846.2	847.8	849.1	849.9	850.8	851.7	852.5	853.4
132.5°	876.0	877.7	879.4	881.0	882.7	883.9	884.6	885.3	885.9	886.6	887.5
135°	929.2	930.5	931.7	933.0	934.3	935.3	936.2	937.0	937.8	938.7	939.3
137.5°	974.7	976.3	977.9	979.5	981.1	982.1	982.6	983.1	983.5	984.0	985.0
140°	1005.0	1006.2	1007.5	1008.8	1010.1	1011.0	1011.6	1012.3	1012.9	1013.5	1014.4
142.5°	1033.1	1034.3	1035.6	1036.8	1038.1	1039.0	1039.7	1040.3	1041.0	1041.5	1042.3
145°	1072.3	1073.7	1075.2	1076.7	1078.2	1079.1	1079.5	1079.9	1080.4	1080.8	1081.2
147.5°	1109.2	1110.2	1111.2	1112.1	1113.0	1113.8	1114.2	1114.6	1115.0	1115.4	1115.9
150°	1132.0	1132.5	1133.2	1133.8	1134.5	1135.0	1135.4	1135.8	1136.3	1136.7	1137.1
152.5°	1152.4	1152.7	1153.0	1153.2	1153.6	1153.8	1154.1	1154.4	1154.6	1154.9	1155.6
155°	1181.2	1180.8	1180.3	1179.9	1179.5	1179.4	1179.6	1179.8	1180.1	1180.2	1181.3
157.5°	1203.5	1203.5	1203.5	1203.4	1203.4	1203.2	1203.1	1202.8	1202.6	1202.4	1203.7
160°	1217.2	1217.0	1216.8	1216.6	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1216.6
162.5°	1230.0	1229.6	1229.0	1228.4	1227.8	1227.5	1227.3	1227.1	1226.9	1226.6	1228.1
165°	1245.6	1245.0	1244.3	1243.7	1243.1	1242.7	1242.4	1242.2	1242.0	1241.8	1243.5
167.5°	1257.8	1256.9	1256.1	1255.2	1254.3	1253.9	1253.9	1253.9	1253.9	1253.9	1255.6
170°	1264.5	1263.7	1262.9	1262.0	1261.2	1260.8	1260.8	1260.8	1260.8	1260.8	1262.4
172.5°	1269.1	1268.1	1267.1	1266.1	1265.0	1264.6	1264.8	1264.9	1265.1	1265.3	1267.0
175°	1275.0	1273.9	1272.8	1271.8	1270.7	1270.3	1270.6	1270.7	1271.0	1271.1	1272.7
177.5°	1276.5	1275.6	1274.8	1274.0	1273.1	1272.8	1272.9	1273.1	1273.3	1273.4	1274.8
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332087-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1484.7	1487.0	1489.3	1490.4	1490.1	1489.9	1489.6	1489.5
5°	1476.9	1479.8	1482.6	1483.8	1483.2	1482.6	1482.1	1481.5
7.5°	1461.3	1463.8	1466.4	1467.5	1467.1	1466.8	1466.5	1466.2
10°	1446.9	1449.4	1452.0	1453.0	1452.5	1451.9	1451.3	1450.7
12.5°	1431.2	1433.1	1434.9	1435.7	1435.3	1435.0	1434.7	1434.4
15°	1402.7	1405.0	1407.3	1407.6	1405.9	1404.2	1402.5	1400.8
17.5°	1366.8	1368.4	1369.9	1370.4	1369.9	1369.2	1368.6	1368.0
20°	1340.3	1341.4	1342.6	1342.6	1341.8	1340.9	1340.1	1339.2
22.5°	1312.1	1313.0	1313.9	1313.9	1312.8	1311.7	1310.6	1309.5
25°	1265.5	1265.8	1266.1	1265.8	1264.9	1264.0	1263.2	1262.3
27.5°	1215.9	1216.1	1216.3	1215.9	1214.9	1213.7	1212.7	1211.6
30°	1181.6	1181.6	1181.6	1180.6	1178.6	1176.6	1174.6	1172.6
32.5°	1145.6	1144.0	1142.4	1141.1	1140.0	1138.9	1137.8	1136.8
35°	1087.2	1085.5	1083.8	1082.2	1080.8	1079.4	1077.9	1076.5
37.5°	1026.8	1024.7	1022.7	1021.2	1020.3	1019.4	1018.5	1017.6
40°	987.4	985.1	982.8	981.1	980.0	978.8	977.7	976.6
42.5°	946.4	944.1	941.8	940.1	939.0	937.8	936.7	935.6
45°	885.2	881.7	878.3	875.9	874.5	873.0	871.6	870.2
47.5°	820.7	817.3	813.9	811.6	810.4	809.1	807.9	806.7
50°	778.0	774.9	771.8	769.4	767.7	766.0	764.3	762.5
52.5°	734.9	732.2	729.5	727.3	725.6	723.9	722.2	720.5
55°	669.1	666.0	662.8	660.6	659.2	657.7	656.3	654.8
57.5°	604.5	601.7	598.8	596.6	595.0	593.4	591.7	590.0
60°	558.8	556.2	553.7	551.6	550.2	548.8	547.4	545.9
62.5°	514.7	512.1	509.6	507.8	506.8	505.8	504.9	503.9
65°	449.1	446.9	444.6	443.0	442.1	441.3	440.4	439.6
67.5°	384.1	382.0	380.1	378.5	377.3	376.1	374.9	373.7
70°	342.0	340.1	338.0	336.3	334.9	333.5	332.1	330.7
72.5°	299.5	297.7	295.9	294.6	293.9	293.2	292.4	291.7
75°	238.1	236.7	235.2	234.1	233.3	232.4	231.5	230.6
77.5°	180.8	179.9	178.9	178.4	178.4	178.4	178.4	178.4
80°	144.2	144.0	143.7	143.6	143.6	143.6	143.6	143.6
82.5°	111.0	110.5	110.0	109.6	109.3	109.2	108.9	108.7
85°	62.9	62.4	61.8	61.6	61.6	61.6	61.6	61.6
87.5°	27.0	26.9	26.9	26.9	27.0	27.1	27.1	27.2
90°	24.4	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	26.9	28.3	29.7	30.4	30.7	31.0	31.2	31.5
95°	32.3	33.8	35.2	36.0	36.0	36.0	36.0	36.0
97.5°	33.8	35.5	37.3	38.2	38.4	38.6	38.8	39.1
100°	34.7	36.3	38.0	39.0	39.1	39.4	39.5	39.8
102.5°	51.9	46.6	41.4	39.1	39.4	39.8	40.2	40.5
105°	132.9	95.6	58.4	40.0	40.4	40.8	41.3	41.7
107.5°	325.5	298.2	270.9	243.2	215.2	187.0	159.0	130.9
110°	413.3	406.3	399.4	380.9	350.8	320.7	290.6	260.5



TEST NUMBER: P332087-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	475.2	475.3	475.5	472.3	465.9	459.6	453.2	446.9
115°	547.9	550.0	552.1	553.6	554.4	555.3	556.1	556.9
117.5°	613.8	615.5	617.1	618.1	618.2	618.4	618.6	618.7
120°	657.0	658.6	660.3	661.1	661.1	661.1	661.1	661.1
122.5°	699.1	700.3	701.5	702.1	702.3	702.5	702.7	702.9
125°	758.6	759.0	759.5	759.9	760.3	760.8	761.2	761.6
127.5°	818.2	818.9	819.5	819.7	819.3	818.9	818.5	818.0
130°	854.2	855.0	855.9	856.1	855.7	855.2	854.8	854.4
132.5°	888.3	889.2	890.0	890.1	889.5	888.9	888.4	887.7
135°	940.0	940.6	941.3	941.3	940.6	940.0	939.3	938.7
137.5°	986.0	987.0	988.0	988.3	987.9	987.5	987.1	986.6
140°	1015.2	1016.0	1016.9	1017.1	1016.7	1016.3	1015.9	1015.5
142.5°	1042.9	1043.6	1044.2	1044.3	1043.7	1043.1	1042.5	1042.0
145°	1081.7	1082.1	1082.5	1082.6	1082.6	1082.6	1082.6	1082.6
147.5°	1116.3	1116.7	1117.1	1116.9	1115.9	1114.9	1113.9	1113.0
150°	1137.5	1137.9	1138.3	1138.2	1137.6	1137.0	1136.4	1135.7
152.5°	1156.3	1157.2	1157.9	1157.8	1156.8	1155.8	1154.9	1153.9
155°	1182.3	1183.4	1184.5	1184.3	1183.1	1181.9	1180.6	1179.3
157.5°	1204.9	1206.2	1207.5	1207.3	1205.7	1204.0	1202.3	1200.7
160°	1217.8	1219.0	1220.3	1220.3	1218.8	1217.3	1215.8	1214.3
162.5°	1229.6	1230.9	1232.4	1232.4	1231.1	1229.8	1228.5	1227.2
165°	1245.2	1246.8	1248.5	1248.6	1247.2	1245.7	1244.2	1242.8
167.5°	1257.3	1259.0	1260.7	1260.7	1259.0	1257.3	1255.6	1253.9
170°	1264.1	1265.8	1267.5	1267.5	1265.8	1264.1	1262.4	1260.8
172.5°	1268.7	1270.3	1272.0	1271.9	1270.1	1268.3	1266.4	1264.5
175°	1274.1	1275.6	1277.1	1276.9	1275.3	1273.6	1271.9	1270.2
177.5°	1276.1	1277.5	1278.8	1278.6	1277.0	1275.3	1273.6	1271.9
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0

(END OF REPORT)