

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332007-927

Luminaire Tested: **S123DIP-S1000D365U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332007-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D365U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4251.3 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332007-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332007-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	70	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57	54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49	46
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	50	45	42	39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	41	36	32	30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	32	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	32	26	22	29	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332007-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.1	2.8
10°-20°	333.5	7.8
20°-30°	492.7	11.6
30°-40°	575.5	13.5
40°-50°	578.6	13.6
50°-60°	508.2	12.0
60°-70°	378.6	8.9
70°-80°	215.7	5.1
80°-90°	63.0	1.5
90°-100°	23.2	0.5
100°-110°	69.5	1.6
110°-120°	118.2	2.8
120°-130°	155.5	3.7
130°-140°	174.7	4.1
140°-150°	171.8	4.0
150°-160°	144.6	3.4
160°-170°	96.3	2.3
170°-180°	33.7	0.8
0°-30°	944.3	22.2
0°-40°	1519.8	35.7
0°-60°	2606.6	61.3
0°-90°	3263.9	76.8
90°-120°	210.9	5.0
90°-150°	712.8	16.8
90°-180°	987.0	23.2
0°-180°	4251.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	0	3	7	8	8	4
95°	17	18	21	22	22	19
105°	63	64	66	66	67	67
115°	119	120	119	120	119	118
125°	174	175	174	173	172	155
135°	226	228	227	226	226	174
145°	274	275	275	275	274	171
155°	314	314	314	315	313	144
165°	342	341	341	342	341	96
175°	356	354	354	356	354	34
180°	356	356	356	356	356	



TEST NUMBER: P332007-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.5	22.0	21.5	21.2	20.7	20.4	20.4	20.4	20.4	20.4	20.2
90°	0.3	0.9	1.5	2.1	2.8	3.5	4.3	5.1	5.9	6.7	7.0
92.5°	6.8	7.2	7.6	8.1	8.5	8.9	9.3	9.8	10.3	10.8	10.9
95°	16.6	17.0	17.3	17.8	18.2	18.7	19.3	19.7	20.2	20.8	21.0
97.5°	29.3	29.6	30.0	30.3	30.7	31.0	31.4	31.7	32.1	32.4	32.7
100°	38.1	38.4	38.8	39.2	39.5	39.9	40.2	40.6	40.9	41.1	41.4
102.5°	48.2	48.4	48.6	48.8	49.0	49.4	49.7	50.2	50.6	51.0	51.2
105°	63.0	63.1	63.2	63.4	63.5	63.8	64.4	65.0	65.5	66.1	66.1
107.5°	80.2	80.3	80.4	80.5	80.6	80.6	80.9	81.1	81.4	81.6	81.8
110°	91.0	91.1	91.3	91.3	91.5	91.6	91.7	91.9	92.0	92.1	92.4



TEST NUMBER: P332007-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	102.2	102.3	102.3	102.4	102.5	102.5	102.6	102.6	102.6	102.7	102.9
115°	119.0	119.1	119.4	119.5	119.7	119.8	119.6	119.5	119.4	119.2	119.3
117.5°	135.9	136.0	136.2	136.3	136.4	136.3	136.2	136.0	135.9	135.7	135.7
120°	146.4	146.8	147.2	147.5	147.9	147.9	147.7	147.3	147.0	146.7	146.6
122.5°	157.4	157.6	158.0	158.2	158.5	158.5	158.4	158.2	158.0	157.9	157.7
125°	174.1	174.3	174.5	174.7	174.9	174.9	174.8	174.7	174.5	174.4	174.1
127.5°	189.6	190.0	190.4	190.8	191.2	191.3	191.2	191.0	190.9	190.8	190.4
130°	199.9	200.3	200.9	201.4	201.8	202.0	201.8	201.7	201.5	201.3	201.1
132.5°	210.2	210.7	211.2	211.7	212.1	212.4	212.2	212.1	211.9	211.8	211.5
135°	225.9	226.3	226.6	227.0	227.4	227.6	227.5	227.4	227.4	227.4	227.0
137.5°	240.5	240.8	241.1	241.4	241.7	241.9	242.1	242.2	242.4	242.6	242.3
140°	250.6	250.9	251.2	251.5	251.8	252.0	252.1	252.1	252.2	252.2	252.2
142.5°	259.8	260.1	260.4	260.7	260.9	261.2	261.3	261.4	261.5	261.7	261.6
145°	274.1	274.2	274.3	274.4	274.6	274.7	274.9	275.1	275.3	275.4	275.4
147.5°	286.6	286.8	287.1	287.3	287.5	287.7	287.9	288.0	288.2	288.4	288.4
150°	295.3	295.5	295.6	295.7	295.9	296.0	296.1	296.2	296.4	296.4	296.4
152.5°	302.5	302.7	302.9	303.0	303.2	303.3	303.4	303.5	303.6	303.6	303.7
155°	313.9	313.9	313.9	313.9	313.9	313.9	313.9	313.9	314.0	314.1	314.3
157.5°	323.4	323.4	323.3	323.2	323.1	323.1	323.2	323.2	323.3	323.4	323.6
160°	329.5	329.4	329.2	329.2	329.0	328.9	328.9	328.9	328.9	328.9	329.2
162.5°	334.9	334.7	334.5	334.4	334.1	334.1	334.1	334.2	334.3	334.3	334.6
165°	341.8	341.7	341.4	341.3	341.0	341.0	341.0	341.0	341.0	341.0	341.4
167.5°	347.4	347.1	346.9	346.6	346.3	346.3	346.3	346.3	346.4	346.5	346.8
170°	350.5	350.2	350.0	349.7	349.5	349.4	349.4	349.4	349.4	349.4	349.8
172.5°	353.0	352.7	352.4	352.2	352.0	351.8	351.8	351.8	351.8	351.8	352.2
175°	355.5	355.3	355.1	354.8	354.6	354.4	354.4	354.4	354.4	354.4	354.8
177.5°	356.6	356.4	356.2	356.0	355.8	355.7	355.7	355.7	355.7	355.7	356.0
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4



TEST NUMBER: P332007-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	20.0	19.9	19.7	19.7	19.7	19.7	19.8	19.8
90°	7.2	7.4	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	11.2	11.3	11.6	11.6	11.6	11.5	11.4	11.3
95°	21.2	21.5	21.7	21.9	21.9	21.9	21.9	21.9
97.5°	33.0	33.3	33.6	33.7	33.7	33.7	33.6	33.6
100°	41.5	41.7	41.9	42.1	42.1	42.3	42.5	42.5
102.5°	51.4	51.6	51.7	51.8	51.8	51.8	51.7	51.7
105°	66.1	66.1	66.1	66.1	66.2	66.4	66.5	66.6
107.5°	82.0	82.1	82.4	82.5	82.4	82.3	82.2	82.1
110°	92.6	92.8	93.1	93.2	93.0	92.9	92.8	92.7



TEST NUMBER: P332007-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	103.2	103.5	103.9	103.9	103.9	103.9	103.9	103.9
115°	119.4	119.5	119.5	119.5	119.5	119.4	119.3	119.2
117.5°	135.7	135.7	135.7	135.5	135.4	135.2	135.1	134.9
120°	146.6	146.5	146.5	146.3	146.2	146.1	146.0	145.8
122.5°	157.6	157.4	157.2	157.1	156.9	156.7	156.5	156.4
125°	173.9	173.6	173.4	173.2	172.9	172.7	172.4	172.1
127.5°	190.0	189.7	189.3	189.0	188.8	188.5	188.2	187.9
130°	200.8	200.5	200.3	199.9	199.6	199.1	198.7	198.2
132.5°	211.2	210.9	210.6	210.3	209.9	209.6	209.3	209.0
135°	226.8	226.6	226.3	226.2	226.0	225.9	225.8	225.6
137.5°	242.1	241.9	241.5	241.3	241.1	240.8	240.6	240.3
140°	252.1	252.1	252.0	251.8	251.3	250.9	250.4	250.0
142.5°	261.5	261.4	261.4	261.2	260.9	260.5	260.2	259.8
145°	275.4	275.3	275.2	275.0	274.8	274.6	274.3	274.1
147.5°	288.4	288.4	288.4	288.2	287.9	287.5	287.1	286.7
150°	296.4	296.4	296.4	296.3	295.9	295.6	295.2	294.8
152.5°	303.8	304.0	304.0	303.9	303.6	303.2	302.9	302.6
155°	314.6	314.8	315.1	315.0	314.6	314.1	313.7	313.2
157.5°	323.8	324.2	324.4	324.3	324.0	323.7	323.3	323.0
160°	329.5	329.9	330.2	330.2	329.9	329.7	329.5	329.2
162.5°	334.9	335.3	335.6	335.5	335.1	334.7	334.3	333.9
165°	341.7	342.1	342.5	342.5	342.0	341.6	341.1	340.7
167.5°	347.2	347.6	348.0	348.0	347.6	347.2	346.8	346.5
170°	350.2	350.7	351.1	351.1	350.7	350.2	349.8	349.4
172.5°	352.6	353.0	353.4	353.4	352.9	352.5	352.0	351.6
175°	355.1	355.5	355.9	355.8	355.5	355.0	354.6	354.1
177.5°	356.3	356.6	356.9	356.9	356.6	356.2	355.8	355.5
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4

(END OF REPORT)