

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332052-930

Luminaire Tested: **S123DIP-S1165D365U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332052-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D365U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4895.6 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332052-930
CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332052-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79
1	104	100	96	92	99	95	92	88	87	85	82	80	78	76	73	72	70	67
2	95	87	81	75	90	83	78	73	77	72	68	70	67	63	64	61	59	56
3	87	77	69	63	82	73	66	61	68	62	57	62	57	53	57	53	50	47
4	79	68	59	53	75	65	58	52	60	54	49	55	50	46	51	47	43	40
5	73	61	52	46	69	58	50	45	54	47	42	50	44	40	46	41	38	35
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33	31
7	62	49	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30	27
8	58	45	37	31	55	44	36	31	41	34	29	38	32	28	35	30	26	24
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	28	24	22
10	51	38	30	25	49	37	30	25	34	28	24	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16043	16043	16043
5°	16119	15896	16008
10°	16010	15759	15856
15°	15824	15581	15610
20°	15605	15326	15340
25°	15311	15023	14992
30°	14989	14686	14574
35°	14651	14331	14146
40°	14299	13939	13722
45°	13910	13577	13247
50°	13520	13134	12769
55°	13011	12675	12288
60°	12499	12140	11752
65°	12045	11556	11196
70°	11374	10889	10408
75°	10393	10019	9590
80°	9372	8976	8901
85°	8225	7916	7608



TEST NUMBER: P332052-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	2.9
10°-20°	396.4	8.1
20°-30°	585.6	12.0
30°-40°	684.0	14.0
40°-50°	687.7	14.0
50°-60°	604.1	12.3
60°-70°	450.0	9.2
70°-80°	256.4	5.2
80°-90°	74.7	1.5
90°-100°	23.9	0.5
100°-110°	71.5	1.5
110°-120°	121.6	2.5
120°-130°	160.0	3.3
130°-140°	179.8	3.7
140°-150°	176.8	3.6
150°-160°	148.8	3.0
160°-170°	99.1	2.0
170°-180°	34.7	0.7
0°-30°	1122.4	22.9
0°-40°	1806.5	36.9
0°-60°	3098.3	63.3
0°-90°	3879.4	79.2
90°-120°	217.1	4.4
90°-150°	733.7	15.0
90°-180°	1016.0	20.8
0°-180°	4895.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1492	1485	1471	1483	1482	141
15°	1420	1414	1398	1407	1401	400
25°	1289	1281	1265	1266	1262	594
35°	1115	1107	1091	1083	1076	697
45°	914	908	892	877	870	705
55°	693	691	675	662	655	621
65°	473	466	454	444	440	466
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	0	3	7	8	9	5
95°	17	19	21	22	22	19
105°	65	66	68	68	69	69
115°	122	123	123	123	123	121
125°	179	180	180	178	177	160
135°	232	234	234	233	232	179
145°	282	283	284	283	282	176
155°	323	323	323	324	322	149
165°	352	351	351	352	351	99
175°	366	365	365	366	364	35
180°	367	367	367	367	367	



TEST NUMBER: P332052-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1495.6	1494.7	1493.8	1492.9	1491.9	1490.2	1487.8	1485.2	1482.7	1480.2	1482.5
5°	1491.8	1490.4	1488.9	1487.5	1486.0	1483.8	1480.7	1477.5	1474.4	1471.2	1474.1
7.5°	1477.2	1475.7	1474.3	1472.8	1471.5	1469.1	1465.8	1462.6	1459.4	1456.1	1458.7
10°	1464.8	1463.4	1462.0	1460.5	1459.1	1456.6	1452.9	1449.2	1445.4	1441.8	1444.3
12.5°	1448.5	1447.2	1446.0	1444.9	1443.7	1441.3	1437.9	1434.4	1430.9	1427.4	1429.3
15°	1420.0	1418.9	1417.7	1416.6	1415.4	1413.0	1409.3	1405.6	1401.9	1398.2	1400.4
17.5°	1386.9	1385.4	1384.0	1382.5	1381.0	1378.4	1374.7	1371.0	1367.3	1363.6	1365.2
20°	1362.3	1360.6	1358.9	1357.1	1355.5	1352.7	1349.1	1345.4	1341.7	1338.0	1339.1
22.5°	1334.6	1332.9	1331.2	1329.5	1327.8	1325.1	1321.4	1317.7	1314.0	1310.3	1311.2
25°	1289.2	1287.5	1285.8	1284.1	1282.5	1279.7	1276.0	1272.4	1268.6	1264.9	1265.2
27.5°	1240.8	1239.2	1237.5	1235.8	1234.2	1231.4	1227.4	1223.4	1219.4	1215.4	1215.7
30°	1206.0	1204.5	1203.1	1201.7	1200.3	1197.6	1193.6	1189.6	1185.6	1181.6	1181.6
32.5°	1171.1	1169.2	1167.3	1165.5	1163.6	1161.1	1158.1	1155.0	1151.9	1148.8	1147.2
35°	1115.0	1113.3	1111.6	1109.9	1108.2	1105.5	1101.7	1098.0	1094.3	1090.6	1088.9
37.5°	1057.5	1055.4	1053.2	1051.1	1048.9	1045.9	1042.2	1038.4	1034.7	1030.9	1028.8
40°	1017.6	1015.9	1014.2	1012.4	1010.7	1007.9	1003.9	999.9	995.9	992.0	989.7
42.5°	977.5	975.7	973.7	971.8	969.8	966.9	962.9	958.9	954.9	951.0	948.7
45°	913.8	912.6	911.5	910.4	909.2	906.8	903.1	899.4	895.7	891.9	888.6
47.5°	850.4	848.8	847.2	845.5	843.8	841.3	837.8	834.3	830.9	827.4	824.0
50°	807.4	806.0	804.5	803.2	801.7	799.2	795.4	791.7	788.0	784.3	781.2
52.5°	762.3	761.3	760.3	759.4	758.4	755.9	752.0	748.1	744.2	740.2	737.5
55°	693.3	693.1	692.8	692.5	692.2	690.2	686.5	682.8	679.1	675.4	672.3
57.5°	627.7	626.7	625.7	624.8	623.9	621.9	618.9	616.0	613.0	610.0	607.2
60°	580.6	580.2	580.0	579.7	579.4	577.6	574.1	570.7	567.3	563.9	561.3
62.5°	538.5	537.8	537.0	536.3	535.6	533.5	530.0	526.6	523.3	519.8	517.2
65°	472.9	471.5	470.0	468.6	467.2	465.0	462.2	459.3	456.5	453.7	451.4
67.5°	403.4	402.2	401.0	399.7	398.4	396.7	394.5	392.4	390.2	388.1	386.0
70°	361.4	359.7	358.0	356.3	354.6	352.9	351.1	349.4	347.7	346.0	344.1
72.5°	317.3	316.1	314.8	313.6	312.3	310.7	308.8	306.8	304.9	303.0	301.2
75°	249.9	248.7	247.6	246.5	245.3	244.3	243.5	242.6	241.8	240.9	239.5
77.5°	190.2	189.6	188.9	188.3	187.7	186.9	185.8	184.8	183.8	182.8	181.8
80°	151.2	150.3	149.5	148.6	147.8	147.1	146.5	145.9	145.4	144.8	144.6
82.5°	113.3	113.1	112.9	112.8	112.6	112.4	112.3	112.3	112.1	112.0	111.5
85°	66.6	66.0	65.5	64.9	64.3	64.1	64.1	64.1	64.1	64.1	63.5
87.5°	26.7	26.2	25.6	25.0	24.5	24.2	24.1	24.1	24.0	24.0	23.7
90°	0.3	0.9	1.5	2.2	2.9	3.6	4.4	5.2	6.1	6.9	7.2
92.5°	7.0	7.4	7.8	8.3	8.7	9.1	9.6	10.1	10.6	11.1	11.3
95°	17.0	17.4	17.9	18.3	18.8	19.2	19.8	20.3	20.8	21.4	21.6
97.5°	30.2	30.5	30.9	31.2	31.6	31.9	32.3	32.6	33.0	33.3	33.7
100°	39.2	39.5	39.9	40.4	40.7	41.1	41.4	41.7	42.1	42.3	42.6
102.5°	49.6	49.8	50.0	50.2	50.5	50.8	51.2	51.7	52.1	52.5	52.7
105°	64.8	65.0	65.1	65.2	65.3	65.7	66.3	66.9	67.4	68.0	68.0
107.5°	82.6	82.7	82.8	82.8	82.9	83.0	83.2	83.5	83.7	84.0	84.1
110°	93.7	93.8	93.9	94.0	94.2	94.2	94.4	94.6	94.7	94.8	95.1



TEST NUMBER: P332052-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	105.2	105.3	105.3	105.4	105.5	105.5	105.6	105.6	105.6	105.7	105.9
115°	122.5	122.6	122.9	123.0	123.2	123.3	123.1	123.0	122.9	122.7	122.8
117.5°	139.8	140.0	140.1	140.2	140.4	140.3	140.1	140.0	139.8	139.7	139.7
120°	150.7	151.1	151.5	151.8	152.2	152.2	152.0	151.6	151.3	151.0	150.9
122.5°	162.0	162.2	162.6	162.8	163.1	163.1	163.0	162.8	162.7	162.5	162.3
125°	179.2	179.4	179.6	179.8	180.0	180.0	179.9	179.8	179.6	179.5	179.2
127.5°	195.1	195.5	195.9	196.3	196.7	196.9	196.7	196.6	196.5	196.3	196.0
130°	205.7	206.2	206.8	207.2	207.7	207.9	207.7	207.6	207.3	207.2	206.9
132.5°	216.3	216.9	217.4	217.8	218.3	218.6	218.4	218.3	218.1	218.0	217.7
135°	232.5	232.9	233.3	233.7	234.1	234.2	234.2	234.1	234.0	234.0	233.7
137.5°	247.5	247.9	248.1	248.4	248.7	249.0	249.2	249.3	249.5	249.6	249.4
140°	257.9	258.2	258.5	258.9	259.2	259.3	259.4	259.4	259.5	259.6	259.5
142.5°	267.3	267.7	268.0	268.3	268.6	268.8	269.0	269.0	269.1	269.3	269.2
145°	282.1	282.2	282.3	282.4	282.6	282.7	282.9	283.2	283.3	283.5	283.5
147.5°	295.0	295.2	295.5	295.7	295.9	296.1	296.3	296.4	296.6	296.9	296.9
150°	303.9	304.1	304.2	304.4	304.5	304.6	304.8	304.8	305.0	305.1	305.1
152.5°	311.4	311.5	311.7	311.9	312.1	312.2	312.3	312.3	312.4	312.5	312.6
155°	323.0	323.0	323.0	323.0	323.0	323.0	323.1	323.1	323.2	323.3	323.5
157.5°	332.9	332.8	332.7	332.6	332.6	332.6	332.6	332.6	332.7	332.8	333.0
160°	339.1	339.0	338.8	338.8	338.6	338.5	338.5	338.5	338.5	338.5	338.8
162.5°	344.6	344.5	344.3	344.1	343.9	343.9	343.9	344.0	344.1	344.1	344.4
165°	351.8	351.6	351.4	351.2	351.0	350.9	350.9	350.9	350.9	350.9	351.3
167.5°	357.5	357.3	357.0	356.7	356.4	356.4	356.4	356.4	356.5	356.6	356.9
170°	360.7	360.4	360.2	360.0	359.7	359.5	359.5	359.5	359.5	359.5	360.0
172.5°	363.3	363.0	362.7	362.5	362.2	362.1	362.1	362.1	362.1	362.1	362.5
175°	365.9	365.7	365.4	365.2	364.9	364.8	364.8	364.8	364.8	364.8	365.2
177.5°	367.0	366.8	366.6	366.4	366.2	366.1	366.1	366.1	366.1	366.1	366.4
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8



TEST NUMBER: P332052-930
 CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1484.7	1487.0	1489.3	1490.4	1490.1	1489.9	1489.6	1489.5
5°	1476.9	1479.8	1482.6	1483.8	1483.2	1482.6	1482.1	1481.5
7.5°	1461.3	1463.8	1466.4	1467.5	1467.1	1466.8	1466.5	1466.2
10°	1446.9	1449.4	1452.0	1453.0	1452.5	1451.9	1451.3	1450.7
12.5°	1431.2	1433.1	1434.9	1435.7	1435.3	1435.0	1434.7	1434.4
15°	1402.7	1405.0	1407.3	1407.6	1405.9	1404.2	1402.5	1400.8
17.5°	1366.8	1368.4	1369.9	1370.4	1369.9	1369.2	1368.6	1368.0
20°	1340.3	1341.4	1342.6	1342.6	1341.8	1340.9	1340.1	1339.2
22.5°	1312.1	1313.0	1313.9	1313.9	1312.8	1311.7	1310.6	1309.5
25°	1265.5	1265.8	1266.1	1265.8	1264.9	1264.0	1263.2	1262.3
27.5°	1215.9	1216.1	1216.3	1215.9	1214.9	1213.7	1212.7	1211.6
30°	1181.6	1181.6	1181.6	1180.6	1178.6	1176.6	1174.6	1172.6
32.5°	1145.6	1144.0	1142.4	1141.1	1140.0	1138.9	1137.8	1136.8
35°	1087.2	1085.5	1083.8	1082.2	1080.8	1079.4	1077.9	1076.5
37.5°	1026.8	1024.7	1022.7	1021.2	1020.3	1019.4	1018.5	1017.6
40°	987.4	985.1	982.8	981.1	980.0	978.8	977.7	976.6
42.5°	946.4	944.1	941.8	940.1	939.0	937.8	936.7	935.6
45°	885.2	881.7	878.3	875.9	874.5	873.0	871.6	870.2
47.5°	820.7	817.3	813.9	811.6	810.4	809.1	807.9	806.7
50°	778.0	774.9	771.8	769.4	767.7	766.0	764.3	762.5
52.5°	734.9	732.2	729.5	727.3	725.6	723.9	722.2	720.5
55°	669.1	666.0	662.8	660.6	659.2	657.7	656.3	654.8
57.5°	604.5	601.7	598.8	596.6	595.0	593.4	591.7	590.0
60°	558.8	556.2	553.7	551.6	550.2	548.8	547.4	545.9
62.5°	514.7	512.1	509.6	507.8	506.8	505.8	504.9	503.9
65°	449.1	446.9	444.6	443.0	442.1	441.3	440.4	439.6
67.5°	384.1	382.0	380.1	378.5	377.3	376.1	374.9	373.7
70°	342.0	340.1	338.0	336.3	334.9	333.5	332.1	330.7
72.5°	299.5	297.7	295.9	294.6	293.9	293.2	292.4	291.7
75°	238.1	236.7	235.2	234.1	233.3	232.4	231.5	230.6
77.5°	180.8	179.9	178.9	178.4	178.4	178.4	178.4	178.4
80°	144.2	144.0	143.7	143.6	143.6	143.6	143.6	143.6
82.5°	111.0	110.5	110.0	109.6	109.3	109.2	108.9	108.7
85°	62.9	62.4	61.8	61.6	61.6	61.6	61.6	61.6
87.5°	23.6	23.4	23.2	23.2	23.2	23.2	23.2	23.2
90°	7.4	7.7	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	11.5	11.7	11.9	12.0	11.9	11.8	11.7	11.7
95°	21.9	22.1	22.3	22.5	22.5	22.5	22.5	22.5
97.5°	33.9	34.2	34.6	34.7	34.7	34.7	34.6	34.6
100°	42.7	43.0	43.1	43.3	43.4	43.5	43.7	43.8
102.5°	52.9	53.1	53.2	53.3	53.3	53.3	53.2	53.2
105°	68.0	68.0	68.0	68.1	68.2	68.3	68.5	68.6
107.5°	84.4	84.5	84.8	84.9	84.8	84.7	84.6	84.5
110°	95.3	95.6	95.8	95.9	95.7	95.6	95.5	95.4



TEST NUMBER: P332052-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	106.2	106.6	106.9	107.0	107.0	107.0	106.9	106.9
115°	122.9	122.9	123.0	123.0	122.9	122.9	122.8	122.7
117.5°	139.7	139.7	139.7	139.5	139.3	139.2	139.0	138.8
120°	150.8	150.7	150.7	150.6	150.5	150.3	150.3	150.1
122.5°	162.2	162.0	161.8	161.7	161.5	161.3	161.1	160.9
125°	179.0	178.7	178.5	178.2	178.0	177.7	177.4	177.2
127.5°	195.6	195.3	194.9	194.5	194.3	194.0	193.7	193.4
130°	206.7	206.4	206.1	205.8	205.4	204.9	204.5	204.0
132.5°	217.4	217.0	216.8	216.5	216.1	215.7	215.4	215.1
135°	233.4	233.2	232.9	232.8	232.6	232.4	232.4	232.2
137.5°	249.2	248.9	248.6	248.3	248.1	247.9	247.6	247.4
140°	259.4	259.4	259.3	259.1	258.6	258.2	257.7	257.3
142.5°	269.1	269.0	269.0	268.8	268.5	268.2	267.7	267.4
145°	283.4	283.3	283.2	283.1	282.8	282.6	282.3	282.1
147.5°	296.9	296.9	296.9	296.6	296.3	295.9	295.5	295.1
150°	305.1	305.1	305.1	304.9	304.5	304.2	303.8	303.4
152.5°	312.7	312.8	312.9	312.7	312.4	312.1	311.8	311.4
155°	323.8	324.0	324.3	324.2	323.8	323.3	322.9	322.4
157.5°	333.3	333.6	333.9	333.8	333.5	333.1	332.7	332.4
160°	339.2	339.5	339.8	339.8	339.6	339.3	339.1	338.8
162.5°	344.7	345.0	345.4	345.3	344.9	344.5	344.1	343.6
165°	351.7	352.0	352.5	352.5	352.0	351.6	351.1	350.7
167.5°	357.3	357.8	358.2	358.2	357.8	357.3	356.9	356.6
170°	360.4	360.9	361.3	361.3	360.9	360.4	360.0	359.5
172.5°	362.9	363.3	363.7	363.7	363.2	362.8	362.3	361.9
175°	365.5	365.9	366.3	366.2	365.8	365.3	364.9	364.4
177.5°	366.7	367.0	367.3	367.3	367.0	366.6	366.2	365.8
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8

(END OF REPORT)