

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831250

Luminaire Tested: S123DIP-S1165D365U930-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831250
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D365U930-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5358.1 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 52.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	115	115	115	115	110	110	110	110	101	101	101	92	92	92	85	85	85	81				
1	106	101	98	94	101	97	94	91	90	87	85	83	81	79	76	75	73	70				
2	97	90	84	79	93	86	81	76	80	75	72	74	70	67	68	65	63	60				
3	89	80	73	67	85	77	70	65	71	66	61	66	62	58	61	58	55	52				
4	82	72	64	58	79	69	62	56	64	58	54	60	55	51	56	52	48	46				
5	76	65	56	51	73	62	55	49	58	52	47	54	49	45	51	46	43	40				
6	71	59	51	45	68	57	49	44	53	47	42	50	44	40	47	42	39	36				
7	66	54	46	40	63	52	45	39	49	42	38	46	40	36	43	38	35	33				
8	62	49	42	36	59	48	41	36	45	39	34	42	37	33	40	35	32	30				
9	58	46	38	33	56	44	37	32	42	36	31	39	34	30	37	33	29	27				
10	54	42	35	30	52	41	34	30	39	33	29	37	32	28	35	30	27	25				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	29068	29068	29068	29068	29068
5°	36761	34696	29327	23634	21718
10°	37117	38241	29133	18840	16463
15°	27956	35504	28934	15954	13923
20°	19479	28730	28565	13952	12646
25°	14853	22094	27935	12836	11861
30°	12849	17554	26929	12048	11230
35°	11922	14820	25769	11477	10786
40°	11286	13294	24140	10935	10635
45°	10911	12304	22071	10511	10567
50°	10722	11521	19621	10124	10513
55°	10323	10946	17214	9758	10558
60°	9954	10331	14837	9414	10385
65°	9352	9750	12798	9049	10180
70°	8636	9010	10886	8441	9583
75°	7819	8077	9328	7844	8754
80°	6447	7067	7376	6837	7376
85°	5113	5730	5422	5805	5879

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 25199 cd/sqm



TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.3	4.8
10°-20°	635.1	11.9
20°-30°	752.0	14.0
30°-40°	756.1	14.1
40°-50°	693.7	12.9
50°-60°	572.6	10.7
60°-70°	405.0	7.6
70°-80°	216.2	4.0
80°-90°	55.6	1.0
90°-100°	23.6	0.4
100°-110°	71.5	1.3
110°-120°	121.7	2.3
120°-130°	160.0	3.0
130°-140°	179.9	3.4
140°-150°	176.9	3.3
150°-160°	148.9	2.8
160°-170°	99.1	1.9
170°-180°	34.7	0.6
0°-30°	1642.5	30.7
0°-40°	2398.6	44.8
0°-60°	3665.0	68.4
0°-90°	4341.8	81.0
90°-120°	216.7	4.0
90°-150°	733.5	13.7
90°-180°	1016.0	19.0
0°-180°	5358.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2700	2700	2700	2700	2700	
5°	3402	3211	2714	2187	2010	324
15°	2509	3186	2596	1432	1249	693
25°	1251	1860	2352	1081	999	590
35°	907	1128	1961	873	821	570
45°	717	808	1450	690	694	555
55°	550	583	917	520	563	492
65°	367	383	502	355	400	365
75°	188	194	224	189	210	198
85°	41	46	44	47	48	46
90°	9	7	0	7	9	7
95°	22	21	17	21	22	23
105°	69	68	65	68	69	73
115°	123	123	122	123	123	122
125°	177	180	179	180	177	158
135°	232	234	232	234	232	179
145°	282	284	282	284	282	176
155°	322	323	323	323	322	149
165°	351	351	352	351	351	99
175°	364	365	366	365	364	35
180°	367	367	367	367	367	



TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5
2.5°	3043.8	3040.7	3037.6	3021.9	3006.2	2998.7	2991.2	2968.6	2946.1	2921.0	2896.0
5°	3402.2	3411.0	3419.8	3409.7	3399.7	3369.0	3338.3	3297.6	3256.8	3211.1	3165.4
7.5°	3567.6	3572.6	3577.6	3571.4	3565.1	3557.0	3548.8	3512.5	3476.1	3429.2	3382.2
10°	3395.9	3407.2	3418.5	3442.9	3467.4	3494.9	3522.5	3517.5	3512.5	3498.7	3484.9
12.5°	3018.8	3032.5	3046.3	3095.2	3144.1	3206.7	3269.4	3323.3	3377.1	3414.7	3452.3
15°	2508.7	2547.0	2585.2	2629.7	2674.2	2766.3	2858.4	2971.8	3085.2	3186.0	3286.9
17.5°	2066.4	2080.8	2095.2	2142.8	2190.4	2306.4	2422.3	2553.2	2684.2	2851.5	3018.8
20°	1700.5	1713.6	1726.8	1789.5	1852.1	1943.0	2033.8	2181.0	2328.3	2508.1	2687.9
22.5°	1428.6	1449.2	1469.9	1505.0	1540.1	1627.2	1714.3	1845.2	1976.2	2174.8	2373.4
25°	1250.6	1265.6	1280.7	1302.0	1323.3	1392.8	1462.4	1570.2	1677.9	1860.3	2042.6
27.5°	1129.1	1135.3	1141.6	1162.9	1184.2	1229.3	1274.4	1367.1	1459.9	1614.6	1769.4
30°	1033.8	1038.2	1042.6	1061.4	1080.2	1110.9	1141.6	1208.6	1275.7	1412.3	1548.9
32.5°	967.4	970.5	973.7	988.1	1002.5	1024.4	1046.4	1095.2	1144.1	1256.9	1369.7
35°	907.3	909.1	911.0	921.7	932.3	948.6	964.9	1001.9	1038.8	1127.8	1216.8
37.5°	854.6	857.1	859.6	865.9	872.2	886.6	901.0	930.4	959.9	1028.2	1096.5
40°	803.2	807.6	812.0	816.4	820.8	832.7	844.6	867.2	889.7	946.1	1002.5
42.5°	759.4	763.8	768.2	770.0	771.9	778.8	785.7	806.4	827.1	869.0	911.0
45°	716.8	718.7	720.5	722.4	724.3	729.9	735.6	753.7	771.9	808.3	844.6
47.5°	677.9	677.9	677.9	679.2	680.4	685.5	690.5	703.6	716.8	745.0	773.2
50°	640.3	640.3	640.3	638.5	636.6	639.7	642.8	652.9	662.9	688.0	713.0
52.5°	595.2	595.2	595.2	595.9	596.5	596.5	596.5	605.3	614.0	636.6	659.1
55°	550.1	552.6	555.1	553.3	551.4	552.6	553.9	559.5	565.2	583.3	601.5
57.5°	505.0	506.3	507.5	506.9	506.3	506.9	507.5	512.5	517.5	531.3	545.1
60°	462.4	462.4	462.4	461.1	459.9	461.1	462.4	464.9	467.4	479.9	492.5
62.5°	414.8	415.4	416.0	416.7	417.3	416.0	414.8	417.9	421.0	430.4	439.8
65°	367.2	367.8	368.4	370.3	372.2	370.9	369.7	372.8	375.9	382.8	389.7
67.5°	324.6	323.3	322.1	322.7	323.3	325.2	327.1	327.7	328.3	335.8	343.4
70°	274.4	275.7	276.9	276.3	275.7	276.3	276.9	278.8	280.7	286.3	292.0
72.5°	229.3	229.9	230.6	230.6	230.6	231.8	233.1	235.0	236.8	240.0	243.1
75°	188.0	188.0	188.0	189.2	190.5	191.1	191.7	191.7	191.7	194.2	196.7
77.5°	142.9	146.0	149.1	148.5	147.9	149.1	150.4	152.3	154.1	155.4	156.6
80°	104.0	104.0	104.0	104.6	105.3	107.1	109.0	110.3	111.5	114.0	116.5
82.5°	66.4	67.0	67.7	69.5	71.4	72.7	73.9	75.8	77.7	77.7	77.7
85°	41.4	40.1	38.8	40.1	41.4	42.6	43.9	44.5	45.1	46.4	47.6
87.5°	20.0	20.0	20.0	20.0	20.0	20.7	21.3	21.3	21.3	21.3	21.3
90°	8.6	8.5	8.4	8.3	8.1	7.9	7.7	7.4	7.2	6.9	6.1
92.5°	12.4	12.5	12.6	12.8	12.9	12.9	12.7	12.5	12.3	12.1	11.7
95°	22.5	22.5	22.5	22.5	22.5	22.3	22.1	21.8	21.6	21.3	20.8
97.5°	32.3	32.3	32.4	32.5	32.5	32.4	32.1	31.8	31.4	31.1	30.7
100°	43.8	43.7	43.5	43.4	43.3	43.1	42.9	42.7	42.5	42.4	42.0
102.5°	55.6	55.7	55.7	55.8	55.9	55.8	55.6	55.4	55.2	55.0	54.6
105°	68.6	68.4	68.3	68.2	68.1	68.0	68.0	68.0	68.0	68.0	67.4
107.5°	81.8	81.9	82.0	82.0	82.1	82.0	81.8	81.6	81.4	81.2	81.0
110°	95.4	95.5	95.6	95.8	95.9	95.8	95.6	95.3	95.0	94.8	94.7



TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	109.8	109.8	109.8	109.8	109.8	109.6	109.3	109.0	108.7	108.3	108.3
115°	122.7	122.8	122.9	122.9	123.0	123.0	122.9	122.9	122.8	122.7	122.9
117.5°	136.0	136.2	136.4	136.6	136.8	136.9	136.9	136.9	136.9	136.9	137.0
120°	150.1	150.2	150.4	150.5	150.6	150.7	150.8	150.8	150.9	151.0	151.3
122.5°	163.7	163.8	164.0	164.2	164.4	164.6	164.8	165.0	165.2	165.4	165.5
125°	177.2	177.4	177.7	178.0	178.2	178.5	178.7	179.0	179.2	179.5	179.6
127.5°	190.7	191.0	191.2	191.5	191.8	192.1	192.5	192.8	193.2	193.6	193.7
130°	204.0	204.4	204.9	205.3	205.8	206.1	206.4	206.6	206.9	207.2	207.3
132.5°	217.8	218.1	218.5	218.8	219.1	219.4	219.7	220.1	220.4	220.7	220.8
135°	232.2	232.4	232.5	232.6	232.7	232.9	233.2	233.4	233.7	234.0	234.0
137.5°	244.9	245.1	245.3	245.5	245.7	245.9	246.2	246.6	246.9	247.2	247.0
140°	257.3	257.7	258.2	258.6	259.1	259.3	259.4	259.5	259.5	259.6	259.5
142.5°	270.0	270.3	270.6	270.9	271.2	271.4	271.5	271.6	271.6	271.7	271.6
145°	282.1	282.3	282.6	282.8	283.1	283.3	283.3	283.4	283.4	283.5	283.3
147.5°	293.0	293.4	293.8	294.2	294.6	294.7	294.7	294.7	294.7	294.7	294.6
150°	303.4	303.8	304.2	304.5	304.9	305.1	305.1	305.1	305.1	305.1	305.0
152.5°	313.5	313.8	314.1	314.4	314.8	314.9	314.7	314.6	314.5	314.3	314.3
155°	322.4	322.9	323.3	323.7	324.2	324.3	324.0	323.8	323.5	323.3	323.2
157.5°	330.8	331.1	331.5	331.9	332.3	332.4	332.1	331.8	331.6	331.3	331.3
160°	338.8	339.1	339.3	339.6	339.9	339.8	339.5	339.2	338.9	338.5	338.5
162.5°	344.9	345.3	345.8	346.2	346.7	346.7	346.4	346.1	345.8	345.5	345.4
165°	350.6	351.1	351.5	352.0	352.4	352.5	352.1	351.7	351.3	350.9	350.9
167.5°	355.8	356.2	356.6	357.0	357.4	357.4	357.0	356.6	356.2	355.8	355.8
170°	359.6	360.0	360.5	360.9	361.4	361.4	360.9	360.5	360.0	359.6	359.6
172.5°	362.5	362.9	363.4	363.8	364.2	364.3	363.9	363.5	363.1	362.7	362.7
175°	364.5	364.9	365.4	365.8	366.3	366.3	365.9	365.5	365.1	364.8	364.8
177.5°	365.6	366.1	366.5	367.0	367.4	367.4	367.1	366.7	366.3	365.9	365.9
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8



TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5
2.5°	2888.4	2880.9	2853.3	2825.8	2794.4	2763.1	2739.9	2716.8	2682.3	2647.8	2619.6
5°	3130.3	3095.2	3036.9	2978.7	2899.7	2820.8	2767.5	2714.2	2642.8	2571.4	2514.4
7.5°	3322.0	3261.9	3180.4	3099.0	2995.6	2892.2	2794.4	2696.7	2587.7	2478.7	2389.7
10°	3444.2	3403.5	3309.5	3215.5	3077.0	2938.6	2802.0	2665.4	2525.0	2384.7	2266.9
12.5°	3456.1	3459.9	3373.4	3286.9	3130.3	2973.6	2807.6	2641.6	2464.9	2288.2	2151.0
15°	3351.5	3416.0	3368.4	3320.8	3162.9	3005.0	2800.7	2596.5	2392.8	2189.2	2030.7
17.5°	3157.2	3295.7	3302.6	3309.5	3151.6	2993.7	2767.5	2541.3	2310.7	2080.2	1913.5
20°	2892.2	3096.5	3166.6	3236.8	3108.4	2979.9	2736.8	2493.7	2235.6	1977.4	1802.6
22.5°	2621.5	2869.6	2998.1	3126.5	3031.3	2936.1	2677.3	2418.5	2146.0	1873.4	1696.1
25°	2313.3	2583.9	2781.3	2978.7	2920.4	2862.1	2607.1	2352.1	2062.0	1771.9	1590.8
27.5°	2044.5	2319.5	2557.6	2795.7	2783.2	2770.6	2517.5	2264.4	1967.4	1670.4	1495.6
30°	1805.1	2061.4	2327.7	2594.0	2624.7	2655.4	2411.0	2166.6	1869.0	1571.4	1402.9
32.5°	1593.3	1817.0	2102.7	2388.4	2448.6	2508.7	2288.2	2067.6	1773.2	1478.7	1316.4
35°	1419.8	1622.8	1908.5	2194.2	2269.4	2344.6	2152.9	1961.1	1674.2	1387.2	1232.4
37.5°	1266.3	1436.1	1714.9	1993.7	2085.8	2177.9	2006.2	1834.6	1565.8	1297.0	1154.7
40°	1139.1	1275.7	1531.9	1788.2	1894.7	2001.2	1859.6	1718.0	1463.0	1208.0	1077.1
42.5°	1032.6	1154.1	1386.6	1619.0	1721.2	1823.3	1703.6	1583.9	1357.1	1130.3	1010.6
45°	941.7	1038.8	1250.0	1461.1	1558.3	1655.4	1552.6	1449.9	1250.0	1050.1	938.6
47.5°	856.5	939.8	1120.3	1300.7	1387.2	1473.7	1393.5	1313.3	1144.1	974.9	874.0
50°	780.1	847.1	1005.0	1162.9	1238.1	1313.3	1242.5	1171.7	1032.6	893.5	805.8
52.5°	713.6	768.2	900.4	1032.6	1097.1	1161.6	1100.9	1040.1	929.8	819.5	743.1
55°	647.9	694.2	808.9	923.5	967.4	1011.3	964.3	917.3	828.3	739.3	674.8
57.5°	586.5	627.8	721.8	815.8	849.6	883.4	840.8	798.2	731.2	664.2	610.3
60°	526.3	560.1	638.5	716.8	737.5	758.1	723.7	689.2	642.2	595.2	547.0
62.5°	470.5	501.2	559.5	617.8	631.6	645.4	619.0	592.7	557.0	521.3	483.7
65°	412.9	436.1	483.7	531.3	540.1	548.9	525.7	502.5	475.6	448.6	421.0
67.5°	359.6	375.9	414.8	453.6	454.3	454.9	436.1	417.3	402.3	387.2	365.3
70°	307.6	323.3	349.0	374.7	375.3	375.9	360.9	345.9	334.6	323.3	307.0
72.5°	254.4	265.7	285.1	304.5	303.3	302.0	292.6	283.2	274.4	265.7	253.8
75°	206.1	215.5	228.7	241.9	238.1	234.3	229.3	224.3	216.8	209.3	201.8
77.5°	162.3	167.9	175.4	183.0	180.4	177.9	173.6	169.2	163.5	157.9	154.8
80°	119.0	121.6	126.6	131.6	130.3	129.1	124.1	119.0	117.8	116.5	112.2
82.5°	80.8	84.0	85.2	86.5	85.8	85.2	81.5	77.7	76.4	75.2	74.6
85°	48.2	48.9	49.5	50.1	48.2	46.4	45.1	43.9	43.9	43.9	43.2
87.5°	21.9	22.6	22.6	22.6	21.9	21.3	20.0	18.8	19.4	20.0	20.0
90°	5.3	4.4	3.6	2.8	2.2	1.6	0.9	0.3	0.9	1.6	2.2
92.5°	11.3	10.9	10.6	10.2	9.8	9.4	9.0	8.6	9.0	9.4	9.8
95°	20.3	19.8	19.3	18.8	18.3	17.9	17.4	17.0	17.4	17.9	18.3
97.5°	30.3	30.0	29.6	29.2	28.9	28.6	28.3	27.9	28.3	28.6	28.9
100°	41.7	41.4	41.1	40.7	40.3	40.0	39.6	39.2	39.6	40.0	40.3
102.5°	54.1	53.7	53.2	52.9	52.7	52.5	52.3	52.1	52.3	52.5	52.7
105°	66.8	66.3	65.7	65.3	65.2	65.1	65.0	64.8	65.0	65.1	65.2
107.5°	80.7	80.5	80.2	80.1	80.0	79.9	79.9	79.8	79.9	79.9	80.0
110°	94.5	94.4	94.3	94.2	94.0	93.9	93.8	93.6	93.8	93.9	94.0



TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	108.3	108.3	108.3	108.3	108.2	108.2	108.1	108.0	108.1	108.2	108.2
115°	123.0	123.1	123.3	123.2	123.0	122.8	122.6	122.5	122.6	122.8	123.0
117.5°	137.1	137.2	137.4	137.4	137.3	137.3	137.2	137.1	137.2	137.3	137.3
120°	151.6	151.9	152.3	152.2	151.8	151.5	151.1	150.7	151.1	151.5	151.8
122.5°	165.6	165.8	165.9	165.8	165.6	165.3	165.1	164.8	165.1	165.3	165.6
125°	179.8	179.9	180.0	180.0	179.8	179.6	179.4	179.2	179.4	179.6	179.8
127.5°	193.9	194.0	194.1	194.0	193.6	193.2	192.8	192.5	192.8	193.2	193.6
130°	207.5	207.7	207.9	207.8	207.3	206.7	206.2	205.7	206.2	206.7	207.3
132.5°	221.0	221.1	221.2	221.0	220.5	220.0	219.5	219.0	219.5	220.0	220.5
135°	234.1	234.1	234.2	234.0	233.7	233.3	232.9	232.5	232.9	233.3	233.7
137.5°	246.8	246.6	246.4	246.2	245.9	245.5	245.2	244.9	245.2	245.5	245.9
140°	259.5	259.4	259.3	259.1	258.8	258.5	258.2	257.9	258.2	258.5	258.8
142.5°	271.4	271.3	271.2	271.0	270.6	270.3	270.0	269.7	270.0	270.3	270.6
145°	283.1	282.9	282.7	282.6	282.5	282.3	282.2	282.1	282.2	282.3	282.5
147.5°	294.4	294.2	294.0	293.8	293.5	293.2	293.0	292.7	293.0	293.2	293.5
150°	304.9	304.7	304.6	304.5	304.3	304.2	304.1	304.0	304.1	304.2	304.3
152.5°	314.2	314.1	314.1	314.0	313.8	313.6	313.4	313.2	313.4	313.6	313.8
155°	323.1	323.1	323.0	323.0	323.0	323.0	323.0	323.0	323.0	323.0	323.0
157.5°	331.2	331.1	331.1	331.1	331.1	331.2	331.3	331.3	331.3	331.2	331.1
160°	338.5	338.5	338.5	338.6	338.7	338.9	339.0	339.1	339.0	338.9	338.7
162.5°	345.3	345.3	345.2	345.3	345.5	345.6	345.8	346.0	345.8	345.6	345.5
165°	350.9	350.9	350.9	351.0	351.2	351.4	351.6	351.8	351.6	351.4	351.2
167.5°	355.7	355.6	355.6	355.7	355.9	356.2	356.4	356.7	356.4	356.2	355.9
170°	359.6	359.6	359.6	359.7	360.0	360.2	360.5	360.7	360.5	360.2	360.0
172.5°	362.7	362.7	362.7	362.9	363.1	363.4	363.6	363.9	363.6	363.4	363.1
175°	364.8	364.8	364.8	364.9	365.1	365.4	365.7	365.9	365.7	365.4	365.1
177.5°	365.9	365.9	365.9	366.0	366.3	366.6	366.8	367.1	366.8	366.6	366.3
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8



TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5	2700.5
2.5°	2591.4	2567.0	2542.6	2523.8	2505.0	2473.0	2441.1	2433.6	2426.0	2415.4	2404.7
5°	2457.4	2397.2	2337.1	2283.2	2229.3	2187.3	2145.3	2117.8	2090.2	2070.1	2050.1
7.5°	2300.7	2210.5	2120.3	2056.4	1992.5	1931.7	1870.9	1851.5	1832.1	1805.7	1779.4
10°	2149.1	2049.5	1949.8	1866.5	1783.2	1723.7	1664.1	1640.3	1616.5	1583.3	1550.1
12.5°	2013.8	1904.7	1795.7	1711.8	1627.8	1570.2	1512.5	1478.1	1443.6	1424.8	1406.0
15°	1872.2	1755.6	1639.1	1561.4	1483.7	1431.7	1379.7	1349.6	1319.5	1301.4	1283.2
17.5°	1746.8	1631.6	1516.3	1441.7	1367.1	1319.5	1271.9	1245.6	1219.3	1205.5	1191.7
20°	1627.8	1515.0	1402.2	1329.6	1256.9	1218.0	1179.2	1162.3	1145.3	1134.1	1122.8
22.5°	1518.8	1407.9	1297.0	1234.9	1172.9	1141.6	1110.3	1098.4	1086.5	1077.1	1067.7
25°	1409.8	1310.8	1211.8	1159.1	1106.5	1080.8	1055.1	1043.2	1031.3	1021.9	1012.5
27.5°	1320.8	1226.2	1131.6	1086.5	1041.3	1021.3	1001.2	991.8	982.4	973.7	964.9
30°	1234.3	1149.7	1065.1	1026.3	987.5	969.3	951.1	941.7	932.3	924.2	916.0
32.5°	1154.1	1081.4	1008.8	973.0	937.3	922.3	907.3	896.0	884.7	878.4	872.2
35°	1077.7	1012.5	947.4	917.9	888.5	873.4	858.4	849.0	839.6	834.6	829.6
37.5°	1012.5	954.2	896.0	867.8	839.6	825.2	810.8	802.6	794.5	792.6	790.7
40°	946.1	896.0	845.9	818.3	790.7	778.2	765.7	760.6	755.6	754.4	753.1
42.5°	891.0	842.1	793.2	768.2	743.1	732.4	721.8	719.3	716.8	718.7	720.5
45°	827.1	786.3	745.6	722.4	699.2	690.5	681.7	679.8	677.9	681.7	685.5
47.5°	773.2	735.6	698.0	676.1	654.1	647.9	641.6	641.0	640.3	645.4	650.4
50°	718.0	681.7	645.4	627.8	610.3	604.6	599.0	600.9	602.7	610.9	619.0
52.5°	666.7	632.8	599.0	582.7	566.4	562.6	558.9	563.3	567.7	576.4	585.2
55°	610.3	579.6	548.9	536.3	523.8	520.0	516.3	525.1	533.8	542.0	550.1
57.5°	556.4	529.4	502.5	491.2	479.9	479.3	478.7	486.8	495.0	503.8	512.5
60°	498.7	476.2	453.6	444.9	436.1	437.3	438.6	448.0	457.4	464.3	471.2
62.5°	446.1	427.3	408.5	400.4	392.2	395.4	398.5	407.9	417.3	425.4	433.6
65°	393.5	377.8	362.2	356.5	350.9	355.3	359.6	367.8	375.9	381.6	387.2
67.5°	343.4	330.2	317.0	312.7	308.3	312.7	317.0	325.2	333.3	339.0	344.6
70°	290.7	280.1	269.4	266.3	263.2	268.2	273.2	280.1	287.0	292.6	298.2
72.5°	241.9	233.7	225.6	224.9	224.3	228.7	233.1	240.0	246.9	250.6	254.4
75°	194.2	189.8	185.5	184.8	184.2	188.6	193.0	196.7	200.5	203.6	206.8
77.5°	151.6	147.9	144.1	144.7	145.4	148.5	151.6	155.4	159.1	161.0	162.9
80°	107.8	106.5	105.3	106.5	107.8	110.3	112.8	115.3	117.8	119.0	120.3
82.5°	73.9	72.7	71.4	73.3	75.2	77.1	78.9	80.8	82.7	83.3	84.0
85°	42.6	44.5	46.4	46.4	46.4	47.0	47.6	48.2	48.9	48.2	47.6
87.5°	20.0	20.7	21.3	21.3	21.3	21.9	22.6	22.6	22.6	21.9	21.3
90°	2.8	3.6	4.4	5.3	6.1	6.9	7.2	7.4	7.7	7.9	8.1
92.5°	10.2	10.6	10.9	11.3	11.7	12.1	12.3	12.5	12.7	12.9	12.9
95°	18.8	19.3	19.8	20.3	20.8	21.3	21.6	21.8	22.1	22.3	22.5
97.5°	29.2	29.6	30.0	30.3	30.7	31.1	31.4	31.8	32.1	32.4	32.5
100°	40.7	41.1	41.4	41.7	42.0	42.4	42.5	42.7	42.9	43.1	43.3
102.5°	52.9	53.2	53.7	54.1	54.6	55.0	55.2	55.4	55.6	55.8	55.9
105°	65.3	65.7	66.3	66.8	67.4	68.0	68.0	68.0	68.0	68.0	68.1
107.5°	80.1	80.2	80.5	80.7	81.0	81.2	81.4	81.6	81.8	82.0	82.1
110°	94.2	94.3	94.4	94.5	94.7	94.8	95.0	95.3	95.6	95.8	95.9



TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	108.3	108.3	108.3	108.3	108.3	108.3	108.7	109.0	109.3	109.6	109.8
115°	123.2	123.3	123.1	123.0	122.9	122.7	122.8	122.9	122.9	123.0	123.0
117.5°	137.4	137.4	137.2	137.1	137.0	136.9	136.9	136.9	136.9	136.9	136.8
120°	152.2	152.3	151.9	151.6	151.3	151.0	150.9	150.8	150.8	150.7	150.6
122.5°	165.8	165.9	165.8	165.6	165.5	165.4	165.2	165.0	164.8	164.6	164.4
125°	180.0	180.0	179.9	179.8	179.6	179.5	179.2	179.0	178.7	178.5	178.2
127.5°	194.0	194.1	194.0	193.9	193.7	193.6	193.2	192.8	192.5	192.1	191.8
130°	207.8	207.9	207.7	207.5	207.3	207.2	206.9	206.6	206.4	206.1	205.8
132.5°	221.0	221.2	221.1	221.0	220.8	220.7	220.4	220.1	219.7	219.4	219.1
135°	234.0	234.2	234.1	234.1	234.0	234.0	233.7	233.4	233.2	232.9	232.7
137.5°	246.2	246.4	246.6	246.8	247.0	247.2	246.9	246.6	246.2	245.9	245.7
140°	259.1	259.3	259.4	259.5	259.5	259.6	259.5	259.5	259.4	259.3	259.1
142.5°	271.0	271.2	271.3	271.4	271.6	271.7	271.6	271.6	271.5	271.4	271.2
145°	282.6	282.7	282.9	283.1	283.3	283.5	283.4	283.4	283.3	283.3	283.1
147.5°	293.8	294.0	294.2	294.4	294.6	294.7	294.7	294.7	294.7	294.7	294.6
150°	304.5	304.6	304.7	304.9	305.0	305.1	305.1	305.1	305.1	305.1	304.9
152.5°	314.0	314.1	314.1	314.2	314.3	314.3	314.5	314.6	314.7	314.9	314.8
155°	323.0	323.0	323.1	323.1	323.2	323.3	323.5	323.8	324.0	324.3	324.2
157.5°	331.1	331.1	331.1	331.2	331.3	331.3	331.6	331.8	332.1	332.4	332.3
160°	338.6	338.5	338.5	338.5	338.5	338.5	338.9	339.2	339.5	339.8	339.9
162.5°	345.3	345.2	345.3	345.3	345.4	345.5	345.8	346.1	346.4	346.7	346.7
165°	351.0	350.9	350.9	350.9	350.9	350.9	351.3	351.7	352.1	352.5	352.4
167.5°	355.7	355.6	355.6	355.7	355.8	355.8	356.2	356.6	357.0	357.4	357.4
170°	359.7	359.6	359.6	359.6	359.6	359.6	360.0	360.5	360.9	361.4	361.4
172.5°	362.9	362.7	362.7	362.7	362.7	362.7	363.1	363.5	363.9	364.3	364.2
175°	364.9	364.8	364.8	364.8	364.8	364.8	365.1	365.5	365.9	366.3	366.3
177.5°	366.0	365.9	365.9	365.9	365.9	365.9	366.3	366.7	367.1	367.4	367.4
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8



TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2700.5	2700.5	2700.5	2700.5
2.5°	2400.3	2396.0	2378.4	2360.9
5°	2035.1	2020.0	2015.0	2010.0
7.5°	1778.2	1776.9	1750.6	1724.3
10°	1552.0	1553.9	1530.1	1506.2
12.5°	1390.3	1374.7	1372.8	1370.9
15°	1268.8	1254.4	1251.9	1249.4
17.5°	1182.9	1174.2	1171.7	1169.2
20°	1117.8	1112.8	1108.4	1104.0
22.5°	1061.4	1055.1	1051.4	1047.6
25°	1006.9	1001.2	1000.0	998.7
27.5°	958.0	951.1	951.1	951.1
30°	911.6	907.3	905.4	903.5
32.5°	868.4	864.7	864.7	864.7
35°	827.7	825.8	823.3	820.8
37.5°	790.7	790.7	789.5	788.2
40°	755.0	756.9	756.9	756.9
42.5°	722.4	724.3	724.3	724.3
45°	688.6	691.7	693.0	694.2
47.5°	655.4	660.4	661.6	662.9
50°	622.8	626.6	627.2	627.8
52.5°	589.6	594.0	597.1	600.2
55°	554.5	558.9	560.8	562.6
57.5°	516.9	521.3	521.9	522.5
60°	475.6	479.9	481.2	482.4
62.5°	436.1	438.6	439.8	441.1
65°	391.0	394.7	397.2	399.7
67.5°	347.7	350.9	350.9	350.9
70°	299.5	300.7	302.6	304.5
72.5°	255.0	255.6	255.6	255.6
75°	208.0	209.3	209.9	210.5
77.5°	163.5	164.2	164.2	164.2
80°	119.7	119.0	119.0	119.0
82.5°	82.1	80.2	80.2	80.2
85°	47.0	46.4	47.0	47.6
87.5°	21.3	21.3	21.3	21.3
90°	8.3	8.4	8.5	8.6
92.5°	12.8	12.6	12.5	12.4
95°	22.5	22.5	22.5	22.5
97.5°	32.5	32.4	32.3	32.3
100°	43.4	43.5	43.7	43.8
102.5°	55.8	55.7	55.7	55.6
105°	68.2	68.3	68.4	68.6
107.5°	82.0	82.0	81.9	81.8
110°	95.8	95.6	95.5	95.4



TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	109.8	109.8	109.8	109.8
115°	122.9	122.9	122.8	122.7
117.5°	136.6	136.4	136.2	136.0
120°	150.5	150.4	150.2	150.1
122.5°	164.2	164.0	163.8	163.7
125°	178.0	177.7	177.4	177.2
127.5°	191.5	191.2	191.0	190.7
130°	205.3	204.9	204.4	204.0
132.5°	218.8	218.5	218.1	217.8
135°	232.6	232.5	232.4	232.2
137.5°	245.5	245.3	245.1	244.9
140°	258.6	258.2	257.7	257.3
142.5°	270.9	270.6	270.3	270.0
145°	282.8	282.6	282.3	282.1
147.5°	294.2	293.8	293.4	293.0
150°	304.5	304.2	303.8	303.4
152.5°	314.4	314.1	313.8	313.5
155°	323.7	323.3	322.9	322.4
157.5°	331.9	331.5	331.1	330.8
160°	339.6	339.3	339.1	338.8
162.5°	346.2	345.8	345.3	344.9
165°	352.0	351.5	351.1	350.6
167.5°	357.0	356.6	356.2	355.8
170°	360.9	360.5	360.0	359.6
172.5°	363.8	363.4	362.9	362.5
175°	365.8	365.4	364.9	364.5
177.5°	367.0	366.5	366.1	365.6
180°	366.8	366.8	366.8	366.8



TEST NUMBER: P831250

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.81	18.97	18.45	19.62	20.37	20.04	21.21	20.69	21.86	22.60
	3H	19.48	20.52	20.13	21.18	21.96	21.49	22.53	22.15	23.19	23.98
	4H	20.07	21.05	20.74	21.72	22.52	21.95	22.93	22.63	23.61	24.40
	6H	20.45	21.35	21.14	22.04	22.85	22.24	23.15	22.93	23.83	24.64
	8H	20.56	21.42	21.26	22.12	22.94	22.31	23.17	23.02	23.88	24.69
	12H	20.61	21.43	21.32	22.13	22.97	22.34	23.16	23.05	23.86	24.70
4H	2H	18.42	19.40	19.10	20.07	20.87	20.24	21.22	20.92	21.90	22.69
	3H	20.27	21.09	20.96	21.80	22.61	21.89	22.70	22.58	23.41	24.23
	4H	20.98	21.72	21.69	22.43	23.28	22.48	23.22	23.19	23.93	24.78
	6H	21.47	22.11	22.20	22.85	23.71	22.90	23.54	23.63	24.28	25.14
	8H	21.61	22.21	22.35	22.95	23.81	23.02	23.62	23.75	24.35	25.22
	12H	21.69	22.23	22.45	22.99	23.86	23.08	23.61	23.83	24.37	25.25
8H	4H	21.27	21.86	22.00	22.60	23.47	22.61	23.21	23.34	23.94	24.81
	6H	21.87	22.36	22.63	23.14	24.01	23.12	23.61	23.88	24.39	25.26
	8H	22.08	22.51	22.85	23.30	24.18	23.30	23.74	24.08	24.52	25.41
	12H	22.21	22.60	22.99	23.37	24.32	23.42	23.80	24.19	24.57	25.52
12H	4H	21.28	21.82	22.03	22.58	23.45	22.60	23.13	23.35	23.89	24.77
	6H	21.92	22.36	22.69	23.14	24.02	23.14	23.58	23.91	24.36	25.24
	8H	22.17	22.55	22.94	23.32	24.27	23.35	23.74	24.13	24.51	25.45