

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831140

Luminaire Tested: S123DIP-S1000D585U927-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831140
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U927-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5332.4 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 50.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831140
CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69				
1	103	98	95	91	97	93	90	87	83	81	78	74	72	71	66	64	63	59				
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	56	54	51				
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47	44				
4	80	69	61	55	75	66	59	53	59	54	49	53	49	45	48	44	42	39				
5	74	62	54	48	69	59	52	47	54	48	43	49	44	40	44	40	37	34				
6	68	56	48	43	64	54	47	41	49	43	39	44	40	36	40	36	33	31				
7	64	51	44	38	60	49	42	37	45	39	35	41	36	32	37	33	30	28				
8	59	47	40	34	56	45	38	33	41	35	31	38	33	29	34	30	27	25				
9	56	43	36	31	53	42	35	30	38	32	28	35	30	27	32	28	25	23				
10	52	40	33	28	49	39	32	28	36	30	26	33	28	25	30	26	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	24455	24455	24455	24455	24455
5°	30927	29190	24673	19883	18271
10°	31227	32172	24509	15850	13850
15°	23520	29869	24342	13422	11713
20°	16387	24171	24032	11738	10639
25°	12495	18587	23502	10799	9979
30°	10811	14767	22656	10136	9447
35°	10030	12468	21680	9656	9073
40°	9496	11185	20310	9199	8948
45°	9179	10351	18568	8843	8891
50°	9021	9692	16506	8519	8845
55°	8685	9211	14482	8210	8884
60°	8374	8693	12482	7920	8738
65°	7868	8204	10769	7613	8565
70°	7267	7582	9158	7100	8063
75°	6575	6796	7848	6600	7365
80°	5424	5945	6211	5752	6211
85°	4298	4817	4557	4878	4952

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 21200 cd/sqm



TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	4.0
10°-20°	534.3	10.0
20°-30°	632.7	11.9
30°-40°	636.1	11.9
40°-50°	583.6	10.9
50°-60°	481.7	9.0
60°-70°	340.8	6.4
70°-80°	181.9	3.4
80°-90°	47.4	0.9
90°-100°	121.1	2.3
100°-110°	354.6	6.7
110°-120°	346.3	6.5
120°-130°	275.8	5.2
130°-140°	217.6	4.1
140°-150°	162.3	3.0
150°-160°	113.2	2.1
160°-170°	66.5	1.2
170°-180°	21.6	0.4
0°-30°	1381.8	25.9
0°-40°	2018.0	37.8
0°-60°	3083.3	57.8
0°-90°	3653.4	68.5
90°-120°	822.0	15.4
90°-150°	1477.7	27.7
90°-180°	1679.0	31.5
0°-180°	5332.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2272	2272	2272	2272	2272	
5°	2862	2702	2284	1840	1691	273
15°	2111	2680	2184	1204	1051	583
25°	1052	1565	1979	909	840	497
35°	763	949	1650	735	690	480
45°	603	680	1220	581	584	467
55°	463	491	772	438	473	414
65°	309	322	423	299	336	307
75°	158	163	189	159	177	166
85°	35	39	37	40	40	39
90°	13	11	1	11	13	9
95°	52	268	15	268	52	85
105°	575	363	52	363	575	573
115°	699	278	93	278	699	682
125°	551	259	129	259	551	499
135°	447	256	151	256	447	347
145°	349	253	172	253	349	222
155°	290	244	196	244	290	135
165°	253	234	214	234	253	72
175°	227	225	223	225	227	22
180°	223	223	223	223	223	



TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9
2.5°	2560.8	2558.1	2555.5	2542.3	2529.1	2522.8	2516.5	2497.5	2478.5	2457.5	2436.4
5°	2862.3	2869.7	2877.0	2868.6	2860.2	2834.3	2808.5	2774.3	2740.0	2701.5	2663.0
7.5°	3001.4	3005.7	3009.9	3004.6	2999.3	2992.5	2985.6	2955.1	2924.5	2885.0	2845.4
10°	2857.0	2866.5	2876.0	2896.5	2917.1	2940.3	2963.5	2959.3	2955.1	2943.5	2931.9
12.5°	2539.7	2551.3	2562.9	2604.0	2645.1	2697.8	2750.5	2795.9	2841.2	2872.8	2904.5
15°	2110.6	2142.8	2174.9	2212.3	2249.8	2327.3	2404.7	2500.2	2595.6	2680.4	2765.3
17.5°	1738.5	1750.6	1762.7	1802.8	1842.8	1940.3	2037.9	2148.0	2258.2	2398.9	2539.7
20°	1430.6	1441.7	1452.8	1505.5	1558.2	1634.6	1711.0	1834.9	1958.8	2110.1	2261.4
22.5°	1201.8	1219.2	1236.6	1266.2	1295.7	1368.9	1442.2	1552.4	1662.5	1829.6	1996.7
25°	1052.1	1064.8	1077.4	1095.4	1113.3	1171.8	1230.3	1321.0	1411.6	1565.0	1718.4
27.5°	949.9	955.1	960.4	978.3	996.3	1034.2	1072.2	1150.2	1228.2	1358.4	1488.6
30°	869.8	873.4	877.1	892.9	908.8	934.6	960.4	1016.8	1073.2	1188.1	1303.1
32.5°	813.9	816.5	819.2	831.3	843.4	861.8	880.3	921.4	962.5	1057.4	1152.3
35°	763.3	764.9	766.4	775.4	784.4	798.1	811.8	842.9	874.0	948.8	1023.7
37.5°	719.0	721.1	723.2	728.5	733.8	745.9	758.0	782.8	807.6	865.0	922.5
40°	675.8	679.5	683.2	686.8	690.5	700.5	710.6	729.5	748.5	796.0	843.4
42.5°	638.9	642.6	646.3	647.8	649.4	655.2	661.0	678.4	695.8	731.1	766.4
45°	603.0	604.6	606.2	607.8	609.4	614.1	618.8	634.1	649.4	680.0	710.6
47.5°	570.3	570.3	570.3	571.4	572.5	576.7	580.9	592.0	603.0	626.8	650.5
50°	538.7	538.7	538.7	537.1	535.6	538.2	540.8	549.3	557.7	578.8	599.9
52.5°	500.8	500.8	500.8	501.3	501.8	501.8	501.8	509.2	516.6	535.6	554.5
55°	462.8	464.9	467.0	465.5	463.9	464.9	466.0	470.7	475.5	490.8	506.0
57.5°	424.9	425.9	427.0	426.4	425.9	426.4	427.0	431.2	435.4	447.0	458.6
60°	389.0	389.0	389.0	388.0	386.9	388.0	389.0	391.1	393.2	403.8	414.3
62.5°	349.0	349.5	350.0	350.5	351.1	350.0	349.0	351.6	354.2	362.1	370.0
65°	308.9	309.4	309.9	311.5	313.1	312.1	311.0	313.6	316.3	322.1	327.9
67.5°	273.1	272.0	270.9	271.5	272.0	273.6	275.2	275.7	276.2	282.5	288.9
70°	230.9	231.9	233.0	232.5	231.9	232.5	233.0	234.6	236.2	240.9	245.6
72.5°	192.9	193.5	194.0	194.0	194.0	195.0	196.1	197.7	199.3	201.9	204.5
75°	158.1	158.1	158.1	159.2	160.2	160.8	161.3	161.3	161.3	163.4	165.5
77.5°	120.2	122.8	125.5	124.9	124.4	125.5	126.5	128.1	129.7	130.7	131.8
80°	87.5	87.5	87.5	88.0	88.6	90.1	91.7	92.8	93.8	95.9	98.0
82.5°	55.9	56.4	56.9	58.5	60.1	61.1	62.2	63.8	65.4	65.4	65.4
85°	34.8	33.7	32.7	33.7	34.8	35.8	36.9	37.4	38.0	39.0	40.1
87.5°	16.9	16.9	16.9	16.9	16.9	17.4	17.9	17.9	17.9	17.9	17.9
90°	13.1	13.6	13.1	12.7	13.1	12.2	11.7	11.3	10.8	11.3	9.9
92.5°	23.9	24.9	24.4	26.2	27.1	30.3	34.8	44.7	62.8	84.0	93.1
95°	52.4	54.2	57.4	61.5	70.0	86.3	110.2	162.7	217.3	267.9	238.6
97.5°	107.5	112.5	123.4	140.5	170.8	222.3	281.9	373.7	426.1	412.1	307.7
100°	283.3	282.9	300.5	333.5	379.1	443.3	496.1	532.7	516.9	427.9	289.2
102.5°	448.7	461.8	475.8	500.2	533.2	568.0	593.3	585.6	521.4	398.5	262.1
105°	574.7	577.0	591.5	608.6	629.4	641.2	632.6	587.4	493.0	363.3	240.8
107.5°	657.0	661.9	667.8	676.0	678.7	666.5	631.2	560.3	452.3	332.1	225.5
110°	704.0	704.9	705.8	702.2	689.5	657.9	600.9	517.8	414.3	306.3	217.3

TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	713.5	713.0	708.5	695.4	669.6	626.7	561.2	475.8	381.4	289.2	212.8
115°	699.0	696.7	687.7	667.8	633.9	584.7	518.3	439.6	356.0	277.9	212.4
117.5°	667.4	664.2	650.6	628.5	593.3	542.2	481.2	411.6	339.3	270.2	212.8
120°	625.8	623.1	612.2	586.9	551.2	505.6	451.4	390.4	326.7	265.2	214.6
122.5°	586.9	583.3	571.1	549.0	518.3	476.7	427.4	373.7	316.3	262.1	217.8
125°	551.2	548.1	536.8	516.9	488.0	451.8	408.5	359.2	307.7	259.4	220.9
127.5°	520.5	517.8	507.4	490.2	464.0	430.6	390.8	346.1	299.6	258.0	224.6
130°	495.2	491.6	482.1	465.8	441.9	411.2	374.6	333.9	293.2	256.6	228.2
132.5°	470.4	468.1	460.0	443.7	421.6	392.6	359.2	322.6	287.4	256.2	230.9
135°	446.9	443.7	435.6	422.0	399.9	374.1	344.8	312.7	282.4	255.7	233.6
137.5°	422.0	419.3	412.5	398.5	379.5	356.5	330.3	303.2	277.9	254.8	235.4
140°	395.8	396.3	389.0	376.4	359.2	339.8	318.1	295.1	273.8	254.4	237.2
142.5°	371.4	371.9	365.5	354.7	340.7	324.4	306.3	287.4	270.2	253.5	238.6
145°	349.3	348.4	344.8	335.3	324.0	310.9	296.4	281.5	267.0	252.6	239.0
147.5°	330.3	329.8	326.2	319.5	310.4	300.9	288.7	276.5	263.9	251.2	239.0
150°	314.0	314.0	311.3	306.3	299.6	291.0	281.5	271.1	260.7	249.4	239.0
152.5°	300.5	300.5	299.1	294.6	289.6	282.9	274.7	266.1	257.1	247.2	237.7
155°	289.6	289.2	288.3	284.7	280.6	275.2	268.4	261.2	253.5	244.4	236.8
157.5°	279.2	279.2	278.3	275.6	272.0	267.5	262.1	255.7	249.4	242.2	235.4
160°	269.3	269.7	269.7	267.0	263.9	260.7	256.2	251.2	245.3	239.5	234.5
162.5°	260.3	260.7	260.7	258.5	256.6	253.9	249.9	245.8	241.3	236.8	232.7
165°	252.6	252.6	253.0	251.2	249.4	247.2	244.0	241.3	237.7	234.1	230.9
167.5°	244.9	244.9	245.3	244.0	243.1	241.3	239.5	237.2	234.1	231.3	229.1
170°	238.1	238.1	238.6	237.7	237.2	236.3	234.5	233.1	230.9	228.6	227.3
172.5°	231.8	232.2	233.1	232.2	232.2	231.8	230.4	229.5	227.7	226.4	225.9
175°	227.3	227.7	228.2	227.7	227.7	227.7	226.8	226.4	225.5	224.6	224.6
177.5°	224.1	224.1	225.0	224.6	225.0	225.0	224.6	224.1	223.7	223.2	223.7
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9
2.5°	2430.0	2423.7	2400.5	2377.3	2351.0	2324.6	2305.1	2285.6	2256.6	2227.6	2203.9
5°	2633.5	2604.0	2555.0	2505.9	2439.5	2373.1	2328.3	2283.5	2223.4	2163.3	2115.3
7.5°	2794.8	2744.2	2675.7	2607.2	2520.2	2433.2	2351.0	2268.7	2177.0	2085.3	2010.5
10°	2897.6	2863.3	2784.3	2705.2	2588.7	2472.2	2357.3	2242.4	2124.3	2006.2	1907.1
12.5°	2907.6	2910.8	2838.0	2765.3	2633.5	2501.7	2362.0	2222.4	2073.7	1925.1	1809.6
15°	2819.6	2873.9	2833.8	2793.8	2660.9	2528.1	2356.2	2184.4	2013.1	1841.8	1708.4
17.5°	2656.2	2772.7	2778.5	2784.3	2651.4	2518.6	2328.3	2138.0	1944.0	1750.1	1609.8
20°	2433.2	2605.0	2664.1	2723.1	2615.1	2507.0	2302.5	2098.0	1880.8	1663.6	1516.5
22.5°	2205.5	2414.2	2522.3	2630.3	2550.2	2470.1	2252.4	2034.7	1805.4	1576.1	1426.9
25°	1946.1	2173.9	2339.9	2505.9	2456.9	2407.9	2193.4	1978.8	1734.8	1490.7	1338.4
27.5°	1720.0	1951.4	2151.7	2352.0	2341.5	2330.9	2118.0	1905.0	1655.2	1405.3	1258.2
30°	1518.6	1734.2	1958.3	2182.3	2208.1	2234.0	2028.4	1822.8	1572.4	1322.0	1180.2
32.5°	1340.5	1528.7	1769.0	2009.4	2060.0	2110.6	1925.1	1739.5	1491.8	1244.0	1107.5
35°	1194.5	1365.3	1605.6	1846.0	1909.2	1972.5	1811.2	1649.9	1408.5	1167.1	1036.9
37.5°	1065.3	1208.2	1442.7	1677.3	1754.8	1832.3	1687.9	1543.4	1317.3	1091.1	971.5
40°	958.3	1073.2	1288.8	1504.4	1594.0	1683.6	1564.5	1445.4	1230.8	1016.3	906.1
42.5°	868.7	971.0	1166.5	1362.1	1448.0	1533.9	1433.3	1332.6	1141.8	950.9	850.3
45°	792.3	874.0	1051.6	1229.3	1311.0	1392.7	1306.2	1219.8	1051.6	883.5	789.6
47.5°	720.6	790.7	942.5	1094.3	1167.1	1239.8	1172.3	1104.9	962.5	820.2	735.3
50°	656.3	712.7	845.5	978.3	1041.6	1104.9	1045.3	985.7	868.7	751.7	677.9
52.5°	600.4	646.3	757.5	868.7	923.0	977.3	926.2	875.0	782.3	689.5	625.2
55°	545.0	584.1	680.5	777.0	813.9	850.8	811.2	771.7	696.9	622.0	567.7
57.5°	493.4	528.2	607.2	686.3	714.8	743.2	707.4	671.6	615.2	558.8	513.4
60°	442.8	471.2	537.1	603.0	620.4	637.8	608.8	579.8	540.3	500.8	460.2
62.5°	395.9	421.7	470.7	519.7	531.3	542.9	520.8	498.7	468.6	438.6	406.9
65°	347.4	366.9	406.9	447.0	454.4	461.8	442.3	422.8	400.1	377.4	354.2
67.5°	302.6	316.3	349.0	381.6	382.2	382.7	366.9	351.1	338.4	325.8	307.3
70°	258.8	272.0	293.6	315.2	315.7	316.3	303.6	291.0	281.5	272.0	258.3
72.5°	214.0	223.5	239.8	256.2	255.1	254.1	246.2	238.3	230.9	223.5	213.5
75°	173.4	181.3	192.4	203.5	200.3	197.1	192.9	188.7	182.4	176.1	169.7
77.5°	136.5	141.3	147.6	153.9	151.8	149.7	146.0	142.3	137.6	132.8	130.2
80°	100.2	102.3	106.5	110.7	109.6	108.6	104.4	100.2	99.1	98.0	94.4
82.5°	68.0	70.6	71.7	72.7	72.2	71.7	68.5	65.4	64.3	63.3	62.7
85°	40.6	41.1	41.6	42.2	40.6	39.0	38.0	36.9	36.9	36.9	36.4
87.5°	18.4	19.0	19.0	19.0	18.4	17.9	16.9	15.8	16.3	16.9	16.9
90°	8.6	7.2	5.9	5.0	4.1	2.7	1.8	0.9	1.8	2.7	4.1
92.5°	69.6	45.6	31.2	23.0	18.5	14.5	9.9	6.8	9.9	14.5	18.5
95°	164.5	97.1	58.7	41.1	29.4	21.7	16.7	15.4	16.7	21.7	29.4
97.5°	183.0	104.8	66.9	47.4	35.7	28.9	24.9	24.4	24.9	28.9	35.7
100°	170.3	103.5	71.8	54.2	43.4	37.1	33.9	33.4	33.9	37.1	43.4
102.5°	159.5	105.3	77.7	61.9	52.4	46.5	43.8	42.9	43.8	46.5	52.4
105°	155.4	108.9	84.5	70.5	61.9	56.5	53.8	52.4	53.8	56.5	61.9
107.5°	154.5	114.8	93.1	80.0	71.8	66.4	63.7	62.4	63.7	66.4	71.8
110°	156.8	122.4	102.1	89.5	81.8	76.8	74.6	73.2	74.6	76.8	81.8



TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	161.3	130.1	111.6	99.4	91.7	86.8	84.5	83.1	84.5	86.8	91.7
115°	166.3	138.7	121.5	109.3	101.7	97.1	94.4	92.6	94.4	97.1	101.7
117.5°	172.6	147.8	130.6	119.3	110.7	106.6	104.4	102.1	104.4	106.6	110.7
120°	179.8	156.3	140.1	128.8	120.2	115.7	113.4	112.1	113.4	115.7	120.2
122.5°	186.6	165.4	149.6	137.4	129.2	124.3	122.0	120.6	122.0	124.3	129.2
125°	193.8	174.0	158.1	145.9	137.4	132.4	129.7	128.8	129.7	132.4	137.4
127.5°	199.7	181.6	166.3	154.1	144.6	139.6	136.5	135.1	136.5	139.6	144.6
130°	205.6	188.4	173.5	161.3	151.8	146.4	142.3	141.0	142.3	146.4	151.8
132.5°	211.0	194.3	179.8	168.1	158.6	151.8	147.3	145.5	147.3	151.8	158.6
135°	215.5	200.2	186.2	174.0	164.5	157.7	152.7	150.9	152.7	157.7	164.5
137.5°	219.1	204.2	190.7	179.4	169.9	162.7	157.7	155.9	157.7	162.7	169.9
140°	221.9	208.3	195.2	183.9	174.9	167.6	163.1	160.9	163.1	167.6	174.9
142.5°	224.6	211.5	198.8	188.4	179.4	173.1	168.1	166.3	168.1	173.1	179.4
145°	226.4	214.2	202.4	192.0	184.4	177.6	173.5	172.2	173.5	177.6	184.4
147.5°	227.7	216.4	205.6	196.6	188.9	183.0	178.9	178.0	178.9	183.0	188.9
150°	228.2	218.7	208.3	200.2	193.8	188.0	184.4	183.9	184.4	188.0	193.8
152.5°	229.1	220.0	211.5	203.8	198.4	193.4	189.8	189.8	189.8	193.4	198.4
155°	229.1	221.9	214.2	207.8	202.9	198.4	195.6	195.6	195.6	198.4	202.9
157.5°	229.5	222.8	216.4	211.5	206.9	202.9	200.6	200.2	200.6	202.9	206.9
160°	229.5	224.1	218.7	214.2	211.0	207.4	205.6	205.6	205.6	207.4	211.0
162.5°	229.1	224.6	220.0	216.4	213.7	211.0	209.7	209.7	209.7	211.0	213.7
165°	228.2	225.0	221.4	218.2	216.4	214.2	213.3	213.7	213.3	214.2	216.4
167.5°	227.7	225.0	222.3	220.0	218.7	216.9	216.4	216.9	216.4	216.9	218.7
170°	226.4	224.6	222.3	221.4	220.5	219.1	218.7	219.6	218.7	219.1	220.5
172.5°	225.9	224.6	222.8	222.3	221.9	220.9	220.9	221.4	220.9	220.9	221.9
175°	225.0	224.1	223.2	222.8	222.8	221.9	222.3	222.8	222.3	221.9	222.8
177.5°	224.6	223.7	223.2	223.2	223.2	222.8	223.2	223.7	223.2	222.8	223.2
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9	2271.9
2.5°	2180.2	2159.6	2139.1	2123.3	2107.4	2080.6	2053.7	2047.4	2041.0	2032.1	2023.1
5°	2067.4	2016.8	1966.2	1920.8	1875.5	1840.2	1804.9	1781.7	1758.5	1741.6	1724.8
7.5°	1935.6	1859.7	1783.8	1730.0	1676.3	1625.1	1574.0	1557.7	1541.3	1519.2	1497.0
10°	1808.0	1724.2	1640.4	1570.3	1500.2	1450.1	1400.0	1380.0	1360.0	1332.0	1304.1
12.5°	1694.2	1602.5	1510.7	1440.1	1369.5	1321.0	1272.5	1243.5	1214.5	1198.7	1182.9
15°	1575.0	1477.0	1379.0	1313.6	1248.2	1204.5	1160.7	1135.4	1110.1	1094.8	1079.6
17.5°	1469.6	1372.6	1275.6	1212.9	1150.2	1110.1	1070.1	1047.9	1025.8	1014.2	1002.6
20°	1369.5	1274.6	1179.7	1118.6	1057.4	1024.7	992.0	977.8	963.6	954.1	944.6
22.5°	1277.7	1184.4	1091.1	1039.0	986.8	960.4	934.1	924.0	914.0	906.1	898.2
25°	1186.0	1102.7	1019.5	975.2	930.9	909.3	887.7	877.7	867.6	859.7	851.8
27.5°	1111.2	1031.6	952.0	914.0	876.1	859.2	842.3	834.4	826.5	819.2	811.8
30°	1038.4	967.3	896.1	863.4	830.7	815.5	800.2	792.3	784.4	777.5	770.7
32.5°	971.0	909.8	848.7	818.6	788.6	775.9	763.3	753.8	744.3	739.0	733.8
35°	906.7	851.8	797.0	772.2	747.5	734.8	722.2	714.3	706.3	702.1	697.9
37.5°	851.8	802.8	753.8	730.1	706.3	694.2	682.1	675.2	668.4	666.8	665.2
40°	796.0	753.8	711.6	688.4	665.2	654.7	644.1	639.9	635.7	634.7	633.6
42.5°	749.6	708.5	667.3	646.3	625.2	616.2	607.2	605.1	603.0	604.6	606.2
45°	695.8	661.5	627.3	607.8	588.3	580.9	573.5	571.9	570.3	573.5	576.7
47.5°	650.5	618.8	587.2	568.8	550.3	545.0	539.8	539.2	538.7	542.9	547.2
50°	604.1	573.5	542.9	528.2	513.4	508.7	503.9	505.5	507.1	513.9	520.8
52.5°	560.9	532.4	503.9	490.2	476.5	473.4	470.2	473.9	477.6	485.0	492.3
55°	513.4	487.6	461.8	451.2	440.7	437.5	434.4	441.7	449.1	456.0	462.8
57.5°	468.1	445.4	422.8	413.3	403.8	403.3	402.7	409.6	416.4	423.8	431.2
60°	419.6	400.6	381.6	374.3	366.9	367.9	369.0	376.9	384.8	390.6	396.4
62.5°	375.3	359.5	343.7	336.8	330.0	332.6	335.3	343.2	351.1	357.9	364.8
65°	331.0	317.9	304.7	299.9	295.2	298.9	302.6	309.4	316.3	321.0	325.8
67.5°	288.9	277.8	266.7	263.0	259.3	263.0	266.7	273.6	280.4	285.2	289.9
70°	244.6	235.6	226.7	224.0	221.4	225.6	229.8	235.6	241.4	246.2	250.9
72.5°	203.5	196.6	189.8	189.2	188.7	192.4	196.1	201.9	207.7	210.8	214.0
75°	163.4	159.7	156.0	155.5	155.0	158.7	162.4	165.5	168.7	171.3	174.0
77.5°	127.6	124.4	121.2	121.8	122.3	124.9	127.6	130.7	133.9	135.5	137.1
80°	90.7	89.6	88.6	89.6	90.7	92.8	94.9	97.0	99.1	100.2	101.2
82.5°	62.2	61.1	60.1	61.7	63.3	64.8	66.4	68.0	69.6	70.1	70.6
85°	35.8	37.4	39.0	39.0	39.0	39.5	40.1	40.6	41.1	40.6	40.1
87.5°	16.9	17.4	17.9	17.9	17.9	18.4	19.0	19.0	19.0	18.4	17.9
90°	5.0	5.9	7.2	8.6	9.9	11.3	10.8	11.3	11.7	12.2	13.1
92.5°	23.0	31.2	45.6	69.6	93.1	84.0	62.8	44.7	34.8	30.3	27.1
95°	41.1	58.7	97.1	164.5	238.6	267.9	217.3	162.7	110.2	86.3	70.0
97.5°	47.4	66.9	104.8	183.0	307.7	412.1	426.1	373.7	281.9	222.3	170.8
100°	54.2	71.8	103.5	170.3	289.2	427.9	516.9	532.7	496.1	443.3	379.1
102.5°	61.9	77.7	105.3	159.5	262.1	398.5	521.4	585.6	593.3	568.0	533.2
105°	70.5	84.5	108.9	155.4	240.8	363.3	493.0	587.4	632.6	641.2	629.4
107.5°	80.0	93.1	114.8	154.5	225.5	332.1	452.3	560.3	631.2	666.5	678.7
110°	89.5	102.1	122.4	156.8	217.3	306.3	414.3	517.8	600.9	657.9	689.5



TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	99.4	111.6	130.1	161.3	212.8	289.2	381.4	475.8	561.2	626.7	669.6
115°	109.3	121.5	138.7	166.3	212.4	277.9	356.0	439.6	518.3	584.7	633.9
117.5°	119.3	130.6	147.8	172.6	212.8	270.2	339.3	411.6	481.2	542.2	593.3
120°	128.8	140.1	156.3	179.8	214.6	265.2	326.7	390.4	451.4	505.6	551.2
122.5°	137.4	149.6	165.4	186.6	217.8	262.1	316.3	373.7	427.4	476.7	518.3
125°	145.9	158.1	174.0	193.8	220.9	259.4	307.7	359.2	408.5	451.8	488.0
127.5°	154.1	166.3	181.6	199.7	224.6	258.0	299.6	346.1	390.8	430.6	464.0
130°	161.3	173.5	188.4	205.6	228.2	256.6	293.2	333.9	374.6	411.2	441.9
132.5°	168.1	179.8	194.3	211.0	230.9	256.2	287.4	322.6	359.2	392.6	421.6
135°	174.0	186.2	200.2	215.5	233.6	255.7	282.4	312.7	344.8	374.1	399.9
137.5°	179.4	190.7	204.2	219.1	235.4	254.8	277.9	303.2	330.3	356.5	379.5
140°	183.9	195.2	208.3	221.9	237.2	254.4	273.8	295.1	318.1	339.8	359.2
142.5°	188.4	198.8	211.5	224.6	238.6	253.5	270.2	287.4	306.3	324.4	340.7
145°	192.0	202.4	214.2	226.4	239.0	252.6	267.0	281.5	296.4	310.9	324.0
147.5°	196.6	205.6	216.4	227.7	239.0	251.2	263.9	276.5	288.7	300.9	310.4
150°	200.2	208.3	218.7	228.2	239.0	249.4	260.7	271.1	281.5	291.0	299.6
152.5°	203.8	211.5	220.0	229.1	237.7	247.2	257.1	266.1	274.7	282.9	289.6
155°	207.8	214.2	221.9	229.1	236.8	244.4	253.5	261.2	268.4	275.2	280.6
157.5°	211.5	216.4	222.8	229.5	235.4	242.2	249.4	255.7	262.1	267.5	272.0
160°	214.2	218.7	224.1	229.5	234.5	239.5	245.3	251.2	256.2	260.7	263.9
162.5°	216.4	220.0	224.6	229.1	232.7	236.8	241.3	245.8	249.9	253.9	256.6
165°	218.2	221.4	225.0	228.2	230.9	234.1	237.7	241.3	244.0	247.2	249.4
167.5°	220.0	222.3	225.0	227.7	229.1	231.3	234.1	237.2	239.5	241.3	243.1
170°	221.4	222.3	224.6	226.4	227.3	228.6	230.9	233.1	234.5	236.3	237.2
172.5°	222.3	222.8	224.6	225.9	225.9	226.4	227.7	229.5	230.4	231.8	232.2
175°	222.8	223.2	224.1	225.0	224.6	224.6	225.5	226.4	226.8	227.7	227.7
177.5°	223.2	223.2	223.7	224.6	223.7	223.2	223.7	224.1	224.6	225.0	225.0
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2271.9	2271.9	2271.9	2271.9
2.5°	2019.4	2015.7	2001.0	1986.2
5°	1712.1	1699.4	1695.2	1691.0
7.5°	1496.0	1494.9	1472.8	1450.6
10°	1305.7	1307.3	1287.2	1267.2
12.5°	1169.7	1156.5	1154.9	1153.3
15°	1067.4	1055.3	1053.2	1051.1
17.5°	995.2	987.8	985.7	983.6
20°	940.4	936.2	932.5	928.8
22.5°	892.9	887.7	884.5	881.4
25°	847.1	842.3	841.3	840.2
27.5°	806.0	800.2	800.2	800.2
30°	767.0	763.3	761.7	760.1
32.5°	730.6	727.4	727.4	727.4
35°	696.3	694.7	692.6	690.5
37.5°	665.2	665.2	664.2	663.1
40°	635.2	636.8	636.8	636.8
42.5°	607.8	609.4	609.4	609.4
45°	579.3	581.9	583.0	584.1
47.5°	551.4	555.6	556.6	557.7
50°	524.0	527.1	527.7	528.2
52.5°	496.0	499.7	502.3	505.0
55°	466.5	470.2	471.8	473.4
57.5°	434.9	438.6	439.1	439.6
60°	400.1	403.8	404.8	405.9
62.5°	366.9	369.0	370.0	371.1
65°	328.9	332.1	334.2	336.3
67.5°	292.6	295.2	295.2	295.2
70°	252.0	253.0	254.6	256.2
72.5°	214.5	215.1	215.1	215.1
75°	175.0	176.1	176.6	177.1
77.5°	137.6	138.1	138.1	138.1
80°	100.7	100.2	100.2	100.2
82.5°	69.1	67.5	67.5	67.5
85°	39.5	39.0	39.5	40.1
87.5°	17.9	17.9	17.9	17.9
90°	12.7	13.1	13.6	13.1
92.5°	26.2	24.4	24.9	23.9
95°	61.5	57.4	54.2	52.4
97.5°	140.5	123.4	112.5	107.5
100°	333.5	300.5	282.9	283.3
102.5°	500.2	475.8	461.8	448.7
105°	608.6	591.5	577.0	574.7
107.5°	676.0	667.8	661.9	657.0
110°	702.2	705.8	704.9	704.0



TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	695.4	708.5	713.0	713.5
115°	667.8	687.7	696.7	699.0
117.5°	628.5	650.6	664.2	667.4
120°	586.9	612.2	623.1	625.8
122.5°	549.0	571.1	583.3	586.9
125°	516.9	536.8	548.1	551.2
127.5°	490.2	507.4	517.8	520.5
130°	465.8	482.1	491.6	495.2
132.5°	443.7	460.0	468.1	470.4
135°	422.0	435.6	443.7	446.9
137.5°	398.5	412.5	419.3	422.0
140°	376.4	389.0	396.3	395.8
142.5°	354.7	365.5	371.9	371.4
145°	335.3	344.8	348.4	349.3
147.5°	319.5	326.2	329.8	330.3
150°	306.3	311.3	314.0	314.0
152.5°	294.6	299.1	300.5	300.5
155°	284.7	288.3	289.2	289.6
157.5°	275.6	278.3	279.2	279.2
160°	267.0	269.7	269.7	269.3
162.5°	258.5	260.7	260.7	260.3
165°	251.2	253.0	252.6	252.6
167.5°	244.0	245.3	244.9	244.9
170°	237.7	238.6	238.1	238.1
172.5°	232.2	233.1	232.2	231.8
175°	227.7	228.2	227.7	227.3
177.5°	224.6	225.0	224.1	224.1
180°	223.2	223.2	223.2	223.2



TEST NUMBER: P831140

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.25	17.26	17.04	18.06	19.04	18.49	19.49	19.28	20.30	21.28
	3H	17.91	18.81	18.71	19.62	20.64	19.93	20.82	20.73	21.64	22.65
	4H	18.50	19.34	19.31	20.16	21.19	20.38	21.23	21.20	22.05	23.07
	6H	18.87	19.65	19.70	20.48	21.52	20.66	21.44	21.50	22.27	23.31
	8H	18.97	19.71	19.81	20.56	21.60	20.73	21.47	21.57	22.32	23.36
	12H	19.02	19.73	19.87	20.57	21.63	20.75	21.46	21.60	22.30	23.37
4H	2H	16.85	17.69	17.67	18.51	19.54	18.67	19.52	19.49	20.34	21.36
	3H	18.69	19.39	19.52	20.25	21.29	20.30	21.00	21.14	21.86	22.90
	4H	19.39	20.03	20.24	20.88	21.95	20.89	21.53	21.74	22.38	23.45
	6H	19.87	20.42	20.74	21.30	22.37	21.30	21.85	22.17	22.73	23.80
	8H	20.01	20.53	20.88	21.40	22.48	21.42	21.93	22.28	22.81	23.89
	12H	20.08	20.55	20.97	21.44	22.53	21.47	21.93	22.35	22.82	23.91
8H	4H	19.67	20.18	20.53	21.05	22.14	21.01	21.52	21.87	22.39	23.48
	6H	20.26	20.69	21.15	21.60	22.68	21.51	21.94	22.41	22.85	23.94
	8H	20.47	20.84	21.37	21.75	22.86	21.69	22.07	22.60	22.98	24.08
	12H	20.60	20.93	21.50	21.83	22.98	21.80	22.13	22.71	23.03	24.19
12H	4H	19.67	20.14	20.56	21.03	22.12	20.99	21.45	21.87	22.34	23.43
	6H	20.31	20.69	21.22	21.60	22.70	21.53	21.91	22.43	22.82	23.92
	8H	20.55	20.88	21.46	21.78	22.94	21.73	22.07	22.64	22.97	24.12