

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332063-930

Luminaire Tested: **S123DIP-S1165D805U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332063-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6610.4 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	54	50	47	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14235	14235	14235	14235
5°	16977	14296	12670	14296
10°	21249	14224	11444	14224
15°	26063	14110	10653	14110
20°	31047	13931	10143	13931
25°	32967	13713	10030	13713
30°	28256	13554	10082	13554
35°	19651	13328	10188	13328
40°	14802	13065	10156	13065
45°	12291	12670	10027	12670
50°	11010	11868	9937	11868
55°	10293	11003	9813	11003
60°	9655	10097	9711	10097
65°	9075	9205	9401	9205
70°	8510	8189	8954	8189
75°	7623	7170	8210	7170
80°	6670	5876	7073	5876
85°	5224	4273	4755	4273



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	2.0
10°-20°	417.7	6.3
20°-30°	701.1	10.6
30°-40°	793.9	12.0
40°-50°	711.9	10.8
50°-60°	574.5	8.7
60°-70°	400.3	6.1
70°-80°	210.4	3.2
80°-90°	53.9	0.8
90°-100°	31.2	0.5
100°-110°	148.7	2.2
110°-120°	357.1	5.4
120°-130°	454.7	6.9
130°-140°	485.8	7.3
140°-150°	454.3	6.9
150°-160°	366.5	5.5
160°-170°	236.5	3.6
170°-180°	81.5	1.2
0°-30°	1249.1	18.9
0°-40°	2043.0	30.9
0°-60°	3329.4	50.4
0°-90°	3994.1	60.4
90°-120°	536.9	8.1
90°-150°	1931.8	29.2
90°-180°	2616.0	39.6
0°-180°	6610.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1322	1322	1322	1322	1322	
5°	1571	1323	1173	1323	1571	163
15°	2339	1266	956	1266	2339	675
25°	2776	1155	844	1155	2776	1217
35°	1496	1014	775	1014	1496	972
45°	807	832	659	832	807	639
55°	548	586	523	586	548	492
65°	356	361	369	361	356	355
75°	183	172	197	172	183	196
85°	42	35	38	35	42	50
90°	19	1	19	1	19	11
95°	24	39	24	39	24	20
105°	28	190	28	190	28	64
115°	375	356	375	356	375	346
125°	512	502	512	502	512	458
135°	632	625	632	625	632	487
145°	729	722	729	722	729	455
155°	794	795	794	795	794	366
165°	836	838	836	838	836	236
175°	855	858	855	858	855	81
180°	858	858	858	858	858	



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1403.5	1402.5	1400.0	1402.0	1397.9	1392.2	1391.7	1386.6	1371.7	1370.7	1366.6
5°	1571.2	1566.0	1565.4	1564.7	1555.8	1543.6	1520.5	1518.6	1487.8	1472.4	1453.9
7.5°	1788.2	1790.9	1781.6	1773.4	1746.0	1727.9	1703.2	1671.5	1633.7	1595.4	1569.9
10°	1944.1	1965.2	1938.9	1921.0	1904.4	1872.9	1836.5	1790.9	1745.4	1692.2	1651.9
12.5°	2111.2	2121.6	2116.3	2099.4	2073.5	2025.7	1961.0	1910.9	1869.0	1780.5	1744.7
15°	2338.8	2377.9	2352.9	2295.2	2296.5	2251.0	2166.4	2073.5	2024.1	1946.6	1840.9
17.5°	2581.2	2586.1	2575.4	2527.4	2495.4	2432.9	2354.8	2265.7	2165.8	2072.0	1959.8
20°	2710.4	2706.5	2684.1	2659.2	2604.1	2555.4	2470.1	2370.8	2242.6	2150.4	2028.0
22.5°	2782.2	2775.8	2765.2	2744.2	2698.4	2646.1	2569.6	2461.1	2339.0	2211.9	2070.5
25°	2775.8	2784.1	2785.4	2779.6	2763.6	2732.2	2672.0	2585.5	2463.8	2300.4	2153.0
27.5°	2524.6	2536.4	2570.6	2601.0	2635.0	2669.5	2664.9	2622.0	2531.9	2390.8	2210.6
30°	2273.4	2247.8	2311.2	2391.4	2445.8	2541.9	2595.7	2598.9	2548.3	2427.2	2251.6
32.5°	1924.8	1953.0	1981.1	2079.7	2198.7	2306.6	2413.8	2500.0	2509.9	2429.3	2275.7
35°	1495.5	1530.8	1582.0	1633.3	1761.5	1871.7	2060.0	2224.1	2354.8	2372.1	2277.9
37.5°	1205.2	1222.5	1255.0	1306.4	1390.2	1520.9	1666.6	1874.0	2063.4	2204.2	2210.4
40°	1053.4	1058.5	1095.0	1134.2	1202.1	1309.7	1441.0	1624.3	1851.1	2047.9	2129.9
42.5°	939.6	950.9	966.4	1004.0	1058.0	1139.1	1261.2	1412.6	1620.5	1846.9	2007.3
45°	807.4	820.2	829.8	854.8	893.2	947.7	1032.9	1171.3	1329.6	1563.4	1779.4
47.5°	720.0	721.0	728.1	747.0	773.1	814.0	874.2	963.2	1108.5	1298.2	1519.9
50°	657.5	667.6	670.3	684.9	705.5	735.6	785.5	861.2	980.4	1147.0	1350.7
52.5°	613.3	616.4	623.6	634.2	652.2	675.6	718.9	778.1	871.7	1013.7	1201.0
55°	548.5	548.5	555.5	563.9	574.1	595.3	624.1	667.6	738.8	849.0	1004.0
57.5°	488.5	491.7	496.7	499.3	508.0	522.0	546.1	579.1	632.2	717.0	840.3
60°	448.5	454.3	453.6	458.8	466.5	477.4	497.9	524.8	572.2	640.1	744.0
62.5°	413.7	413.3	413.2	419.3	427.0	437.4	450.7	474.0	514.3	574.5	662.9
65°	356.3	355.0	359.5	363.3	365.9	373.6	383.8	404.3	431.2	476.1	544.6
67.5°	305.2	301.6	303.9	305.2	309.7	315.6	325.2	337.9	359.3	395.3	447.0
70°	270.4	267.2	266.5	267.8	271.7	276.1	283.2	295.4	315.3	344.1	381.9
72.5°	234.5	232.4	232.2	235.1	236.8	239.8	244.8	255.9	271.7	293.3	328.6
75°	183.3	183.3	183.3	183.9	185.8	188.4	192.2	198.0	210.2	225.5	249.2
77.5°	137.4	137.2	136.5	136.3	139.2	140.3	141.2	146.6	153.4	163.8	181.1
80°	107.6	104.4	105.7	107.6	108.9	109.6	111.5	112.8	118.5	124.3	136.5
82.5°	80.0	77.3	77.5	80.5	80.7	81.4	83.3	85.1	87.2	92.5	99.1
85°	42.3	42.3	43.0	43.0	43.5	43.0	44.8	45.5	45.5	48.7	52.5
87.5°	19.2	18.1	18.6	19.0	18.4	18.9	19.3	19.7	20.1	20.5	20.6
90°	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5	15.9	15.3	13.5
92.5°	21.2	21.0	20.8	20.6	20.5	20.0	19.0	18.1	17.2	16.3	14.9
95°	24.2	24.2	24.2	24.2	24.2	23.7	22.7	21.8	20.8	19.7	18.2
97.5°	26.3	26.1	26.0	25.8	25.7	25.0	23.9	22.8	21.7	20.5	30.7
100°	26.7	26.7	26.5	26.3	26.2	25.6	24.5	23.3	22.2	21.0	43.1
102.5°	27.3	27.0	26.7	26.5	26.3	27.9	31.4	34.9	38.4	41.9	66.0
105°	28.0	27.8	27.5	27.2	26.9	39.3	64.4	89.4	114.5	139.6	152.3
107.5°	88.1	107.0	125.9	144.8	163.6	182.3	200.7	219.1	237.5	255.8	253.8
110°	175.3	195.5	215.8	236.0	256.3	268.8	273.5	278.1	282.8	287.5	285.9



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	300.8	305.0	309.2	313.6	317.8	319.9	319.8	319.8	319.7	319.6	318.0
115°	374.8	374.2	373.7	373.1	372.5	371.5	370.1	368.7	367.3	365.9	364.6
117.5°	416.4	416.2	416.1	416.0	415.9	415.2	414.2	413.0	411.9	410.7	410.1
120°	444.9	444.9	444.9	444.9	444.9	444.3	443.2	442.1	440.9	439.8	439.4
122.5°	473.0	472.9	472.7	472.6	472.5	472.1	471.2	470.4	469.7	468.9	468.3
125°	512.5	512.2	511.9	511.6	511.4	511.0	510.8	510.5	510.2	509.9	509.3
127.5°	550.5	550.7	551.1	551.3	551.5	551.5	551.1	550.6	550.2	549.7	549.0
130°	574.9	575.2	575.5	575.8	576.1	575.9	575.4	574.8	574.2	573.6	573.1
132.5°	597.4	597.8	598.2	598.6	598.9	598.8	598.3	597.7	597.2	596.6	596.1
135°	631.7	632.1	632.5	632.9	633.3	633.3	632.9	632.5	632.1	631.7	631.1
137.5°	663.9	664.2	664.5	664.8	665.0	664.9	664.1	663.5	662.8	662.1	661.8
140°	683.3	683.5	683.9	684.1	684.4	684.3	683.7	683.1	682.6	682.0	681.6
142.5°	701.2	701.6	701.9	702.3	702.7	702.7	702.2	701.8	701.3	700.9	700.4
145°	728.6	728.6	728.6	728.6	728.6	728.4	728.1	727.8	727.6	727.2	727.0
147.5°	748.9	749.6	750.2	750.9	751.5	751.7	751.5	751.1	750.9	750.6	750.3
150°	764.3	764.7	765.1	765.5	766.0	766.0	765.7	765.4	765.2	764.9	764.6
152.5°	776.5	777.1	777.8	778.4	779.1	779.2	778.6	778.1	777.6	777.1	777.0
155°	793.5	794.4	795.2	796.1	797.0	797.0	796.3	795.7	794.9	794.2	794.0
157.5°	808.0	809.1	810.2	811.3	812.4	812.5	811.6	810.8	810.0	809.1	809.3
160°	817.2	818.2	819.1	820.1	821.1	821.2	820.4	819.5	818.6	817.7	817.9
162.5°	825.8	826.7	827.5	828.4	829.3	829.2	828.3	827.4	826.4	825.4	825.6
165°	836.3	837.2	838.2	839.3	840.2	840.2	839.0	837.9	836.7	835.6	835.8
167.5°	843.8	844.9	846.0	847.2	848.3	848.3	847.2	846.0	844.9	843.8	843.8
170°	848.4	849.5	850.6	851.7	852.9	852.9	851.7	850.6	849.5	848.4	848.4
172.5°	850.9	852.2	853.5	854.7	855.9	856.0	854.8	853.7	852.6	851.4	851.3
175°	854.8	855.9	857.0	858.2	859.2	859.3	858.3	857.4	856.4	855.4	855.2
177.5°	855.9	857.0	858.2	859.3	860.5	860.5	859.7	858.8	857.9	856.9	856.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1363.5	1359.4	1355.4	1348.2	1342.0	1333.3	1330.7	1327.6	1318.4	1310.3	1304.1
5°	1446.8	1431.4	1409.0	1388.5	1371.9	1349.5	1336.6	1323.1	1303.9	1286.6	1272.5
7.5°	1534.0	1503.7	1468.8	1431.2	1396.1	1362.3	1335.0	1310.6	1283.7	1258.2	1238.4
10°	1603.2	1559.6	1510.9	1458.4	1413.5	1369.9	1333.4	1301.4	1266.8	1236.6	1211.7
12.5°	1682.1	1617.6	1550.4	1486.5	1433.5	1373.0	1328.8	1288.1	1248.9	1212.6	1184.5
15°	1775.6	1693.5	1614.0	1526.3	1445.5	1369.9	1317.4	1266.2	1220.7	1183.5	1147.6
17.5°	1860.7	1767.7	1663.0	1556.2	1458.9	1369.2	1295.6	1237.7	1180.8	1135.3	1099.5
20°	1908.9	1803.1	1684.6	1573.7	1466.1	1366.1	1285.4	1216.2	1154.6	1106.6	1066.2
22.5°	1950.4	1826.7	1704.1	1585.5	1465.6	1357.9	1266.4	1195.1	1128.5	1081.5	1038.5
25°	1993.4	1845.4	1722.4	1583.3	1449.4	1337.9	1235.4	1154.6	1088.0	1032.9	988.7
27.5°	2030.3	1844.1	1698.1	1548.6	1424.0	1312.3	1202.8	1116.2	1045.5	985.6	940.8
30°	2054.9	1846.7	1673.0	1525.0	1399.5	1284.1	1177.7	1090.5	1016.3	955.4	913.1
32.5°	2070.3	1845.1	1649.9	1492.2	1360.5	1258.4	1150.6	1060.3	984.0	924.1	883.4
35°	2079.3	1833.9	1610.2	1424.4	1297.5	1198.2	1107.9	1014.3	934.3	878.5	832.3
37.5°	2061.3	1810.1	1564.1	1359.0	1220.2	1122.3	1046.4	966.6	890.0	828.7	788.9
40°	2033.1	1794.8	1528.2	1313.0	1166.9	1072.6	1008.0	929.8	854.1	795.8	758.6
42.5°	1979.3	1763.5	1488.7	1261.7	1111.5	1017.2	957.7	892.3	820.8	766.1	729.0
45°	1848.0	1695.4	1429.5	1184.8	1029.7	932.3	879.8	832.3	767.6	714.4	682.4
47.5°	1665.7	1593.1	1343.9	1103.7	944.4	850.7	796.1	757.9	710.6	667.6	636.9
50°	1539.1	1509.0	1286.0	1048.3	887.5	795.8	743.3	708.7	674.7	631.8	603.6
52.5°	1393.0	1411.6	1218.4	990.8	829.6	739.5	690.0	662.5	631.7	596.4	571.9
55°	1187.3	1254.6	1101.5	894.5	743.3	657.5	610.7	586.3	568.3	542.1	521.0
57.5°	994.7	1080.4	975.1	795.2	658.6	584.5	539.6	513.1	501.6	487.9	471.2
60°	880.4	965.0	884.9	728.6	601.7	531.2	491.5	469.0	457.5	447.9	433.8
62.5°	778.4	864.0	796.7	660.9	545.8	480.5	445.8	424.0	415.0	409.9	397.9
65°	638.2	711.9	667.0	555.5	465.9	408.1	376.7	361.4	353.0	351.1	343.5
67.5°	519.4	575.5	542.8	460.8	390.2	340.4	313.7	300.7	294.2	293.6	287.8
70°	441.5	494.0	469.0	394.7	333.9	294.7	271.7	260.2	256.3	255.7	252.5
72.5°	381.0	417.7	397.8	335.7	288.7	253.2	236.3	224.3	219.9	220.8	218.7
75°	281.9	309.5	298.0	255.0	217.2	194.1	180.0	172.4	168.5	170.5	167.9
77.5°	202.8	220.3	209.9	180.2	156.9	140.2	129.8	125.1	121.6	121.5	120.3
80°	153.1	163.4	157.6	139.7	120.5	106.4	98.0	94.8	92.9	92.3	91.6
82.5°	109.1	117.8	111.0	98.7	85.6	77.1	72.4	68.2	66.8	67.2	66.5
85°	55.1	58.3	55.8	48.0	43.0	39.1	36.5	34.6	33.3	34.0	32.7
87.5°	21.3	21.4	19.6	17.1	15.8	14.0	13.8	12.4	11.7	12.0	11.7
90°	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7	2.0	3.5	4.9
92.5°	13.5	12.1	10.8	10.3	10.7	11.1	11.5	11.8	11.5	11.1	10.7
95°	16.6	15.1	13.5	15.7	21.4	27.2	33.1	38.9	33.1	27.2	21.4
97.5°	40.9	51.1	61.3	67.8	70.4	73.0	75.6	78.1	75.6	73.0	70.4
100°	65.2	87.3	109.4	119.0	116.2	113.4	110.6	107.7	110.6	113.4	116.2
102.5°	90.2	114.4	138.5	149.5	147.5	145.4	143.4	141.4	143.4	145.4	147.5
105°	165.1	177.8	190.6	196.2	194.6	193.1	191.5	190.0	191.5	193.1	194.6
107.5°	251.8	249.8	247.8	246.1	244.9	243.7	242.5	241.2	242.5	243.7	244.9
110°	284.4	282.8	281.2	279.9	278.8	277.6	276.5	275.3	276.5	277.6	278.8



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.5	315.0	313.3	312.1	311.0	310.1	309.0	308.0	309.0	310.1	311.0
115°	363.3	362.1	360.8	359.7	358.9	358.0	357.2	356.3	357.2	358.0	358.9
117.5°	409.4	408.8	408.1	407.2	406.3	405.2	404.1	403.1	404.1	405.2	406.3
120°	439.0	438.5	438.1	437.2	435.9	434.7	433.4	432.2	433.4	434.7	435.9
122.5°	467.8	467.2	466.7	465.9	464.9	463.8	462.8	461.7	462.8	463.8	464.9
125°	508.7	508.3	507.7	506.8	505.6	504.5	503.4	502.3	503.4	504.5	505.6
127.5°	548.4	547.6	547.0	546.1	544.9	543.8	542.7	541.5	542.7	543.8	544.9
130°	572.5	571.9	571.4	570.5	569.4	568.3	567.1	566.0	567.1	568.3	569.4
132.5°	595.7	595.3	594.8	594.0	592.9	591.7	590.6	589.5	590.6	591.7	592.9
135°	630.6	630.0	629.4	628.7	627.9	627.0	626.1	625.3	626.1	627.0	627.9
137.5°	661.5	661.2	660.9	660.1	659.1	658.0	657.0	655.9	657.0	658.0	659.1
140°	681.2	680.8	680.3	679.7	678.8	678.0	677.1	676.3	677.1	678.0	678.8
142.5°	700.0	699.6	699.2	698.5	697.7	696.8	696.0	695.1	696.0	696.8	697.7
145°	726.7	726.4	726.1	725.5	724.5	723.5	722.5	721.5	722.5	723.5	724.5
147.5°	750.0	749.7	749.5	749.0	748.4	747.7	747.1	746.4	747.1	747.7	748.4
150°	764.3	764.0	763.8	763.4	763.0	762.5	762.1	761.7	762.1	762.5	763.0
152.5°	776.7	776.6	776.4	776.2	776.1	775.8	775.7	775.4	775.7	775.8	776.1
155°	793.9	793.8	793.6	793.7	794.0	794.3	794.6	794.8	794.6	794.3	794.0
157.5°	809.4	809.5	809.7	809.8	809.8	809.8	809.8	809.8	809.8	809.8	809.8
160°	818.1	818.2	818.3	818.5	818.6	818.8	818.9	819.0	818.9	818.8	818.6
162.5°	825.7	825.8	826.0	826.2	826.6	827.0	827.4	827.7	827.4	827.0	826.6
165°	835.9	836.1	836.2	836.5	836.9	837.3	837.7	838.2	837.7	837.3	836.9
167.5°	843.8	843.8	843.8	844.1	844.7	845.2	845.8	846.4	845.8	845.2	844.7
170°	848.4	848.4	848.4	848.6	849.2	849.8	850.4	850.9	850.4	849.8	849.2
172.5°	851.2	851.1	851.0	851.3	851.9	852.6	853.3	853.9	853.3	852.6	851.9
175°	855.1	854.9	854.8	855.1	855.8	856.6	857.2	857.9	857.2	856.6	855.8
177.5°	856.7	856.6	856.5	856.7	857.3	857.9	858.4	858.9	858.4	857.9	857.3
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1300.5	1296.9	1291.8	1284.1	1277.9	1268.2	1268.2	1269.7	1269.7	1269.3	1268.2
5°	1261.0	1251.4	1239.9	1226.5	1212.4	1198.2	1195.6	1190.5	1186.7	1184.1	1181.0
7.5°	1219.4	1202.3	1185.5	1166.7	1149.5	1135.3	1125.4	1117.2	1112.0	1106.4	1102.2
10°	1191.2	1170.0	1150.1	1130.3	1108.5	1091.2	1080.4	1072.6	1066.9	1061.8	1059.2
12.5°	1157.9	1133.7	1111.7	1092.9	1069.0	1051.2	1040.9	1037.2	1030.5	1019.7	1014.1
15°	1109.1	1086.7	1060.5	1031.6	1020.1	998.3	986.1	980.4	976.5	968.2	965.6
17.5°	1067.5	1038.1	1008.7	987.2	965.7	948.0	941.3	934.1	929.0	922.2	920.1
20°	1034.2	1008.0	981.0	958.0	935.5	916.3	910.5	905.4	900.3	897.1	894.5
22.5°	1000.4	974.1	951.8	930.3	906.3	893.7	887.5	881.8	878.2	876.0	873.5
25°	952.8	929.8	904.7	885.5	866.3	857.9	854.1	850.9	848.4	845.1	844.5
27.5°	910.3	885.2	864.9	846.9	833.2	826.2	822.5	820.9	821.5	822.6	823.4
30°	878.5	855.4	838.8	823.4	810.6	804.1	803.5	803.5	806.1	806.7	808.0
32.5°	849.3	830.3	813.7	798.7	789.0	784.6	787.1	787.1	789.1	790.8	793.1
35°	806.7	790.0	777.2	764.4	756.1	758.0	759.3	760.6	763.8	767.6	770.2
37.5°	766.1	751.6	738.3	728.3	724.5	727.9	731.0	733.7	737.4	740.4	742.9
40°	736.9	725.9	713.1	704.2	705.5	707.4	710.0	713.1	716.4	718.3	720.9
42.5°	709.7	698.3	688.6	681.1	682.9	685.3	686.9	688.6	692.3	695.8	697.2
45°	668.3	659.3	650.4	645.9	647.2	648.5	649.7	651.7	654.8	657.5	658.0
47.5°	621.8	615.6	609.5	605.1	607.2	606.7	608.4	612.5	613.4	615.0	618.6
50°	592.1	586.3	579.3	578.0	578.0	578.0	578.6	583.8	583.8	586.3	588.9
52.5°	559.3	555.5	551.1	548.8	547.7	547.7	550.4	553.0	554.0	557.6	560.2
55°	510.7	506.9	503.0	501.1	499.8	501.1	506.2	507.4	510.7	512.6	514.5
57.5°	460.1	457.1	454.0	453.0	452.7	454.4	457.2	461.1	461.9	467.7	470.7
60°	426.7	422.2	419.7	419.7	418.4	424.2	422.9	429.3	430.6	434.5	439.0
62.5°	392.4	386.4	385.4	385.4	387.2	388.8	390.6	393.5	396.7	401.6	405.1
65°	337.0	333.9	338.3	337.7	336.4	340.2	340.2	343.5	347.3	351.8	358.8
67.5°	284.6	283.0	283.3	283.3	285.3	287.5	289.3	292.0	296.7	301.4	306.1
70°	249.2	251.2	248.0	250.5	252.5	253.1	254.4	258.2	263.3	266.5	271.7
72.5°	214.9	214.7	215.2	216.2	218.1	219.2	220.5	224.9	230.6	233.3	237.3
75°	165.3	164.7	166.6	166.6	169.8	171.0	172.4	174.3	179.4	183.3	186.5
77.5°	120.7	121.5	121.1	123.3	122.4	122.6	126.6	128.6	129.1	136.6	138.3
80°	91.0	92.3	92.9	93.5	94.2	92.9	97.4	99.3	99.3	103.8	107.0
82.5°	65.4	66.1	67.8	68.4	68.6	69.9	70.2	71.7	73.2	75.1	79.3
85°	32.7	34.6	35.2	34.6	35.2	34.0	35.9	36.5	37.2	37.2	37.2
87.5°	11.5	12.3	12.2	13.1	13.0	13.9	13.9	13.0	13.1	14.8	12.8
90°	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5	17.0	17.5	18.0
92.5°	10.3	10.8	12.1	13.5	14.9	16.3	17.2	18.1	19.0	20.0	20.5
95°	15.7	13.5	15.1	16.6	18.2	19.7	20.8	21.8	22.7	23.7	24.2
97.5°	67.8	61.3	51.1	40.9	30.7	20.5	21.7	22.8	23.9	25.0	25.7
100°	119.0	109.4	87.3	65.2	43.1	21.0	22.2	23.3	24.5	25.6	26.2
102.5°	149.5	138.5	114.4	90.2	66.0	41.9	38.4	34.9	31.4	27.9	26.3
105°	196.2	190.6	177.8	165.1	152.3	139.6	114.5	89.4	64.4	39.3	26.9
107.5°	246.1	247.8	249.8	251.8	253.8	255.8	237.5	219.1	200.7	182.3	163.6
110°	279.9	281.2	282.8	284.4	285.9	287.5	282.8	278.1	273.5	268.8	256.3



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	312.1	313.3	315.0	316.5	318.0	319.6	319.7	319.8	319.8	319.9	317.8
115°	359.7	360.8	362.1	363.3	364.6	365.9	367.3	368.7	370.1	371.5	372.5
117.5°	407.2	408.1	408.8	409.4	410.1	410.7	411.9	413.0	414.2	415.2	415.9
120°	437.2	438.1	438.5	439.0	439.4	439.8	440.9	442.1	443.2	444.3	444.9
122.5°	465.9	466.7	467.2	467.8	468.3	468.9	469.7	470.4	471.2	472.1	472.5
125°	506.8	507.7	508.3	508.7	509.3	509.9	510.2	510.5	510.8	511.0	511.4
127.5°	546.1	547.0	547.6	548.4	549.0	549.7	550.2	550.6	551.1	551.5	551.5
130°	570.5	571.4	571.9	572.5	573.1	573.6	574.2	574.8	575.4	575.9	576.1
132.5°	594.0	594.8	595.3	595.7	596.1	596.6	597.2	597.7	598.3	598.8	598.9
135°	628.7	629.4	630.0	630.6	631.1	631.7	632.1	632.5	632.9	633.3	633.3
137.5°	660.1	660.9	661.2	661.5	661.8	662.1	662.8	663.5	664.1	664.9	665.0
140°	679.7	680.3	680.8	681.2	681.6	682.0	682.6	683.1	683.7	684.3	684.4
142.5°	698.5	699.2	699.6	700.0	700.4	700.9	701.3	701.8	702.2	702.7	702.7
145°	725.5	726.1	726.4	726.7	727.0	727.2	727.6	727.8	728.1	728.4	728.6
147.5°	749.0	749.5	749.7	750.0	750.3	750.6	750.9	751.1	751.5	751.7	751.5
150°	763.4	763.8	764.0	764.3	764.6	764.9	765.2	765.4	765.7	766.0	766.0
152.5°	776.2	776.4	776.6	776.7	777.0	777.1	777.6	778.1	778.6	779.2	779.1
155°	793.7	793.6	793.8	793.9	794.0	794.2	794.9	795.7	796.3	797.0	797.0
157.5°	809.8	809.7	809.5	809.4	809.3	809.1	810.0	810.8	811.6	812.5	812.4
160°	818.5	818.3	818.2	818.1	817.9	817.7	818.6	819.5	820.4	821.2	821.1
162.5°	826.2	826.0	825.8	825.7	825.6	825.4	826.4	827.4	828.3	829.2	829.3
165°	836.5	836.2	836.1	835.9	835.8	835.6	836.7	837.9	839.0	840.2	840.2
167.5°	844.1	843.8	843.8	843.8	843.8	843.8	844.9	846.0	847.2	848.3	848.3
170°	848.6	848.4	848.4	848.4	848.4	848.4	849.5	850.6	851.7	852.9	852.9
172.5°	851.3	851.0	851.1	851.2	851.3	851.4	852.6	853.7	854.8	856.0	855.9
175°	855.1	854.8	854.9	855.1	855.2	855.4	856.4	857.4	858.3	859.3	859.2
177.5°	856.7	856.5	856.6	856.7	856.8	856.9	857.9	858.8	859.7	860.5	860.5
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1264.6	1264.1	1267.7	1265.1	1267.7	1264.1	1264.6	1268.2	1269.3	1269.7	1269.7
5°	1177.0	1179.0	1172.6	1172.6	1172.6	1179.0	1177.0	1181.0	1184.1	1186.7	1190.5
7.5°	1099.2	1096.3	1096.6	1093.2	1096.6	1096.3	1099.2	1102.2	1106.4	1112.0	1117.2
10°	1051.5	1047.7	1046.4	1047.0	1046.4	1047.7	1051.5	1059.2	1061.8	1066.9	1072.6
12.5°	1012.0	1011.2	1002.8	1002.9	1002.8	1011.2	1012.0	1014.1	1019.7	1030.5	1037.2
15°	965.6	953.5	952.2	956.0	952.2	953.5	965.6	965.6	968.2	976.5	980.4
17.5°	919.1	912.7	913.1	911.2	913.1	912.7	919.1	920.1	922.2	929.0	934.1
20°	894.5	890.6	890.0	885.5	890.0	890.6	894.5	894.5	897.1	900.3	905.4
22.5°	872.0	870.7	871.1	866.1	871.1	870.7	872.0	873.5	876.0	878.2	881.8
25°	843.9	847.1	844.5	844.5	844.5	847.1	843.9	844.5	845.1	848.4	850.9
27.5°	824.9	824.8	823.5	823.5	823.5	824.8	824.9	823.4	822.6	821.5	820.9
30°	810.6	809.9	811.2	811.2	811.2	809.9	810.6	808.0	806.7	806.1	803.5
32.5°	796.2	797.1	797.4	797.9	797.4	797.1	796.2	793.1	790.8	789.1	787.1
35°	774.0	774.7	776.6	775.3	776.6	774.7	774.0	770.2	767.6	763.8	760.6
37.5°	744.0	747.0	746.3	747.4	746.3	747.0	744.0	742.9	740.4	737.4	733.7
40°	721.5	723.4	722.8	722.8	722.8	723.4	721.5	720.9	718.3	716.4	713.1
42.5°	698.5	699.9	698.1	697.2	698.1	699.9	698.5	697.2	695.8	692.3	688.6
45°	660.6	659.3	661.3	658.7	661.3	659.3	660.6	658.0	657.5	654.8	651.7
47.5°	618.3	619.6	620.1	622.1	620.1	619.6	618.3	618.6	615.0	613.4	612.5
50°	590.1	593.9	593.9	593.4	593.9	593.9	590.1	588.9	586.3	583.8	583.8
52.5°	562.5	564.3	566.8	566.7	566.8	564.3	562.5	560.2	557.6	554.0	553.0
55°	519.7	521.0	522.2	522.9	522.2	521.0	519.7	514.5	512.6	510.7	507.4
57.5°	475.3	474.8	477.8	478.7	477.8	474.8	475.3	470.7	467.7	461.9	461.1
60°	444.0	444.0	449.1	451.1	449.1	444.0	444.0	439.0	434.5	430.6	429.3
62.5°	410.7	412.8	417.9	415.2	417.9	412.8	410.7	405.1	401.6	396.7	393.5
65°	362.0	367.1	366.5	369.1	366.5	367.1	362.0	358.8	351.8	347.3	343.5
67.5°	311.1	314.4	318.9	319.4	318.9	314.4	311.1	306.1	301.4	296.7	292.0
70°	276.8	280.0	282.6	284.5	282.6	280.0	276.8	271.7	266.5	263.3	258.2
72.5°	243.5	245.2	251.3	248.6	251.3	245.2	243.5	237.3	233.3	230.6	224.9
75°	190.9	195.4	199.3	197.4	199.3	195.4	190.9	186.5	183.3	179.4	174.3
77.5°	141.2	145.7	147.5	145.9	147.5	145.7	141.2	138.3	136.6	129.1	128.6
80°	111.5	110.9	114.7	114.1	114.7	110.9	111.5	107.0	103.8	99.3	99.3
82.5°	81.8	81.1	82.9	83.3	82.9	81.1	81.8	79.3	75.1	73.2	71.7
85°	39.7	41.7	39.1	38.5	39.1	41.7	39.7	37.2	37.2	37.2	36.5
87.5°	12.9	13.0	12.5	12.1	12.5	13.0	12.9	12.8	14.8	13.1	13.0
90°	18.3	18.6	18.8	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5
92.5°	20.6	20.8	21.0	21.2	21.0	20.8	20.6	20.5	20.0	19.0	18.1
95°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	23.7	22.7	21.8
97.5°	25.8	26.0	26.1	26.3	26.1	26.0	25.8	25.7	25.0	23.9	22.8
100°	26.3	26.5	26.7	26.7	26.7	26.5	26.3	26.2	25.6	24.5	23.3
102.5°	26.5	26.7	27.0	27.3	27.0	26.7	26.5	26.3	27.9	31.4	34.9
105°	27.2	27.5	27.8	28.0	27.8	27.5	27.2	26.9	39.3	64.4	89.4
107.5°	144.8	125.9	107.0	88.1	107.0	125.9	144.8	163.6	182.3	200.7	219.1
110°	236.0	215.8	195.5	175.3	195.5	215.8	236.0	256.3	268.8	273.5	278.1



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	313.6	309.2	305.0	300.8	305.0	309.2	313.6	317.8	319.9	319.8	319.8
115°	373.1	373.7	374.2	374.8	374.2	373.7	373.1	372.5	371.5	370.1	368.7
117.5°	416.0	416.1	416.2	416.4	416.2	416.1	416.0	415.9	415.2	414.2	413.0
120°	444.9	444.9	444.9	444.9	444.9	444.9	444.9	444.9	444.3	443.2	442.1
122.5°	472.6	472.7	472.9	473.0	472.9	472.7	472.6	472.5	472.1	471.2	470.4
125°	511.6	511.9	512.2	512.5	512.2	511.9	511.6	511.4	511.0	510.8	510.5
127.5°	551.3	551.1	550.7	550.5	550.7	551.1	551.3	551.5	551.5	551.1	550.6
130°	575.8	575.5	575.2	574.9	575.2	575.5	575.8	576.1	575.9	575.4	574.8
132.5°	598.6	598.2	597.8	597.4	597.8	598.2	598.6	598.9	598.8	598.3	597.7
135°	632.9	632.5	632.1	631.7	632.1	632.5	632.9	633.3	633.3	632.9	632.5
137.5°	664.8	664.5	664.2	663.9	664.2	664.5	664.8	665.0	664.9	664.1	663.5
140°	684.1	683.9	683.5	683.3	683.5	683.9	684.1	684.4	684.3	683.7	683.1
142.5°	702.3	701.9	701.6	701.2	701.6	701.9	702.3	702.7	702.7	702.2	701.8
145°	728.6	728.6	728.6	728.6	728.6	728.6	728.6	728.6	728.4	728.1	727.8
147.5°	750.9	750.2	749.6	748.9	749.6	750.2	750.9	751.5	751.7	751.5	751.1
150°	765.5	765.1	764.7	764.3	764.7	765.1	765.5	766.0	766.0	765.7	765.4
152.5°	778.4	777.8	777.1	776.5	777.1	777.8	778.4	779.1	779.2	778.6	778.1
155°	796.1	795.2	794.4	793.5	794.4	795.2	796.1	797.0	797.0	796.3	795.7
157.5°	811.3	810.2	809.1	808.0	809.1	810.2	811.3	812.4	812.5	811.6	810.8
160°	820.1	819.1	818.2	817.2	818.2	819.1	820.1	821.1	821.2	820.4	819.5
162.5°	828.4	827.5	826.7	825.8	826.7	827.5	828.4	829.3	829.2	828.3	827.4
165°	839.3	838.2	837.2	836.3	837.2	838.2	839.3	840.2	840.2	839.0	837.9
167.5°	847.2	846.0	844.9	843.8	844.9	846.0	847.2	848.3	848.3	847.2	846.0
170°	851.7	850.6	849.5	848.4	849.5	850.6	851.7	852.9	852.9	851.7	850.6
172.5°	854.7	853.5	852.2	850.9	852.2	853.5	854.7	855.9	856.0	854.8	853.7
175°	858.2	857.0	855.9	854.8	855.9	857.0	858.2	859.2	859.3	858.3	857.4
177.5°	859.3	858.2	857.0	855.9	857.0	858.2	859.3	860.5	860.5	859.7	858.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1268.2	1268.2	1277.9	1284.1	1291.8	1296.9	1300.5	1304.1	1310.3	1318.4	1327.6
5°	1195.6	1198.2	1212.4	1226.5	1239.9	1251.4	1261.0	1272.5	1286.6	1303.9	1323.1
7.5°	1125.4	1135.3	1149.5	1166.7	1185.5	1202.3	1219.4	1238.4	1258.2	1283.7	1310.6
10°	1080.4	1091.2	1108.5	1130.3	1150.1	1170.0	1191.2	1211.7	1236.6	1266.8	1301.4
12.5°	1040.9	1051.2	1069.0	1092.9	1111.7	1133.7	1157.9	1184.5	1212.6	1248.9	1288.1
15°	986.1	998.3	1020.1	1031.6	1060.5	1086.7	1109.1	1147.6	1183.5	1220.7	1266.2
17.5°	941.3	948.0	965.7	987.2	1008.7	1038.1	1067.5	1099.5	1135.3	1180.8	1237.7
20°	910.5	916.3	935.5	958.0	981.0	1008.0	1034.2	1066.2	1106.6	1154.6	1216.2
22.5°	887.5	893.7	906.3	930.3	951.8	974.1	1000.4	1038.5	1081.5	1128.5	1195.1
25°	854.1	857.9	866.3	885.5	904.7	929.8	952.8	988.7	1032.9	1088.0	1154.6
27.5°	822.5	826.2	833.2	846.9	864.9	885.2	910.3	940.8	985.6	1045.5	1116.2
30°	803.5	804.1	810.6	823.4	838.8	855.4	878.5	913.1	955.4	1016.3	1090.5
32.5°	787.1	784.6	789.0	798.7	813.7	830.3	849.3	883.4	924.1	984.0	1060.3
35°	759.3	758.0	756.1	764.4	777.2	790.0	806.7	832.3	878.5	934.3	1014.3
37.5°	731.0	727.9	724.5	728.3	738.3	751.6	766.1	788.9	828.7	890.0	966.6
40°	710.0	707.4	705.5	704.2	713.1	725.9	736.9	758.6	795.8	854.1	929.8
42.5°	686.9	685.3	682.9	681.1	688.6	698.3	709.7	729.0	766.1	820.8	892.3
45°	649.7	648.5	647.2	645.9	650.4	659.3	668.3	682.4	714.4	767.6	832.3
47.5°	608.4	606.7	607.2	605.1	609.5	615.6	621.8	636.9	667.6	710.6	757.9
50°	578.6	578.0	578.0	578.0	579.3	586.3	592.1	603.6	631.8	674.7	708.7
52.5°	550.4	547.7	547.7	548.8	551.1	555.5	559.3	571.9	596.4	631.7	662.5
55°	506.2	501.1	499.8	501.1	503.0	506.9	510.7	521.0	542.1	568.3	586.3
57.5°	457.2	454.4	452.7	453.0	454.0	457.1	460.1	471.2	487.9	501.6	513.1
60°	422.9	424.2	418.4	419.7	419.7	422.2	426.7	433.8	447.9	457.5	469.0
62.5°	390.6	388.8	387.2	385.4	385.4	386.4	392.4	397.9	409.9	415.0	424.0
65°	340.2	340.2	336.4	337.7	338.3	333.9	337.0	343.5	351.1	353.0	361.4
67.5°	289.3	287.5	285.3	283.3	283.3	283.0	284.6	287.8	293.6	294.2	300.7
70°	254.4	253.1	252.5	250.5	248.0	251.2	249.2	252.5	255.7	256.3	260.2
72.5°	220.5	219.2	218.1	216.2	215.2	214.7	214.9	218.7	220.8	219.9	224.3
75°	172.4	171.0	169.8	166.6	166.6	164.7	165.3	167.9	170.5	168.5	172.4
77.5°	126.6	122.6	122.4	123.3	121.1	121.5	120.7	120.3	121.5	121.6	125.1
80°	97.4	92.9	94.2	93.5	92.9	92.3	91.0	91.6	92.3	92.9	94.8
82.5°	70.2	69.9	68.6	68.4	67.8	66.1	65.4	66.5	67.2	66.8	68.2
85°	35.9	34.0	35.2	34.6	35.2	34.6	32.7	32.7	34.0	33.3	34.6
87.5°	13.9	13.9	13.0	13.1	12.2	12.3	11.5	11.7	12.0	11.7	12.4
90°	15.9	15.3	13.5	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7
92.5°	17.2	16.3	14.9	13.5	12.1	10.8	10.3	10.7	11.1	11.5	11.8
95°	20.8	19.7	18.2	16.6	15.1	13.5	15.7	21.4	27.2	33.1	38.9
97.5°	21.7	20.5	30.7	40.9	51.1	61.3	67.8	70.4	73.0	75.6	78.1
100°	22.2	21.0	43.1	65.2	87.3	109.4	119.0	116.2	113.4	110.6	107.7
102.5°	38.4	41.9	66.0	90.2	114.4	138.5	149.5	147.5	145.4	143.4	141.4
105°	114.5	139.6	152.3	165.1	177.8	190.6	196.2	194.6	193.1	191.5	190.0
107.5°	237.5	255.8	253.8	251.8	249.8	247.8	246.1	244.9	243.7	242.5	241.2
110°	282.8	287.5	285.9	284.4	282.8	281.2	279.9	278.8	277.6	276.5	275.3



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	319.7	319.6	318.0	316.5	315.0	313.3	312.1	311.0	310.1	309.0	308.0
115°	367.3	365.9	364.6	363.3	362.1	360.8	359.7	358.9	358.0	357.2	356.3
117.5°	411.9	410.7	410.1	409.4	408.8	408.1	407.2	406.3	405.2	404.1	403.1
120°	440.9	439.8	439.4	439.0	438.5	438.1	437.2	435.9	434.7	433.4	432.2
122.5°	469.7	468.9	468.3	467.8	467.2	466.7	465.9	464.9	463.8	462.8	461.7
125°	510.2	509.9	509.3	508.7	508.3	507.7	506.8	505.6	504.5	503.4	502.3
127.5°	550.2	549.7	549.0	548.4	547.6	547.0	546.1	544.9	543.8	542.7	541.5
130°	574.2	573.6	573.1	572.5	571.9	571.4	570.5	569.4	568.3	567.1	566.0
132.5°	597.2	596.6	596.1	595.7	595.3	594.8	594.0	592.9	591.7	590.6	589.5
135°	632.1	631.7	631.1	630.6	630.0	629.4	628.7	627.9	627.0	626.1	625.3
137.5°	662.8	662.1	661.8	661.5	661.2	660.9	660.1	659.1	658.0	657.0	655.9
140°	682.6	682.0	681.6	681.2	680.8	680.3	679.7	678.8	678.0	677.1	676.3
142.5°	701.3	700.9	700.4	700.0	699.6	699.2	698.5	697.7	696.8	696.0	695.1
145°	727.6	727.2	727.0	726.7	726.4	726.1	725.5	724.5	723.5	722.5	721.5
147.5°	750.9	750.6	750.3	750.0	749.7	749.5	749.0	748.4	747.7	747.1	746.4
150°	765.2	764.9	764.6	764.3	764.0	763.8	763.4	763.0	762.5	762.1	761.7
152.5°	777.6	777.1	777.0	776.7	776.6	776.4	776.2	776.1	775.8	775.7	775.4
155°	794.9	794.2	794.0	793.9	793.8	793.6	793.7	794.0	794.3	794.6	794.8
157.5°	810.0	809.1	809.3	809.4	809.5	809.7	809.8	809.8	809.8	809.8	809.8
160°	818.6	817.7	817.9	818.1	818.2	818.3	818.5	818.6	818.8	818.9	819.0
162.5°	826.4	825.4	825.6	825.7	825.8	826.0	826.2	826.6	827.0	827.4	827.7
165°	836.7	835.6	835.8	835.9	836.1	836.2	836.5	836.9	837.3	837.7	838.2
167.5°	844.9	843.8	843.8	843.8	843.8	843.8	844.1	844.7	845.2	845.8	846.4
170°	849.5	848.4	848.4	848.4	848.4	848.4	848.6	849.2	849.8	850.4	850.9
172.5°	852.6	851.4	851.3	851.2	851.1	851.0	851.3	851.9	852.6	853.3	853.9
175°	856.4	855.4	855.2	855.1	854.9	854.8	855.1	855.8	856.6	857.2	857.9
177.5°	857.9	856.9	856.8	856.7	856.6	856.5	856.7	857.3	857.9	858.4	858.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1330.7	1333.3	1342.0	1348.2	1355.4	1359.4	1363.5	1366.6	1370.7	1371.7	1386.6
5°	1336.6	1349.5	1371.9	1388.5	1409.0	1431.4	1446.8	1453.9	1472.4	1487.8	1518.6
7.5°	1335.0	1362.3	1396.1	1431.2	1468.8	1503.7	1534.0	1569.9	1595.4	1633.7	1671.5
10°	1333.4	1369.9	1413.5	1458.4	1510.9	1559.6	1603.2	1651.9	1692.2	1745.4	1790.9
12.5°	1328.8	1373.0	1433.5	1486.5	1550.4	1617.6	1682.1	1744.7	1780.5	1869.0	1910.9
15°	1317.4	1369.9	1445.5	1526.3	1614.0	1693.5	1775.6	1840.9	1946.6	2024.1	2073.5
17.5°	1295.6	1369.2	1458.9	1556.2	1663.0	1767.7	1860.7	1959.8	2072.0	2165.8	2265.7
20°	1285.4	1366.1	1466.1	1573.7	1684.6	1803.1	1908.9	2028.0	2150.4	2242.6	2370.8
22.5°	1266.4	1357.9	1465.6	1585.5	1704.1	1826.7	1950.4	2070.5	2211.9	2339.0	2461.1
25°	1235.4	1337.9	1449.4	1583.3	1722.4	1845.4	1993.4	2153.0	2300.4	2463.8	2585.5
27.5°	1202.8	1312.3	1424.0	1548.6	1698.1	1844.1	2030.3	2210.6	2390.8	2531.9	2622.0
30°	1177.7	1284.1	1399.5	1525.0	1673.0	1846.7	2054.9	2251.6	2427.2	2548.3	2598.9
32.5°	1150.6	1258.4	1360.5	1492.2	1649.9	1845.1	2070.3	2275.7	2429.3	2509.9	2500.0
35°	1107.9	1198.2	1297.5	1424.4	1610.2	1833.9	2079.3	2277.9	2372.1	2354.8	2224.1
37.5°	1046.4	1122.3	1220.2	1359.0	1564.1	1810.1	2061.3	2210.4	2204.2	2063.4	1874.0
40°	1008.0	1072.6	1166.9	1313.0	1528.2	1794.8	2033.1	2129.9	2047.9	1851.1	1624.3
42.5°	957.7	1017.2	1111.5	1261.7	1488.7	1763.5	1979.3	2007.3	1846.9	1620.5	1412.6
45°	879.8	932.3	1029.7	1184.8	1429.5	1695.4	1848.0	1779.4	1563.4	1329.6	1171.3
47.5°	796.1	850.7	944.4	1103.7	1343.9	1593.1	1665.7	1519.9	1298.2	1108.5	963.2
50°	743.3	795.8	887.5	1048.3	1286.0	1509.0	1539.1	1350.7	1147.0	980.4	861.2
52.5°	690.0	739.5	829.6	990.8	1218.4	1411.6	1393.0	1201.0	1013.7	871.7	778.1
55°	610.7	657.5	743.3	894.5	1101.5	1254.6	1187.3	1004.0	849.0	738.8	667.6
57.5°	539.6	584.5	658.6	795.2	975.1	1080.4	994.7	840.3	717.0	632.2	579.1
60°	491.5	531.2	601.7	728.6	884.9	965.0	880.4	744.0	640.1	572.2	524.8
62.5°	445.8	480.5	545.8	660.9	796.7	864.0	778.4	662.9	574.5	514.3	474.0
65°	376.7	408.1	465.9	555.5	667.0	711.9	638.2	544.6	476.1	431.2	404.3
67.5°	313.7	340.4	390.2	460.8	542.8	575.5	519.4	447.0	395.3	359.3	337.9
70°	271.7	294.7	333.9	394.7	469.0	494.0	441.5	381.9	344.1	315.3	295.4
72.5°	236.3	253.2	288.7	335.7	397.8	417.7	381.0	328.6	293.3	271.7	255.9
75°	180.0	194.1	217.2	255.0	298.0	309.5	281.9	249.2	225.5	210.2	198.0
77.5°	129.8	140.2	156.9	180.2	209.9	220.3	202.8	181.1	163.8	153.4	146.6
80°	98.0	106.4	120.5	139.7	157.6	163.4	153.1	136.5	124.3	118.5	112.8
82.5°	72.4	77.1	85.6	98.7	111.0	117.8	109.1	99.1	92.5	87.2	85.1
85°	36.5	39.1	43.0	48.0	55.8	58.3	55.1	52.5	48.7	45.5	45.5
87.5°	13.8	14.0	15.8	17.1	19.6	21.4	21.3	20.6	20.5	20.1	19.7
90°	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5
92.5°	11.5	11.1	10.7	10.3	10.8	12.1	13.5	14.9	16.3	17.2	18.1
95°	33.1	27.2	21.4	15.7	13.5	15.1	16.6	18.2	19.7	20.8	21.8
97.5°	75.6	73.0	70.4	67.8	61.3	51.1	40.9	30.7	20.5	21.7	22.8
100°	110.6	113.4	116.2	119.0	109.4	87.3	65.2	43.1	21.0	22.2	23.3
102.5°	143.4	145.4	147.5	149.5	138.5	114.4	90.2	66.0	41.9	38.4	34.9
105°	191.5	193.1	194.6	196.2	190.6	177.8	165.1	152.3	139.6	114.5	89.4
107.5°	242.5	243.7	244.9	246.1	247.8	249.8	251.8	253.8	255.8	237.5	219.1
110°	276.5	277.6	278.8	279.9	281.2	282.8	284.4	285.9	287.5	282.8	278.1



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	309.0	310.1	311.0	312.1	313.3	315.0	316.5	318.0	319.6	319.7	319.8
115°	357.2	358.0	358.9	359.7	360.8	362.1	363.3	364.6	365.9	367.3	368.7
117.5°	404.1	405.2	406.3	407.2	408.1	408.8	409.4	410.1	410.7	411.9	413.0
120°	433.4	434.7	435.9	437.2	438.1	438.5	439.0	439.4	439.8	440.9	442.1
122.5°	462.8	463.8	464.9	465.9	466.7	467.2	467.8	468.3	468.9	469.7	470.4
125°	503.4	504.5	505.6	506.8	507.7	508.3	508.7	509.3	509.9	510.2	510.5
127.5°	542.7	543.8	544.9	546.1	547.0	547.6	548.4	549.0	549.7	550.2	550.6
130°	567.1	568.3	569.4	570.5	571.4	571.9	572.5	573.1	573.6	574.2	574.8
132.5°	590.6	591.7	592.9	594.0	594.8	595.3	595.7	596.1	596.6	597.2	597.7
135°	626.1	627.0	627.9	628.7	629.4	630.0	630.6	631.1	631.7	632.1	632.5
137.5°	657.0	658.0	659.1	660.1	660.9	661.2	661.5	661.8	662.1	662.8	663.5
140°	677.1	678.0	678.8	679.7	680.3	680.8	681.2	681.6	682.0	682.6	683.1
142.5°	696.0	696.8	697.7	698.5	699.2	699.6	700.0	700.4	700.9	701.3	701.8
145°	722.5	723.5	724.5	725.5	726.1	726.4	726.7	727.0	727.2	727.6	727.8
147.5°	747.1	747.7	748.4	749.0	749.5	749.7	750.0	750.3	750.6	750.9	751.1
150°	762.1	762.5	763.0	763.4	763.8	764.0	764.3	764.6	764.9	765.2	765.4
152.5°	775.7	775.8	776.1	776.2	776.4	776.6	776.7	777.0	777.1	777.6	778.1
155°	794.6	794.3	794.0	793.7	793.6	793.8	793.9	794.0	794.2	794.9	795.7
157.5°	809.8	809.8	809.8	809.8	809.7	809.5	809.4	809.3	809.1	810.0	810.8
160°	818.9	818.8	818.6	818.5	818.3	818.2	818.1	817.9	817.7	818.6	819.5
162.5°	827.4	827.0	826.6	826.2	826.0	825.8	825.7	825.6	825.4	826.4	827.4
165°	837.7	837.3	836.9	836.5	836.2	836.1	835.9	835.8	835.6	836.7	837.9
167.5°	845.8	845.2	844.7	844.1	843.8	843.8	843.8	843.8	843.8	844.9	846.0
170°	850.4	849.8	849.2	848.6	848.4	848.4	848.4	848.4	848.4	849.5	850.6
172.5°	853.3	852.6	851.9	851.3	851.0	851.1	851.2	851.3	851.4	852.6	853.7
175°	857.2	856.6	855.8	855.1	854.8	854.9	855.1	855.2	855.4	856.4	857.4
177.5°	858.4	857.9	857.3	856.7	856.5	856.6	856.7	856.8	856.9	857.9	858.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1391.7	1392.2	1397.9	1402.0	1400.0	1402.5	1403.5
5°	1520.5	1543.6	1555.8	1564.7	1565.4	1566.0	1571.2
7.5°	1703.2	1727.9	1746.0	1773.4	1781.6	1790.9	1788.2
10°	1836.5	1872.9	1904.4	1921.0	1938.9	1965.2	1944.1
12.5°	1961.0	2025.7	2073.5	2099.4	2116.3	2121.6	2111.2
15°	2166.4	2251.0	2296.5	2295.2	2352.9	2377.9	2338.8
17.5°	2354.8	2432.9	2495.4	2527.4	2575.4	2586.1	2581.2
20°	2470.1	2555.4	2604.1	2659.2	2684.1	2706.5	2710.4
22.5°	2569.6	2646.1	2698.4	2744.2	2765.2	2775.8	2782.2
25°	2672.0	2732.2	2763.6	2779.6	2785.4	2784.1	2775.8
27.5°	2664.9	2669.5	2635.0	2601.0	2570.6	2536.4	2524.6
30°	2595.7	2541.9	2445.8	2391.4	2311.2	2247.8	2273.4
32.5°	2413.8	2306.6	2198.7	2079.7	1981.1	1953.0	1924.8
35°	2060.0	1871.7	1761.5	1633.3	1582.0	1530.8	1495.5
37.5°	1666.6	1520.9	1390.2	1306.4	1255.0	1222.5	1205.2
40°	1441.0	1309.7	1202.1	1134.2	1095.0	1058.5	1053.4
42.5°	1261.2	1139.1	1058.0	1004.0	966.4	950.9	939.6
45°	1032.9	947.7	893.2	854.8	829.8	820.2	807.4
47.5°	874.2	814.0	773.1	747.0	728.1	721.0	720.0
50°	785.5	735.6	705.5	684.9	670.3	667.6	657.5
52.5°	718.9	675.6	652.2	634.2	623.6	616.4	613.3
55°	624.1	595.3	574.1	563.9	555.5	548.5	548.5
57.5°	546.1	522.0	508.0	499.3	496.7	491.7	488.5
60°	497.9	477.4	466.5	458.8	453.6	454.3	448.5
62.5°	450.7	437.4	427.0	419.3	413.2	413.3	413.7
65°	383.8	373.6	365.9	363.3	359.5	355.0	356.3
67.5°	325.2	315.6	309.7	305.2	303.9	301.6	305.2
70°	283.2	276.1	271.7	267.8	266.5	267.2	270.4
72.5°	244.8	239.8	236.8	235.1	232.2	232.4	234.5
75°	192.2	188.4	185.8	183.9	183.3	183.3	183.3
77.5°	141.2	140.3	139.2	136.3	136.5	137.2	137.4
80°	111.5	109.6	108.9	107.6	105.7	104.4	107.6
82.5°	83.3	81.4	80.7	80.5	77.5	77.3	80.0
85°	44.8	43.0	43.5	43.0	43.0	42.3	42.3
87.5°	19.3	18.9	18.4	19.0	18.6	18.1	19.2
90°	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	19.0	20.0	20.5	20.6	20.8	21.0	21.2
95°	22.7	23.7	24.2	24.2	24.2	24.2	24.2
97.5°	23.9	25.0	25.7	25.8	26.0	26.1	26.3
100°	24.5	25.6	26.2	26.3	26.5	26.7	26.7
102.5°	31.4	27.9	26.3	26.5	26.7	27.0	27.3
105°	64.4	39.3	26.9	27.2	27.5	27.8	28.0
107.5°	200.7	182.3	163.6	144.8	125.9	107.0	88.1
110°	273.5	268.8	256.3	236.0	215.8	195.5	175.3



TEST NUMBER: P332063-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	319.8	319.9	317.8	313.6	309.2	305.0	300.8
115°	370.1	371.5	372.5	373.1	373.7	374.2	374.8
117.5°	414.2	415.2	415.9	416.0	416.1	416.2	416.4
120°	443.2	444.3	444.9	444.9	444.9	444.9	444.9
122.5°	471.2	472.1	472.5	472.6	472.7	472.9	473.0
125°	510.8	511.0	511.4	511.6	511.9	512.2	512.5
127.5°	551.1	551.5	551.5	551.3	551.1	550.7	550.5
130°	575.4	575.9	576.1	575.8	575.5	575.2	574.9
132.5°	598.3	598.8	598.9	598.6	598.2	597.8	597.4
135°	632.9	633.3	633.3	632.9	632.5	632.1	631.7
137.5°	664.1	664.9	665.0	664.8	664.5	664.2	663.9
140°	683.7	684.3	684.4	684.1	683.9	683.5	683.3
142.5°	702.2	702.7	702.7	702.3	701.9	701.6	701.2
145°	728.1	728.4	728.6	728.6	728.6	728.6	728.6
147.5°	751.5	751.7	751.5	750.9	750.2	749.6	748.9
150°	765.7	766.0	766.0	765.5	765.1	764.7	764.3
152.5°	778.6	779.2	779.1	778.4	777.8	777.1	776.5
155°	796.3	797.0	797.0	796.1	795.2	794.4	793.5
157.5°	811.6	812.5	812.4	811.3	810.2	809.1	808.0
160°	820.4	821.2	821.1	820.1	819.1	818.2	817.2
162.5°	828.3	829.2	829.3	828.4	827.5	826.7	825.8
165°	839.0	840.2	840.2	839.3	838.2	837.2	836.3
167.5°	847.2	848.3	848.3	847.2	846.0	844.9	843.8
170°	851.7	852.9	852.9	851.7	850.6	849.5	848.4
172.5°	854.8	856.0	855.9	854.7	853.5	852.2	850.9
175°	858.3	859.3	859.2	858.2	857.0	855.9	854.8
177.5°	859.7	860.5	860.5	859.3	858.2	857.0	855.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9

(END OF REPORT)