

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332080-927

Luminaire Tested: **S123DIP-S1165D1025U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332080-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1025U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6710.3 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332080-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332080-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	55	53	52	47
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44	39
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	40	37	33
4	75	64	56	50	70	60	53	47	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	25	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15588	15588	15588
5°	15662	15446	15554
10°	15557	15312	15407
15°	15375	15139	15166
20°	15163	14892	14905
25°	14878	14598	14567
30°	14564	14270	14162
35°	14236	13925	13745
40°	13893	13543	13333
45°	13516	13192	12871
50°	13137	12762	12407
55°	12643	12314	11941
60°	12144	11795	11418
65°	11703	11227	10878
70°	11053	10581	10112
75°	10098	9736	9320
80°	9106	8722	8647
85°	7991	7694	7385



TEST NUMBER: P332080-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.4	2.0
10°-20°	385.2	5.7
20°-30°	569.0	8.5
30°-40°	664.6	9.9
40°-50°	668.2	10.0
50°-60°	587.0	8.7
60°-70°	437.3	6.5
70°-80°	249.1	3.7
80°-90°	74.5	1.1
90°-100°	217.4	3.2
100°-110°	615.6	9.2
110°-120°	605.5	9.0
120°-130°	483.0	7.2
130°-140°	380.8	5.7
140°-150°	284.2	4.2
150°-160°	198.1	3.0
160°-170°	116.4	1.7
170°-180°	37.9	0.6
0°-30°	1090.6	16.3
0°-40°	1755.3	26.2
0°-60°	3010.4	44.9
0°-90°	3771.4	56.2
90°-120°	1438.5	21.4
90°-150°	2586.5	38.5
90°-180°	2939.0	43.8
0°-180°	6710.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1448	1448	1448	1448	1448	
5°	1450	1443	1430	1441	1440	137
15°	1380	1374	1358	1368	1361	389
25°	1253	1245	1229	1230	1226	577
35°	1083	1075	1060	1052	1046	677
45°	888	882	867	852	846	685
55°	674	672	656	643	636	603
65°	460	453	441	431	427	453
75°	243	238	234	228	224	260
85°	65	62	62	60	60	71
90°	2	10	20	22	23	5
95°	27	87	469	137	92	29
105°	92	136	636	1112	1006	97
115°	162	202	486	1066	1223	160
125°	225	266	454	822	965	200
135°	264	315	448	677	782	204
145°	301	345	442	556	611	189
155°	342	369	428	486	507	157
165°	374	385	410	434	442	105
175°	390	390	393	398	398	37
180°	391	391	391	391	391	



TEST NUMBER: P332080-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1453.2	1452.3	1451.4	1450.6	1449.6	1448.0	1445.6	1443.1	1440.7	1438.2	1440.4
5°	1449.5	1448.1	1446.7	1445.3	1443.9	1441.7	1438.7	1435.6	1432.6	1429.5	1432.3
7.5°	1435.3	1433.8	1432.5	1431.1	1429.7	1427.4	1424.3	1421.2	1418.0	1414.8	1417.3
10°	1423.3	1421.9	1420.5	1419.1	1417.8	1415.3	1411.7	1408.1	1404.5	1400.9	1403.4
12.5°	1407.4	1406.2	1405.0	1403.9	1402.7	1400.4	1397.1	1393.7	1390.3	1387.0	1388.8
15°	1379.7	1378.6	1377.5	1376.4	1375.3	1372.9	1369.4	1365.7	1362.2	1358.5	1360.7
17.5°	1347.6	1346.2	1344.7	1343.3	1341.8	1339.3	1335.7	1332.1	1328.5	1324.9	1326.5
20°	1323.7	1322.0	1320.3	1318.7	1317.1	1314.4	1310.8	1307.3	1303.6	1300.1	1301.2
22.5°	1296.8	1295.1	1293.5	1291.8	1290.1	1287.5	1283.9	1280.3	1276.8	1273.1	1274.0
25°	1252.7	1251.0	1249.4	1247.7	1246.1	1243.4	1239.8	1236.3	1232.6	1229.1	1229.3
27.5°	1205.6	1204.0	1202.5	1200.8	1199.2	1196.5	1192.6	1188.7	1184.9	1181.0	1181.2
30°	1171.8	1170.4	1169.0	1167.6	1166.3	1163.6	1159.8	1155.9	1152.0	1148.1	1148.1
32.5°	1137.9	1136.1	1134.2	1132.4	1130.6	1128.1	1125.2	1122.2	1119.2	1116.3	1114.7
35°	1083.4	1081.7	1080.1	1078.4	1076.7	1074.1	1070.5	1066.9	1063.3	1059.7	1058.0
37.5°	1027.5	1025.5	1023.3	1021.3	1019.1	1016.3	1012.6	1009.0	1005.4	1001.6	999.7
40°	988.7	987.1	985.4	983.7	982.1	979.3	975.4	971.5	967.7	963.8	961.6
42.5°	949.8	948.0	946.1	944.2	942.3	939.4	935.6	931.7	927.8	924.0	921.8
45°	887.9	886.8	885.7	884.6	883.4	881.1	877.5	873.9	870.3	866.6	863.4
47.5°	826.3	824.7	823.2	821.5	819.9	817.5	814.0	810.6	807.3	803.9	800.7
50°	784.5	783.2	781.7	780.4	779.0	776.5	772.9	769.3	765.6	762.1	759.1
52.5°	740.7	739.7	738.8	737.8	736.9	734.5	730.7	726.9	723.1	719.2	716.6
55°	673.7	673.4	673.1	672.9	672.6	670.7	667.0	663.5	659.8	656.2	653.2
57.5°	609.9	609.0	608.0	607.1	606.2	604.3	601.3	598.5	595.6	592.7	590.0
60°	564.1	563.8	563.6	563.2	563.0	561.2	557.9	554.5	551.2	547.9	545.4
62.5°	523.2	522.5	521.8	521.1	520.4	518.3	515.0	511.7	508.4	505.1	502.6
65°	459.5	458.1	456.7	455.3	453.9	451.9	449.1	446.3	443.5	440.8	438.6
67.5°	392.0	390.8	389.6	388.3	387.1	385.5	383.3	381.3	379.1	377.1	375.1
70°	351.2	349.5	347.8	346.2	344.5	342.9	341.2	339.5	337.9	336.2	334.3
72.5°	308.3	307.1	305.9	304.7	303.5	301.9	300.0	298.1	296.3	294.4	292.6
75°	242.8	241.7	240.6	239.5	238.4	237.4	236.6	235.8	235.0	234.1	232.7
77.5°	184.8	184.2	183.5	183.0	182.4	181.6	180.5	179.6	178.6	177.6	176.7
80°	146.9	146.1	145.3	144.4	143.6	142.9	142.4	141.8	141.2	140.7	140.5
82.5°	110.1	109.9	109.7	109.6	109.4	109.2	109.2	109.1	108.9	108.8	108.4
85°	64.7	64.2	63.6	63.1	62.5	62.3	62.3	62.3	62.3	62.3	61.7
87.5°	26.2	25.9	25.5	25.3	25.0	24.9	25.1	25.3	25.6	25.9	25.5
90°	1.6	3.2	4.8	7.1	8.7	10.3	12.7	15.1	17.4	19.8	19.0
92.5°	9.8	14.6	21.2	27.3	34.0	45.7	66.4	100.4	133.8	121.6	91.7
95°	26.9	29.2	37.9	51.4	71.9	102.8	170.0	287.8	417.5	468.9	380.3
97.5°	45.9	46.7	53.5	65.1	85.4	118.7	183.0	315.8	532.0	726.7	777.4
100°	58.5	59.3	64.9	75.9	94.9	125.7	181.1	298.1	506.0	748.8	904.6
102.5°	71.8	73.2	78.1	88.6	105.7	134.0	183.6	282.9	468.1	707.7	910.9
105°	91.7	94.1	98.9	108.4	123.3	147.9	190.6	272.0	421.4	635.7	862.7
107.5°	112.9	115.3	119.9	129.2	143.3	166.0	203.5	271.2	391.7	572.2	778.2
110°	128.1	130.5	134.4	143.1	156.5	178.7	214.3	274.4	380.3	536.1	725.1



TEST NUMBER: P332080-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.0	144.4	148.4	157.0	170.5	192.0	225.1	280.7	374.0	512.1	678.9
115°	162.1	165.2	170.0	177.9	191.4	212.7	242.7	291.0	371.6	486.3	623.1
117.5°	182.2	185.8	189.8	197.0	212.1	231.9	261.6	304.6	373.0	471.1	589.4
120°	196.1	198.4	202.4	210.3	225.4	245.1	273.6	314.7	375.6	464.1	571.7
122.5°	208.1	210.5	214.4	223.0	237.4	258.4	286.2	324.2	380.0	459.7	557.1
125°	225.4	227.0	231.7	240.3	255.4	276.8	304.4	339.2	386.7	453.9	538.5
127.5°	238.5	240.8	246.7	255.6	272.2	293.5	320.3	351.6	394.3	451.1	522.0
130°	246.7	249.1	256.2	265.7	282.3	303.6	329.7	359.8	399.3	449.2	513.2
132.5°	253.0	256.0	263.8	275.2	291.8	312.5	337.9	367.4	403.1	448.5	504.9
135°	264.1	267.3	276.0	287.8	304.4	325.7	350.3	377.2	408.8	447.6	494.2
137.5°	274.6	277.9	286.4	299.0	315.5	335.3	358.9	384.4	412.6	445.8	484.9
140°	281.5	285.4	293.3	306.0	321.9	341.6	364.6	388.2	415.1	445.2	479.2
142.5°	289.1	292.4	301.0	312.4	328.1	346.7	369.0	392.1	417.0	443.9	474.1
145°	301.3	303.6	310.8	322.7	336.0	354.3	374.8	396.2	418.3	442.0	467.3
147.5°	313.6	315.1	322.0	332.2	345.2	360.8	379.5	398.7	418.3	439.0	460.7
150°	321.9	322.7	328.9	339.2	350.3	364.6	382.7	399.3	418.3	436.5	456.2
152.5°	330.0	330.2	336.5	345.5	355.4	369.0	384.6	400.6	416.4	433.3	451.2
155°	342.4	342.4	347.1	355.1	363.8	374.8	388.2	400.9	414.3	427.8	443.6
157.5°	352.2	352.8	356.6	363.6	371.0	379.5	390.3	401.7	411.7	422.9	435.1
160°	359.8	359.8	363.0	369.2	374.8	382.7	392.2	401.7	410.4	419.1	429.4
162.5°	365.5	365.5	368.0	373.0	378.0	384.6	392.8	401.1	407.9	415.3	423.7
165°	374.0	373.2	374.8	378.7	381.9	387.5	393.8	399.3	404.1	409.6	415.9
167.5°	380.5	379.5	380.3	383.3	385.6	389.0	393.6	398.1	400.3	403.9	408.5
170°	384.3	382.7	383.5	385.9	387.5	389.0	393.0	396.2	397.8	400.1	404.1
172.5°	386.8	385.9	386.0	387.8	388.7	389.7	393.0	395.5	395.9	397.0	399.7
175°	389.8	389.0	388.2	389.8	389.8	390.6	392.2	393.8	393.0	393.0	394.6
177.5°	391.3	390.6	390.0	390.6	390.6	390.6	391.3	392.5	391.3	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P332080-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1442.6	1444.9	1447.1	1448.1	1447.9	1447.6	1447.4	1447.2
5°	1435.0	1437.8	1440.6	1441.7	1441.1	1440.6	1440.0	1439.5
7.5°	1419.8	1422.3	1424.8	1425.8	1425.5	1425.2	1424.9	1424.6
10°	1405.9	1408.3	1410.9	1411.8	1411.3	1410.7	1410.2	1409.6
12.5°	1390.6	1392.4	1394.2	1395.0	1394.6	1394.3	1394.0	1393.7
15°	1362.9	1365.2	1367.4	1367.7	1366.0	1364.4	1362.7	1361.0
17.5°	1328.0	1329.6	1331.1	1331.6	1331.0	1330.4	1329.8	1329.2
20°	1302.3	1303.4	1304.5	1304.6	1303.8	1302.9	1302.1	1301.2
22.5°	1274.9	1275.8	1276.7	1276.6	1275.6	1274.5	1273.4	1272.4
25°	1229.6	1229.9	1230.2	1229.9	1229.1	1228.2	1227.4	1226.5
27.5°	1181.5	1181.6	1181.9	1181.5	1180.4	1179.3	1178.3	1177.3
30°	1148.1	1148.1	1148.1	1147.2	1145.2	1143.3	1141.3	1139.4
32.5°	1113.1	1111.6	1110.0	1108.7	1107.7	1106.6	1105.6	1104.5
35°	1056.4	1054.7	1053.0	1051.5	1050.1	1048.8	1047.3	1046.0
37.5°	997.7	995.7	993.7	992.3	991.3	990.5	989.6	988.7
40°	959.4	957.2	955.0	953.3	952.2	951.1	950.0	948.9
42.5°	919.6	917.3	915.1	913.5	912.4	911.2	910.1	909.0
45°	860.1	856.7	853.4	851.0	849.7	848.3	846.9	845.5
47.5°	797.4	794.2	790.8	788.6	787.4	786.2	785.0	783.8
50°	756.0	753.0	749.9	747.6	745.9	744.3	742.6	740.9
52.5°	714.1	711.5	708.8	706.7	705.0	703.4	701.7	700.1
55°	650.1	647.1	644.0	641.8	640.5	639.1	637.7	636.3
57.5°	587.3	584.6	581.9	579.7	578.1	576.6	574.9	573.3
60°	543.0	540.4	538.0	536.0	534.6	533.2	531.9	530.4
62.5°	500.1	497.6	495.1	493.4	492.4	491.5	490.6	489.6
65°	436.4	434.2	432.0	430.5	429.6	428.8	427.9	427.1
67.5°	373.2	371.2	369.3	367.7	366.6	365.4	364.2	363.1
70°	332.3	330.4	328.4	326.8	325.4	324.0	322.7	321.3
72.5°	291.0	289.2	287.5	286.3	285.6	284.9	284.2	283.4
75°	231.3	230.0	228.5	227.4	226.6	225.8	225.0	224.1
77.5°	175.7	174.8	173.8	173.3	173.3	173.3	173.3	173.3
80°	140.1	139.9	139.6	139.5	139.5	139.5	139.5	139.5
82.5°	107.8	107.3	106.9	106.5	106.2	106.1	105.8	105.6
85°	61.2	60.6	60.0	59.8	59.8	59.8	59.8	59.8
87.5°	25.4	25.3	25.3	25.5	25.3	25.5	25.7	25.5
90°	19.8	20.6	21.4	22.9	22.1	22.9	23.7	22.9
92.5°	66.5	52.8	46.7	42.5	41.1	38.7	39.5	38.1
95°	284.6	193.0	151.1	122.6	107.6	100.4	94.9	91.7
97.5°	709.6	568.4	466.4	371.8	313.5	277.9	256.5	249.7
100°	932.3	868.2	775.7	663.5	583.6	525.9	495.0	495.8
102.5°	1006.3	1004.2	950.3	879.2	817.0	771.3	745.5	727.3
105°	1027.9	1107.1	1122.0	1101.5	1065.1	1035.1	1009.8	1005.8
107.5°	965.7	1094.1	1163.3	1191.5	1192.2	1182.0	1173.5	1166.2
110°	906.2	1051.7	1151.3	1206.7	1228.8	1235.2	1233.6	1232.0



TEST NUMBER: P332080-927

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	847.3	996.0	1107.6	1178.8	1219.3	1238.9	1244.9	1245.2
115°	769.4	907.0	1023.2	1109.4	1168.7	1203.5	1219.3	1223.3
117.5°	713.0	831.7	936.0	1023.5	1085.4	1125.2	1148.0	1153.3
120°	683.2	790.0	884.9	964.7	1027.1	1071.4	1090.4	1095.2
122.5°	659.8	756.5	844.4	918.5	974.1	1013.9	1034.7	1040.8
125°	628.7	714.9	790.8	854.0	904.6	939.4	959.2	964.7
127.5°	601.4	678.3	746.8	804.3	849.4	879.2	897.0	902.1
130°	584.4	655.5	719.5	773.3	815.2	843.8	860.3	866.6
132.5°	568.5	634.0	693.6	744.9	784.3	812.7	827.4	831.9
135°	547.2	603.3	654.7	699.8	738.6	762.2	776.5	782.0
137.5°	527.8	573.8	618.1	657.1	689.7	713.8	725.7	729.4
140°	516.3	556.7	594.6	628.7	658.7	680.8	693.5	692.7
142.5°	505.6	540.3	573.1	602.7	628.4	647.9	659.3	658.5
145°	492.7	518.7	544.0	567.0	586.7	603.3	609.7	611.2
147.5°	482.0	502.7	523.2	539.5	554.4	565.7	571.7	572.4
150°	474.4	492.7	509.2	524.3	536.1	544.8	549.5	549.5
152.5°	467.5	483.2	497.9	510.3	519.7	527.8	530.6	530.6
155°	457.0	469.7	481.6	491.1	498.2	504.5	506.0	506.8
157.5°	446.0	456.5	465.7	473.2	479.3	484.1	485.4	485.2
160°	439.7	448.4	456.2	461.8	467.3	472.1	472.1	471.3
162.5°	432.1	439.5	446.8	451.7	455.3	459.4	459.4	458.6
165°	422.2	427.0	432.5	436.5	439.7	442.8	442.0	442.0
167.5°	413.7	417.3	420.5	423.3	424.8	427.0	426.2	426.2
170°	408.1	410.4	413.5	415.1	415.9	417.5	416.7	416.7
172.5°	403.0	404.7	407.3	408.2	408.4	410.0	408.5	407.9
175°	396.2	397.0	398.5	398.5	398.5	399.3	398.5	397.8
177.5°	391.9	392.5	393.2	393.2	392.5	393.2	391.9	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

(END OF REPORT)