

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332071-930

Luminaire Tested: **S123DIP-S1165D805U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332071-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6249.8 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332071-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332071-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	57	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	48	44
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	41	37
4	76	65	57	51	71	61	54	49	54	48	44	48	43	39	41	38	35	32
5	70	58	50	44	65	55	47	42	49	42	38	43	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16043	16043	16043
5°	16119	15896	16008
10°	16010	15759	15856
15°	15824	15581	15610
20°	15605	15326	15340
25°	15311	15023	14992
30°	14989	14686	14574
35°	14651	14331	14146
40°	14299	13939	13722
45°	13910	13577	13247
50°	13520	13134	12769
55°	13011	12675	12288
60°	12499	12140	11752
65°	12045	11556	11196
70°	11374	10889	10408
75°	10393	10019	9590
80°	9372	8976	8901
85°	8225	7916	7608



TEST NUMBER: P332071-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	2.2
10°-20°	396.4	6.3
20°-30°	585.6	9.4
30°-40°	684.0	10.9
40°-50°	687.7	11.0
50°-60°	604.1	9.7
60°-70°	450.0	7.2
70°-80°	256.4	4.1
80°-90°	76.0	1.2
90°-100°	175.2	2.8
100°-110°	496.2	7.9
110°-120°	488.1	7.8
120°-130°	389.3	6.2
130°-140°	307.0	4.9
140°-150°	229.1	3.7
150°-160°	159.7	2.6
160°-170°	93.8	1.5
170°-180°	30.5	0.5
0°-30°	1122.4	18.0
0°-40°	1806.5	28.9
0°-60°	3098.3	49.6
0°-90°	3880.8	62.1
90°-120°	1159.6	18.6
90°-150°	2085.0	33.4
90°-180°	2369.0	37.9
0°-180°	6249.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1492	1485	1471	1483	1482	141
15°	1420	1414	1398	1407	1401	400
25°	1289	1281	1265	1266	1262	594
35°	1115	1107	1091	1083	1076	697
45°	914	908	892	877	870	705
55°	693	691	675	662	655	621
65°	473	466	454	444	440	466
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	8	16	18	18	5
95°	22	70	378	110	74	23
105°	74	109	512	896	811	79
115°	131	163	392	860	986	129
125°	182	214	366	663	778	161
135°	213	254	361	546	630	164
145°	243	278	356	448	493	152
155°	276	298	345	392	408	127
165°	302	310	330	350	356	85
175°	314	315	317	321	321	30
180°	315	315	315	315	315	



TEST NUMBER: P332071-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1495.6	1494.7	1493.8	1492.9	1491.9	1490.2	1487.8	1485.2	1482.7	1480.2	1482.5
5°	1491.8	1490.4	1488.9	1487.5	1486.0	1483.8	1480.7	1477.5	1474.4	1471.2	1474.1
7.5°	1477.2	1475.7	1474.3	1472.8	1471.5	1469.1	1465.8	1462.6	1459.4	1456.1	1458.7
10°	1464.8	1463.4	1462.0	1460.5	1459.1	1456.6	1452.9	1449.2	1445.4	1441.8	1444.3
12.5°	1448.5	1447.2	1446.0	1444.9	1443.7	1441.3	1437.9	1434.4	1430.9	1427.4	1429.3
15°	1420.0	1418.9	1417.7	1416.6	1415.4	1413.0	1409.3	1405.6	1401.9	1398.2	1400.4
17.5°	1386.9	1385.4	1384.0	1382.5	1381.0	1378.4	1374.7	1371.0	1367.3	1363.6	1365.2
20°	1362.3	1360.6	1358.9	1357.1	1355.5	1352.7	1349.1	1345.4	1341.7	1338.0	1339.1
22.5°	1334.6	1332.9	1331.2	1329.5	1327.8	1325.1	1321.4	1317.7	1314.0	1310.3	1311.2
25°	1289.2	1287.5	1285.8	1284.1	1282.5	1279.7	1276.0	1272.4	1268.6	1264.9	1265.2
27.5°	1240.8	1239.2	1237.5	1235.8	1234.2	1231.4	1227.4	1223.4	1219.4	1215.4	1215.7
30°	1206.0	1204.5	1203.1	1201.7	1200.3	1197.6	1193.6	1189.6	1185.6	1181.6	1181.6
32.5°	1171.1	1169.2	1167.3	1165.5	1163.6	1161.1	1158.1	1155.0	1151.9	1148.8	1147.2
35°	1115.0	1113.3	1111.6	1109.9	1108.2	1105.5	1101.7	1098.0	1094.3	1090.6	1088.9
37.5°	1057.5	1055.4	1053.2	1051.1	1048.9	1045.9	1042.2	1038.4	1034.7	1030.9	1028.8
40°	1017.6	1015.9	1014.2	1012.4	1010.7	1007.9	1003.9	999.9	995.9	992.0	989.7
42.5°	977.5	975.7	973.7	971.8	969.8	966.9	962.9	958.9	954.9	951.0	948.7
45°	913.8	912.6	911.5	910.4	909.2	906.8	903.1	899.4	895.7	891.9	888.6
47.5°	850.4	848.8	847.2	845.5	843.8	841.3	837.8	834.3	830.9	827.4	824.0
50°	807.4	806.0	804.5	803.2	801.7	799.2	795.4	791.7	788.0	784.3	781.2
52.5°	762.3	761.3	760.3	759.4	758.4	755.9	752.0	748.1	744.2	740.2	737.5
55°	693.3	693.1	692.8	692.5	692.2	690.2	686.5	682.8	679.1	675.4	672.3
57.5°	627.7	626.7	625.7	624.8	623.9	621.9	618.9	616.0	613.0	610.0	607.2
60°	580.6	580.2	580.0	579.7	579.4	577.6	574.1	570.7	567.3	563.9	561.3
62.5°	538.5	537.8	537.0	536.3	535.6	533.5	530.0	526.6	523.3	519.8	517.2
65°	472.9	471.5	470.0	468.6	467.2	465.0	462.2	459.3	456.5	453.7	451.4
67.5°	403.4	402.2	401.0	399.7	398.4	396.7	394.5	392.4	390.2	388.1	386.0
70°	361.4	359.7	358.0	356.3	354.6	352.9	351.1	349.4	347.7	346.0	344.1
72.5°	317.3	316.1	314.8	313.6	312.3	310.7	308.8	306.8	304.9	303.0	301.2
75°	249.9	248.7	247.6	246.5	245.3	244.3	243.5	242.6	241.8	240.9	239.5
77.5°	190.2	189.6	188.9	188.3	187.7	186.9	185.8	184.8	183.8	182.8	181.8
80°	151.2	150.3	149.5	148.6	147.8	147.1	146.5	145.9	145.4	144.8	144.6
82.5°	113.3	113.1	112.9	112.8	112.6	112.4	112.3	112.3	112.1	112.0	111.5
85°	66.6	66.0	65.5	64.9	64.3	64.1	64.1	64.1	64.1	64.1	63.5
87.5°	26.9	26.5	26.1	25.8	25.4	25.1	25.3	25.4	25.6	25.8	25.4
90°	1.3	2.5	3.8	5.7	7.0	8.3	10.2	12.1	14.0	15.9	15.3
92.5°	7.9	11.7	17.1	22.1	27.4	36.9	53.6	81.0	107.9	98.0	73.9
95°	21.7	23.6	30.6	41.4	58.0	82.8	137.1	232.0	336.6	378.0	306.6
97.5°	36.9	37.6	43.1	52.5	68.8	95.7	147.5	254.6	428.8	585.8	626.7
100°	47.2	47.8	52.3	61.2	76.5	101.3	145.9	240.3	408.0	603.6	729.2
102.5°	57.9	59.0	62.9	71.4	85.2	107.9	148.0	228.0	377.3	570.5	734.3
105°	73.9	75.8	79.7	87.3	99.5	119.2	153.6	219.2	339.7	512.5	695.5
107.5°	91.0	92.9	96.6	104.1	115.5	133.9	164.0	218.7	315.8	461.2	627.4
110°	103.3	105.2	108.4	115.4	126.2	144.1	172.8	221.2	306.6	432.2	584.5



TEST NUMBER: P332071-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	114.5	116.4	119.6	126.6	137.5	154.7	181.4	226.2	301.5	412.8	547.3
115°	130.7	133.2	137.1	143.4	154.3	171.5	195.7	234.6	299.6	392.0	502.3
117.5°	146.8	149.8	153.0	158.8	171.0	186.9	210.8	245.6	300.8	379.8	475.2
120°	158.1	160.0	163.1	169.6	181.6	197.6	220.5	253.7	302.8	374.1	460.9
122.5°	167.8	169.7	172.8	179.8	191.4	208.3	230.7	261.3	306.3	370.6	449.1
125°	181.6	183.0	186.8	193.8	205.9	223.1	245.4	273.5	311.7	365.9	434.1
127.5°	192.2	194.1	198.9	206.0	219.4	236.6	258.1	283.4	317.8	363.6	420.9
130°	198.9	200.8	206.5	214.2	227.6	244.8	265.8	290.0	321.9	362.1	413.7
132.5°	204.0	206.4	212.6	221.8	235.2	251.9	272.4	296.1	325.0	361.5	407.1
135°	212.9	215.5	222.5	232.0	245.4	262.6	282.3	304.0	329.5	360.8	398.4
137.5°	221.3	224.0	230.9	241.1	254.3	270.3	289.3	309.9	332.6	359.4	390.9
140°	226.9	230.1	236.5	246.7	259.4	275.3	293.8	313.0	334.7	358.9	386.3
142.5°	233.0	235.7	242.6	251.8	264.6	279.4	297.4	316.0	336.1	357.8	382.2
145°	242.9	244.8	250.5	260.1	270.9	285.6	302.1	319.4	337.2	356.3	376.7
147.5°	252.8	254.0	259.6	267.8	278.3	290.8	306.0	321.4	337.2	353.9	371.4
150°	259.4	260.1	265.1	273.5	282.3	293.8	308.5	321.9	337.2	351.9	367.8
152.5°	266.0	266.2	271.3	278.6	286.4	297.4	310.1	322.9	335.7	349.3	363.7
155°	276.0	276.0	279.8	286.2	293.2	302.1	313.0	323.2	334.0	344.9	357.6
157.5°	283.9	284.4	287.5	293.1	299.1	306.0	314.6	323.8	331.8	340.9	350.7
160°	290.0	290.0	292.6	297.7	302.1	308.5	316.2	323.8	330.8	337.9	346.1
162.5°	294.6	294.6	296.7	300.8	304.7	310.1	316.7	323.3	328.8	334.8	341.5
165°	301.5	300.8	302.1	305.3	307.9	312.3	317.4	321.9	325.7	330.2	335.3
167.5°	306.7	306.0	306.6	309.0	310.8	313.6	317.3	320.9	322.7	325.6	329.3
170°	309.8	308.5	309.2	311.0	312.3	313.6	316.8	319.4	320.7	322.5	325.7
172.5°	311.9	311.0	311.2	312.6	313.3	314.1	316.8	318.9	319.1	320.0	322.1
175°	314.2	313.6	313.0	314.2	314.2	314.9	316.2	317.4	316.8	316.8	318.0
177.5°	315.4	314.9	314.4	314.9	314.9	314.9	315.4	316.4	315.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332071-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1484.7	1487.0	1489.3	1490.4	1490.1	1489.9	1489.6	1489.5
5°	1476.9	1479.8	1482.6	1483.8	1483.2	1482.6	1482.1	1481.5
7.5°	1461.3	1463.8	1466.4	1467.5	1467.1	1466.8	1466.5	1466.2
10°	1446.9	1449.4	1452.0	1453.0	1452.5	1451.9	1451.3	1450.7
12.5°	1431.2	1433.1	1434.9	1435.7	1435.3	1435.0	1434.7	1434.4
15°	1402.7	1405.0	1407.3	1407.6	1405.9	1404.2	1402.5	1400.8
17.5°	1366.8	1368.4	1369.9	1370.4	1369.9	1369.2	1368.6	1368.0
20°	1340.3	1341.4	1342.6	1342.6	1341.8	1340.9	1340.1	1339.2
22.5°	1312.1	1313.0	1313.9	1313.9	1312.8	1311.7	1310.6	1309.5
25°	1265.5	1265.8	1266.1	1265.8	1264.9	1264.0	1263.2	1262.3
27.5°	1215.9	1216.1	1216.3	1215.9	1214.9	1213.7	1212.7	1211.6
30°	1181.6	1181.6	1181.6	1180.6	1178.6	1176.6	1174.6	1172.6
32.5°	1145.6	1144.0	1142.4	1141.1	1140.0	1138.9	1137.8	1136.8
35°	1087.2	1085.5	1083.8	1082.2	1080.8	1079.4	1077.9	1076.5
37.5°	1026.8	1024.7	1022.7	1021.2	1020.3	1019.4	1018.5	1017.6
40°	987.4	985.1	982.8	981.1	980.0	978.8	977.7	976.6
42.5°	946.4	944.1	941.8	940.1	939.0	937.8	936.7	935.6
45°	885.2	881.7	878.3	875.9	874.5	873.0	871.6	870.2
47.5°	820.7	817.3	813.9	811.6	810.4	809.1	807.9	806.7
50°	778.0	774.9	771.8	769.4	767.7	766.0	764.3	762.5
52.5°	734.9	732.2	729.5	727.3	725.6	723.9	722.2	720.5
55°	669.1	666.0	662.8	660.6	659.2	657.7	656.3	654.8
57.5°	604.5	601.7	598.8	596.6	595.0	593.4	591.7	590.0
60°	558.8	556.2	553.7	551.6	550.2	548.8	547.4	545.9
62.5°	514.7	512.1	509.6	507.8	506.8	505.8	504.9	503.9
65°	449.1	446.9	444.6	443.0	442.1	441.3	440.4	439.6
67.5°	384.1	382.0	380.1	378.5	377.3	376.1	374.9	373.7
70°	342.0	340.1	338.0	336.3	334.9	333.5	332.1	330.7
72.5°	299.5	297.7	295.9	294.6	293.9	293.2	292.4	291.7
75°	238.1	236.7	235.2	234.1	233.3	232.4	231.5	230.6
77.5°	180.8	179.9	178.9	178.4	178.4	178.4	178.4	178.4
80°	144.2	144.0	143.7	143.6	143.6	143.6	143.6	143.6
82.5°	111.0	110.5	110.0	109.6	109.3	109.2	108.9	108.7
85°	62.9	62.4	61.8	61.6	61.6	61.6	61.6	61.6
87.5°	25.3	25.2	25.1	25.2	25.1	25.2	25.4	25.2
90°	15.9	16.6	17.2	18.5	17.9	18.5	19.2	18.5
92.5°	53.6	42.6	37.6	34.3	33.2	31.2	31.9	30.7
95°	229.5	155.6	121.7	98.8	86.7	81.0	76.5	73.9
97.5°	572.0	458.2	375.9	299.7	252.7	224.0	206.8	201.3
100°	751.5	699.9	625.3	534.8	470.4	423.9	399.0	399.7
102.5°	811.1	809.5	766.1	708.7	658.6	621.7	601.0	586.3
105°	828.7	892.3	904.5	887.9	858.6	834.4	814.0	810.8
107.5°	778.4	881.9	937.8	960.4	961.0	952.8	945.9	940.0
110°	730.5	847.7	928.1	972.7	990.5	995.6	994.3	993.1



TEST NUMBER: P332071-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	683.1	802.9	892.9	950.2	982.9	998.7	1003.6	1003.8
115°	620.2	731.1	824.8	894.3	942.1	970.1	982.9	986.1
117.5°	574.7	670.4	754.6	825.1	874.9	907.0	925.4	929.8
120°	550.7	636.7	713.3	777.6	828.0	863.7	879.0	882.8
122.5°	531.9	609.8	680.6	740.5	785.1	817.3	834.1	838.9
125°	506.7	576.3	637.4	688.4	729.2	757.2	773.1	777.6
127.5°	484.9	546.7	602.0	648.4	684.7	708.7	723.1	727.2
130°	471.1	528.4	580.1	623.4	657.2	680.1	693.5	698.6
132.5°	458.3	511.1	559.1	600.5	632.2	655.2	667.0	670.6
135°	441.1	486.3	527.7	564.1	595.3	614.5	625.9	630.4
137.5°	425.4	462.5	498.2	529.7	556.0	575.4	585.1	588.0
140°	416.2	448.7	479.3	506.7	531.0	548.8	559.1	558.4
142.5°	407.6	435.5	462.0	485.8	506.5	522.3	531.5	530.8
145°	397.1	418.2	438.5	457.1	473.0	486.3	491.5	492.7
147.5°	388.6	405.3	421.8	434.9	446.9	456.0	460.9	461.4
150°	382.5	397.1	410.5	422.6	432.2	439.2	443.0	443.0
152.5°	376.8	389.5	401.3	411.4	418.9	425.4	427.7	427.7
155°	368.4	378.6	388.2	395.8	401.5	406.7	408.0	408.5
157.5°	359.5	368.0	375.4	381.4	386.4	390.2	391.3	391.1
160°	354.4	361.4	367.8	372.3	376.7	380.5	380.5	379.9
162.5°	348.3	354.2	360.1	364.1	367.0	370.3	370.3	369.7
165°	340.4	344.2	348.7	351.9	354.4	356.9	356.3	356.3
167.5°	333.5	336.4	339.0	341.3	342.4	344.2	343.6	343.6
170°	328.9	330.8	333.4	334.7	335.3	336.6	335.9	335.9
172.5°	324.8	326.2	328.2	329.1	329.1	330.4	329.3	328.8
175°	319.4	320.0	321.2	321.2	321.2	321.9	321.2	320.7
177.5°	315.9	316.4	316.9	316.9	316.4	316.9	315.9	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9

(END OF REPORT)