

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332083-927

Luminaire Tested: **S123DIP-S1165D1195U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332083-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7302.8 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	87	91	88	84	82	75	73	71	63	62	60	53	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13832	13832	13832	13832
5°	16495	13891	12310	13891
10°	20647	13821	11119	13821
15°	25324	13710	10351	13710
20°	30166	13536	9856	13536
25°	32033	13324	9745	13324
30°	27455	13170	9797	13170
35°	19094	12951	9900	12951
40°	14383	12694	9868	12694
45°	11942	12310	9742	12310
50°	10697	11531	9656	11531
55°	10001	10691	9533	10691
60°	9382	9810	9436	9810
65°	8818	8945	9133	8945
70°	8271	7956	8699	7956
75°	7407	6966	7977	6966
80°	6484	5709	6868	5709
85°	5076	4150	4619	4150



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	1.7
10°-20°	405.9	5.6
20°-30°	681.2	9.3
30°-40°	771.4	10.6
40°-50°	691.7	9.5
50°-60°	558.2	7.6
60°-70°	389.0	5.3
70°-80°	204.5	2.8
80°-90°	53.5	0.7
90°-100°	253.0	3.5
100°-110°	716.5	9.8
110°-120°	704.8	9.7
120°-130°	562.2	7.7
130°-140°	443.3	6.1
140°-150°	330.8	4.5
150°-160°	230.6	3.2
160°-170°	135.5	1.9
170°-180°	44.1	0.6
0°-30°	1213.7	16.6
0°-40°	1985.1	27.2
0°-60°	3235.0	44.3
0°-90°	3882.0	53.2
90°-120°	1674.3	22.9
90°-150°	3010.6	41.2
90°-180°	3421.0	46.8
0°-180°	7302.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1285	1285	1285	1285	1285	
5°	1527	1286	1139	1286	1527	158
15°	2272	1230	929	1230	2272	656
25°	2697	1122	820	1122	2697	1183
35°	1453	986	753	986	1453	944
45°	784	809	640	809	784	621
55°	533	570	508	570	533	478
65°	346	351	359	351	346	345
75°	178	168	192	168	178	191
85°	41	34	37	34	41	49
90°	27	2	27	2	27	16
95°	107	31	107	31	107	192
105°	1171	107	1171	107	1171	1155
115°	1424	189	1424	189	1424	1383
125°	1123	262	1123	262	1123	1018
135°	910	307	910	307	910	706
145°	712	351	712	351	712	452
155°	590	398	590	398	590	275
165°	514	435	514	435	514	147
175°	463	454	463	454	463	45
180°	455	455	455	455	455	



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1363.7	1362.7	1360.3	1362.2	1358.3	1352.7	1352.3	1347.3	1332.8	1331.8	1327.9
5°	1526.6	1521.6	1521.0	1520.4	1511.6	1499.8	1477.4	1475.5	1445.7	1430.7	1412.7
7.5°	1737.5	1740.1	1731.1	1723.1	1696.5	1678.9	1654.9	1624.1	1587.4	1550.1	1525.3
10°	1889.0	1909.5	1884.0	1866.5	1850.4	1819.8	1784.4	1740.1	1695.9	1644.3	1605.0
12.5°	2051.4	2061.4	2056.3	2039.9	2014.7	1968.3	1905.4	1856.7	1816.0	1730.0	1695.2
15°	2272.5	2310.5	2286.2	2230.2	2231.3	2187.1	2105.0	2014.7	1966.8	1891.4	1788.7
17.5°	2508.0	2512.8	2502.4	2455.8	2424.6	2363.9	2288.1	2201.5	2104.4	2013.3	1904.2
20°	2633.5	2629.8	2608.0	2583.8	2530.2	2482.9	2400.1	2303.6	2179.1	2089.5	1970.5
22.5°	2703.3	2697.1	2686.8	2666.4	2621.9	2571.0	2496.7	2391.3	2272.7	2149.2	2011.8
25°	2697.1	2705.1	2706.4	2700.8	2685.3	2654.8	2596.2	2512.2	2393.9	2235.1	2091.9
27.5°	2453.0	2464.5	2497.8	2527.2	2560.3	2593.8	2589.3	2547.7	2460.1	2323.0	2147.9
30°	2208.9	2184.0	2245.7	2323.5	2376.5	2469.8	2522.1	2525.2	2476.0	2358.4	2187.8
32.5°	1870.3	1897.7	1924.9	2020.7	2136.4	2241.2	2345.3	2429.1	2438.7	2360.4	2211.2
35°	1453.1	1487.4	1537.2	1587.0	1711.5	1818.6	2001.6	2161.0	2288.1	2304.9	2213.3
37.5°	1171.0	1187.9	1219.4	1269.3	1350.8	1477.8	1619.4	1820.8	2004.9	2141.7	2147.7
40°	1023.6	1028.5	1064.0	1102.0	1168.0	1272.6	1400.2	1578.3	1798.6	1989.8	2069.5
42.5°	913.0	923.9	939.0	975.5	1028.0	1106.8	1225.4	1372.5	1574.5	1794.5	1950.4
45°	784.5	796.9	806.3	830.5	867.9	920.8	1003.6	1138.1	1291.9	1519.1	1728.9
47.5°	699.6	700.5	707.5	725.8	751.2	790.9	849.5	935.9	1077.1	1261.4	1476.8
50°	638.8	648.7	651.3	665.5	685.5	714.7	763.3	836.8	952.6	1114.4	1312.4
52.5°	596.0	599.0	605.9	616.2	633.7	656.5	698.5	756.1	847.0	984.9	1167.0
55°	532.9	532.9	539.8	547.9	557.9	578.4	606.4	648.7	717.9	824.9	975.6
57.5°	474.7	477.8	482.6	485.1	493.6	507.2	530.6	562.7	614.3	696.6	816.5
60°	435.8	441.4	440.8	445.8	453.3	463.8	483.8	509.9	556.0	621.9	722.9
62.5°	402.0	401.6	401.5	407.4	414.9	425.0	437.9	460.6	499.7	558.3	644.1
65°	346.2	344.9	349.3	353.0	355.5	363.0	373.0	392.8	419.0	462.6	529.2
67.5°	296.6	293.0	295.3	296.6	300.9	306.7	316.0	328.4	349.1	384.1	434.4
70°	262.8	259.6	259.0	260.2	264.0	268.3	275.2	287.0	306.3	334.3	371.1
72.5°	227.8	225.8	225.6	228.4	230.1	233.0	237.8	248.7	264.0	285.0	319.2
75°	178.1	178.1	178.1	178.7	180.5	183.1	186.8	192.3	204.2	219.1	242.2
77.5°	133.5	133.3	132.6	132.5	135.2	136.3	137.2	142.4	149.0	159.1	175.9
80°	104.6	101.5	102.7	104.6	105.8	106.5	108.4	109.6	115.2	120.8	132.6
82.5°	77.7	75.1	75.3	78.2	78.4	79.1	81.0	82.7	84.8	89.9	96.3
85°	41.1	41.1	41.7	41.7	42.3	41.7	43.6	44.2	44.2	47.3	51.0
87.5°	20.3	19.5	19.8	20.1	19.8	19.9	20.2	20.5	20.8	21.5	21.5
90°	26.7	27.6	26.7	25.7	26.7	24.9	23.9	23.0	22.1	23.0	20.3
92.5°	44.4	46.0	45.1	47.8	49.5	54.3	61.5	77.5	106.8	141.6	155.7
95°	106.8	110.4	116.9	125.2	142.7	175.8	224.6	331.4	442.7	545.8	486.0
97.5°	290.7	298.6	323.4	364.9	432.8	542.9	661.6	825.9	904.9	845.8	619.2
100°	577.1	576.2	612.0	679.2	772.2	902.9	1010.6	1085.1	1053.0	871.6	589.1
102.5°	846.6	867.8	897.8	950.9	1023.3	1106.1	1168.9	1171.3	1060.3	823.8	544.9
105°	1170.8	1175.4	1204.8	1239.8	1282.1	1306.1	1288.6	1196.5	1004.2	740.0	490.6
107.5°	1357.4	1365.9	1375.8	1387.6	1386.9	1354.1	1273.4	1123.9	905.9	666.0	456.0
110°	1434.0	1435.8	1437.7	1430.3	1404.5	1340.1	1224.2	1054.8	844.0	624.0	442.7



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1449.5	1449.1	1442.1	1419.3	1372.1	1289.3	1159.4	986.3	790.3	596.0	435.4
115°	1423.9	1419.3	1400.8	1360.3	1291.3	1191.0	1055.7	895.6	725.2	566.0	432.6
117.5°	1342.5	1336.3	1309.7	1263.4	1191.4	1089.6	968.0	829.8	686.0	548.3	434.3
120°	1274.8	1269.2	1247.1	1195.6	1122.9	1029.9	919.5	795.2	665.4	540.3	437.2
122.5°	1211.4	1204.4	1180.1	1133.8	1069.1	982.8	880.4	767.9	648.5	535.1	442.4
125°	1122.9	1116.4	1093.4	1053.0	994.0	920.4	832.0	731.7	626.8	528.3	450.0
127.5°	1050.0	1044.1	1023.3	988.7	936.2	869.2	789.5	700.1	607.7	525.0	458.9
130°	1008.8	1001.4	982.1	949.0	900.2	837.6	763.0	680.2	597.3	522.8	464.8
132.5°	968.3	963.1	945.9	912.8	867.0	807.4	738.0	661.8	587.8	522.0	469.2
135°	910.3	903.8	887.2	859.7	814.5	762.1	702.3	636.9	575.3	520.9	475.9
137.5°	849.0	844.7	830.8	802.8	764.9	719.4	667.8	614.3	564.4	518.9	480.3
140°	806.3	807.2	792.5	766.7	731.7	692.1	647.9	601.0	557.8	518.2	483.2
142.5°	766.5	767.4	754.2	731.3	701.6	667.1	628.8	588.5	551.8	516.7	485.4
145°	711.5	709.6	702.3	682.9	659.9	633.3	603.8	573.4	544.0	514.5	486.9
147.5°	666.1	665.4	658.5	645.4	627.9	609.0	585.2	561.1	536.2	511.0	486.9
150°	639.7	639.7	634.1	624.0	610.2	592.7	573.4	552.2	531.1	508.0	486.9
152.5°	617.6	617.6	614.3	604.9	594.1	579.5	562.4	544.2	525.2	504.4	484.7
155°	589.9	589.1	587.2	579.9	571.6	560.5	546.7	532.0	516.3	498.0	482.3
157.5°	564.7	564.9	563.5	557.9	550.7	542.1	531.5	519.1	506.4	492.3	479.2
160°	548.6	549.5	549.5	544.0	537.5	531.1	521.9	511.7	499.8	487.8	477.7
162.5°	533.9	534.7	534.7	530.0	525.7	520.0	511.6	502.9	493.1	483.4	474.8
165°	514.5	514.5	515.4	511.7	508.0	503.4	497.0	491.5	484.1	476.7	470.3
167.5°	496.1	496.1	497.0	494.4	492.8	489.5	485.8	481.6	475.5	470.2	465.9
170°	485.1	485.1	486.0	484.1	483.2	481.3	477.7	474.9	470.3	465.7	463.0
172.5°	474.8	475.5	477.1	475.3	475.1	474.0	471.0	469.1	465.2	462.0	460.7
175°	463.0	463.9	464.8	463.9	463.9	463.9	462.0	461.1	459.3	457.4	457.4
177.5°	456.1	456.1	457.6	456.9	457.6	457.6	456.9	456.1	455.4	454.7	455.4
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1324.8	1320.9	1316.9	1310.0	1303.9	1295.5	1293.0	1290.0	1281.0	1273.1	1267.1
5°	1405.8	1390.8	1369.0	1349.2	1333.0	1311.2	1298.7	1285.6	1266.9	1250.1	1236.4
7.5°	1490.5	1461.1	1427.2	1390.6	1356.5	1323.7	1297.1	1273.4	1247.3	1222.5	1203.2
10°	1557.7	1515.4	1468.1	1417.1	1373.4	1331.1	1295.6	1264.5	1230.9	1201.6	1177.3
12.5°	1634.4	1571.7	1506.4	1444.4	1392.9	1334.1	1291.1	1251.6	1213.5	1178.2	1151.0
15°	1725.2	1645.5	1568.3	1483.0	1404.5	1331.1	1280.1	1230.3	1186.1	1149.9	1115.1
17.5°	1807.9	1717.6	1615.9	1512.1	1417.5	1330.4	1258.9	1202.6	1147.3	1103.1	1068.3
20°	1854.7	1752.0	1636.8	1529.1	1424.5	1327.4	1249.0	1181.7	1121.9	1075.2	1036.0
22.5°	1895.1	1774.9	1655.7	1540.6	1424.0	1319.4	1230.5	1161.3	1096.5	1050.8	1009.1
25°	1936.9	1793.1	1673.6	1538.4	1408.3	1300.0	1200.4	1121.9	1057.2	1003.6	960.7
27.5°	1972.8	1791.8	1650.0	1504.7	1383.6	1275.1	1168.7	1084.6	1015.8	957.7	914.1
30°	1996.6	1794.3	1625.6	1481.8	1359.8	1247.7	1144.3	1059.6	987.5	928.3	887.2
32.5°	2011.6	1792.8	1603.1	1449.9	1321.9	1222.7	1117.9	1030.2	956.1	897.9	858.3
35°	2020.3	1781.9	1564.6	1384.0	1260.8	1164.3	1076.5	985.6	907.8	853.6	808.7
37.5°	2002.9	1758.8	1519.7	1320.5	1185.6	1090.5	1016.7	939.2	864.7	805.2	766.5
40°	1975.5	1743.9	1484.9	1275.7	1133.8	1042.2	979.4	903.4	829.9	773.2	737.1
42.5°	1923.2	1713.5	1446.5	1225.9	1080.0	988.4	930.5	867.0	797.6	744.3	708.3
45°	1795.6	1647.3	1389.0	1151.2	1000.5	905.9	854.8	808.7	745.8	694.2	663.1
47.5°	1618.5	1547.9	1305.8	1072.4	917.6	826.6	773.5	736.4	690.5	648.7	618.9
50°	1495.5	1466.2	1249.5	1018.6	862.3	773.2	722.2	688.6	655.6	613.9	586.5
52.5°	1353.5	1371.6	1183.8	962.7	806.0	718.5	670.4	643.7	613.8	579.5	555.6
55°	1153.7	1219.0	1070.2	869.1	722.2	638.8	593.3	569.7	552.2	526.7	506.2
57.5°	966.5	1049.7	947.5	772.6	639.9	567.9	524.3	498.6	487.4	474.0	457.9
60°	855.5	937.6	859.8	707.9	584.6	516.1	477.5	455.7	444.5	435.2	421.5
62.5°	756.3	839.5	774.1	642.1	530.3	466.8	433.2	411.9	403.2	398.3	386.7
65°	620.1	691.7	648.1	539.8	452.7	396.6	366.1	351.2	343.0	341.2	333.7
67.5°	504.7	559.2	527.4	447.7	379.1	330.7	304.8	292.2	285.9	285.3	279.6
70°	429.0	480.0	455.7	383.5	324.4	286.4	264.0	252.8	249.1	248.4	245.3
72.5°	370.2	405.8	386.5	326.2	280.5	246.1	229.6	217.9	213.7	214.5	212.5
75°	273.9	300.7	289.5	247.8	211.0	188.6	174.9	167.5	163.7	165.6	163.1
77.5°	197.1	214.0	204.0	175.1	152.4	136.3	126.1	121.5	118.2	118.0	116.9
80°	148.8	158.8	153.1	135.7	117.1	103.4	95.2	92.1	90.3	89.7	89.0
82.5°	106.0	114.5	107.8	95.9	83.2	74.9	70.3	66.2	64.9	65.3	64.6
85°	53.6	56.6	54.2	46.7	41.7	37.9	35.5	33.6	32.4	33.0	31.8
87.5°	21.9	21.9	19.8	17.4	16.1	14.0	13.7	12.4	11.7	12.0	12.1
90°	17.5	14.7	12.0	10.1	8.3	5.5	3.6	1.8	3.6	5.5	8.3
92.5°	116.9	77.3	53.2	39.6	31.8	24.6	17.0	11.4	17.0	24.6	31.8
95°	335.0	197.9	119.6	83.7	59.8	44.2	34.1	31.3	34.1	44.2	59.8
97.5°	367.6	213.0	138.2	99.4	75.8	62.2	54.3	53.4	54.3	62.2	75.8
100°	347.0	210.8	146.3	110.4	88.3	75.5	69.0	68.1	69.0	75.5	88.3
102.5°	329.3	213.7	155.9	122.9	103.1	90.9	85.2	83.6	85.2	90.9	103.1
105°	316.6	221.8	172.1	143.5	126.1	115.0	109.6	106.8	109.6	115.0	126.1
107.5°	315.7	236.9	193.3	166.8	150.4	139.5	134.2	131.4	134.2	139.5	150.4
110°	319.4	249.5	208.0	182.2	166.6	156.5	151.9	149.1	151.9	156.5	166.6



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	326.8	262.0	223.5	198.4	182.8	172.7	168.1	165.3	168.1	172.7	182.8
115°	338.7	282.6	247.6	222.8	207.1	197.9	192.3	188.7	192.3	197.9	207.1
117.5°	354.5	304.4	269.9	246.8	229.3	220.9	216.3	212.1	216.3	220.9	229.3
120°	366.3	318.5	285.3	262.3	244.9	235.6	231.0	228.2	231.0	235.6	244.9
122.5°	377.4	333.2	300.8	276.3	259.5	249.6	245.0	242.2	245.0	249.6	259.5
125°	394.8	354.3	322.1	297.3	279.8	269.7	264.2	262.3	264.2	269.7	279.8
127.5°	409.2	372.7	341.7	316.8	297.5	287.2	280.4	277.6	280.4	287.2	297.5
130°	418.7	383.8	353.4	328.6	309.3	298.2	289.9	287.2	289.9	298.2	309.3
132.5°	427.6	393.4	363.8	339.6	320.3	307.0	298.0	294.5	298.0	307.0	320.3
135°	439.0	407.7	379.2	354.3	335.0	321.2	311.1	307.4	311.1	321.2	335.0
137.5°	447.5	417.6	390.2	367.3	348.1	333.4	323.4	319.6	323.4	333.4	348.1
140°	451.9	424.3	397.6	374.6	356.2	341.4	332.2	327.6	332.2	341.4	356.2
142.5°	456.3	429.4	403.5	382.0	363.5	350.3	340.4	336.5	340.4	350.3	363.5
145°	461.1	436.3	412.3	391.2	375.5	361.7	353.4	350.7	353.4	361.7	375.5
147.5°	464.1	441.8	419.9	401.9	386.7	374.8	366.7	365.0	366.7	374.8	386.7
150°	464.8	445.4	424.3	407.7	394.8	382.9	375.5	374.6	375.5	382.9	394.8
152.5°	466.3	447.7	429.4	413.6	402.2	391.7	384.4	384.2	384.4	391.7	402.2
155°	466.7	451.9	436.3	423.3	413.3	404.1	398.5	398.5	398.5	404.1	413.3
157.5°	467.5	454.3	441.8	431.8	423.2	415.1	410.7	410.0	410.7	415.1	423.2
160°	467.5	456.5	445.4	436.3	429.8	422.5	418.7	418.7	418.7	422.5	429.8
162.5°	466.8	457.2	447.7	440.0	434.3	428.3	425.4	425.4	425.4	428.3	434.3
165°	464.8	458.4	451.0	444.6	440.8	436.3	434.4	435.4	434.4	436.3	440.8
167.5°	463.3	458.2	452.8	448.8	446.2	442.7	441.8	442.9	441.8	442.7	446.2
170°	461.1	457.4	452.8	451.0	449.2	446.4	445.4	447.3	445.4	446.4	449.2
172.5°	460.4	457.4	453.6	452.5	451.4	449.3	449.2	450.3	449.2	449.3	451.4
175°	458.4	456.5	454.7	453.8	453.8	451.9	452.8	453.8	452.8	451.9	453.8
177.5°	456.9	455.4	454.7	454.7	454.7	453.9	454.7	455.4	454.7	453.9	454.7
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1263.6	1260.1	1255.1	1247.7	1241.7	1232.2	1232.2	1233.7	1233.7	1233.3	1232.2
5°	1225.3	1215.9	1204.8	1191.7	1178.0	1164.3	1161.7	1156.7	1153.0	1150.6	1147.5
7.5°	1184.8	1168.2	1151.9	1133.6	1116.9	1103.1	1093.5	1085.5	1080.5	1075.0	1071.0
10°	1157.4	1136.9	1117.5	1098.3	1077.1	1060.3	1049.7	1042.2	1036.6	1031.7	1029.1
12.5°	1125.1	1101.5	1080.2	1061.9	1038.7	1021.4	1011.4	1007.8	1001.2	990.8	985.3
15°	1077.7	1055.9	1030.4	1002.3	991.2	970.0	958.1	952.6	948.8	940.7	938.3
17.5°	1037.2	1008.7	980.1	959.2	938.3	921.1	914.6	907.6	902.6	896.0	894.1
20°	1004.9	979.4	953.2	930.8	908.9	890.3	884.7	879.7	874.7	871.6	869.1
22.5°	972.0	946.5	924.8	903.9	880.6	868.4	862.3	856.8	853.3	851.2	848.7
25°	925.8	903.4	879.1	860.4	841.8	833.6	829.9	826.8	824.3	821.2	820.5
27.5°	884.5	860.1	840.3	822.9	809.5	802.8	799.2	797.6	798.2	799.3	800.0
30°	853.6	831.2	815.0	800.0	787.6	781.3	780.7	780.7	783.2	783.9	785.1
32.5°	825.2	806.8	790.6	776.1	766.7	762.4	764.8	764.8	766.8	768.4	770.6
35°	783.9	767.6	755.2	742.8	734.7	736.5	737.8	739.0	742.1	745.8	748.4
37.5°	744.3	730.3	717.3	707.7	703.9	707.3	710.3	712.9	716.4	719.4	721.8
40°	716.0	705.4	692.9	684.2	685.5	687.4	689.8	692.9	696.1	697.9	700.4
42.5°	689.6	678.5	669.1	661.8	663.5	665.9	667.4	669.1	672.6	676.0	677.5
45°	649.4	640.6	631.9	627.6	628.8	630.1	631.3	633.2	636.3	638.8	639.4
47.5°	604.2	598.1	592.2	588.0	589.9	589.5	591.1	595.1	596.0	597.5	601.0
50°	575.3	569.7	562.8	561.6	561.6	561.6	562.2	567.2	567.2	569.7	572.2
52.5°	543.4	539.8	535.4	533.2	532.2	532.2	534.8	537.3	538.3	541.8	544.3
55°	496.2	492.5	488.7	486.9	485.6	486.9	491.9	493.1	496.2	498.0	499.9
57.5°	447.0	444.2	441.2	440.1	439.9	441.6	444.3	448.0	448.8	454.5	457.3
60°	414.6	410.3	407.8	407.8	406.5	412.2	410.9	417.2	418.4	422.2	426.5
62.5°	381.3	375.4	374.5	374.5	376.2	377.8	379.5	382.3	385.5	390.2	393.6
65°	327.5	324.4	328.8	328.1	326.9	330.6	330.6	333.7	337.5	341.8	348.6
67.5°	276.6	275.0	275.3	275.3	277.2	279.3	281.1	283.8	288.3	292.9	297.4
70°	242.2	244.1	241.0	243.4	245.3	245.9	247.2	250.9	255.9	259.0	264.0
72.5°	208.8	208.7	209.1	210.1	211.9	213.0	214.3	218.6	224.0	226.6	230.6
75°	160.7	160.0	161.8	161.8	165.0	166.2	167.5	169.4	174.4	178.1	181.2
77.5°	117.3	118.0	117.6	119.8	118.9	119.1	123.0	124.9	125.4	132.8	134.4
80°	88.4	89.7	90.3	90.9	91.5	90.3	94.7	96.5	96.5	100.8	103.9
82.5°	63.5	64.2	65.9	66.5	66.6	67.9	68.2	69.6	71.1	73.0	77.1
85°	31.8	33.6	34.2	33.6	34.2	33.0	34.9	35.5	36.1	36.1	36.1
87.5°	12.0	12.8	12.9	13.9	14.0	15.1	14.9	14.1	14.3	15.9	14.3
90°	10.1	12.0	14.7	17.5	20.3	23.0	22.1	23.0	23.9	24.9	26.7
92.5°	39.6	53.2	77.3	116.9	155.7	141.6	106.8	77.5	61.5	54.3	49.5
95°	83.7	119.6	197.9	335.0	486.0	545.8	442.7	331.4	224.6	175.8	142.7
97.5°	99.4	138.2	213.0	367.6	619.2	845.8	904.9	825.9	661.6	542.9	432.8
100°	110.4	146.3	210.8	347.0	589.1	871.6	1053.0	1085.1	1010.6	902.9	772.2
102.5°	122.9	155.9	213.7	329.3	544.9	823.8	1060.3	1171.3	1168.9	1106.1	1023.3
105°	143.5	172.1	221.8	316.6	490.6	740.0	1004.2	1196.5	1288.6	1306.1	1282.1
107.5°	166.8	193.3	236.9	315.7	456.0	666.0	905.9	1123.9	1273.4	1354.1	1386.9
110°	182.2	208.0	249.5	319.4	442.7	624.0	844.0	1054.8	1224.2	1340.1	1404.5



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	198.4	223.5	262.0	326.8	435.4	596.0	790.3	986.3	1159.4	1289.3	1372.1
115°	222.8	247.6	282.6	338.7	432.6	566.0	725.2	895.6	1055.7	1191.0	1291.3
117.5°	246.8	269.9	304.4	354.5	434.3	548.3	686.0	829.8	968.0	1089.6	1191.4
120°	262.3	285.3	318.5	366.3	437.2	540.3	665.4	795.2	919.5	1029.9	1122.9
122.5°	276.3	300.8	333.2	377.4	442.4	535.1	648.5	767.9	880.4	982.8	1069.1
125°	297.3	322.1	354.3	394.8	450.0	528.3	626.8	731.7	832.0	920.4	994.0
127.5°	316.8	341.7	372.7	409.2	458.9	525.0	607.7	700.1	789.5	869.2	936.2
130°	328.6	353.4	383.8	418.7	464.8	522.8	597.3	680.2	763.0	837.6	900.2
132.5°	339.6	363.8	393.4	427.6	469.2	522.0	587.8	661.8	738.0	807.4	867.0
135°	354.3	379.2	407.7	439.0	475.9	520.9	575.3	636.9	702.3	762.1	814.5
137.5°	367.3	390.2	417.6	447.5	480.3	518.9	564.4	614.3	667.8	719.4	764.9
140°	374.6	397.6	424.3	451.9	483.2	518.2	557.8	601.0	647.9	692.1	731.7
142.5°	382.0	403.5	429.4	456.3	485.4	516.7	551.8	588.5	628.8	667.1	701.6
145°	391.2	412.3	436.3	461.1	486.9	514.5	544.0	573.4	603.8	633.3	659.9
147.5°	401.9	419.9	441.8	464.1	486.9	511.0	536.2	561.1	585.2	609.0	627.9
150°	407.7	424.3	445.4	464.8	486.9	508.0	531.1	552.2	573.4	592.7	610.2
152.5°	413.6	429.4	447.7	466.3	484.7	504.4	525.2	544.2	562.4	579.5	594.1
155°	423.3	436.3	451.9	466.7	482.3	498.0	516.3	532.0	546.7	560.5	571.6
157.5°	431.8	441.8	454.3	467.5	479.2	492.3	506.4	519.1	531.5	542.1	550.7
160°	436.3	445.4	456.5	467.5	477.7	487.8	499.8	511.7	521.9	531.1	537.5
162.5°	440.0	447.7	457.2	466.8	474.8	483.4	493.1	502.9	511.6	520.0	525.7
165°	444.6	451.0	458.4	464.8	470.3	476.7	484.1	491.5	497.0	503.4	508.0
167.5°	448.8	452.8	458.2	463.3	465.9	470.2	475.5	481.6	485.8	489.5	492.8
170°	451.0	452.8	457.4	461.1	463.0	465.7	470.3	474.9	477.7	481.3	483.2
172.5°	452.5	453.6	457.4	460.4	460.7	462.0	465.2	469.1	471.0	474.0	475.1
175°	453.8	454.7	456.5	458.4	457.4	457.4	459.3	461.1	462.0	463.9	463.9
177.5°	454.7	454.7	455.4	456.9	455.4	454.7	455.4	456.1	456.9	457.6	457.6
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1228.8	1228.3	1231.8	1229.2	1231.8	1228.3	1228.8	1232.2	1233.3	1233.7	1233.7
5°	1143.7	1145.6	1139.3	1139.3	1139.3	1145.6	1143.7	1147.5	1150.6	1153.0	1156.7
7.5°	1068.0	1065.2	1065.5	1062.2	1065.5	1065.2	1068.0	1071.0	1075.0	1080.5	1085.5
10°	1021.7	1018.0	1016.7	1017.3	1016.7	1018.0	1021.7	1029.1	1031.7	1036.6	1042.2
12.5°	983.3	982.5	974.4	974.5	974.4	982.5	983.3	985.3	990.8	1001.2	1007.8
15°	938.3	926.5	925.2	928.9	925.2	926.5	938.3	938.3	940.7	948.8	952.6
17.5°	893.0	886.8	887.2	885.3	887.2	886.8	893.0	894.1	896.0	902.6	907.6
20°	869.1	865.4	864.7	860.4	864.7	865.4	869.1	869.1	871.6	874.7	879.7
22.5°	847.2	846.0	846.4	841.5	846.4	846.0	847.2	848.7	851.2	853.3	856.8
25°	820.0	823.1	820.5	820.5	820.5	823.1	820.0	820.5	821.2	824.3	826.8
27.5°	801.5	801.4	800.2	800.2	800.2	801.4	801.5	800.0	799.3	798.2	797.6
30°	787.6	787.0	788.2	788.2	788.2	787.0	787.6	785.1	783.9	783.2	780.7
32.5°	773.6	774.5	774.8	775.2	774.8	774.5	773.6	770.6	768.4	766.8	764.8
35°	752.1	752.7	754.6	753.4	754.6	752.7	752.1	748.4	745.8	742.1	739.0
37.5°	722.9	725.8	725.2	726.2	725.2	725.8	722.9	721.8	719.4	716.4	712.9
40°	701.0	702.9	702.3	702.3	702.3	702.9	701.0	700.4	697.9	696.1	692.9
42.5°	678.7	680.0	678.3	677.4	678.3	680.0	678.7	677.5	676.0	672.6	669.1
45°	641.9	640.6	642.5	640.0	642.5	640.6	641.9	639.4	638.8	636.3	633.2
47.5°	600.8	602.1	602.5	604.4	602.5	602.1	600.8	601.0	597.5	596.0	595.1
50°	573.4	577.1	577.1	576.6	577.1	577.1	573.4	572.2	569.7	567.2	567.2
52.5°	546.5	548.3	550.7	550.6	550.7	548.3	546.5	544.3	541.8	538.3	537.3
55°	504.9	506.2	507.4	508.0	507.4	506.2	504.9	499.9	498.0	496.2	493.1
57.5°	461.8	461.4	464.3	465.2	464.3	461.4	461.8	457.3	454.5	448.8	448.0
60°	431.4	431.4	436.4	438.3	436.4	431.4	431.4	426.5	422.2	418.4	417.2
62.5°	399.1	401.1	406.1	403.5	406.1	401.1	399.1	393.6	390.2	385.5	382.3
65°	351.7	356.7	356.1	358.6	356.1	356.7	351.7	348.6	341.8	337.5	333.7
67.5°	302.3	305.5	309.9	310.3	309.9	305.5	302.3	297.4	292.9	288.3	283.8
70°	268.9	272.0	274.6	276.4	274.6	272.0	268.9	264.0	259.0	255.9	250.9
72.5°	236.6	238.2	244.2	241.5	244.2	238.2	236.6	230.6	226.6	224.0	218.6
75°	185.5	189.9	193.6	191.8	193.6	189.9	185.5	181.2	178.1	174.4	169.4
77.5°	137.2	141.6	143.3	141.7	143.3	141.6	137.2	134.4	132.8	125.4	124.9
80°	108.4	107.7	111.5	110.8	111.5	107.7	108.4	103.9	100.8	96.5	96.5
82.5°	79.5	78.8	80.6	81.0	80.6	78.8	79.5	77.1	73.0	71.1	69.6
85°	38.6	40.5	37.9	37.4	37.9	40.5	38.6	36.1	36.1	36.1	35.5
87.5°	14.1	14.3	14.0	13.3	14.0	14.3	14.1	14.3	15.9	14.3	14.1
90°	25.7	26.7	27.6	26.7	27.6	26.7	25.7	26.7	24.9	23.9	23.0
92.5°	47.8	45.1	46.0	44.4	46.0	45.1	47.8	49.5	54.3	61.5	77.5
95°	125.2	116.9	110.4	106.8	110.4	116.9	125.2	142.7	175.8	224.6	331.4
97.5°	364.9	323.4	298.6	290.7	298.6	323.4	364.9	432.8	542.9	661.6	825.9
100°	679.2	612.0	576.2	577.1	576.2	612.0	679.2	772.2	902.9	1010.6	1085.1
102.5°	950.9	897.8	867.8	846.6	867.8	897.8	950.9	1023.3	1106.1	1168.9	1171.3
105°	1239.8	1204.8	1175.4	1170.8	1175.4	1204.8	1239.8	1282.1	1306.1	1288.6	1196.5
107.5°	1387.6	1375.8	1365.9	1357.4	1365.9	1375.8	1387.6	1386.9	1354.1	1273.4	1123.9
110°	1430.3	1437.7	1435.8	1434.0	1435.8	1437.7	1430.3	1404.5	1340.1	1224.2	1054.8



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1419.3	1442.1	1449.1	1449.5	1449.1	1442.1	1419.3	1372.1	1289.3	1159.4	986.3
115°	1360.3	1400.8	1419.3	1423.9	1419.3	1400.8	1360.3	1291.3	1191.0	1055.7	895.6
117.5°	1263.4	1309.7	1336.3	1342.5	1336.3	1309.7	1263.4	1191.4	1089.6	968.0	829.8
120°	1195.6	1247.1	1269.2	1274.8	1269.2	1247.1	1195.6	1122.9	1029.9	919.5	795.2
122.5°	1133.8	1180.1	1204.4	1211.4	1204.4	1180.1	1133.8	1069.1	982.8	880.4	767.9
125°	1053.0	1093.4	1116.4	1122.9	1116.4	1093.4	1053.0	994.0	920.4	832.0	731.7
127.5°	988.7	1023.3	1044.1	1050.0	1044.1	1023.3	988.7	936.2	869.2	789.5	700.1
130°	949.0	982.1	1001.4	1008.8	1001.4	982.1	949.0	900.2	837.6	763.0	680.2
132.5°	912.8	945.9	963.1	968.3	963.1	945.9	912.8	867.0	807.4	738.0	661.8
135°	859.7	887.2	903.8	910.3	903.8	887.2	859.7	814.5	762.1	702.3	636.9
137.5°	802.8	830.8	844.7	849.0	844.7	830.8	802.8	764.9	719.4	667.8	614.3
140°	766.7	792.5	807.2	806.3	807.2	792.5	766.7	731.7	692.1	647.9	601.0
142.5°	731.3	754.2	767.4	766.5	767.4	754.2	731.3	701.6	667.1	628.8	588.5
145°	682.9	702.3	709.6	711.5	709.6	702.3	682.9	659.9	633.3	603.8	573.4
147.5°	645.4	658.5	665.4	666.1	665.4	658.5	645.4	627.9	609.0	585.2	561.1
150°	624.0	634.1	639.7	639.7	639.7	634.1	624.0	610.2	592.7	573.4	552.2
152.5°	604.9	614.3	617.6	617.6	617.6	614.3	604.9	594.1	579.5	562.4	544.2
155°	579.9	587.2	589.1	589.9	589.1	587.2	579.9	571.6	560.5	546.7	532.0
157.5°	557.9	563.5	564.9	564.7	564.9	563.5	557.9	550.7	542.1	531.5	519.1
160°	544.0	549.5	549.5	548.6	549.5	549.5	544.0	537.5	531.1	521.9	511.7
162.5°	530.0	534.7	534.7	533.9	534.7	534.7	530.0	525.7	520.0	511.6	502.9
165°	511.7	515.4	514.5	514.5	514.5	515.4	511.7	508.0	503.4	497.0	491.5
167.5°	494.4	497.0	496.1	496.1	496.1	497.0	494.4	492.8	489.5	485.8	481.6
170°	484.1	486.0	485.1	485.1	485.1	486.0	484.1	483.2	481.3	477.7	474.9
172.5°	475.3	477.1	475.5	474.8	475.5	477.1	475.3	475.1	474.0	471.0	469.1
175°	463.9	464.8	463.9	463.0	463.9	464.8	463.9	463.9	463.9	462.0	461.1
177.5°	456.9	457.6	456.1	456.1	456.1	457.6	456.9	457.6	457.6	456.9	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1232.2	1232.2	1241.7	1247.7	1255.1	1260.1	1263.6	1267.1	1273.1	1281.0	1290.0
5°	1161.7	1164.3	1178.0	1191.7	1204.8	1215.9	1225.3	1236.4	1250.1	1266.9	1285.6
7.5°	1093.5	1103.1	1116.9	1133.6	1151.9	1168.2	1184.8	1203.2	1222.5	1247.3	1273.4
10°	1049.7	1060.3	1077.1	1098.3	1117.5	1136.9	1157.4	1177.3	1201.6	1230.9	1264.5
12.5°	1011.4	1021.4	1038.7	1061.9	1080.2	1101.5	1125.1	1151.0	1178.2	1213.5	1251.6
15°	958.1	970.0	991.2	1002.3	1030.4	1055.9	1077.7	1115.1	1149.9	1186.1	1230.3
17.5°	914.6	921.1	938.3	959.2	980.1	1008.7	1037.2	1068.3	1103.1	1147.3	1202.6
20°	884.7	890.3	908.9	930.8	953.2	979.4	1004.9	1036.0	1075.2	1121.9	1181.7
22.5°	862.3	868.4	880.6	903.9	924.8	946.5	972.0	1009.1	1050.8	1096.5	1161.3
25°	829.9	833.6	841.8	860.4	879.1	903.4	925.8	960.7	1003.6	1057.2	1121.9
27.5°	799.2	802.8	809.5	822.9	840.3	860.1	884.5	914.1	957.7	1015.8	1084.6
30°	780.7	781.3	787.6	800.0	815.0	831.2	853.6	887.2	928.3	987.5	1059.6
32.5°	764.8	762.4	766.7	776.1	790.6	806.8	825.2	858.3	897.9	956.1	1030.2
35°	737.8	736.5	734.7	742.8	755.2	767.6	783.9	808.7	853.6	907.8	985.6
37.5°	710.3	707.3	703.9	707.7	717.3	730.3	744.3	766.5	805.2	864.7	939.2
40°	689.8	687.4	685.5	684.2	692.9	705.4	716.0	737.1	773.2	829.9	903.4
42.5°	667.4	665.9	663.5	661.8	669.1	678.5	689.6	708.3	744.3	797.6	867.0
45°	631.3	630.1	628.8	627.6	631.9	640.6	649.4	663.1	694.2	745.8	808.7
47.5°	591.1	589.5	589.9	588.0	592.2	598.1	604.2	618.9	648.7	690.5	736.4
50°	562.2	561.6	561.6	561.6	562.8	569.7	575.3	586.5	613.9	655.6	688.6
52.5°	534.8	532.2	532.2	533.2	535.4	539.8	543.4	555.6	579.5	613.8	643.7
55°	491.9	486.9	485.6	486.9	488.7	492.5	496.2	506.2	526.7	552.2	569.7
57.5°	444.3	441.6	439.9	440.1	441.2	444.2	447.0	457.9	474.0	487.4	498.6
60°	410.9	412.2	406.5	407.8	407.8	410.3	414.6	421.5	435.2	444.5	455.7
62.5°	379.5	377.8	376.2	374.5	374.5	375.4	381.3	386.7	398.3	403.2	411.9
65°	330.6	330.6	326.9	328.1	328.8	324.4	327.5	333.7	341.2	343.0	351.2
67.5°	281.1	279.3	277.2	275.3	275.3	275.0	276.6	279.6	285.3	285.9	292.2
70°	247.2	245.9	245.3	243.4	241.0	244.1	242.2	245.3	248.4	249.1	252.8
72.5°	214.3	213.0	211.9	210.1	209.1	208.7	208.8	212.5	214.5	213.7	217.9
75°	167.5	166.2	165.0	161.8	161.8	160.0	160.7	163.1	165.6	163.7	167.5
77.5°	123.0	119.1	118.9	119.8	117.6	118.0	117.3	116.9	118.0	118.2	121.5
80°	94.7	90.3	91.5	90.9	90.3	89.7	88.4	89.0	89.7	90.3	92.1
82.5°	68.2	67.9	66.6	66.5	65.9	64.2	63.5	64.6	65.3	64.9	66.2
85°	34.9	33.0	34.2	33.6	34.2	33.6	31.8	31.8	33.0	32.4	33.6
87.5°	14.9	15.1	14.0	13.9	12.9	12.8	12.0	12.1	12.0	11.7	12.4
90°	22.1	23.0	20.3	17.5	14.7	12.0	10.1	8.3	5.5	3.6	1.8
92.5°	106.8	141.6	155.7	116.9	77.3	53.2	39.6	31.8	24.6	17.0	11.4
95°	442.7	545.8	486.0	335.0	197.9	119.6	83.7	59.8	44.2	34.1	31.3
97.5°	904.9	845.8	619.2	367.6	213.0	138.2	99.4	75.8	62.2	54.3	53.4
100°	1053.0	871.6	589.1	347.0	210.8	146.3	110.4	88.3	75.5	69.0	68.1
102.5°	1060.3	823.8	544.9	329.3	213.7	155.9	122.9	103.1	90.9	85.2	83.6
105°	1004.2	740.0	490.6	316.6	221.8	172.1	143.5	126.1	115.0	109.6	106.8
107.5°	905.9	666.0	456.0	315.7	236.9	193.3	166.8	150.4	139.5	134.2	131.4
110°	844.0	624.0	442.7	319.4	249.5	208.0	182.2	166.6	156.5	151.9	149.1



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	790.3	596.0	435.4	326.8	262.0	223.5	198.4	182.8	172.7	168.1	165.3
115°	725.2	566.0	432.6	338.7	282.6	247.6	222.8	207.1	197.9	192.3	188.7
117.5°	686.0	548.3	434.3	354.5	304.4	269.9	246.8	229.3	220.9	216.3	212.1
120°	665.4	540.3	437.2	366.3	318.5	285.3	262.3	244.9	235.6	231.0	228.2
122.5°	648.5	535.1	442.4	377.4	333.2	300.8	276.3	259.5	249.6	245.0	242.2
125°	626.8	528.3	450.0	394.8	354.3	322.1	297.3	279.8	269.7	264.2	262.3
127.5°	607.7	525.0	458.9	409.2	372.7	341.7	316.8	297.5	287.2	280.4	277.6
130°	597.3	522.8	464.8	418.7	383.8	353.4	328.6	309.3	298.2	289.9	287.2
132.5°	587.8	522.0	469.2	427.6	393.4	363.8	339.6	320.3	307.0	298.0	294.5
135°	575.3	520.9	475.9	439.0	407.7	379.2	354.3	335.0	321.2	311.1	307.4
137.5°	564.4	518.9	480.3	447.5	417.6	390.2	367.3	348.1	333.4	323.4	319.6
140°	557.8	518.2	483.2	451.9	424.3	397.6	374.6	356.2	341.4	332.2	327.6
142.5°	551.8	516.7	485.4	456.3	429.4	403.5	382.0	363.5	350.3	340.4	336.5
145°	544.0	514.5	486.9	461.1	436.3	412.3	391.2	375.5	361.7	353.4	350.7
147.5°	536.2	511.0	486.9	464.1	441.8	419.9	401.9	386.7	374.8	366.7	365.0
150°	531.1	508.0	486.9	464.8	445.4	424.3	407.7	394.8	382.9	375.5	374.6
152.5°	525.2	504.4	484.7	466.3	447.7	429.4	413.6	402.2	391.7	384.4	384.2
155°	516.3	498.0	482.3	466.7	451.9	436.3	423.3	413.3	404.1	398.5	398.5
157.5°	506.4	492.3	479.2	467.5	454.3	441.8	431.8	423.2	415.1	410.7	410.0
160°	499.8	487.8	477.7	467.5	456.5	445.4	436.3	429.8	422.5	418.7	418.7
162.5°	493.1	483.4	474.8	466.8	457.2	447.7	440.0	434.3	428.3	425.4	425.4
165°	484.1	476.7	470.3	464.8	458.4	451.0	444.6	440.8	436.3	434.4	435.4
167.5°	475.5	470.2	465.9	463.3	458.2	452.8	448.8	446.2	442.7	441.8	442.9
170°	470.3	465.7	463.0	461.1	457.4	452.8	451.0	449.2	446.4	445.4	447.3
172.5°	465.2	462.0	460.7	460.4	457.4	453.6	452.5	451.4	449.3	449.2	450.3
175°	459.3	457.4	457.4	458.4	456.5	454.7	453.8	453.8	451.9	452.8	453.8
177.5°	455.4	454.7	455.4	456.9	455.4	454.7	454.7	454.7	453.9	454.7	455.4
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1293.0	1295.5	1303.9	1310.0	1316.9	1320.9	1324.8	1327.9	1331.8	1332.8	1347.3
5°	1298.7	1311.2	1333.0	1349.2	1369.0	1390.8	1405.8	1412.7	1430.7	1445.7	1475.5
7.5°	1297.1	1323.7	1356.5	1390.6	1427.2	1461.1	1490.5	1525.3	1550.1	1587.4	1624.1
10°	1295.6	1331.1	1373.4	1417.1	1468.1	1515.4	1557.7	1605.0	1644.3	1695.9	1740.1
12.5°	1291.1	1334.1	1392.9	1444.4	1506.4	1571.7	1634.4	1695.2	1730.0	1816.0	1856.7
15°	1280.1	1331.1	1404.5	1483.0	1568.3	1645.5	1725.2	1788.7	1891.4	1966.8	2014.7
17.5°	1258.9	1330.4	1417.5	1512.1	1615.9	1717.6	1807.9	1904.2	2013.3	2104.4	2201.5
20°	1249.0	1327.4	1424.5	1529.1	1636.8	1752.0	1854.7	1970.5	2089.5	2179.1	2303.6
22.5°	1230.5	1319.4	1424.0	1540.6	1655.7	1774.9	1895.1	2011.8	2149.2	2272.7	2391.3
25°	1200.4	1300.0	1408.3	1538.4	1673.6	1793.1	1936.9	2091.9	2235.1	2393.9	2512.2
27.5°	1168.7	1275.1	1383.6	1504.7	1650.0	1791.8	1972.8	2147.9	2323.0	2460.1	2547.7
30°	1144.3	1247.7	1359.8	1481.8	1625.6	1794.3	1996.6	2187.8	2358.4	2476.0	2525.2
32.5°	1117.9	1222.7	1321.9	1449.9	1603.1	1792.8	2011.6	2211.2	2360.4	2438.7	2429.1
35°	1076.5	1164.3	1260.8	1384.0	1564.6	1781.9	2020.3	2213.3	2304.9	2288.1	2161.0
37.5°	1016.7	1090.5	1185.6	1320.5	1519.7	1758.8	2002.9	2147.7	2141.7	2004.9	1820.8
40°	979.4	1042.2	1133.8	1275.7	1484.9	1743.9	1975.5	2069.5	1989.8	1798.6	1578.3
42.5°	930.5	988.4	1080.0	1225.9	1446.5	1713.5	1923.2	1950.4	1794.5	1574.5	1372.5
45°	854.8	905.9	1000.5	1151.2	1389.0	1647.3	1795.6	1728.9	1519.1	1291.9	1138.1
47.5°	773.5	826.6	917.6	1072.4	1305.8	1547.9	1618.5	1476.8	1261.4	1077.1	935.9
50°	722.2	773.2	862.3	1018.6	1249.5	1466.2	1495.5	1312.4	1114.4	952.6	836.8
52.5°	670.4	718.5	806.0	962.7	1183.8	1371.6	1353.5	1167.0	984.9	847.0	756.1
55°	593.3	638.8	722.2	869.1	1070.2	1219.0	1153.7	975.6	824.9	717.9	648.7
57.5°	524.3	567.9	639.9	772.6	947.5	1049.7	966.5	816.5	696.6	614.3	562.7
60°	477.5	516.1	584.6	707.9	859.8	937.6	855.5	722.9	621.9	556.0	509.9
62.5°	433.2	466.8	530.3	642.1	774.1	839.5	756.3	644.1	558.3	499.7	460.6
65°	366.1	396.6	452.7	539.8	648.1	691.7	620.1	529.2	462.6	419.0	392.8
67.5°	304.8	330.7	379.1	447.7	527.4	559.2	504.7	434.4	384.1	349.1	328.4
70°	264.0	286.4	324.4	383.5	455.7	480.0	429.0	371.1	334.3	306.3	287.0
72.5°	229.6	246.1	280.5	326.2	386.5	405.8	370.2	319.2	285.0	264.0	248.7
75°	174.9	188.6	211.0	247.8	289.5	300.7	273.9	242.2	219.1	204.2	192.3
77.5°	126.1	136.3	152.4	175.1	204.0	214.0	197.1	175.9	159.1	149.0	142.4
80°	95.2	103.4	117.1	135.7	153.1	158.8	148.8	132.6	120.8	115.2	109.6
82.5°	70.3	74.9	83.2	95.9	107.8	114.5	106.0	96.3	89.9	84.8	82.7
85°	35.5	37.9	41.7	46.7	54.2	56.6	53.6	51.0	47.3	44.2	44.2
87.5°	13.7	14.0	16.1	17.4	19.8	21.9	21.9	21.5	21.5	20.8	20.5
90°	3.6	5.5	8.3	10.1	12.0	14.7	17.5	20.3	23.0	22.1	23.0
92.5°	17.0	24.6	31.8	39.6	53.2	77.3	116.9	155.7	141.6	106.8	77.5
95°	34.1	44.2	59.8	83.7	119.6	197.9	335.0	486.0	545.8	442.7	331.4
97.5°	54.3	62.2	75.8	99.4	138.2	213.0	367.6	619.2	845.8	904.9	825.9
100°	69.0	75.5	88.3	110.4	146.3	210.8	347.0	589.1	871.6	1053.0	1085.1
102.5°	85.2	90.9	103.1	122.9	155.9	213.7	329.3	544.9	823.8	1060.3	1171.3
105°	109.6	115.0	126.1	143.5	172.1	221.8	316.6	490.6	740.0	1004.2	1196.5
107.5°	134.2	139.5	150.4	166.8	193.3	236.9	315.7	456.0	666.0	905.9	1123.9
110°	151.9	156.5	166.6	182.2	208.0	249.5	319.4	442.7	624.0	844.0	1054.8



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.1	172.7	182.8	198.4	223.5	262.0	326.8	435.4	596.0	790.3	986.3
115°	192.3	197.9	207.1	222.8	247.6	282.6	338.7	432.6	566.0	725.2	895.6
117.5°	216.3	220.9	229.3	246.8	269.9	304.4	354.5	434.3	548.3	686.0	829.8
120°	231.0	235.6	244.9	262.3	285.3	318.5	366.3	437.2	540.3	665.4	795.2
122.5°	245.0	249.6	259.5	276.3	300.8	333.2	377.4	442.4	535.1	648.5	767.9
125°	264.2	269.7	279.8	297.3	322.1	354.3	394.8	450.0	528.3	626.8	731.7
127.5°	280.4	287.2	297.5	316.8	341.7	372.7	409.2	458.9	525.0	607.7	700.1
130°	289.9	298.2	309.3	328.6	353.4	383.8	418.7	464.8	522.8	597.3	680.2
132.5°	298.0	307.0	320.3	339.6	363.8	393.4	427.6	469.2	522.0	587.8	661.8
135°	311.1	321.2	335.0	354.3	379.2	407.7	439.0	475.9	520.9	575.3	636.9
137.5°	323.4	333.4	348.1	367.3	390.2	417.6	447.5	480.3	518.9	564.4	614.3
140°	332.2	341.4	356.2	374.6	397.6	424.3	451.9	483.2	518.2	557.8	601.0
142.5°	340.4	350.3	363.5	382.0	403.5	429.4	456.3	485.4	516.7	551.8	588.5
145°	353.4	361.7	375.5	391.2	412.3	436.3	461.1	486.9	514.5	544.0	573.4
147.5°	366.7	374.8	386.7	401.9	419.9	441.8	464.1	486.9	511.0	536.2	561.1
150°	375.5	382.9	394.8	407.7	424.3	445.4	464.8	486.9	508.0	531.1	552.2
152.5°	384.4	391.7	402.2	413.6	429.4	447.7	466.3	484.7	504.4	525.2	544.2
155°	398.5	404.1	413.3	423.3	436.3	451.9	466.7	482.3	498.0	516.3	532.0
157.5°	410.7	415.1	423.2	431.8	441.8	454.3	467.5	479.2	492.3	506.4	519.1
160°	418.7	422.5	429.8	436.3	445.4	456.5	467.5	477.7	487.8	499.8	511.7
162.5°	425.4	428.3	434.3	440.0	447.7	457.2	466.8	474.8	483.4	493.1	502.9
165°	434.4	436.3	440.8	444.6	451.0	458.4	464.8	470.3	476.7	484.1	491.5
167.5°	441.8	442.7	446.2	448.8	452.8	458.2	463.3	465.9	470.2	475.5	481.6
170°	445.4	446.4	449.2	451.0	452.8	457.4	461.1	463.0	465.7	470.3	474.9
172.5°	449.2	449.3	451.4	452.5	453.6	457.4	460.4	460.7	462.0	465.2	469.1
175°	452.8	451.9	453.8	453.8	454.7	456.5	458.4	457.4	457.4	459.3	461.1
177.5°	454.7	453.9	454.7	454.7	454.7	455.4	456.9	455.4	454.7	455.4	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1352.3	1352.7	1358.3	1362.2	1360.3	1362.7	1363.7
5°	1477.4	1499.8	1511.6	1520.4	1521.0	1521.6	1526.6
7.5°	1654.9	1678.9	1696.5	1723.1	1731.1	1740.1	1737.5
10°	1784.4	1819.8	1850.4	1866.5	1884.0	1909.5	1889.0
12.5°	1905.4	1968.3	2014.7	2039.9	2056.3	2061.4	2051.4
15°	2105.0	2187.1	2231.3	2230.2	2286.2	2310.5	2272.5
17.5°	2288.1	2363.9	2424.6	2455.8	2502.4	2512.8	2508.0
20°	2400.1	2482.9	2530.2	2583.8	2608.0	2629.8	2633.5
22.5°	2496.7	2571.0	2621.9	2666.4	2686.8	2697.1	2703.3
25°	2596.2	2654.8	2685.3	2700.8	2706.4	2705.1	2697.1
27.5°	2589.3	2593.8	2560.3	2527.2	2497.8	2464.5	2453.0
30°	2522.1	2469.8	2376.5	2323.5	2245.7	2184.0	2208.9
32.5°	2345.3	2241.2	2136.4	2020.7	1924.9	1897.7	1870.3
35°	2001.6	1818.6	1711.5	1587.0	1537.2	1487.4	1453.1
37.5°	1619.4	1477.8	1350.8	1269.3	1219.4	1187.9	1171.0
40°	1400.2	1272.6	1168.0	1102.0	1064.0	1028.5	1023.6
42.5°	1225.4	1106.8	1028.0	975.5	939.0	923.9	913.0
45°	1003.6	920.8	867.9	830.5	806.3	796.9	784.5
47.5°	849.5	790.9	751.2	725.8	707.5	700.5	699.6
50°	763.3	714.7	685.5	665.5	651.3	648.7	638.8
52.5°	698.5	656.5	633.7	616.2	605.9	599.0	596.0
55°	606.4	578.4	557.9	547.9	539.8	532.9	532.9
57.5°	530.6	507.2	493.6	485.1	482.6	477.8	474.7
60°	483.8	463.8	453.3	445.8	440.8	441.4	435.8
62.5°	437.9	425.0	414.9	407.4	401.5	401.6	402.0
65°	373.0	363.0	355.5	353.0	349.3	344.9	346.2
67.5°	316.0	306.7	300.9	296.6	295.3	293.0	296.6
70°	275.2	268.3	264.0	260.2	259.0	259.6	262.8
72.5°	237.8	233.0	230.1	228.4	225.6	225.8	227.8
75°	186.8	183.1	180.5	178.7	178.1	178.1	178.1
77.5°	137.2	136.3	135.2	132.5	132.6	133.3	133.5
80°	108.4	106.5	105.8	104.6	102.7	101.5	104.6
82.5°	81.0	79.1	78.4	78.2	75.3	75.1	77.7
85°	43.6	41.7	42.3	41.7	41.7	41.1	41.1
87.5°	20.2	19.9	19.8	20.1	19.8	19.5	20.3
90°	23.9	24.9	26.7	25.7	26.7	27.6	26.7
92.5°	61.5	54.3	49.5	47.8	45.1	46.0	44.4
95°	224.6	175.8	142.7	125.2	116.9	110.4	106.8
97.5°	661.6	542.9	432.8	364.9	323.4	298.6	290.7
100°	1010.6	902.9	772.2	679.2	612.0	576.2	577.1
102.5°	1168.9	1106.1	1023.3	950.9	897.8	867.8	846.6
105°	1288.6	1306.1	1282.1	1239.8	1204.8	1175.4	1170.8
107.5°	1273.4	1354.1	1386.9	1387.6	1375.8	1365.9	1357.4
110°	1224.2	1340.1	1404.5	1430.3	1437.7	1435.8	1434.0



TEST NUMBER: P332083-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1159.4	1289.3	1372.1	1419.3	1442.1	1449.1	1449.5
115°	1055.7	1191.0	1291.3	1360.3	1400.8	1419.3	1423.9
117.5°	968.0	1089.6	1191.4	1263.4	1309.7	1336.3	1342.5
120°	919.5	1029.9	1122.9	1195.6	1247.1	1269.2	1274.8
122.5°	880.4	982.8	1069.1	1133.8	1180.1	1204.4	1211.4
125°	832.0	920.4	994.0	1053.0	1093.4	1116.4	1122.9
127.5°	789.5	869.2	936.2	988.7	1023.3	1044.1	1050.0
130°	763.0	837.6	900.2	949.0	982.1	1001.4	1008.8
132.5°	738.0	807.4	867.0	912.8	945.9	963.1	968.3
135°	702.3	762.1	814.5	859.7	887.2	903.8	910.3
137.5°	667.8	719.4	764.9	802.8	830.8	844.7	849.0
140°	647.9	692.1	731.7	766.7	792.5	807.2	806.3
142.5°	628.8	667.1	701.6	731.3	754.2	767.4	766.5
145°	603.8	633.3	659.9	682.9	702.3	709.6	711.5
147.5°	585.2	609.0	627.9	645.4	658.5	665.4	666.1
150°	573.4	592.7	610.2	624.0	634.1	639.7	639.7
152.5°	562.4	579.5	594.1	604.9	614.3	617.6	617.6
155°	546.7	560.5	571.6	579.9	587.2	589.1	589.9
157.5°	531.5	542.1	550.7	557.9	563.5	564.9	564.7
160°	521.9	531.1	537.5	544.0	549.5	549.5	548.6
162.5°	511.6	520.0	525.7	530.0	534.7	534.7	533.9
165°	497.0	503.4	508.0	511.7	515.4	514.5	514.5
167.5°	485.8	489.5	492.8	494.4	497.0	496.1	496.1
170°	477.7	481.3	483.2	484.1	486.0	485.1	485.1
172.5°	471.0	474.0	475.1	475.3	477.1	475.5	474.8
175°	462.0	463.9	463.9	463.9	464.8	463.9	463.0
177.5°	456.9	457.6	457.6	456.9	457.6	456.1	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7

(END OF REPORT)