

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332089-927

Luminaire Tested: **S123DIP-S1165D1195U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332089-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7192.7 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332089-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332089-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	51	50	49	44
2	89	82	76	71	82	76	71	66	65	61	57	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30	27
5	68	57	49	43	63	53	46	40	46	40	35	39	34	31	32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	18	16
9	50	38	31	25	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15588	15588	15588
5°	15662	15446	15554
10°	15557	15312	15407
15°	15375	15139	15166
20°	15163	14892	14905
25°	14878	14598	14567
30°	14564	14270	14162
35°	14236	13925	13745
40°	13893	13543	13333
45°	13516	13192	12871
50°	13137	12762	12407
55°	12643	12314	11941
60°	12144	11795	11418
65°	11703	11227	10878
70°	11053	10581	10112
75°	10098	9736	9320
80°	9106	8722	8647
85°	7991	7694	7385



TEST NUMBER: P332089-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.4	1.9
10°-20°	385.2	5.4
20°-30°	569.0	7.9
30°-40°	664.6	9.2
40°-50°	668.2	9.3
50°-60°	587.0	8.2
60°-70°	437.3	6.1
70°-80°	249.1	3.5
80°-90°	75.0	1.0
90°-100°	253.0	3.5
100°-110°	716.5	10.0
110°-120°	704.8	9.8
120°-130°	562.2	7.8
130°-140°	443.3	6.2
140°-150°	330.8	4.6
150°-160°	230.6	3.2
160°-170°	135.5	1.9
170°-180°	44.1	0.6
0°-30°	1090.6	15.2
0°-40°	1755.3	24.4
0°-60°	3010.4	41.9
0°-90°	3771.9	52.4
90°-120°	1674.3	23.3
90°-150°	3010.6	41.9
90°-180°	3421.0	47.6
0°-180°	7192.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1448	1448	1448	1448	1448	
5°	1450	1443	1430	1441	1440	137
15°	1380	1374	1358	1368	1361	389
25°	1253	1245	1229	1230	1226	577
35°	1083	1075	1060	1052	1046	677
45°	888	882	867	852	846	685
55°	674	672	656	643	636	603
65°	460	453	441	431	427	453
75°	243	238	234	228	224	260
85°	65	62	62	60	60	71
90°	2	11	23	26	27	6
95°	31	102	546	159	107	34
105°	107	158	740	1294	1171	113
115°	189	235	566	1241	1424	187
125°	262	310	528	957	1123	233
135°	307	367	521	788	910	237
145°	351	402	514	647	712	220
155°	398	430	498	566	590	183
165°	435	448	477	506	514	123
175°	454	454	457	464	463	43
180°	455	455	455	455	455	



TEST NUMBER: P332089-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1453.2	1452.3	1451.4	1450.6	1449.6	1448.0	1445.6	1443.1	1440.7	1438.2	1440.4
5°	1449.5	1448.1	1446.7	1445.3	1443.9	1441.7	1438.7	1435.6	1432.6	1429.5	1432.3
7.5°	1435.3	1433.8	1432.5	1431.1	1429.7	1427.4	1424.3	1421.2	1418.0	1414.8	1417.3
10°	1423.3	1421.9	1420.5	1419.1	1417.8	1415.3	1411.7	1408.1	1404.5	1400.9	1403.4
12.5°	1407.4	1406.2	1405.0	1403.9	1402.7	1400.4	1397.1	1393.7	1390.3	1387.0	1388.8
15°	1379.7	1378.6	1377.5	1376.4	1375.3	1372.9	1369.4	1365.7	1362.2	1358.5	1360.7
17.5°	1347.6	1346.2	1344.7	1343.3	1341.8	1339.3	1335.7	1332.1	1328.5	1324.9	1326.5
20°	1323.7	1322.0	1320.3	1318.7	1317.1	1314.4	1310.8	1307.3	1303.6	1300.1	1301.2
22.5°	1296.8	1295.1	1293.5	1291.8	1290.1	1287.5	1283.9	1280.3	1276.8	1273.1	1274.0
25°	1252.7	1251.0	1249.4	1247.7	1246.1	1243.4	1239.8	1236.3	1232.6	1229.1	1229.3
27.5°	1205.6	1204.0	1202.5	1200.8	1199.2	1196.5	1192.6	1188.7	1184.9	1181.0	1181.2
30°	1171.8	1170.4	1169.0	1167.6	1166.3	1163.6	1159.8	1155.9	1152.0	1148.1	1148.1
32.5°	1137.9	1136.1	1134.2	1132.4	1130.6	1128.1	1125.2	1122.2	1119.2	1116.3	1114.7
35°	1083.4	1081.7	1080.1	1078.4	1076.7	1074.1	1070.5	1066.9	1063.3	1059.7	1058.0
37.5°	1027.5	1025.5	1023.3	1021.3	1019.1	1016.3	1012.6	1009.0	1005.4	1001.6	999.7
40°	988.7	987.1	985.4	983.7	982.1	979.3	975.4	971.5	967.7	963.8	961.6
42.5°	949.8	948.0	946.1	944.2	942.3	939.4	935.6	931.7	927.8	924.0	921.8
45°	887.9	886.8	885.7	884.6	883.4	881.1	877.5	873.9	870.3	866.6	863.4
47.5°	826.3	824.7	823.2	821.5	819.9	817.5	814.0	810.6	807.3	803.9	800.7
50°	784.5	783.2	781.7	780.4	779.0	776.5	772.9	769.3	765.6	762.1	759.1
52.5°	740.7	739.7	738.8	737.8	736.9	734.5	730.7	726.9	723.1	719.2	716.6
55°	673.7	673.4	673.1	672.9	672.6	670.7	667.0	663.5	659.8	656.2	653.2
57.5°	609.9	609.0	608.0	607.1	606.2	604.3	601.3	598.5	595.6	592.7	590.0
60°	564.1	563.8	563.6	563.2	563.0	561.2	557.9	554.5	551.2	547.9	545.4
62.5°	523.2	522.5	521.8	521.1	520.4	518.3	515.0	511.7	508.4	505.1	502.6
65°	459.5	458.1	456.7	455.3	453.9	451.9	449.1	446.3	443.5	440.8	438.6
67.5°	392.0	390.8	389.6	388.3	387.1	385.5	383.3	381.3	379.1	377.1	375.1
70°	351.2	349.5	347.8	346.2	344.5	342.9	341.2	339.5	337.9	336.2	334.3
72.5°	308.3	307.1	305.9	304.7	303.5	301.9	300.0	298.1	296.3	294.4	292.6
75°	242.8	241.7	240.6	239.5	238.4	237.4	236.6	235.8	235.0	234.1	232.7
77.5°	184.8	184.2	183.5	183.0	182.4	181.6	180.5	179.6	178.6	177.6	176.7
80°	146.9	146.1	145.3	144.4	143.6	142.9	142.4	141.8	141.2	140.7	140.5
82.5°	110.1	109.9	109.7	109.6	109.4	109.2	109.2	109.1	108.9	108.8	108.4
85°	64.7	64.2	63.6	63.1	62.5	62.3	62.3	62.3	62.3	62.3	61.7
87.5°	26.3	26.0	25.7	25.6	25.3	25.2	25.5	25.8	26.2	26.5	26.1
90°	1.8	3.6	5.5	8.3	10.1	12.0	14.7	17.5	20.3	23.0	22.1
92.5°	11.4	17.0	24.6	31.8	39.6	53.2	77.3	116.9	155.7	141.6	106.8
95°	31.3	34.1	44.2	59.8	83.7	119.6	197.9	335.0	486.0	545.8	442.7
97.5°	53.4	54.3	62.2	75.8	99.4	138.2	213.0	367.6	619.2	845.8	904.9
100°	68.1	69.0	75.5	88.3	110.4	146.3	210.8	347.0	589.1	871.6	1053.0
102.5°	83.6	85.2	90.9	103.1	122.9	155.9	213.7	329.3	544.9	823.8	1060.3
105°	106.8	109.6	115.0	126.1	143.5	172.1	221.8	316.6	490.6	740.0	1004.2
107.5°	131.4	134.2	139.5	150.4	166.8	193.3	236.9	315.7	456.0	666.0	905.9
110°	149.1	151.9	156.5	166.6	182.2	208.0	249.5	319.4	442.7	624.0	844.0



TEST NUMBER: P332089-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.3	168.1	172.7	182.8	198.4	223.5	262.0	326.8	435.4	596.0	790.3
115°	188.7	192.3	197.9	207.1	222.8	247.6	282.6	338.7	432.6	566.0	725.2
117.5°	212.1	216.3	220.9	229.3	246.8	269.9	304.4	354.5	434.3	548.3	686.0
120°	228.2	231.0	235.6	244.9	262.3	285.3	318.5	366.3	437.2	540.3	665.4
122.5°	242.2	245.0	249.6	259.5	276.3	300.8	333.2	377.4	442.4	535.1	648.5
125°	262.3	264.2	269.7	279.8	297.3	322.1	354.3	394.8	450.0	528.3	626.8
127.5°	277.6	280.4	287.2	297.5	316.8	341.7	372.7	409.2	458.9	525.0	607.7
130°	287.2	289.9	298.2	309.3	328.6	353.4	383.8	418.7	464.8	522.8	597.3
132.5°	294.5	298.0	307.0	320.3	339.6	363.8	393.4	427.6	469.2	522.0	587.8
135°	307.4	311.1	321.2	335.0	354.3	379.2	407.7	439.0	475.9	520.9	575.3
137.5°	319.6	323.4	333.4	348.1	367.3	390.2	417.6	447.5	480.3	518.9	564.4
140°	327.6	332.2	341.4	356.2	374.6	397.6	424.3	451.9	483.2	518.2	557.8
142.5°	336.5	340.4	350.3	363.5	382.0	403.5	429.4	456.3	485.4	516.7	551.8
145°	350.7	353.4	361.7	375.5	391.2	412.3	436.3	461.1	486.9	514.5	544.0
147.5°	365.0	366.7	374.8	386.7	401.9	419.9	441.8	464.1	486.9	511.0	536.2
150°	374.6	375.5	382.9	394.8	407.7	424.3	445.4	464.8	486.9	508.0	531.1
152.5°	384.2	384.4	391.7	402.2	413.6	429.4	447.7	466.3	484.7	504.4	525.2
155°	398.5	398.5	404.1	413.3	423.3	436.3	451.9	466.7	482.3	498.0	516.3
157.5°	410.0	410.7	415.1	423.2	431.8	441.8	454.3	467.5	479.2	492.3	506.4
160°	418.7	418.7	422.5	429.8	436.3	445.4	456.5	467.5	477.7	487.8	499.8
162.5°	425.4	425.4	428.3	434.3	440.0	447.7	457.2	466.8	474.8	483.4	493.1
165°	435.4	434.4	436.3	440.8	444.6	451.0	458.4	464.8	470.3	476.7	484.1
167.5°	442.9	441.8	442.7	446.2	448.8	452.8	458.2	463.3	465.9	470.2	475.5
170°	447.3	445.4	446.4	449.2	451.0	452.8	457.4	461.1	463.0	465.7	470.3
172.5°	450.3	449.2	449.3	451.4	452.5	453.6	457.4	460.4	460.7	462.0	465.2
175°	453.8	452.8	451.9	453.8	453.8	454.7	456.5	458.4	457.4	457.4	459.3
177.5°	455.4	454.7	453.9	454.7	454.7	454.7	455.4	456.9	455.4	454.7	455.4
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332089-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1442.6	1444.9	1447.1	1448.1	1447.9	1447.6	1447.4	1447.2
5°	1435.0	1437.8	1440.6	1441.7	1441.1	1440.6	1440.0	1439.5
7.5°	1419.8	1422.3	1424.8	1425.8	1425.5	1425.2	1424.9	1424.6
10°	1405.9	1408.3	1410.9	1411.8	1411.3	1410.7	1410.2	1409.6
12.5°	1390.6	1392.4	1394.2	1395.0	1394.6	1394.3	1394.0	1393.7
15°	1362.9	1365.2	1367.4	1367.7	1366.0	1364.4	1362.7	1361.0
17.5°	1328.0	1329.6	1331.1	1331.6	1331.0	1330.4	1329.8	1329.2
20°	1302.3	1303.4	1304.5	1304.6	1303.8	1302.9	1302.1	1301.2
22.5°	1274.9	1275.8	1276.7	1276.6	1275.6	1274.5	1273.4	1272.4
25°	1229.6	1229.9	1230.2	1229.9	1229.1	1228.2	1227.4	1226.5
27.5°	1181.5	1181.6	1181.9	1181.5	1180.4	1179.3	1178.3	1177.3
30°	1148.1	1148.1	1148.1	1147.2	1145.2	1143.3	1141.3	1139.4
32.5°	1113.1	1111.6	1110.0	1108.7	1107.7	1106.6	1105.6	1104.5
35°	1056.4	1054.7	1053.0	1051.5	1050.1	1048.8	1047.3	1046.0
37.5°	997.7	995.7	993.7	992.3	991.3	990.5	989.6	988.7
40°	959.4	957.2	955.0	953.3	952.2	951.1	950.0	948.9
42.5°	919.6	917.3	915.1	913.5	912.4	911.2	910.1	909.0
45°	860.1	856.7	853.4	851.0	849.7	848.3	846.9	845.5
47.5°	797.4	794.2	790.8	788.6	787.4	786.2	785.0	783.8
50°	756.0	753.0	749.9	747.6	745.9	744.3	742.6	740.9
52.5°	714.1	711.5	708.8	706.7	705.0	703.4	701.7	700.1
55°	650.1	647.1	644.0	641.8	640.5	639.1	637.7	636.3
57.5°	587.3	584.6	581.9	579.7	578.1	576.6	574.9	573.3
60°	543.0	540.4	538.0	536.0	534.6	533.2	531.9	530.4
62.5°	500.1	497.6	495.1	493.4	492.4	491.5	490.6	489.6
65°	436.4	434.2	432.0	430.5	429.6	428.8	427.9	427.1
67.5°	373.2	371.2	369.3	367.7	366.6	365.4	364.2	363.1
70°	332.3	330.4	328.4	326.8	325.4	324.0	322.7	321.3
72.5°	291.0	289.2	287.5	286.3	285.6	284.9	284.2	283.4
75°	231.3	230.0	228.5	227.4	226.6	225.8	225.0	224.1
77.5°	175.7	174.8	173.8	173.3	173.3	173.3	173.3	173.3
80°	140.1	139.9	139.6	139.5	139.5	139.5	139.5	139.5
82.5°	107.8	107.3	106.9	106.5	106.2	106.1	105.8	105.6
85°	61.2	60.6	60.0	59.8	59.8	59.8	59.8	59.8
87.5°	26.1	26.1	26.0	26.2	26.1	26.2	26.5	26.2
90°	23.0	23.9	24.9	26.7	25.7	26.7	27.6	26.7
92.5°	77.5	61.5	54.3	49.5	47.8	45.1	46.0	44.4
95°	331.4	224.6	175.8	142.7	125.2	116.9	110.4	106.8
97.5°	825.9	661.6	542.9	432.8	364.9	323.4	298.6	290.7
100°	1085.1	1010.6	902.9	772.2	679.2	612.0	576.2	577.1
102.5°	1171.3	1168.9	1106.1	1023.3	950.9	897.8	867.8	846.6
105°	1196.5	1288.6	1306.1	1282.1	1239.8	1204.8	1175.4	1170.8
107.5°	1123.9	1273.4	1354.1	1386.9	1387.6	1375.8	1365.9	1357.4
110°	1054.8	1224.2	1340.1	1404.5	1430.3	1437.7	1435.8	1434.0



TEST NUMBER: P332089-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	986.3	1159.4	1289.3	1372.1	1419.3	1442.1	1449.1	1449.5
115°	895.6	1055.7	1191.0	1291.3	1360.3	1400.8	1419.3	1423.9
117.5°	829.8	968.0	1089.6	1191.4	1263.4	1309.7	1336.3	1342.5
120°	795.2	919.5	1029.9	1122.9	1195.6	1247.1	1269.2	1274.8
122.5°	767.9	880.4	982.8	1069.1	1133.8	1180.1	1204.4	1211.4
125°	731.7	832.0	920.4	994.0	1053.0	1093.4	1116.4	1122.9
127.5°	700.1	789.5	869.2	936.2	988.7	1023.3	1044.1	1050.0
130°	680.2	763.0	837.6	900.2	949.0	982.1	1001.4	1008.8
132.5°	661.8	738.0	807.4	867.0	912.8	945.9	963.1	968.3
135°	636.9	702.3	762.1	814.5	859.7	887.2	903.8	910.3
137.5°	614.3	667.8	719.4	764.9	802.8	830.8	844.7	849.0
140°	601.0	647.9	692.1	731.7	766.7	792.5	807.2	806.3
142.5°	588.5	628.8	667.1	701.6	731.3	754.2	767.4	766.5
145°	573.4	603.8	633.3	659.9	682.9	702.3	709.6	711.5
147.5°	561.1	585.2	609.0	627.9	645.4	658.5	665.4	666.1
150°	552.2	573.4	592.7	610.2	624.0	634.1	639.7	639.7
152.5°	544.2	562.4	579.5	594.1	604.9	614.3	617.6	617.6
155°	532.0	546.7	560.5	571.6	579.9	587.2	589.1	589.9
157.5°	519.1	531.5	542.1	550.7	557.9	563.5	564.9	564.7
160°	511.7	521.9	531.1	537.5	544.0	549.5	549.5	548.6
162.5°	502.9	511.6	520.0	525.7	530.0	534.7	534.7	533.9
165°	491.5	497.0	503.4	508.0	511.7	515.4	514.5	514.5
167.5°	481.6	485.8	489.5	492.8	494.4	497.0	496.1	496.1
170°	474.9	477.7	481.3	483.2	484.1	486.0	485.1	485.1
172.5°	469.1	471.0	474.0	475.1	475.3	477.1	475.5	474.8
175°	461.1	462.0	463.9	463.9	463.9	464.8	463.9	463.0
177.5°	456.1	456.9	457.6	457.6	456.9	457.6	456.1	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7

(END OF REPORT)