

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831219

Luminaire Tested: S123DIP-S1165D1195U927-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831219
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U927-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7996.9 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 73.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53				53
1	99	95	91	88	92	88	85	82	75	73	71	63	62	60	53	52	51				46	
2	91	83	78	73	84	78	73	68	67	63	60	56	54	51	47	45	44				39	
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38				34	
4	76	66	58	53	71	62	55	50	53	48	44	46	42	39	38	36	33				30	
5	70	59	51	46	65	55	48	43	48	43	39	41	37	34	35	32	29				26	
6	65	53	46	40	60	50	43	38	44	38	34	38	33	30	32	29	26				24	
7	61	49	41	36	56	46	39	34	40	34	30	35	30	27	30	26	24				21	
8	56	44	37	32	52	42	35	30	37	31	27	32	28	25	27	24	22				19	
9	53	41	34	29	49	38	32	27	34	29	25	30	25	22	25	22	20				18	
10	49	38	31	26	46	36	29	25	31	26	23	28	23	20	24	21	18				16	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	28243	28243	28243	28243	28243
5°	35718	33713	28496	22964	21102
10°	36066	37156	28306	18306	15996
15°	27164	34497	28113	15502	13527
20°	18927	27915	27755	13557	12287
25°	14433	21467	27143	12473	11525
30°	12485	17055	26166	11706	10912
35°	11583	14399	25039	11152	10479
40°	10967	12917	23456	10624	10333
45°	10602	11954	21444	10213	10268
50°	10419	11194	19063	9838	10215
55°	10031	10637	16726	9483	10260
60°	9672	10038	14417	9147	10092
65°	9088	9475	12437	8792	9892
70°	8393	8755	10578	8201	9312
75°	7594	7848	9062	7619	8509
80°	6267	6868	7172	6639	7172
85°	4965	5570	5261	5644	5718

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 24484 cd/sqm



TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.1	3.1
10°-20°	617.1	7.7
20°-30°	730.7	9.1
30°-40°	734.7	9.2
40°-50°	674.1	8.4
50°-60°	556.4	7.0
60°-70°	393.6	4.9
70°-80°	210.1	2.6
80°-90°	55.8	0.7
90°-100°	43.7	0.5
100°-110°	211.1	2.6
110°-120°	517.5	6.5
120°-130°	657.0	8.2
130°-140°	701.9	8.8
140°-150°	656.4	8.2
150°-160°	529.4	6.6
160°-170°	341.7	4.3
170°-180°	117.7	1.5
0°-30°	1595.9	20.0
0°-40°	2330.6	29.1
0°-60°	3561.0	44.5
0°-90°	4220.5	52.8
90°-120°	772.4	9.7
90°-150°	2787.7	34.9
90°-180°	3776.0	47.2
0°-180°	7996.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2624	2624	2624	2624	2624	
5°	3306	3120	2637	2125	1953	315
15°	2438	3096	2523	1391	1214	673
25°	1215	1808	2285	1050	970	573
35°	882	1096	1906	849	798	554
45°	696	785	1409	671	674	539
55°	534	567	891	505	547	478
65°	357	372	488	345	388	355
75°	183	189	218	183	205	192
85°	40	45	43	46	46	45
90°	28	22	1	22	28	15
95°	35	28	56	28	35	29
105°	40	202	274	202	40	84
115°	541	528	514	528	541	509
125°	740	736	725	736	740	661
135°	912	912	903	912	912	704
145°	1052	1050	1042	1050	1052	657
155°	1146	1147	1148	1147	1146	529
165°	1208	1207	1210	1207	1208	341
175°	1234	1235	1239	1235	1234	117
180°	1239	1239	1239	1239	1239	



TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2957.5	2954.5	2951.4	2936.2	2921.0	2913.7	2906.4	2884.5	2862.5	2838.2	2813.8
5°	3305.7	3314.3	3322.8	3313.0	3303.3	3273.5	3243.6	3204.1	3164.5	3120.1	3075.6
7.5°	3466.5	3471.3	3476.2	3470.1	3464.0	3456.1	3448.2	3412.9	3377.6	3331.9	3286.3
10°	3299.7	3310.6	3321.6	3345.3	3369.1	3395.8	3422.6	3417.8	3412.9	3399.5	3386.1
12.5°	2933.2	2946.6	2959.9	3007.4	3054.9	3115.8	3176.7	3229.0	3281.4	3317.9	3354.4
15°	2437.6	2474.7	2511.9	2555.1	2598.3	2687.8	2777.3	2887.5	2997.7	3095.7	3193.7
17.5°	2007.8	2021.8	2035.8	2082.1	2128.3	2241.0	2353.6	2480.8	2608.1	2770.6	2933.2
20°	1652.3	1665.0	1677.8	1738.7	1799.6	1887.9	1976.1	2119.2	2262.3	2437.0	2611.7
22.5°	1388.0	1408.1	1428.2	1462.3	1496.4	1581.0	1665.7	1792.9	1920.1	2113.1	2306.1
25°	1215.2	1229.8	1244.4	1265.1	1285.8	1353.3	1420.9	1525.6	1630.3	1807.5	1984.7
27.5°	1097.0	1103.1	1109.2	1129.9	1150.6	1194.5	1238.3	1328.4	1418.5	1568.9	1719.2
30°	1004.5	1008.8	1013.0	1031.3	1049.6	1079.4	1109.2	1174.4	1239.5	1372.2	1504.9
32.5°	940.0	943.0	946.1	960.1	974.1	995.4	1016.7	1064.2	1111.7	1221.2	1330.8
35°	881.5	883.4	885.2	895.5	905.9	921.7	937.5	973.5	1009.4	1095.8	1182.3
37.5°	830.4	832.8	835.3	841.4	847.4	861.4	875.4	904.1	932.7	999.0	1065.4
40°	780.5	784.7	789.0	793.3	797.5	809.1	820.7	842.6	864.5	919.3	974.1
42.5°	737.9	742.1	746.4	748.2	750.0	756.7	763.4	783.5	803.6	844.4	885.2
45°	696.5	698.3	700.1	701.9	703.8	709.2	714.7	732.4	750.0	785.3	820.7
47.5°	658.7	658.7	658.7	659.9	661.1	666.0	670.9	683.7	696.5	723.9	751.3
50°	622.2	622.2	622.2	620.4	618.5	621.6	624.6	634.4	644.1	668.5	692.8
52.5°	578.4	578.4	578.4	579.0	579.6	579.6	579.6	588.1	596.6	618.5	640.4
55°	534.5	537.0	539.4	537.6	535.7	537.0	538.2	543.7	549.1	566.8	584.4
57.5°	490.7	491.9	493.1	492.5	491.9	492.5	493.1	498.0	502.9	516.3	529.6
60°	449.3	449.3	449.3	448.1	446.9	448.1	449.3	451.7	454.2	466.3	478.5
62.5°	403.0	403.6	404.2	404.8	405.5	404.2	403.0	406.1	409.1	418.2	427.4
65°	356.8	357.4	358.0	359.8	361.6	360.4	359.2	362.2	365.3	372.0	378.7
67.5°	315.4	314.1	312.9	313.5	314.1	316.0	317.8	318.4	319.0	326.3	333.6
70°	266.7	267.9	269.1	268.5	267.9	268.5	269.1	270.9	272.7	278.2	283.7
72.5°	222.8	223.4	224.0	224.0	224.0	225.3	226.5	228.3	230.1	233.2	236.2
75°	182.6	182.6	182.6	183.9	185.1	185.7	186.3	186.3	186.3	188.7	191.2
77.5°	138.8	141.8	144.9	144.3	143.7	144.9	146.1	147.9	149.8	151.0	152.2
80°	101.1	101.1	101.1	101.7	102.3	104.1	105.9	107.1	108.4	110.8	113.2
82.5°	64.5	65.1	65.7	67.6	69.4	70.6	71.8	73.7	75.5	75.5	75.5
85°	40.2	39.0	37.7	39.0	40.2	41.4	42.6	43.2	43.8	45.1	46.3
87.5°	19.5	19.5	19.5	19.5	19.5	20.1	20.7	20.7	20.7	20.7	20.7
90°	27.6	27.2	26.8	26.4	26.0	25.4	24.5	23.7	22.9	22.1	19.4
92.5°	31.3	31.1	30.9	30.7	30.5	29.7	28.2	26.8	25.4	23.9	22.1
95°	35.0	35.0	35.0	35.0	35.0	34.3	32.8	31.4	30.0	28.5	26.3
97.5°	37.7	37.5	37.3	37.1	36.9	36.0	34.4	32.7	31.1	29.5	39.9
100°	38.7	38.5	38.2	38.0	37.8	36.9	35.3	33.6	32.0	30.4	62.3
102.5°	39.6	39.2	38.8	38.3	37.9	41.1	47.9	54.6	61.4	68.1	103.7
105°	40.5	40.1	39.7	39.3	38.9	56.8	93.0	129.2	165.4	201.6	220.0
107.5°	95.7	122.5	149.3	176.1	202.9	232.0	263.5	295.0	326.5	358.0	355.0
110°	253.1	282.3	311.6	340.8	370.1	388.1	394.8	401.6	408.3	415.1	412.8



TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	479.5	479.9	480.3	480.7	481.1	480.4	478.6	476.7	474.9	473.1	470.8
115°	541.2	540.4	539.5	538.7	537.9	536.5	534.4	532.4	530.3	528.3	526.4
117.5°	590.9	590.7	590.5	590.3	590.1	589.1	587.5	585.9	584.2	582.6	581.6
120°	642.4	642.4	642.4	642.4	642.4	641.6	640.0	638.3	636.7	635.1	634.4
122.5°	693.0	692.8	692.6	692.4	692.2	691.6	690.6	689.6	688.5	687.5	686.7
125°	740.0	739.6	739.2	738.7	738.3	737.9	737.5	737.1	736.7	736.3	735.5
127.5°	786.0	786.4	786.8	787.2	787.6	787.5	786.9	786.3	785.7	785.1	784.0
130°	830.2	830.6	831.0	831.4	831.8	831.6	830.8	830.0	829.1	828.3	827.5
132.5°	870.7	871.3	871.9	872.5	873.1	873.0	872.2	871.4	870.6	869.7	869.1
135°	912.1	912.7	913.3	913.9	914.5	914.5	913.9	913.3	912.7	912.1	911.3
137.5°	951.7	952.1	952.5	952.9	953.3	953.0	952.0	950.9	949.9	948.9	948.5
140°	986.6	987.0	987.4	987.9	988.3	988.1	987.2	986.4	985.6	984.8	984.2
142.5°	1018.8	1019.5	1020.1	1020.7	1021.3	1021.3	1020.7	1020.1	1019.5	1018.8	1018.2
145°	1052.0	1052.0	1052.0	1052.0	1052.0	1051.8	1051.4	1051.0	1050.5	1050.1	1049.7
147.5°	1075.9	1076.9	1078.0	1079.0	1080.0	1080.3	1079.9	1079.5	1079.1	1078.7	1078.3
150°	1103.5	1104.1	1104.7	1105.4	1106.0	1106.1	1105.7	1105.3	1104.8	1104.4	1104.0
152.5°	1125.6	1126.6	1127.7	1128.7	1129.7	1129.8	1129.0	1128.2	1127.3	1126.5	1126.3
155°	1145.9	1147.1	1148.3	1149.5	1150.8	1150.9	1149.8	1148.8	1147.8	1146.8	1146.6
157.5°	1163.3	1165.0	1166.6	1168.2	1169.9	1170.1	1168.9	1167.6	1166.4	1165.2	1165.4
160°	1179.9	1181.3	1182.8	1184.2	1185.6	1185.7	1184.5	1183.3	1182.1	1180.8	1181.0
162.5°	1195.6	1196.8	1198.0	1199.2	1200.5	1200.4	1198.9	1197.5	1196.1	1194.6	1194.8
165°	1207.5	1208.9	1210.4	1211.8	1213.2	1213.1	1211.5	1209.9	1208.2	1206.6	1206.8
167.5°	1216.7	1218.4	1220.0	1221.6	1223.3	1223.3	1221.6	1220.0	1218.4	1216.7	1216.7
170°	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0	1225.0
172.5°	1229.6	1231.4	1233.3	1235.1	1237.0	1237.1	1235.4	1233.8	1232.2	1230.5	1230.3
175°	1234.2	1235.8	1237.5	1239.1	1240.8	1240.9	1239.4	1238.0	1236.6	1235.1	1234.9
177.5°	1235.1	1237.2	1239.2	1241.3	1243.3	1243.5	1241.9	1240.2	1238.6	1237.0	1236.8
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2806.5	2799.2	2772.4	2745.7	2715.2	2684.8	2662.3	2639.7	2606.2	2572.8	2545.4
5°	3041.5	3007.4	2950.8	2894.2	2817.5	2740.8	2689.0	2637.3	2567.9	2498.5	2443.1
7.5°	3227.8	3169.4	3090.2	3011.1	2910.6	2810.2	2715.2	2620.2	2514.3	2408.4	2321.9
10°	3346.5	3307.0	3215.6	3124.3	2989.8	2855.2	2722.5	2589.8	2453.4	2317.1	2202.6
12.5°	3358.1	3361.8	3277.7	3193.7	3041.5	2889.3	2728.0	2566.7	2395.0	2223.3	2090.0
15°	3256.4	3319.1	3272.9	3226.6	3073.2	2919.8	2721.3	2522.8	2325.0	2127.1	1973.1
17.5°	3067.7	3202.2	3208.9	3215.6	3062.2	2908.8	2689.0	2469.3	2245.2	2021.2	1859.3
20°	2810.2	3008.7	3076.8	3145.0	3020.2	2895.4	2659.2	2423.0	2172.2	1921.3	1751.5
22.5°	2547.2	2788.3	2913.1	3037.9	2945.3	2852.8	2601.4	2349.9	2085.1	1820.3	1648.0
25°	2247.7	2510.7	2702.4	2894.2	2837.6	2781.0	2533.2	2285.4	2003.5	1721.7	1545.7
27.5°	1986.5	2253.8	2485.1	2716.4	2704.3	2692.1	2446.1	2200.2	1911.6	1623.0	1453.2
30°	1753.9	2002.9	2261.7	2520.4	2550.2	2580.1	2342.6	2105.2	1816.0	1526.9	1363.1
32.5°	1548.2	1765.5	2043.1	2320.7	2379.2	2437.6	2223.3	2009.0	1722.9	1436.8	1279.1
35°	1379.5	1576.8	1854.4	2132.0	2205.0	2278.1	2091.8	1905.5	1626.7	1347.9	1197.5
37.5°	1230.4	1395.4	1666.3	1937.2	2026.7	2116.2	1949.4	1782.5	1521.4	1260.2	1122.0
40°	1106.8	1239.5	1488.5	1737.5	1841.0	1944.5	1806.9	1669.3	1421.5	1173.8	1046.5
42.5°	1003.3	1121.4	1347.3	1573.1	1672.4	1771.6	1655.3	1539.0	1318.6	1098.3	982.0
45°	915.0	1009.4	1214.5	1419.7	1514.1	1608.4	1508.6	1408.7	1214.5	1020.3	912.0
47.5°	832.2	913.2	1088.5	1263.9	1347.9	1431.9	1354.0	1276.0	1111.7	947.3	849.3
50°	757.9	823.1	976.5	1129.9	1203.0	1276.0	1207.2	1138.4	1003.3	868.1	782.9
52.5°	693.4	746.4	874.8	1003.3	1066.0	1128.7	1069.6	1010.6	903.4	796.3	722.0
55°	629.5	674.5	786.0	897.4	940.0	982.6	936.9	891.3	804.8	718.4	655.7
57.5°	569.8	610.0	701.3	792.6	825.5	858.4	817.0	775.6	710.5	645.3	593.0
60°	511.4	544.3	620.4	696.5	716.5	736.6	703.2	669.7	624.0	578.4	531.5
62.5°	457.2	487.0	543.7	600.3	613.7	627.1	601.5	575.9	541.2	506.5	470.0
65°	401.2	423.7	470.0	516.3	524.8	533.3	510.8	488.3	462.1	435.9	409.1
67.5°	349.4	365.3	403.0	440.8	441.4	442.0	423.7	405.5	390.8	376.2	354.9
70°	298.9	314.1	339.1	364.1	364.7	365.3	350.7	336.1	325.1	314.1	298.3
72.5°	247.2	258.1	277.0	295.9	294.7	293.4	284.3	275.2	266.7	258.1	246.6
75°	200.3	209.4	222.2	235.0	231.3	227.7	222.8	217.9	210.6	203.3	196.0
77.5°	157.7	163.2	170.5	177.8	175.3	172.9	168.6	164.4	158.9	153.4	150.4
80°	115.7	118.1	123.0	127.8	126.6	125.4	120.5	115.7	114.5	113.2	109.0
82.5°	78.5	81.6	82.8	84.0	83.4	82.8	79.1	75.5	74.3	73.1	72.4
85°	46.9	47.5	48.1	48.7	46.9	45.1	43.8	42.6	42.6	42.6	42.0
87.5°	21.3	21.9	21.9	21.9	21.3	20.7	19.5	18.3	18.9	19.5	19.5
90°	16.8	14.1	11.5	9.1	7.1	5.0	3.0	0.9	3.0	5.0	7.1
92.5°	20.2	18.4	16.6	16.3	17.5	18.7	19.9	21.2	19.9	18.7	17.5
95°	24.0	21.8	19.5	22.6	31.0	39.4	47.8	56.1	47.8	39.4	31.0
97.5°	50.3	60.7	71.2	79.3	85.0	90.7	96.4	102.2	96.4	90.7	85.0
100°	94.2	126.1	158.0	171.9	167.8	163.7	159.6	155.5	159.6	163.7	167.8
102.5°	139.3	174.9	210.5	226.9	224.3	221.6	218.9	216.3	218.9	221.6	224.3
105°	238.4	256.8	275.2	283.3	281.0	278.8	276.5	274.3	276.5	278.8	281.0
107.5°	351.9	348.8	345.8	343.3	341.5	339.6	337.8	335.9	337.8	339.6	341.5
110°	410.6	408.3	406.1	404.1	402.5	400.9	399.2	397.6	399.2	400.9	402.5



TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	468.6	466.3	464.1	462.2	460.8	459.4	457.9	456.5	457.9	459.4	460.8
115°	524.6	522.8	520.9	519.4	518.2	516.9	515.7	514.5	515.7	516.9	518.2
117.5°	580.5	579.5	578.5	577.3	575.8	574.4	573.0	571.5	573.0	574.4	575.8
120°	633.8	633.2	632.6	631.4	629.5	627.7	625.8	624.0	625.8	627.7	629.5
122.5°	685.9	685.1	684.2	683.1	681.7	680.3	678.8	677.4	678.8	680.3	681.7
125°	734.7	733.8	733.0	731.8	730.2	728.5	726.9	725.2	726.9	728.5	730.2
127.5°	783.0	782.0	781.0	779.7	778.0	776.4	774.7	773.1	774.7	776.4	778.0
130°	826.7	825.9	825.1	823.8	822.2	820.6	818.9	817.3	818.9	820.6	822.2
132.5°	868.5	867.9	867.3	866.2	864.5	862.9	861.3	859.6	861.3	862.9	864.5
135°	910.4	909.6	908.8	907.8	906.6	905.3	904.1	902.9	904.1	905.3	906.6
137.5°	948.1	947.7	947.3	946.2	944.6	943.0	941.3	939.7	941.3	943.0	944.6
140°	983.6	982.9	982.3	981.4	980.2	979.0	977.7	976.5	977.7	979.0	980.2
142.5°	1017.6	1017.0	1016.4	1015.5	1014.2	1013.0	1011.8	1010.6	1011.8	1013.0	1014.2
145°	1049.3	1048.9	1048.5	1047.6	1046.1	1044.7	1043.3	1041.9	1043.3	1044.7	1046.1
147.5°	1077.8	1077.4	1077.0	1076.3	1075.3	1074.3	1073.2	1072.2	1073.2	1074.3	1075.3
150°	1103.6	1103.2	1102.8	1102.3	1101.7	1101.1	1100.4	1099.8	1100.4	1101.1	1101.7
152.5°	1126.1	1125.9	1125.7	1125.5	1125.3	1125.1	1124.9	1124.7	1124.9	1125.1	1125.3
155°	1146.4	1146.2	1146.0	1146.1	1146.5	1146.9	1147.3	1147.7	1147.3	1146.9	1146.5
157.5°	1165.6	1165.8	1166.0	1166.1	1166.1	1166.1	1166.1	1166.1	1166.1	1166.1	1166.1
160°	1181.2	1181.4	1181.6	1181.8	1182.1	1182.3	1182.5	1182.7	1182.5	1182.3	1182.1
162.5°	1195.0	1195.2	1195.5	1195.9	1196.5	1197.1	1197.7	1198.3	1197.7	1197.1	1196.5
165°	1207.0	1207.2	1207.4	1207.8	1208.4	1209.1	1209.7	1210.3	1209.7	1209.1	1208.4
167.5°	1216.7	1216.7	1216.7	1217.1	1217.9	1218.8	1219.6	1220.4	1219.6	1218.8	1217.9
170°	1225.0	1225.0	1225.0	1225.4	1226.2	1227.0	1227.9	1228.7	1227.9	1227.0	1226.2
172.5°	1230.1	1229.9	1229.7	1230.1	1231.1	1232.2	1233.2	1234.2	1233.2	1232.2	1231.1
175°	1234.7	1234.5	1234.3	1234.7	1235.7	1236.8	1237.8	1238.8	1237.8	1236.8	1235.7
177.5°	1236.6	1236.4	1236.2	1236.6	1237.6	1238.6	1239.6	1240.7	1239.6	1238.6	1237.6
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2518.0	2494.2	2470.5	2452.2	2434.0	2402.9	2371.9	2364.6	2357.2	2346.9	2336.5
5°	2387.7	2329.2	2270.8	2218.4	2166.1	2125.3	2084.5	2057.7	2030.9	2011.5	1992.0
7.5°	2235.5	2147.8	2060.2	1998.1	1936.0	1876.9	1817.9	1799.0	1780.1	1754.5	1729.0
10°	2088.2	1991.4	1894.6	1813.6	1732.6	1674.8	1617.0	1593.8	1570.7	1538.4	1506.2
12.5°	1956.7	1850.7	1744.8	1663.2	1581.6	1525.6	1469.6	1436.1	1402.7	1384.4	1366.1
15°	1819.1	1705.8	1592.6	1517.1	1441.6	1391.1	1340.6	1311.3	1282.1	1264.5	1246.8
17.5°	1697.3	1585.3	1473.3	1400.8	1328.4	1282.1	1235.8	1210.3	1184.7	1171.3	1157.9
20°	1581.6	1472.1	1362.5	1291.9	1221.2	1183.5	1145.7	1129.3	1112.9	1101.9	1091.0
22.5°	1475.7	1368.0	1260.2	1199.9	1139.7	1109.2	1078.8	1067.2	1055.6	1046.5	1037.4
25°	1369.8	1273.6	1177.4	1126.3	1075.1	1050.2	1025.2	1013.6	1002.1	992.9	983.8
27.5°	1283.3	1191.4	1099.5	1055.6	1011.8	992.3	972.9	963.7	954.6	946.1	937.5
30°	1199.3	1117.1	1034.9	997.2	959.5	941.8	924.1	915.0	905.9	898.0	890.1
32.5°	1121.4	1050.8	980.2	945.5	910.8	896.1	881.5	870.6	859.6	853.5	847.4
35°	1047.1	983.8	920.5	891.9	863.3	848.7	834.0	824.9	815.8	810.9	806.0
37.5°	983.8	927.2	870.6	843.2	815.8	801.8	787.8	779.9	771.9	770.1	768.3
40°	919.3	870.6	821.9	795.1	768.3	756.1	743.9	739.1	734.2	733.0	731.8
42.5°	865.7	818.2	770.7	746.4	722.0	711.7	701.3	698.9	696.5	698.3	700.1
45°	803.6	764.0	724.5	701.9	679.4	670.9	662.4	660.5	658.7	662.4	666.0
47.5°	751.3	714.7	678.2	656.9	635.6	629.5	623.4	622.8	622.2	627.1	631.9
50°	697.7	662.4	627.1	610.0	593.0	587.5	582.0	583.8	585.7	593.6	601.5
52.5°	647.8	614.9	582.0	566.2	550.3	546.7	543.0	547.3	551.6	560.1	568.6
55°	593.0	563.1	533.3	521.1	509.0	505.3	501.6	510.2	518.7	526.6	534.5
57.5°	540.6	514.4	488.3	477.3	466.3	465.7	465.1	473.0	480.9	489.5	498.0
60°	484.6	462.7	440.8	432.2	423.7	424.9	426.2	435.3	444.4	451.1	457.8
62.5°	433.5	415.2	396.9	389.0	381.1	384.1	387.2	396.3	405.5	413.4	421.3
65°	382.3	367.1	351.9	346.4	340.9	345.2	349.4	357.4	365.3	370.8	376.2
67.5°	333.6	320.8	308.0	303.8	299.5	303.8	308.0	316.0	323.9	329.4	334.8
70°	282.5	272.1	261.8	258.7	255.7	260.6	265.4	272.1	278.8	284.3	289.8
72.5°	235.0	227.1	219.2	218.6	217.9	222.2	226.5	233.2	239.9	243.5	247.2
75°	188.7	184.5	180.2	179.6	179.0	183.2	187.5	191.2	194.8	197.9	200.9
77.5°	147.3	143.7	140.0	140.6	141.2	144.3	147.3	151.0	154.6	156.5	158.3
80°	104.7	103.5	102.3	103.5	104.7	107.1	109.6	112.0	114.5	115.7	116.9
82.5°	71.8	70.6	69.4	71.2	73.1	74.9	76.7	78.5	80.4	81.0	81.6
85°	41.4	43.2	45.1	45.1	45.1	45.7	46.3	46.9	47.5	46.9	46.3
87.5°	19.5	20.1	20.7	20.7	20.7	21.3	21.9	21.9	21.9	21.3	20.7
90°	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.7	24.5	25.4	26.0
92.5°	16.3	16.6	18.4	20.2	22.1	23.9	25.4	26.8	28.2	29.7	30.5
95°	22.6	19.5	21.8	24.0	26.3	28.5	30.0	31.4	32.8	34.3	35.0
97.5°	79.3	71.2	60.7	50.3	39.9	29.5	31.1	32.7	34.4	36.0	36.9
100°	171.9	158.0	126.1	94.2	62.3	30.4	32.0	33.6	35.3	36.9	37.8
102.5°	226.9	210.5	174.9	139.3	103.7	68.1	61.4	54.6	47.9	41.1	37.9
105°	283.3	275.2	256.8	238.4	220.0	201.6	165.4	129.2	93.0	56.8	38.9
107.5°	343.3	345.8	348.8	351.9	355.0	358.0	326.5	295.0	263.5	232.0	202.9
110°	404.1	406.1	408.3	410.6	412.8	415.1	408.3	401.6	394.8	388.1	370.1



TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	462.2	464.1	466.3	468.6	470.8	473.1	474.9	476.7	478.6	480.4	481.1
115°	519.4	520.9	522.8	524.6	526.4	528.3	530.3	532.4	534.4	536.5	537.9
117.5°	577.3	578.5	579.5	580.5	581.6	582.6	584.2	585.9	587.5	589.1	590.1
120°	631.4	632.6	633.2	633.8	634.4	635.1	636.7	638.3	640.0	641.6	642.4
122.5°	683.1	684.2	685.1	685.9	686.7	687.5	688.5	689.6	690.6	691.6	692.2
125°	731.8	733.0	733.8	734.7	735.5	736.3	736.7	737.1	737.5	737.9	738.3
127.5°	779.7	781.0	782.0	783.0	784.0	785.1	785.7	786.3	786.9	787.5	787.6
130°	823.8	825.1	825.9	826.7	827.5	828.3	829.1	830.0	830.8	831.6	831.8
132.5°	866.2	867.3	867.9	868.5	869.1	869.7	870.6	871.4	872.2	873.0	873.1
135°	907.8	908.8	909.6	910.4	911.3	912.1	912.7	913.3	913.9	914.5	914.5
137.5°	946.2	947.3	947.7	948.1	948.5	948.9	949.9	950.9	952.0	953.0	953.3
140°	981.4	982.3	982.9	983.6	984.2	984.8	985.6	986.4	987.2	988.1	988.3
142.5°	1015.5	1016.4	1017.0	1017.6	1018.2	1018.8	1019.5	1020.1	1020.7	1021.3	1021.3
145°	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5	1051.0	1051.4	1051.8	1052.0
147.5°	1076.3	1077.0	1077.4	1077.8	1078.3	1078.7	1079.1	1079.5	1079.9	1080.3	1080.0
150°	1102.3	1102.8	1103.2	1103.6	1104.0	1104.4	1104.8	1105.3	1105.7	1106.1	1106.0
152.5°	1125.5	1125.7	1125.9	1126.1	1126.3	1126.5	1127.3	1128.2	1129.0	1129.8	1129.7
155°	1146.1	1146.0	1146.2	1146.4	1146.6	1146.8	1147.8	1148.8	1149.8	1150.9	1150.8
157.5°	1166.1	1166.0	1165.8	1165.6	1165.4	1165.2	1166.4	1167.6	1168.9	1170.1	1169.9
160°	1181.8	1181.6	1181.4	1181.2	1181.0	1180.8	1182.1	1183.3	1184.5	1185.7	1185.6
162.5°	1195.9	1195.5	1195.2	1195.0	1194.8	1194.6	1196.1	1197.5	1198.9	1200.4	1200.5
165°	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2	1209.9	1211.5	1213.1	1213.2
167.5°	1217.1	1216.7	1216.7	1216.7	1216.7	1216.7	1218.4	1220.0	1221.6	1223.3	1223.3
170°	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5
172.5°	1230.1	1229.7	1229.9	1230.1	1230.3	1230.5	1232.2	1233.8	1235.4	1237.1	1237.0
175°	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6	1238.0	1239.4	1240.9	1240.8
177.5°	1236.6	1236.2	1236.4	1236.6	1236.8	1237.0	1238.6	1240.2	1241.9	1243.5	1243.3
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2623.9	2623.9	2623.9	2623.9
2.5°	2332.3	2328.0	2311.0	2293.9
5°	1977.4	1962.7	1957.9	1953.0
7.5°	1727.8	1726.5	1701.0	1675.4
10°	1508.0	1509.8	1486.7	1463.5
12.5°	1350.9	1335.7	1333.9	1332.0
15°	1232.8	1218.8	1216.4	1213.9
17.5°	1149.4	1140.9	1138.4	1136.0
20°	1086.1	1081.2	1077.0	1072.7
22.5°	1031.3	1025.2	1021.6	1017.9
25°	978.3	972.9	971.6	970.4
27.5°	930.8	924.1	924.1	924.1
30°	885.8	881.5	879.7	877.9
32.5°	843.8	840.1	840.1	840.1
35°	804.2	802.4	800.0	797.5
37.5°	768.3	768.3	767.1	765.9
40°	733.6	735.4	735.4	735.4
42.5°	701.9	703.8	703.8	703.8
45°	669.1	672.1	673.3	674.5
47.5°	636.8	641.7	642.9	644.1
50°	605.1	608.8	609.4	610.0
52.5°	572.9	577.1	580.2	583.2
55°	538.8	543.0	544.9	546.7
57.5°	502.3	506.5	507.1	507.7
60°	462.1	466.3	467.6	468.8
62.5°	423.7	426.2	427.4	428.6
65°	379.9	383.5	386.0	388.4
67.5°	337.9	340.9	340.9	340.9
70°	291.0	292.2	294.0	295.9
72.5°	247.8	248.4	248.4	248.4
75°	202.1	203.3	203.9	204.6
77.5°	158.9	159.5	159.5	159.5
80°	116.3	115.7	115.7	115.7
82.5°	79.8	77.9	77.9	77.9
85°	45.7	45.1	45.7	46.3
87.5°	20.7	20.7	20.7	20.7
90°	26.4	26.8	27.2	27.6
92.5°	30.7	30.9	31.1	31.3
95°	35.0	35.0	35.0	35.0
97.5°	37.1	37.3	37.5	37.7
100°	38.0	38.2	38.5	38.7
102.5°	38.3	38.8	39.2	39.6
105°	39.3	39.7	40.1	40.5
107.5°	176.1	149.3	122.5	95.7
110°	340.8	311.6	282.3	253.1



TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	480.7	480.3	479.9	479.5
115°	538.7	539.5	540.4	541.2
117.5°	590.3	590.5	590.7	590.9
120°	642.4	642.4	642.4	642.4
122.5°	692.4	692.6	692.8	693.0
125°	738.7	739.2	739.6	740.0
127.5°	787.2	786.8	786.4	786.0
130°	831.4	831.0	830.6	830.2
132.5°	872.5	871.9	871.3	870.7
135°	913.9	913.3	912.7	912.1
137.5°	952.9	952.5	952.1	951.7
140°	987.9	987.4	987.0	986.6
142.5°	1020.7	1020.1	1019.5	1018.8
145°	1052.0	1052.0	1052.0	1052.0
147.5°	1079.0	1078.0	1076.9	1075.9
150°	1105.4	1104.7	1104.1	1103.5
152.5°	1128.7	1127.7	1126.6	1125.6
155°	1149.5	1148.3	1147.1	1145.9
157.5°	1168.2	1166.6	1165.0	1163.3
160°	1184.2	1182.8	1181.3	1179.9
162.5°	1199.2	1198.0	1196.8	1195.6
165°	1211.8	1210.4	1208.9	1207.5
167.5°	1221.6	1220.0	1218.4	1216.7
170°	1229.9	1228.3	1226.6	1225.0
172.5°	1235.1	1233.3	1231.4	1229.6
175°	1239.1	1237.5	1235.8	1234.2
177.5°	1241.3	1239.2	1237.2	1235.1
180°	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P831219

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.43	16.28	16.37	17.23	18.47	17.67	18.52	18.61	19.47	20.70
	3H	17.08	17.84	18.03	18.80	20.06	19.09	19.85	20.04	20.81	22.07
	4H	17.65	18.37	18.62	19.34	20.61	19.54	20.26	20.51	21.23	22.49
	6H	18.03	18.69	19.00	19.66	20.94	19.82	20.48	20.79	21.45	22.73
	8H	18.12	18.75	19.11	19.74	21.01	19.88	20.51	20.86	21.50	22.77
	12H	18.17	18.76	19.15	19.75	21.05	19.90	20.50	20.89	21.48	22.78
4H	2H	16.01	16.72	16.98	17.69	18.96	17.83	18.55	18.80	19.51	20.78
	3H	17.83	18.43	18.81	19.43	20.71	19.45	20.05	20.43	21.04	22.32
	4H	18.53	19.08	19.52	20.07	21.37	20.03	20.58	21.02	21.57	22.87
	6H	19.01	19.47	20.01	20.49	21.79	20.44	20.90	21.44	21.92	23.22
	8H	19.14	19.58	20.14	20.59	21.90	20.55	20.98	21.55	21.99	23.31
	12H	19.21	19.60	20.23	20.62	21.95	20.59	20.99	21.61	22.01	23.33
8H	4H	18.80	19.23	19.80	20.24	21.56	20.14	20.57	21.14	21.58	22.90
	6H	19.38	19.75	20.41	20.79	22.11	20.64	21.00	21.67	22.05	23.36
	8H	19.59	19.91	20.63	20.94	22.28	20.82	21.14	21.85	22.17	23.50
	12H	19.72	19.99	20.75	21.02	22.40	20.92	21.20	21.96	22.23	23.60
12H	4H	18.80	19.19	19.82	20.21	21.53	20.11	20.51	21.13	21.53	22.85
	6H	19.43	19.75	20.47	20.79	22.12	20.65	20.97	21.69	22.00	23.34
	8H	19.67	19.95	20.71	20.98	22.35	20.85	21.13	21.89	22.16	23.54