

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331892-930

Luminaire Tested: **S123DIP-S340D1025U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331892-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D1025U930-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4526.6 lumens  
Efficiency: N/A  
Efficacy: 121.4 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	88	85	81	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	68	61	55	50	48	44	40	35	33	31	24	22	21	16
4	70	60	53	47	63	54	48	43	42	38	34	32	29	26	21	20	18	14
5	65	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	18	16	14	11
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	12	10
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4219	4219	4219	4219
5°	5032	4238	3756	4238
10°	6299	4217	3393	4217
15°	7725	4182	3158	4182
20°	9203	4129	3007	4129
25°	9772	4065	2973	4065
30°	8376	4018	2988	4018
35°	5825	3951	3020	3951
40°	4388	3873	3011	3873
45°	3643	3755	2973	3755
50°	3264	3518	2946	3518
55°	3051	3262	2909	3262
60°	2863	2992	2878	2992
65°	2690	2728	2786	2728
70°	2521	2426	2653	2426
75°	2258	2125	2433	2125
80°	1977	1742	2095	1742
85°	1556	1272	1408	1272



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.6	0.9
10°-20°	123.8	2.7
20°-30°	207.8	4.6
30°-40°	235.3	5.2
40°-50°	211.0	4.7
50°-60°	170.3	3.8
60°-70°	118.7	2.6
70°-80°	62.4	1.4
80°-90°	18.3	0.4
90°-100°	39.8	0.9
100°-110°	189.8	4.2
110°-120°	455.9	10.1
120°-130°	580.5	12.8
130°-140°	620.3	13.7
140°-150°	580.0	12.8
150°-160°	467.9	10.3
160°-170°	302.0	6.7
170°-180°	104.1	2.3
0°-30°	370.3	8.2
0°-40°	605.6	13.4
0°-60°	986.9	21.8
0°-90°	1186.3	26.2
90°-120°	685.5	15.1
90°-150°	2466.4	54.5
90°-180°	3340.0	73.8
0°-180°	4526.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	392	392	392	392	392	
5°	466	392	348	392	466	48
15°	693	375	283	375	693	200
25°	823	342	250	342	823	361
35°	443	301	230	301	443	288
45°	239	247	195	247	239	189
55°	163	174	155	174	163	146
65°	106	107	109	107	106	105
75°	54	51	58	51	54	58
85°	13	10	11	10	13	16
90°	24	1	24	1	24	12
95°	31	50	31	50	31	26
105°	36	242	36	242	36	82
115°	478	455	478	455	478	442
125°	654	641	654	641	654	584
135°	806	798	806	798	806	622
145°	930	921	930	921	930	581
155°	1013	1015	1013	1015	1013	467
165°	1068	1070	1068	1070	1068	301
175°	1091	1095	1091	1095	1091	104
180°	1095	1095	1095	1095	1095	



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	416.0	415.7	415.0	415.6	414.3	412.7	412.5	411.0	406.6	406.3	405.1
5°	465.7	464.2	464.0	463.8	461.1	457.5	450.7	450.1	441.0	436.5	431.0
7.5°	530.1	530.8	528.1	525.7	517.6	512.2	504.8	495.5	484.3	472.9	465.4
10°	576.3	582.5	574.8	569.4	564.5	555.2	544.4	530.8	517.4	501.7	489.7
12.5°	625.8	628.8	627.3	622.3	614.7	600.5	581.3	566.4	554.0	527.7	517.1
15°	693.2	704.8	697.4	680.4	680.7	667.2	642.2	614.7	600.0	577.0	545.7
17.5°	765.2	766.5	763.4	749.2	739.7	721.1	698.0	671.6	642.0	614.2	580.9
20°	803.4	802.3	795.7	788.2	771.9	757.5	732.2	702.8	664.8	637.4	601.1
22.5°	824.7	822.8	819.6	813.4	799.9	784.4	761.7	729.5	693.3	655.7	613.8
25°	822.8	825.2	825.7	823.9	819.2	809.9	792.1	766.4	730.3	681.8	638.2
27.5°	748.4	751.9	762.0	771.0	781.1	791.3	789.9	777.2	750.5	708.7	655.3
30°	673.9	666.3	685.1	708.8	725.0	753.5	769.4	770.4	755.4	719.5	667.4
32.5°	570.5	578.9	587.3	616.4	651.8	683.7	715.5	741.0	744.0	720.1	674.6
35°	443.3	453.8	469.0	484.1	522.1	554.8	610.7	659.3	698.0	703.1	675.2
37.5°	357.3	362.4	372.0	387.3	412.1	450.9	494.0	555.5	611.6	653.4	655.2
40°	312.3	313.8	324.6	336.1	356.3	388.2	427.1	481.5	548.7	607.1	631.4
42.5°	278.5	281.8	286.5	297.6	313.6	337.6	373.8	418.7	480.4	547.5	595.0
45°	239.3	243.1	246.0	253.4	264.8	281.0	306.1	347.2	394.1	463.4	527.4
47.5°	213.4	213.7	215.8	221.4	229.2	241.3	259.2	285.5	328.6	384.8	450.5
50°	194.9	197.9	198.7	203.0	209.1	218.0	232.8	255.3	290.6	340.0	400.4
52.5°	181.8	182.7	184.8	188.0	193.3	200.2	213.1	230.6	258.4	300.5	356.0
55°	162.6	162.6	164.7	167.1	170.2	176.4	185.0	197.9	219.0	251.7	297.7
57.5°	144.8	145.8	147.2	148.0	150.6	154.7	161.8	171.7	187.4	212.5	249.1
60°	133.0	134.7	134.4	136.0	138.3	141.5	147.6	155.6	169.6	189.7	220.5
62.5°	122.6	122.5	122.5	124.3	126.5	129.6	133.6	140.5	152.5	170.3	196.5
65°	105.6	105.3	106.6	107.7	108.4	110.7	113.7	119.8	127.8	141.1	161.4
67.5°	90.5	89.4	90.1	90.5	91.8	93.6	96.4	100.2	106.5	117.2	132.5
70°	80.1	79.2	79.0	79.4	80.6	81.9	84.0	87.6	93.4	102.0	113.2
72.5°	69.5	68.9	68.8	69.7	70.2	71.1	72.6	75.8	80.6	87.0	97.4
75°	54.3	54.3	54.3	54.5	55.1	55.8	57.0	58.7	62.3	66.9	73.9
77.5°	40.7	40.7	40.4	40.4	41.3	41.6	41.8	43.5	45.5	48.5	53.6
80°	31.9	31.0	31.3	31.9	32.3	32.4	33.0	33.4	35.1	36.9	40.4
82.5°	23.7	22.9	23.0	23.9	24.0	24.1	24.7	25.2	25.8	27.4	29.4
85°	12.6	12.6	12.7	12.7	12.9	12.7	13.3	13.5	13.5	14.4	15.6
87.5°	9.5	9.0	9.1	9.2	9.0	9.0	9.0	9.0	9.0	9.0	8.7
90°	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0	20.2	19.6	17.2
92.5°	27.0	26.8	26.6	26.3	26.2	25.4	24.3	23.2	22.0	20.9	19.1
95°	30.9	30.9	30.9	30.9	30.9	30.3	29.0	27.7	26.5	25.2	23.2
97.5°	33.5	33.3	33.2	33.0	32.8	32.0	30.6	29.1	27.6	26.2	39.2
100°	34.2	34.0	33.8	33.7	33.4	32.6	31.2	29.8	28.3	26.8	55.0
102.5°	34.8	34.5	34.2	33.8	33.5	35.6	40.1	44.6	49.1	53.6	84.4
105°	35.8	35.5	35.1	34.7	34.3	50.2	82.2	114.2	146.2	178.2	194.5
107.5°	112.4	136.6	160.7	184.8	209.0	232.8	256.2	279.7	303.2	326.7	324.1
110°	223.8	249.6	275.5	301.3	327.3	343.2	349.1	355.1	361.0	367.0	365.0



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.9	389.4	394.8	400.3	405.8	408.5	408.4	408.2	408.1	408.1	406.0
115°	478.5	477.8	477.0	476.3	475.6	474.3	472.5	470.8	469.0	467.1	465.5
117.5°	531.6	531.4	531.2	531.2	531.0	530.2	528.7	527.3	525.9	524.4	523.6
120°	568.0	568.0	568.0	568.0	568.0	567.3	565.8	564.4	563.0	561.5	561.0
122.5°	603.8	603.6	603.6	603.4	603.2	602.7	601.7	600.6	599.7	598.6	597.9
125°	654.3	654.0	653.5	653.2	652.8	652.5	652.1	651.8	651.4	651.0	650.3
127.5°	702.8	703.1	703.5	703.8	704.3	704.1	703.5	703.0	702.4	701.8	700.9
130°	734.0	734.4	734.7	735.2	735.5	735.3	734.6	733.9	733.1	732.4	731.6
132.5°	762.7	763.2	763.7	764.2	764.7	764.6	763.9	763.1	762.5	761.7	761.2
135°	806.5	807.0	807.6	808.1	808.6	808.6	808.1	807.6	807.0	806.5	805.8
137.5°	847.7	848.0	848.4	848.7	849.1	848.8	848.0	847.1	846.2	845.4	845.0
140°	872.4	872.8	873.1	873.4	873.8	873.7	872.9	872.2	871.5	870.7	870.3
142.5°	895.2	895.7	896.2	896.7	897.2	897.2	896.6	896.0	895.4	894.9	894.3
145°	930.2	930.2	930.2	930.2	930.2	930.0	929.6	929.3	928.9	928.5	928.1
147.5°	956.2	957.0	957.9	958.7	959.5	959.8	959.4	959.0	958.7	958.3	958.0
150°	975.8	976.2	976.8	977.4	977.9	978.0	977.6	977.3	976.9	976.6	976.2
152.5°	991.3	992.2	993.0	993.8	994.7	994.7	994.1	993.4	992.8	992.1	992.0
155°	1013.2	1014.2	1015.4	1016.4	1017.5	1017.6	1016.7	1015.8	1014.9	1014.0	1013.8
157.5°	1031.6	1033.0	1034.4	1035.8	1037.2	1037.4	1036.2	1035.2	1034.1	1033.0	1033.2
160°	1043.3	1044.6	1045.8	1047.1	1048.3	1048.4	1047.3	1046.3	1045.2	1044.1	1044.2
162.5°	1054.3	1055.5	1056.5	1057.7	1058.8	1058.7	1057.5	1056.3	1055.1	1053.9	1054.0
165°	1067.7	1068.9	1070.2	1071.5	1072.8	1072.7	1071.2	1069.8	1068.3	1066.9	1067.1
167.5°	1077.3	1078.7	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3	1077.3
170°	1083.1	1084.6	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1	1083.1
172.5°	1086.4	1088.0	1089.6	1091.2	1092.7	1092.8	1091.4	1090.0	1088.5	1087.0	1086.9
175°	1091.3	1092.7	1094.2	1095.6	1097.1	1097.1	1095.9	1094.6	1093.4	1092.1	1091.9
177.5°	1092.7	1094.2	1095.7	1097.1	1098.5	1098.7	1097.6	1096.3	1095.2	1094.1	1093.9
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	404.1	403.0	401.8	399.7	397.8	395.3	394.4	393.5	390.8	388.4	386.5
5°	428.8	424.3	417.7	411.6	406.7	400.0	396.2	392.2	386.5	381.4	377.2
7.5°	454.7	445.7	435.4	424.3	413.8	403.8	395.7	388.5	380.5	373.0	367.0
10°	475.2	462.3	447.8	432.3	419.0	406.1	395.3	385.8	375.5	366.6	359.1
12.5°	498.6	479.5	459.6	440.7	424.9	407.0	393.9	381.8	370.1	359.5	351.1
15°	526.3	502.0	478.4	452.4	428.5	406.1	390.5	375.3	361.8	350.8	340.1
17.5°	551.5	524.0	492.9	461.3	432.4	405.9	384.1	366.9	350.0	336.6	326.0
20°	565.8	534.5	499.4	466.5	434.6	405.0	381.0	360.5	342.3	328.0	316.1
22.5°	578.1	541.4	505.1	469.9	434.4	402.5	375.4	354.2	334.5	320.6	307.9
25°	590.9	547.0	510.5	469.4	429.7	396.6	366.2	342.3	322.5	306.1	293.1
27.5°	601.9	546.7	503.4	459.0	422.1	389.0	356.5	330.8	309.9	292.1	278.8
30°	609.1	547.4	495.9	452.1	414.8	380.7	349.1	323.3	301.3	283.2	270.7
32.5°	613.7	546.9	489.1	442.3	403.2	373.0	341.0	314.3	291.6	273.9	261.9
35°	616.4	543.6	477.3	422.2	384.7	355.1	328.4	300.7	277.0	260.4	246.7
37.5°	611.0	536.5	463.7	402.8	361.7	332.7	310.1	286.6	263.8	245.6	233.8
40°	602.7	532.0	453.0	389.1	345.8	318.0	298.8	275.6	253.2	235.9	224.9
42.5°	586.7	522.8	441.3	374.0	329.5	301.6	283.9	264.5	243.3	227.1	216.1
45°	547.8	502.6	423.7	351.2	305.2	276.4	260.8	246.7	227.6	211.8	202.3
47.5°	493.7	472.2	398.4	327.2	279.9	252.2	235.9	224.7	210.7	197.9	188.8
50°	456.2	447.3	381.2	310.7	263.1	235.9	220.3	210.1	200.0	187.3	179.0
52.5°	412.9	418.4	361.2	293.8	245.9	219.2	204.6	196.4	187.3	176.8	169.5
55°	352.0	371.9	326.5	265.1	220.3	194.9	181.0	173.8	168.4	160.7	154.4
57.5°	294.9	320.2	289.0	235.7	195.2	173.3	160.0	152.1	148.7	144.6	139.7
60°	261.0	286.0	262.3	216.0	178.4	157.4	145.7	139.0	135.6	132.7	128.6
62.5°	230.7	256.1	236.2	195.9	161.8	142.4	132.2	125.6	123.0	121.6	118.0
65°	189.1	211.0	197.7	164.7	138.1	121.0	111.7	107.1	104.7	104.1	101.8
67.5°	153.9	170.6	160.9	136.6	115.7	100.9	93.0	89.1	87.2	87.0	85.3
70°	130.9	146.4	139.0	117.0	99.0	87.4	80.6	77.1	76.0	75.8	74.8
72.5°	112.9	123.8	117.9	99.5	85.6	75.1	70.0	66.4	65.2	65.5	64.8
75°	83.6	91.7	88.3	75.6	64.4	57.6	53.4	51.1	50.0	50.5	49.7
77.5°	60.2	65.3	62.2	53.4	46.5	41.6	38.5	37.1	36.0	36.0	35.7
80°	45.4	48.4	46.7	41.4	35.7	31.6	29.0	28.1	27.6	27.3	27.1
82.5°	32.4	34.9	32.9	29.3	25.4	22.8	21.4	20.2	19.8	19.9	19.7
85°	16.3	17.3	16.6	14.3	12.7	11.6	10.8	10.3	9.9	10.0	9.7
87.5°	8.6	8.2	7.3	6.4	5.6	4.8	4.5	3.8	3.8	4.2	4.4
90°	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8	2.6	4.4	6.3
92.5°	17.3	15.5	13.8	13.1	13.6	14.1	14.6	15.2	14.6	14.1	13.6
95°	21.3	19.2	17.3	20.0	27.4	34.8	42.2	49.7	42.2	34.8	27.4
97.5°	52.3	65.3	78.3	86.4	89.8	93.1	96.4	99.8	96.4	93.1	89.8
100°	83.2	111.5	139.7	152.0	148.4	144.8	141.1	137.5	141.1	144.8	148.4
102.5°	115.2	146.0	176.8	190.9	188.3	185.7	183.1	180.5	183.1	185.7	188.3
105°	210.8	227.1	243.3	250.5	248.5	246.5	244.5	242.5	244.5	246.5	248.5
107.5°	321.6	318.9	316.4	314.3	312.7	311.1	309.6	307.9	309.6	311.1	312.7
110°	363.1	361.0	359.1	357.3	355.9	354.4	353.0	351.6	353.0	354.4	355.9





TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	404.1	402.1	400.1	398.4	397.1	395.8	394.5	393.2	394.5	395.8	397.1
115°	463.8	462.2	460.6	459.3	458.2	457.1	456.0	454.9	456.0	457.1	458.2
117.5°	522.8	521.9	521.1	520.0	518.7	517.3	516.0	514.6	516.0	517.3	518.7
120°	560.4	559.9	559.4	558.2	556.6	555.0	553.3	551.7	553.3	555.0	556.6
122.5°	597.3	596.6	595.9	594.8	593.5	592.2	590.8	589.5	590.8	592.2	593.5
125°	649.5	648.9	648.2	647.0	645.6	644.2	642.7	641.2	642.7	644.2	645.6
127.5°	700.1	699.2	698.3	697.2	695.7	694.3	692.8	691.4	692.8	694.3	695.7
130°	731.0	730.3	729.5	728.5	727.0	725.5	724.1	722.7	724.1	725.5	727.0
132.5°	760.5	759.9	759.4	758.4	756.9	755.5	754.1	752.6	754.1	755.5	756.9
135°	805.0	804.3	803.6	802.7	801.6	800.5	799.4	798.3	799.4	800.5	801.6
137.5°	844.6	844.2	843.8	842.9	841.6	840.2	838.8	837.4	838.8	840.2	841.6
140°	869.7	869.1	868.6	867.8	866.7	865.6	864.5	863.4	864.5	865.6	866.7
142.5°	893.7	893.2	892.7	891.9	890.8	889.7	888.6	887.5	888.6	889.7	890.8
145°	927.8	927.5	927.1	926.3	925.0	923.7	922.5	921.2	922.5	923.7	925.0
147.5°	957.6	957.2	956.8	956.3	955.4	954.6	953.8	952.9	953.8	954.6	955.4
150°	975.8	975.4	975.1	974.6	974.1	973.5	973.1	972.5	973.1	973.5	974.1
152.5°	991.7	991.5	991.3	991.1	990.8	990.6	990.3	990.0	990.3	990.6	990.8
155°	1013.6	1013.4	1013.3	1013.3	1013.7	1014.1	1014.4	1014.8	1014.4	1014.1	1013.7
157.5°	1033.4	1033.6	1033.7	1033.9	1033.9	1034.0	1034.0	1034.0	1034.0	1034.0	1033.9
160°	1044.5	1044.6	1044.8	1045.0	1045.2	1045.4	1045.5	1045.7	1045.5	1045.4	1045.2
162.5°	1054.2	1054.4	1054.6	1054.9	1055.4	1055.8	1056.3	1056.8	1056.3	1055.8	1055.4
165°	1067.2	1067.4	1067.6	1068.0	1068.5	1069.0	1069.6	1070.2	1069.6	1069.0	1068.5
167.5°	1077.3	1077.3	1077.3	1077.7	1078.4	1079.1	1079.9	1080.5	1079.9	1079.1	1078.4
170°	1083.1	1083.1	1083.1	1083.5	1084.3	1085.0	1085.7	1086.4	1085.7	1085.0	1084.3
172.5°	1086.8	1086.6	1086.5	1086.9	1087.7	1088.6	1089.5	1090.3	1089.5	1088.6	1087.7
175°	1091.8	1091.5	1091.4	1091.8	1092.7	1093.6	1094.5	1095.4	1094.5	1093.6	1092.7
177.5°	1093.8	1093.6	1093.5	1093.8	1094.5	1095.2	1095.9	1096.7	1095.9	1095.2	1094.5
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	385.5	384.4	382.9	380.7	378.8	375.9	375.9	376.3	376.3	376.3	375.9
5°	373.8	371.0	367.5	363.5	359.4	355.1	354.4	352.9	351.8	351.0	350.1
7.5°	361.4	356.4	351.4	345.8	340.7	336.6	333.6	331.2	329.6	327.9	326.7
10°	353.1	346.8	341.0	335.1	328.6	323.4	320.2	318.0	316.3	314.7	314.0
12.5°	343.2	336.1	329.5	323.9	316.9	311.6	308.5	307.4	305.5	302.2	300.6
15°	328.8	322.1	314.4	305.8	302.4	296.0	292.3	290.6	289.4	287.0	286.3
17.5°	316.4	307.8	299.0	292.6	286.3	281.0	279.0	276.9	275.4	273.4	272.7
20°	306.6	298.8	290.8	284.0	277.3	271.6	269.9	268.4	266.8	266.0	265.1
22.5°	296.5	288.8	282.1	275.7	268.6	264.9	263.1	261.4	260.3	259.7	258.9
25°	282.4	275.6	268.2	262.5	256.8	254.3	253.2	252.3	251.4	250.5	250.3
27.5°	269.9	262.4	256.4	251.0	247.0	244.9	243.8	243.4	243.5	243.9	244.1
30°	260.4	253.6	248.7	244.1	240.3	238.4	238.1	238.1	239.0	239.1	239.5
32.5°	251.8	246.1	241.2	236.8	233.9	232.6	233.3	233.3	233.9	234.4	235.1
35°	239.1	234.2	230.4	226.6	224.1	224.7	225.1	225.4	226.4	227.6	228.3
37.5°	227.1	222.8	218.8	215.9	214.7	215.7	216.7	217.4	218.6	219.5	220.2
40°	218.4	215.2	211.4	208.7	209.1	209.7	210.4	211.4	212.4	213.0	213.7
42.5°	210.3	207.0	204.1	201.9	202.4	203.2	203.6	204.1	205.2	206.3	206.7
45°	198.1	195.4	192.8	191.4	191.8	192.2	192.6	193.1	194.1	194.9	195.1
47.5°	184.3	182.5	180.7	179.4	180.0	179.9	180.3	181.6	181.8	182.3	183.4
50°	175.5	173.8	171.7	171.3	171.3	171.3	171.5	173.0	173.0	173.8	174.6
52.5°	165.8	164.7	163.4	162.7	162.3	162.3	163.1	163.9	164.2	165.3	166.1
55°	151.4	150.3	149.1	148.5	148.1	148.5	150.0	150.4	151.4	152.0	152.5
57.5°	136.4	135.5	134.6	134.3	134.2	134.7	135.5	136.6	136.9	138.7	139.5
60°	126.5	125.1	124.4	124.4	124.0	125.7	125.4	127.3	127.7	128.8	130.1
62.5°	116.3	114.5	114.2	114.2	114.8	115.3	115.8	116.6	117.6	119.0	120.1
65°	99.9	99.0	100.3	100.1	99.7	100.9	100.9	101.8	103.0	104.3	106.4
67.5°	84.4	83.9	84.0	84.0	84.5	85.2	85.8	86.6	88.0	89.4	90.7
70°	73.9	74.4	73.5	74.3	74.8	75.0	75.4	76.6	78.0	79.0	80.6
72.5°	63.7	63.7	63.8	64.1	64.7	65.0	65.4	66.7	68.3	69.1	70.4
75°	49.0	48.8	49.4	49.4	50.3	50.7	51.1	51.7	53.2	54.3	55.3
77.5°	35.8	36.0	35.9	36.5	36.3	36.4	37.5	38.1	38.2	40.5	41.0
80°	27.0	27.3	27.6	27.7	27.9	27.6	28.9	29.4	29.4	30.7	31.7
82.5°	19.4	19.6	20.1	20.3	20.3	20.7	20.8	21.2	21.7	22.3	23.5
85°	9.7	10.3	10.4	10.3	10.4	10.0	10.6	10.8	11.0	11.0	11.0
87.5°	4.6	5.2	5.5	6.2	6.4	7.1	7.3	7.1	7.3	7.8	7.3
90°	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0	21.7	22.4	23.0
92.5°	13.1	13.8	15.5	17.3	19.1	20.9	22.0	23.2	24.3	25.4	26.2
95°	20.0	17.3	19.2	21.3	23.2	25.2	26.5	27.7	29.0	30.3	30.9
97.5°	86.4	78.3	65.3	52.3	39.2	26.2	27.6	29.1	30.6	32.0	32.8
100°	152.0	139.7	111.5	83.2	55.0	26.8	28.3	29.8	31.2	32.6	33.4
102.5°	190.9	176.8	146.0	115.2	84.4	53.6	49.1	44.6	40.1	35.6	33.5
105°	250.5	243.3	227.1	210.8	194.5	178.2	146.2	114.2	82.2	50.2	34.3
107.5°	314.3	316.4	318.9	321.6	324.1	326.7	303.2	279.7	256.2	232.8	209.0
110°	357.3	359.1	361.0	363.1	365.0	367.0	361.0	355.1	349.1	343.2	327.3



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	398.4	400.1	402.1	404.1	406.0	408.1	408.1	408.2	408.4	408.5	405.8
115°	459.3	460.6	462.2	463.8	465.5	467.1	469.0	470.8	472.5	474.3	475.6
117.5°	520.0	521.1	521.9	522.8	523.6	524.4	525.9	527.3	528.7	530.2	531.0
120°	558.2	559.4	559.9	560.4	561.0	561.5	563.0	564.4	565.8	567.3	568.0
122.5°	594.8	595.9	596.6	597.3	597.9	598.6	599.7	600.6	601.7	602.7	603.2
125°	647.0	648.2	648.9	649.5	650.3	651.0	651.4	651.8	652.1	652.5	652.8
127.5°	697.2	698.3	699.2	700.1	700.9	701.8	702.4	703.0	703.5	704.1	704.3
130°	728.5	729.5	730.3	731.0	731.6	732.4	733.1	733.9	734.6	735.3	735.5
132.5°	758.4	759.4	759.9	760.5	761.2	761.7	762.5	763.1	763.9	764.6	764.7
135°	802.7	803.6	804.3	805.0	805.8	806.5	807.0	807.6	808.1	808.6	808.6
137.5°	842.9	843.8	844.2	844.6	845.0	845.4	846.2	847.1	848.0	848.8	849.1
140°	867.8	868.6	869.1	869.7	870.3	870.7	871.5	872.2	872.9	873.7	873.8
142.5°	891.9	892.7	893.2	893.7	894.3	894.9	895.4	896.0	896.6	897.2	897.2
145°	926.3	927.1	927.5	927.8	928.1	928.5	928.9	929.3	929.6	930.0	930.2
147.5°	956.3	956.8	957.2	957.6	958.0	958.3	958.7	959.0	959.4	959.8	959.5
150°	974.6	975.1	975.4	975.8	976.2	976.6	976.9	977.3	977.6	978.0	977.9
152.5°	991.1	991.3	991.5	991.7	992.0	992.1	992.8	993.4	994.1	994.7	994.7
155°	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9	1015.8	1016.7	1017.6	1017.5
157.5°	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1	1035.2	1036.2	1037.4	1037.2
160°	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2	1046.3	1047.3	1048.4	1048.3
162.5°	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1	1056.3	1057.5	1058.7	1058.8
165°	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3	1069.8	1071.2	1072.7	1072.8
167.5°	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7	1080.2	1081.7	1083.0	1083.0
170°	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6	1086.1	1087.5	1088.9	1088.9
172.5°	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5	1090.0	1091.4	1092.8	1092.7
175°	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4	1094.6	1095.9	1097.1	1097.1
177.5°	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2	1096.3	1097.6	1098.7	1098.5
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	374.9	374.7	375.8	375.0	375.8	374.7	374.9	375.9	376.3	376.3	376.3
5°	348.9	349.5	347.6	347.6	347.6	349.5	348.9	350.1	351.0	351.8	352.9
7.5°	325.8	325.0	325.1	324.0	325.1	325.0	325.8	326.7	327.9	329.6	331.2
10°	311.7	310.5	310.1	310.4	310.1	310.5	311.7	314.0	314.7	316.3	318.0
12.5°	299.9	299.8	297.3	297.3	297.3	299.8	299.9	300.6	302.2	305.5	307.4
15°	286.3	282.7	282.3	283.4	282.3	282.7	286.3	286.3	287.0	289.4	290.6
17.5°	272.5	270.5	270.7	270.1	270.7	270.5	272.5	272.7	273.4	275.4	276.9
20°	265.1	264.0	263.8	262.5	263.8	264.0	265.1	265.1	266.0	266.8	268.4
22.5°	258.4	258.1	258.2	256.7	258.2	258.1	258.4	258.9	259.7	260.3	261.4
25°	250.1	251.1	250.3	250.3	250.3	251.1	250.1	250.3	250.5	251.4	252.3
27.5°	244.5	244.5	244.1	244.1	244.1	244.5	244.5	244.1	243.9	243.5	243.4
30°	240.3	240.1	240.4	240.4	240.4	240.1	240.3	239.5	239.1	239.0	238.1
32.5°	236.0	236.3	236.4	236.5	236.4	236.3	236.0	235.1	234.4	233.9	233.3
35°	229.4	229.7	230.2	229.8	230.2	229.7	229.4	228.3	227.6	226.4	225.4
37.5°	220.5	221.4	221.3	221.5	221.3	221.4	220.5	220.2	219.5	218.6	217.4
40°	213.9	214.4	214.3	214.3	214.3	214.4	213.9	213.7	213.0	212.4	211.4
42.5°	207.0	207.4	206.9	206.7	206.9	207.4	207.0	206.7	206.3	205.2	204.1
45°	195.8	195.4	196.0	195.3	196.0	195.4	195.8	195.1	194.9	194.1	193.1
47.5°	183.3	183.7	183.8	184.4	183.8	183.7	183.3	183.4	182.3	181.8	181.6
50°	175.0	176.1	176.1	175.9	176.1	176.1	175.0	174.6	173.8	173.0	173.0
52.5°	166.7	167.2	168.0	168.0	168.0	167.2	166.7	166.1	165.3	164.2	163.9
55°	154.0	154.4	154.8	155.0	154.8	154.4	154.0	152.5	152.0	151.4	150.4
57.5°	140.9	140.7	141.6	141.9	141.6	140.7	140.9	139.5	138.7	136.9	136.6
60°	131.6	131.6	133.1	133.7	133.1	131.6	131.6	130.1	128.8	127.7	127.3
62.5°	121.7	122.4	123.8	123.1	123.8	122.4	121.7	120.1	119.0	117.6	116.6
65°	107.3	108.8	108.7	109.4	108.7	108.8	107.3	106.4	104.3	103.0	101.8
67.5°	92.2	93.2	94.6	94.7	94.6	93.2	92.2	90.7	89.4	88.0	86.6
70°	82.0	83.0	83.7	84.3	83.7	83.0	82.0	80.6	79.0	78.0	76.6
72.5°	72.2	72.6	74.5	73.7	74.5	72.6	72.2	70.4	69.1	68.3	66.7
75°	56.6	58.0	59.1	58.5	59.1	58.0	56.6	55.3	54.3	53.2	51.7
77.5°	41.8	43.2	43.7	43.2	43.7	43.2	41.8	41.0	40.5	38.2	38.1
80°	33.0	32.9	34.0	33.8	34.0	32.9	33.0	31.7	30.7	29.4	29.4
82.5°	24.2	24.1	24.5	24.7	24.5	24.1	24.2	23.5	22.3	21.7	21.2
85°	11.7	12.3	11.6	11.4	11.6	12.3	11.7	11.0	11.0	11.0	10.8
87.5°	7.4	7.5	7.4	7.3	7.4	7.5	7.4	7.3	7.8	7.3	7.1
90°	23.3	23.7	24.1	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0
92.5°	26.3	26.6	26.8	27.0	26.8	26.6	26.3	26.2	25.4	24.3	23.2
95°	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.3	29.0	27.7
97.5°	33.0	33.2	33.3	33.5	33.3	33.2	33.0	32.8	32.0	30.6	29.1
100°	33.7	33.8	34.0	34.2	34.0	33.8	33.7	33.4	32.6	31.2	29.8
102.5°	33.8	34.2	34.5	34.8	34.5	34.2	33.8	33.5	35.6	40.1	44.6
105°	34.7	35.1	35.5	35.8	35.5	35.1	34.7	34.3	50.2	82.2	114.2
107.5°	184.8	160.7	136.6	112.4	136.6	160.7	184.8	209.0	232.8	256.2	279.7
110°	301.3	275.5	249.6	223.8	249.6	275.5	301.3	327.3	343.2	349.1	355.1



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	400.3	394.8	389.4	383.9	389.4	394.8	400.3	405.8	408.5	408.4	408.2
115°	476.3	477.0	477.8	478.5	477.8	477.0	476.3	475.6	474.3	472.5	470.8
117.5°	531.2	531.2	531.4	531.6	531.4	531.2	531.2	531.0	530.2	528.7	527.3
120°	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	567.3	565.8	564.4
122.5°	603.4	603.6	603.6	603.8	603.6	603.6	603.4	603.2	602.7	601.7	600.6
125°	653.2	653.5	654.0	654.3	654.0	653.5	653.2	652.8	652.5	652.1	651.8
127.5°	703.8	703.5	703.1	702.8	703.1	703.5	703.8	704.3	704.1	703.5	703.0
130°	735.2	734.7	734.4	734.0	734.4	734.7	735.2	735.5	735.3	734.6	733.9
132.5°	764.2	763.7	763.2	762.7	763.2	763.7	764.2	764.7	764.6	763.9	763.1
135°	808.1	807.6	807.0	806.5	807.0	807.6	808.1	808.6	808.6	808.1	807.6
137.5°	848.7	848.4	848.0	847.7	848.0	848.4	848.7	849.1	848.8	848.0	847.1
140°	873.4	873.1	872.8	872.4	872.8	873.1	873.4	873.8	873.7	872.9	872.2
142.5°	896.7	896.2	895.7	895.2	895.7	896.2	896.7	897.2	897.2	896.6	896.0
145°	930.2	930.2	930.2	930.2	930.2	930.2	930.2	930.2	930.0	929.6	929.3
147.5°	958.7	957.9	957.0	956.2	957.0	957.9	958.7	959.5	959.8	959.4	959.0
150°	977.4	976.8	976.2	975.8	976.2	976.8	977.4	977.9	978.0	977.6	977.3
152.5°	993.8	993.0	992.2	991.3	992.2	993.0	993.8	994.7	994.7	994.1	993.4
155°	1016.4	1015.4	1014.2	1013.2	1014.2	1015.4	1016.4	1017.5	1017.6	1016.7	1015.8
157.5°	1035.8	1034.4	1033.0	1031.6	1033.0	1034.4	1035.8	1037.2	1037.4	1036.2	1035.2
160°	1047.1	1045.8	1044.6	1043.3	1044.6	1045.8	1047.1	1048.3	1048.4	1047.3	1046.3
162.5°	1057.7	1056.5	1055.5	1054.3	1055.5	1056.5	1057.7	1058.8	1058.7	1057.5	1056.3
165°	1071.5	1070.2	1068.9	1067.7	1068.9	1070.2	1071.5	1072.8	1072.7	1071.2	1069.8
167.5°	1081.7	1080.2	1078.7	1077.3	1078.7	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2
170°	1087.5	1086.1	1084.6	1083.1	1084.6	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1
172.5°	1091.2	1089.6	1088.0	1086.4	1088.0	1089.6	1091.2	1092.7	1092.8	1091.4	1090.0
175°	1095.6	1094.2	1092.7	1091.3	1092.7	1094.2	1095.6	1097.1	1097.1	1095.9	1094.6
177.5°	1097.1	1095.7	1094.2	1092.7	1094.2	1095.7	1097.1	1098.5	1098.7	1097.6	1096.3
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	375.9	375.9	378.8	380.7	382.9	384.4	385.5	386.5	388.4	390.8	393.5
5°	354.4	355.1	359.4	363.5	367.5	371.0	373.8	377.2	381.4	386.5	392.2
7.5°	333.6	336.6	340.7	345.8	351.4	356.4	361.4	367.0	373.0	380.5	388.5
10°	320.2	323.4	328.6	335.1	341.0	346.8	353.1	359.1	366.6	375.5	385.8
12.5°	308.5	311.6	316.9	323.9	329.5	336.1	343.2	351.1	359.5	370.1	381.8
15°	292.3	296.0	302.4	305.8	314.4	322.1	328.8	340.1	350.8	361.8	375.3
17.5°	279.0	281.0	286.3	292.6	299.0	307.8	316.4	326.0	336.6	350.0	366.9
20°	269.9	271.6	277.3	284.0	290.8	298.8	306.6	316.1	328.0	342.3	360.5
22.5°	263.1	264.9	268.6	275.7	282.1	288.8	296.5	307.9	320.6	334.5	354.2
25°	253.2	254.3	256.8	262.5	268.2	275.6	282.4	293.1	306.1	322.5	342.3
27.5°	243.8	244.9	247.0	251.0	256.4	262.4	269.9	278.8	292.1	309.9	330.8
30°	238.1	238.4	240.3	244.1	248.7	253.6	260.4	270.7	283.2	301.3	323.3
32.5°	233.3	232.6	233.9	236.8	241.2	246.1	251.8	261.9	273.9	291.6	314.3
35°	225.1	224.7	224.1	226.6	230.4	234.2	239.1	246.7	260.4	277.0	300.7
37.5°	216.7	215.7	214.7	215.9	218.8	222.8	227.1	233.8	245.6	263.8	286.6
40°	210.4	209.7	209.1	208.7	211.4	215.2	218.4	224.9	235.9	253.2	275.6
42.5°	203.6	203.2	202.4	201.9	204.1	207.0	210.3	216.1	227.1	243.3	264.5
45°	192.6	192.2	191.8	191.4	192.8	195.4	198.1	202.3	211.8	227.6	246.7
47.5°	180.3	179.9	180.0	179.4	180.7	182.5	184.3	188.8	197.9	210.7	224.7
50°	171.5	171.3	171.3	171.3	171.7	173.8	175.5	179.0	187.3	200.0	210.1
52.5°	163.1	162.3	162.3	162.7	163.4	164.7	165.8	169.5	176.8	187.3	196.4
55°	150.0	148.5	148.1	148.5	149.1	150.3	151.4	154.4	160.7	168.4	173.8
57.5°	135.5	134.7	134.2	134.3	134.6	135.5	136.4	139.7	144.6	148.7	152.1
60°	125.4	125.7	124.0	124.4	124.4	125.1	126.5	128.6	132.7	135.6	139.0
62.5°	115.8	115.3	114.8	114.2	114.2	114.5	116.3	118.0	121.6	123.0	125.6
65°	100.9	100.9	99.7	100.1	100.3	99.0	99.9	101.8	104.1	104.7	107.1
67.5°	85.8	85.2	84.5	84.0	84.0	83.9	84.4	85.3	87.0	87.2	89.1
70°	75.4	75.0	74.8	74.3	73.5	74.4	73.9	74.8	75.8	76.0	77.1
72.5°	65.4	65.0	64.7	64.1	63.8	63.7	63.7	64.8	65.5	65.2	66.4
75°	51.1	50.7	50.3	49.4	49.4	48.8	49.0	49.7	50.5	50.0	51.1
77.5°	37.5	36.4	36.3	36.5	35.9	36.0	35.8	35.7	36.0	36.0	37.1
80°	28.9	27.6	27.9	27.7	27.6	27.3	27.0	27.1	27.3	27.6	28.1
82.5°	20.8	20.7	20.3	20.3	20.1	19.6	19.4	19.7	19.9	19.8	20.2
85°	10.6	10.0	10.4	10.3	10.4	10.3	9.7	9.7	10.0	9.9	10.3
87.5°	7.3	7.1	6.4	6.2	5.5	5.2	4.6	4.4	4.2	3.8	3.8
90°	20.2	19.6	17.2	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8
92.5°	22.0	20.9	19.1	17.3	15.5	13.8	13.1	13.6	14.1	14.6	15.2
95°	26.5	25.2	23.2	21.3	19.2	17.3	20.0	27.4	34.8	42.2	49.7
97.5°	27.6	26.2	39.2	52.3	65.3	78.3	86.4	89.8	93.1	96.4	99.8
100°	28.3	26.8	55.0	83.2	111.5	139.7	152.0	148.4	144.8	141.1	137.5
102.5°	49.1	53.6	84.4	115.2	146.0	176.8	190.9	188.3	185.7	183.1	180.5
105°	146.2	178.2	194.5	210.8	227.1	243.3	250.5	248.5	246.5	244.5	242.5
107.5°	303.2	326.7	324.1	321.6	318.9	316.4	314.3	312.7	311.1	309.6	307.9
110°	361.0	367.0	365.0	363.1	361.0	359.1	357.3	355.9	354.4	353.0	351.6



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	408.1	408.1	406.0	404.1	402.1	400.1	398.4	397.1	395.8	394.5	393.2
115°	469.0	467.1	465.5	463.8	462.2	460.6	459.3	458.2	457.1	456.0	454.9
117.5°	525.9	524.4	523.6	522.8	521.9	521.1	520.0	518.7	517.3	516.0	514.6
120°	563.0	561.5	561.0	560.4	559.9	559.4	558.2	556.6	555.0	553.3	551.7
122.5°	599.7	598.6	597.9	597.3	596.6	595.9	594.8	593.5	592.2	590.8	589.5
125°	651.4	651.0	650.3	649.5	648.9	648.2	647.0	645.6	644.2	642.7	641.2
127.5°	702.4	701.8	700.9	700.1	699.2	698.3	697.2	695.7	694.3	692.8	691.4
130°	733.1	732.4	731.6	731.0	730.3	729.5	728.5	727.0	725.5	724.1	722.7
132.5°	762.5	761.7	761.2	760.5	759.9	759.4	758.4	756.9	755.5	754.1	752.6
135°	807.0	806.5	805.8	805.0	804.3	803.6	802.7	801.6	800.5	799.4	798.3
137.5°	846.2	845.4	845.0	844.6	844.2	843.8	842.9	841.6	840.2	838.8	837.4
140°	871.5	870.7	870.3	869.7	869.1	868.6	867.8	866.7	865.6	864.5	863.4
142.5°	895.4	894.9	894.3	893.7	893.2	892.7	891.9	890.8	889.7	888.6	887.5
145°	928.9	928.5	928.1	927.8	927.5	927.1	926.3	925.0	923.7	922.5	921.2
147.5°	958.7	958.3	958.0	957.6	957.2	956.8	956.3	955.4	954.6	953.8	952.9
150°	976.9	976.6	976.2	975.8	975.4	975.1	974.6	974.1	973.5	973.1	972.5
152.5°	992.8	992.1	992.0	991.7	991.5	991.3	991.1	990.8	990.6	990.3	990.0
155°	1014.9	1014.0	1013.8	1013.6	1013.4	1013.3	1013.3	1013.7	1014.1	1014.4	1014.8
157.5°	1034.1	1033.0	1033.2	1033.4	1033.6	1033.7	1033.9	1033.9	1034.0	1034.0	1034.0
160°	1045.2	1044.1	1044.2	1044.5	1044.6	1044.8	1045.0	1045.2	1045.4	1045.5	1045.7
162.5°	1055.1	1053.9	1054.0	1054.2	1054.4	1054.6	1054.9	1055.4	1055.8	1056.3	1056.8
165°	1068.3	1066.9	1067.1	1067.2	1067.4	1067.6	1068.0	1068.5	1069.0	1069.6	1070.2
167.5°	1078.7	1077.3	1077.3	1077.3	1077.3	1077.3	1077.7	1078.4	1079.1	1079.9	1080.5
170°	1084.6	1083.1	1083.1	1083.1	1083.1	1083.1	1083.5	1084.3	1085.0	1085.7	1086.4
172.5°	1088.5	1087.0	1086.9	1086.8	1086.6	1086.5	1086.9	1087.7	1088.6	1089.5	1090.3
175°	1093.4	1092.1	1091.9	1091.8	1091.5	1091.4	1091.8	1092.7	1093.6	1094.5	1095.4
177.5°	1095.2	1094.1	1093.9	1093.8	1093.6	1093.5	1093.8	1094.5	1095.2	1095.9	1096.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	394.4	395.3	397.8	399.7	401.8	403.0	404.1	405.1	406.3	406.6	411.0
5°	396.2	400.0	406.7	411.6	417.7	424.3	428.8	431.0	436.5	441.0	450.1
7.5°	395.7	403.8	413.8	424.3	435.4	445.7	454.7	465.4	472.9	484.3	495.5
10°	395.3	406.1	419.0	432.3	447.8	462.3	475.2	489.7	501.7	517.4	530.8
12.5°	393.9	407.0	424.9	440.7	459.6	479.5	498.6	517.1	527.7	554.0	566.4
15°	390.5	406.1	428.5	452.4	478.4	502.0	526.3	545.7	577.0	600.0	614.7
17.5°	384.1	405.9	432.4	461.3	492.9	524.0	551.5	580.9	614.2	642.0	671.6
20°	381.0	405.0	434.6	466.5	499.4	534.5	565.8	601.1	637.4	664.8	702.8
22.5°	375.4	402.5	434.4	469.9	505.1	541.4	578.1	613.8	655.7	693.3	729.5
25°	366.2	396.6	429.7	469.4	510.5	547.0	590.9	638.2	681.8	730.3	766.4
27.5°	356.5	389.0	422.1	459.0	503.4	546.7	601.9	655.3	708.7	750.5	777.2
30°	349.1	380.7	414.8	452.1	495.9	547.4	609.1	667.4	719.5	755.4	770.4
32.5°	341.0	373.0	403.2	442.3	489.1	546.9	613.7	674.6	720.1	744.0	741.0
35°	328.4	355.1	384.7	422.2	477.3	543.6	616.4	675.2	703.1	698.0	659.3
37.5°	310.1	332.7	361.7	402.8	463.7	536.5	611.0	655.2	653.4	611.6	555.5
40°	298.8	318.0	345.8	389.1	453.0	532.0	602.7	631.4	607.1	548.7	481.5
42.5°	283.9	301.6	329.5	374.0	441.3	522.8	586.7	595.0	547.5	480.4	418.7
45°	260.8	276.4	305.2	351.2	423.7	502.6	547.8	527.4	463.4	394.1	347.2
47.5°	235.9	252.2	279.9	327.2	398.4	472.2	493.7	450.5	384.8	328.6	285.5
50°	220.3	235.9	263.1	310.7	381.2	447.3	456.2	400.4	340.0	290.6	255.3
52.5°	204.6	219.2	245.9	293.8	361.2	418.4	412.9	356.0	300.5	258.4	230.6
55°	181.0	194.9	220.3	265.1	326.5	371.9	352.0	297.7	251.7	219.0	197.9
57.5°	160.0	173.3	195.2	235.7	289.0	320.2	294.9	249.1	212.5	187.4	171.7
60°	145.7	157.4	178.4	216.0	262.3	286.0	261.0	220.5	189.7	169.6	155.6
62.5°	132.2	142.4	161.8	195.9	236.2	256.1	230.7	196.5	170.3	152.5	140.5
65°	111.7	121.0	138.1	164.7	197.7	211.0	189.1	161.4	141.1	127.8	119.8
67.5°	93.0	100.9	115.7	136.6	160.9	170.6	153.9	132.5	117.2	106.5	100.2
70°	80.6	87.4	99.0	117.0	139.0	146.4	130.9	113.2	102.0	93.4	87.6
72.5°	70.0	75.1	85.6	99.5	117.9	123.8	112.9	97.4	87.0	80.6	75.8
75°	53.4	57.6	64.4	75.6	88.3	91.7	83.6	73.9	66.9	62.3	58.7
77.5°	38.5	41.6	46.5	53.4	62.2	65.3	60.2	53.6	48.5	45.5	43.5
80°	29.0	31.6	35.7	41.4	46.7	48.4	45.4	40.4	36.9	35.1	33.4
82.5°	21.4	22.8	25.4	29.3	32.9	34.9	32.4	29.4	27.4	25.8	25.2
85°	10.8	11.6	12.7	14.3	16.6	17.3	16.3	15.6	14.4	13.5	13.5
87.5°	4.5	4.8	5.6	6.4	7.3	8.2	8.6	8.7	9.0	9.0	9.0
90°	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0
92.5°	14.6	14.1	13.6	13.1	13.8	15.5	17.3	19.1	20.9	22.0	23.2
95°	42.2	34.8	27.4	20.0	17.3	19.2	21.3	23.2	25.2	26.5	27.7
97.5°	96.4	93.1	89.8	86.4	78.3	65.3	52.3	39.2	26.2	27.6	29.1
100°	141.1	144.8	148.4	152.0	139.7	111.5	83.2	55.0	26.8	28.3	29.8
102.5°	183.1	185.7	188.3	190.9	176.8	146.0	115.2	84.4	53.6	49.1	44.6
105°	244.5	246.5	248.5	250.5	243.3	227.1	210.8	194.5	178.2	146.2	114.2
107.5°	309.6	311.1	312.7	314.3	316.4	318.9	321.6	324.1	326.7	303.2	279.7
110°	353.0	354.4	355.9	357.3	359.1	361.0	363.1	365.0	367.0	361.0	355.1





TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	394.5	395.8	397.1	398.4	400.1	402.1	404.1	406.0	408.1	408.1	408.2
115°	456.0	457.1	458.2	459.3	460.6	462.2	463.8	465.5	467.1	469.0	470.8
117.5°	516.0	517.3	518.7	520.0	521.1	521.9	522.8	523.6	524.4	525.9	527.3
120°	553.3	555.0	556.6	558.2	559.4	559.9	560.4	561.0	561.5	563.0	564.4
122.5°	590.8	592.2	593.5	594.8	595.9	596.6	597.3	597.9	598.6	599.7	600.6
125°	642.7	644.2	645.6	647.0	648.2	648.9	649.5	650.3	651.0	651.4	651.8
127.5°	692.8	694.3	695.7	697.2	698.3	699.2	700.1	700.9	701.8	702.4	703.0
130°	724.1	725.5	727.0	728.5	729.5	730.3	731.0	731.6	732.4	733.1	733.9
132.5°	754.1	755.5	756.9	758.4	759.4	759.9	760.5	761.2	761.7	762.5	763.1
135°	799.4	800.5	801.6	802.7	803.6	804.3	805.0	805.8	806.5	807.0	807.6
137.5°	838.8	840.2	841.6	842.9	843.8	844.2	844.6	845.0	845.4	846.2	847.1
140°	864.5	865.6	866.7	867.8	868.6	869.1	869.7	870.3	870.7	871.5	872.2
142.5°	888.6	889.7	890.8	891.9	892.7	893.2	893.7	894.3	894.9	895.4	896.0
145°	922.5	923.7	925.0	926.3	927.1	927.5	927.8	928.1	928.5	928.9	929.3
147.5°	953.8	954.6	955.4	956.3	956.8	957.2	957.6	958.0	958.3	958.7	959.0
150°	973.1	973.5	974.1	974.6	975.1	975.4	975.8	976.2	976.6	976.9	977.3
152.5°	990.3	990.6	990.8	991.1	991.3	991.5	991.7	992.0	992.1	992.8	993.4
155°	1014.4	1014.1	1013.7	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9	1015.8
157.5°	1034.0	1034.0	1033.9	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1	1035.2
160°	1045.5	1045.4	1045.2	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2	1046.3
162.5°	1056.3	1055.8	1055.4	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1	1056.3
165°	1069.6	1069.0	1068.5	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3	1069.8
167.5°	1079.9	1079.1	1078.4	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7	1080.2
170°	1085.7	1085.0	1084.3	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6	1086.1
172.5°	1089.5	1088.6	1087.7	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5	1090.0
175°	1094.5	1093.6	1092.7	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4	1094.6
177.5°	1095.9	1095.2	1094.5	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2	1096.3
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	412.5	412.7	414.3	415.6	415.0	415.7	416.0
5°	450.7	457.5	461.1	463.8	464.0	464.2	465.7
7.5°	504.8	512.2	517.6	525.7	528.1	530.8	530.1
10°	544.4	555.2	564.5	569.4	574.8	582.5	576.3
12.5°	581.3	600.5	614.7	622.3	627.3	628.8	625.8
15°	642.2	667.2	680.7	680.4	697.4	704.8	693.2
17.5°	698.0	721.1	739.7	749.2	763.4	766.5	765.2
20°	732.2	757.5	771.9	788.2	795.7	802.3	803.4
22.5°	761.7	784.4	799.9	813.4	819.6	822.8	824.7
25°	792.1	809.9	819.2	823.9	825.7	825.2	822.8
27.5°	789.9	791.3	781.1	771.0	762.0	751.9	748.4
30°	769.4	753.5	725.0	708.8	685.1	666.3	673.9
32.5°	715.5	683.7	651.8	616.4	587.3	578.9	570.5
35°	610.7	554.8	522.1	484.1	469.0	453.8	443.3
37.5°	494.0	450.9	412.1	387.3	372.0	362.4	357.3
40°	427.1	388.2	356.3	336.1	324.6	313.8	312.3
42.5°	373.8	337.6	313.6	297.6	286.5	281.8	278.5
45°	306.1	281.0	264.8	253.4	246.0	243.1	239.3
47.5°	259.2	241.3	229.2	221.4	215.8	213.7	213.4
50°	232.8	218.0	209.1	203.0	198.7	197.9	194.9
52.5°	213.1	200.2	193.3	188.0	184.8	182.7	181.8
55°	185.0	176.4	170.2	167.1	164.7	162.6	162.6
57.5°	161.8	154.7	150.6	148.0	147.2	145.8	144.8
60°	147.6	141.5	138.3	136.0	134.4	134.7	133.0
62.5°	133.6	129.6	126.5	124.3	122.5	122.5	122.6
65°	113.7	110.7	108.4	107.7	106.6	105.3	105.6
67.5°	96.4	93.6	91.8	90.5	90.1	89.4	90.5
70°	84.0	81.9	80.6	79.4	79.0	79.2	80.1
72.5°	72.6	71.1	70.2	69.7	68.8	68.9	69.5
75°	57.0	55.8	55.1	54.5	54.3	54.3	54.3
77.5°	41.8	41.6	41.3	40.4	40.4	40.7	40.7
80°	33.0	32.4	32.3	31.9	31.3	31.0	31.9
82.5°	24.7	24.1	24.0	23.9	23.0	22.9	23.7
85°	13.3	12.7	12.9	12.7	12.7	12.6	12.6
87.5°	9.0	9.0	9.0	9.2	9.1	9.0	9.5
90°	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	24.3	25.4	26.2	26.3	26.6	26.8	27.0
95°	29.0	30.3	30.9	30.9	30.9	30.9	30.9
97.5°	30.6	32.0	32.8	33.0	33.2	33.3	33.5
100°	31.2	32.6	33.4	33.7	33.8	34.0	34.2
102.5°	40.1	35.6	33.5	33.8	34.2	34.5	34.8
105°	82.2	50.2	34.3	34.7	35.1	35.5	35.8
107.5°	256.2	232.8	209.0	184.8	160.7	136.6	112.4
110°	349.1	343.2	327.3	301.3	275.5	249.6	223.8



TEST NUMBER: P331892-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	408.4	408.5	405.8	400.3	394.8	389.4	383.9
115°	472.5	474.3	475.6	476.3	477.0	477.8	478.5
117.5°	528.7	530.2	531.0	531.2	531.2	531.4	531.6
120°	565.8	567.3	568.0	568.0	568.0	568.0	568.0
122.5°	601.7	602.7	603.2	603.4	603.6	603.6	603.8
125°	652.1	652.5	652.8	653.2	653.5	654.0	654.3
127.5°	703.5	704.1	704.3	703.8	703.5	703.1	702.8
130°	734.6	735.3	735.5	735.2	734.7	734.4	734.0
132.5°	763.9	764.6	764.7	764.2	763.7	763.2	762.7
135°	808.1	808.6	808.6	808.1	807.6	807.0	806.5
137.5°	848.0	848.8	849.1	848.7	848.4	848.0	847.7
140°	872.9	873.7	873.8	873.4	873.1	872.8	872.4
142.5°	896.6	897.2	897.2	896.7	896.2	895.7	895.2
145°	929.6	930.0	930.2	930.2	930.2	930.2	930.2
147.5°	959.4	959.8	959.5	958.7	957.9	957.0	956.2
150°	977.6	978.0	977.9	977.4	976.8	976.2	975.8
152.5°	994.1	994.7	994.7	993.8	993.0	992.2	991.3
155°	1016.7	1017.6	1017.5	1016.4	1015.4	1014.2	1013.2
157.5°	1036.2	1037.4	1037.2	1035.8	1034.4	1033.0	1031.6
160°	1047.3	1048.4	1048.3	1047.1	1045.8	1044.6	1043.3
162.5°	1057.5	1058.7	1058.8	1057.7	1056.5	1055.5	1054.3
165°	1071.2	1072.7	1072.8	1071.5	1070.2	1068.9	1067.7
167.5°	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3
170°	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1
172.5°	1091.4	1092.8	1092.7	1091.2	1089.6	1088.0	1086.4
175°	1095.9	1097.1	1097.1	1095.6	1094.2	1092.7	1091.3
177.5°	1097.6	1098.7	1098.5	1097.1	1095.7	1094.2	1092.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4

(END OF REPORT)