

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332051-927

Luminaire Tested: **S123DIP-S1165D365U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332051-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D365U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4918.5 lumens  
Efficiency: N/A  
Efficacy: 98.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332051-927

CATALOG NUMBER: S123DIP-S1165D365U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332051-927

CATALOG NUMBER: S123DIP-S1165D365U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	69	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57	54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49	46
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	50	45	42	39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	38	48	41	36	44	39	34	41	36	32	30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15588	15588	15588
5°	15662	15446	15554
10°	15557	15312	15407
15°	15375	15139	15166
20°	15163	14892	14905
25°	14878	14598	14567
30°	14564	14270	14162
35°	14236	13925	13745
40°	13893	13543	13333
45°	13516	13192	12871
50°	13137	12762	12407
55°	12643	12314	11941
60°	12144	11795	11418
65°	11703	11227	10878
70°	11053	10581	10112
75°	10098	9736	9320
80°	9106	8722	8647
85°	7991	7694	7385



TEST NUMBER: P332051-927

CATALOG NUMBER: S123DIP-S1165D365U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.4	2.8
10°-20°	385.2	7.8
20°-30°	569.0	11.6
30°-40°	664.6	13.5
40°-50°	668.2	13.6
50°-60°	587.0	11.9
60°-70°	437.3	8.9
70°-80°	249.1	5.1
80°-90°	72.6	1.5
90°-100°	13.7	0.3
100°-110°	65.3	1.3
110°-120°	156.8	3.2
120°-130°	199.7	4.1
130°-140°	213.4	4.3
140°-150°	199.5	4.1
150°-160°	160.9	3.3
160°-170°	103.9	2.1
170°-180°	35.8	0.7
0°-30°	1090.6	22.2
0°-40°	1755.3	35.7
0°-60°	3010.4	61.2
0°-90°	3769.4	76.6
90°-120°	235.8	4.8
90°-150°	848.4	17.2
90°-180°	1149.0	23.4
0°-180°	4918.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1448	1448	1448	1448	1448	
5°	1450	1443	1430	1441	1440	137
15°	1380	1374	1358	1368	1361	389
25°	1253	1245	1229	1230	1226	577
35°	1083	1075	1060	1052	1046	677
45°	888	882	867	852	846	685
55°	674	672	656	643	636	603
65°	460	453	441	431	427	453
75°	243	238	234	228	224	260
85°	65	62	62	60	60	71
90°	0	3	7	8	8	4
95°	17	6	9	11	11	21
105°	83	85	61	15	12	88
115°	156	158	161	163	165	154
125°	221	223	224	224	225	197
135°	275	276	277	278	277	211
145°	317	319	319	320	320	198
155°	349	349	349	350	348	161
165°	368	367	367	369	367	104
175°	377	376	376	377	375	36
180°	377	377	377	377	377	



TEST NUMBER: P332051-927

CATALOG NUMBER: S123DIP-S1165D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1453.2	1452.3	1451.4	1450.6	1449.6	1448.0	1445.6	1443.1	1440.7	1438.2	1440.4
5°	1449.5	1448.1	1446.7	1445.3	1443.9	1441.7	1438.7	1435.6	1432.6	1429.5	1432.3
7.5°	1435.3	1433.8	1432.5	1431.1	1429.7	1427.4	1424.3	1421.2	1418.0	1414.8	1417.3
10°	1423.3	1421.9	1420.5	1419.1	1417.8	1415.3	1411.7	1408.1	1404.5	1400.9	1403.4
12.5°	1407.4	1406.2	1405.0	1403.9	1402.7	1400.4	1397.1	1393.7	1390.3	1387.0	1388.8
15°	1379.7	1378.6	1377.5	1376.4	1375.3	1372.9	1369.4	1365.7	1362.2	1358.5	1360.7
17.5°	1347.6	1346.2	1344.7	1343.3	1341.8	1339.3	1335.7	1332.1	1328.5	1324.9	1326.5
20°	1323.7	1322.0	1320.3	1318.7	1317.1	1314.4	1310.8	1307.3	1303.6	1300.1	1301.2
22.5°	1296.8	1295.1	1293.5	1291.8	1290.1	1287.5	1283.9	1280.3	1276.8	1273.1	1274.0
25°	1252.7	1251.0	1249.4	1247.7	1246.1	1243.4	1239.8	1236.3	1232.6	1229.1	1229.3
27.5°	1205.6	1204.0	1202.5	1200.8	1199.2	1196.5	1192.6	1188.7	1184.9	1181.0	1181.2
30°	1171.8	1170.4	1169.0	1167.6	1166.3	1163.6	1159.8	1155.9	1152.0	1148.1	1148.1
32.5°	1137.9	1136.1	1134.2	1132.4	1130.6	1128.1	1125.2	1122.2	1119.2	1116.3	1114.7
35°	1083.4	1081.7	1080.1	1078.4	1076.7	1074.1	1070.5	1066.9	1063.3	1059.7	1058.0
37.5°	1027.5	1025.5	1023.3	1021.3	1019.1	1016.3	1012.6	1009.0	1005.4	1001.6	999.7
40°	988.7	987.1	985.4	983.7	982.1	979.3	975.4	971.5	967.7	963.8	961.6
42.5°	949.8	948.0	946.1	944.2	942.3	939.4	935.6	931.7	927.8	924.0	921.8
45°	887.9	886.8	885.7	884.6	883.4	881.1	877.5	873.9	870.3	866.6	863.4
47.5°	826.3	824.7	823.2	821.5	819.9	817.5	814.0	810.6	807.3	803.9	800.7
50°	784.5	783.2	781.7	780.4	779.0	776.5	772.9	769.3	765.6	762.1	759.1
52.5°	740.7	739.7	738.8	737.8	736.9	734.5	730.7	726.9	723.1	719.2	716.6
55°	673.7	673.4	673.1	672.9	672.6	670.7	667.0	663.5	659.8	656.2	653.2
57.5°	609.9	609.0	608.0	607.1	606.2	604.3	601.3	598.5	595.6	592.7	590.0
60°	564.1	563.8	563.6	563.2	563.0	561.2	557.9	554.5	551.2	547.9	545.4
62.5°	523.2	522.5	521.8	521.1	520.4	518.3	515.0	511.7	508.4	505.1	502.6
65°	459.5	458.1	456.7	455.3	453.9	451.9	449.1	446.3	443.5	440.8	438.6
67.5°	392.0	390.8	389.6	388.3	387.1	385.5	383.3	381.3	379.1	377.1	375.1
70°	351.2	349.5	347.8	346.2	344.5	342.9	341.2	339.5	337.9	336.2	334.3
72.5°	308.3	307.1	305.9	304.7	303.5	301.9	300.0	298.1	296.3	294.4	292.6
75°	242.8	241.7	240.6	239.5	238.4	237.4	236.6	235.8	235.0	234.1	232.7
77.5°	184.8	184.2	183.5	183.0	182.4	181.6	180.5	179.6	178.6	177.6	176.7
80°	146.9	146.1	145.3	144.4	143.6	142.9	142.4	141.8	141.2	140.7	140.5
82.5°	110.1	109.9	109.7	109.6	109.4	109.2	109.2	109.1	108.9	108.8	108.4
85°	64.7	64.2	63.6	63.1	62.5	62.3	62.3	62.3	62.3	62.3	61.7
87.5°	26.0	25.4	24.9	24.3	23.8	23.5	23.4	23.4	23.3	23.3	23.1
90°	0.3	0.9	1.5	2.1	2.8	3.5	4.3	5.1	5.9	6.7	7.0
92.5°	5.2	5.1	4.8	4.7	4.5	4.8	5.3	5.9	6.6	7.1	7.5
95°	17.1	14.5	12.0	9.4	6.9	5.9	6.7	7.3	8.0	8.7	9.1
97.5°	34.3	33.2	32.0	30.9	29.7	26.9	22.4	18.0	13.5	9.0	9.5
100°	47.3	48.6	49.8	51.0	52.3	48.1	38.3	28.7	18.9	9.3	9.7
102.5°	62.1	63.0	63.8	64.8	65.7	60.8	50.2	39.6	29.0	18.5	16.9
105°	83.4	84.1	84.8	85.5	86.2	83.7	78.1	72.5	66.9	61.3	50.3
107.5°	105.9	106.5	107.0	107.6	108.1	108.8	109.7	110.6	111.5	112.3	104.3
110°	121.0	121.4	121.9	122.4	122.9	123.5	124.2	124.8	125.6	126.3	124.2



TEST NUMBER: P332051-927

CATALOG NUMBER: S123DIP-S1165D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	135.2	135.7	136.2	136.6	137.0	137.6	138.3	139.0	139.7	140.4	140.4
115°	156.5	156.9	157.2	157.6	158.0	158.4	159.0	159.5	160.1	160.7	161.3
117.5°	177.1	177.5	177.9	178.4	178.9	179.3	179.5	179.8	180.1	180.4	180.9
120°	189.8	190.4	190.9	191.5	192.0	192.4	192.6	192.8	193.0	193.1	193.7
122.5°	202.8	203.3	203.7	204.1	204.6	204.9	205.2	205.4	205.7	205.9	206.3
125°	220.6	221.1	221.6	222.0	222.6	222.9	223.2	223.5	223.7	223.9	224.1
127.5°	237.8	238.4	238.8	239.3	239.8	240.2	240.5	240.8	241.1	241.4	241.6
130°	248.6	249.1	249.5	250.1	250.6	251.0	251.2	251.4	251.7	251.9	252.2
132.5°	258.9	259.4	259.9	260.4	260.9	261.2	261.4	261.7	261.8	262.1	262.3
135°	274.6	275.0	275.4	275.8	276.1	276.4	276.6	276.9	277.2	277.4	277.6
137.5°	288.0	288.5	289.0	289.5	289.9	290.3	290.4	290.5	290.7	290.8	291.1
140°	297.0	297.4	297.8	298.1	298.5	298.8	299.0	299.1	299.4	299.5	299.8
142.5°	305.3	305.7	306.0	306.4	306.8	307.0	307.3	307.4	307.6	307.8	308.0
145°	316.9	317.3	317.7	318.2	318.6	318.9	319.0	319.2	319.2	319.4	319.6
147.5°	327.8	328.1	328.4	328.7	328.9	329.2	329.3	329.4	329.5	329.6	329.8
150°	334.5	334.7	334.9	335.1	335.3	335.4	335.6	335.6	335.8	335.9	336.0
152.5°	340.6	340.6	340.7	340.8	340.9	341.0	341.0	341.1	341.2	341.3	341.5
155°	349.1	349.0	348.8	348.7	348.6	348.6	348.6	348.6	348.7	348.8	349.1
157.5°	355.7	355.7	355.7	355.6	355.6	355.6	355.5	355.5	355.4	355.4	355.7
160°	359.7	359.7	359.6	359.5	359.5	359.4	359.3	359.3	359.3	359.2	359.5
162.5°	363.5	363.4	363.2	363.1	362.9	362.7	362.7	362.7	362.6	362.5	362.9
165°	368.1	367.9	367.7	367.6	367.3	367.3	367.2	367.1	367.0	367.0	367.5
167.5°	371.7	371.5	371.2	371.0	370.7	370.6	370.6	370.6	370.6	370.6	371.1
170°	373.7	373.4	373.2	373.0	372.7	372.6	372.6	372.6	372.6	372.6	373.1
172.5°	375.0	374.8	374.5	374.1	373.8	373.8	373.8	373.8	373.9	373.9	374.5
175°	376.8	376.4	376.1	375.9	375.6	375.4	375.5	375.6	375.6	375.7	376.1
177.5°	377.2	377.0	376.8	376.5	376.2	376.1	376.2	376.2	376.3	376.4	376.8
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8



TEST NUMBER: P332051-927

CATALOG NUMBER: S123DIP-S1165D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1442.6	1444.9	1447.1	1448.1	1447.9	1447.6	1447.4	1447.2
5°	1435.0	1437.8	1440.6	1441.7	1441.1	1440.6	1440.0	1439.5
7.5°	1419.8	1422.3	1424.8	1425.8	1425.5	1425.2	1424.9	1424.6
10°	1405.9	1408.3	1410.9	1411.8	1411.3	1410.7	1410.2	1409.6
12.5°	1390.6	1392.4	1394.2	1395.0	1394.6	1394.3	1394.0	1393.7
15°	1362.9	1365.2	1367.4	1367.7	1366.0	1364.4	1362.7	1361.0
17.5°	1328.0	1329.6	1331.1	1331.6	1331.0	1330.4	1329.8	1329.2
20°	1302.3	1303.4	1304.5	1304.6	1303.8	1302.9	1302.1	1301.2
22.5°	1274.9	1275.8	1276.7	1276.6	1275.6	1274.5	1273.4	1272.4
25°	1229.6	1229.9	1230.2	1229.9	1229.1	1228.2	1227.4	1226.5
27.5°	1181.5	1181.6	1181.9	1181.5	1180.4	1179.3	1178.3	1177.3
30°	1148.1	1148.1	1148.1	1147.2	1145.2	1143.3	1141.3	1139.4
32.5°	1113.1	1111.6	1110.0	1108.7	1107.7	1106.6	1105.6	1104.5
35°	1056.4	1054.7	1053.0	1051.5	1050.1	1048.8	1047.3	1046.0
37.5°	997.7	995.7	993.7	992.3	991.3	990.5	989.6	988.7
40°	959.4	957.2	955.0	953.3	952.2	951.1	950.0	948.9
42.5°	919.6	917.3	915.1	913.5	912.4	911.2	910.1	909.0
45°	860.1	856.7	853.4	851.0	849.7	848.3	846.9	845.5
47.5°	797.4	794.2	790.8	788.6	787.4	786.2	785.0	783.8
50°	756.0	753.0	749.9	747.6	745.9	744.3	742.6	740.9
52.5°	714.1	711.5	708.8	706.7	705.0	703.4	701.7	700.1
55°	650.1	647.1	644.0	641.8	640.5	639.1	637.7	636.3
57.5°	587.3	584.6	581.9	579.7	578.1	576.6	574.9	573.3
60°	543.0	540.4	538.0	536.0	534.6	533.2	531.9	530.4
62.5°	500.1	497.6	495.1	493.4	492.4	491.5	490.6	489.6
65°	436.4	434.2	432.0	430.5	429.6	428.8	427.9	427.1
67.5°	373.2	371.2	369.3	367.7	366.6	365.4	364.2	363.1
70°	332.3	330.4	328.4	326.8	325.4	324.0	322.7	321.3
72.5°	291.0	289.2	287.5	286.3	285.6	284.9	284.2	283.4
75°	231.3	230.0	228.5	227.4	226.6	225.8	225.0	224.1
77.5°	175.7	174.8	173.8	173.3	173.3	173.3	173.3	173.3
80°	140.1	139.9	139.6	139.5	139.5	139.5	139.5	139.5
82.5°	107.8	107.3	106.9	106.5	106.2	106.1	105.8	105.6
85°	61.2	60.6	60.0	59.8	59.8	59.8	59.8	59.8
87.5°	22.9	22.7	22.6	22.5	22.5	22.6	22.6	22.6
90°	7.2	7.4	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	8.0	8.4	8.8	9.0	9.0	9.1	9.2	9.3
95°	9.6	10.0	10.5	10.6	10.6	10.6	10.6	10.6
97.5°	10.0	10.5	11.0	11.2	11.3	11.4	11.5	11.6
100°	10.2	10.7	11.2	11.5	11.6	11.6	11.7	11.7
102.5°	15.4	13.8	12.3	11.6	11.6	11.7	11.9	12.0
105°	39.3	28.3	17.3	11.8	12.0	12.0	12.2	12.3
107.5°	96.3	88.2	80.1	71.9	63.6	55.3	47.0	38.7
110°	122.2	120.1	118.0	112.6	103.7	94.7	85.9	77.0





TEST NUMBER: P332051-927

CATALOG NUMBER: S123DIP-S1165D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	140.5	140.5	140.5	139.6	137.7	135.9	134.0	132.1
115°	161.9	162.6	163.2	163.6	163.8	164.1	164.4	164.6
117.5°	181.4	181.9	182.4	182.7	182.7	182.8	182.8	182.8
120°	194.2	194.6	195.1	195.4	195.4	195.4	195.4	195.4
122.5°	206.6	207.0	207.3	207.5	207.6	207.6	207.6	207.7
125°	224.2	224.3	224.4	224.6	224.7	224.8	225.0	225.1
127.5°	241.8	242.0	242.2	242.2	242.1	242.0	241.9	241.8
130°	252.5	252.7	252.9	253.0	252.9	252.8	252.6	252.5
132.5°	262.5	262.8	263.0	263.1	262.8	262.7	262.5	262.4
135°	277.8	278.0	278.1	278.1	278.0	277.8	277.6	277.4
137.5°	291.4	291.7	292.0	292.1	291.9	291.8	291.7	291.6
140°	300.0	300.2	300.6	300.6	300.5	300.3	300.2	300.1
142.5°	308.2	308.4	308.6	308.6	308.5	308.2	308.1	307.9
145°	319.6	319.8	319.9	320.0	320.0	320.0	320.0	320.0
147.5°	329.9	330.0	330.2	330.1	329.8	329.5	329.2	328.9
150°	336.2	336.3	336.4	336.4	336.2	336.0	335.8	335.6
152.5°	341.7	342.0	342.2	342.1	341.9	341.6	341.3	341.0
155°	349.4	349.7	350.1	350.0	349.7	349.3	348.9	348.5
157.5°	356.1	356.5	356.9	356.8	356.3	355.8	355.3	354.8
160°	359.9	360.3	360.7	360.6	360.2	359.7	359.3	358.9
162.5°	363.4	363.8	364.2	364.2	363.8	363.5	363.1	362.7
165°	368.0	368.5	369.0	369.0	368.6	368.1	367.7	367.3
167.5°	371.5	372.1	372.6	372.6	372.1	371.5	371.1	370.6
170°	373.6	374.1	374.5	374.5	374.1	373.6	373.1	372.6
172.5°	374.9	375.4	375.9	375.9	375.3	374.8	374.2	373.7
175°	376.5	377.0	377.4	377.4	376.9	376.4	375.9	375.4
177.5°	377.2	377.6	378.0	377.9	377.4	376.9	376.4	375.9
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8

(END OF REPORT)