

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331902-930

Luminaire Tested: **S123DIP-S340D1195U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331902-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1195U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4527.9 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	88	85	81	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	68	61	55	50	48	44	40	35	33	31	24	22	21	16
4	70	60	53	47	63	54	48	43	42	38	34	32	29	26	21	20	18	14
5	65	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	18	16	14	11
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	12	10
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4219	4219	4219	4219
5°	5032	4238	3756	4238
10°	6299	4217	3393	4217
15°	7725	4182	3158	4182
20°	9203	4129	3007	4129
25°	9772	4065	2973	4065
30°	8376	4018	2988	4018
35°	5825	3951	3020	3951
40°	4388	3873	3011	3873
45°	3643	3755	2973	3755
50°	3264	3518	2946	3518
55°	3051	3262	2909	3262
60°	2863	2992	2878	2992
65°	2690	2728	2786	2728
70°	2521	2426	2653	2426
75°	2258	2125	2433	2125
80°	1977	1742	2095	1742
85°	1556	1272	1408	1272



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.6	0.9
10°-20°	123.8	2.7
20°-30°	207.8	4.6
30°-40°	235.3	5.2
40°-50°	211.0	4.7
50°-60°	170.3	3.8
60°-70°	118.7	2.6
70°-80°	62.4	1.4
80°-90°	18.8	0.4
90°-100°	78.6	1.7
100°-110°	235.1	5.2
110°-120°	399.9	8.8
120°-130°	526.0	11.6
130°-140°	591.2	13.1
140°-150°	581.2	12.8
150°-160°	489.3	10.8
160°-170°	325.7	7.2
170°-180°	114.0	2.5
0°-30°	370.3	8.2
0°-40°	605.6	13.4
0°-60°	986.9	21.8
0°-90°	1186.8	26.2
90°-120°	713.6	15.8
90°-150°	2412.1	53.3
90°-180°	3341.0	73.8
0°-180°	4527.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	392	392	392	392	392	
5°	466	392	348	392	466	48
15°	693	375	283	375	693	200
25°	823	342	250	342	823	361
35°	443	301	230	301	443	288
45°	239	247	195	247	239	189
55°	163	174	155	174	163	146
65°	106	107	109	107	106	105
75°	54	51	58	51	54	58
85°	13	10	11	10	13	16
90°	28	1	28	1	28	14
95°	74	56	74	56	74	76
105°	225	213	225	213	225	239
115°	404	403	404	403	404	400
125°	583	589	583	589	583	521
135°	764	764	764	764	764	587
145°	927	927	927	927	927	579
155°	1060	1062	1060	1062	1060	488
165°	1153	1157	1153	1157	1153	325
175°	1198	1203	1198	1203	1198	114
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	416.0	415.7	415.0	415.6	414.3	412.7	412.5	411.0	406.6	406.3	405.1
5°	465.7	464.2	464.0	463.8	461.1	457.5	450.7	450.1	441.0	436.5	431.0
7.5°	530.1	530.8	528.1	525.7	517.6	512.2	504.8	495.5	484.3	472.9	465.4
10°	576.3	582.5	574.8	569.4	564.5	555.2	544.4	530.8	517.4	501.7	489.7
12.5°	625.8	628.8	627.3	622.3	614.7	600.5	581.3	566.4	554.0	527.7	517.1
15°	693.2	704.8	697.4	680.4	680.7	667.2	642.2	614.7	600.0	577.0	545.7
17.5°	765.2	766.5	763.4	749.2	739.7	721.1	698.0	671.6	642.0	614.2	580.9
20°	803.4	802.3	795.7	788.2	771.9	757.5	732.2	702.8	664.8	637.4	601.1
22.5°	824.7	822.8	819.6	813.4	799.9	784.4	761.7	729.5	693.3	655.7	613.8
25°	822.8	825.2	825.7	823.9	819.2	809.9	792.1	766.4	730.3	681.8	638.2
27.5°	748.4	751.9	762.0	771.0	781.1	791.3	789.9	777.2	750.5	708.7	655.3
30°	673.9	666.3	685.1	708.8	725.0	753.5	769.4	770.4	755.4	719.5	667.4
32.5°	570.5	578.9	587.3	616.4	651.8	683.7	715.5	741.0	744.0	720.1	674.6
35°	443.3	453.8	469.0	484.1	522.1	554.8	610.7	659.3	698.0	703.1	675.2
37.5°	357.3	362.4	372.0	387.3	412.1	450.9	494.0	555.5	611.6	653.4	655.2
40°	312.3	313.8	324.6	336.1	356.3	388.2	427.1	481.5	548.7	607.1	631.4
42.5°	278.5	281.8	286.5	297.6	313.6	337.6	373.8	418.7	480.4	547.5	595.0
45°	239.3	243.1	246.0	253.4	264.8	281.0	306.1	347.2	394.1	463.4	527.4
47.5°	213.4	213.7	215.8	221.4	229.2	241.3	259.2	285.5	328.6	384.8	450.5
50°	194.9	197.9	198.7	203.0	209.1	218.0	232.8	255.3	290.6	340.0	400.4
52.5°	181.8	182.7	184.8	188.0	193.3	200.2	213.1	230.6	258.4	300.5	356.0
55°	162.6	162.6	164.7	167.1	170.2	176.4	185.0	197.9	219.0	251.7	297.7
57.5°	144.8	145.8	147.2	148.0	150.6	154.7	161.8	171.7	187.4	212.5	249.1
60°	133.0	134.7	134.4	136.0	138.3	141.5	147.6	155.6	169.6	189.7	220.5
62.5°	122.6	122.5	122.5	124.3	126.5	129.6	133.6	140.5	152.5	170.3	196.5
65°	105.6	105.3	106.6	107.7	108.4	110.7	113.7	119.8	127.8	141.1	161.4
67.5°	90.5	89.4	90.1	90.5	91.8	93.6	96.4	100.2	106.5	117.2	132.5
70°	80.1	79.2	79.0	79.4	80.6	81.9	84.0	87.6	93.4	102.0	113.2
72.5°	69.5	68.9	68.8	69.7	70.2	71.1	72.6	75.8	80.6	87.0	97.4
75°	54.3	54.3	54.3	54.5	55.1	55.8	57.0	58.7	62.3	66.9	73.9
77.5°	40.7	40.7	40.4	40.4	41.3	41.6	41.8	43.5	45.5	48.5	53.6
80°	31.9	31.0	31.3	31.9	32.3	32.4	33.0	33.4	35.1	36.9	40.4
82.5°	23.7	22.9	23.0	23.9	24.0	24.1	24.7	25.2	25.8	27.4	29.4
85°	12.6	12.6	12.7	12.7	12.9	12.7	13.3	13.5	13.5	14.4	15.6
87.5°	10.3	9.9	9.9	10.0	9.8	9.8	9.8	9.8	9.7	9.7	9.3
90°	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.5	23.6	22.7	20.0
92.5°	38.2	38.5	38.8	39.1	39.3	39.1	38.4	37.7	37.0	36.4	34.8
95°	73.9	73.9	73.9	73.9	73.9	73.5	72.6	71.7	70.9	70.1	68.4
97.5°	113.7	113.7	113.8	113.9	114.0	113.6	112.6	111.6	110.6	109.7	108.4
100°	144.0	143.6	143.2	142.8	142.3	141.8	141.1	140.5	139.9	139.3	138.2
102.5°	175.0	175.1	175.2	175.3	175.4	175.1	174.5	173.8	173.3	172.6	171.2
105°	225.4	225.0	224.6	224.2	223.8	223.6	223.6	223.6	223.6	223.6	221.7
107.5°	277.9	278.2	278.4	278.7	278.9	278.8	278.1	277.4	276.7	276.1	275.2
110°	313.6	314.0	314.4	314.8	315.2	315.0	314.2	313.3	312.5	311.7	311.2



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.5	351.6	351.6	351.7	351.8	351.3	350.3	349.3	348.3	347.2	347.2
115°	403.6	403.7	404.0	404.1	404.4	404.4	404.1	404.0	403.7	403.6	404.0
117.5°	456.4	457.0	457.5	458.2	458.8	459.1	459.1	459.2	459.2	459.3	459.8
120°	493.5	494.0	494.4	494.8	495.2	495.5	495.8	495.9	496.2	496.4	497.4
122.5°	529.1	529.7	530.4	530.9	531.5	532.1	532.6	533.2	533.7	534.3	534.8
125°	582.6	583.4	584.2	585.1	586.0	586.8	587.7	588.5	589.3	590.2	590.6
127.5°	635.9	636.7	637.7	638.7	639.7	640.7	642.0	643.1	644.3	645.5	646.0
130°	670.7	672.1	673.6	675.1	676.5	677.8	678.6	679.4	680.3	681.1	681.8
132.5°	707.0	708.2	709.3	710.5	711.6	712.7	713.7	714.7	715.7	716.7	717.1
135°	763.5	763.9	764.3	764.8	765.2	765.8	766.6	767.5	768.3	769.2	769.4
137.5°	813.3	814.2	815.0	815.7	816.5	817.3	818.2	819.1	820.0	820.9	820.4
140°	846.0	847.4	848.9	850.4	851.8	852.6	852.9	853.0	853.3	853.5	853.3
142.5°	879.3	880.4	881.5	882.6	883.8	884.5	884.7	884.9	885.1	885.3	884.9
145°	927.4	928.2	929.0	929.9	930.7	931.3	931.5	931.7	931.9	932.1	931.5
147.5°	970.2	971.4	972.7	974.0	975.3	975.9	975.9	975.9	975.9	975.9	975.3
150°	997.5	998.7	1000.0	1001.3	1002.6	1003.1	1003.1	1003.1	1003.1	1003.1	1002.7
152.5°	1024.0	1025.1	1026.2	1027.3	1028.4	1028.7	1028.4	1028.1	1027.8	1027.4	1027.2
155°	1060.0	1061.5	1063.0	1064.5	1065.9	1066.2	1065.4	1064.5	1063.7	1062.8	1062.7
157.5°	1092.7	1094.0	1095.1	1096.3	1097.5	1097.6	1096.7	1095.8	1095.0	1094.1	1094.0
160°	1114.0	1114.8	1115.7	1116.6	1117.4	1117.3	1116.2	1115.2	1114.1	1113.0	1113.0
162.5°	1129.9	1131.2	1132.6	1133.9	1135.3	1135.5	1134.4	1133.3	1132.3	1131.2	1131.1
165°	1152.8	1154.3	1155.8	1157.2	1158.7	1158.9	1157.6	1156.3	1155.0	1153.8	1153.8
167.5°	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3	1172.2
170°	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2	1182.2
172.5°	1189.8	1191.2	1192.7	1194.2	1195.7	1195.8	1194.5	1193.2	1191.9	1190.6	1190.6
175°	1198.3	1199.8	1201.3	1202.7	1204.2	1204.3	1203.1	1201.8	1200.5	1199.2	1199.2
177.5°	1202.9	1204.0	1205.2	1206.4	1207.5	1207.6	1206.6	1205.7	1204.6	1203.6	1203.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	404.1	403.0	401.8	399.7	397.8	395.3	394.4	393.5	390.8	388.4	386.5
5°	428.8	424.3	417.7	411.6	406.7	400.0	396.2	392.2	386.5	381.4	377.2
7.5°	454.7	445.7	435.4	424.3	413.8	403.8	395.7	388.5	380.5	373.0	367.0
10°	475.2	462.3	447.8	432.3	419.0	406.1	395.3	385.8	375.5	366.6	359.1
12.5°	498.6	479.5	459.6	440.7	424.9	407.0	393.9	381.8	370.1	359.5	351.1
15°	526.3	502.0	478.4	452.4	428.5	406.1	390.5	375.3	361.8	350.8	340.1
17.5°	551.5	524.0	492.9	461.3	432.4	405.9	384.1	366.9	350.0	336.6	326.0
20°	565.8	534.5	499.4	466.5	434.6	405.0	381.0	360.5	342.3	328.0	316.1
22.5°	578.1	541.4	505.1	469.9	434.4	402.5	375.4	354.2	334.5	320.6	307.9
25°	590.9	547.0	510.5	469.4	429.7	396.6	366.2	342.3	322.5	306.1	293.1
27.5°	601.9	546.7	503.4	459.0	422.1	389.0	356.5	330.8	309.9	292.1	278.8
30°	609.1	547.4	495.9	452.1	414.8	380.7	349.1	323.3	301.3	283.2	270.7
32.5°	613.7	546.9	489.1	442.3	403.2	373.0	341.0	314.3	291.6	273.9	261.9
35°	616.4	543.6	477.3	422.2	384.7	355.1	328.4	300.7	277.0	260.4	246.7
37.5°	611.0	536.5	463.7	402.8	361.7	332.7	310.1	286.6	263.8	245.6	233.8
40°	602.7	532.0	453.0	389.1	345.8	318.0	298.8	275.6	253.2	235.9	224.9
42.5°	586.7	522.8	441.3	374.0	329.5	301.6	283.9	264.5	243.3	227.1	216.1
45°	547.8	502.6	423.7	351.2	305.2	276.4	260.8	246.7	227.6	211.8	202.3
47.5°	493.7	472.2	398.4	327.2	279.9	252.2	235.9	224.7	210.7	197.9	188.8
50°	456.2	447.3	381.2	310.7	263.1	235.9	220.3	210.1	200.0	187.3	179.0
52.5°	412.9	418.4	361.2	293.8	245.9	219.2	204.6	196.4	187.3	176.8	169.5
55°	352.0	371.9	326.5	265.1	220.3	194.9	181.0	173.8	168.4	160.7	154.4
57.5°	294.9	320.2	289.0	235.7	195.2	173.3	160.0	152.1	148.7	144.6	139.7
60°	261.0	286.0	262.3	216.0	178.4	157.4	145.7	139.0	135.6	132.7	128.6
62.5°	230.7	256.1	236.2	195.9	161.8	142.4	132.2	125.6	123.0	121.6	118.0
65°	189.1	211.0	197.7	164.7	138.1	121.0	111.7	107.1	104.7	104.1	101.8
67.5°	153.9	170.6	160.9	136.6	115.7	100.9	93.0	89.1	87.2	87.0	85.3
70°	130.9	146.4	139.0	117.0	99.0	87.4	80.6	77.1	76.0	75.8	74.8
72.5°	112.9	123.8	117.9	99.5	85.6	75.1	70.0	66.4	65.2	65.5	64.8
75°	83.6	91.7	88.3	75.6	64.4	57.6	53.4	51.1	50.0	50.5	49.7
77.5°	60.2	65.3	62.2	53.4	46.5	41.6	38.5	37.1	36.0	36.0	35.7
80°	45.4	48.4	46.7	41.4	35.7	31.6	29.0	28.1	27.6	27.3	27.1
82.5°	32.4	34.9	32.9	29.3	25.4	22.8	21.4	20.2	19.8	19.9	19.7
85°	16.3	17.3	16.6	14.3	12.7	11.6	10.8	10.3	9.9	10.0	9.7
87.5°	9.0	8.6	7.7	6.6	5.9	5.0	4.6	3.8	3.9	4.4	4.6
90°	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0	3.0	5.1	7.3
92.5°	33.3	31.7	30.2	28.6	27.2	25.8	24.4	22.9	24.4	25.8	27.2
95°	66.7	65.1	63.3	61.8	60.3	58.9	57.4	55.9	57.4	58.9	60.3
97.5°	107.3	106.1	104.8	103.6	102.6	101.5	100.4	99.3	100.4	101.5	102.6
100°	137.1	136.1	135.0	133.9	132.6	131.3	130.1	128.8	130.1	131.3	132.6
102.5°	169.8	168.4	167.1	166.0	165.2	164.4	163.7	162.9	163.7	164.4	165.2
105°	219.8	217.8	216.0	214.8	214.4	214.0	213.5	213.1	213.5	214.0	214.4
107.5°	274.5	273.8	273.0	272.5	272.2	272.0	271.7	271.5	271.7	272.0	272.2
110°	310.8	310.4	310.0	309.6	309.2	308.7	308.3	307.9	308.3	308.7	309.2



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	347.1	347.0	346.9	346.7	346.5	346.3	346.0	345.8	346.0	346.3	346.5
115°	404.4	404.8	405.2	405.1	404.5	403.8	403.2	402.6	403.2	403.8	404.5
117.5°	460.3	460.9	461.5	461.5	461.1	460.6	460.2	459.8	460.2	460.6	461.1
120°	498.5	499.5	500.6	500.5	499.2	498.0	496.7	495.5	496.7	498.0	499.2
122.5°	535.3	535.9	536.5	536.3	535.3	534.4	533.5	532.6	533.5	534.4	535.3
125°	591.0	591.4	591.8	591.7	591.1	590.4	589.9	589.2	589.9	590.4	591.1
127.5°	646.4	646.9	647.3	646.9	645.6	644.2	642.9	641.5	642.9	644.2	645.6
130°	682.3	683.0	683.6	683.1	681.4	679.7	678.0	676.4	678.0	679.7	681.4
132.5°	717.6	718.1	718.6	718.0	716.2	714.6	712.9	711.2	712.9	714.6	716.2
135°	769.6	769.8	770.1	769.5	768.3	767.0	765.7	764.4	765.7	767.0	768.3
137.5°	819.8	819.3	818.7	817.9	816.8	815.8	814.7	813.8	814.7	815.8	816.8
140°	853.0	852.9	852.6	852.0	851.0	849.9	848.9	847.8	848.9	849.9	851.0
142.5°	884.6	884.2	883.8	883.1	882.1	881.0	880.0	878.9	880.0	881.0	882.1
145°	930.8	930.3	929.6	929.0	928.6	928.2	927.8	927.4	927.8	928.2	928.6
147.5°	974.7	974.1	973.5	972.9	972.1	971.3	970.6	969.8	970.6	971.3	972.1
150°	1002.3	1001.9	1001.5	1001.1	1000.6	1000.2	999.8	999.4	999.8	1000.2	1000.6
152.5°	1027.0	1026.6	1026.4	1026.0	1025.4	1024.8	1024.3	1023.6	1024.3	1024.8	1025.4
155°	1062.4	1062.3	1062.0	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9
157.5°	1093.8	1093.6	1093.4	1093.5	1093.7	1094.0	1094.2	1094.5	1094.2	1094.0	1093.7
160°	1113.0	1113.0	1113.0	1113.3	1113.7	1114.1	1114.5	1114.9	1114.5	1114.1	1113.7
162.5°	1130.9	1130.7	1130.6	1130.8	1131.4	1132.0	1132.5	1133.1	1132.5	1132.0	1131.4
165°	1153.8	1153.8	1153.8	1154.1	1154.7	1155.4	1156.0	1156.7	1156.0	1155.4	1154.7
167.5°	1172.0	1171.8	1171.7	1172.0	1172.9	1173.7	1174.5	1175.4	1174.5	1173.7	1172.9
170°	1182.2	1182.2	1182.2	1182.6	1183.5	1184.3	1185.1	1186.0	1185.1	1184.3	1183.5
172.5°	1190.6	1190.6	1190.6	1191.0	1191.8	1192.6	1193.5	1194.3	1193.5	1192.6	1191.8
175°	1199.2	1199.2	1199.2	1199.7	1200.5	1201.3	1202.2	1203.1	1202.2	1201.3	1200.5
177.5°	1203.6	1203.6	1203.6	1204.0	1204.6	1205.3	1206.0	1206.6	1206.0	1205.3	1204.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	385.5	384.4	382.9	380.7	378.8	375.9	375.9	376.3	376.3	376.3	375.9
5°	373.8	371.0	367.5	363.5	359.4	355.1	354.4	352.9	351.8	351.0	350.1
7.5°	361.4	356.4	351.4	345.8	340.7	336.6	333.6	331.2	329.6	327.9	326.7
10°	353.1	346.8	341.0	335.1	328.6	323.4	320.2	318.0	316.3	314.7	314.0
12.5°	343.2	336.1	329.5	323.9	316.9	311.6	308.5	307.4	305.5	302.2	300.6
15°	328.8	322.1	314.4	305.8	302.4	296.0	292.3	290.6	289.4	287.0	286.3
17.5°	316.4	307.8	299.0	292.6	286.3	281.0	279.0	276.9	275.4	273.4	272.7
20°	306.6	298.8	290.8	284.0	277.3	271.6	269.9	268.4	266.8	266.0	265.1
22.5°	296.5	288.8	282.1	275.7	268.6	264.9	263.1	261.4	260.3	259.7	258.9
25°	282.4	275.6	268.2	262.5	256.8	254.3	253.2	252.3	251.4	250.5	250.3
27.5°	269.9	262.4	256.4	251.0	247.0	244.9	243.8	243.4	243.5	243.9	244.1
30°	260.4	253.6	248.7	244.1	240.3	238.4	238.1	238.1	239.0	239.1	239.5
32.5°	251.8	246.1	241.2	236.8	233.9	232.6	233.3	233.3	233.9	234.4	235.1
35°	239.1	234.2	230.4	226.6	224.1	224.7	225.1	225.4	226.4	227.6	228.3
37.5°	227.1	222.8	218.8	215.9	214.7	215.7	216.7	217.4	218.6	219.5	220.2
40°	218.4	215.2	211.4	208.7	209.1	209.7	210.4	211.4	212.4	213.0	213.7
42.5°	210.3	207.0	204.1	201.9	202.4	203.2	203.6	204.1	205.2	206.3	206.7
45°	198.1	195.4	192.8	191.4	191.8	192.2	192.6	193.1	194.1	194.9	195.1
47.5°	184.3	182.5	180.7	179.4	180.0	179.9	180.3	181.6	181.8	182.3	183.4
50°	175.5	173.8	171.7	171.3	171.3	171.3	171.5	173.0	173.0	173.8	174.6
52.5°	165.8	164.7	163.4	162.7	162.3	162.3	163.1	163.9	164.2	165.3	166.1
55°	151.4	150.3	149.1	148.5	148.1	148.5	150.0	150.4	151.4	152.0	152.5
57.5°	136.4	135.5	134.6	134.3	134.2	134.7	135.5	136.6	136.9	138.7	139.5
60°	126.5	125.1	124.4	124.4	124.0	125.7	125.4	127.3	127.7	128.8	130.1
62.5°	116.3	114.5	114.2	114.2	114.8	115.3	115.8	116.6	117.6	119.0	120.1
65°	99.9	99.0	100.3	100.1	99.7	100.9	100.9	101.8	103.0	104.3	106.4
67.5°	84.4	83.9	84.0	84.0	84.5	85.2	85.8	86.6	88.0	89.4	90.7
70°	73.9	74.4	73.5	74.3	74.8	75.0	75.4	76.6	78.0	79.0	80.6
72.5°	63.7	63.7	63.8	64.1	64.7	65.0	65.4	66.7	68.3	69.1	70.4
75°	49.0	48.8	49.4	49.4	50.3	50.7	51.1	51.7	53.2	54.3	55.3
77.5°	35.8	36.0	35.9	36.5	36.3	36.4	37.5	38.1	38.2	40.5	41.0
80°	27.0	27.3	27.6	27.7	27.9	27.6	28.9	29.4	29.4	30.7	31.7
82.5°	19.4	19.6	20.1	20.3	20.3	20.7	20.8	21.2	21.7	22.3	23.5
85°	9.7	10.3	10.4	10.3	10.4	10.0	10.6	10.8	11.0	11.0	11.0
87.5°	4.9	5.5	6.0	6.6	7.0	7.7	7.9	7.7	7.9	8.6	8.1
90°	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.5	25.3	26.1	26.7
92.5°	28.6	30.2	31.7	33.3	34.8	36.4	37.0	37.7	38.4	39.1	39.3
95°	61.8	63.3	65.1	66.7	68.4	70.1	70.9	71.7	72.6	73.5	73.9
97.5°	103.6	104.8	106.1	107.3	108.4	109.7	110.6	111.6	112.6	113.6	114.0
100°	133.9	135.0	136.1	137.1	138.2	139.3	139.9	140.5	141.1	141.8	142.3
102.5°	166.0	167.1	168.4	169.8	171.2	172.6	173.3	173.8	174.5	175.1	175.4
105°	214.8	216.0	217.8	219.8	221.7	223.6	223.6	223.6	223.6	223.6	223.8
107.5°	272.5	273.0	273.8	274.5	275.2	276.1	276.7	277.4	278.1	278.8	278.9
110°	309.6	310.0	310.4	310.8	311.2	311.7	312.5	313.3	314.2	315.0	315.2



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	346.7	346.9	347.0	347.1	347.2	347.2	348.3	349.3	350.3	351.3	351.8
115°	405.1	405.2	404.8	404.4	404.0	403.6	403.7	404.0	404.1	404.4	404.4
117.5°	461.5	461.5	460.9	460.3	459.8	459.3	459.2	459.2	459.1	459.1	458.8
120°	500.5	500.6	499.5	498.5	497.4	496.4	496.2	495.9	495.8	495.5	495.2
122.5°	536.3	536.5	535.9	535.3	534.8	534.3	533.7	533.2	532.6	532.1	531.5
125°	591.7	591.8	591.4	591.0	590.6	590.2	589.3	588.5	587.7	586.8	586.0
127.5°	646.9	647.3	646.9	646.4	646.0	645.5	644.3	643.1	642.0	640.7	639.7
130°	683.1	683.6	683.0	682.3	681.8	681.1	680.3	679.4	678.6	677.8	676.5
132.5°	718.0	718.6	718.1	717.6	717.1	716.7	715.7	714.7	713.7	712.7	711.6
135°	769.5	770.1	769.8	769.6	769.4	769.2	768.3	767.5	766.6	765.8	765.2
137.5°	817.9	818.7	819.3	819.8	820.4	820.9	820.0	819.1	818.2	817.3	816.5
140°	852.0	852.6	852.9	853.0	853.3	853.5	853.3	853.0	852.9	852.6	851.8
142.5°	883.1	883.8	884.2	884.6	884.9	885.3	885.1	884.9	884.7	884.5	883.8
145°	929.0	929.6	930.3	930.8	931.5	932.1	931.9	931.7	931.5	931.3	930.7
147.5°	972.9	973.5	974.1	974.7	975.3	975.9	975.9	975.9	975.9	975.9	975.3
150°	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1	1003.1	1003.1	1003.1	1002.6
152.5°	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8	1028.1	1028.4	1028.7	1028.4
155°	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7	1064.5	1065.4	1066.2	1065.9
157.5°	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0	1095.8	1096.7	1097.6	1097.5
160°	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1	1115.2	1116.2	1117.3	1117.4
162.5°	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3	1133.3	1134.4	1135.5	1135.3
165°	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0	1156.3	1157.6	1158.9	1158.7
167.5°	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5
170°	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1
172.5°	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9	1193.2	1194.5	1195.8	1195.7
175°	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5	1201.8	1203.1	1204.3	1204.2
177.5°	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6	1205.7	1206.6	1207.6	1207.5
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	374.9	374.7	375.8	375.0	375.8	374.7	374.9	375.9	376.3	376.3	376.3
5°	348.9	349.5	347.6	347.6	347.6	349.5	348.9	350.1	351.0	351.8	352.9
7.5°	325.8	325.0	325.1	324.0	325.1	325.0	325.8	326.7	327.9	329.6	331.2
10°	311.7	310.5	310.1	310.4	310.1	310.5	311.7	314.0	314.7	316.3	318.0
12.5°	299.9	299.8	297.3	297.3	297.3	299.8	299.9	300.6	302.2	305.5	307.4
15°	286.3	282.7	282.3	283.4	282.3	282.7	286.3	286.3	287.0	289.4	290.6
17.5°	272.5	270.5	270.7	270.1	270.7	270.5	272.5	272.7	273.4	275.4	276.9
20°	265.1	264.0	263.8	262.5	263.8	264.0	265.1	265.1	266.0	266.8	268.4
22.5°	258.4	258.1	258.2	256.7	258.2	258.1	258.4	258.9	259.7	260.3	261.4
25°	250.1	251.1	250.3	250.3	250.3	251.1	250.1	250.3	250.5	251.4	252.3
27.5°	244.5	244.5	244.1	244.1	244.1	244.5	244.5	244.1	243.9	243.5	243.4
30°	240.3	240.1	240.4	240.4	240.4	240.1	240.3	239.5	239.1	239.0	238.1
32.5°	236.0	236.3	236.4	236.5	236.4	236.3	236.0	235.1	234.4	233.9	233.3
35°	229.4	229.7	230.2	229.8	230.2	229.7	229.4	228.3	227.6	226.4	225.4
37.5°	220.5	221.4	221.3	221.5	221.3	221.4	220.5	220.2	219.5	218.6	217.4
40°	213.9	214.4	214.3	214.3	214.3	214.4	213.9	213.7	213.0	212.4	211.4
42.5°	207.0	207.4	206.9	206.7	206.9	207.4	207.0	206.7	206.3	205.2	204.1
45°	195.8	195.4	196.0	195.3	196.0	195.4	195.8	195.1	194.9	194.1	193.1
47.5°	183.3	183.7	183.8	184.4	183.8	183.7	183.3	183.4	182.3	181.8	181.6
50°	175.0	176.1	176.1	175.9	176.1	176.1	175.0	174.6	173.8	173.0	173.0
52.5°	166.7	167.2	168.0	168.0	168.0	167.2	166.7	166.1	165.3	164.2	163.9
55°	154.0	154.4	154.8	155.0	154.8	154.4	154.0	152.5	152.0	151.4	150.4
57.5°	140.9	140.7	141.6	141.9	141.6	140.7	140.9	139.5	138.7	136.9	136.6
60°	131.6	131.6	133.1	133.7	133.1	131.6	131.6	130.1	128.8	127.7	127.3
62.5°	121.7	122.4	123.8	123.1	123.8	122.4	121.7	120.1	119.0	117.6	116.6
65°	107.3	108.8	108.7	109.4	108.7	108.8	107.3	106.4	104.3	103.0	101.8
67.5°	92.2	93.2	94.6	94.7	94.6	93.2	92.2	90.7	89.4	88.0	86.6
70°	82.0	83.0	83.7	84.3	83.7	83.0	82.0	80.6	79.0	78.0	76.6
72.5°	72.2	72.6	74.5	73.7	74.5	72.6	72.2	70.4	69.1	68.3	66.7
75°	56.6	58.0	59.1	58.5	59.1	58.0	56.6	55.3	54.3	53.2	51.7
77.5°	41.8	43.2	43.7	43.2	43.7	43.2	41.8	41.0	40.5	38.2	38.1
80°	33.0	32.9	34.0	33.8	34.0	32.9	33.0	31.7	30.7	29.4	29.4
82.5°	24.2	24.1	24.5	24.7	24.5	24.1	24.2	23.5	22.3	21.7	21.2
85°	11.7	12.3	11.6	11.4	11.6	12.3	11.7	11.0	11.0	11.0	10.8
87.5°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.1	8.6	7.9	7.7
90°	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.5
92.5°	39.1	38.8	38.5	38.2	38.5	38.8	39.1	39.3	39.1	38.4	37.7
95°	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.5	72.6	71.7
97.5°	113.9	113.8	113.7	113.7	113.7	113.8	113.9	114.0	113.6	112.6	111.6
100°	142.8	143.2	143.6	144.0	143.6	143.2	142.8	142.3	141.8	141.1	140.5
102.5°	175.3	175.2	175.1	175.0	175.1	175.2	175.3	175.4	175.1	174.5	173.8
105°	224.2	224.6	225.0	225.4	225.0	224.6	224.2	223.8	223.6	223.6	223.6
107.5°	278.7	278.4	278.2	277.9	278.2	278.4	278.7	278.9	278.8	278.1	277.4
110°	314.8	314.4	314.0	313.6	314.0	314.4	314.8	315.2	315.0	314.2	313.3



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	351.7	351.6	351.6	351.5	351.6	351.6	351.7	351.8	351.3	350.3	349.3
115°	404.1	404.0	403.7	403.6	403.7	404.0	404.1	404.4	404.4	404.1	404.0
117.5°	458.2	457.5	457.0	456.4	457.0	457.5	458.2	458.8	459.1	459.1	459.2
120°	494.8	494.4	494.0	493.5	494.0	494.4	494.8	495.2	495.5	495.8	495.9
122.5°	530.9	530.4	529.7	529.1	529.7	530.4	530.9	531.5	532.1	532.6	533.2
125°	585.1	584.2	583.4	582.6	583.4	584.2	585.1	586.0	586.8	587.7	588.5
127.5°	638.7	637.7	636.7	635.9	636.7	637.7	638.7	639.7	640.7	642.0	643.1
130°	675.1	673.6	672.1	670.7	672.1	673.6	675.1	676.5	677.8	678.6	679.4
132.5°	710.5	709.3	708.2	707.0	708.2	709.3	710.5	711.6	712.7	713.7	714.7
135°	764.8	764.3	763.9	763.5	763.9	764.3	764.8	765.2	765.8	766.6	767.5
137.5°	815.7	815.0	814.2	813.3	814.2	815.0	815.7	816.5	817.3	818.2	819.1
140°	850.4	848.9	847.4	846.0	847.4	848.9	850.4	851.8	852.6	852.9	853.0
142.5°	882.6	881.5	880.4	879.3	880.4	881.5	882.6	883.8	884.5	884.7	884.9
145°	929.9	929.0	928.2	927.4	928.2	929.0	929.9	930.7	931.3	931.5	931.7
147.5°	974.0	972.7	971.4	970.2	971.4	972.7	974.0	975.3	975.9	975.9	975.9
150°	1001.3	1000.0	998.7	997.5	998.7	1000.0	1001.3	1002.6	1003.1	1003.1	1003.1
152.5°	1027.3	1026.2	1025.1	1024.0	1025.1	1026.2	1027.3	1028.4	1028.7	1028.4	1028.1
155°	1064.5	1063.0	1061.5	1060.0	1061.5	1063.0	1064.5	1065.9	1066.2	1065.4	1064.5
157.5°	1096.3	1095.1	1094.0	1092.7	1094.0	1095.1	1096.3	1097.5	1097.6	1096.7	1095.8
160°	1116.6	1115.7	1114.8	1114.0	1114.8	1115.7	1116.6	1117.4	1117.3	1116.2	1115.2
162.5°	1133.9	1132.6	1131.2	1129.9	1131.2	1132.6	1133.9	1135.3	1135.5	1134.4	1133.3
165°	1157.2	1155.8	1154.3	1152.8	1154.3	1155.8	1157.2	1158.7	1158.9	1157.6	1156.3
167.5°	1176.2	1174.9	1173.6	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9
170°	1186.7	1185.1	1183.7	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1
172.5°	1194.2	1192.7	1191.2	1189.8	1191.2	1192.7	1194.2	1195.7	1195.8	1194.5	1193.2
175°	1202.7	1201.3	1199.8	1198.3	1199.8	1201.3	1202.7	1204.2	1204.3	1203.1	1201.8
177.5°	1206.4	1205.2	1204.0	1202.9	1204.0	1205.2	1206.4	1207.5	1207.6	1206.6	1205.7
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	375.9	375.9	378.8	380.7	382.9	384.4	385.5	386.5	388.4	390.8	393.5
5°	354.4	355.1	359.4	363.5	367.5	371.0	373.8	377.2	381.4	386.5	392.2
7.5°	333.6	336.6	340.7	345.8	351.4	356.4	361.4	367.0	373.0	380.5	388.5
10°	320.2	323.4	328.6	335.1	341.0	346.8	353.1	359.1	366.6	375.5	385.8
12.5°	308.5	311.6	316.9	323.9	329.5	336.1	343.2	351.1	359.5	370.1	381.8
15°	292.3	296.0	302.4	305.8	314.4	322.1	328.8	340.1	350.8	361.8	375.3
17.5°	279.0	281.0	286.3	292.6	299.0	307.8	316.4	326.0	336.6	350.0	366.9
20°	269.9	271.6	277.3	284.0	290.8	298.8	306.6	316.1	328.0	342.3	360.5
22.5°	263.1	264.9	268.6	275.7	282.1	288.8	296.5	307.9	320.6	334.5	354.2
25°	253.2	254.3	256.8	262.5	268.2	275.6	282.4	293.1	306.1	322.5	342.3
27.5°	243.8	244.9	247.0	251.0	256.4	262.4	269.9	278.8	292.1	309.9	330.8
30°	238.1	238.4	240.3	244.1	248.7	253.6	260.4	270.7	283.2	301.3	323.3
32.5°	233.3	232.6	233.9	236.8	241.2	246.1	251.8	261.9	273.9	291.6	314.3
35°	225.1	224.7	224.1	226.6	230.4	234.2	239.1	246.7	260.4	277.0	300.7
37.5°	216.7	215.7	214.7	215.9	218.8	222.8	227.1	233.8	245.6	263.8	286.6
40°	210.4	209.7	209.1	208.7	211.4	215.2	218.4	224.9	235.9	253.2	275.6
42.5°	203.6	203.2	202.4	201.9	204.1	207.0	210.3	216.1	227.1	243.3	264.5
45°	192.6	192.2	191.8	191.4	192.8	195.4	198.1	202.3	211.8	227.6	246.7
47.5°	180.3	179.9	180.0	179.4	180.7	182.5	184.3	188.8	197.9	210.7	224.7
50°	171.5	171.3	171.3	171.3	171.7	173.8	175.5	179.0	187.3	200.0	210.1
52.5°	163.1	162.3	162.3	162.7	163.4	164.7	165.8	169.5	176.8	187.3	196.4
55°	150.0	148.5	148.1	148.5	149.1	150.3	151.4	154.4	160.7	168.4	173.8
57.5°	135.5	134.7	134.2	134.3	134.6	135.5	136.4	139.7	144.6	148.7	152.1
60°	125.4	125.7	124.0	124.4	124.4	125.1	126.5	128.6	132.7	135.6	139.0
62.5°	115.8	115.3	114.8	114.2	114.2	114.5	116.3	118.0	121.6	123.0	125.6
65°	100.9	100.9	99.7	100.1	100.3	99.0	99.9	101.8	104.1	104.7	107.1
67.5°	85.8	85.2	84.5	84.0	84.0	83.9	84.4	85.3	87.0	87.2	89.1
70°	75.4	75.0	74.8	74.3	73.5	74.4	73.9	74.8	75.8	76.0	77.1
72.5°	65.4	65.0	64.7	64.1	63.8	63.7	63.7	64.8	65.5	65.2	66.4
75°	51.1	50.7	50.3	49.4	49.4	48.8	49.0	49.7	50.5	50.0	51.1
77.5°	37.5	36.4	36.3	36.5	35.9	36.0	35.8	35.7	36.0	36.0	37.1
80°	28.9	27.6	27.9	27.7	27.6	27.3	27.0	27.1	27.3	27.6	28.1
82.5°	20.8	20.7	20.3	20.3	20.1	19.6	19.4	19.7	19.9	19.8	20.2
85°	10.6	10.0	10.4	10.3	10.4	10.3	9.7	9.7	10.0	9.9	10.3
87.5°	7.9	7.7	7.0	6.6	6.0	5.5	4.9	4.6	4.4	3.9	3.8
90°	23.6	22.7	20.0	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0
92.5°	37.0	36.4	34.8	33.3	31.7	30.2	28.6	27.2	25.8	24.4	22.9
95°	70.9	70.1	68.4	66.7	65.1	63.3	61.8	60.3	58.9	57.4	55.9
97.5°	110.6	109.7	108.4	107.3	106.1	104.8	103.6	102.6	101.5	100.4	99.3
100°	139.9	139.3	138.2	137.1	136.1	135.0	133.9	132.6	131.3	130.1	128.8
102.5°	173.3	172.6	171.2	169.8	168.4	167.1	166.0	165.2	164.4	163.7	162.9
105°	223.6	223.6	221.7	219.8	217.8	216.0	214.8	214.4	214.0	213.5	213.1
107.5°	276.7	276.1	275.2	274.5	273.8	273.0	272.5	272.2	272.0	271.7	271.5
110°	312.5	311.7	311.2	310.8	310.4	310.0	309.6	309.2	308.7	308.3	307.9



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	348.3	347.2	347.2	347.1	347.0	346.9	346.7	346.5	346.3	346.0	345.8
115°	403.7	403.6	404.0	404.4	404.8	405.2	405.1	404.5	403.8	403.2	402.6
117.5°	459.2	459.3	459.8	460.3	460.9	461.5	461.5	461.1	460.6	460.2	459.8
120°	496.2	496.4	497.4	498.5	499.5	500.6	500.5	499.2	498.0	496.7	495.5
122.5°	533.7	534.3	534.8	535.3	535.9	536.5	536.3	535.3	534.4	533.5	532.6
125°	589.3	590.2	590.6	591.0	591.4	591.8	591.7	591.1	590.4	589.9	589.2
127.5°	644.3	645.5	646.0	646.4	646.9	647.3	646.9	645.6	644.2	642.9	641.5
130°	680.3	681.1	681.8	682.3	683.0	683.6	683.1	681.4	679.7	678.0	676.4
132.5°	715.7	716.7	717.1	717.6	718.1	718.6	718.0	716.2	714.6	712.9	711.2
135°	768.3	769.2	769.4	769.6	769.8	770.1	769.5	768.3	767.0	765.7	764.4
137.5°	820.0	820.9	820.4	819.8	819.3	818.7	817.9	816.8	815.8	814.7	813.8
140°	853.3	853.5	853.3	853.0	852.9	852.6	852.0	851.0	849.9	848.9	847.8
142.5°	885.1	885.3	884.9	884.6	884.2	883.8	883.1	882.1	881.0	880.0	878.9
145°	931.9	932.1	931.5	930.8	930.3	929.6	929.0	928.6	928.2	927.8	927.4
147.5°	975.9	975.9	975.3	974.7	974.1	973.5	972.9	972.1	971.3	970.6	969.8
150°	1003.1	1003.1	1002.7	1002.3	1001.9	1001.5	1001.1	1000.6	1000.2	999.8	999.4
152.5°	1027.8	1027.4	1027.2	1027.0	1026.6	1026.4	1026.0	1025.4	1024.8	1024.3	1023.6
155°	1063.7	1062.8	1062.7	1062.4	1062.3	1062.0	1061.9	1061.9	1061.9	1061.9	1061.9
157.5°	1095.0	1094.1	1094.0	1093.8	1093.6	1093.4	1093.5	1093.7	1094.0	1094.2	1094.5
160°	1114.1	1113.0	1113.0	1113.0	1113.0	1113.0	1113.3	1113.7	1114.1	1114.5	1114.9
162.5°	1132.3	1131.2	1131.1	1130.9	1130.7	1130.6	1130.8	1131.4	1132.0	1132.5	1133.1
165°	1155.0	1153.8	1153.8	1153.8	1153.8	1153.8	1154.1	1154.7	1155.4	1156.0	1156.7
167.5°	1173.6	1172.3	1172.2	1172.0	1171.8	1171.7	1172.0	1172.9	1173.7	1174.5	1175.4
170°	1183.7	1182.2	1182.2	1182.2	1182.2	1182.2	1182.6	1183.5	1184.3	1185.1	1186.0
172.5°	1191.9	1190.6	1190.6	1190.6	1190.6	1190.6	1191.0	1191.8	1192.6	1193.5	1194.3
175°	1200.5	1199.2	1199.2	1199.2	1199.2	1199.2	1199.7	1200.5	1201.3	1202.2	1203.1
177.5°	1204.6	1203.6	1203.6	1203.6	1203.6	1203.6	1204.0	1204.6	1205.3	1206.0	1206.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	394.4	395.3	397.8	399.7	401.8	403.0	404.1	405.1	406.3	406.6	411.0
5°	396.2	400.0	406.7	411.6	417.7	424.3	428.8	431.0	436.5	441.0	450.1
7.5°	395.7	403.8	413.8	424.3	435.4	445.7	454.7	465.4	472.9	484.3	495.5
10°	395.3	406.1	419.0	432.3	447.8	462.3	475.2	489.7	501.7	517.4	530.8
12.5°	393.9	407.0	424.9	440.7	459.6	479.5	498.6	517.1	527.7	554.0	566.4
15°	390.5	406.1	428.5	452.4	478.4	502.0	526.3	545.7	577.0	600.0	614.7
17.5°	384.1	405.9	432.4	461.3	492.9	524.0	551.5	580.9	614.2	642.0	671.6
20°	381.0	405.0	434.6	466.5	499.4	534.5	565.8	601.1	637.4	664.8	702.8
22.5°	375.4	402.5	434.4	469.9	505.1	541.4	578.1	613.8	655.7	693.3	729.5
25°	366.2	396.6	429.7	469.4	510.5	547.0	590.9	638.2	681.8	730.3	766.4
27.5°	356.5	389.0	422.1	459.0	503.4	546.7	601.9	655.3	708.7	750.5	777.2
30°	349.1	380.7	414.8	452.1	495.9	547.4	609.1	667.4	719.5	755.4	770.4
32.5°	341.0	373.0	403.2	442.3	489.1	546.9	613.7	674.6	720.1	744.0	741.0
35°	328.4	355.1	384.7	422.2	477.3	543.6	616.4	675.2	703.1	698.0	659.3
37.5°	310.1	332.7	361.7	402.8	463.7	536.5	611.0	655.2	653.4	611.6	555.5
40°	298.8	318.0	345.8	389.1	453.0	532.0	602.7	631.4	607.1	548.7	481.5
42.5°	283.9	301.6	329.5	374.0	441.3	522.8	586.7	595.0	547.5	480.4	418.7
45°	260.8	276.4	305.2	351.2	423.7	502.6	547.8	527.4	463.4	394.1	347.2
47.5°	235.9	252.2	279.9	327.2	398.4	472.2	493.7	450.5	384.8	328.6	285.5
50°	220.3	235.9	263.1	310.7	381.2	447.3	456.2	400.4	340.0	290.6	255.3
52.5°	204.6	219.2	245.9	293.8	361.2	418.4	412.9	356.0	300.5	258.4	230.6
55°	181.0	194.9	220.3	265.1	326.5	371.9	352.0	297.7	251.7	219.0	197.9
57.5°	160.0	173.3	195.2	235.7	289.0	320.2	294.9	249.1	212.5	187.4	171.7
60°	145.7	157.4	178.4	216.0	262.3	286.0	261.0	220.5	189.7	169.6	155.6
62.5°	132.2	142.4	161.8	195.9	236.2	256.1	230.7	196.5	170.3	152.5	140.5
65°	111.7	121.0	138.1	164.7	197.7	211.0	189.1	161.4	141.1	127.8	119.8
67.5°	93.0	100.9	115.7	136.6	160.9	170.6	153.9	132.5	117.2	106.5	100.2
70°	80.6	87.4	99.0	117.0	139.0	146.4	130.9	113.2	102.0	93.4	87.6
72.5°	70.0	75.1	85.6	99.5	117.9	123.8	112.9	97.4	87.0	80.6	75.8
75°	53.4	57.6	64.4	75.6	88.3	91.7	83.6	73.9	66.9	62.3	58.7
77.5°	38.5	41.6	46.5	53.4	62.2	65.3	60.2	53.6	48.5	45.5	43.5
80°	29.0	31.6	35.7	41.4	46.7	48.4	45.4	40.4	36.9	35.1	33.4
82.5°	21.4	22.8	25.4	29.3	32.9	34.9	32.4	29.4	27.4	25.8	25.2
85°	10.8	11.6	12.7	14.3	16.6	17.3	16.3	15.6	14.4	13.5	13.5
87.5°	4.6	5.0	5.9	6.6	7.7	8.6	9.0	9.3	9.7	9.7	9.8
90°	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.5
92.5°	24.4	25.8	27.2	28.6	30.2	31.7	33.3	34.8	36.4	37.0	37.7
95°	57.4	58.9	60.3	61.8	63.3	65.1	66.7	68.4	70.1	70.9	71.7
97.5°	100.4	101.5	102.6	103.6	104.8	106.1	107.3	108.4	109.7	110.6	111.6
100°	130.1	131.3	132.6	133.9	135.0	136.1	137.1	138.2	139.3	139.9	140.5
102.5°	163.7	164.4	165.2	166.0	167.1	168.4	169.8	171.2	172.6	173.3	173.8
105°	213.5	214.0	214.4	214.8	216.0	217.8	219.8	221.7	223.6	223.6	223.6
107.5°	271.7	272.0	272.2	272.5	273.0	273.8	274.5	275.2	276.1	276.7	277.4
110°	308.3	308.7	309.2	309.6	310.0	310.4	310.8	311.2	311.7	312.5	313.3



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	346.0	346.3	346.5	346.7	346.9	347.0	347.1	347.2	347.2	348.3	349.3
115°	403.2	403.8	404.5	405.1	405.2	404.8	404.4	404.0	403.6	403.7	404.0
117.5°	460.2	460.6	461.1	461.5	461.5	460.9	460.3	459.8	459.3	459.2	459.2
120°	496.7	498.0	499.2	500.5	500.6	499.5	498.5	497.4	496.4	496.2	495.9
122.5°	533.5	534.4	535.3	536.3	536.5	535.9	535.3	534.8	534.3	533.7	533.2
125°	589.9	590.4	591.1	591.7	591.8	591.4	591.0	590.6	590.2	589.3	588.5
127.5°	642.9	644.2	645.6	646.9	647.3	646.9	646.4	646.0	645.5	644.3	643.1
130°	678.0	679.7	681.4	683.1	683.6	683.0	682.3	681.8	681.1	680.3	679.4
132.5°	712.9	714.6	716.2	718.0	718.6	718.1	717.6	717.1	716.7	715.7	714.7
135°	765.7	767.0	768.3	769.5	770.1	769.8	769.6	769.4	769.2	768.3	767.5
137.5°	814.7	815.8	816.8	817.9	818.7	819.3	819.8	820.4	820.9	820.0	819.1
140°	848.9	849.9	851.0	852.0	852.6	852.9	853.0	853.3	853.5	853.3	853.0
142.5°	880.0	881.0	882.1	883.1	883.8	884.2	884.6	884.9	885.3	885.1	884.9
145°	927.8	928.2	928.6	929.0	929.6	930.3	930.8	931.5	932.1	931.9	931.7
147.5°	970.6	971.3	972.1	972.9	973.5	974.1	974.7	975.3	975.9	975.9	975.9
150°	999.8	1000.2	1000.6	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1	1003.1
152.5°	1024.3	1024.8	1025.4	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8	1028.1
155°	1061.9	1061.9	1061.9	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7	1064.5
157.5°	1094.2	1094.0	1093.7	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0	1095.8
160°	1114.5	1114.1	1113.7	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1	1115.2
162.5°	1132.5	1132.0	1131.4	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3	1133.3
165°	1156.0	1155.4	1154.7	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0	1156.3
167.5°	1174.5	1173.7	1172.9	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6	1174.9
170°	1185.1	1184.3	1183.5	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7	1185.1
172.5°	1193.5	1192.6	1191.8	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9	1193.2
175°	1202.2	1201.3	1200.5	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5	1201.8
177.5°	1206.0	1205.3	1204.6	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6	1205.7
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	412.5	412.7	414.3	415.6	415.0	415.7	416.0
5°	450.7	457.5	461.1	463.8	464.0	464.2	465.7
7.5°	504.8	512.2	517.6	525.7	528.1	530.8	530.1
10°	544.4	555.2	564.5	569.4	574.8	582.5	576.3
12.5°	581.3	600.5	614.7	622.3	627.3	628.8	625.8
15°	642.2	667.2	680.7	680.4	697.4	704.8	693.2
17.5°	698.0	721.1	739.7	749.2	763.4	766.5	765.2
20°	732.2	757.5	771.9	788.2	795.7	802.3	803.4
22.5°	761.7	784.4	799.9	813.4	819.6	822.8	824.7
25°	792.1	809.9	819.2	823.9	825.7	825.2	822.8
27.5°	789.9	791.3	781.1	771.0	762.0	751.9	748.4
30°	769.4	753.5	725.0	708.8	685.1	666.3	673.9
32.5°	715.5	683.7	651.8	616.4	587.3	578.9	570.5
35°	610.7	554.8	522.1	484.1	469.0	453.8	443.3
37.5°	494.0	450.9	412.1	387.3	372.0	362.4	357.3
40°	427.1	388.2	356.3	336.1	324.6	313.8	312.3
42.5°	373.8	337.6	313.6	297.6	286.5	281.8	278.5
45°	306.1	281.0	264.8	253.4	246.0	243.1	239.3
47.5°	259.2	241.3	229.2	221.4	215.8	213.7	213.4
50°	232.8	218.0	209.1	203.0	198.7	197.9	194.9
52.5°	213.1	200.2	193.3	188.0	184.8	182.7	181.8
55°	185.0	176.4	170.2	167.1	164.7	162.6	162.6
57.5°	161.8	154.7	150.6	148.0	147.2	145.8	144.8
60°	147.6	141.5	138.3	136.0	134.4	134.7	133.0
62.5°	133.6	129.6	126.5	124.3	122.5	122.5	122.6
65°	113.7	110.7	108.4	107.7	106.6	105.3	105.6
67.5°	96.4	93.6	91.8	90.5	90.1	89.4	90.5
70°	84.0	81.9	80.6	79.4	79.0	79.2	80.1
72.5°	72.6	71.1	70.2	69.7	68.8	68.9	69.5
75°	57.0	55.8	55.1	54.5	54.3	54.3	54.3
77.5°	41.8	41.6	41.3	40.4	40.4	40.7	40.7
80°	33.0	32.4	32.3	31.9	31.3	31.0	31.9
82.5°	24.7	24.1	24.0	23.9	23.0	22.9	23.7
85°	13.3	12.7	12.9	12.7	12.7	12.6	12.6
87.5°	9.8	9.8	9.8	10.0	9.9	9.9	10.3
90°	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	38.4	39.1	39.3	39.1	38.8	38.5	38.2
95°	72.6	73.5	73.9	73.9	73.9	73.9	73.9
97.5°	112.6	113.6	114.0	113.9	113.8	113.7	113.7
100°	141.1	141.8	142.3	142.8	143.2	143.6	144.0
102.5°	174.5	175.1	175.4	175.3	175.2	175.1	175.0
105°	223.6	223.6	223.8	224.2	224.6	225.0	225.4
107.5°	278.1	278.8	278.9	278.7	278.4	278.2	277.9
110°	314.2	315.0	315.2	314.8	314.4	314.0	313.6



TEST NUMBER: P331902-930

CATALOG NUMBER: S123DIP-S340D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	350.3	351.3	351.8	351.7	351.6	351.6	351.5
115°	404.1	404.4	404.4	404.1	404.0	403.7	403.6
117.5°	459.1	459.1	458.8	458.2	457.5	457.0	456.4
120°	495.8	495.5	495.2	494.8	494.4	494.0	493.5
122.5°	532.6	532.1	531.5	530.9	530.4	529.7	529.1
125°	587.7	586.8	586.0	585.1	584.2	583.4	582.6
127.5°	642.0	640.7	639.7	638.7	637.7	636.7	635.9
130°	678.6	677.8	676.5	675.1	673.6	672.1	670.7
132.5°	713.7	712.7	711.6	710.5	709.3	708.2	707.0
135°	766.6	765.8	765.2	764.8	764.3	763.9	763.5
137.5°	818.2	817.3	816.5	815.7	815.0	814.2	813.3
140°	852.9	852.6	851.8	850.4	848.9	847.4	846.0
142.5°	884.7	884.5	883.8	882.6	881.5	880.4	879.3
145°	931.5	931.3	930.7	929.9	929.0	928.2	927.4
147.5°	975.9	975.9	975.3	974.0	972.7	971.4	970.2
150°	1003.1	1003.1	1002.6	1001.3	1000.0	998.7	997.5
152.5°	1028.4	1028.7	1028.4	1027.3	1026.2	1025.1	1024.0
155°	1065.4	1066.2	1065.9	1064.5	1063.0	1061.5	1060.0
157.5°	1096.7	1097.6	1097.5	1096.3	1095.1	1094.0	1092.7
160°	1116.2	1117.3	1117.4	1116.6	1115.7	1114.8	1114.0
162.5°	1134.4	1135.5	1135.3	1133.9	1132.6	1131.2	1129.9
165°	1157.6	1158.9	1158.7	1157.2	1155.8	1154.3	1152.8
167.5°	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3
170°	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2
172.5°	1194.5	1195.8	1195.7	1194.2	1192.7	1191.2	1189.8
175°	1203.1	1204.3	1204.2	1202.7	1201.3	1199.8	1198.3
177.5°	1206.6	1207.6	1207.5	1206.4	1205.2	1204.0	1202.9
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9

(END OF REPORT)