

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331873-930

Luminaire Tested: **S123DIP-S340D365U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331873-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D365U930-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2221.5 lumens  
Efficiency: N/A  
Efficacy: 109.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331873-930

CATALOG NUMBER: S123DIP-S340D365U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331873-930

CATALOG NUMBER: S123DIP-S340D365U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4755	4755	4755
5°	4778	4712	4744
10°	4746	4671	4701
15°	4690	4619	4627
20°	4625	4543	4548
25°	4538	4454	4444
30°	4443	4354	4320
35°	4343	4248	4193
40°	4239	4131	4068
45°	4122	4025	3927
50°	4007	3893	3785
55°	3856	3757	3643
60°	3705	3597	3483
65°	3568	3423	3319
70°	3371	3229	3084
75°	3082	2969	2845
80°	2777	2665	2641
85°	2433	2347	2260



TEST NUMBER: P331873-930

CATALOG NUMBER: S123DIP-S340D365U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.6	1.9
10°-20°	117.5	5.3
20°-30°	173.6	7.8
30°-40°	202.8	9.1
40°-50°	203.9	9.2
50°-60°	179.1	8.1
60°-70°	133.4	6.0
70°-80°	76.0	3.4
80°-90°	22.9	1.0
90°-100°	79.2	3.6
100°-110°	224.3	10.1
110°-120°	220.6	9.9
120°-130°	176.0	7.9
130°-140°	138.8	6.2
140°-150°	103.6	4.7
150°-160°	72.2	3.2
160°-170°	42.4	1.9
170°-180°	13.8	0.6
0°-30°	332.7	15.0
0°-40°	535.5	24.1
0°-60°	918.4	41.3
0°-90°	1150.7	51.8
90°-120°	524.1	23.6
90°-150°	942.4	42.4
90°-180°	1071.0	48.2
0°-180°	2221.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	440	439	42
15°	421	419	414	417	415	119
25°	382	380	375	375	374	176
35°	330	328	323	321	319	207
45°	271	269	264	260	258	209
55°	206	205	200	196	194	184
65°	140	138	134	132	130	138
75°	74	73	71	70	68	79
85°	20	19	19	18	18	22
90°	1	4	7	8	8	2
95°	10	32	171	50	33	11
105°	33	49	232	405	366	36
115°	59	74	177	388	446	58
125°	82	97	165	300	352	73
135°	96	115	163	247	285	74
145°	110	126	161	202	223	69
155°	125	135	156	177	185	57
165°	136	140	149	158	161	38
175°	142	142	143	145	145	13
180°	142	142	142	142	142	



TEST NUMBER: P331873-930

CATALOG NUMBER: S123DIP-S340D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	443.4	443.0	442.8	442.5	442.2	441.7	441.0	440.3	439.5	438.8	439.4
5°	442.2	441.7	441.3	440.9	440.5	439.9	438.9	438.0	437.0	436.1	436.9
7.5°	437.9	437.4	437.0	436.6	436.2	435.5	434.6	433.6	432.6	431.6	432.4
10°	434.2	433.8	433.3	432.9	432.5	431.8	430.6	429.6	428.4	427.4	428.1
12.5°	429.3	429.0	428.6	428.3	428.0	427.2	426.2	425.2	424.1	423.1	423.7
15°	420.9	420.6	420.2	419.9	419.6	418.8	417.8	416.6	415.6	414.5	415.2
17.5°	411.1	410.7	410.3	409.8	409.4	408.6	407.5	406.4	405.3	404.2	404.6
20°	403.8	403.3	402.8	402.3	401.8	401.0	399.9	398.8	397.7	396.6	397.0
22.5°	395.6	395.1	394.6	394.1	393.6	392.8	391.7	390.6	389.5	388.4	388.7
25°	382.1	381.6	381.2	380.7	380.2	379.4	378.2	377.2	376.0	375.0	375.0
27.5°	367.8	367.3	366.8	366.3	365.8	365.0	363.9	362.6	361.5	360.3	360.4
30°	357.5	357.0	356.6	356.2	355.8	355.0	353.8	352.6	351.5	350.3	350.3
32.5°	347.2	346.6	346.0	345.4	345.0	344.1	343.2	342.3	341.4	340.6	340.1
35°	330.5	330.0	329.5	329.0	328.5	327.7	326.6	325.5	324.4	323.3	322.8
37.5°	313.5	312.8	312.2	311.5	311.0	310.1	308.9	307.8	306.7	305.6	305.0
40°	301.7	301.1	300.6	300.1	299.6	298.7	297.6	296.4	295.2	294.0	293.3
42.5°	289.8	289.2	288.6	288.0	287.5	286.6	285.4	284.2	283.1	281.8	281.2
45°	270.8	270.5	270.2	269.9	269.5	268.8	267.7	266.6	265.5	264.4	263.4
47.5°	252.1	251.6	251.1	250.6	250.1	249.4	248.3	247.3	246.3	245.2	244.3
50°	239.3	238.9	238.5	238.1	237.7	236.8	235.8	234.7	233.6	232.5	231.5
52.5°	225.9	225.7	225.3	225.1	224.8	224.0	222.9	221.8	220.6	219.4	218.7
55°	205.5	205.5	205.4	205.3	205.2	204.6	203.5	202.4	201.3	200.2	199.3
57.5°	186.1	185.8	185.5	185.2	184.9	184.3	183.4	182.5	181.7	180.8	180.0
60°	172.1	172.0	171.9	171.9	171.8	171.2	170.2	169.2	168.2	167.1	166.4
62.5°	159.6	159.4	159.2	159.0	158.7	158.2	157.1	156.1	155.1	154.1	153.4
65°	140.1	139.7	139.3	138.9	138.5	137.9	137.1	136.2	135.3	134.4	133.8
67.5°	119.6	119.2	118.9	118.5	118.1	117.6	117.0	116.3	115.7	115.0	114.5
70°	107.1	106.6	106.2	105.6	105.1	104.6	104.1	103.5	103.1	102.6	102.0
72.5°	94.1	93.7	93.4	92.9	92.5	92.1	91.6	91.0	90.4	89.8	89.3
75°	74.1	73.7	73.4	73.1	72.7	72.4	72.2	71.9	71.7	71.4	71.0
77.5°	56.3	56.2	56.0	55.8	55.6	55.4	55.1	54.8	54.5	54.1	53.9
80°	44.8	44.6	44.4	44.1	43.8	43.6	43.5	43.3	43.1	43.0	42.8
82.5°	33.6	33.5	33.5	33.4	33.3	33.3	33.3	33.3	33.3	33.2	33.0
85°	19.7	19.6	19.4	19.2	19.1	19.0	19.0	19.0	19.0	19.0	18.8
87.5°	8.0	7.9	7.8	7.8	7.7	7.7	7.8	7.9	8.0	8.2	8.0
90°	0.6	1.1	1.7	2.6	3.2	3.8	4.6	5.5	6.4	7.2	6.9
92.5°	3.6	5.3	7.7	9.9	12.4	16.6	24.2	36.6	48.8	44.3	33.4
95°	9.8	10.7	13.9	18.8	26.3	37.4	62.0	104.8	152.1	170.9	138.6
97.5°	16.7	17.0	19.5	23.7	31.1	43.3	66.7	115.0	193.9	264.8	283.2
100°	21.4	21.6	23.6	27.6	34.6	45.8	66.0	108.6	184.4	272.9	329.6
102.5°	26.2	26.7	28.5	32.3	38.5	48.8	66.9	103.1	170.6	257.9	331.9
105°	33.4	34.3	36.0	39.5	44.9	53.9	69.5	99.1	153.6	231.6	314.3
107.5°	41.2	42.0	43.7	47.0	52.2	60.5	74.2	98.8	142.8	208.5	283.6
110°	46.6	47.5	49.0	52.2	57.1	65.1	78.1	100.0	138.6	195.3	264.2



TEST NUMBER: P331873-930

CATALOG NUMBER: S123DIP-S340D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	51.8	52.6	54.1	57.2	62.1	70.0	82.0	102.3	136.2	186.5	247.4
115°	59.0	60.3	62.0	64.8	69.7	77.5	88.5	106.0	135.4	177.2	227.1
117.5°	66.4	67.7	69.1	71.8	77.3	84.5	95.3	111.0	135.9	171.6	214.7
120°	71.4	72.3	73.8	76.6	82.1	89.3	99.7	114.6	136.9	169.1	208.3
122.5°	75.8	76.7	78.1	81.3	86.5	94.2	104.3	118.1	138.4	167.5	203.0
125°	82.1	82.7	84.4	87.6	93.0	100.9	111.0	123.6	140.9	165.3	196.2
127.5°	86.9	87.7	89.9	93.1	99.1	107.0	116.7	128.1	143.7	164.4	190.2
130°	89.9	90.7	93.4	96.8	102.9	110.6	120.2	131.1	145.5	163.6	186.9
132.5°	92.2	93.3	96.1	100.3	106.3	113.9	123.1	133.9	146.9	163.4	184.0
135°	96.2	97.3	100.5	104.8	111.0	118.7	127.6	137.5	149.0	163.1	180.1
137.5°	100.0	101.3	104.4	108.9	115.0	122.1	130.8	140.1	150.3	162.4	176.7
140°	102.6	104.0	106.9	111.5	117.2	124.5	132.8	141.5	151.2	162.2	174.6
142.5°	105.3	106.6	109.7	113.8	119.6	126.3	134.4	142.8	152.0	161.8	172.8
145°	109.7	110.6	113.2	117.6	122.5	129.1	136.6	144.3	152.4	161.0	170.2
147.5°	114.3	114.8	117.3	121.1	125.8	131.4	138.3	145.3	152.4	160.0	167.9
150°	117.2	117.6	119.8	123.6	127.6	132.8	139.4	145.5	152.4	159.1	166.2
152.5°	120.3	120.3	122.6	125.9	129.5	134.4	140.1	145.9	151.7	157.9	164.4
155°	124.7	124.7	126.5	129.4	132.6	136.6	141.5	146.1	151.0	155.9	161.6
157.5°	128.3	128.6	130.0	132.5	135.2	138.3	142.2	146.3	150.0	154.1	158.5
160°	131.1	131.1	132.2	134.5	136.6	139.4	142.9	146.3	149.5	152.7	156.5
162.5°	133.1	133.1	134.1	135.9	137.7	140.1	143.2	146.1	148.6	151.3	154.3
165°	136.2	136.0	136.6	138.0	139.2	141.2	143.5	145.5	147.2	149.3	151.6
167.5°	138.6	138.3	138.6	139.7	140.5	141.8	143.4	145.0	145.9	147.2	148.9
170°	140.0	139.4	139.7	140.6	141.2	141.8	143.2	144.3	145.0	145.8	147.2
172.5°	141.0	140.6	140.6	141.3	141.6	141.9	143.2	144.1	144.2	144.6	145.6
175°	142.0	141.8	141.5	142.0	142.0	142.4	142.9	143.5	143.2	143.2	143.7
177.5°	142.6	142.4	142.1	142.4	142.4	142.4	142.6	143.0	142.6	142.4	142.6
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P331873-930

CATALOG NUMBER: S123DIP-S340D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	440.1	440.8	441.5	441.8	441.7	441.6	441.6	441.5
5°	437.8	438.6	439.5	439.9	439.7	439.5	439.3	439.1
7.5°	433.2	433.9	434.6	435.0	434.9	434.8	434.7	434.6
10°	428.9	429.7	430.4	430.7	430.6	430.4	430.2	430.1
12.5°	424.2	424.8	425.3	425.6	425.5	425.3	425.3	425.2
15°	415.8	416.5	417.2	417.3	416.7	416.2	415.7	415.2
17.5°	405.1	405.6	406.1	406.3	406.0	405.9	405.7	405.5
20°	397.3	397.6	397.9	398.0	397.7	397.5	397.2	397.0
22.5°	388.9	389.2	389.5	389.5	389.1	388.8	388.5	388.2
25°	375.1	375.2	375.3	375.2	375.0	374.7	374.5	374.2
27.5°	360.4	360.5	360.5	360.4	360.1	359.8	359.5	359.1
30°	350.3	350.3	350.3	349.9	349.4	348.8	348.2	347.6
32.5°	339.6	339.1	338.7	338.3	337.9	337.6	337.3	337.0
35°	322.3	321.8	321.2	320.8	320.4	319.9	319.5	319.1
37.5°	304.4	303.8	303.1	302.7	302.5	302.1	301.9	301.7
40°	292.7	292.0	291.3	290.8	290.5	290.2	289.8	289.5
42.5°	280.5	279.8	279.2	278.7	278.3	278.0	277.7	277.3
45°	262.4	261.4	260.3	259.7	259.2	258.8	258.4	258.0
47.5°	243.3	242.3	241.2	240.6	240.2	239.9	239.5	239.1
50°	230.6	229.7	228.8	228.0	227.6	227.1	226.6	226.0
52.5°	217.8	217.0	216.2	215.6	215.1	214.6	214.1	213.6
55°	198.4	197.4	196.5	195.8	195.4	194.9	194.5	194.1
57.5°	179.2	178.3	177.5	176.8	176.3	175.9	175.4	174.9
60°	165.7	164.9	164.1	163.5	163.1	162.7	162.2	161.8
62.5°	152.5	151.8	151.1	150.5	150.3	149.9	149.7	149.4
65°	133.1	132.5	131.8	131.3	131.1	130.8	130.5	130.3
67.5°	113.8	113.2	112.7	112.2	111.9	111.5	111.1	110.8
70°	101.4	100.8	100.2	99.7	99.3	98.9	98.4	98.0
72.5°	88.8	88.2	87.7	87.3	87.2	86.9	86.7	86.4
75°	70.6	70.1	69.7	69.4	69.1	68.9	68.6	68.4
77.5°	53.6	53.3	53.0	52.9	52.9	52.9	52.9	52.9
80°	42.7	42.6	42.6	42.6	42.6	42.6	42.6	42.6
82.5°	32.9	32.8	32.6	32.4	32.4	32.4	32.3	32.2
85°	18.7	18.5	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	8.0	8.0	8.0	8.1	8.0	8.1	8.1	8.1
90°	7.2	7.5	7.7	8.3	8.1	8.3	8.6	8.3
92.5°	24.3	19.2	17.0	15.5	15.0	14.1	14.4	13.9
95°	103.7	70.3	55.0	44.7	39.2	36.6	34.6	33.4
97.5°	258.5	207.1	169.9	135.5	114.2	101.3	93.4	91.0
100°	339.7	316.3	282.7	241.7	212.6	191.6	180.3	180.7
102.5°	366.6	365.9	346.3	320.3	297.7	281.0	271.7	265.0
105°	374.5	403.3	408.8	401.4	388.1	377.2	367.9	366.5
107.5°	351.8	398.6	423.9	434.1	434.4	430.6	427.5	424.9
110°	330.2	383.2	419.5	439.7	447.8	450.0	449.5	448.9





TEST NUMBER: P331873-930

CATALOG NUMBER: S123DIP-S340D365U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	308.8	362.9	403.6	429.5	444.3	451.4	453.6	453.7
115°	280.3	330.4	372.8	404.2	425.8	438.5	444.3	445.7
117.5°	259.8	303.0	341.0	372.9	395.5	410.0	418.2	420.2
120°	248.9	287.8	322.4	351.5	374.2	390.4	397.3	399.0
122.5°	240.4	275.6	307.6	334.7	354.9	369.4	377.0	379.2
125°	229.0	260.5	288.1	311.2	329.6	342.3	349.5	351.5
127.5°	219.2	247.1	272.1	293.1	309.5	320.3	326.9	328.6
130°	212.9	238.9	262.2	281.8	297.0	307.4	313.5	315.8
132.5°	207.2	231.0	252.7	271.4	285.8	296.1	301.5	303.1
135°	199.3	219.8	238.6	254.9	269.1	277.8	282.9	284.9
137.5°	192.2	209.0	225.2	239.5	251.3	260.1	264.4	265.8
140°	188.2	202.8	216.6	229.0	240.0	248.1	252.7	252.4
142.5°	184.3	196.8	208.8	219.6	228.9	236.1	240.2	239.9
145°	179.5	189.0	198.2	206.6	213.8	219.8	222.2	222.7
147.5°	175.6	183.2	190.6	196.6	202.0	206.1	208.3	208.6
150°	172.8	179.5	185.6	191.0	195.3	198.5	200.2	200.2
152.5°	170.3	176.0	181.4	186.0	189.3	192.2	193.3	193.3
155°	166.6	171.1	175.5	178.9	181.5	183.8	184.4	184.7
157.5°	162.5	166.3	169.7	172.4	174.6	176.3	176.8	176.8
160°	160.2	163.4	166.2	168.3	170.2	172.0	172.0	171.7
162.5°	157.4	160.1	162.8	164.6	165.9	167.4	167.4	167.1
165°	153.8	155.6	157.6	159.1	160.2	161.3	161.0	161.0
167.5°	150.7	152.1	153.2	154.3	154.7	155.6	155.3	155.3
170°	148.6	149.5	150.7	151.2	151.6	152.1	151.8	151.8
172.5°	146.8	147.5	148.4	148.7	148.8	149.4	148.9	148.6
175°	144.3	144.6	145.2	145.2	145.2	145.5	145.2	145.0
177.5°	142.8	143.0	143.2	143.2	143.0	143.2	142.8	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4

(END OF REPORT)