

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831274

Luminaire Tested: S123DIP-S1165D585U927-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831274
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D585U927-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5813.0 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 57.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73	
1	104	99	96	92	98	94	91	88	85	83	80	77	75	73	69	68	66	66	66	66	63	
2	95	88	82	77	90	84	78	74	76	72	68	69	65	62	62	59	57	57	57	57	54	
3	87	78	71	65	83	74	68	63	68	63	58	61	57	54	56	52	50	50	50	50	47	
4	80	70	62	56	76	67	60	54	61	55	51	55	51	47	50	47	44	44	44	44	41	
5	74	63	55	49	71	60	53	48	55	49	45	50	46	42	46	42	39	39	39	39	36	
6	69	57	49	43	65	55	47	42	50	44	40	46	41	37	42	38	35	35	35	35	32	
7	64	52	44	39	61	50	43	38	46	40	36	42	37	34	39	35	32	32	32	32	29	
8	60	48	40	35	57	46	39	34	43	37	32	39	34	30	36	32	29	29	29	29	27	
9	56	44	37	32	54	43	36	31	39	34	29	36	31	28	34	29	26	26	26	26	24	
10	53	41	34	29	50	39	33	28	37	31	27	34	29	26	32	27	24	24	24	24	23	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	28243	28243	28243	28243	28243
5°	35718	33713	28496	22964	21102
10°	36066	37156	28306	18306	15996
15°	27164	34497	28113	15502	13527
20°	18927	27915	27755	13557	12287
25°	14433	21467	27143	12473	11525
30°	12485	17055	26166	11706	10912
35°	11583	14399	25039	11152	10479
40°	10967	12917	23456	10624	10333
45°	10602	11954	21444	10213	10268
50°	10419	11194	19063	9838	10215
55°	10031	10637	16726	9483	10260
60°	9672	10038	14417	9147	10092
65°	9088	9475	12437	8792	9892
70°	8393	8755	10578	8201	9312
75°	7594	7848	9062	7619	8509
80°	6267	6868	7172	6639	7172
85°	4965	5570	5261	5644	5718

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 24484 cd/sqm



TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.1	4.3
10°-20°	617.1	10.6
20°-30°	730.7	12.6
30°-40°	734.7	12.6
40°-50°	674.1	11.6
50°-60°	556.4	9.6
60°-70°	393.6	6.8
70°-80°	210.1	3.6
80°-90°	54.5	0.9
90°-100°	37.0	0.6
100°-110°	112.1	1.9
110°-120°	190.8	3.3
120°-130°	251.0	4.3
130°-140°	282.1	4.9
140°-150°	277.4	4.8
150°-160°	233.5	4.0
160°-170°	155.5	2.7
170°-180°	54.4	0.9
0°-30°	1595.9	27.5
0°-40°	2330.6	40.1
0°-60°	3561.0	61.3
0°-90°	4219.2	72.6
90°-120°	339.9	5.8
90°-150°	1150.4	19.8
90°-180°	1594.0	27.4
0°-180°	5813.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2624	2624	2624	2624	2624	
5°	3306	3120	2637	2125	1953	315
15°	2438	3096	2523	1391	1214	673
25°	1215	1808	2285	1050	970	573
35°	882	1096	1906	849	798	554
45°	696	785	1409	671	674	539
55°	534	567	891	505	547	478
65°	357	372	488	345	388	355
75°	183	189	218	183	205	192
85°	40	45	43	46	46	45
90°	14	11	0	11	14	9
95°	35	33	27	33	35	35
105°	108	107	102	107	108	114
115°	192	192	192	192	192	191
125°	278	282	281	282	278	249
135°	364	367	365	367	364	280
145°	442	445	442	445	442	276
155°	506	507	506	507	506	233
165°	550	550	552	550	550	155
175°	572	572	574	572	572	54
180°	575	575	575	575	575	



TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2957.5	2954.5	2951.4	2936.2	2921.0	2913.7	2906.4	2884.5	2862.5	2838.2	2813.8
5°	3305.7	3314.3	3322.8	3313.0	3303.3	3273.5	3243.6	3204.1	3164.5	3120.1	3075.6
7.5°	3466.5	3471.3	3476.2	3470.1	3464.0	3456.1	3448.2	3412.9	3377.6	3331.9	3286.3
10°	3299.7	3310.6	3321.6	3345.3	3369.1	3395.8	3422.6	3417.8	3412.9	3399.5	3386.1
12.5°	2933.2	2946.6	2959.9	3007.4	3054.9	3115.8	3176.7	3229.0	3281.4	3317.9	3354.4
15°	2437.6	2474.7	2511.9	2555.1	2598.3	2687.8	2777.3	2887.5	2997.7	3095.7	3193.7
17.5°	2007.8	2021.8	2035.8	2082.1	2128.3	2241.0	2353.6	2480.8	2608.1	2770.6	2933.2
20°	1652.3	1665.0	1677.8	1738.7	1799.6	1887.9	1976.1	2119.2	2262.3	2437.0	2611.7
22.5°	1388.0	1408.1	1428.2	1462.3	1496.4	1581.0	1665.7	1792.9	1920.1	2113.1	2306.1
25°	1215.2	1229.8	1244.4	1265.1	1285.8	1353.3	1420.9	1525.6	1630.3	1807.5	1984.7
27.5°	1097.0	1103.1	1109.2	1129.9	1150.6	1194.5	1238.3	1328.4	1418.5	1568.9	1719.2
30°	1004.5	1008.8	1013.0	1031.3	1049.6	1079.4	1109.2	1174.4	1239.5	1372.2	1504.9
32.5°	940.0	943.0	946.1	960.1	974.1	995.4	1016.7	1064.2	1111.7	1221.2	1330.8
35°	881.5	883.4	885.2	895.5	905.9	921.7	937.5	973.5	1009.4	1095.8	1182.3
37.5°	830.4	832.8	835.3	841.4	847.4	861.4	875.4	904.1	932.7	999.0	1065.4
40°	780.5	784.7	789.0	793.3	797.5	809.1	820.7	842.6	864.5	919.3	974.1
42.5°	737.9	742.1	746.4	748.2	750.0	756.7	763.4	783.5	803.6	844.4	885.2
45°	696.5	698.3	700.1	701.9	703.8	709.2	714.7	732.4	750.0	785.3	820.7
47.5°	658.7	658.7	658.7	659.9	661.1	666.0	670.9	683.7	696.5	723.9	751.3
50°	622.2	622.2	622.2	620.4	618.5	621.6	624.6	634.4	644.1	668.5	692.8
52.5°	578.4	578.4	578.4	579.0	579.6	579.6	579.6	588.1	596.6	618.5	640.4
55°	534.5	537.0	539.4	537.6	535.7	537.0	538.2	543.7	549.1	566.8	584.4
57.5°	490.7	491.9	493.1	492.5	491.9	492.5	493.1	498.0	502.9	516.3	529.6
60°	449.3	449.3	449.3	448.1	446.9	448.1	449.3	451.7	454.2	466.3	478.5
62.5°	403.0	403.6	404.2	404.8	405.5	404.2	403.0	406.1	409.1	418.2	427.4
65°	356.8	357.4	358.0	359.8	361.6	360.4	359.2	362.2	365.3	372.0	378.7
67.5°	315.4	314.1	312.9	313.5	314.1	316.0	317.8	318.4	319.0	326.3	333.6
70°	266.7	267.9	269.1	268.5	267.9	268.5	269.1	270.9	272.7	278.2	283.7
72.5°	222.8	223.4	224.0	224.0	224.0	225.3	226.5	228.3	230.1	233.2	236.2
75°	182.6	182.6	182.6	183.9	185.1	185.7	186.3	186.3	186.3	188.7	191.2
77.5°	138.8	141.8	144.9	144.3	143.7	144.9	146.1	147.9	149.8	151.0	152.2
80°	101.1	101.1	101.1	101.7	102.3	104.1	105.9	107.1	108.4	110.8	113.2
82.5°	64.5	65.1	65.7	67.6	69.4	70.6	71.8	73.7	75.5	75.5	75.5
85°	40.2	39.0	37.7	39.0	40.2	41.4	42.6	43.2	43.8	45.1	46.3
87.5°	19.5	19.5	19.5	19.5	19.5	20.1	20.7	20.7	20.7	20.7	20.7
90°	13.6	13.4	13.2	13.0	12.8	12.5	12.0	11.6	11.2	10.8	9.5
92.5°	19.4	19.6	19.8	20.0	20.2	20.2	19.9	19.6	19.3	19.0	18.4
95°	35.2	35.2	35.2	35.2	35.2	35.0	34.6	34.2	33.8	33.4	32.6
97.5°	50.6	50.7	50.8	50.9	51.0	50.8	50.3	49.8	49.3	48.8	48.2
100°	68.7	68.5	68.3	68.1	67.9	67.6	67.3	67.0	66.7	66.4	65.9
102.5°	87.2	87.3	87.4	87.5	87.6	87.5	87.2	86.9	86.6	86.3	85.6
105°	107.5	107.3	107.1	106.9	106.7	106.6	106.6	106.6	106.6	106.6	105.7
107.5°	128.3	128.4	128.5	128.6	128.7	128.6	128.3	128.0	127.7	127.4	127.0
110°	149.6	149.8	150.0	150.2	150.4	150.3	149.9	149.5	149.1	148.7	148.5



TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.2	172.2	172.2	172.2	172.2	171.9	171.4	170.9	170.4	169.9	169.9
115°	192.5	192.6	192.7	192.8	192.9	192.9	192.8	192.7	192.6	192.5	192.7
117.5°	213.3	213.6	213.9	214.2	214.5	214.6	214.6	214.6	214.6	214.6	214.8
120°	235.4	235.6	235.8	236.0	236.2	236.4	236.5	236.6	236.7	236.8	237.3
122.5°	256.7	257.0	257.3	257.6	257.9	258.2	258.5	258.8	259.1	259.4	259.6
125°	277.9	278.3	278.7	279.1	279.5	279.9	280.3	280.7	281.1	281.5	281.7
127.5°	299.1	299.5	299.9	300.3	300.7	301.2	301.8	302.4	303.0	303.6	303.8
130°	319.9	320.6	321.3	322.0	322.7	323.3	323.7	324.1	324.5	324.9	325.2
132.5°	341.6	342.1	342.6	343.1	343.6	344.1	344.6	345.1	345.6	346.1	346.3
135°	364.2	364.4	364.6	364.8	365.0	365.3	365.7	366.1	366.5	366.9	367.0
137.5°	384.1	384.4	384.7	385.0	385.3	385.7	386.2	386.7	387.2	387.7	387.4
140°	403.5	404.2	404.9	405.6	406.3	406.7	406.8	406.9	407.0	407.1	407.0
142.5°	423.4	423.9	424.4	424.9	425.4	425.7	425.8	425.9	426.0	426.1	425.9
145°	442.4	442.8	443.2	443.6	444.0	444.2	444.3	444.4	444.5	444.6	444.3
147.5°	459.5	460.1	460.7	461.3	461.9	462.2	462.2	462.2	462.2	462.2	461.9
150°	475.8	476.4	477.0	477.6	478.2	478.5	478.5	478.5	478.5	478.5	478.3
152.5°	491.6	492.1	492.6	493.1	493.6	493.8	493.6	493.4	493.2	493.0	492.9
155°	505.6	506.3	507.0	507.7	508.4	508.6	508.2	507.8	507.4	507.0	506.9
157.5°	518.7	519.3	519.9	520.5	521.1	521.2	520.8	520.4	520.0	519.6	519.5
160°	531.4	531.8	532.2	532.6	533.0	532.9	532.4	531.9	531.4	530.9	530.9
162.5°	540.9	541.6	542.3	543.0	543.7	543.8	543.3	542.8	542.3	541.8	541.7
165°	549.9	550.6	551.3	552.0	552.7	552.8	552.2	551.6	551.0	550.4	550.4
167.5°	558.0	558.6	559.2	559.8	560.4	560.4	559.8	559.2	558.6	558.0	557.9
170°	563.9	564.6	565.3	566.0	566.7	566.7	566.0	565.3	564.6	563.9	563.9
172.5°	568.4	569.1	569.8	570.5	571.2	571.3	570.7	570.1	569.5	568.9	568.9
175°	571.6	572.3	573.0	573.7	574.4	574.5	573.9	573.3	572.6	572.0	572.0
177.5°	573.4	574.1	574.8	575.5	576.2	576.3	575.7	575.1	574.5	573.9	573.9
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2



TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2806.5	2799.2	2772.4	2745.7	2715.2	2684.8	2662.3	2639.7	2606.2	2572.8	2545.4
5°	3041.5	3007.4	2950.8	2894.2	2817.5	2740.8	2689.0	2637.3	2567.9	2498.5	2443.1
7.5°	3227.8	3169.4	3090.2	3011.1	2910.6	2810.2	2715.2	2620.2	2514.3	2408.4	2321.9
10°	3346.5	3307.0	3215.6	3124.3	2989.8	2855.2	2722.5	2589.8	2453.4	2317.1	2202.6
12.5°	3358.1	3361.8	3277.7	3193.7	3041.5	2889.3	2728.0	2566.7	2395.0	2223.3	2090.0
15°	3256.4	3319.1	3272.9	3226.6	3073.2	2919.8	2721.3	2522.8	2325.0	2127.1	1973.1
17.5°	3067.7	3202.2	3208.9	3215.6	3062.2	2908.8	2689.0	2469.3	2245.2	2021.2	1859.3
20°	2810.2	3008.7	3076.8	3145.0	3020.2	2895.4	2659.2	2423.0	2172.2	1921.3	1751.5
22.5°	2547.2	2788.3	2913.1	3037.9	2945.3	2852.8	2601.4	2349.9	2085.1	1820.3	1648.0
25°	2247.7	2510.7	2702.4	2894.2	2837.6	2781.0	2533.2	2285.4	2003.5	1721.7	1545.7
27.5°	1986.5	2253.8	2485.1	2716.4	2704.3	2692.1	2446.1	2200.2	1911.6	1623.0	1453.2
30°	1753.9	2002.9	2261.7	2520.4	2550.2	2580.1	2342.6	2105.2	1816.0	1526.9	1363.1
32.5°	1548.2	1765.5	2043.1	2320.7	2379.2	2437.6	2223.3	2009.0	1722.9	1436.8	1279.1
35°	1379.5	1576.8	1854.4	2132.0	2205.0	2278.1	2091.8	1905.5	1626.7	1347.9	1197.5
37.5°	1230.4	1395.4	1666.3	1937.2	2026.7	2116.2	1949.4	1782.5	1521.4	1260.2	1122.0
40°	1106.8	1239.5	1488.5	1737.5	1841.0	1944.5	1806.9	1669.3	1421.5	1173.8	1046.5
42.5°	1003.3	1121.4	1347.3	1573.1	1672.4	1771.6	1655.3	1539.0	1318.6	1098.3	982.0
45°	915.0	1009.4	1214.5	1419.7	1514.1	1608.4	1508.6	1408.7	1214.5	1020.3	912.0
47.5°	832.2	913.2	1088.5	1263.9	1347.9	1431.9	1354.0	1276.0	1111.7	947.3	849.3
50°	757.9	823.1	976.5	1129.9	1203.0	1276.0	1207.2	1138.4	1003.3	868.1	782.9
52.5°	693.4	746.4	874.8	1003.3	1066.0	1128.7	1069.6	1010.6	903.4	796.3	722.0
55°	629.5	674.5	786.0	897.4	940.0	982.6	936.9	891.3	804.8	718.4	655.7
57.5°	569.8	610.0	701.3	792.6	825.5	858.4	817.0	775.6	710.5	645.3	593.0
60°	511.4	544.3	620.4	696.5	716.5	736.6	703.2	669.7	624.0	578.4	531.5
62.5°	457.2	487.0	543.7	600.3	613.7	627.1	601.5	575.9	541.2	506.5	470.0
65°	401.2	423.7	470.0	516.3	524.8	533.3	510.8	488.3	462.1	435.9	409.1
67.5°	349.4	365.3	403.0	440.8	441.4	442.0	423.7	405.5	390.8	376.2	354.9
70°	298.9	314.1	339.1	364.1	364.7	365.3	350.7	336.1	325.1	314.1	298.3
72.5°	247.2	258.1	277.0	295.9	294.7	293.4	284.3	275.2	266.7	258.1	246.6
75°	200.3	209.4	222.2	235.0	231.3	227.7	222.8	217.9	210.6	203.3	196.0
77.5°	157.7	163.2	170.5	177.8	175.3	172.9	168.6	164.4	158.9	153.4	150.4
80°	115.7	118.1	123.0	127.8	126.6	125.4	120.5	115.7	114.5	113.2	109.0
82.5°	78.5	81.6	82.8	84.0	83.4	82.8	79.1	75.5	74.3	73.1	72.4
85°	46.9	47.5	48.1	48.7	46.9	45.1	43.8	42.6	42.6	42.6	42.0
87.5°	21.3	21.9	21.9	21.9	21.3	20.7	19.5	18.3	18.9	19.5	19.5
90°	8.2	6.9	5.6	4.5	3.5	2.5	1.5	0.5	1.5	2.5	3.5
92.5°	17.8	17.2	16.6	16.0	15.4	14.8	14.2	13.6	14.2	14.8	15.4
95°	31.8	31.0	30.2	29.5	28.8	28.1	27.4	26.7	27.4	28.1	28.8
97.5°	47.6	47.0	46.4	45.8	45.3	44.8	44.3	43.8	44.3	44.8	45.3
100°	65.4	64.9	64.4	63.9	63.3	62.7	62.1	61.5	62.1	62.7	63.3
102.5°	84.9	84.2	83.5	83.0	82.7	82.4	82.1	81.8	82.1	82.4	82.7
105°	104.8	103.9	103.0	102.5	102.3	102.1	101.9	101.7	101.9	102.1	102.3
107.5°	126.6	126.2	125.8	125.6	125.5	125.4	125.3	125.2	125.3	125.4	125.5
110°	148.3	148.1	147.9	147.7	147.5	147.3	147.1	146.9	147.1	147.3	147.5



TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	169.9	169.9	169.9	169.8	169.7	169.6	169.5	169.4	169.5	169.6	169.7
115°	192.9	193.1	193.3	193.2	192.9	192.6	192.3	192.0	192.3	192.6	192.9
117.5°	215.0	215.2	215.4	215.5	215.4	215.3	215.2	215.1	215.2	215.3	215.4
120°	237.8	238.3	238.8	238.7	238.1	237.5	236.9	236.3	236.9	237.5	238.1
122.5°	259.8	260.0	260.2	260.1	259.7	259.3	258.9	258.5	258.9	259.3	259.7
125°	281.9	282.1	282.3	282.3	282.0	281.7	281.4	281.1	281.4	281.7	282.0
127.5°	304.0	304.2	304.4	304.2	303.6	303.0	302.4	301.8	302.4	303.0	303.6
130°	325.5	325.8	326.1	325.8	325.0	324.2	323.4	322.6	323.4	324.2	325.0
132.5°	346.5	346.7	346.9	346.6	345.8	345.0	344.2	343.4	344.2	345.0	345.8
135°	367.1	367.2	367.3	367.1	366.5	365.9	365.2	364.6	365.2	365.9	366.5
137.5°	387.1	386.8	386.5	386.1	385.6	385.1	384.6	384.1	384.6	385.1	385.6
140°	406.9	406.8	406.7	406.4	405.9	405.4	404.9	404.4	404.9	405.4	405.9
142.5°	425.7	425.5	425.3	424.9	424.4	423.9	423.4	422.9	423.4	423.9	424.4
145°	444.0	443.7	443.4	443.2	443.0	442.8	442.6	442.4	442.6	442.8	443.0
147.5°	461.6	461.3	461.0	460.7	460.3	459.9	459.5	459.1	459.5	459.9	460.3
150°	478.1	477.9	477.7	477.5	477.3	477.1	476.9	476.7	476.9	477.1	477.3
152.5°	492.8	492.7	492.6	492.4	492.1	491.8	491.5	491.2	491.5	491.8	492.1
155°	506.8	506.7	506.6	506.5	506.5	506.5	506.5	506.5	506.5	506.5	506.5
157.5°	519.4	519.3	519.2	519.2	519.3	519.4	519.5	519.6	519.5	519.4	519.3
160°	530.9	530.9	530.9	531.0	531.2	531.4	531.6	531.8	531.6	531.4	531.2
162.5°	541.6	541.5	541.4	541.5	541.8	542.1	542.4	542.7	542.4	542.1	541.8
165°	550.4	550.4	550.4	550.5	550.8	551.1	551.4	551.7	551.4	551.1	550.8
167.5°	557.8	557.7	557.6	557.8	558.2	558.6	559.0	559.4	559.0	558.6	558.2
170°	563.9	563.9	563.9	564.1	564.5	564.9	565.3	565.7	565.3	564.9	564.5
172.5°	568.9	568.9	568.9	569.1	569.5	569.9	570.3	570.7	570.3	569.9	569.5
175°	572.0	572.0	572.0	572.2	572.6	573.0	573.5	573.9	573.5	573.0	572.6
177.5°	573.9	573.9	573.9	574.1	574.5	574.9	575.3	575.7	575.3	574.9	574.5
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2



TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2518.0	2494.2	2470.5	2452.2	2434.0	2402.9	2371.9	2364.6	2357.2	2346.9	2336.5
5°	2387.7	2329.2	2270.8	2218.4	2166.1	2125.3	2084.5	2057.7	2030.9	2011.5	1992.0
7.5°	2235.5	2147.8	2060.2	1998.1	1936.0	1876.9	1817.9	1799.0	1780.1	1754.5	1729.0
10°	2088.2	1991.4	1894.6	1813.6	1732.6	1674.8	1617.0	1593.8	1570.7	1538.4	1506.2
12.5°	1956.7	1850.7	1744.8	1663.2	1581.6	1525.6	1469.6	1436.1	1402.7	1384.4	1366.1
15°	1819.1	1705.8	1592.6	1517.1	1441.6	1391.1	1340.6	1311.3	1282.1	1264.5	1246.8
17.5°	1697.3	1585.3	1473.3	1400.8	1328.4	1282.1	1235.8	1210.3	1184.7	1171.3	1157.9
20°	1581.6	1472.1	1362.5	1291.9	1221.2	1183.5	1145.7	1129.3	1112.9	1101.9	1091.0
22.5°	1475.7	1368.0	1260.2	1199.9	1139.7	1109.2	1078.8	1067.2	1055.6	1046.5	1037.4
25°	1369.8	1273.6	1177.4	1126.3	1075.1	1050.2	1025.2	1013.6	1002.1	992.9	983.8
27.5°	1283.3	1191.4	1099.5	1055.6	1011.8	992.3	972.9	963.7	954.6	946.1	937.5
30°	1199.3	1117.1	1034.9	997.2	959.5	941.8	924.1	915.0	905.9	898.0	890.1
32.5°	1121.4	1050.8	980.2	945.5	910.8	896.1	881.5	870.6	859.6	853.5	847.4
35°	1047.1	983.8	920.5	891.9	863.3	848.7	834.0	824.9	815.8	810.9	806.0
37.5°	983.8	927.2	870.6	843.2	815.8	801.8	787.8	779.9	771.9	770.1	768.3
40°	919.3	870.6	821.9	795.1	768.3	756.1	743.9	739.1	734.2	733.0	731.8
42.5°	865.7	818.2	770.7	746.4	722.0	711.7	701.3	698.9	696.5	698.3	700.1
45°	803.6	764.0	724.5	701.9	679.4	670.9	662.4	660.5	658.7	662.4	666.0
47.5°	751.3	714.7	678.2	656.9	635.6	629.5	623.4	622.8	622.2	627.1	631.9
50°	697.7	662.4	627.1	610.0	593.0	587.5	582.0	583.8	585.7	593.6	601.5
52.5°	647.8	614.9	582.0	566.2	550.3	546.7	543.0	547.3	551.6	560.1	568.6
55°	593.0	563.1	533.3	521.1	509.0	505.3	501.6	510.2	518.7	526.6	534.5
57.5°	540.6	514.4	488.3	477.3	466.3	465.7	465.1	473.0	480.9	489.5	498.0
60°	484.6	462.7	440.8	432.2	423.7	424.9	426.2	435.3	444.4	451.1	457.8
62.5°	433.5	415.2	396.9	389.0	381.1	384.1	387.2	396.3	405.5	413.4	421.3
65°	382.3	367.1	351.9	346.4	340.9	345.2	349.4	357.4	365.3	370.8	376.2
67.5°	333.6	320.8	308.0	303.8	299.5	303.8	308.0	316.0	323.9	329.4	334.8
70°	282.5	272.1	261.8	258.7	255.7	260.6	265.4	272.1	278.8	284.3	289.8
72.5°	235.0	227.1	219.2	218.6	217.9	222.2	226.5	233.2	239.9	243.5	247.2
75°	188.7	184.5	180.2	179.6	179.0	183.2	187.5	191.2	194.8	197.9	200.9
77.5°	147.3	143.7	140.0	140.6	141.2	144.3	147.3	151.0	154.6	156.5	158.3
80°	104.7	103.5	102.3	103.5	104.7	107.1	109.6	112.0	114.5	115.7	116.9
82.5°	71.8	70.6	69.4	71.2	73.1	74.9	76.7	78.5	80.4	81.0	81.6
85°	41.4	43.2	45.1	45.1	45.1	45.7	46.3	46.9	47.5	46.9	46.3
87.5°	19.5	20.1	20.7	20.7	20.7	21.3	21.9	21.9	21.9	21.3	20.7
90°	4.5	5.6	6.9	8.2	9.5	10.8	11.2	11.6	12.0	12.5	12.8
92.5°	16.0	16.6	17.2	17.8	18.4	19.0	19.3	19.6	19.9	20.2	20.2
95°	29.5	30.2	31.0	31.8	32.6	33.4	33.8	34.2	34.6	35.0	35.2
97.5°	45.8	46.4	47.0	47.6	48.2	48.8	49.3	49.8	50.3	50.8	51.0
100°	63.9	64.4	64.9	65.4	65.9	66.4	66.7	67.0	67.3	67.6	67.9
102.5°	83.0	83.5	84.2	84.9	85.6	86.3	86.6	86.9	87.2	87.5	87.6
105°	102.5	103.0	103.9	104.8	105.7	106.6	106.6	106.6	106.6	106.6	106.7
107.5°	125.6	125.8	126.2	126.6	127.0	127.4	127.7	128.0	128.3	128.6	128.7
110°	147.7	147.9	148.1	148.3	148.5	148.7	149.1	149.5	149.9	150.3	150.4



TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	169.8	169.9	169.9	169.9	169.9	169.9	170.4	170.9	171.4	171.9	172.2
115°	193.2	193.3	193.1	192.9	192.7	192.5	192.6	192.7	192.8	192.9	192.9
117.5°	215.5	215.4	215.2	215.0	214.8	214.6	214.6	214.6	214.6	214.6	214.5
120°	238.7	238.8	238.3	237.8	237.3	236.8	236.7	236.6	236.5	236.4	236.2
122.5°	260.1	260.2	260.0	259.8	259.6	259.4	259.1	258.8	258.5	258.2	257.9
125°	282.3	282.3	282.1	281.9	281.7	281.5	281.1	280.7	280.3	279.9	279.5
127.5°	304.2	304.4	304.2	304.0	303.8	303.6	303.0	302.4	301.8	301.2	300.7
130°	325.8	326.1	325.8	325.5	325.2	324.9	324.5	324.1	323.7	323.3	322.7
132.5°	346.6	346.9	346.7	346.5	346.3	346.1	345.6	345.1	344.6	344.1	343.6
135°	367.1	367.3	367.2	367.1	367.0	366.9	366.5	366.1	365.7	365.3	365.0
137.5°	386.1	386.5	386.8	387.1	387.4	387.7	387.2	386.7	386.2	385.7	385.3
140°	406.4	406.7	406.8	406.9	407.0	407.1	407.0	406.9	406.8	406.7	406.3
142.5°	424.9	425.3	425.5	425.7	425.9	426.1	426.0	425.9	425.8	425.7	425.4
145°	443.2	443.4	443.7	444.0	444.3	444.6	444.5	444.4	444.3	444.2	444.0
147.5°	460.7	461.0	461.3	461.6	461.9	462.2	462.2	462.2	462.2	462.2	461.9
150°	477.5	477.7	477.9	478.1	478.3	478.5	478.5	478.5	478.5	478.5	478.2
152.5°	492.4	492.6	492.7	492.8	492.9	493.0	493.2	493.4	493.6	493.8	493.6
155°	506.5	506.6	506.7	506.8	506.9	507.0	507.4	507.8	508.2	508.6	508.4
157.5°	519.2	519.2	519.3	519.4	519.5	519.6	520.0	520.4	520.8	521.2	521.1
160°	531.0	530.9	530.9	530.9	530.9	530.9	531.4	531.9	532.4	532.9	533.0
162.5°	541.5	541.4	541.5	541.6	541.7	541.8	542.3	542.8	543.3	543.8	543.7
165°	550.5	550.4	550.4	550.4	550.4	550.4	551.0	551.6	552.2	552.8	552.7
167.5°	557.8	557.6	557.7	557.8	557.9	558.0	558.6	559.2	559.8	560.4	560.4
170°	564.1	563.9	563.9	563.9	563.9	563.9	564.6	565.3	566.0	566.7	566.7
172.5°	569.1	568.9	568.9	568.9	568.9	568.9	569.5	570.1	570.7	571.3	571.2
175°	572.2	572.0	572.0	572.0	572.0	572.0	572.6	573.3	573.9	574.5	574.4
177.5°	574.1	573.9	573.9	573.9	573.9	573.9	574.5	575.1	575.7	576.3	576.2
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2



TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2623.9	2623.9	2623.9	2623.9
2.5°	2332.3	2328.0	2311.0	2293.9
5°	1977.4	1962.7	1957.9	1953.0
7.5°	1727.8	1726.5	1701.0	1675.4
10°	1508.0	1509.8	1486.7	1463.5
12.5°	1350.9	1335.7	1333.9	1332.0
15°	1232.8	1218.8	1216.4	1213.9
17.5°	1149.4	1140.9	1138.4	1136.0
20°	1086.1	1081.2	1077.0	1072.7
22.5°	1031.3	1025.2	1021.6	1017.9
25°	978.3	972.9	971.6	970.4
27.5°	930.8	924.1	924.1	924.1
30°	885.8	881.5	879.7	877.9
32.5°	843.8	840.1	840.1	840.1
35°	804.2	802.4	800.0	797.5
37.5°	768.3	768.3	767.1	765.9
40°	733.6	735.4	735.4	735.4
42.5°	701.9	703.8	703.8	703.8
45°	669.1	672.1	673.3	674.5
47.5°	636.8	641.7	642.9	644.1
50°	605.1	608.8	609.4	610.0
52.5°	572.9	577.1	580.2	583.2
55°	538.8	543.0	544.9	546.7
57.5°	502.3	506.5	507.1	507.7
60°	462.1	466.3	467.6	468.8
62.5°	423.7	426.2	427.4	428.6
65°	379.9	383.5	386.0	388.4
67.5°	337.9	340.9	340.9	340.9
70°	291.0	292.2	294.0	295.9
72.5°	247.8	248.4	248.4	248.4
75°	202.1	203.3	203.9	204.6
77.5°	158.9	159.5	159.5	159.5
80°	116.3	115.7	115.7	115.7
82.5°	79.8	77.9	77.9	77.9
85°	45.7	45.1	45.7	46.3
87.5°	20.7	20.7	20.7	20.7
90°	13.0	13.2	13.4	13.6
92.5°	20.0	19.8	19.6	19.4
95°	35.2	35.2	35.2	35.2
97.5°	50.9	50.8	50.7	50.6
100°	68.1	68.3	68.5	68.7
102.5°	87.5	87.4	87.3	87.2
105°	106.9	107.1	107.3	107.5
107.5°	128.6	128.5	128.4	128.3
110°	150.2	150.0	149.8	149.6



TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	172.2	172.2	172.2	172.2
115°	192.8	192.7	192.6	192.5
117.5°	214.2	213.9	213.6	213.3
120°	236.0	235.8	235.6	235.4
122.5°	257.6	257.3	257.0	256.7
125°	279.1	278.7	278.3	277.9
127.5°	300.3	299.9	299.5	299.1
130°	322.0	321.3	320.6	319.9
132.5°	343.1	342.6	342.1	341.6
135°	364.8	364.6	364.4	364.2
137.5°	385.0	384.7	384.4	384.1
140°	405.6	404.9	404.2	403.5
142.5°	424.9	424.4	423.9	423.4
145°	443.6	443.2	442.8	442.4
147.5°	461.3	460.7	460.1	459.5
150°	477.6	477.0	476.4	475.8
152.5°	493.1	492.6	492.1	491.6
155°	507.7	507.0	506.3	505.6
157.5°	520.5	519.9	519.3	518.7
160°	532.6	532.2	531.8	531.4
162.5°	543.0	542.3	541.6	540.9
165°	552.0	551.3	550.6	549.9
167.5°	559.8	559.2	558.6	558.0
170°	566.0	565.3	564.6	563.9
172.5°	570.5	569.8	569.1	568.4
175°	573.7	573.0	572.3	571.6
177.5°	575.5	574.8	574.1	573.4
180°	575.2	575.2	575.2	575.2



TEST NUMBER: P831274

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.07	18.12	17.82	18.88	19.79	19.31	20.36	20.05	21.11	22.03
	3H	18.73	19.67	19.49	20.44	21.38	20.75	21.69	21.50	22.45	23.40
	4H	19.32	20.20	20.09	20.98	21.94	21.20	22.09	21.98	22.87	23.82
	6H	19.70	20.51	20.49	21.30	22.27	21.49	22.31	22.28	23.09	24.06
	8H	19.80	20.58	20.60	21.38	22.35	21.56	22.33	22.35	23.14	24.11
	12H	19.85	20.59	20.65	21.39	22.38	21.58	22.32	22.38	23.12	24.12
4H	2H	17.67	18.55	18.45	19.33	20.29	19.49	20.38	20.27	21.16	22.11
	3H	19.51	20.25	20.30	21.06	22.03	21.13	21.86	21.92	22.68	23.65
	4H	20.22	20.89	21.02	21.70	22.70	21.72	22.39	22.52	23.20	24.20
	6H	20.70	21.28	21.53	22.12	23.12	22.13	22.71	22.96	23.55	24.55
	8H	20.84	21.38	21.67	22.22	23.23	22.25	22.79	23.07	23.62	24.64
	12H	20.92	21.40	21.76	22.26	23.28	22.30	22.79	23.15	23.64	24.66
8H	4H	20.50	21.04	21.32	21.87	22.89	21.84	22.38	22.66	23.21	24.23
	6H	21.09	21.54	21.95	22.41	23.43	22.35	22.79	23.20	23.67	24.69
	8H	21.30	21.70	22.17	22.57	23.60	22.53	22.92	23.39	23.79	24.83
	12H	21.43	21.78	22.30	22.64	23.73	22.64	22.99	23.50	23.85	24.94
12H	4H	20.51	20.99	21.35	21.85	22.87	21.82	22.31	22.67	23.16	24.18
	6H	21.14	21.54	22.01	22.41	23.45	22.36	22.76	23.23	23.63	24.66
	8H	21.39	21.74	22.25	22.60	23.69	22.57	22.92	23.44	23.78	24.87