

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831275

Luminaire Tested: S123DIP-S1165D585U927-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831275  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D585U927-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5898.2 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 57.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831275  
CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot



TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72				72
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	68	67	66	62				62
2	95	88	82	77	90	83	78	73	75	71	68	68	65	62	61	59	56	53				53
3	87	78	71	65	82	74	68	63	67	62	58	61	57	53	55	52	49	46				46
4	80	70	62	56	76	66	59	54	61	55	50	55	50	47	50	46	43	40				40
5	74	63	55	49	70	60	53	47	55	49	44	50	45	41	45	42	38	36				36
6	69	57	49	43	65	55	47	42	50	44	39	46	41	37	42	38	34	32				32
7	64	52	44	39	61	50	43	38	46	40	35	42	37	33	38	34	31	29				29
8	60	48	40	35	57	46	39	34	42	36	32	39	34	30	36	32	28	26				26
9	56	44	37	32	53	42	35	31	39	33	29	36	31	28	33	29	26	24				24
10	53	41	34	29	50	39	33	28	36	31	27	34	29	25	31	27	24	22				22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	28243	28243	28243	28243	28243
5°	35718	33713	28496	22964	21102
10°	36066	37156	28306	18306	15996
15°	27164	34497	28113	15502	13527
20°	18927	27915	27755	13557	12287
25°	14433	21467	27143	12473	11525
30°	12485	17055	26166	11706	10912
35°	11583	14399	25039	11152	10479
40°	10967	12917	23456	10624	10333
45°	10602	11954	21444	10213	10268
50°	10419	11194	19063	9838	10215
55°	10031	10637	16726	9483	10260
60°	9672	10038	14417	9147	10092
65°	9088	9475	12437	8792	9892
70°	8393	8755	10578	8201	9312
75°	7594	7848	9062	7619	8509
80°	6267	6868	7172	6639	7172
85°	4965	5570	5261	5644	5718

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 24484 cd/sqm



TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	248.1	4.2
10°-20°	617.1	10.5
20°-30°	730.7	12.4
30°-40°	734.7	12.5
40°-50°	674.1	11.4
50°-60°	556.4	9.4
60°-70°	393.6	6.7
70°-80°	210.1	3.6
80°-90°	54.5	0.9
90°-100°	121.1	2.1
100°-110°	354.6	6.0
110°-120°	346.3	5.9
120°-130°	275.8	4.7
130°-140°	217.6	3.7
140°-150°	162.3	2.8
150°-160°	113.2	1.9
160°-170°	66.5	1.1
170°-180°	21.6	0.4
0°-30°	1595.9	27.1
0°-40°	2330.6	39.5
0°-60°	3561.0	60.4
0°-90°	4219.2	71.5
90°-120°	822.0	13.9
90°-150°	1477.7	25.1
90°-180°	1679.0	28.5
0°-180°	5898.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2624	2624	2624	2624	2624	
5°	3306	3120	2637	2125	1953	315
15°	2438	3096	2523	1391	1214	673
25°	1215	1808	2285	1050	970	573
35°	882	1096	1906	849	798	554
45°	696	785	1409	671	674	539
55°	534	567	891	505	547	478
65°	357	372	488	345	388	355
75°	183	189	218	183	205	192
85°	40	45	43	46	46	45
90°	13	11	1	11	13	10
95°	52	268	15	268	52	85
105°	575	363	52	363	575	573
115°	699	278	93	278	699	682
125°	551	259	129	259	551	499
135°	447	256	151	256	447	347
145°	349	253	172	253	349	222
155°	290	244	196	244	290	135
165°	253	234	214	234	253	72
175°	227	225	223	225	227	22
180°	223	223	223	223	223	



TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2957.5	2954.5	2951.4	2936.2	2921.0	2913.7	2906.4	2884.5	2862.5	2838.2	2813.8
5°	3305.7	3314.3	3322.8	3313.0	3303.3	3273.5	3243.6	3204.1	3164.5	3120.1	3075.6
7.5°	3466.5	3471.3	3476.2	3470.1	3464.0	3456.1	3448.2	3412.9	3377.6	3331.9	3286.3
10°	3299.7	3310.6	3321.6	3345.3	3369.1	3395.8	3422.6	3417.8	3412.9	3399.5	3386.1
12.5°	2933.2	2946.6	2959.9	3007.4	3054.9	3115.8	3176.7	3229.0	3281.4	3317.9	3354.4
15°	2437.6	2474.7	2511.9	2555.1	2598.3	2687.8	2777.3	2887.5	2997.7	3095.7	3193.7
17.5°	2007.8	2021.8	2035.8	2082.1	2128.3	2241.0	2353.6	2480.8	2608.1	2770.6	2933.2
20°	1652.3	1665.0	1677.8	1738.7	1799.6	1887.9	1976.1	2119.2	2262.3	2437.0	2611.7
22.5°	1388.0	1408.1	1428.2	1462.3	1496.4	1581.0	1665.7	1792.9	1920.1	2113.1	2306.1
25°	1215.2	1229.8	1244.4	1265.1	1285.8	1353.3	1420.9	1525.6	1630.3	1807.5	1984.7
27.5°	1097.0	1103.1	1109.2	1129.9	1150.6	1194.5	1238.3	1328.4	1418.5	1568.9	1719.2
30°	1004.5	1008.8	1013.0	1031.3	1049.6	1079.4	1109.2	1174.4	1239.5	1372.2	1504.9
32.5°	940.0	943.0	946.1	960.1	974.1	995.4	1016.7	1064.2	1111.7	1221.2	1330.8
35°	881.5	883.4	885.2	895.5	905.9	921.7	937.5	973.5	1009.4	1095.8	1182.3
37.5°	830.4	832.8	835.3	841.4	847.4	861.4	875.4	904.1	932.7	999.0	1065.4
40°	780.5	784.7	789.0	793.3	797.5	809.1	820.7	842.6	864.5	919.3	974.1
42.5°	737.9	742.1	746.4	748.2	750.0	756.7	763.4	783.5	803.6	844.4	885.2
45°	696.5	698.3	700.1	701.9	703.8	709.2	714.7	732.4	750.0	785.3	820.7
47.5°	658.7	658.7	658.7	659.9	661.1	666.0	670.9	683.7	696.5	723.9	751.3
50°	622.2	622.2	622.2	620.4	618.5	621.6	624.6	634.4	644.1	668.5	692.8
52.5°	578.4	578.4	578.4	579.0	579.6	579.6	579.6	588.1	596.6	618.5	640.4
55°	534.5	537.0	539.4	537.6	535.7	537.0	538.2	543.7	549.1	566.8	584.4
57.5°	490.7	491.9	493.1	492.5	491.9	492.5	493.1	498.0	502.9	516.3	529.6
60°	449.3	449.3	449.3	448.1	446.9	448.1	449.3	451.7	454.2	466.3	478.5
62.5°	403.0	403.6	404.2	404.8	405.5	404.2	403.0	406.1	409.1	418.2	427.4
65°	356.8	357.4	358.0	359.8	361.6	360.4	359.2	362.2	365.3	372.0	378.7
67.5°	315.4	314.1	312.9	313.5	314.1	316.0	317.8	318.4	319.0	326.3	333.6
70°	266.7	267.9	269.1	268.5	267.9	268.5	269.1	270.9	272.7	278.2	283.7
72.5°	222.8	223.4	224.0	224.0	224.0	225.3	226.5	228.3	230.1	233.2	236.2
75°	182.6	182.6	182.6	183.9	185.1	185.7	186.3	186.3	186.3	188.7	191.2
77.5°	138.8	141.8	144.9	144.3	143.7	144.9	146.1	147.9	149.8	151.0	152.2
80°	101.1	101.1	101.1	101.7	102.3	104.1	105.9	107.1	108.4	110.8	113.2
82.5°	64.5	65.1	65.7	67.6	69.4	70.6	71.8	73.7	75.5	75.5	75.5
85°	40.2	39.0	37.7	39.0	40.2	41.4	42.6	43.2	43.8	45.1	46.3
87.5°	19.5	19.5	19.5	19.5	19.5	20.1	20.7	20.7	20.7	20.7	20.7
90°	13.1	13.6	13.1	12.7	13.1	12.2	11.7	11.3	10.8	11.3	9.9
92.5°	23.9	24.9	24.4	26.2	27.1	30.3	34.8	44.7	62.8	84.0	93.1
95°	52.4	54.2	57.4	61.5	70.0	86.3	110.2	162.7	217.3	267.9	238.6
97.5°	107.5	112.5	123.4	140.5	170.8	222.3	281.9	373.7	426.1	412.1	307.7
100°	283.3	282.9	300.5	333.5	379.1	443.3	496.1	532.7	516.9	427.9	289.2
102.5°	448.7	461.8	475.8	500.2	533.2	568.0	593.3	585.6	521.4	398.5	262.1
105°	574.7	577.0	591.5	608.6	629.4	641.2	632.6	587.4	493.0	363.3	240.8
107.5°	657.0	661.9	667.8	676.0	678.7	666.5	631.2	560.3	452.3	332.1	225.5
110°	704.0	704.9	705.8	702.2	689.5	657.9	600.9	517.8	414.3	306.3	217.3



TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	713.5	713.0	708.5	695.4	669.6	626.7	561.2	475.8	381.4	289.2	212.8
115°	699.0	696.7	687.7	667.8	633.9	584.7	518.3	439.6	356.0	277.9	212.4
117.5°	667.4	664.2	650.6	628.5	593.3	542.2	481.2	411.6	339.3	270.2	212.8
120°	625.8	623.1	612.2	586.9	551.2	505.6	451.4	390.4	326.7	265.2	214.6
122.5°	586.9	583.3	571.1	549.0	518.3	476.7	427.4	373.7	316.3	262.1	217.8
125°	551.2	548.1	536.8	516.9	488.0	451.8	408.5	359.2	307.7	259.4	220.9
127.5°	520.5	517.8	507.4	490.2	464.0	430.6	390.8	346.1	299.6	258.0	224.6
130°	495.2	491.6	482.1	465.8	441.9	411.2	374.6	333.9	293.2	256.6	228.2
132.5°	470.4	468.1	460.0	443.7	421.6	392.6	359.2	322.6	287.4	256.2	230.9
135°	446.9	443.7	435.6	422.0	399.9	374.1	344.8	312.7	282.4	255.7	233.6
137.5°	422.0	419.3	412.5	398.5	379.5	356.5	330.3	303.2	277.9	254.8	235.4
140°	395.8	396.3	389.0	376.4	359.2	339.8	318.1	295.1	273.8	254.4	237.2
142.5°	371.4	371.9	365.5	354.7	340.7	324.4	306.3	287.4	270.2	253.5	238.6
145°	349.3	348.4	344.8	335.3	324.0	310.9	296.4	281.5	267.0	252.6	239.0
147.5°	330.3	329.8	326.2	319.5	310.4	300.9	288.7	276.5	263.9	251.2	239.0
150°	314.0	314.0	311.3	306.3	299.6	291.0	281.5	271.1	260.7	249.4	239.0
152.5°	300.5	300.5	299.1	294.6	289.6	282.9	274.7	266.1	257.1	247.2	237.7
155°	289.6	289.2	288.3	284.7	280.6	275.2	268.4	261.2	253.5	244.4	236.8
157.5°	279.2	279.2	278.3	275.6	272.0	267.5	262.1	255.7	249.4	242.2	235.4
160°	269.3	269.7	269.7	267.0	263.9	260.7	256.2	251.2	245.3	239.5	234.5
162.5°	260.3	260.7	260.7	258.5	256.6	253.9	249.9	245.8	241.3	236.8	232.7
165°	252.6	252.6	253.0	251.2	249.4	247.2	244.0	241.3	237.7	234.1	230.9
167.5°	244.9	244.9	245.3	244.0	243.1	241.3	239.5	237.2	234.1	231.3	229.1
170°	238.1	238.1	238.6	237.7	237.2	236.3	234.5	233.1	230.9	228.6	227.3
172.5°	231.8	232.2	233.1	232.2	232.2	231.8	230.4	229.5	227.7	226.4	225.9
175°	227.3	227.7	228.2	227.7	227.7	227.7	226.8	226.4	225.5	224.6	224.6
177.5°	224.1	224.1	225.0	224.6	225.0	225.0	224.6	224.1	223.7	223.2	223.7
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2806.5	2799.2	2772.4	2745.7	2715.2	2684.8	2662.3	2639.7	2606.2	2572.8	2545.4
5°	3041.5	3007.4	2950.8	2894.2	2817.5	2740.8	2689.0	2637.3	2567.9	2498.5	2443.1
7.5°	3227.8	3169.4	3090.2	3011.1	2910.6	2810.2	2715.2	2620.2	2514.3	2408.4	2321.9
10°	3346.5	3307.0	3215.6	3124.3	2989.8	2855.2	2722.5	2589.8	2453.4	2317.1	2202.6
12.5°	3358.1	3361.8	3277.7	3193.7	3041.5	2889.3	2728.0	2566.7	2395.0	2223.3	2090.0
15°	3256.4	3319.1	3272.9	3226.6	3073.2	2919.8	2721.3	2522.8	2325.0	2127.1	1973.1
17.5°	3067.7	3202.2	3208.9	3215.6	3062.2	2908.8	2689.0	2469.3	2245.2	2021.2	1859.3
20°	2810.2	3008.7	3076.8	3145.0	3020.2	2895.4	2659.2	2423.0	2172.2	1921.3	1751.5
22.5°	2547.2	2788.3	2913.1	3037.9	2945.3	2852.8	2601.4	2349.9	2085.1	1820.3	1648.0
25°	2247.7	2510.7	2702.4	2894.2	2837.6	2781.0	2533.2	2285.4	2003.5	1721.7	1545.7
27.5°	1986.5	2253.8	2485.1	2716.4	2704.3	2692.1	2446.1	2200.2	1911.6	1623.0	1453.2
30°	1753.9	2002.9	2261.7	2520.4	2550.2	2580.1	2342.6	2105.2	1816.0	1526.9	1363.1
32.5°	1548.2	1765.5	2043.1	2320.7	2379.2	2437.6	2223.3	2009.0	1722.9	1436.8	1279.1
35°	1379.5	1576.8	1854.4	2132.0	2205.0	2278.1	2091.8	1905.5	1626.7	1347.9	1197.5
37.5°	1230.4	1395.4	1666.3	1937.2	2026.7	2116.2	1949.4	1782.5	1521.4	1260.2	1122.0
40°	1106.8	1239.5	1488.5	1737.5	1841.0	1944.5	1806.9	1669.3	1421.5	1173.8	1046.5
42.5°	1003.3	1121.4	1347.3	1573.1	1672.4	1771.6	1655.3	1539.0	1318.6	1098.3	982.0
45°	915.0	1009.4	1214.5	1419.7	1514.1	1608.4	1508.6	1408.7	1214.5	1020.3	912.0
47.5°	832.2	913.2	1088.5	1263.9	1347.9	1431.9	1354.0	1276.0	1111.7	947.3	849.3
50°	757.9	823.1	976.5	1129.9	1203.0	1276.0	1207.2	1138.4	1003.3	868.1	782.9
52.5°	693.4	746.4	874.8	1003.3	1066.0	1128.7	1069.6	1010.6	903.4	796.3	722.0
55°	629.5	674.5	786.0	897.4	940.0	982.6	936.9	891.3	804.8	718.4	655.7
57.5°	569.8	610.0	701.3	792.6	825.5	858.4	817.0	775.6	710.5	645.3	593.0
60°	511.4	544.3	620.4	696.5	716.5	736.6	703.2	669.7	624.0	578.4	531.5
62.5°	457.2	487.0	543.7	600.3	613.7	627.1	601.5	575.9	541.2	506.5	470.0
65°	401.2	423.7	470.0	516.3	524.8	533.3	510.8	488.3	462.1	435.9	409.1
67.5°	349.4	365.3	403.0	440.8	441.4	442.0	423.7	405.5	390.8	376.2	354.9
70°	298.9	314.1	339.1	364.1	364.7	365.3	350.7	336.1	325.1	314.1	298.3
72.5°	247.2	258.1	277.0	295.9	294.7	293.4	284.3	275.2	266.7	258.1	246.6
75°	200.3	209.4	222.2	235.0	231.3	227.7	222.8	217.9	210.6	203.3	196.0
77.5°	157.7	163.2	170.5	177.8	175.3	172.9	168.6	164.4	158.9	153.4	150.4
80°	115.7	118.1	123.0	127.8	126.6	125.4	120.5	115.7	114.5	113.2	109.0
82.5°	78.5	81.6	82.8	84.0	83.4	82.8	79.1	75.5	74.3	73.1	72.4
85°	46.9	47.5	48.1	48.7	46.9	45.1	43.8	42.6	42.6	42.6	42.0
87.5°	21.3	21.9	21.9	21.9	21.3	20.7	19.5	18.3	18.9	19.5	19.5
90°	8.6	7.2	5.9	5.0	4.1	2.7	1.8	0.9	1.8	2.7	4.1
92.5°	69.6	45.6	31.2	23.0	18.5	14.5	9.9	6.8	9.9	14.5	18.5
95°	164.5	97.1	58.7	41.1	29.4	21.7	16.7	15.4	16.7	21.7	29.4
97.5°	183.0	104.8	66.9	47.4	35.7	28.9	24.9	24.4	24.9	28.9	35.7
100°	170.3	103.5	71.8	54.2	43.4	37.1	33.9	33.4	33.9	37.1	43.4
102.5°	159.5	105.3	77.7	61.9	52.4	46.5	43.8	42.9	43.8	46.5	52.4
105°	155.4	108.9	84.5	70.5	61.9	56.5	53.8	52.4	53.8	56.5	61.9
107.5°	154.5	114.8	93.1	80.0	71.8	66.4	63.7	62.4	63.7	66.4	71.8
110°	156.8	122.4	102.1	89.5	81.8	76.8	74.6	73.2	74.6	76.8	81.8





TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	161.3	130.1	111.6	99.4	91.7	86.8	84.5	83.1	84.5	86.8	91.7
115°	166.3	138.7	121.5	109.3	101.7	97.1	94.4	92.6	94.4	97.1	101.7
117.5°	172.6	147.8	130.6	119.3	110.7	106.6	104.4	102.1	104.4	106.6	110.7
120°	179.8	156.3	140.1	128.8	120.2	115.7	113.4	112.1	113.4	115.7	120.2
122.5°	186.6	165.4	149.6	137.4	129.2	124.3	122.0	120.6	122.0	124.3	129.2
125°	193.8	174.0	158.1	145.9	137.4	132.4	129.7	128.8	129.7	132.4	137.4
127.5°	199.7	181.6	166.3	154.1	144.6	139.6	136.5	135.1	136.5	139.6	144.6
130°	205.6	188.4	173.5	161.3	151.8	146.4	142.3	141.0	142.3	146.4	151.8
132.5°	211.0	194.3	179.8	168.1	158.6	151.8	147.3	145.5	147.3	151.8	158.6
135°	215.5	200.2	186.2	174.0	164.5	157.7	152.7	150.9	152.7	157.7	164.5
137.5°	219.1	204.2	190.7	179.4	169.9	162.7	157.7	155.9	157.7	162.7	169.9
140°	221.9	208.3	195.2	183.9	174.9	167.6	163.1	160.9	163.1	167.6	174.9
142.5°	224.6	211.5	198.8	188.4	179.4	173.1	168.1	166.3	168.1	173.1	179.4
145°	226.4	214.2	202.4	192.0	184.4	177.6	173.5	172.2	173.5	177.6	184.4
147.5°	227.7	216.4	205.6	196.6	188.9	183.0	178.9	178.0	178.9	183.0	188.9
150°	228.2	218.7	208.3	200.2	193.8	188.0	184.4	183.9	184.4	188.0	193.8
152.5°	229.1	220.0	211.5	203.8	198.4	193.4	189.8	189.8	189.8	193.4	198.4
155°	229.1	221.9	214.2	207.8	202.9	198.4	195.6	195.6	195.6	198.4	202.9
157.5°	229.5	222.8	216.4	211.5	206.9	202.9	200.6	200.2	200.6	202.9	206.9
160°	229.5	224.1	218.7	214.2	211.0	207.4	205.6	205.6	205.6	207.4	211.0
162.5°	229.1	224.6	220.0	216.4	213.7	211.0	209.7	209.7	209.7	211.0	213.7
165°	228.2	225.0	221.4	218.2	216.4	214.2	213.3	213.7	213.3	214.2	216.4
167.5°	227.7	225.0	222.3	220.0	218.7	216.9	216.4	216.9	216.4	216.9	218.7
170°	226.4	224.6	222.3	221.4	220.5	219.1	218.7	219.6	218.7	219.1	220.5
172.5°	225.9	224.6	222.8	222.3	221.9	220.9	220.9	221.4	220.9	220.9	221.9
175°	225.0	224.1	223.2	222.8	222.8	221.9	222.3	222.8	222.3	221.9	222.8
177.5°	224.6	223.7	223.2	223.2	223.2	222.8	223.2	223.7	223.2	222.8	223.2
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2518.0	2494.2	2470.5	2452.2	2434.0	2402.9	2371.9	2364.6	2357.2	2346.9	2336.5
5°	2387.7	2329.2	2270.8	2218.4	2166.1	2125.3	2084.5	2057.7	2030.9	2011.5	1992.0
7.5°	2235.5	2147.8	2060.2	1998.1	1936.0	1876.9	1817.9	1799.0	1780.1	1754.5	1729.0
10°	2088.2	1991.4	1894.6	1813.6	1732.6	1674.8	1617.0	1593.8	1570.7	1538.4	1506.2
12.5°	1956.7	1850.7	1744.8	1663.2	1581.6	1525.6	1469.6	1436.1	1402.7	1384.4	1366.1
15°	1819.1	1705.8	1592.6	1517.1	1441.6	1391.1	1340.6	1311.3	1282.1	1264.5	1246.8
17.5°	1697.3	1585.3	1473.3	1400.8	1328.4	1282.1	1235.8	1210.3	1184.7	1171.3	1157.9
20°	1581.6	1472.1	1362.5	1291.9	1221.2	1183.5	1145.7	1129.3	1112.9	1101.9	1091.0
22.5°	1475.7	1368.0	1260.2	1199.9	1139.7	1109.2	1078.8	1067.2	1055.6	1046.5	1037.4
25°	1369.8	1273.6	1177.4	1126.3	1075.1	1050.2	1025.2	1013.6	1002.1	992.9	983.8
27.5°	1283.3	1191.4	1099.5	1055.6	1011.8	992.3	972.9	963.7	954.6	946.1	937.5
30°	1199.3	1117.1	1034.9	997.2	959.5	941.8	924.1	915.0	905.9	898.0	890.1
32.5°	1121.4	1050.8	980.2	945.5	910.8	896.1	881.5	870.6	859.6	853.5	847.4
35°	1047.1	983.8	920.5	891.9	863.3	848.7	834.0	824.9	815.8	810.9	806.0
37.5°	983.8	927.2	870.6	843.2	815.8	801.8	787.8	779.9	771.9	770.1	768.3
40°	919.3	870.6	821.9	795.1	768.3	756.1	743.9	739.1	734.2	733.0	731.8
42.5°	865.7	818.2	770.7	746.4	722.0	711.7	701.3	698.9	696.5	698.3	700.1
45°	803.6	764.0	724.5	701.9	679.4	670.9	662.4	660.5	658.7	662.4	666.0
47.5°	751.3	714.7	678.2	656.9	635.6	629.5	623.4	622.8	622.2	627.1	631.9
50°	697.7	662.4	627.1	610.0	593.0	587.5	582.0	583.8	585.7	593.6	601.5
52.5°	647.8	614.9	582.0	566.2	550.3	546.7	543.0	547.3	551.6	560.1	568.6
55°	593.0	563.1	533.3	521.1	509.0	505.3	501.6	510.2	518.7	526.6	534.5
57.5°	540.6	514.4	488.3	477.3	466.3	465.7	465.1	473.0	480.9	489.5	498.0
60°	484.6	462.7	440.8	432.2	423.7	424.9	426.2	435.3	444.4	451.1	457.8
62.5°	433.5	415.2	396.9	389.0	381.1	384.1	387.2	396.3	405.5	413.4	421.3
65°	382.3	367.1	351.9	346.4	340.9	345.2	349.4	357.4	365.3	370.8	376.2
67.5°	333.6	320.8	308.0	303.8	299.5	303.8	308.0	316.0	323.9	329.4	334.8
70°	282.5	272.1	261.8	258.7	255.7	260.6	265.4	272.1	278.8	284.3	289.8
72.5°	235.0	227.1	219.2	218.6	217.9	222.2	226.5	233.2	239.9	243.5	247.2
75°	188.7	184.5	180.2	179.6	179.0	183.2	187.5	191.2	194.8	197.9	200.9
77.5°	147.3	143.7	140.0	140.6	141.2	144.3	147.3	151.0	154.6	156.5	158.3
80°	104.7	103.5	102.3	103.5	104.7	107.1	109.6	112.0	114.5	115.7	116.9
82.5°	71.8	70.6	69.4	71.2	73.1	74.9	76.7	78.5	80.4	81.0	81.6
85°	41.4	43.2	45.1	45.1	45.1	45.7	46.3	46.9	47.5	46.9	46.3
87.5°	19.5	20.1	20.7	20.7	20.7	21.3	21.9	21.9	21.9	21.3	20.7
90°	5.0	5.9	7.2	8.6	9.9	11.3	10.8	11.3	11.7	12.2	13.1
92.5°	23.0	31.2	45.6	69.6	93.1	84.0	62.8	44.7	34.8	30.3	27.1
95°	41.1	58.7	97.1	164.5	238.6	267.9	217.3	162.7	110.2	86.3	70.0
97.5°	47.4	66.9	104.8	183.0	307.7	412.1	426.1	373.7	281.9	222.3	170.8
100°	54.2	71.8	103.5	170.3	289.2	427.9	516.9	532.7	496.1	443.3	379.1
102.5°	61.9	77.7	105.3	159.5	262.1	398.5	521.4	585.6	593.3	568.0	533.2
105°	70.5	84.5	108.9	155.4	240.8	363.3	493.0	587.4	632.6	641.2	629.4
107.5°	80.0	93.1	114.8	154.5	225.5	332.1	452.3	560.3	631.2	666.5	678.7
110°	89.5	102.1	122.4	156.8	217.3	306.3	414.3	517.8	600.9	657.9	689.5



TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	99.4	111.6	130.1	161.3	212.8	289.2	381.4	475.8	561.2	626.7	669.6
115°	109.3	121.5	138.7	166.3	212.4	277.9	356.0	439.6	518.3	584.7	633.9
117.5°	119.3	130.6	147.8	172.6	212.8	270.2	339.3	411.6	481.2	542.2	593.3
120°	128.8	140.1	156.3	179.8	214.6	265.2	326.7	390.4	451.4	505.6	551.2
122.5°	137.4	149.6	165.4	186.6	217.8	262.1	316.3	373.7	427.4	476.7	518.3
125°	145.9	158.1	174.0	193.8	220.9	259.4	307.7	359.2	408.5	451.8	488.0
127.5°	154.1	166.3	181.6	199.7	224.6	258.0	299.6	346.1	390.8	430.6	464.0
130°	161.3	173.5	188.4	205.6	228.2	256.6	293.2	333.9	374.6	411.2	441.9
132.5°	168.1	179.8	194.3	211.0	230.9	256.2	287.4	322.6	359.2	392.6	421.6
135°	174.0	186.2	200.2	215.5	233.6	255.7	282.4	312.7	344.8	374.1	399.9
137.5°	179.4	190.7	204.2	219.1	235.4	254.8	277.9	303.2	330.3	356.5	379.5
140°	183.9	195.2	208.3	221.9	237.2	254.4	273.8	295.1	318.1	339.8	359.2
142.5°	188.4	198.8	211.5	224.6	238.6	253.5	270.2	287.4	306.3	324.4	340.7
145°	192.0	202.4	214.2	226.4	239.0	252.6	267.0	281.5	296.4	310.9	324.0
147.5°	196.6	205.6	216.4	227.7	239.0	251.2	263.9	276.5	288.7	300.9	310.4
150°	200.2	208.3	218.7	228.2	239.0	249.4	260.7	271.1	281.5	291.0	299.6
152.5°	203.8	211.5	220.0	229.1	237.7	247.2	257.1	266.1	274.7	282.9	289.6
155°	207.8	214.2	221.9	229.1	236.8	244.4	253.5	261.2	268.4	275.2	280.6
157.5°	211.5	216.4	222.8	229.5	235.4	242.2	249.4	255.7	262.1	267.5	272.0
160°	214.2	218.7	224.1	229.5	234.5	239.5	245.3	251.2	256.2	260.7	263.9
162.5°	216.4	220.0	224.6	229.1	232.7	236.8	241.3	245.8	249.9	253.9	256.6
165°	218.2	221.4	225.0	228.2	230.9	234.1	237.7	241.3	244.0	247.2	249.4
167.5°	220.0	222.3	225.0	227.7	229.1	231.3	234.1	237.2	239.5	241.3	243.1
170°	221.4	222.3	224.6	226.4	227.3	228.6	230.9	233.1	234.5	236.3	237.2
172.5°	222.3	222.8	224.6	225.9	225.9	226.4	227.7	229.5	230.4	231.8	232.2
175°	222.8	223.2	224.1	225.0	224.6	224.6	225.5	226.4	226.8	227.7	227.7
177.5°	223.2	223.2	223.7	224.6	223.7	223.2	223.7	224.1	224.6	225.0	225.0
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2623.9	2623.9	2623.9	2623.9
2.5°	2332.3	2328.0	2311.0	2293.9
5°	1977.4	1962.7	1957.9	1953.0
7.5°	1727.8	1726.5	1701.0	1675.4
10°	1508.0	1509.8	1486.7	1463.5
12.5°	1350.9	1335.7	1333.9	1332.0
15°	1232.8	1218.8	1216.4	1213.9
17.5°	1149.4	1140.9	1138.4	1136.0
20°	1086.1	1081.2	1077.0	1072.7
22.5°	1031.3	1025.2	1021.6	1017.9
25°	978.3	972.9	971.6	970.4
27.5°	930.8	924.1	924.1	924.1
30°	885.8	881.5	879.7	877.9
32.5°	843.8	840.1	840.1	840.1
35°	804.2	802.4	800.0	797.5
37.5°	768.3	768.3	767.1	765.9
40°	733.6	735.4	735.4	735.4
42.5°	701.9	703.8	703.8	703.8
45°	669.1	672.1	673.3	674.5
47.5°	636.8	641.7	642.9	644.1
50°	605.1	608.8	609.4	610.0
52.5°	572.9	577.1	580.2	583.2
55°	538.8	543.0	544.9	546.7
57.5°	502.3	506.5	507.1	507.7
60°	462.1	466.3	467.6	468.8
62.5°	423.7	426.2	427.4	428.6
65°	379.9	383.5	386.0	388.4
67.5°	337.9	340.9	340.9	340.9
70°	291.0	292.2	294.0	295.9
72.5°	247.8	248.4	248.4	248.4
75°	202.1	203.3	203.9	204.6
77.5°	158.9	159.5	159.5	159.5
80°	116.3	115.7	115.7	115.7
82.5°	79.8	77.9	77.9	77.9
85°	45.7	45.1	45.7	46.3
87.5°	20.7	20.7	20.7	20.7
90°	12.7	13.1	13.6	13.1
92.5°	26.2	24.4	24.9	23.9
95°	61.5	57.4	54.2	52.4
97.5°	140.5	123.4	112.5	107.5
100°	333.5	300.5	282.9	283.3
102.5°	500.2	475.8	461.8	448.7
105°	608.6	591.5	577.0	574.7
107.5°	676.0	667.8	661.9	657.0
110°	702.2	705.8	704.9	704.0



TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	695.4	708.5	713.0	713.5
115°	667.8	687.7	696.7	699.0
117.5°	628.5	650.6	664.2	667.4
120°	586.9	612.2	623.1	625.8
122.5°	549.0	571.1	583.3	586.9
125°	516.9	536.8	548.1	551.2
127.5°	490.2	507.4	517.8	520.5
130°	465.8	482.1	491.6	495.2
132.5°	443.7	460.0	468.1	470.4
135°	422.0	435.6	443.7	446.9
137.5°	398.5	412.5	419.3	422.0
140°	376.4	389.0	396.3	395.8
142.5°	354.7	365.5	371.9	371.4
145°	335.3	344.8	348.4	349.3
147.5°	319.5	326.2	329.8	330.3
150°	306.3	311.3	314.0	314.0
152.5°	294.6	299.1	300.5	300.5
155°	284.7	288.3	289.2	289.6
157.5°	275.6	278.3	279.2	279.2
160°	267.0	269.7	269.7	269.3
162.5°	258.5	260.7	260.7	260.3
165°	251.2	253.0	252.6	252.6
167.5°	244.0	245.3	244.9	244.9
170°	237.7	238.6	238.1	238.1
172.5°	232.2	233.1	232.2	231.8
175°	227.7	228.2	227.7	227.3
177.5°	224.6	225.0	224.1	224.1
180°	223.2	223.2	223.2	223.2



TEST NUMBER: P831275

CATALOG NUMBER: S123DIP-S1165D585U927-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.99	18.03	17.75	18.80	19.73	19.23	20.26	19.98	21.03	21.96
	3H	18.65	19.58	19.42	20.36	21.32	20.66	21.59	21.43	22.37	23.33
	4H	19.24	20.11	20.02	20.90	21.87	21.12	22.00	21.91	22.79	23.76
	6H	19.61	20.42	20.41	21.22	22.21	21.41	22.21	22.21	23.01	24.00
	8H	19.72	20.48	20.53	21.30	22.29	21.47	22.24	22.28	23.06	24.04
	12H	19.77	20.50	20.58	21.31	22.32	21.50	22.23	22.31	23.04	24.05
4H	2H	17.59	18.46	18.38	19.25	20.22	19.41	20.29	20.20	21.08	22.05
	3H	19.43	20.16	20.23	20.98	21.97	21.04	21.77	21.85	22.60	23.59
	4H	20.13	20.80	20.95	21.62	22.64	21.63	22.30	22.45	23.12	24.14
	6H	20.62	21.19	21.45	22.04	23.06	22.05	22.62	22.88	23.47	24.49
	8H	20.76	21.29	21.60	22.14	23.17	22.16	22.70	23.00	23.54	24.57
	12H	20.83	21.31	21.69	22.18	23.22	22.22	22.70	23.07	23.56	24.60
8H	4H	20.41	20.95	21.25	21.79	22.82	21.75	22.29	22.59	23.13	24.16
	6H	21.01	21.45	21.87	22.33	23.37	22.26	22.70	23.13	23.59	24.62
	8H	21.22	21.61	22.09	22.49	23.54	22.44	22.83	23.32	23.71	24.77
	12H	21.35	21.69	22.23	22.56	23.67	22.55	22.90	23.43	23.77	24.87
12H	4H	20.42	20.90	21.28	21.77	22.80	21.74	22.21	22.59	23.08	24.12
	6H	21.06	21.45	21.94	22.33	23.38	22.28	22.67	23.15	23.55	24.60
	8H	21.30	21.65	22.18	22.52	23.62	22.48	22.83	23.36	23.70	24.81