

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331948-930

Luminaire Tested: **S123DIP-S560D1195U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331948-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D1195U930-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5469.4 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	32	31	26
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	30	28	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	10
10	45	33	26	22	41	31	25	20	25	21	17	20	17	14	16	13	12	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6937	6937	6937	6937
5°	8272	6967	6174	6967
10°	10355	6932	5576	6932
15°	12700	6876	5192	6876
20°	15131	6788	4943	6788
25°	16066	6683	4888	6683
30°	13770	6606	4913	6606
35°	9577	6495	4964	6495
40°	7213	6367	4949	6367
45°	5990	6174	4886	6174
50°	5365	5784	4843	5784
55°	5016	5362	4782	5362
60°	4706	4921	4732	4921
65°	4422	4485	4582	4485
70°	4148	3991	4362	3991
75°	3714	3493	4001	3493
80°	3248	2864	3446	2864
85°	2544	2087	2322	2087



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.5	1.2
10°-20°	203.6	3.7
20°-30°	341.7	6.2
30°-40°	386.9	7.1
40°-50°	346.9	6.3
50°-60°	280.0	5.1
60°-70°	195.1	3.6
70°-80°	102.5	1.9
80°-90°	28.7	0.5
90°-100°	260.4	4.8
100°-110°	737.4	13.5
110°-120°	725.4	13.3
120°-130°	578.6	10.6
130°-140°	456.2	8.3
140°-150°	340.5	6.2
150°-160°	237.3	4.3
160°-170°	139.4	2.5
170°-180°	45.4	0.8
0°-30°	608.7	11.1
0°-40°	995.6	18.2
0°-60°	1622.5	29.7
0°-90°	1948.9	35.6
90°-120°	1723.2	31.5
90°-150°	3098.5	56.7
90°-180°	3521.0	64.4
0°-180°	5469.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	644	644	644	644	644	
5°	766	645	571	645	766	79
15°	1140	617	466	617	1140	329
25°	1353	563	412	563	1353	593
35°	729	494	378	494	729	473
45°	394	406	321	406	394	311
55°	267	286	255	286	267	240
65°	174	176	180	176	174	173
75°	89	84	96	84	89	96
85°	21	17	19	17	21	25
90°	28	2	28	2	28	16
95°	110	32	110	32	110	198
105°	1205	110	1205	110	1205	1189
115°	1465	194	1465	194	1465	1424
125°	1156	270	1156	270	1156	1047
135°	937	316	937	316	937	727
145°	732	361	732	361	732	466
155°	607	410	607	410	607	283
165°	530	448	530	448	530	151
175°	476	467	476	467	476	46
180°	468	468	468	468	468	



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	684.0	683.5	682.2	683.2	681.2	678.5	678.2	675.7	668.5	668.0	666.0
5°	765.6	763.1	762.9	762.5	758.1	752.2	740.9	740.0	725.0	717.5	708.5
7.5°	871.5	872.8	868.2	864.2	850.8	842.0	830.0	814.6	796.1	777.5	765.0
10°	947.4	957.7	944.9	936.1	928.1	912.7	895.0	872.8	850.6	824.7	805.0
12.5°	1028.8	1033.9	1031.4	1023.0	1010.5	987.2	955.6	931.2	910.8	867.6	850.2
15°	1139.7	1158.8	1146.6	1118.5	1119.2	1097.0	1055.7	1010.5	986.4	948.6	897.1
17.5°	1257.9	1260.3	1255.1	1231.7	1216.0	1185.6	1147.5	1104.2	1055.4	1009.7	955.0
20°	1320.9	1319.0	1308.1	1295.8	1269.0	1245.3	1203.7	1155.4	1092.9	1047.9	988.3
22.5°	1355.8	1352.7	1347.5	1337.3	1315.0	1289.5	1252.2	1199.3	1139.9	1077.9	1009.0
25°	1352.7	1356.7	1357.4	1354.5	1346.8	1331.5	1302.1	1260.0	1200.6	1121.0	1049.2
27.5°	1230.3	1236.0	1252.7	1267.5	1284.1	1300.9	1298.7	1277.7	1233.9	1165.1	1077.3
30°	1107.9	1095.4	1126.3	1165.3	1191.9	1238.7	1264.9	1266.5	1241.9	1182.8	1097.2
32.5°	938.0	951.8	965.4	1013.4	1071.5	1124.1	1176.2	1218.3	1223.1	1183.8	1109.0
35°	728.8	746.0	770.9	796.0	858.4	912.1	1003.9	1083.9	1147.5	1155.9	1110.0
37.5°	587.3	595.8	611.6	636.6	677.4	741.2	812.2	913.2	1005.5	1074.2	1077.2
40°	513.3	515.8	533.6	552.7	585.8	638.2	702.3	791.6	902.1	998.0	1038.0
42.5°	457.9	463.4	470.9	489.3	515.6	555.1	614.6	688.4	789.7	900.0	978.2
45°	393.5	399.7	404.4	416.5	435.3	461.8	503.4	570.8	647.9	761.9	867.2
47.5°	350.8	351.3	354.8	364.0	376.7	396.7	426.1	469.4	540.2	632.6	740.7
50°	320.4	325.4	326.6	333.8	343.8	358.5	382.9	419.6	477.8	559.0	658.3
52.5°	298.9	300.4	303.9	309.1	317.8	329.2	350.3	379.2	424.8	494.0	585.3
55°	267.3	267.3	270.8	274.8	279.8	290.1	304.1	325.4	360.0	413.8	489.3
57.5°	238.1	239.6	242.1	243.3	247.5	254.4	266.1	282.3	308.1	349.4	409.5
60°	218.6	221.4	221.1	223.6	227.3	232.6	242.6	255.8	278.8	311.9	362.6
62.5°	201.6	201.4	201.4	204.3	208.1	213.1	219.6	231.0	250.6	280.0	323.0
65°	173.6	173.0	175.2	177.1	178.3	182.1	187.0	197.1	210.2	232.0	265.4
67.5°	148.8	146.9	148.1	148.8	150.9	153.8	158.5	164.7	175.1	192.7	217.8
70°	131.8	130.2	129.9	130.5	132.4	134.6	138.0	144.0	153.6	167.7	186.1
72.5°	114.3	113.2	113.2	114.5	115.4	116.8	119.3	124.7	132.4	142.9	160.1
75°	89.3	89.3	89.3	89.6	90.6	91.8	93.7	96.4	102.4	109.9	121.5
77.5°	66.9	66.9	66.5	66.4	67.8	68.4	68.8	71.4	74.8	79.8	88.2
80°	52.4	50.9	51.5	52.4	53.1	53.4	54.3	55.0	57.8	60.6	66.5
82.5°	39.0	37.7	37.7	39.2	39.4	39.6	40.6	41.5	42.6	45.1	48.3
85°	20.6	20.6	21.0	21.0	21.2	21.0	21.9	22.2	22.2	23.7	25.6
87.5°	13.0	12.7	12.7	12.8	12.7	12.6	12.6	12.7	12.8	13.2	12.9
90°	27.5	28.5	27.5	26.5	27.5	25.6	24.6	23.6	22.7	23.6	20.9
92.5°	45.7	47.4	46.4	49.2	51.0	55.8	63.3	79.7	109.9	145.7	160.3
95°	109.9	113.7	120.3	128.8	146.8	180.9	231.1	341.0	455.6	561.7	500.2
97.5°	299.1	307.3	332.9	375.5	445.4	558.7	680.9	850.0	931.3	870.5	637.3
100°	593.9	593.0	629.9	699.0	794.8	929.3	1040.1	1116.8	1083.7	897.1	606.3
102.5°	871.3	893.1	924.0	978.7	1053.1	1138.4	1203.0	1205.5	1091.2	847.8	560.8
105°	1204.9	1209.7	1240.0	1275.9	1319.6	1344.2	1326.2	1231.4	1033.5	761.6	504.9
107.5°	1397.0	1405.7	1415.9	1428.1	1427.3	1393.6	1310.6	1156.7	932.3	685.4	469.3
110°	1475.9	1477.7	1479.6	1472.0	1445.5	1379.2	1259.9	1085.6	868.6	642.2	455.6



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1491.8	1491.3	1484.2	1460.7	1412.2	1326.9	1193.2	1015.0	813.3	613.4	448.1
115°	1465.4	1460.7	1441.7	1400.0	1329.0	1225.7	1086.5	921.7	746.4	582.5	445.2
117.5°	1381.7	1375.2	1347.9	1300.2	1226.1	1121.4	996.3	854.0	706.0	564.4	446.9
120°	1312.0	1306.3	1283.5	1230.4	1155.7	1060.0	946.3	818.4	684.9	556.0	450.0
122.5°	1246.8	1239.6	1214.6	1166.9	1100.3	1011.5	906.1	790.4	667.4	550.7	455.3
125°	1155.7	1149.0	1125.4	1083.7	1023.0	947.2	856.3	753.1	645.1	543.7	463.2
127.5°	1080.6	1074.6	1053.1	1017.6	963.5	894.5	812.5	720.5	625.4	540.3	472.3
130°	1038.2	1030.6	1010.7	976.6	926.4	862.0	785.3	700.0	614.7	538.0	478.3
132.5°	996.5	991.2	973.5	939.5	892.3	831.0	759.5	681.1	605.0	537.3	482.9
135°	936.9	930.2	913.1	884.8	838.3	784.3	722.8	655.5	592.1	536.1	489.8
137.5°	873.8	869.4	855.0	826.2	787.2	740.4	687.3	632.2	580.8	534.0	494.3
140°	829.8	830.7	815.6	789.0	753.1	712.3	666.8	618.6	574.1	533.3	497.3
142.5°	788.9	789.8	776.2	752.7	722.0	686.6	647.2	605.7	567.9	531.8	499.6
145°	732.2	730.3	722.8	702.9	679.1	651.8	621.4	590.1	559.9	529.5	501.1
147.5°	685.6	684.9	677.7	664.2	646.2	626.7	602.3	577.5	551.9	525.9	501.1
150°	658.4	658.4	652.6	642.2	628.0	610.0	590.1	568.3	546.6	522.9	501.1
152.5°	635.6	635.6	632.2	622.6	611.4	596.4	578.8	560.0	540.5	519.1	498.8
155°	607.2	606.3	604.4	596.8	588.2	576.9	562.6	547.5	531.4	512.5	496.4
157.5°	581.2	581.4	579.9	574.2	566.8	557.9	547.0	534.3	521.1	506.6	493.2
160°	564.6	565.5	565.5	559.9	553.2	546.6	537.1	526.7	514.4	502.1	491.6
162.5°	549.4	550.3	550.3	545.4	541.0	535.2	526.5	517.6	507.5	497.5	488.6
165°	529.5	529.5	530.4	526.7	522.9	518.1	511.5	505.8	498.2	490.6	484.0
167.5°	510.5	510.5	511.5	508.8	507.2	503.8	499.9	495.6	489.3	483.9	479.5
170°	499.2	499.2	500.2	498.2	497.3	495.4	491.6	488.8	484.0	479.3	476.5
172.5°	488.6	489.3	491.1	489.2	488.9	487.9	484.8	482.7	478.7	475.5	474.2
175°	476.5	477.4	478.3	477.4	477.4	477.4	475.5	474.6	472.7	470.8	470.8
177.5°	469.4	469.4	471.0	470.2	471.0	471.0	470.2	469.4	468.7	468.0	468.7
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	664.5	662.5	660.5	657.0	654.0	649.7	648.5	647.0	642.5	638.5	635.5
5°	705.1	697.6	686.6	676.6	668.5	657.6	651.3	644.8	635.4	627.0	620.1
7.5°	747.5	732.8	715.8	697.5	680.4	663.8	650.5	638.7	625.6	613.1	603.5
10°	781.3	760.0	736.3	710.7	688.8	667.6	649.8	634.2	617.3	602.7	590.4
12.5°	819.7	788.2	755.5	724.4	698.5	669.1	647.6	627.7	608.6	590.9	577.2
15°	865.3	825.3	786.6	743.8	704.4	667.6	642.0	617.0	594.8	576.7	559.2
17.5°	906.7	861.4	810.4	758.4	710.9	667.2	631.4	603.2	575.4	553.3	535.8
20°	930.2	878.6	820.9	766.9	714.4	665.7	626.4	592.6	562.7	539.2	519.6
22.5°	950.5	890.1	830.4	772.7	714.2	661.7	617.2	582.4	549.9	527.0	506.1
25°	971.4	899.3	839.4	771.6	706.3	652.0	602.0	562.7	530.2	503.4	481.8
27.5°	989.4	898.7	827.5	754.6	694.0	639.5	586.2	544.0	509.5	480.3	458.4
30°	1001.4	899.9	815.3	743.1	682.0	625.7	573.9	531.5	495.2	465.5	445.0
32.5°	1008.9	899.2	804.0	727.2	663.0	613.3	560.7	516.7	479.5	450.4	430.5
35°	1013.3	893.6	784.7	694.1	632.3	583.9	539.9	494.3	455.3	428.1	405.6
37.5°	1004.5	882.2	762.2	662.3	594.6	547.0	509.9	471.1	433.7	403.8	384.4
40°	990.8	874.7	744.7	639.8	568.6	522.7	491.2	453.1	416.2	387.8	369.7
42.5°	964.6	859.4	725.5	614.8	541.6	495.7	466.7	434.9	400.0	373.3	355.2
45°	900.6	826.2	696.7	577.4	501.8	454.4	428.8	405.6	374.1	348.1	332.6
47.5°	811.7	776.3	654.9	537.9	460.2	414.6	387.9	369.3	346.3	325.4	310.4
50°	750.1	735.4	626.7	510.9	432.4	387.8	362.2	345.4	328.8	307.9	294.2
52.5°	678.8	687.9	593.7	482.9	404.2	360.4	336.2	322.9	307.9	290.7	278.7
55°	578.6	611.4	536.8	435.9	362.2	320.4	297.6	285.7	277.0	264.2	253.9
57.5°	484.8	526.4	475.2	387.5	320.9	284.9	263.0	250.1	244.4	237.7	229.7
60°	429.0	470.3	431.2	355.1	293.2	258.9	239.5	228.6	223.0	218.3	211.4
62.5°	379.4	421.0	388.2	322.0	266.0	234.2	217.3	206.6	202.2	199.7	193.9
65°	311.0	346.9	325.1	270.8	227.0	198.9	183.6	176.1	172.0	171.1	167.4
67.5°	253.2	280.5	264.6	224.5	190.1	165.8	152.9	146.5	143.4	143.1	140.2
70°	215.2	240.8	228.6	192.3	162.7	143.7	132.4	126.8	124.9	124.6	123.0
72.5°	185.6	203.5	193.9	163.6	140.7	123.4	115.1	109.3	107.1	107.6	106.6
75°	137.4	150.8	145.2	124.3	105.8	94.6	87.7	84.0	82.1	83.1	81.8
77.5°	98.9	107.4	102.3	87.8	76.5	68.3	63.3	61.0	59.3	59.2	58.6
80°	74.6	79.7	76.8	68.1	58.7	51.9	47.8	46.2	45.2	45.0	44.7
82.5°	53.2	57.4	54.1	48.1	41.7	37.6	35.3	33.3	32.5	32.7	32.4
85°	26.8	28.5	27.1	23.4	21.0	19.1	17.8	16.9	16.2	16.6	15.9
87.5°	12.9	12.6	11.2	9.9	9.0	7.7	7.3	6.4	6.3	6.6	6.9
90°	18.0	15.2	12.3	10.4	8.6	5.7	3.8	1.9	3.8	5.7	8.6
92.5°	120.3	79.6	54.8	40.8	32.8	25.4	17.4	11.7	17.4	25.4	32.8
95°	344.8	203.7	123.1	86.2	61.6	45.5	35.1	32.2	35.1	45.5	61.6
97.5°	378.3	219.2	142.3	102.3	78.0	64.0	55.8	55.0	55.8	64.0	78.0
100°	357.1	217.0	150.6	113.7	90.9	77.7	71.0	70.1	71.0	77.7	90.9
102.5°	338.9	220.0	160.5	126.5	106.1	93.6	87.7	86.0	87.7	93.6	106.1
105°	325.9	228.3	177.2	147.7	129.8	118.4	112.8	109.9	112.8	118.4	129.8
107.5°	324.9	243.9	198.9	171.6	154.7	143.6	138.1	135.3	138.1	143.6	154.7
110°	328.7	256.7	214.1	187.5	171.5	161.0	156.3	153.4	156.3	161.0	171.5





TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	336.3	269.6	230.0	204.2	188.1	177.7	173.0	170.2	173.0	177.7	188.1
115°	348.6	290.8	254.8	229.3	213.1	203.7	198.0	194.2	198.0	203.7	213.1
117.5°	364.8	313.3	277.8	254.0	236.0	227.3	222.6	218.3	222.6	227.3	236.0
120°	377.0	327.8	293.7	269.9	252.0	242.5	237.7	234.9	237.7	242.5	252.0
122.5°	388.4	342.9	309.6	284.4	267.1	256.9	252.2	249.3	252.2	256.9	267.1
125°	406.3	364.7	331.5	306.0	288.0	277.5	271.9	269.9	271.9	277.5	288.0
127.5°	421.2	383.6	351.6	326.0	306.1	295.5	288.5	285.7	288.5	295.5	306.1
130°	431.0	395.0	363.7	338.2	318.3	306.9	298.4	295.5	298.4	306.9	318.3
132.5°	440.1	404.9	374.4	349.5	329.6	316.0	306.7	303.1	306.7	316.0	329.6
135°	451.8	419.6	390.3	364.7	344.8	330.6	320.2	316.4	320.2	330.6	344.8
137.5°	460.6	429.8	401.6	378.0	358.2	343.1	332.9	328.9	332.9	343.1	358.2
140°	465.1	436.7	409.2	385.6	366.6	351.4	341.9	337.2	341.9	351.4	366.6
142.5°	469.6	442.0	415.3	393.1	374.1	360.5	350.3	346.3	350.3	360.5	374.1
145°	474.6	449.0	424.4	402.6	386.5	372.3	363.7	360.9	363.7	372.3	386.5
147.5°	477.6	454.7	432.1	413.6	398.0	385.7	377.4	375.7	377.4	385.7	398.0
150°	478.3	458.4	436.7	419.6	406.3	394.0	386.5	385.6	386.5	394.0	406.3
152.5°	479.9	460.7	442.0	425.7	413.9	403.2	395.6	395.4	395.6	403.2	413.9
155°	480.3	465.1	449.0	435.7	425.3	415.9	410.2	410.2	410.2	415.9	425.3
157.5°	481.2	467.6	454.7	444.4	435.5	427.2	422.7	421.9	422.7	427.2	435.5
160°	481.2	469.9	458.4	449.0	442.4	434.8	431.0	431.0	431.0	434.8	442.4
162.5°	480.5	470.6	460.7	452.8	446.9	440.8	437.8	437.8	437.8	440.8	446.9
165°	478.3	471.7	464.1	457.5	453.7	449.0	447.1	448.1	447.1	449.0	453.7
167.5°	476.9	471.6	466.0	461.9	459.3	455.6	454.7	455.8	454.7	455.6	459.3
170°	474.6	470.8	466.0	464.1	462.3	459.4	458.4	460.4	458.4	459.4	462.3
172.5°	473.9	470.8	466.8	465.7	464.6	462.4	462.3	463.4	462.3	462.4	464.6
175°	471.7	469.9	468.0	467.0	467.0	465.1	466.0	467.0	466.0	465.1	467.0
177.5°	470.2	468.7	468.0	468.0	468.0	467.2	468.0	468.7	468.0	467.2	468.0
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	633.7	632.0	629.5	625.7	622.7	618.0	618.0	618.7	618.7	618.5	618.0
5°	614.5	609.8	604.2	597.7	590.8	583.9	582.7	580.2	578.3	577.1	575.5
7.5°	594.2	586.0	577.7	568.6	560.2	553.3	548.5	544.5	541.8	539.2	537.1
10°	580.5	570.1	560.5	550.8	540.2	531.7	526.4	522.7	519.9	517.4	516.2
12.5°	564.3	552.4	541.8	532.6	521.0	512.3	507.2	505.5	502.1	496.9	494.2
15°	540.5	529.6	516.8	502.7	497.1	486.5	480.5	477.8	475.9	471.8	470.6
17.5°	520.2	505.9	491.5	481.0	470.6	462.0	458.7	455.2	452.7	449.4	448.4
20°	504.0	491.2	478.1	466.8	455.9	446.5	443.7	441.2	438.7	437.2	435.9
22.5°	487.5	474.7	463.8	453.3	441.6	435.5	432.4	429.7	428.0	426.9	425.7
25°	464.3	453.1	440.9	431.5	422.2	418.1	416.2	414.7	413.4	411.9	411.6
27.5°	443.6	431.4	421.5	412.7	406.0	402.6	400.8	400.1	400.3	400.9	401.2
30°	428.1	416.9	408.7	401.2	395.0	391.9	391.6	391.6	392.8	393.1	393.8
32.5°	413.8	404.6	396.5	389.2	384.5	382.4	383.6	383.6	384.6	385.4	386.5
35°	393.1	385.0	378.8	372.5	368.4	369.4	370.0	370.6	372.2	374.1	375.4
37.5°	373.3	366.3	359.8	354.9	353.0	354.7	356.2	357.5	359.4	360.8	362.0
40°	359.1	353.8	347.6	343.2	343.8	344.7	346.0	347.6	349.1	350.0	351.3
42.5°	345.8	340.3	335.6	331.9	332.8	334.0	334.8	335.6	337.4	339.1	339.8
45°	325.7	321.3	316.9	314.8	315.4	316.0	316.7	317.6	319.1	320.4	320.7
47.5°	303.0	299.9	297.0	294.9	295.9	295.6	296.4	298.5	299.0	299.7	301.4
50°	288.5	285.7	282.3	281.7	281.7	281.7	281.9	284.5	284.5	285.7	287.0
52.5°	272.6	270.8	268.6	267.4	266.9	266.9	268.2	269.5	269.9	271.7	273.0
55°	248.8	247.0	245.2	244.2	243.5	244.2	246.7	247.3	248.8	249.8	250.7
57.5°	224.2	222.7	221.3	220.8	220.6	221.4	222.8	224.7	225.1	228.0	229.3
60°	208.0	205.8	204.6	204.6	203.9	206.7	206.1	209.2	209.9	211.7	213.9
62.5°	191.2	188.3	187.8	187.8	188.7	189.5	190.4	191.8	193.4	195.8	197.4
65°	164.3	162.7	164.9	164.5	164.0	165.8	165.8	167.4	169.3	171.5	174.9
67.5°	138.7	137.9	138.1	138.1	139.0	140.1	141.0	142.4	144.6	146.9	149.1
70°	121.5	122.4	120.8	122.1	123.0	123.4	123.9	125.8	128.3	129.9	132.4
72.5°	104.8	104.7	104.8	105.3	106.3	106.9	107.5	109.6	112.3	113.7	115.7
75°	80.6	80.2	81.2	81.2	82.8	83.4	84.0	85.0	87.4	89.3	90.9
77.5°	58.9	59.2	59.0	60.1	59.7	59.8	61.7	62.6	62.9	66.6	67.4
80°	44.4	45.0	45.2	45.6	45.9	45.2	47.5	48.4	48.4	50.5	52.2
82.5°	31.9	32.2	33.0	33.3	33.4	34.0	34.2	34.9	35.6	36.6	38.6
85°	15.9	16.9	17.2	16.9	17.2	16.6	17.4	17.8	18.1	18.1	18.1
87.5°	7.1	7.7	8.0	8.8	9.1	9.9	9.8	9.5	9.7	10.6	10.0
90°	10.4	12.3	15.2	18.0	20.9	23.6	22.7	23.6	24.6	25.6	27.5
92.5°	40.8	54.8	79.6	120.3	160.3	145.7	109.9	79.7	63.3	55.8	51.0
95°	86.2	123.1	203.7	344.8	500.2	561.7	455.6	341.0	231.1	180.9	146.8
97.5°	102.3	142.3	219.2	378.3	637.3	870.5	931.3	850.0	680.9	558.7	445.4
100°	113.7	150.6	217.0	357.1	606.3	897.1	1083.7	1116.8	1040.1	929.3	794.8
102.5°	126.5	160.5	220.0	338.9	560.8	847.8	1091.2	1205.5	1203.0	1138.4	1053.1
105°	147.7	177.2	228.3	325.9	504.9	761.6	1033.5	1231.4	1326.2	1344.2	1319.6
107.5°	171.6	198.9	243.9	324.9	469.3	685.4	932.3	1156.7	1310.6	1393.6	1427.3
110°	187.5	214.1	256.7	328.7	455.6	642.2	868.6	1085.6	1259.9	1379.2	1445.5



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.2	230.0	269.6	336.3	448.1	613.4	813.3	1015.0	1193.2	1326.9	1412.2
115°	229.3	254.8	290.8	348.6	445.2	582.5	746.4	921.7	1086.5	1225.7	1329.0
117.5°	254.0	277.8	313.3	364.8	446.9	564.4	706.0	854.0	996.3	1121.4	1226.1
120°	269.9	293.7	327.8	377.0	450.0	556.0	684.9	818.4	946.3	1060.0	1155.7
122.5°	284.4	309.6	342.9	388.4	455.3	550.7	667.4	790.4	906.1	1011.5	1100.3
125°	306.0	331.5	364.7	406.3	463.2	543.7	645.1	753.1	856.3	947.2	1023.0
127.5°	326.0	351.6	383.6	421.2	472.3	540.3	625.4	720.5	812.5	894.5	963.5
130°	338.2	363.7	395.0	431.0	478.3	538.0	614.7	700.0	785.3	862.0	926.4
132.5°	349.5	374.4	404.9	440.1	482.9	537.3	605.0	681.1	759.5	831.0	892.3
135°	364.7	390.3	419.6	451.8	489.8	536.1	592.1	655.5	722.8	784.3	838.3
137.5°	378.0	401.6	429.8	460.6	494.3	534.0	580.8	632.2	687.3	740.4	787.2
140°	385.6	409.2	436.7	465.1	497.3	533.3	574.1	618.6	666.8	712.3	753.1
142.5°	393.1	415.3	442.0	469.6	499.6	531.8	567.9	605.7	647.2	686.6	722.0
145°	402.6	424.4	449.0	474.6	501.1	529.5	559.9	590.1	621.4	651.8	679.1
147.5°	413.6	432.1	454.7	477.6	501.1	525.9	551.9	577.5	602.3	626.7	646.2
150°	419.6	436.7	458.4	478.3	501.1	522.9	546.6	568.3	590.1	610.0	628.0
152.5°	425.7	442.0	460.7	479.9	498.8	519.1	540.5	560.0	578.8	596.4	611.4
155°	435.7	449.0	465.1	480.3	496.4	512.5	531.4	547.5	562.6	576.9	588.2
157.5°	444.4	454.7	467.6	481.2	493.2	506.6	521.1	534.3	547.0	557.9	566.8
160°	449.0	458.4	469.9	481.2	491.6	502.1	514.4	526.7	537.1	546.6	553.2
162.5°	452.8	460.7	470.6	480.5	488.6	497.5	507.5	517.6	526.5	535.2	541.0
165°	457.5	464.1	471.7	478.3	484.0	490.6	498.2	505.8	511.5	518.1	522.9
167.5°	461.9	466.0	471.6	476.9	479.5	483.9	489.3	495.6	499.9	503.8	507.2
170°	464.1	466.0	470.8	474.6	476.5	479.3	484.0	488.8	491.6	495.4	497.3
172.5°	465.7	466.8	470.8	473.9	474.2	475.5	478.7	482.7	484.8	487.9	488.9
175°	467.0	468.0	469.9	471.7	470.8	470.8	472.7	474.6	475.5	477.4	477.4
177.5°	468.0	468.0	468.7	470.2	468.7	468.0	468.7	469.4	470.2	471.0	471.0
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	616.3	616.0	617.8	616.5	617.8	616.0	616.3	618.0	618.5	618.7	618.7
5°	573.6	574.5	571.4	571.4	571.4	574.5	573.6	575.5	577.1	578.3	580.2
7.5°	535.7	534.3	534.4	532.7	534.4	534.3	535.7	537.1	539.2	541.8	544.5
10°	512.4	510.5	509.9	510.2	509.9	510.5	512.4	516.2	517.4	519.9	522.7
12.5°	493.2	492.8	488.7	488.8	488.7	492.8	493.2	494.2	496.9	502.1	505.5
15°	470.6	464.6	464.0	465.9	464.0	464.6	470.6	470.6	471.8	475.9	477.8
17.5°	447.9	444.7	445.0	444.0	445.0	444.7	447.9	448.4	449.4	452.7	455.2
20°	435.9	434.1	433.7	431.5	433.7	434.1	435.9	435.9	437.2	438.7	441.2
22.5°	424.9	424.3	424.4	422.1	424.4	424.3	424.9	425.7	426.9	428.0	429.7
25°	411.2	412.8	411.6	411.6	411.6	412.8	411.2	411.6	411.9	413.4	414.7
27.5°	402.0	401.9	401.3	401.3	401.3	401.9	402.0	401.2	400.9	400.3	400.1
30°	395.0	394.7	395.3	395.3	395.3	394.7	395.0	393.8	393.1	392.8	391.6
32.5°	388.0	388.4	388.6	388.8	388.6	388.4	388.0	386.5	385.4	384.6	383.6
35°	377.2	377.5	378.5	377.8	378.5	377.5	377.2	375.4	374.1	372.2	370.6
37.5°	362.6	364.0	363.7	364.2	363.7	364.0	362.6	362.0	360.8	359.4	357.5
40°	351.6	352.5	352.2	352.2	352.2	352.5	351.6	351.3	350.0	349.1	347.6
42.5°	340.4	341.0	340.2	339.7	340.2	341.0	340.4	339.8	339.1	337.4	335.6
45°	322.0	321.3	322.3	321.0	322.3	321.3	322.0	320.7	320.4	319.1	317.6
47.5°	301.3	302.0	302.2	303.1	302.2	302.0	301.3	301.4	299.7	299.0	298.5
50°	287.6	289.4	289.4	289.2	289.4	289.4	287.6	287.0	285.7	284.5	284.5
52.5°	274.1	275.0	276.2	276.1	276.2	275.0	274.1	273.0	271.7	269.9	269.5
55°	253.2	253.9	254.5	254.8	254.5	253.9	253.2	250.7	249.8	248.8	247.3
57.5°	231.6	231.4	232.8	233.3	232.8	231.4	231.6	229.3	228.0	225.1	224.7
60°	216.4	216.4	218.9	219.8	218.9	216.4	216.4	213.9	211.7	209.9	209.2
62.5°	200.2	201.1	203.7	202.4	203.7	201.1	200.2	197.4	195.8	193.4	191.8
65°	176.4	179.0	178.6	179.9	178.6	179.0	176.4	174.9	171.5	169.3	167.4
67.5°	151.6	153.2	155.5	155.6	155.5	153.2	151.6	149.1	146.9	144.6	142.4
70°	134.9	136.5	137.7	138.6	137.7	136.5	134.9	132.4	129.9	128.3	125.8
72.5°	118.6	119.4	122.5	121.2	122.5	119.4	118.6	115.7	113.7	112.3	109.6
75°	93.0	95.2	97.1	96.2	97.1	95.2	93.0	90.9	89.3	87.4	85.0
77.5°	68.8	71.0	71.9	71.1	71.9	71.0	68.8	67.4	66.6	62.9	62.6
80°	54.3	54.1	55.9	55.6	55.9	54.1	54.3	52.2	50.5	48.4	48.4
82.5°	39.9	39.5	40.4	40.6	40.4	39.5	39.9	38.6	36.6	35.6	34.9
85°	19.3	20.3	19.1	18.8	19.1	20.3	19.3	18.1	18.1	18.1	17.8
87.5°	9.8	10.0	9.9	9.5	9.9	10.0	9.8	10.0	10.6	9.7	9.5
90°	26.5	27.5	28.5	27.5	28.5	27.5	26.5	27.5	25.6	24.6	23.6
92.5°	49.2	46.4	47.4	45.7	47.4	46.4	49.2	51.0	55.8	63.3	79.7
95°	128.8	120.3	113.7	109.9	113.7	120.3	128.8	146.8	180.9	231.1	341.0
97.5°	375.5	332.9	307.3	299.1	307.3	332.9	375.5	445.4	558.7	680.9	850.0
100°	699.0	629.9	593.0	593.9	593.0	629.9	699.0	794.8	929.3	1040.1	1116.8
102.5°	978.7	924.0	893.1	871.3	893.1	924.0	978.7	1053.1	1138.4	1203.0	1205.5
105°	1275.9	1240.0	1209.7	1204.9	1209.7	1240.0	1275.9	1319.6	1344.2	1326.2	1231.4
107.5°	1428.1	1415.9	1405.7	1397.0	1405.7	1415.9	1428.1	1427.3	1393.6	1310.6	1156.7
110°	1472.0	1479.6	1477.7	1475.9	1477.7	1479.6	1472.0	1445.5	1379.2	1259.9	1085.6



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1460.7	1484.2	1491.3	1491.8	1491.3	1484.2	1460.7	1412.2	1326.9	1193.2	1015.0
115°	1400.0	1441.7	1460.7	1465.4	1460.7	1441.7	1400.0	1329.0	1225.7	1086.5	921.7
117.5°	1300.2	1347.9	1375.2	1381.7	1375.2	1347.9	1300.2	1226.1	1121.4	996.3	854.0
120°	1230.4	1283.5	1306.3	1312.0	1306.3	1283.5	1230.4	1155.7	1060.0	946.3	818.4
122.5°	1166.9	1214.6	1239.6	1246.8	1239.6	1214.6	1166.9	1100.3	1011.5	906.1	790.4
125°	1083.7	1125.4	1149.0	1155.7	1149.0	1125.4	1083.7	1023.0	947.2	856.3	753.1
127.5°	1017.6	1053.1	1074.6	1080.6	1074.6	1053.1	1017.6	963.5	894.5	812.5	720.5
130°	976.6	1010.7	1030.6	1038.2	1030.6	1010.7	976.6	926.4	862.0	785.3	700.0
132.5°	939.5	973.5	991.2	996.5	991.2	973.5	939.5	892.3	831.0	759.5	681.1
135°	884.8	913.1	930.2	936.9	930.2	913.1	884.8	838.3	784.3	722.8	655.5
137.5°	826.2	855.0	869.4	873.8	869.4	855.0	826.2	787.2	740.4	687.3	632.2
140°	789.0	815.6	830.7	829.8	830.7	815.6	789.0	753.1	712.3	666.8	618.6
142.5°	752.7	776.2	789.8	788.9	789.8	776.2	752.7	722.0	686.6	647.2	605.7
145°	702.9	722.8	730.3	732.2	730.3	722.8	702.9	679.1	651.8	621.4	590.1
147.5°	664.2	677.7	684.9	685.6	684.9	677.7	664.2	646.2	626.7	602.3	577.5
150°	642.2	652.6	658.4	658.4	658.4	652.6	642.2	628.0	610.0	590.1	568.3
152.5°	622.6	632.2	635.6	635.6	635.6	632.2	622.6	611.4	596.4	578.8	560.0
155°	596.8	604.4	606.3	607.2	606.3	604.4	596.8	588.2	576.9	562.6	547.5
157.5°	574.2	579.9	581.4	581.2	581.4	579.9	574.2	566.8	557.9	547.0	534.3
160°	559.9	565.5	565.5	564.6	565.5	565.5	559.9	553.2	546.6	537.1	526.7
162.5°	545.4	550.3	550.3	549.4	550.3	550.3	545.4	541.0	535.2	526.5	517.6
165°	526.7	530.4	529.5	529.5	529.5	530.4	526.7	522.9	518.1	511.5	505.8
167.5°	508.8	511.5	510.5	510.5	510.5	511.5	508.8	507.2	503.8	499.9	495.6
170°	498.2	500.2	499.2	499.2	499.2	500.2	498.2	497.3	495.4	491.6	488.8
172.5°	489.2	491.1	489.3	488.6	489.3	491.1	489.2	488.9	487.9	484.8	482.7
175°	477.4	478.3	477.4	476.5	477.4	478.3	477.4	477.4	477.4	475.5	474.6
177.5°	470.2	471.0	469.4	469.4	469.4	471.0	470.2	471.0	471.0	470.2	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	618.0	618.0	622.7	625.7	629.5	632.0	633.7	635.5	638.5	642.5	647.0
5°	582.7	583.9	590.8	597.7	604.2	609.8	614.5	620.1	627.0	635.4	644.8
7.5°	548.5	553.3	560.2	568.6	577.7	586.0	594.2	603.5	613.1	625.6	638.7
10°	526.4	531.7	540.2	550.8	560.5	570.1	580.5	590.4	602.7	617.3	634.2
12.5°	507.2	512.3	521.0	532.6	541.8	552.4	564.3	577.2	590.9	608.6	627.7
15°	480.5	486.5	497.1	502.7	516.8	529.6	540.5	559.2	576.7	594.8	617.0
17.5°	458.7	462.0	470.6	481.0	491.5	505.9	520.2	535.8	553.3	575.4	603.2
20°	443.7	446.5	455.9	466.8	478.1	491.2	504.0	519.6	539.2	562.7	592.6
22.5°	432.4	435.5	441.6	453.3	463.8	474.7	487.5	506.1	527.0	549.9	582.4
25°	416.2	418.1	422.2	431.5	440.9	453.1	464.3	481.8	503.4	530.2	562.7
27.5°	400.8	402.6	406.0	412.7	421.5	431.4	443.6	458.4	480.3	509.5	544.0
30°	391.6	391.9	395.0	401.2	408.7	416.9	428.1	445.0	465.5	495.2	531.5
32.5°	383.6	382.4	384.5	389.2	396.5	404.6	413.8	430.5	450.4	479.5	516.7
35°	370.0	369.4	368.4	372.5	378.8	385.0	393.1	405.6	428.1	455.3	494.3
37.5°	356.2	354.7	353.0	354.9	359.8	366.3	373.3	384.4	403.8	433.7	471.1
40°	346.0	344.7	343.8	343.2	347.6	353.8	359.1	369.7	387.8	416.2	453.1
42.5°	334.8	334.0	332.8	331.9	335.6	340.3	345.8	355.2	373.3	400.0	434.9
45°	316.7	316.0	315.4	314.8	316.9	321.3	325.7	332.6	348.1	374.1	405.6
47.5°	296.4	295.6	295.9	294.9	297.0	299.9	303.0	310.4	325.4	346.3	369.3
50°	281.9	281.7	281.7	281.7	282.3	285.7	288.5	294.2	307.9	328.8	345.4
52.5°	268.2	266.9	266.9	267.4	268.6	270.8	272.6	278.7	290.7	307.9	322.9
55°	246.7	244.2	243.5	244.2	245.2	247.0	248.8	253.9	264.2	277.0	285.7
57.5°	222.8	221.4	220.6	220.8	221.3	222.7	224.2	229.7	237.7	244.4	250.1
60°	206.1	206.7	203.9	204.6	204.6	205.8	208.0	211.4	218.3	223.0	228.6
62.5°	190.4	189.5	188.7	187.8	187.8	188.3	191.2	193.9	199.7	202.2	206.6
65°	165.8	165.8	164.0	164.5	164.9	162.7	164.3	167.4	171.1	172.0	176.1
67.5°	141.0	140.1	139.0	138.1	138.1	137.9	138.7	140.2	143.1	143.4	146.5
70°	123.9	123.4	123.0	122.1	120.8	122.4	121.5	123.0	124.6	124.9	126.8
72.5°	107.5	106.9	106.3	105.3	104.8	104.7	104.8	106.6	107.6	107.1	109.3
75°	84.0	83.4	82.8	81.2	81.2	80.2	80.6	81.8	83.1	82.1	84.0
77.5°	61.7	59.8	59.7	60.1	59.0	59.2	58.9	58.6	59.2	59.3	61.0
80°	47.5	45.2	45.9	45.6	45.2	45.0	44.4	44.7	45.0	45.2	46.2
82.5°	34.2	34.0	33.4	33.3	33.0	32.2	31.9	32.4	32.7	32.5	33.3
85°	17.4	16.6	17.2	16.9	17.2	16.9	15.9	15.9	16.6	16.2	16.9
87.5°	9.8	9.9	9.1	8.8	8.0	7.7	7.1	6.9	6.6	6.3	6.4
90°	22.7	23.6	20.9	18.0	15.2	12.3	10.4	8.6	5.7	3.8	1.9
92.5°	109.9	145.7	160.3	120.3	79.6	54.8	40.8	32.8	25.4	17.4	11.7
95°	455.6	561.7	500.2	344.8	203.7	123.1	86.2	61.6	45.5	35.1	32.2
97.5°	931.3	870.5	637.3	378.3	219.2	142.3	102.3	78.0	64.0	55.8	55.0
100°	1083.7	897.1	606.3	357.1	217.0	150.6	113.7	90.9	77.7	71.0	70.1
102.5°	1091.2	847.8	560.8	338.9	220.0	160.5	126.5	106.1	93.6	87.7	86.0
105°	1033.5	761.6	504.9	325.9	228.3	177.2	147.7	129.8	118.4	112.8	109.9
107.5°	932.3	685.4	469.3	324.9	243.9	198.9	171.6	154.7	143.6	138.1	135.3
110°	868.6	642.2	455.6	328.7	256.7	214.1	187.5	171.5	161.0	156.3	153.4



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	813.3	613.4	448.1	336.3	269.6	230.0	204.2	188.1	177.7	173.0	170.2
115°	746.4	582.5	445.2	348.6	290.8	254.8	229.3	213.1	203.7	198.0	194.2
117.5°	706.0	564.4	446.9	364.8	313.3	277.8	254.0	236.0	227.3	222.6	218.3
120°	684.9	556.0	450.0	377.0	327.8	293.7	269.9	252.0	242.5	237.7	234.9
122.5°	667.4	550.7	455.3	388.4	342.9	309.6	284.4	267.1	256.9	252.2	249.3
125°	645.1	543.7	463.2	406.3	364.7	331.5	306.0	288.0	277.5	271.9	269.9
127.5°	625.4	540.3	472.3	421.2	383.6	351.6	326.0	306.1	295.5	288.5	285.7
130°	614.7	538.0	478.3	431.0	395.0	363.7	338.2	318.3	306.9	298.4	295.5
132.5°	605.0	537.3	482.9	440.1	404.9	374.4	349.5	329.6	316.0	306.7	303.1
135°	592.1	536.1	489.8	451.8	419.6	390.3	364.7	344.8	330.6	320.2	316.4
137.5°	580.8	534.0	494.3	460.6	429.8	401.6	378.0	358.2	343.1	332.9	328.9
140°	574.1	533.3	497.3	465.1	436.7	409.2	385.6	366.6	351.4	341.9	337.2
142.5°	567.9	531.8	499.6	469.6	442.0	415.3	393.1	374.1	360.5	350.3	346.3
145°	559.9	529.5	501.1	474.6	449.0	424.4	402.6	386.5	372.3	363.7	360.9
147.5°	551.9	525.9	501.1	477.6	454.7	432.1	413.6	398.0	385.7	377.4	375.7
150°	546.6	522.9	501.1	478.3	458.4	436.7	419.6	406.3	394.0	386.5	385.6
152.5°	540.5	519.1	498.8	479.9	460.7	442.0	425.7	413.9	403.2	395.6	395.4
155°	531.4	512.5	496.4	480.3	465.1	449.0	435.7	425.3	415.9	410.2	410.2
157.5°	521.1	506.6	493.2	481.2	467.6	454.7	444.4	435.5	427.2	422.7	421.9
160°	514.4	502.1	491.6	481.2	469.9	458.4	449.0	442.4	434.8	431.0	431.0
162.5°	507.5	497.5	488.6	480.5	470.6	460.7	452.8	446.9	440.8	437.8	437.8
165°	498.2	490.6	484.0	478.3	471.7	464.1	457.5	453.7	449.0	447.1	448.1
167.5°	489.3	483.9	479.5	476.9	471.6	466.0	461.9	459.3	455.6	454.7	455.8
170°	484.0	479.3	476.5	474.6	470.8	466.0	464.1	462.3	459.4	458.4	460.4
172.5°	478.7	475.5	474.2	473.9	470.8	466.8	465.7	464.6	462.4	462.3	463.4
175°	472.7	470.8	470.8	471.7	469.9	468.0	467.0	467.0	465.1	466.0	467.0
177.5°	468.7	468.0	468.7	470.2	468.7	468.0	468.0	468.0	467.2	468.0	468.7
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	648.5	649.7	654.0	657.0	660.5	662.5	664.5	666.0	668.0	668.5	675.7
5°	651.3	657.6	668.5	676.6	686.6	697.6	705.1	708.5	717.5	725.0	740.0
7.5°	650.5	663.8	680.4	697.5	715.8	732.8	747.5	765.0	777.5	796.1	814.6
10°	649.8	667.6	688.8	710.7	736.3	760.0	781.3	805.0	824.7	850.6	872.8
12.5°	647.6	669.1	698.5	724.4	755.5	788.2	819.7	850.2	867.6	910.8	931.2
15°	642.0	667.6	704.4	743.8	786.6	825.3	865.3	897.1	948.6	986.4	1010.5
17.5°	631.4	667.2	710.9	758.4	810.4	861.4	906.7	955.0	1009.7	1055.4	1104.2
20°	626.4	665.7	714.4	766.9	820.9	878.6	930.2	988.3	1047.9	1092.9	1155.4
22.5°	617.2	661.7	714.2	772.7	830.4	890.1	950.5	1009.0	1077.9	1139.9	1199.3
25°	602.0	652.0	706.3	771.6	839.4	899.3	971.4	1049.2	1121.0	1200.6	1260.0
27.5°	586.2	639.5	694.0	754.6	827.5	898.7	989.4	1077.3	1165.1	1233.9	1277.7
30°	573.9	625.7	682.0	743.1	815.3	899.9	1001.4	1097.2	1182.8	1241.9	1266.5
32.5°	560.7	613.3	663.0	727.2	804.0	899.2	1008.9	1109.0	1183.8	1223.1	1218.3
35°	539.9	583.9	632.3	694.1	784.7	893.6	1013.3	1110.0	1155.9	1147.5	1083.9
37.5°	509.9	547.0	594.6	662.3	762.2	882.2	1004.5	1077.2	1074.2	1005.5	913.2
40°	491.2	522.7	568.6	639.8	744.7	874.7	990.8	1038.0	998.0	902.1	791.6
42.5°	466.7	495.7	541.6	614.8	725.5	859.4	964.6	978.2	900.0	789.7	688.4
45°	428.8	454.4	501.8	577.4	696.7	826.2	900.6	867.2	761.9	647.9	570.8
47.5°	387.9	414.6	460.2	537.9	654.9	776.3	811.7	740.7	632.6	540.2	469.4
50°	362.2	387.8	432.4	510.9	626.7	735.4	750.1	658.3	559.0	477.8	419.6
52.5°	336.2	360.4	404.2	482.9	593.7	687.9	678.8	585.3	494.0	424.8	379.2
55°	297.6	320.4	362.2	435.9	536.8	611.4	578.6	489.3	413.8	360.0	325.4
57.5°	263.0	284.9	320.9	387.5	475.2	526.4	484.8	409.5	349.4	308.1	282.3
60°	239.5	258.9	293.2	355.1	431.2	470.3	429.0	362.6	311.9	278.8	255.8
62.5°	217.3	234.2	266.0	322.0	388.2	421.0	379.4	323.0	280.0	250.6	231.0
65°	183.6	198.9	227.0	270.8	325.1	346.9	311.0	265.4	232.0	210.2	197.1
67.5°	152.9	165.8	190.1	224.5	264.6	280.5	253.2	217.8	192.7	175.1	164.7
70°	132.4	143.7	162.7	192.3	228.6	240.8	215.2	186.1	167.7	153.6	144.0
72.5°	115.1	123.4	140.7	163.6	193.9	203.5	185.6	160.1	142.9	132.4	124.7
75°	87.7	94.6	105.8	124.3	145.2	150.8	137.4	121.5	109.9	102.4	96.4
77.5°	63.3	68.3	76.5	87.8	102.3	107.4	98.9	88.2	79.8	74.8	71.4
80°	47.8	51.9	58.7	68.1	76.8	79.7	74.6	66.5	60.6	57.8	55.0
82.5°	35.3	37.6	41.7	48.1	54.1	57.4	53.2	48.3	45.1	42.6	41.5
85°	17.8	19.1	21.0	23.4	27.1	28.5	26.8	25.6	23.7	22.2	22.2
87.5°	7.3	7.7	9.0	9.9	11.2	12.6	12.9	12.9	13.2	12.8	12.7
90°	3.8	5.7	8.6	10.4	12.3	15.2	18.0	20.9	23.6	22.7	23.6
92.5°	17.4	25.4	32.8	40.8	54.8	79.6	120.3	160.3	145.7	109.9	79.7
95°	35.1	45.5	61.6	86.2	123.1	203.7	344.8	500.2	561.7	455.6	341.0
97.5°	55.8	64.0	78.0	102.3	142.3	219.2	378.3	637.3	870.5	931.3	850.0
100°	71.0	77.7	90.9	113.7	150.6	217.0	357.1	606.3	897.1	1083.7	1116.8
102.5°	87.7	93.6	106.1	126.5	160.5	220.0	338.9	560.8	847.8	1091.2	1205.5
105°	112.8	118.4	129.8	147.7	177.2	228.3	325.9	504.9	761.6	1033.5	1231.4
107.5°	138.1	143.6	154.7	171.6	198.9	243.9	324.9	469.3	685.4	932.3	1156.7
110°	156.3	161.0	171.5	187.5	214.1	256.7	328.7	455.6	642.2	868.6	1085.6





TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.0	177.7	188.1	204.2	230.0	269.6	336.3	448.1	613.4	813.3	1015.0
115°	198.0	203.7	213.1	229.3	254.8	290.8	348.6	445.2	582.5	746.4	921.7
117.5°	222.6	227.3	236.0	254.0	277.8	313.3	364.8	446.9	564.4	706.0	854.0
120°	237.7	242.5	252.0	269.9	293.7	327.8	377.0	450.0	556.0	684.9	818.4
122.5°	252.2	256.9	267.1	284.4	309.6	342.9	388.4	455.3	550.7	667.4	790.4
125°	271.9	277.5	288.0	306.0	331.5	364.7	406.3	463.2	543.7	645.1	753.1
127.5°	288.5	295.5	306.1	326.0	351.6	383.6	421.2	472.3	540.3	625.4	720.5
130°	298.4	306.9	318.3	338.2	363.7	395.0	431.0	478.3	538.0	614.7	700.0
132.5°	306.7	316.0	329.6	349.5	374.4	404.9	440.1	482.9	537.3	605.0	681.1
135°	320.2	330.6	344.8	364.7	390.3	419.6	451.8	489.8	536.1	592.1	655.5
137.5°	332.9	343.1	358.2	378.0	401.6	429.8	460.6	494.3	534.0	580.8	632.2
140°	341.9	351.4	366.6	385.6	409.2	436.7	465.1	497.3	533.3	574.1	618.6
142.5°	350.3	360.5	374.1	393.1	415.3	442.0	469.6	499.6	531.8	567.9	605.7
145°	363.7	372.3	386.5	402.6	424.4	449.0	474.6	501.1	529.5	559.9	590.1
147.5°	377.4	385.7	398.0	413.6	432.1	454.7	477.6	501.1	525.9	551.9	577.5
150°	386.5	394.0	406.3	419.6	436.7	458.4	478.3	501.1	522.9	546.6	568.3
152.5°	395.6	403.2	413.9	425.7	442.0	460.7	479.9	498.8	519.1	540.5	560.0
155°	410.2	415.9	425.3	435.7	449.0	465.1	480.3	496.4	512.5	531.4	547.5
157.5°	422.7	427.2	435.5	444.4	454.7	467.6	481.2	493.2	506.6	521.1	534.3
160°	431.0	434.8	442.4	449.0	458.4	469.9	481.2	491.6	502.1	514.4	526.7
162.5°	437.8	440.8	446.9	452.8	460.7	470.6	480.5	488.6	497.5	507.5	517.6
165°	447.1	449.0	453.7	457.5	464.1	471.7	478.3	484.0	490.6	498.2	505.8
167.5°	454.7	455.6	459.3	461.9	466.0	471.6	476.9	479.5	483.9	489.3	495.6
170°	458.4	459.4	462.3	464.1	466.0	470.8	474.6	476.5	479.3	484.0	488.8
172.5°	462.3	462.4	464.6	465.7	466.8	470.8	473.9	474.2	475.5	478.7	482.7
175°	466.0	465.1	467.0	467.0	468.0	469.9	471.7	470.8	470.8	472.7	474.6
177.5°	468.0	467.2	468.0	468.0	468.0	468.7	470.2	468.7	468.0	468.7	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	678.2	678.5	681.2	683.2	682.2	683.5	684.0
5°	740.9	752.2	758.1	762.5	762.9	763.1	765.6
7.5°	830.0	842.0	850.8	864.2	868.2	872.8	871.5
10°	895.0	912.7	928.1	936.1	944.9	957.7	947.4
12.5°	955.6	987.2	1010.5	1023.0	1031.4	1033.9	1028.8
15°	1055.7	1097.0	1119.2	1118.5	1146.6	1158.8	1139.7
17.5°	1147.5	1185.6	1216.0	1231.7	1255.1	1260.3	1257.9
20°	1203.7	1245.3	1269.0	1295.8	1308.1	1319.0	1320.9
22.5°	1252.2	1289.5	1315.0	1337.3	1347.5	1352.7	1355.8
25°	1302.1	1331.5	1346.8	1354.5	1357.4	1356.7	1352.7
27.5°	1298.7	1300.9	1284.1	1267.5	1252.7	1236.0	1230.3
30°	1264.9	1238.7	1191.9	1165.3	1126.3	1095.4	1107.9
32.5°	1176.2	1124.1	1071.5	1013.4	965.4	951.8	938.0
35°	1003.9	912.1	858.4	796.0	770.9	746.0	728.8
37.5°	812.2	741.2	677.4	636.6	611.6	595.8	587.3
40°	702.3	638.2	585.8	552.7	533.6	515.8	513.3
42.5°	614.6	555.1	515.6	489.3	470.9	463.4	457.9
45°	503.4	461.8	435.3	416.5	404.4	399.7	393.5
47.5°	426.1	396.7	376.7	364.0	354.8	351.3	350.8
50°	382.9	358.5	343.8	333.8	326.6	325.4	320.4
52.5°	350.3	329.2	317.8	309.1	303.9	300.4	298.9
55°	304.1	290.1	279.8	274.8	270.8	267.3	267.3
57.5°	266.1	254.4	247.5	243.3	242.1	239.6	238.1
60°	242.6	232.6	227.3	223.6	221.1	221.4	218.6
62.5°	219.6	213.1	208.1	204.3	201.4	201.4	201.6
65°	187.0	182.1	178.3	177.1	175.2	173.0	173.6
67.5°	158.5	153.8	150.9	148.8	148.1	146.9	148.8
70°	138.0	134.6	132.4	130.5	129.9	130.2	131.8
72.5°	119.3	116.8	115.4	114.5	113.2	113.2	114.3
75°	93.7	91.8	90.6	89.6	89.3	89.3	89.3
77.5°	68.8	68.4	67.8	66.4	66.5	66.9	66.9
80°	54.3	53.4	53.1	52.4	51.5	50.9	52.4
82.5°	40.6	39.6	39.4	39.2	37.7	37.7	39.0
85°	21.9	21.0	21.2	21.0	21.0	20.6	20.6
87.5°	12.6	12.6	12.7	12.8	12.7	12.7	13.0
90°	24.6	25.6	27.5	26.5	27.5	28.5	27.5
92.5°	63.3	55.8	51.0	49.2	46.4	47.4	45.7
95°	231.1	180.9	146.8	128.8	120.3	113.7	109.9
97.5°	680.9	558.7	445.4	375.5	332.9	307.3	299.1
100°	1040.1	929.3	794.8	699.0	629.9	593.0	593.9
102.5°	1203.0	1138.4	1053.1	978.7	924.0	893.1	871.3
105°	1326.2	1344.2	1319.6	1275.9	1240.0	1209.7	1204.9
107.5°	1310.6	1393.6	1427.3	1428.1	1415.9	1405.7	1397.0
110°	1259.9	1379.2	1445.5	1472.0	1479.6	1477.7	1475.9



TEST NUMBER: P331948-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	<i>1193.2</i>	<i>1326.9</i>	<i>1412.2</i>	<i>1460.7</i>	<i>1484.2</i>	<i>1491.3</i>	<i>1491.8</i>
115°	1086.5	1225.7	1329.0	1400.0	1441.7	1460.7	1465.4
117.5°	996.3	1121.4	1226.1	1300.2	1347.9	1375.2	1381.7
120°	946.3	1060.0	1155.7	1230.4	1283.5	1306.3	1312.0
122.5°	906.1	1011.5	1100.3	1166.9	1214.6	1239.6	1246.8
125°	856.3	947.2	1023.0	1083.7	1125.4	1149.0	1155.7
127.5°	812.5	894.5	963.5	1017.6	1053.1	1074.6	1080.6
130°	785.3	862.0	926.4	976.6	1010.7	1030.6	1038.2
132.5°	759.5	831.0	892.3	939.5	973.5	991.2	996.5
135°	722.8	784.3	838.3	884.8	913.1	930.2	936.9
137.5°	687.3	740.4	787.2	826.2	855.0	869.4	873.8
140°	666.8	712.3	753.1	789.0	815.6	830.7	829.8
142.5°	647.2	686.6	722.0	752.7	776.2	789.8	788.9
145°	621.4	651.8	679.1	702.9	722.8	730.3	732.2
147.5°	602.3	626.7	646.2	664.2	677.7	684.9	685.6
150°	590.1	610.0	628.0	642.2	652.6	658.4	658.4
152.5°	578.8	596.4	611.4	622.6	632.2	635.6	635.6
155°	562.6	576.9	588.2	596.8	604.4	606.3	607.2
157.5°	547.0	557.9	566.8	574.2	579.9	581.4	581.2
160°	537.1	546.6	553.2	559.9	565.5	565.5	564.6
162.5°	526.5	535.2	541.0	545.4	550.3	550.3	549.4
165°	511.5	518.1	522.9	526.7	530.4	529.5	529.5
167.5°	499.9	503.8	507.2	508.8	511.5	510.5	510.5
170°	491.6	495.4	497.3	498.2	500.2	499.2	499.2
172.5°	484.8	487.9	488.9	489.2	491.1	489.3	488.6
175°	475.5	477.4	477.4	477.4	478.3	477.4	476.5
177.5°	470.2	471.0	471.0	470.2	471.0	469.4	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0

(END OF REPORT)