

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331954-930

Luminaire Tested: **S123DIP-S560D1195U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331954-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1195U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5414.2 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331954-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331954-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	56	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	29	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	26	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7854	7747	7800
10°	7803	7679	7726
15°	7710	7592	7608
20°	7605	7468	7475
25°	7462	7321	7305
30°	7305	7157	7102
35°	7139	6984	6893
40°	6968	6792	6687
45°	6779	6616	6454
50°	6589	6400	6223
55°	6341	6176	5988
60°	6090	5916	5726
65°	5871	5631	5456
70°	5542	5306	5070
75°	5065	4882	4675
80°	4568	4376	4339
85°	4001	3853	3705



TEST NUMBER: P331954-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	1.3
10°-20°	193.2	3.6
20°-30°	285.4	5.3
30°-40°	333.3	6.2
40°-50°	335.1	6.2
50°-60°	294.4	5.4
60°-70°	219.3	4.1
70°-80°	124.9	2.3
80°-90°	39.5	0.7
90°-100°	260.4	4.8
100°-110°	737.4	13.6
110°-120°	725.4	13.4
120°-130°	578.6	10.7
130°-140°	456.2	8.4
140°-150°	340.5	6.3
150°-160°	237.3	4.4
160°-170°	139.4	2.6
170°-180°	45.4	0.8
0°-30°	547.0	10.1
0°-40°	880.3	16.3
0°-60°	1509.9	27.9
0°-90°	1893.6	35.0
90°-120°	1723.2	31.8
90°-150°	3098.5	57.2
90°-180°	3521.0	65.0
0°-180°	5414.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	727	724	717	723	722	69
15°	692	689	681	686	683	195
25°	628	624	616	617	615	289
35°	543	539	532	528	525	340
45°	445	442	435	427	424	344
55°	338	337	329	322	319	303
65°	230	227	221	216	214	227
75°	122	119	117	114	112	130
85°	32	31	31	30	30	36
90°	2	11	24	27	28	4
95°	32	105	562	164	110	35
105°	110	162	762	1332	1205	117
115°	194	242	582	1277	1465	192
125°	270	319	544	985	1156	239
135°	316	378	536	811	937	244
145°	361	414	530	665	732	226
155°	410	442	512	583	607	189
165°	448	461	491	520	530	126
175°	467	468	471	477	476	44
180°	468	468	468	468	468	



TEST NUMBER: P331954-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	728.8	728.4	728.0	727.5	727.1	726.2	725.0	723.7	722.6	721.4	722.4
5°	726.9	726.3	725.5	724.9	724.1	723.1	721.5	720.0	718.5	717.0	718.4
7.5°	719.8	719.2	718.4	717.8	717.1	715.9	714.4	712.7	711.2	709.6	710.9
10°	713.9	713.1	712.5	711.8	711.1	709.8	708.0	706.2	704.4	702.6	703.8
12.5°	705.9	705.2	704.7	704.1	703.5	702.4	700.7	699.0	697.3	695.6	696.5
15°	691.9	691.5	690.9	690.3	689.7	688.6	686.8	685.0	683.1	681.3	682.5
17.5°	675.9	675.1	674.4	673.7	672.9	671.7	669.9	668.1	666.3	664.5	665.3
20°	663.9	663.1	662.2	661.4	660.6	659.3	657.5	655.7	653.8	652.0	652.6
22.5°	650.4	649.5	648.7	647.9	647.0	645.7	643.9	642.1	640.3	638.5	639.0
25°	628.3	627.5	626.6	625.8	624.9	623.6	621.8	620.0	618.2	616.4	616.5
27.5°	604.7	603.9	603.1	602.3	601.4	600.1	598.1	596.2	594.3	592.3	592.4
30°	587.7	587.0	586.3	585.6	584.9	583.6	581.6	579.7	577.8	575.8	575.8
32.5°	570.7	569.8	568.8	567.9	567.0	565.8	564.4	562.8	561.3	559.9	559.1
35°	543.3	542.5	541.7	540.9	540.1	538.7	536.9	535.1	533.3	531.5	530.7
37.5°	515.4	514.3	513.2	512.2	511.1	509.7	507.8	506.1	504.2	502.4	501.4
40°	495.9	495.0	494.2	493.4	492.5	491.1	489.2	487.3	485.3	483.4	482.2
42.5°	476.4	475.5	474.5	473.5	472.6	471.2	469.2	467.3	465.4	463.4	462.3
45°	445.3	444.7	444.2	443.6	443.0	441.9	440.1	438.3	436.5	434.6	433.0
47.5°	414.4	413.6	412.9	412.1	411.2	409.9	408.3	406.6	404.9	403.2	401.5
50°	393.5	392.7	392.1	391.3	390.7	389.5	387.6	385.8	384.0	382.2	380.7
52.5°	371.5	371.0	370.6	370.1	369.6	368.4	366.5	364.6	362.6	360.8	359.5
55°	337.9	337.7	337.6	337.5	337.3	336.3	334.5	332.7	330.9	329.1	327.6
57.5°	305.9	305.4	304.9	304.5	304.0	303.0	301.6	300.2	298.7	297.3	296.0
60°	282.9	282.7	282.7	282.5	282.3	281.4	279.8	278.1	276.5	274.8	273.5
62.5°	262.4	262.0	261.7	261.4	261.0	260.0	258.3	256.7	254.9	253.3	252.1
65°	230.5	229.8	229.1	228.4	227.7	226.7	225.3	223.9	222.5	221.1	220.0
67.5°	196.6	196.0	195.3	194.8	194.1	193.3	192.2	191.2	190.1	189.1	188.2
70°	176.1	175.3	174.5	173.7	172.8	171.9	171.1	170.3	169.4	168.6	167.6
72.5°	154.7	154.0	153.4	152.8	152.2	151.4	150.5	149.5	148.5	147.7	146.8
75°	121.8	121.2	120.7	120.1	119.6	119.1	118.6	118.2	117.8	117.4	116.8
77.5°	92.7	92.4	92.0	91.8	91.5	91.1	90.6	90.1	89.5	89.0	88.6
80°	73.7	73.3	72.9	72.5	72.0	71.7	71.4	71.1	70.8	70.6	70.4
82.5°	55.2	55.1	55.0	55.0	54.9	54.8	54.8	54.7	54.6	54.6	54.3
85°	32.4	32.2	32.0	31.6	31.4	31.2	31.2	31.2	31.2	31.2	31.0
87.5°	13.4	13.5	13.5	13.7	13.8	13.9	14.3	14.8	15.2	15.7	15.4
90°	1.9	3.8	5.7	8.6	10.4	12.3	15.2	18.0	20.9	23.6	22.7
92.5°	11.7	17.4	25.4	32.8	40.8	54.8	79.6	120.3	160.3	145.7	109.9
95°	32.2	35.1	45.5	61.6	86.2	123.1	203.7	344.8	500.2	561.7	455.6
97.5°	55.0	55.8	64.0	78.0	102.3	142.3	219.2	378.3	637.3	870.5	931.3
100°	70.1	71.0	77.7	90.9	113.7	150.6	217.0	357.1	606.3	897.1	1083.7
102.5°	86.0	87.7	93.6	106.1	126.5	160.5	220.0	338.9	560.8	847.8	1091.2
105°	109.9	112.8	118.4	129.8	147.7	177.2	228.3	325.9	504.9	761.6	1033.5
107.5°	135.3	138.1	143.6	154.7	171.6	198.9	243.9	324.9	469.3	685.4	932.3
110°	153.4	156.3	161.0	171.5	187.5	214.1	256.7	328.7	455.6	642.2	868.6



TEST NUMBER: P331954-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.2	173.0	177.7	188.1	204.2	230.0	269.6	336.3	448.1	613.4	813.3
115°	194.2	198.0	203.7	213.1	229.3	254.8	290.8	348.6	445.2	582.5	746.4
117.5°	218.3	222.6	227.3	236.0	254.0	277.8	313.3	364.8	446.9	564.4	706.0
120°	234.9	237.7	242.5	252.0	269.9	293.7	327.8	377.0	450.0	556.0	684.9
122.5°	249.3	252.2	256.9	267.1	284.4	309.6	342.9	388.4	455.3	550.7	667.4
125°	269.9	271.9	277.5	288.0	306.0	331.5	364.7	406.3	463.2	543.7	645.1
127.5°	285.7	288.5	295.5	306.1	326.0	351.6	383.6	421.2	472.3	540.3	625.4
130°	295.5	298.4	306.9	318.3	338.2	363.7	395.0	431.0	478.3	538.0	614.7
132.5°	303.1	306.7	316.0	329.6	349.5	374.4	404.9	440.1	482.9	537.3	605.0
135°	316.4	320.2	330.6	344.8	364.7	390.3	419.6	451.8	489.8	536.1	592.1
137.5°	328.9	332.9	343.1	358.2	378.0	401.6	429.8	460.6	494.3	534.0	580.8
140°	337.2	341.9	351.4	366.6	385.6	409.2	436.7	465.1	497.3	533.3	574.1
142.5°	346.3	350.3	360.5	374.1	393.1	415.3	442.0	469.6	499.6	531.8	567.9
145°	360.9	363.7	372.3	386.5	402.6	424.4	449.0	474.6	501.1	529.5	559.9
147.5°	375.7	377.4	385.7	398.0	413.6	432.1	454.7	477.6	501.1	525.9	551.9
150°	385.6	386.5	394.0	406.3	419.6	436.7	458.4	478.3	501.1	522.9	546.6
152.5°	395.4	395.6	403.2	413.9	425.7	442.0	460.7	479.9	498.8	519.1	540.5
155°	410.2	410.2	415.9	425.3	435.7	449.0	465.1	480.3	496.4	512.5	531.4
157.5°	421.9	422.7	427.2	435.5	444.4	454.7	467.6	481.2	493.2	506.6	521.1
160°	431.0	431.0	434.8	442.4	449.0	458.4	469.9	481.2	491.6	502.1	514.4
162.5°	437.8	437.8	440.8	446.9	452.8	460.7	470.6	480.5	488.6	497.5	507.5
165°	448.1	447.1	449.0	453.7	457.5	464.1	471.7	478.3	484.0	490.6	498.2
167.5°	455.8	454.7	455.6	459.3	461.9	466.0	471.6	476.9	479.5	483.9	489.3
170°	460.4	458.4	459.4	462.3	464.1	466.0	470.8	474.6	476.5	479.3	484.0
172.5°	463.4	462.3	462.4	464.6	465.7	466.8	470.8	473.9	474.2	475.5	478.7
175°	467.0	466.0	465.1	467.0	467.0	468.0	469.9	471.7	470.8	470.8	472.7
177.5°	468.7	468.0	467.2	468.0	468.0	468.0	468.7	470.2	468.7	468.0	468.7
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P331954-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	723.6	724.6	725.8	726.3	726.2	726.0	725.9	725.9
5°	719.7	721.1	722.5	723.1	722.8	722.5	722.3	721.9
7.5°	712.1	713.3	714.6	715.1	714.9	714.8	714.6	714.4
10°	705.1	706.4	707.6	708.1	707.8	707.5	707.3	706.9
12.5°	697.4	698.4	699.3	699.6	699.4	699.3	699.1	699.0
15°	683.6	684.7	685.8	685.9	685.1	684.3	683.5	682.7
17.5°	666.1	666.8	667.6	667.8	667.6	667.2	666.9	666.6
20°	653.1	653.7	654.2	654.3	653.9	653.5	653.1	652.6
22.5°	639.4	639.8	640.3	640.3	639.8	639.2	638.7	638.1
25°	616.7	616.9	616.9	616.9	616.4	616.0	615.6	615.1
27.5°	592.6	592.6	592.7	592.6	592.0	591.5	590.9	590.4
30°	575.8	575.8	575.8	575.4	574.4	573.4	572.4	571.4
32.5°	558.3	557.5	556.7	556.0	555.5	555.1	554.5	554.0
35°	529.8	529.0	528.2	527.4	526.7	526.0	525.3	524.6
37.5°	500.3	499.4	498.4	497.7	497.3	496.8	496.4	495.9
40°	481.2	480.0	479.0	478.1	477.5	477.0	476.5	475.9
42.5°	461.2	460.1	458.9	458.1	457.5	457.1	456.5	455.9
45°	431.4	429.7	428.0	426.8	426.2	425.4	424.8	424.0
47.5°	399.9	398.3	396.6	395.5	394.9	394.3	393.7	393.1
50°	379.2	377.6	376.1	375.0	374.1	373.2	372.4	371.6
52.5°	358.2	356.9	355.6	354.4	353.6	352.8	352.0	351.1
55°	326.0	324.6	323.0	321.9	321.2	320.5	319.8	319.1
57.5°	294.6	293.2	291.9	290.7	289.9	289.2	288.4	287.6
60°	272.3	271.1	269.8	268.8	268.2	267.4	266.8	266.0
62.5°	250.8	249.6	248.3	247.4	247.0	246.5	246.1	245.6
65°	218.8	217.8	216.6	215.9	215.5	215.1	214.7	214.2
67.5°	187.2	186.2	185.2	184.4	183.8	183.3	182.7	182.1
70°	166.6	165.8	164.8	163.9	163.2	162.5	161.8	161.1
72.5°	145.9	145.0	144.2	143.6	143.2	142.8	142.5	142.1
75°	116.0	115.4	114.6	114.1	113.7	113.2	112.8	112.4
77.5°	88.1	87.6	87.2	86.9	86.9	86.9	86.9	86.9
80°	70.3	70.1	70.0	70.0	70.0	70.0	70.0	70.0
82.5°	54.1	53.8	53.6	53.4	53.3	53.2	53.1	53.0
85°	30.7	30.4	30.1	30.0	30.0	30.0	30.0	30.0
87.5°	15.5	15.6	15.7	16.0	15.8	16.0	16.1	16.0
90°	23.6	24.6	25.6	27.5	26.5	27.5	28.5	27.5
92.5°	79.7	63.3	55.8	51.0	49.2	46.4	47.4	45.7
95°	341.0	231.1	180.9	146.8	128.8	120.3	113.7	109.9
97.5°	850.0	680.9	558.7	445.4	375.5	332.9	307.3	299.1
100°	1116.8	1040.1	929.3	794.8	699.0	629.9	593.0	593.9
102.5°	1205.5	1203.0	1138.4	1053.1	978.7	924.0	893.1	871.3
105°	1231.4	1326.2	1344.2	1319.6	1275.9	1240.0	1209.7	1204.9
107.5°	1156.7	1310.6	1393.6	1427.3	1428.1	1415.9	1405.7	1397.0
110°	1085.6	1259.9	1379.2	1445.5	1472.0	1479.6	1477.7	1475.9



TEST NUMBER: P331954-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1015.0	1193.2	1326.9	1412.2	1460.7	1484.2	1491.3	1491.8
115°	921.7	1086.5	1225.7	1329.0	1400.0	1441.7	1460.7	1465.4
117.5°	854.0	996.3	1121.4	1226.1	1300.2	1347.9	1375.2	1381.7
120°	818.4	946.3	1060.0	1155.7	1230.4	1283.5	1306.3	1312.0
122.5°	790.4	906.1	1011.5	1100.3	1166.9	1214.6	1239.6	1246.8
125°	753.1	856.3	947.2	1023.0	1083.7	1125.4	1149.0	1155.7
127.5°	720.5	812.5	894.5	963.5	1017.6	1053.1	1074.6	1080.6
130°	700.0	785.3	862.0	926.4	976.6	1010.7	1030.6	1038.2
132.5°	681.1	759.5	831.0	892.3	939.5	973.5	991.2	996.5
135°	655.5	722.8	784.3	838.3	884.8	913.1	930.2	936.9
137.5°	632.2	687.3	740.4	787.2	826.2	855.0	869.4	873.8
140°	618.6	666.8	712.3	753.1	789.0	815.6	830.7	829.8
142.5°	605.7	647.2	686.6	722.0	752.7	776.2	789.8	788.9
145°	590.1	621.4	651.8	679.1	702.9	722.8	730.3	732.2
147.5°	577.5	602.3	626.7	646.2	664.2	677.7	684.9	685.6
150°	568.3	590.1	610.0	628.0	642.2	652.6	658.4	658.4
152.5°	560.0	578.8	596.4	611.4	622.6	632.2	635.6	635.6
155°	547.5	562.6	576.9	588.2	596.8	604.4	606.3	607.2
157.5°	534.3	547.0	557.9	566.8	574.2	579.9	581.4	581.2
160°	526.7	537.1	546.6	553.2	559.9	565.5	565.5	564.6
162.5°	517.6	526.5	535.2	541.0	545.4	550.3	550.3	549.4
165°	505.8	511.5	518.1	522.9	526.7	530.4	529.5	529.5
167.5°	495.6	499.9	503.8	507.2	508.8	511.5	510.5	510.5
170°	488.8	491.6	495.4	497.3	498.2	500.2	499.2	499.2
172.5°	482.7	484.8	487.9	488.9	489.2	491.1	489.3	488.6
175°	474.6	475.5	477.4	477.4	477.4	478.3	477.4	476.5
177.5°	469.4	470.2	471.0	471.0	470.2	471.0	469.4	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0

(END OF REPORT)