

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332070-927

Luminaire Tested: **S123DIP-S1165D805U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332070-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5955.2 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332070-927

CATALOG NUMBER: S123DIP-S1165D805U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332070-927

CATALOG NUMBER: S123DIP-S1165D805U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	103	103	103	103	91	91	91		79	79	79		68	68	68	63
1	101	96	92	89	94	90	87	84	80	77	74		70	68	66		60	59	58	53
2	92	84	78	72	86	79	73	69	70	65	62		61	58	55		53	51	48	44
3	84	74	66	60	78	70	63	57	61	56	52		54	50	46		47	44	41	38
4	77	65	57	51	71	62	54	49	55	49	44		48	43	40		42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38		43	38	35		38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33		39	34	30		34	30	27	25
7	60	47	39	33	56	45	37	32	40	34	29		36	31	27		31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26		33	28	24		29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24		30	25	22		27	23	20	18
10	49	36	29	24	46	34	28	23	31	25	21		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15588	15588	15588
5°	15662	15446	15554
10°	15557	15312	15407
15°	15375	15139	15166
20°	15163	14892	14905
25°	14878	14598	14567
30°	14564	14270	14162
35°	14236	13925	13745
40°	13893	13543	13333
45°	13516	13192	12871
50°	13137	12762	12407
55°	12643	12314	11941
60°	12144	11795	11418
65°	11703	11227	10878
70°	11053	10581	10112
75°	10098	9736	9320
80°	9106	8722	8647
85°	7991	7694	7385



TEST NUMBER: P332070-927

CATALOG NUMBER: S123DIP-S1165D805U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.4	2.3
10°-20°	385.2	6.5
20°-30°	569.0	9.6
30°-40°	664.6	11.2
40°-50°	668.2	11.2
50°-60°	587.0	9.9
60°-70°	437.3	7.3
70°-80°	249.1	4.2
80°-90°	73.9	1.2
90°-100°	51.4	0.9
100°-110°	153.7	2.6
110°-120°	261.5	4.4
120°-130°	343.9	5.8
130°-140°	386.6	6.5
140°-150°	380.0	6.4
150°-160°	319.9	5.4
160°-170°	212.9	3.6
170°-180°	74.6	1.3
0°-30°	1090.6	18.3
0°-40°	1755.3	29.5
0°-60°	3010.4	50.6
0°-90°	3770.7	63.3
90°-120°	466.6	7.8
90°-150°	1577.1	26.5
90°-180°	2185.0	36.7
0°-180°	5955.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1448	1448	1448	1448	1448	
5°	1450	1443	1430	1441	1440	137
15°	1380	1374	1358	1368	1361	389
25°	1253	1245	1229	1230	1226	577
35°	1083	1075	1060	1052	1046	677
45°	888	882	867	852	846	685
55°	674	672	656	643	636	603
65°	460	453	441	431	427	453
75°	243	238	234	228	224	260
85°	65	62	62	60	60	71
90°	1	7	15	17	19	6
95°	36	41	46	48	48	41
105°	139	141	146	146	147	149
115°	263	265	264	264	264	260
125°	385	387	386	383	381	343
135°	500	503	503	500	499	385
145°	606	608	609	609	606	379
155°	694	694	695	697	693	319
165°	756	754	754	758	754	213
175°	787	784	784	787	784	75
180°	788	788	788	788	788	



TEST NUMBER: P332070-927

CATALOG NUMBER: S123DIP-S1165D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1453.2	1452.3	1451.4	1450.6	1449.6	1448.0	1445.6	1443.1	1440.7	1438.2	1440.4
5°	1449.5	1448.1	1446.7	1445.3	1443.9	1441.7	1438.7	1435.6	1432.6	1429.5	1432.3
7.5°	1435.3	1433.8	1432.5	1431.1	1429.7	1427.4	1424.3	1421.2	1418.0	1414.8	1417.3
10°	1423.3	1421.9	1420.5	1419.1	1417.8	1415.3	1411.7	1408.1	1404.5	1400.9	1403.4
12.5°	1407.4	1406.2	1405.0	1403.9	1402.7	1400.4	1397.1	1393.7	1390.3	1387.0	1388.8
15°	1379.7	1378.6	1377.5	1376.4	1375.3	1372.9	1369.4	1365.7	1362.2	1358.5	1360.7
17.5°	1347.6	1346.2	1344.7	1343.3	1341.8	1339.3	1335.7	1332.1	1328.5	1324.9	1326.5
20°	1323.7	1322.0	1320.3	1318.7	1317.1	1314.4	1310.8	1307.3	1303.6	1300.1	1301.2
22.5°	1296.8	1295.1	1293.5	1291.8	1290.1	1287.5	1283.9	1280.3	1276.8	1273.1	1274.0
25°	1252.7	1251.0	1249.4	1247.7	1246.1	1243.4	1239.8	1236.3	1232.6	1229.1	1229.3
27.5°	1205.6	1204.0	1202.5	1200.8	1199.2	1196.5	1192.6	1188.7	1184.9	1181.0	1181.2
30°	1171.8	1170.4	1169.0	1167.6	1166.3	1163.6	1159.8	1155.9	1152.0	1148.1	1148.1
32.5°	1137.9	1136.1	1134.2	1132.4	1130.6	1128.1	1125.2	1122.2	1119.2	1116.3	1114.7
35°	1083.4	1081.7	1080.1	1078.4	1076.7	1074.1	1070.5	1066.9	1063.3	1059.7	1058.0
37.5°	1027.5	1025.5	1023.3	1021.3	1019.1	1016.3	1012.6	1009.0	1005.4	1001.6	999.7
40°	988.7	987.1	985.4	983.7	982.1	979.3	975.4	971.5	967.7	963.8	961.6
42.5°	949.8	948.0	946.1	944.2	942.3	939.4	935.6	931.7	927.8	924.0	921.8
45°	887.9	886.8	885.7	884.6	883.4	881.1	877.5	873.9	870.3	866.6	863.4
47.5°	826.3	824.7	823.2	821.5	819.9	817.5	814.0	810.6	807.3	803.9	800.7
50°	784.5	783.2	781.7	780.4	779.0	776.5	772.9	769.3	765.6	762.1	759.1
52.5°	740.7	739.7	738.8	737.8	736.9	734.5	730.7	726.9	723.1	719.2	716.6
55°	673.7	673.4	673.1	672.9	672.6	670.7	667.0	663.5	659.8	656.2	653.2
57.5°	609.9	609.0	608.0	607.1	606.2	604.3	601.3	598.5	595.6	592.7	590.0
60°	564.1	563.8	563.6	563.2	563.0	561.2	557.9	554.5	551.2	547.9	545.4
62.5°	523.2	522.5	521.8	521.1	520.4	518.3	515.0	511.7	508.4	505.1	502.6
65°	459.5	458.1	456.7	455.3	453.9	451.9	449.1	446.3	443.5	440.8	438.6
67.5°	392.0	390.8	389.6	388.3	387.1	385.5	383.3	381.3	379.1	377.1	375.1
70°	351.2	349.5	347.8	346.2	344.5	342.9	341.2	339.5	337.9	336.2	334.3
72.5°	308.3	307.1	305.9	304.7	303.5	301.9	300.0	298.1	296.3	294.4	292.6
75°	242.8	241.7	240.6	239.5	238.4	237.4	236.6	235.8	235.0	234.1	232.7
77.5°	184.8	184.2	183.5	183.0	182.4	181.6	180.5	179.6	178.6	177.6	176.7
80°	146.9	146.1	145.3	144.4	143.6	142.9	142.4	141.8	141.2	140.7	140.5
82.5°	110.1	109.9	109.7	109.6	109.4	109.2	109.2	109.1	108.9	108.8	108.4
85°	64.7	64.2	63.6	63.1	62.5	62.3	62.3	62.3	62.3	62.3	61.7
87.5°	26.1	25.7	25.3	24.9	24.5	24.3	24.5	24.6	24.7	24.9	24.8
90°	0.6	2.0	3.4	4.8	6.1	7.7	9.5	11.2	13.1	14.9	15.4
92.5°	15.0	15.9	16.9	17.8	18.7	19.7	20.8	21.8	22.7	23.8	24.2
95°	36.5	37.5	38.5	39.5	40.4	41.4	42.5	43.6	44.8	45.9	46.4
97.5°	64.9	65.6	66.3	67.0	67.8	68.5	69.3	70.1	70.9	71.7	72.3
100°	84.2	85.1	85.9	86.7	87.5	88.3	89.0	89.7	90.4	91.0	91.5
102.5°	106.5	107.0	107.5	108.1	108.5	109.2	110.1	111.1	111.9	112.9	113.3
105°	139.3	139.7	139.9	140.2	140.5	141.2	142.4	143.7	145.0	146.2	146.2
107.5°	177.5	177.7	177.8	178.0	178.2	178.5	179.0	179.5	180.0	180.5	180.9
110°	201.3	201.5	201.8	202.1	202.4	202.6	203.0	203.2	203.5	203.7	204.3



TEST NUMBER: P332070-927

CATALOG NUMBER: S123DIP-S1165D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	226.1	226.2	226.4	226.6	226.7	226.8	226.9	227.0	227.0	227.0	227.8
115°	263.2	263.6	264.0	264.4	264.9	265.0	264.7	264.4	264.1	263.9	264.0
117.5°	300.6	301.0	301.2	301.4	301.7	301.7	301.3	301.0	300.6	300.2	300.2
120°	323.9	324.7	325.6	326.4	327.3	327.3	326.6	325.9	325.3	324.6	324.4
122.5°	348.2	348.8	349.4	350.0	350.6	350.8	350.4	350.1	349.7	349.4	349.0
125°	385.2	385.6	386.0	386.5	386.9	387.0	386.7	386.4	386.1	385.9	385.3
127.5°	419.5	420.3	421.2	422.1	422.9	423.3	422.9	422.6	422.3	422.0	421.3
130°	442.2	443.3	444.4	445.5	446.6	446.9	446.6	446.2	445.8	445.3	444.7
132.5°	465.0	466.1	467.2	468.3	469.4	469.8	469.5	469.2	468.9	468.6	467.9
135°	499.8	500.7	501.5	502.3	503.1	503.5	503.4	503.2	503.0	503.0	502.4
137.5°	532.0	532.7	533.4	534.1	534.8	535.3	535.7	536.0	536.4	536.7	536.1
140°	554.3	555.0	555.7	556.4	557.1	557.5	557.6	557.8	557.9	558.0	557.9
142.5°	574.6	575.4	576.0	576.7	577.4	577.9	578.1	578.4	578.6	578.8	578.7
145°	606.3	606.7	606.9	607.2	607.4	607.8	608.2	608.6	609.0	609.4	609.3
147.5°	634.1	634.6	635.1	635.6	636.1	636.5	636.9	637.3	637.7	638.1	638.1
150°	653.4	653.7	653.9	654.3	654.5	654.8	655.1	655.4	655.6	655.9	655.9
152.5°	669.3	669.6	670.0	670.4	670.8	671.1	671.3	671.5	671.6	671.8	672.0
155°	694.3	694.3	694.3	694.3	694.3	694.3	694.5	694.7	694.8	694.9	695.5
157.5°	715.6	715.4	715.3	715.1	714.9	714.9	715.0	715.2	715.3	715.3	716.0
160°	729.0	728.7	728.4	728.2	727.9	727.8	727.8	727.8	727.8	727.8	728.4
162.5°	740.8	740.5	740.1	739.7	739.3	739.2	739.3	739.4	739.5	739.7	740.3
165°	756.2	755.8	755.4	755.0	754.6	754.4	754.4	754.4	754.4	754.4	755.2
167.5°	768.5	767.9	767.4	766.8	766.3	766.1	766.2	766.3	766.4	766.5	767.4
170°	775.5	774.9	774.4	773.8	773.2	772.9	772.9	772.9	772.9	772.9	774.0
172.5°	780.9	780.4	779.8	779.3	778.7	778.4	778.4	778.4	778.4	778.4	779.3
175°	786.6	786.0	785.5	785.0	784.4	784.1	784.1	784.1	784.1	784.1	785.0
177.5°	788.9	788.5	788.1	787.6	787.2	787.0	787.0	787.0	787.0	787.0	787.6
180°	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5



TEST NUMBER: P332070-927

CATALOG NUMBER: S123DIP-S1165D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1442.6	1444.9	1447.1	1448.1	1447.9	1447.6	1447.4	1447.2
5°	1435.0	1437.8	1440.6	1441.7	1441.1	1440.6	1440.0	1439.5
7.5°	1419.8	1422.3	1424.8	1425.8	1425.5	1425.2	1424.9	1424.6
10°	1405.9	1408.3	1410.9	1411.8	1411.3	1410.7	1410.2	1409.6
12.5°	1390.6	1392.4	1394.2	1395.0	1394.6	1394.3	1394.0	1393.7
15°	1362.9	1365.2	1367.4	1367.7	1366.0	1364.4	1362.7	1361.0
17.5°	1328.0	1329.6	1331.1	1331.6	1331.0	1330.4	1329.8	1329.2
20°	1302.3	1303.4	1304.5	1304.6	1303.8	1302.9	1302.1	1301.2
22.5°	1274.9	1275.8	1276.7	1276.6	1275.6	1274.5	1273.4	1272.4
25°	1229.6	1229.9	1230.2	1229.9	1229.1	1228.2	1227.4	1226.5
27.5°	1181.5	1181.6	1181.9	1181.5	1180.4	1179.3	1178.3	1177.3
30°	1148.1	1148.1	1148.1	1147.2	1145.2	1143.3	1141.3	1139.4
32.5°	1113.1	1111.6	1110.0	1108.7	1107.7	1106.6	1105.6	1104.5
35°	1056.4	1054.7	1053.0	1051.5	1050.1	1048.8	1047.3	1046.0
37.5°	997.7	995.7	993.7	992.3	991.3	990.5	989.6	988.7
40°	959.4	957.2	955.0	953.3	952.2	951.1	950.0	948.9
42.5°	919.6	917.3	915.1	913.5	912.4	911.2	910.1	909.0
45°	860.1	856.7	853.4	851.0	849.7	848.3	846.9	845.5
47.5°	797.4	794.2	790.8	788.6	787.4	786.2	785.0	783.8
50°	756.0	753.0	749.9	747.6	745.9	744.3	742.6	740.9
52.5°	714.1	711.5	708.8	706.7	705.0	703.4	701.7	700.1
55°	650.1	647.1	644.0	641.8	640.5	639.1	637.7	636.3
57.5°	587.3	584.6	581.9	579.7	578.1	576.6	574.9	573.3
60°	543.0	540.4	538.0	536.0	534.6	533.2	531.9	530.4
62.5°	500.1	497.6	495.1	493.4	492.4	491.5	490.6	489.6
65°	436.4	434.2	432.0	430.5	429.6	428.8	427.9	427.1
67.5°	373.2	371.2	369.3	367.7	366.6	365.4	364.2	363.1
70°	332.3	330.4	328.4	326.8	325.4	324.0	322.7	321.3
72.5°	291.0	289.2	287.5	286.3	285.6	284.9	284.2	283.4
75°	231.3	230.0	228.5	227.4	226.6	225.8	225.0	224.1
77.5°	175.7	174.8	173.8	173.3	173.3	173.3	173.3	173.3
80°	140.1	139.9	139.6	139.5	139.5	139.5	139.5	139.5
82.5°	107.8	107.3	106.9	106.5	106.2	106.1	105.8	105.6
85°	61.2	60.6	60.0	59.8	59.8	59.8	59.8	59.8
87.5°	24.6	24.6	24.5	24.4	24.5	24.6	24.6	24.6
90°	16.0	16.5	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	24.6	25.1	25.5	25.7	25.5	25.3	25.2	25.0
95°	46.9	47.5	48.0	48.3	48.3	48.3	48.3	48.3
97.5°	73.0	73.6	74.2	74.5	74.5	74.5	74.4	74.3
100°	91.9	92.3	92.7	93.1	93.3	93.6	93.9	94.1
102.5°	113.7	114.1	114.5	114.7	114.6	114.5	114.5	114.5
105°	146.2	146.2	146.2	146.3	146.6	146.9	147.1	147.4
107.5°	181.3	181.8	182.3	182.4	182.2	182.0	181.9	181.7
110°	204.9	205.4	206.0	206.1	205.8	205.6	205.3	205.0



TEST NUMBER: P332070-927

CATALOG NUMBER: S123DIP-S1165D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.4	229.0	229.7	230.0	230.0	229.9	229.8	229.8
115°	264.1	264.3	264.4	264.4	264.3	264.1	264.0	263.9
117.5°	300.2	300.2	300.2	299.9	299.6	299.2	298.8	298.4
120°	324.2	324.2	324.0	323.8	323.5	323.2	323.0	322.7
122.5°	348.6	348.2	347.9	347.5	347.1	346.7	346.3	345.9
125°	384.8	384.2	383.7	383.1	382.5	382.0	381.4	380.9
127.5°	420.5	419.7	419.0	418.3	417.6	417.0	416.4	415.7
130°	444.3	443.7	443.1	442.4	441.4	440.5	439.5	438.5
132.5°	467.3	466.6	466.0	465.2	464.5	463.7	463.0	462.3
135°	501.8	501.3	500.7	500.3	500.0	499.8	499.5	499.2
137.5°	535.6	535.0	534.4	533.9	533.4	532.8	532.3	531.8
140°	557.8	557.6	557.5	557.0	556.0	555.0	554.1	553.1
142.5°	578.6	578.5	578.3	577.9	577.1	576.4	575.6	574.9
145°	609.2	609.0	608.9	608.6	608.0	607.4	606.9	606.3
147.5°	638.1	638.1	638.1	637.6	636.8	636.0	635.2	634.4
150°	655.9	655.9	655.9	655.5	654.7	653.9	653.0	652.2
152.5°	672.2	672.4	672.6	672.4	671.7	671.0	670.3	669.6
155°	696.0	696.6	697.1	696.9	695.9	695.0	694.0	693.1
157.5°	716.5	717.1	717.6	717.6	716.8	716.1	715.3	714.5
160°	729.1	729.8	730.5	730.6	730.0	729.4	728.9	728.3
162.5°	741.0	741.7	742.4	742.3	741.4	740.5	739.7	738.8
165°	756.1	756.9	757.7	757.6	756.7	755.7	754.7	753.8
167.5°	768.3	769.1	769.9	769.9	769.1	768.3	767.4	766.5
170°	774.9	775.9	776.8	776.8	775.9	774.9	774.0	772.9
172.5°	780.1	781.0	781.8	781.8	780.8	779.8	778.9	777.9
175°	785.8	786.6	787.4	787.3	786.4	785.4	784.4	783.5
177.5°	788.3	788.9	789.6	789.6	788.8	788.0	787.3	786.5
180°	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5

(END OF REPORT)