

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331916-930

Luminaire Tested: **S123DIP-S560D365U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331916-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D365U930-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3073.6 lumens  
Efficiency: N/A  
Efficacy: 111.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331916-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331916-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7819	7819	7819
5°	7854	7747	7800
10°	7803	7679	7726
15°	7710	7592	7608
20°	7605	7468	7475
25°	7462	7321	7305
30°	7305	7157	7102
35°	7139	6984	6893
40°	6968	6792	6687
45°	6779	6616	6454
50°	6589	6400	6223
55°	6341	6176	5988
60°	6090	5916	5726
65°	5871	5631	5456
70°	5542	5306	5070
75°	5065	4882	4675
80°	4568	4376	4339
85°	4001	3853	3705



TEST NUMBER: P331916-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.4	2.2
10°-20°	193.2	6.3
20°-30°	285.4	9.3
30°-40°	333.3	10.8
40°-50°	335.1	10.9
50°-60°	294.4	9.6
60°-70°	219.3	7.1
70°-80°	124.9	4.1
80°-90°	36.9	1.2
90°-100°	14.1	0.5
100°-110°	67.2	2.2
110°-120°	161.4	5.3
120°-130°	205.5	6.7
130°-140°	219.6	7.1
140°-150°	205.4	6.7
150°-160°	165.6	5.4
160°-170°	106.9	3.5
170°-180°	36.8	1.2
0°-30°	547.0	17.8
0°-40°	880.3	28.6
0°-60°	1509.9	49.1
0°-90°	1891.1	61.5
90°-120°	242.7	7.9
90°-150°	873.2	28.4
90°-180°	1183.0	38.5
0°-180°	3073.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	727	724	717	723	722	69
15°	692	689	681	686	683	195
25°	628	624	616	617	615	289
35°	543	539	532	528	525	340
45°	445	442	435	427	424	344
55°	338	337	329	322	319	303
65°	230	227	221	216	214	227
75°	122	119	117	114	112	130
85°	32	31	31	30	30	36
90°	0	3	7	8	9	3
95°	18	7	9	11	11	22
105°	86	87	63	15	13	91
115°	161	163	165	168	169	159
125°	227	229	230	231	232	203
135°	283	284	286	286	286	217
145°	326	328	329	329	329	204
155°	359	359	359	360	359	165
165°	379	378	378	380	378	107
175°	388	386	387	388	386	37
180°	388	388	388	388	388	



TEST NUMBER: P331916-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	728.8	728.4	728.0	727.5	727.1	726.2	725.0	723.7	722.6	721.4	722.4
5°	726.9	726.3	725.5	724.9	724.1	723.1	721.5	720.0	718.5	717.0	718.4
7.5°	719.8	719.2	718.4	717.8	717.1	715.9	714.4	712.7	711.2	709.6	710.9
10°	713.9	713.1	712.5	711.8	711.1	709.8	708.0	706.2	704.4	702.6	703.8
12.5°	705.9	705.2	704.7	704.1	703.5	702.4	700.7	699.0	697.3	695.6	696.5
15°	691.9	691.5	690.9	690.3	689.7	688.6	686.8	685.0	683.1	681.3	682.5
17.5°	675.9	675.1	674.4	673.7	672.9	671.7	669.9	668.1	666.3	664.5	665.3
20°	663.9	663.1	662.2	661.4	660.6	659.3	657.5	655.7	653.8	652.0	652.6
22.5°	650.4	649.5	648.7	647.9	647.0	645.7	643.9	642.1	640.3	638.5	639.0
25°	628.3	627.5	626.6	625.8	624.9	623.6	621.8	620.0	618.2	616.4	616.5
27.5°	604.7	603.9	603.1	602.3	601.4	600.1	598.1	596.2	594.3	592.3	592.4
30°	587.7	587.0	586.3	585.6	584.9	583.6	581.6	579.7	577.8	575.8	575.8
32.5°	570.7	569.8	568.8	567.9	567.0	565.8	564.4	562.8	561.3	559.9	559.1
35°	543.3	542.5	541.7	540.9	540.1	538.7	536.9	535.1	533.3	531.5	530.7
37.5°	515.4	514.3	513.2	512.2	511.1	509.7	507.8	506.1	504.2	502.4	501.4
40°	495.9	495.0	494.2	493.4	492.5	491.1	489.2	487.3	485.3	483.4	482.2
42.5°	476.4	475.5	474.5	473.5	472.6	471.2	469.2	467.3	465.4	463.4	462.3
45°	445.3	444.7	444.2	443.6	443.0	441.9	440.1	438.3	436.5	434.6	433.0
47.5°	414.4	413.6	412.9	412.1	411.2	409.9	408.3	406.6	404.9	403.2	401.5
50°	393.5	392.7	392.1	391.3	390.7	389.5	387.6	385.8	384.0	382.2	380.7
52.5°	371.5	371.0	370.6	370.1	369.6	368.4	366.5	364.6	362.6	360.8	359.5
55°	337.9	337.7	337.6	337.5	337.3	336.3	334.5	332.7	330.9	329.1	327.6
57.5°	305.9	305.4	304.9	304.5	304.0	303.0	301.6	300.2	298.7	297.3	296.0
60°	282.9	282.7	282.7	282.5	282.3	281.4	279.8	278.1	276.5	274.8	273.5
62.5°	262.4	262.0	261.7	261.4	261.0	260.0	258.3	256.7	254.9	253.3	252.1
65°	230.5	229.8	229.1	228.4	227.7	226.7	225.3	223.9	222.5	221.1	220.0
67.5°	196.6	196.0	195.3	194.8	194.1	193.3	192.2	191.2	190.1	189.1	188.2
70°	176.1	175.3	174.5	173.7	172.8	171.9	171.1	170.3	169.4	168.6	167.6
72.5°	154.7	154.0	153.4	152.8	152.2	151.4	150.5	149.5	148.5	147.7	146.8
75°	121.8	121.2	120.7	120.1	119.6	119.1	118.6	118.2	117.8	117.4	116.8
77.5°	92.7	92.4	92.0	91.8	91.5	91.1	90.6	90.1	89.5	89.0	88.6
80°	73.7	73.3	72.9	72.5	72.0	71.7	71.4	71.1	70.8	70.6	70.4
82.5°	55.2	55.1	55.0	55.0	54.9	54.8	54.8	54.7	54.6	54.6	54.3
85°	32.4	32.2	32.0	31.6	31.4	31.2	31.2	31.2	31.2	31.2	31.0
87.5°	13.0	12.9	12.6	12.4	12.2	12.1	12.2	12.2	12.3	12.4	12.3
90°	0.3	0.9	1.5	2.2	2.9	3.6	4.4	5.2	6.1	6.9	7.2
92.5°	5.4	5.2	5.0	4.8	4.6	4.9	5.5	6.1	6.8	7.3	7.7
95°	17.6	14.9	12.3	9.7	7.1	6.1	6.8	7.5	8.2	9.0	9.4
97.5°	35.3	34.2	32.9	31.8	30.6	27.7	23.1	18.5	13.9	9.3	9.8
100°	48.7	50.0	51.3	52.5	53.8	49.5	39.5	29.5	19.5	9.5	10.0
102.5°	63.9	64.8	65.7	66.7	67.6	62.6	51.7	40.8	29.8	19.0	17.4
105°	85.9	86.6	87.2	88.0	88.7	86.2	80.4	74.6	68.9	63.1	51.8
107.5°	109.0	109.6	110.1	110.7	111.3	112.0	112.9	113.8	114.7	115.6	107.3
110°	124.5	125.0	125.5	126.0	126.5	127.1	127.8	128.5	129.2	130.0	127.8



TEST NUMBER: P331916-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	139.2	139.7	140.1	140.6	141.0	141.6	142.4	143.1	143.7	144.5	144.5
115°	161.0	161.4	161.8	162.2	162.6	163.1	163.6	164.2	164.8	165.3	166.0
117.5°	182.2	182.7	183.1	183.6	184.1	184.5	184.7	185.1	185.4	185.6	186.1
120°	195.3	195.9	196.5	197.1	197.6	198.0	198.2	198.4	198.6	198.8	199.3
122.5°	208.7	209.2	209.6	210.1	210.6	210.9	211.2	211.4	211.7	211.9	212.3
125°	227.1	227.6	228.0	228.5	229.1	229.4	229.8	230.0	230.2	230.5	230.6
127.5°	244.8	245.3	245.8	246.3	246.8	247.2	247.5	247.9	248.2	248.4	248.7
130°	255.8	256.3	256.8	257.4	257.9	258.3	258.5	258.8	259.0	259.3	259.5
132.5°	266.4	266.9	267.5	268.0	268.5	268.8	269.0	269.3	269.5	269.7	269.9
135°	282.7	283.0	283.4	283.8	284.1	284.5	284.7	285.0	285.3	285.5	285.7
137.5°	296.4	296.9	297.4	297.9	298.4	298.7	298.9	299.0	299.1	299.3	299.6
140°	305.7	306.1	306.5	306.8	307.2	307.5	307.7	307.9	308.1	308.3	308.5
142.5°	314.2	314.6	315.0	315.4	315.8	316.0	316.3	316.4	316.6	316.8	317.0
145°	326.1	326.6	327.0	327.5	327.9	328.2	328.3	328.5	328.6	328.7	328.9
147.5°	337.4	337.7	337.9	338.3	338.5	338.8	338.9	339.0	339.2	339.2	339.4
150°	344.3	344.5	344.6	344.9	345.0	345.2	345.4	345.4	345.6	345.7	345.8
152.5°	350.5	350.6	350.7	350.7	350.8	351.0	351.0	351.1	351.1	351.2	351.5
155°	359.3	359.1	359.0	358.9	358.7	358.7	358.8	358.8	358.9	359.0	359.3
157.5°	366.1	366.1	366.1	366.0	366.0	366.0	365.9	365.8	365.7	365.7	366.1
160°	370.2	370.1	370.1	370.0	370.0	369.9	369.8	369.7	369.7	369.7	370.0
162.5°	374.1	374.0	373.8	373.7	373.5	373.3	373.2	373.2	373.2	373.1	373.5
165°	378.9	378.6	378.5	378.3	378.1	378.0	377.9	377.8	377.7	377.7	378.2
167.5°	382.5	382.3	382.0	381.8	381.5	381.4	381.4	381.4	381.4	381.4	381.9
170°	384.6	384.3	384.1	383.8	383.6	383.4	383.4	383.4	383.4	383.4	384.0
172.5°	386.0	385.7	385.4	385.1	384.7	384.7	384.7	384.7	384.8	384.8	385.4
175°	387.8	387.4	387.1	386.9	386.5	386.4	386.5	386.5	386.5	386.6	387.1
177.5°	388.2	388.0	387.8	387.5	387.2	387.1	387.2	387.2	387.3	387.3	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P331916-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	723.6	724.6	725.8	726.3	726.2	726.0	725.9	725.9
5°	719.7	721.1	722.5	723.1	722.8	722.5	722.3	721.9
7.5°	712.1	713.3	714.6	715.1	714.9	714.8	714.6	714.4
10°	705.1	706.4	707.6	708.1	707.8	707.5	707.3	706.9
12.5°	697.4	698.4	699.3	699.6	699.4	699.3	699.1	699.0
15°	683.6	684.7	685.8	685.9	685.1	684.3	683.5	682.7
17.5°	666.1	666.8	667.6	667.8	667.6	667.2	666.9	666.6
20°	653.1	653.7	654.2	654.3	653.9	653.5	653.1	652.6
22.5°	639.4	639.8	640.3	640.3	639.8	639.2	638.7	638.1
25°	616.7	616.9	616.9	616.9	616.4	616.0	615.6	615.1
27.5°	592.6	592.6	592.7	592.6	592.0	591.5	590.9	590.4
30°	575.8	575.8	575.8	575.4	574.4	573.4	572.4	571.4
32.5°	558.3	557.5	556.7	556.0	555.5	555.1	554.5	554.0
35°	529.8	529.0	528.2	527.4	526.7	526.0	525.3	524.6
37.5°	500.3	499.4	498.4	497.7	497.3	496.8	496.4	495.9
40°	481.2	480.0	479.0	478.1	477.5	477.0	476.5	475.9
42.5°	461.2	460.1	458.9	458.1	457.5	457.1	456.5	455.9
45°	431.4	429.7	428.0	426.8	426.2	425.4	424.8	424.0
47.5°	399.9	398.3	396.6	395.5	394.9	394.3	393.7	393.1
50°	379.2	377.6	376.1	375.0	374.1	373.2	372.4	371.6
52.5°	358.2	356.9	355.6	354.4	353.6	352.8	352.0	351.1
55°	326.0	324.6	323.0	321.9	321.2	320.5	319.8	319.1
57.5°	294.6	293.2	291.9	290.7	289.9	289.2	288.4	287.6
60°	272.3	271.1	269.8	268.8	268.2	267.4	266.8	266.0
62.5°	250.8	249.6	248.3	247.4	247.0	246.5	246.1	245.6
65°	218.8	217.8	216.6	215.9	215.5	215.1	214.7	214.2
67.5°	187.2	186.2	185.2	184.4	183.8	183.3	182.7	182.1
70°	166.6	165.8	164.8	163.9	163.2	162.5	161.8	161.1
72.5°	145.9	145.0	144.2	143.6	143.2	142.8	142.5	142.1
75°	116.0	115.4	114.6	114.1	113.7	113.2	112.8	112.4
77.5°	88.1	87.6	87.2	86.9	86.9	86.9	86.9	86.9
80°	70.3	70.1	70.0	70.0	70.0	70.0	70.0	70.0
82.5°	54.1	53.8	53.6	53.4	53.3	53.2	53.1	53.0
85°	30.7	30.4	30.1	30.0	30.0	30.0	30.0	30.0
87.5°	12.2	12.2	12.1	12.1	12.1	12.1	12.2	12.2
90°	7.4	7.7	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	8.2	8.6	9.0	9.3	9.3	9.4	9.5	9.5
95°	9.9	10.3	10.8	10.9	10.9	10.9	10.9	10.9
97.5°	10.3	10.8	11.3	11.6	11.7	11.7	11.8	11.9
100°	10.5	11.0	11.6	11.8	11.9	12.0	12.1	12.1
102.5°	15.8	14.2	12.6	11.9	12.0	12.1	12.2	12.3
105°	40.4	29.1	17.8	12.1	12.3	12.4	12.6	12.6
107.5°	99.1	90.7	82.4	73.9	65.5	56.9	48.3	39.8
110°	125.7	123.6	121.5	115.9	106.7	97.5	88.4	79.2





TEST NUMBER: P331916-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	144.6	144.6	144.6	143.7	141.7	139.8	137.9	135.9
115°	166.6	167.3	168.0	168.4	168.6	168.9	169.2	169.4
117.5°	186.7	187.2	187.7	188.0	188.0	188.1	188.2	188.2
120°	199.8	200.3	200.8	201.1	201.1	201.1	201.1	201.1
122.5°	212.6	213.0	213.4	213.5	213.6	213.7	213.7	213.8
125°	230.7	230.9	231.0	231.1	231.2	231.4	231.5	231.6
127.5°	248.8	249.1	249.3	249.3	249.2	249.1	248.9	248.8
130°	259.8	260.1	260.3	260.4	260.2	260.2	260.0	259.8
132.5°	270.2	270.4	270.7	270.8	270.5	270.4	270.2	270.0
135°	285.9	286.1	286.3	286.3	286.1	285.9	285.7	285.5
137.5°	299.9	300.2	300.5	300.6	300.4	300.4	300.2	300.1
140°	308.8	309.0	309.3	309.3	309.2	309.1	309.0	308.8
142.5°	317.2	317.4	317.6	317.6	317.5	317.2	317.1	316.9
145°	329.0	329.1	329.2	329.3	329.3	329.3	329.3	329.3
147.5°	339.5	339.7	339.8	339.7	339.4	339.1	338.8	338.5
150°	346.0	346.1	346.3	346.2	346.0	345.8	345.6	345.4
152.5°	351.7	352.0	352.2	352.1	351.9	351.6	351.2	351.0
155°	359.6	360.0	360.3	360.2	359.9	359.5	359.1	358.7
157.5°	366.5	366.9	367.3	367.2	366.7	366.2	365.7	365.2
160°	370.4	370.8	371.2	371.1	370.7	370.2	369.8	369.3
162.5°	374.0	374.4	374.8	374.9	374.5	374.1	373.7	373.2
165°	378.7	379.3	379.8	379.8	379.4	378.9	378.5	378.0
167.5°	382.4	382.9	383.4	383.4	382.9	382.4	381.9	381.4
170°	384.5	385.0	385.5	385.5	385.0	384.5	384.0	383.4
172.5°	385.9	386.4	386.9	386.9	386.3	385.7	385.1	384.6
175°	387.5	388.0	388.4	388.4	387.9	387.3	386.9	386.4
177.5°	388.2	388.6	389.0	388.9	388.4	387.9	387.3	386.9
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)