

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331893-927

Luminaire Tested: **S123DIP-S340D1025U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331893-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3941.7 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	29	24	43	32	26	22	26	21	18	20	17	14	15	12	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4100	4100	4100	4100
5°	4889	4118	3649	4118
10°	6120	4098	3296	4098
15°	7506	4063	3069	4063
20°	8942	4013	2922	4013
25°	9495	3950	2888	3950
30°	8139	3904	2903	3904
35°	5660	3840	2934	3840
40°	4263	3763	2925	3763
45°	3539	3649	2888	3649
50°	3170	3418	2862	3418
55°	2965	3170	2826	3170
60°	2781	2908	2796	2908
65°	2613	2651	2707	2651
70°	2452	2357	2578	2357
75°	2196	2067	2366	2067
80°	1922	1692	2039	1692
85°	1507	1235	1371	1235



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.5	1.0
10°-20°	120.3	3.1
20°-30°	201.9	5.1
30°-40°	228.6	5.8
40°-50°	205.0	5.2
50°-60°	165.5	4.2
60°-70°	115.3	2.9
70°-80°	60.6	1.5
80°-90°	17.8	0.5
90°-100°	65.6	1.7
100°-110°	196.3	5.0
110°-120°	333.8	8.5
120°-130°	439.1	11.1
130°-140°	493.6	12.5
140°-150°	485.2	12.3
150°-160°	408.4	10.4
160°-170°	271.9	6.9
170°-180°	95.2	2.4
0°-30°	359.8	9.1
0°-40°	588.4	14.9
0°-60°	958.9	24.3
0°-90°	1152.6	29.2
90°-120°	595.7	15.1
90°-150°	2013.5	51.1
90°-180°	2789.0	70.8
0°-180°	3941.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	381	381	381	381	381	
5°	452	381	338	381	452	47
15°	674	365	275	365	674	194
25°	800	333	243	333	800	351
35°	431	292	223	292	431	280
45°	232	240	190	240	232	184
55°	158	169	151	169	158	142
65°	103	104	106	104	103	102
75°	53	50	57	50	53	56
85°	12	10	11	10	12	15
90°	24	1	24	1	24	12
95°	62	47	62	47	62	63
105°	188	178	188	178	188	200
115°	337	336	337	336	337	333
125°	486	492	486	492	486	435
135°	637	638	637	638	637	490
145°	774	774	774	774	774	483
155°	885	886	885	886	885	407
165°	962	966	962	966	962	271
175°	1000	1004	1000	1004	1000	95
180°	1007	1007	1007	1007	1007	



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	404.3	403.9	403.2	403.8	402.6	401.0	400.8	399.3	395.1	394.8	393.6
5°	452.5	451.1	450.8	450.7	448.1	444.6	437.9	437.4	428.5	424.1	418.7
7.5°	515.1	515.8	513.1	510.8	502.9	497.6	490.5	481.4	470.6	459.5	452.2
10°	559.9	566.0	558.5	553.3	548.5	539.5	528.9	515.8	502.7	487.4	475.8
12.5°	608.1	611.0	609.5	604.7	597.2	583.4	564.8	550.3	538.3	512.8	502.5
15°	673.6	684.8	677.6	661.1	661.4	648.3	624.0	597.2	583.0	560.6	530.2
17.5°	743.5	744.8	741.8	727.9	718.7	700.7	678.2	652.6	623.8	596.8	564.4
20°	780.6	779.5	773.1	765.9	750.0	736.0	711.5	682.9	645.9	619.3	584.1
22.5°	801.3	799.5	796.4	790.4	777.2	762.2	740.1	708.8	673.7	637.1	596.4
25°	799.5	801.8	802.2	800.6	796.0	787.0	769.6	744.7	709.6	662.5	620.1
27.5°	727.1	730.6	740.4	749.2	758.9	768.9	767.5	755.2	729.2	688.6	636.7
30°	654.8	647.4	665.7	688.7	704.4	732.1	747.6	748.5	734.0	699.1	648.5
32.5°	554.4	562.5	570.6	599.0	633.3	664.3	695.2	720.0	722.9	699.7	655.5
35°	430.7	440.9	455.7	470.4	507.3	539.1	593.3	640.6	678.2	683.2	656.1
37.5°	347.1	352.1	361.5	376.3	400.4	438.1	480.0	539.7	594.3	634.9	636.6
40°	303.4	304.9	315.4	326.6	346.2	377.2	415.0	467.9	533.1	589.9	613.5
42.5°	270.6	273.9	278.4	289.1	304.8	328.0	363.2	406.9	466.8	532.0	578.1
45°	232.5	236.2	239.0	246.2	257.3	273.0	297.5	337.4	382.9	450.3	512.5
47.5°	207.4	207.6	209.7	215.2	222.7	234.5	251.8	277.4	319.2	373.9	437.8
50°	189.3	192.3	193.1	197.3	203.2	211.8	226.2	248.0	282.3	330.3	389.0
52.5°	176.7	177.5	179.6	182.7	187.8	194.6	207.1	224.1	251.0	292.0	345.9
55°	158.0	158.0	160.0	162.4	165.3	171.4	179.7	192.3	212.8	244.5	289.2
57.5°	140.7	141.6	143.1	143.8	146.3	150.4	157.2	166.8	182.0	206.5	242.0
60°	129.2	130.9	130.6	132.1	134.4	137.5	143.4	151.1	164.8	184.3	214.3
62.5°	119.1	119.1	119.0	120.8	122.9	126.0	129.8	136.5	148.1	165.5	190.9
65°	102.6	102.3	103.5	104.6	105.4	107.6	110.5	116.5	124.2	137.1	156.9
67.5°	87.9	86.8	87.5	87.9	89.2	90.9	93.7	97.4	103.5	113.8	128.7
70°	77.9	76.9	76.8	77.2	78.3	79.5	81.6	85.1	90.8	99.1	110.0
72.5°	67.6	66.9	66.9	67.7	68.2	69.1	70.5	73.7	78.3	84.5	94.7
75°	52.8	52.8	52.8	53.0	53.6	54.3	55.4	57.0	60.5	65.0	71.8
77.5°	39.5	39.5	39.3	39.3	40.1	40.4	40.6	42.2	44.2	47.1	52.1
80°	31.0	30.1	30.4	31.0	31.4	31.5	32.1	32.5	34.1	35.8	39.3
82.5°	23.1	22.3	22.3	23.2	23.3	23.4	24.0	24.5	25.1	26.6	28.5
85°	12.2	12.2	12.4	12.4	12.5	12.4	12.9	13.1	13.1	14.0	15.1
87.5°	9.2	8.8	8.9	9.0	8.7	8.8	8.8	8.8	8.8	8.8	8.5
90°	23.7	23.4	23.1	22.7	22.3	21.8	21.1	20.4	19.6	19.0	16.7
92.5°	31.9	32.2	32.4	32.6	32.8	32.6	32.1	31.5	30.9	30.3	29.1
95°	61.7	61.7	61.7	61.7	61.7	61.3	60.6	59.9	59.3	58.5	57.1
97.5°	94.9	95.0	95.1	95.1	95.1	94.8	94.0	93.2	92.4	91.6	90.5
100°	120.2	119.9	119.5	119.1	118.8	118.4	117.8	117.3	116.8	116.2	115.3
102.5°	146.2	146.2	146.2	146.3	146.4	146.2	145.7	145.1	144.6	144.1	142.9
105°	188.2	187.8	187.5	187.1	186.8	186.6	186.6	186.6	186.6	186.6	185.1
107.5°	232.0	232.2	232.4	232.7	232.8	232.7	232.1	231.6	231.0	230.4	229.8
110°	261.7	262.1	262.4	262.8	263.2	263.0	262.3	261.6	260.9	260.2	259.8



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	293.3	293.4	293.5	293.6	293.7	293.3	292.4	291.6	290.7	289.9	289.9
115°	336.8	337.1	337.2	337.4	337.5	337.5	337.4	337.2	337.1	336.8	337.2
117.5°	381.0	381.5	382.0	382.5	382.9	383.3	383.3	383.3	383.3	383.3	383.8
120°	412.0	412.3	412.7	413.0	413.4	413.7	413.8	414.0	414.2	414.4	415.3
122.5°	441.7	442.2	442.7	443.2	443.7	444.2	444.7	445.0	445.5	446.0	446.5
125°	486.3	487.0	487.7	488.5	489.1	489.8	490.5	491.2	491.9	492.7	493.0
127.5°	530.8	531.6	532.3	533.2	534.0	534.9	535.9	536.9	537.8	538.8	539.2
130°	559.8	561.1	562.3	563.6	564.7	565.8	566.4	567.1	567.8	568.5	569.1
132.5°	590.3	591.2	592.2	593.1	594.1	594.9	595.8	596.6	597.5	598.3	598.7
135°	637.4	637.7	638.0	638.4	638.7	639.3	640.0	640.7	641.4	642.1	642.3
137.5°	679.0	679.6	680.2	681.0	681.6	682.3	683.1	683.8	684.5	685.2	684.8
140°	706.2	707.4	708.6	709.9	711.1	711.8	711.9	712.1	712.3	712.5	712.3
142.5°	734.0	734.9	735.9	736.8	737.8	738.3	738.6	738.7	738.9	739.0	738.7
145°	774.1	774.8	775.5	776.3	777.0	777.4	777.6	777.8	777.9	778.1	777.6
147.5°	809.9	811.0	812.0	813.1	814.1	814.7	814.7	814.7	814.7	814.7	814.1
150°	832.7	833.7	834.8	835.8	836.9	837.4	837.4	837.4	837.4	837.4	837.1
152.5°	854.8	855.7	856.7	857.5	858.5	858.8	858.5	858.3	857.9	857.7	857.5
155°	884.9	886.1	887.3	888.6	889.8	890.0	889.4	888.7	888.0	887.2	887.1
157.5°	912.2	913.2	914.2	915.2	916.2	916.3	915.5	914.8	914.1	913.3	913.2
160°	929.9	930.7	931.4	932.1	932.7	932.6	931.8	930.9	930.0	929.2	929.2
162.5°	943.3	944.4	945.5	946.6	947.7	947.8	947.0	946.1	945.2	944.4	944.2
165°	962.3	963.6	964.8	966.1	967.3	967.3	966.3	965.3	964.2	963.1	963.1
167.5°	978.7	979.8	980.8	981.9	983.0	983.0	981.9	980.8	979.8	978.7	978.5
170°	986.9	988.1	989.4	990.5	991.8	991.8	990.5	989.4	988.1	986.9	986.9
172.5°	993.2	994.4	995.7	996.9	998.1	998.1	997.1	996.0	994.9	993.8	993.8
175°	1000.3	1001.6	1002.7	1004.0	1005.2	1005.4	1004.2	1003.2	1002.2	1001.1	1001.1
177.5°	1004.1	1005.1	1006.1	1007.1	1008.1	1008.1	1007.3	1006.5	1005.6	1004.7	1004.7
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	392.7	391.6	390.4	388.3	386.5	384.0	383.3	382.4	379.7	377.4	375.6
5°	416.7	412.3	405.8	399.9	395.1	388.6	385.0	381.1	375.6	370.6	366.5
7.5°	441.8	433.1	423.0	412.3	402.1	392.4	384.5	377.5	369.7	362.4	356.6
10°	461.8	449.2	435.1	420.0	407.1	394.6	384.0	374.9	364.9	356.2	349.0
12.5°	484.5	465.9	446.6	428.2	412.9	395.5	382.7	371.0	359.7	349.3	341.2
15°	511.4	487.7	464.9	439.6	416.4	394.6	379.5	364.6	351.6	340.9	330.5
17.5°	535.9	509.1	479.0	448.2	420.2	394.3	373.2	356.5	340.1	327.0	316.7
20°	549.8	519.4	485.2	453.3	422.2	393.5	370.2	350.3	332.6	318.7	307.1
22.5°	561.7	526.1	490.8	456.6	422.1	391.1	364.7	344.2	325.0	311.5	299.1
25°	574.2	531.5	496.1	456.1	417.5	385.3	355.8	332.6	313.4	297.5	284.8
27.5°	584.8	531.2	489.1	446.0	410.1	378.0	346.4	321.5	301.1	283.8	270.9
30°	591.8	531.9	481.9	439.3	403.1	369.9	339.2	314.1	292.7	275.2	263.0
32.5°	596.3	531.4	475.2	429.8	391.8	362.4	331.4	305.4	283.4	266.2	254.4
35°	598.9	528.1	463.7	410.3	373.8	345.1	319.1	292.2	269.1	253.0	239.7
37.5°	593.7	521.3	450.5	391.4	351.4	323.3	301.3	278.5	256.4	238.7	227.2
40°	585.6	516.9	440.1	378.1	336.0	309.0	290.3	267.8	246.0	229.2	218.5
42.5°	570.1	507.9	428.8	363.4	320.1	293.0	275.8	257.0	236.4	220.6	209.9
45°	532.3	488.3	411.7	341.3	296.6	268.5	253.4	239.7	221.1	205.8	196.5
47.5°	479.7	458.8	387.1	317.9	272.0	245.0	229.3	218.3	204.7	192.3	183.5
50°	443.3	434.6	370.4	301.9	255.6	229.2	214.0	204.1	194.3	182.0	173.9
52.5°	401.2	406.5	350.9	285.4	238.9	212.9	198.8	190.8	182.0	171.7	164.7
55°	342.0	361.3	317.3	257.6	214.0	189.3	175.9	168.9	163.7	156.1	150.0
57.5°	286.5	311.2	280.8	229.0	189.6	168.3	155.4	147.8	144.5	140.5	135.7
60°	253.6	277.9	254.8	209.8	173.3	153.0	141.6	135.1	131.7	129.0	124.9
62.5°	224.2	248.8	229.5	190.4	157.2	138.4	128.4	122.1	119.5	118.1	114.6
65°	183.8	205.0	192.1	160.0	134.2	117.6	108.5	104.1	101.7	101.2	98.9
67.5°	149.6	165.7	156.4	132.7	112.4	98.1	90.4	86.6	84.8	84.5	82.9
70°	127.1	142.3	135.1	113.7	96.2	84.9	78.3	74.9	73.8	73.7	72.7
72.5°	109.7	120.3	114.5	96.7	83.2	73.0	68.0	64.6	63.4	63.6	63.0
75°	81.2	89.1	85.8	73.4	62.6	55.9	51.9	49.7	48.6	49.1	48.3
77.5°	58.5	63.5	60.4	51.9	45.2	40.4	37.4	36.0	35.0	35.0	34.7
80°	44.1	47.1	45.4	40.2	34.7	30.7	28.2	27.3	26.8	26.5	26.4
82.5°	31.4	33.9	31.9	28.4	24.6	22.2	20.8	19.6	19.3	19.3	19.2
85°	15.8	16.8	16.1	13.9	12.4	11.2	10.5	10.0	9.6	9.7	9.4
87.5°	8.3	8.0	7.1	6.2	5.5	4.7	4.4	3.7	3.7	4.1	4.3
90°	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	27.7	26.5	25.2	23.9	22.7	21.5	20.4	19.2	20.4	21.5	22.7
95°	55.7	54.3	52.9	51.6	50.4	49.1	47.8	46.7	47.8	49.1	50.4
97.5°	89.5	88.5	87.5	86.5	85.6	84.7	83.8	82.9	83.8	84.7	85.6
100°	114.5	113.6	112.7	111.8	110.7	109.6	108.6	107.6	108.6	109.6	110.7
102.5°	141.7	140.6	139.4	138.6	137.9	137.3	136.7	136.0	136.7	137.3	137.9
105°	183.5	181.9	180.3	179.4	179.0	178.6	178.2	177.9	178.2	178.6	179.0
107.5°	229.2	228.5	227.9	227.5	227.3	227.0	226.9	226.6	226.9	227.0	227.3
110°	259.4	259.1	258.7	258.4	258.0	257.7	257.4	257.0	257.4	257.7	258.0



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	289.8	289.7	289.6	289.5	289.2	289.1	288.8	288.6	288.8	289.1	289.2
115°	337.5	337.9	338.3	338.2	337.6	337.2	336.6	336.0	336.6	337.2	337.6
117.5°	384.3	384.8	385.2	385.2	384.9	384.5	384.2	383.8	384.2	384.5	384.9
120°	416.1	417.0	417.9	417.8	416.8	415.7	414.6	413.6	414.6	415.7	416.8
122.5°	446.9	447.3	447.8	447.7	446.9	446.1	445.4	444.6	445.4	446.1	446.9
125°	493.4	493.7	494.1	493.9	493.5	492.9	492.4	491.9	492.4	492.9	493.5
127.5°	539.6	540.0	540.3	540.0	538.8	537.7	536.6	535.5	536.6	537.7	538.8
130°	569.6	570.1	570.7	570.2	568.8	567.4	566.0	564.6	566.0	567.4	568.8
132.5°	599.0	599.4	599.8	599.4	597.9	596.5	595.1	593.7	595.1	596.5	597.9
135°	642.5	642.6	642.8	642.4	641.3	640.2	639.2	638.2	639.2	640.2	641.3
137.5°	684.4	683.9	683.4	682.8	681.9	681.0	680.2	679.3	680.2	681.0	681.9
140°	712.1	711.9	711.8	711.2	710.3	709.5	708.6	707.7	708.6	709.5	710.3
142.5°	738.4	738.1	737.8	737.2	736.3	735.5	734.5	733.6	734.5	735.5	736.3
145°	777.1	776.5	776.0	775.5	775.2	774.8	774.5	774.1	774.5	774.8	775.2
147.5°	813.7	813.2	812.7	812.1	811.5	810.9	810.2	809.6	810.2	810.9	811.5
150°	836.7	836.4	836.0	835.7	835.3	835.0	834.6	834.2	834.6	835.0	835.3
152.5°	857.2	857.1	856.8	856.4	856.0	855.5	855.0	854.5	855.0	855.5	856.0
155°	886.8	886.7	886.5	886.5	886.5	886.5	886.5	886.5	886.5	886.5	886.5
157.5°	913.1	912.9	912.8	912.8	913.0	913.2	913.5	913.6	913.5	913.2	913.0
160°	929.2	929.2	929.2	929.3	929.7	930.0	930.3	930.7	930.3	930.0	929.7
162.5°	944.0	943.9	943.8	944.0	944.4	944.9	945.4	945.9	945.4	944.9	944.4
165°	963.1	963.1	963.1	963.5	963.9	964.5	965.0	965.5	965.0	964.5	963.9
167.5°	978.3	978.3	978.1	978.3	979.1	979.8	980.5	981.2	980.5	979.8	979.1
170°	986.9	986.9	986.9	987.2	987.9	988.6	989.4	990.1	989.4	988.6	987.9
172.5°	993.8	993.8	993.8	994.2	994.9	995.6	996.3	997.0	996.3	995.6	994.9
175°	1001.1	1001.1	1001.1	1001.5	1002.2	1002.8	1003.5	1004.2	1003.5	1002.8	1002.2
177.5°	1004.7	1004.7	1004.7	1005.0	1005.6	1006.2	1006.7	1007.3	1006.7	1006.2	1005.6
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	374.5	373.5	372.1	369.9	368.0	365.3	365.3	365.7	365.7	365.6	365.3
5°	363.2	360.4	357.1	353.2	349.2	345.1	344.4	342.9	341.8	341.0	340.2
7.5°	351.2	346.3	341.4	336.0	331.1	327.0	324.2	321.8	320.3	318.6	317.4
10°	343.1	337.0	331.3	325.6	319.2	314.3	311.2	309.0	307.3	305.8	305.1
12.5°	333.5	326.5	320.2	314.7	307.9	302.8	299.8	298.7	296.8	293.7	292.1
15°	319.5	313.0	305.5	297.1	293.8	287.6	284.0	282.3	281.2	278.8	278.1
17.5°	307.4	299.0	290.5	284.3	278.1	273.1	271.1	269.0	267.6	265.6	265.0
20°	297.9	290.3	282.6	275.9	269.4	263.9	262.2	260.8	259.3	258.4	257.6
22.5°	288.1	280.6	274.1	267.9	261.0	257.4	255.6	254.0	252.9	252.3	251.6
25°	274.4	267.8	260.5	255.1	249.5	247.1	246.0	245.1	244.3	243.4	243.2
27.5°	262.2	254.9	249.1	243.9	240.0	238.0	236.9	236.5	236.6	236.9	237.2
30°	253.0	246.4	241.6	237.2	233.5	231.6	231.4	231.4	232.2	232.3	232.7
32.5°	244.6	239.2	234.3	230.0	227.3	226.0	226.7	226.7	227.3	227.8	228.5
35°	232.3	227.5	223.9	220.1	217.8	218.3	218.7	219.0	220.0	221.1	221.8
37.5°	220.6	216.5	212.6	209.8	208.7	209.6	210.6	211.3	212.4	213.3	214.0
40°	212.2	209.1	205.4	202.8	203.2	203.7	204.5	205.4	206.4	206.9	207.6
42.5°	204.4	201.1	198.3	196.1	196.7	197.4	197.8	198.3	199.4	200.4	200.8
45°	192.5	189.9	187.4	186.0	186.4	186.8	187.1	187.7	188.6	189.3	189.6
47.5°	179.1	177.3	175.5	174.3	174.9	174.8	175.2	176.4	176.7	177.1	178.2
50°	170.6	168.9	166.8	166.4	166.4	166.4	166.7	168.1	168.1	168.9	169.6
52.5°	161.1	160.0	158.8	158.0	157.7	157.7	158.5	159.2	159.5	160.6	161.4
55°	147.1	146.0	144.9	144.3	143.9	144.3	145.8	146.2	147.1	147.7	148.2
57.5°	132.5	131.7	130.8	130.5	130.4	130.9	131.7	132.8	133.0	134.8	135.5
60°	122.9	121.6	120.9	120.9	120.5	122.2	121.8	123.7	124.1	125.2	126.4
62.5°	113.0	111.3	111.0	111.0	111.5	112.0	112.5	113.3	114.3	115.7	116.7
65°	97.0	96.2	97.4	97.3	96.9	98.0	98.0	98.9	100.1	101.3	103.4
67.5°	82.0	81.5	81.6	81.6	82.1	82.8	83.3	84.1	85.5	86.8	88.2
70°	71.8	72.3	71.5	72.2	72.7	72.9	73.3	74.4	75.8	76.8	78.3
72.5°	61.9	61.9	61.9	62.3	62.8	63.1	63.5	64.8	66.4	67.2	68.4
75°	47.6	47.5	48.0	48.0	48.9	49.3	49.7	50.2	51.7	52.8	53.7
77.5°	34.8	35.0	34.9	35.5	35.3	35.3	36.4	37.0	37.2	39.4	39.8
80°	26.2	26.5	26.8	26.9	27.1	26.8	28.0	28.6	28.6	29.9	30.8
82.5°	18.9	19.0	19.5	19.7	19.7	20.1	20.2	20.6	21.1	21.6	22.8
85°	9.4	10.0	10.1	10.0	10.1	9.7	10.3	10.5	10.7	10.7	10.7
87.5°	4.5	5.1	5.4	6.0	6.3	6.9	7.1	6.9	7.1	7.6	7.1
90°	7.8	9.8	12.1	14.4	16.7	19.0	19.6	20.4	21.1	21.8	22.3
92.5°	23.9	25.2	26.5	27.7	29.1	30.3	30.9	31.5	32.1	32.6	32.8
95°	51.6	52.9	54.3	55.7	57.1	58.5	59.3	59.9	60.6	61.3	61.7
97.5°	86.5	87.5	88.5	89.5	90.5	91.6	92.4	93.2	94.0	94.8	95.1
100°	111.8	112.7	113.6	114.5	115.3	116.2	116.8	117.3	117.8	118.4	118.8
102.5°	138.6	139.4	140.6	141.7	142.9	144.1	144.6	145.1	145.7	146.2	146.4
105°	179.4	180.3	181.9	183.5	185.1	186.6	186.6	186.6	186.6	186.6	186.8
107.5°	227.5	227.9	228.5	229.2	229.8	230.4	231.0	231.6	232.1	232.7	232.8
110°	258.4	258.7	259.1	259.4	259.8	260.2	260.9	261.6	262.3	263.0	263.2



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	289.5	289.6	289.7	289.8	289.9	289.9	290.7	291.6	292.4	293.3	293.7
115°	338.2	338.3	337.9	337.5	337.2	336.8	337.1	337.2	337.4	337.5	337.5
117.5°	385.2	385.2	384.8	384.3	383.8	383.3	383.3	383.3	383.3	383.3	382.9
120°	417.8	417.9	417.0	416.1	415.3	414.4	414.2	414.0	413.8	413.7	413.4
122.5°	447.7	447.8	447.3	446.9	446.5	446.0	445.5	445.0	444.7	444.2	443.7
125°	493.9	494.1	493.7	493.4	493.0	492.7	491.9	491.2	490.5	489.8	489.1
127.5°	540.0	540.3	540.0	539.6	539.2	538.8	537.8	536.9	535.9	534.9	534.0
130°	570.2	570.7	570.1	569.6	569.1	568.5	567.8	567.1	566.4	565.8	564.7
132.5°	599.4	599.8	599.4	599.0	598.7	598.3	597.5	596.6	595.8	594.9	594.1
135°	642.4	642.8	642.6	642.5	642.3	642.1	641.4	640.7	640.0	639.3	638.7
137.5°	682.8	683.4	683.9	684.4	684.8	685.2	684.5	683.8	683.1	682.3	681.6
140°	711.2	711.8	711.9	712.1	712.3	712.5	712.3	712.1	711.9	711.8	711.1
142.5°	737.2	737.8	738.1	738.4	738.7	739.0	738.9	738.7	738.6	738.3	737.8
145°	775.5	776.0	776.5	777.1	777.6	778.1	777.9	777.8	777.6	777.4	777.0
147.5°	812.1	812.7	813.2	813.7	814.1	814.7	814.7	814.7	814.7	814.7	814.1
150°	835.7	836.0	836.4	836.7	837.1	837.4	837.4	837.4	837.4	837.4	836.9
152.5°	856.4	856.8	857.1	857.2	857.5	857.7	857.9	858.3	858.5	858.8	858.5
155°	886.5	886.5	886.7	886.8	887.1	887.2	888.0	888.7	889.4	890.0	889.8
157.5°	912.8	912.8	912.9	913.1	913.2	913.3	914.1	914.8	915.5	916.3	916.2
160°	929.3	929.2	929.2	929.2	929.2	929.2	930.0	930.9	931.8	932.6	932.7
162.5°	944.0	943.8	943.9	944.0	944.2	944.4	945.2	946.1	947.0	947.8	947.7
165°	963.5	963.1	963.1	963.1	963.1	963.1	964.2	965.3	966.3	967.3	967.3
167.5°	978.3	978.1	978.3	978.3	978.5	978.7	979.8	980.8	981.9	983.0	983.0
170°	987.2	986.9	986.9	986.9	986.9	986.9	988.1	989.4	990.5	991.8	991.8
172.5°	994.2	993.8	993.8	993.8	993.8	993.8	994.9	996.0	997.1	998.1	998.1
175°	1001.5	1001.1	1001.1	1001.1	1001.1	1001.1	1002.2	1003.2	1004.2	1005.4	1005.2
177.5°	1005.0	1004.7	1004.7	1004.7	1004.7	1004.7	1005.6	1006.5	1007.3	1008.1	1008.1
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	364.2	364.1	365.1	364.4	365.1	364.1	364.2	365.3	365.6	365.7	365.7
5°	339.1	339.6	337.7	337.7	337.7	339.6	339.1	340.2	341.0	341.8	342.9
7.5°	316.6	315.8	315.8	314.8	315.8	315.8	316.6	317.4	318.6	320.3	321.8
10°	302.9	301.7	301.3	301.6	301.3	301.7	302.9	305.1	305.8	307.3	309.0
12.5°	291.4	291.3	288.8	288.8	288.8	291.3	291.4	292.1	293.7	296.8	298.7
15°	278.1	274.6	274.3	275.4	274.3	274.6	278.1	278.1	278.8	281.2	282.3
17.5°	264.7	262.8	263.0	262.4	263.0	262.8	264.7	265.0	265.6	267.6	269.0
20°	257.6	256.5	256.4	255.1	256.4	256.5	257.6	257.6	258.4	259.3	260.8
22.5°	251.1	250.8	250.9	249.5	250.9	250.8	251.1	251.6	252.3	252.9	254.0
25°	243.0	244.0	243.2	243.2	243.2	244.0	243.0	243.2	243.4	244.3	245.1
27.5°	237.6	237.6	237.2	237.2	237.2	237.6	237.6	237.2	236.9	236.6	236.5
30°	233.5	233.3	233.6	233.6	233.6	233.3	233.5	232.7	232.3	232.2	231.4
32.5°	229.3	229.6	229.7	229.8	229.7	229.6	229.3	228.5	227.8	227.3	226.7
35°	222.9	223.2	223.7	223.3	223.7	223.2	222.9	221.8	221.1	220.0	219.0
37.5°	214.3	215.2	215.0	215.2	215.0	215.2	214.3	214.0	213.3	212.4	211.3
40°	207.8	208.3	208.2	208.2	208.2	208.3	207.8	207.6	206.9	206.4	205.4
42.5°	201.1	201.5	201.1	200.8	201.1	201.5	201.1	200.8	200.4	199.4	198.3
45°	190.3	189.9	190.4	189.7	190.4	189.9	190.3	189.6	189.3	188.6	187.7
47.5°	178.1	178.5	178.6	179.2	178.6	178.5	178.1	178.2	177.1	176.7	176.4
50°	170.0	171.1	171.1	170.9	171.1	171.1	170.0	169.6	168.9	168.1	168.1
52.5°	162.0	162.5	163.3	163.2	163.3	162.5	162.0	161.4	160.6	159.5	159.2
55°	149.6	150.0	150.4	150.6	150.4	150.0	149.6	148.2	147.7	147.1	146.2
57.5°	136.9	136.7	137.6	137.9	137.6	136.7	136.9	135.5	134.8	133.0	132.8
60°	127.9	127.9	129.4	129.9	129.4	127.9	127.9	126.4	125.2	124.1	123.7
62.5°	118.3	118.9	120.3	119.6	120.3	118.9	118.3	116.7	115.7	114.3	113.3
65°	104.3	105.8	105.6	106.3	105.6	105.8	104.3	103.4	101.3	100.1	98.9
67.5°	89.6	90.5	91.9	92.0	91.9	90.5	89.6	88.2	86.8	85.5	84.1
70°	79.7	80.6	81.4	81.9	81.4	80.6	79.7	78.3	76.8	75.8	74.4
72.5°	70.1	70.6	72.4	71.6	72.4	70.6	70.1	68.4	67.2	66.4	64.8
75°	55.0	56.3	57.4	56.9	57.4	56.3	55.0	53.7	52.8	51.7	50.2
77.5°	40.6	42.0	42.5	42.0	42.5	42.0	40.6	39.8	39.4	37.2	37.0
80°	32.1	31.9	33.0	32.9	33.0	31.9	32.1	30.8	29.9	28.6	28.6
82.5°	23.5	23.4	23.8	24.0	23.8	23.4	23.5	22.8	21.6	21.1	20.6
85°	11.4	12.0	11.2	11.1	11.2	12.0	11.4	10.7	10.7	10.7	10.5
87.5°	7.2	7.3	7.2	7.1	7.2	7.3	7.2	7.1	7.6	7.1	6.9
90°	22.7	23.1	23.4	23.7	23.4	23.1	22.7	22.3	21.8	21.1	20.4
92.5°	32.6	32.4	32.2	31.9	32.2	32.4	32.6	32.8	32.6	32.1	31.5
95°	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.3	60.6	59.9
97.5°	95.1	95.1	95.0	94.9	95.0	95.1	95.1	95.1	94.8	94.0	93.2
100°	119.1	119.5	119.9	120.2	119.9	119.5	119.1	118.8	118.4	117.8	117.3
102.5°	146.3	146.2	146.2	146.2	146.2	146.2	146.3	146.4	146.2	145.7	145.1
105°	187.1	187.5	187.8	188.2	187.8	187.5	187.1	186.8	186.6	186.6	186.6
107.5°	232.7	232.4	232.2	232.0	232.2	232.4	232.7	232.8	232.7	232.1	231.6
110°	262.8	262.4	262.1	261.7	262.1	262.4	262.8	263.2	263.0	262.3	261.6



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	293.6	293.5	293.4	293.3	293.4	293.5	293.6	293.7	293.3	292.4	291.6
115°	337.4	337.2	337.1	336.8	337.1	337.2	337.4	337.5	337.5	337.4	337.2
117.5°	382.5	382.0	381.5	381.0	381.5	382.0	382.5	382.9	383.3	383.3	383.3
120°	413.0	412.7	412.3	412.0	412.3	412.7	413.0	413.4	413.7	413.8	414.0
122.5°	443.2	442.7	442.2	441.7	442.2	442.7	443.2	443.7	444.2	444.7	445.0
125°	488.5	487.7	487.0	486.3	487.0	487.7	488.5	489.1	489.8	490.5	491.2
127.5°	533.2	532.3	531.6	530.8	531.6	532.3	533.2	534.0	534.9	535.9	536.9
130°	563.6	562.3	561.1	559.8	561.1	562.3	563.6	564.7	565.8	566.4	567.1
132.5°	593.1	592.2	591.2	590.3	591.2	592.2	593.1	594.1	594.9	595.8	596.6
135°	638.4	638.0	637.7	637.4	637.7	638.0	638.4	638.7	639.3	640.0	640.7
137.5°	681.0	680.2	679.6	679.0	679.6	680.2	681.0	681.6	682.3	683.1	683.8
140°	709.9	708.6	707.4	706.2	707.4	708.6	709.9	711.1	711.8	711.9	712.1
142.5°	736.8	735.9	734.9	734.0	734.9	735.9	736.8	737.8	738.3	738.6	738.7
145°	776.3	775.5	774.8	774.1	774.8	775.5	776.3	777.0	777.4	777.6	777.8
147.5°	813.1	812.0	811.0	809.9	811.0	812.0	813.1	814.1	814.7	814.7	814.7
150°	835.8	834.8	833.7	832.7	833.7	834.8	835.8	836.9	837.4	837.4	837.4
152.5°	857.5	856.7	855.7	854.8	855.7	856.7	857.5	858.5	858.8	858.5	858.3
155°	888.6	887.3	886.1	884.9	886.1	887.3	888.6	889.8	890.0	889.4	888.7
157.5°	915.2	914.2	913.2	912.2	913.2	914.2	915.2	916.2	916.3	915.5	914.8
160°	932.1	931.4	930.7	929.9	930.7	931.4	932.1	932.7	932.6	931.8	930.9
162.5°	946.6	945.5	944.4	943.3	944.4	945.5	946.6	947.7	947.8	947.0	946.1
165°	966.1	964.8	963.6	962.3	963.6	964.8	966.1	967.3	967.3	966.3	965.3
167.5°	981.9	980.8	979.8	978.7	979.8	980.8	981.9	983.0	983.0	981.9	980.8
170°	990.5	989.4	988.1	986.9	988.1	989.4	990.5	991.8	991.8	990.5	989.4
172.5°	996.9	995.7	994.4	993.2	994.4	995.7	996.9	998.1	998.1	997.1	996.0
175°	1004.0	1002.7	1001.6	1000.3	1001.6	1002.7	1004.0	1005.2	1005.4	1004.2	1003.2
177.5°	1007.1	1006.1	1005.1	1004.1	1005.1	1006.1	1007.1	1008.1	1008.1	1007.3	1006.5
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	365.3	365.3	368.0	369.9	372.1	373.5	374.5	375.6	377.4	379.7	382.4
5°	344.4	345.1	349.2	353.2	357.1	360.4	363.2	366.5	370.6	375.6	381.1
7.5°	324.2	327.0	331.1	336.0	341.4	346.3	351.2	356.6	362.4	369.7	377.5
10°	311.2	314.3	319.2	325.6	331.3	337.0	343.1	349.0	356.2	364.9	374.9
12.5°	299.8	302.8	307.9	314.7	320.2	326.5	333.5	341.2	349.3	359.7	371.0
15°	284.0	287.6	293.8	297.1	305.5	313.0	319.5	330.5	340.9	351.6	364.6
17.5°	271.1	273.1	278.1	284.3	290.5	299.0	307.4	316.7	327.0	340.1	356.5
20°	262.2	263.9	269.4	275.9	282.6	290.3	297.9	307.1	318.7	332.6	350.3
22.5°	255.6	257.4	261.0	267.9	274.1	280.6	288.1	299.1	311.5	325.0	344.2
25°	246.0	247.1	249.5	255.1	260.5	267.8	274.4	284.8	297.5	313.4	332.6
27.5°	236.9	238.0	240.0	243.9	249.1	254.9	262.2	270.9	283.8	301.1	321.5
30°	231.4	231.6	233.5	237.2	241.6	246.4	253.0	263.0	275.2	292.7	314.1
32.5°	226.7	226.0	227.3	230.0	234.3	239.2	244.6	254.4	266.2	283.4	305.4
35°	218.7	218.3	217.8	220.1	223.9	227.5	232.3	239.7	253.0	269.1	292.2
37.5°	210.6	209.6	208.7	209.8	212.6	216.5	220.6	227.2	238.7	256.4	278.5
40°	204.5	203.7	203.2	202.8	205.4	209.1	212.2	218.5	229.2	246.0	267.8
42.5°	197.8	197.4	196.7	196.1	198.3	201.1	204.4	209.9	220.6	236.4	257.0
45°	187.1	186.8	186.4	186.0	187.4	189.9	192.5	196.5	205.8	221.1	239.7
47.5°	175.2	174.8	174.9	174.3	175.5	177.3	179.1	183.5	192.3	204.7	218.3
50°	166.7	166.4	166.4	166.4	166.8	168.9	170.6	173.9	182.0	194.3	204.1
52.5°	158.5	157.7	157.7	158.0	158.8	160.0	161.1	164.7	171.7	182.0	190.8
55°	145.8	144.3	143.9	144.3	144.9	146.0	147.1	150.0	156.1	163.7	168.9
57.5°	131.7	130.9	130.4	130.5	130.8	131.7	132.5	135.7	140.5	144.5	147.8
60°	121.8	122.2	120.5	120.9	120.9	121.6	122.9	124.9	129.0	131.7	135.1
62.5°	112.5	112.0	111.5	111.0	111.0	111.3	113.0	114.6	118.1	119.5	122.1
65°	98.0	98.0	96.9	97.3	97.4	96.2	97.0	98.9	101.2	101.7	104.1
67.5°	83.3	82.8	82.1	81.6	81.6	81.5	82.0	82.9	84.5	84.8	86.6
70°	73.3	72.9	72.7	72.2	71.5	72.3	71.8	72.7	73.7	73.8	74.9
72.5°	63.5	63.1	62.8	62.3	61.9	61.9	61.9	63.0	63.6	63.4	64.6
75°	49.7	49.3	48.9	48.0	48.0	47.5	47.6	48.3	49.1	48.6	49.7
77.5°	36.4	35.3	35.3	35.5	34.9	35.0	34.8	34.7	35.0	35.0	36.0
80°	28.0	26.8	27.1	26.9	26.8	26.5	26.2	26.4	26.5	26.8	27.3
82.5°	20.2	20.1	19.7	19.7	19.5	19.0	18.9	19.2	19.3	19.3	19.6
85°	10.3	9.7	10.1	10.0	10.1	10.0	9.4	9.4	9.7	9.6	10.0
87.5°	7.1	6.9	6.3	6.0	5.4	5.1	4.5	4.3	4.1	3.7	3.7
90°	19.6	19.0	16.7	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8
92.5°	30.9	30.3	29.1	27.7	26.5	25.2	23.9	22.7	21.5	20.4	19.2
95°	59.3	58.5	57.1	55.7	54.3	52.9	51.6	50.4	49.1	47.8	46.7
97.5°	92.4	91.6	90.5	89.5	88.5	87.5	86.5	85.6	84.7	83.8	82.9
100°	116.8	116.2	115.3	114.5	113.6	112.7	111.8	110.7	109.6	108.6	107.6
102.5°	144.6	144.1	142.9	141.7	140.6	139.4	138.6	137.9	137.3	136.7	136.0
105°	186.6	186.6	185.1	183.5	181.9	180.3	179.4	179.0	178.6	178.2	177.9
107.5°	231.0	230.4	229.8	229.2	228.5	227.9	227.5	227.3	227.0	226.9	226.6
110°	260.9	260.2	259.8	259.4	259.1	258.7	258.4	258.0	257.7	257.4	257.0



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	290.7	289.9	289.9	289.8	289.7	289.6	289.5	289.2	289.1	288.8	288.6
115°	337.1	336.8	337.2	337.5	337.9	338.3	338.2	337.6	337.2	336.6	336.0
117.5°	383.3	383.3	383.8	384.3	384.8	385.2	385.2	384.9	384.5	384.2	383.8
120°	414.2	414.4	415.3	416.1	417.0	417.9	417.8	416.8	415.7	414.6	413.6
122.5°	445.5	446.0	446.5	446.9	447.3	447.8	447.7	446.9	446.1	445.4	444.6
125°	491.9	492.7	493.0	493.4	493.7	494.1	493.9	493.5	492.9	492.4	491.9
127.5°	537.8	538.8	539.2	539.6	540.0	540.3	540.0	538.8	537.7	536.6	535.5
130°	567.8	568.5	569.1	569.6	570.1	570.7	570.2	568.8	567.4	566.0	564.6
132.5°	597.5	598.3	598.7	599.0	599.4	599.8	599.4	597.9	596.5	595.1	593.7
135°	641.4	642.1	642.3	642.5	642.6	642.8	642.4	641.3	640.2	639.2	638.2
137.5°	684.5	685.2	684.8	684.4	683.9	683.4	682.8	681.9	681.0	680.2	679.3
140°	712.3	712.5	712.3	712.1	711.9	711.8	711.2	710.3	709.5	708.6	707.7
142.5°	738.9	739.0	738.7	738.4	738.1	737.8	737.2	736.3	735.5	734.5	733.6
145°	777.9	778.1	777.6	777.1	776.5	776.0	775.5	775.2	774.8	774.5	774.1
147.5°	814.7	814.7	814.1	813.7	813.2	812.7	812.1	811.5	810.9	810.2	809.6
150°	837.4	837.4	837.1	836.7	836.4	836.0	835.7	835.3	835.0	834.6	834.2
152.5°	857.9	857.7	857.5	857.2	857.1	856.8	856.4	856.0	855.5	855.0	854.5
155°	888.0	887.2	887.1	886.8	886.7	886.5	886.5	886.5	886.5	886.5	886.5
157.5°	914.1	913.3	913.2	913.1	912.9	912.8	912.8	913.0	913.2	913.5	913.6
160°	930.0	929.2	929.2	929.2	929.2	929.2	929.3	929.7	930.0	930.3	930.7
162.5°	945.2	944.4	944.2	944.0	943.9	943.8	944.0	944.4	944.9	945.4	945.9
165°	964.2	963.1	963.1	963.1	963.1	963.1	963.5	963.9	964.5	965.0	965.5
167.5°	979.8	978.7	978.5	978.3	978.3	978.1	978.3	979.1	979.8	980.5	981.2
170°	988.1	986.9	986.9	986.9	986.9	986.9	987.2	987.9	988.6	989.4	990.1
172.5°	994.9	993.8	993.8	993.8	993.8	993.8	994.2	994.9	995.6	996.3	997.0
175°	1002.2	1001.1	1001.1	1001.1	1001.1	1001.1	1001.5	1002.2	1002.8	1003.5	1004.2
177.5°	1005.6	1004.7	1004.7	1004.7	1004.7	1004.7	1005.0	1005.6	1006.2	1006.7	1007.3
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	383.3	384.0	386.5	388.3	390.4	391.6	392.7	393.6	394.8	395.1	399.3
5°	385.0	388.6	395.1	399.9	405.8	412.3	416.7	418.7	424.1	428.5	437.4
7.5°	384.5	392.4	402.1	412.3	423.0	433.1	441.8	452.2	459.5	470.6	481.4
10°	384.0	394.6	407.1	420.0	435.1	449.2	461.8	475.8	487.4	502.7	515.8
12.5°	382.7	395.5	412.9	428.2	446.6	465.9	484.5	502.5	512.8	538.3	550.3
15°	379.5	394.6	416.4	439.6	464.9	487.7	511.4	530.2	560.6	583.0	597.2
17.5°	373.2	394.3	420.2	448.2	479.0	509.1	535.9	564.4	596.8	623.8	652.6
20°	370.2	393.5	422.2	453.3	485.2	519.4	549.8	584.1	619.3	645.9	682.9
22.5°	364.7	391.1	422.1	456.6	490.8	526.1	561.7	596.4	637.1	673.7	708.8
25°	355.8	385.3	417.5	456.1	496.1	531.5	574.2	620.1	662.5	709.6	744.7
27.5°	346.4	378.0	410.1	446.0	489.1	531.2	584.8	636.7	688.6	729.2	755.2
30°	339.2	369.9	403.1	439.3	481.9	531.9	591.8	648.5	699.1	734.0	748.5
32.5°	331.4	362.4	391.8	429.8	475.2	531.4	596.3	655.5	699.7	722.9	720.0
35°	319.1	345.1	373.8	410.3	463.7	528.1	598.9	656.1	683.2	678.2	640.6
37.5°	301.3	323.3	351.4	391.4	450.5	521.3	593.7	636.6	634.9	594.3	539.7
40°	290.3	309.0	336.0	378.1	440.1	516.9	585.6	613.5	589.9	533.1	467.9
42.5°	275.8	293.0	320.1	363.4	428.8	507.9	570.1	578.1	532.0	466.8	406.9
45°	253.4	268.5	296.6	341.3	411.7	488.3	532.3	512.5	450.3	382.9	337.4
47.5°	229.3	245.0	272.0	317.9	387.1	458.8	479.7	437.8	373.9	319.2	277.4
50°	214.0	229.2	255.6	301.9	370.4	434.6	443.3	389.0	330.3	282.3	248.0
52.5°	198.8	212.9	238.9	285.4	350.9	406.5	401.2	345.9	292.0	251.0	224.1
55°	175.9	189.3	214.0	257.6	317.3	361.3	342.0	289.2	244.5	212.8	192.3
57.5°	155.4	168.3	189.6	229.0	280.8	311.2	286.5	242.0	206.5	182.0	166.8
60°	141.6	153.0	173.3	209.8	254.8	277.9	253.6	214.3	184.3	164.8	151.1
62.5°	128.4	138.4	157.2	190.4	229.5	248.8	224.2	190.9	165.5	148.1	136.5
65°	108.5	117.6	134.2	160.0	192.1	205.0	183.8	156.9	137.1	124.2	116.5
67.5°	90.4	98.1	112.4	132.7	156.4	165.7	149.6	128.7	113.8	103.5	97.4
70°	78.3	84.9	96.2	113.7	135.1	142.3	127.1	110.0	99.1	90.8	85.1
72.5°	68.0	73.0	83.2	96.7	114.5	120.3	109.7	94.7	84.5	78.3	73.7
75°	51.9	55.9	62.6	73.4	85.8	89.1	81.2	71.8	65.0	60.5	57.0
77.5°	37.4	40.4	45.2	51.9	60.4	63.5	58.5	52.1	47.1	44.2	42.2
80°	28.2	30.7	34.7	40.2	45.4	47.1	44.1	39.3	35.8	34.1	32.5
82.5°	20.8	22.2	24.6	28.4	31.9	33.9	31.4	28.5	26.6	25.1	24.5
85°	10.5	11.2	12.4	13.9	16.1	16.8	15.8	15.1	14.0	13.1	13.1
87.5°	4.4	4.7	5.5	6.2	7.1	8.0	8.3	8.5	8.8	8.8	8.8
90°	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6	20.4
92.5°	20.4	21.5	22.7	23.9	25.2	26.5	27.7	29.1	30.3	30.9	31.5
95°	47.8	49.1	50.4	51.6	52.9	54.3	55.7	57.1	58.5	59.3	59.9
97.5°	83.8	84.7	85.6	86.5	87.5	88.5	89.5	90.5	91.6	92.4	93.2
100°	108.6	109.6	110.7	111.8	112.7	113.6	114.5	115.3	116.2	116.8	117.3
102.5°	136.7	137.3	137.9	138.6	139.4	140.6	141.7	142.9	144.1	144.6	145.1
105°	178.2	178.6	179.0	179.4	180.3	181.9	183.5	185.1	186.6	186.6	186.6
107.5°	226.9	227.0	227.3	227.5	227.9	228.5	229.2	229.8	230.4	231.0	231.6
110°	257.4	257.7	258.0	258.4	258.7	259.1	259.4	259.8	260.2	260.9	261.6



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	288.8	289.1	289.2	289.5	289.6	289.7	289.8	289.9	289.9	290.7	291.6
115°	336.6	337.2	337.6	338.2	338.3	337.9	337.5	337.2	336.8	337.1	337.2
117.5°	384.2	384.5	384.9	385.2	385.2	384.8	384.3	383.8	383.3	383.3	383.3
120°	414.6	415.7	416.8	417.8	417.9	417.0	416.1	415.3	414.4	414.2	414.0
122.5°	445.4	446.1	446.9	447.7	447.8	447.3	446.9	446.5	446.0	445.5	445.0
125°	492.4	492.9	493.5	493.9	494.1	493.7	493.4	493.0	492.7	491.9	491.2
127.5°	536.6	537.7	538.8	540.0	540.3	540.0	539.6	539.2	538.8	537.8	536.9
130°	566.0	567.4	568.8	570.2	570.7	570.1	569.6	569.1	568.5	567.8	567.1
132.5°	595.1	596.5	597.9	599.4	599.8	599.4	599.0	598.7	598.3	597.5	596.6
135°	639.2	640.2	641.3	642.4	642.8	642.6	642.5	642.3	642.1	641.4	640.7
137.5°	680.2	681.0	681.9	682.8	683.4	683.9	684.4	684.8	685.2	684.5	683.8
140°	708.6	709.5	710.3	711.2	711.8	711.9	712.1	712.3	712.5	712.3	712.1
142.5°	734.5	735.5	736.3	737.2	737.8	738.1	738.4	738.7	739.0	738.9	738.7
145°	774.5	774.8	775.2	775.5	776.0	776.5	777.1	777.6	778.1	777.9	777.8
147.5°	810.2	810.9	811.5	812.1	812.7	813.2	813.7	814.1	814.7	814.7	814.7
150°	834.6	835.0	835.3	835.7	836.0	836.4	836.7	837.1	837.4	837.4	837.4
152.5°	855.0	855.5	856.0	856.4	856.8	857.1	857.2	857.5	857.7	857.9	858.3
155°	886.5	886.5	886.5	886.5	886.5	886.7	886.8	887.1	887.2	888.0	888.7
157.5°	913.5	913.2	913.0	912.8	912.8	912.9	913.1	913.2	913.3	914.1	914.8
160°	930.3	930.0	929.7	929.3	929.2	929.2	929.2	929.2	929.2	930.0	930.9
162.5°	945.4	944.9	944.4	944.0	943.8	943.9	944.0	944.2	944.4	945.2	946.1
165°	965.0	964.5	963.9	963.5	963.1	963.1	963.1	963.1	963.1	964.2	965.3
167.5°	980.5	979.8	979.1	978.3	978.1	978.3	978.3	978.5	978.7	979.8	980.8
170°	989.4	988.6	987.9	987.2	986.9	986.9	986.9	986.9	986.9	988.1	989.4
172.5°	996.3	995.6	994.9	994.2	993.8	993.8	993.8	993.8	993.8	994.9	996.0
175°	1003.5	1002.8	1002.2	1001.5	1001.1	1001.1	1001.1	1001.1	1001.1	1002.2	1003.2
177.5°	1006.7	1006.2	1005.6	1005.0	1004.7	1004.7	1004.7	1004.7	1004.7	1005.6	1006.5
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	400.8	401.0	402.6	403.8	403.2	403.9	404.3
5°	437.9	444.6	448.1	450.7	450.8	451.1	452.5
7.5°	490.5	497.6	502.9	510.8	513.1	515.8	515.1
10°	528.9	539.5	548.5	553.3	558.5	566.0	559.9
12.5°	564.8	583.4	597.2	604.7	609.5	611.0	608.1
15°	624.0	648.3	661.4	661.1	677.6	684.8	673.6
17.5°	678.2	700.7	718.7	727.9	741.8	744.8	743.5
20°	711.5	736.0	750.0	765.9	773.1	779.5	780.6
22.5°	740.1	762.2	777.2	790.4	796.4	799.5	801.3
25°	769.6	787.0	796.0	800.6	802.2	801.8	799.5
27.5°	767.5	768.9	758.9	749.2	740.4	730.6	727.1
30°	747.6	732.1	704.4	688.7	665.7	647.4	654.8
32.5°	695.2	664.3	633.3	599.0	570.6	562.5	554.4
35°	593.3	539.1	507.3	470.4	455.7	440.9	430.7
37.5°	480.0	438.1	400.4	376.3	361.5	352.1	347.1
40°	415.0	377.2	346.2	326.6	315.4	304.9	303.4
42.5°	363.2	328.0	304.8	289.1	278.4	273.9	270.6
45°	297.5	273.0	257.3	246.2	239.0	236.2	232.5
47.5°	251.8	234.5	222.7	215.2	209.7	207.6	207.4
50°	226.2	211.8	203.2	197.3	193.1	192.3	189.3
52.5°	207.1	194.6	187.8	182.7	179.6	177.5	176.7
55°	179.7	171.4	165.3	162.4	160.0	158.0	158.0
57.5°	157.2	150.4	146.3	143.8	143.1	141.6	140.7
60°	143.4	137.5	134.4	132.1	130.6	130.9	129.2
62.5°	129.8	126.0	122.9	120.8	119.0	119.1	119.1
65°	110.5	107.6	105.4	104.6	103.5	102.3	102.6
67.5°	93.7	90.9	89.2	87.9	87.5	86.8	87.9
70°	81.6	79.5	78.3	77.2	76.8	76.9	77.9
72.5°	70.5	69.1	68.2	67.7	66.9	66.9	67.6
75°	55.4	54.3	53.6	53.0	52.8	52.8	52.8
77.5°	40.6	40.4	40.1	39.3	39.3	39.5	39.5
80°	32.1	31.5	31.4	31.0	30.4	30.1	31.0
82.5°	24.0	23.4	23.3	23.2	22.3	22.3	23.1
85°	12.9	12.4	12.5	12.4	12.4	12.2	12.2
87.5°	8.8	8.8	8.7	9.0	8.9	8.8	9.2
90°	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	32.1	32.6	32.8	32.6	32.4	32.2	31.9
95°	60.6	61.3	61.7	61.7	61.7	61.7	61.7
97.5°	94.0	94.8	95.1	95.1	95.1	95.0	94.9
100°	117.8	118.4	118.8	119.1	119.5	119.9	120.2
102.5°	145.7	146.2	146.4	146.3	146.2	146.2	146.2
105°	186.6	186.6	186.8	187.1	187.5	187.8	188.2
107.5°	232.1	232.7	232.8	232.7	232.4	232.2	232.0
110°	262.3	263.0	263.2	262.8	262.4	262.1	261.7



TEST NUMBER: P331893-927

CATALOG NUMBER: S123DIP-S340D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	292.4	293.3	293.7	293.6	293.5	293.4	293.3
115°	337.4	337.5	337.5	337.4	337.2	337.1	336.8
117.5°	383.3	383.3	382.9	382.5	382.0	381.5	381.0
120°	413.8	413.7	413.4	413.0	412.7	412.3	412.0
122.5°	444.7	444.2	443.7	443.2	442.7	442.2	441.7
125°	490.5	489.8	489.1	488.5	487.7	487.0	486.3
127.5°	535.9	534.9	534.0	533.2	532.3	531.6	530.8
130°	566.4	565.8	564.7	563.6	562.3	561.1	559.8
132.5°	595.8	594.9	594.1	593.1	592.2	591.2	590.3
135°	640.0	639.3	638.7	638.4	638.0	637.7	637.4
137.5°	683.1	682.3	681.6	681.0	680.2	679.6	679.0
140°	711.9	711.8	711.1	709.9	708.6	707.4	706.2
142.5°	738.6	738.3	737.8	736.8	735.9	734.9	734.0
145°	777.6	777.4	777.0	776.3	775.5	774.8	774.1
147.5°	814.7	814.7	814.1	813.1	812.0	811.0	809.9
150°	837.4	837.4	836.9	835.8	834.8	833.7	832.7
152.5°	858.5	858.8	858.5	857.5	856.7	855.7	854.8
155°	889.4	890.0	889.8	888.6	887.3	886.1	884.9
157.5°	915.5	916.3	916.2	915.2	914.2	913.2	912.2
160°	931.8	932.6	932.7	932.1	931.4	930.7	929.9
162.5°	947.0	947.8	947.7	946.6	945.5	944.4	943.3
165°	966.3	967.3	967.3	966.1	964.8	963.6	962.3
167.5°	981.9	983.0	983.0	981.9	980.8	979.8	978.7
170°	990.5	991.8	991.8	990.5	989.4	988.1	986.9
172.5°	997.1	998.1	998.1	996.9	995.7	994.4	993.2
175°	1004.2	1005.4	1005.2	1004.0	1002.7	1001.6	1000.3
177.5°	1007.3	1008.1	1008.1	1007.1	1006.1	1005.1	1004.1
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6

(END OF REPORT)