

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331908-927

Luminaire Tested: **S123DIP-S340D1195U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331908-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D1195U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4366.9 lumens  
Efficiency: N/A  
Efficacy: 103.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331908-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331908-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	67	60	55	68	60	54	50	47	43	39	35	32	30	23	22	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	21	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	28	24	22	19	17	15	11
6	59	47	39	34	52	42	36	31	33	28	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	31	25	21	25	20	17	19	16	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4621	4621	4621
5°	4643	4578	4611
10°	4611	4539	4568
15°	4558	4488	4496
20°	4495	4415	4418
25°	4410	4327	4318
30°	4318	4230	4197
35°	4221	4127	4075
40°	4118	4014	3953
45°	4007	3911	3815
50°	3893	3783	3677
55°	3748	3652	3539
60°	3599	3496	3384
65°	3469	3326	3224
70°	3276	3138	2996
75°	2994	2886	2766
80°	2703	2585	2566
85°	2371	2285	2186



TEST NUMBER: P331908-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.4	0.9
10°-20°	114.2	2.6
20°-30°	168.7	3.9
30°-40°	197.0	4.5
40°-50°	198.1	4.5
50°-60°	174.0	4.0
60°-70°	129.6	3.0
70°-80°	73.8	1.7
80°-90°	24.7	0.6
90°-100°	76.3	1.7
100°-110°	228.5	5.2
110°-120°	388.6	8.9
120°-130°	511.1	11.7
130°-140°	574.5	13.2
140°-150°	564.7	12.9
150°-160°	475.4	10.9
160°-170°	316.5	7.2
170°-180°	110.8	2.5
0°-30°	323.3	7.4
0°-40°	520.3	11.9
0°-60°	892.4	20.4
0°-90°	1120.5	25.7
90°-120°	693.4	15.9
90°-150°	2343.7	53.7
90°-180°	3246.0	74.3
0°-180°	4366.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	429	429	429	429	429	
5°	430	428	424	427	427	41
15°	409	407	403	405	404	115
25°	371	369	364	365	364	171
35°	321	319	314	312	310	201
45°	263	262	257	253	251	203
55°	200	199	195	191	189	179
65°	136	134	131	128	127	134
75°	72	70	69	68	66	77
85°	19	18	18	18	18	21
90°	1	10	22	26	28	4
95°	54	61	68	72	72	61
105°	207	209	217	217	219	222
115°	391	394	392	393	392	387
125°	572	575	574	570	566	510
135°	743	748	747	744	742	572
145°	901	903	906	905	901	563
155°	1032	1032	1033	1036	1030	475
165°	1124	1121	1121	1126	1120	317
175°	1169	1165	1165	1170	1164	111
180°	1172	1172	1172	1172	1172	



TEST NUMBER: P331908-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	430.8	430.5	430.2	430.0	429.7	429.2	428.5	427.8	427.1	426.4	427.0
5°	429.7	429.2	428.8	428.4	428.0	427.4	426.4	425.6	424.6	423.7	424.5
7.5°	425.5	425.0	424.6	424.2	423.8	423.1	422.2	421.3	420.3	419.4	420.1
10°	421.9	421.5	421.0	420.6	420.3	419.5	418.4	417.4	416.3	415.3	416.0
12.5°	417.2	416.8	416.5	416.1	415.8	415.1	414.2	413.1	412.1	411.1	411.7
15°	409.0	408.7	408.3	408.0	407.7	406.9	405.9	404.8	403.8	402.7	403.4
17.5°	399.4	399.0	398.6	398.2	397.8	397.0	395.9	394.9	393.8	392.8	393.2
20°	392.4	391.9	391.4	390.9	390.4	389.6	388.6	387.5	386.4	385.4	385.7
22.5°	384.4	383.9	383.4	382.9	382.5	381.7	380.6	379.5	378.4	377.4	377.6
25°	371.3	370.8	370.3	369.9	369.4	368.6	367.5	366.5	365.4	364.3	364.4
27.5°	357.4	356.9	356.4	355.9	355.5	354.7	353.6	352.4	351.3	350.1	350.1
30°	347.4	346.9	346.5	346.1	345.7	344.9	343.8	342.6	341.5	340.3	340.3
32.5°	337.3	336.8	336.2	335.6	335.2	334.4	333.5	332.6	331.8	330.9	330.4
35°	321.2	320.7	320.1	319.6	319.2	318.4	317.3	316.2	315.2	314.1	313.6
37.5°	304.6	304.0	303.3	302.7	302.1	301.3	300.2	299.0	298.0	296.9	296.4
40°	293.1	292.6	292.1	291.6	291.1	290.3	289.1	288.0	286.8	285.7	285.0
42.5°	281.5	281.0	280.4	279.9	279.3	278.5	277.3	276.2	275.0	273.9	273.2
45°	263.2	262.8	262.5	262.2	261.9	261.2	260.1	259.0	257.9	256.9	256.0
47.5°	244.9	244.5	244.0	243.5	243.0	242.3	241.3	240.3	239.3	238.3	237.3
50°	232.5	232.1	231.7	231.3	230.9	230.1	229.1	228.1	227.0	225.9	225.0
52.5°	219.5	219.3	219.0	218.7	218.4	217.7	216.6	215.5	214.4	213.2	212.5
55°	199.7	199.6	199.6	199.5	199.4	198.8	197.7	196.6	195.6	194.6	193.6
57.5°	180.8	180.5	180.2	180.0	179.7	179.1	178.2	177.4	176.6	175.7	174.9
60°	167.2	167.2	167.1	167.0	166.9	166.4	165.3	164.4	163.4	162.4	161.7
62.5°	155.1	154.9	154.7	154.5	154.2	153.7	152.7	151.7	150.7	149.7	149.0
65°	136.2	135.8	135.4	135.0	134.6	134.0	133.2	132.3	131.5	130.6	130.0
67.5°	116.2	115.8	115.5	115.1	114.8	114.2	113.7	113.0	112.4	111.8	111.2
70°	104.1	103.6	103.1	102.6	102.1	101.6	101.2	100.6	100.1	99.7	99.1
72.5°	91.4	91.0	90.7	90.3	89.9	89.5	89.0	88.4	87.9	87.3	86.7
75°	72.0	71.6	71.3	71.0	70.7	70.3	70.1	69.9	69.6	69.4	69.0
77.5°	54.7	54.6	54.4	54.3	54.0	53.8	53.6	53.2	52.9	52.6	52.4
80°	43.6	43.3	43.1	42.9	42.5	42.4	42.2	42.1	41.9	41.7	41.6
82.5°	32.6	32.6	32.6	32.5	32.4	32.4	32.3	32.3	32.3	32.2	32.1
85°	19.2	19.0	18.9	18.7	18.5	18.5	18.5	18.5	18.5	18.5	18.3
87.5°	7.8	8.1	8.3	8.5	8.7	9.0	9.5	10.0	10.5	10.9	11.0
90°	1.0	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9
92.5°	22.3	23.7	25.0	26.5	27.8	29.3	30.8	32.3	33.8	35.3	36.0
95°	54.3	55.8	57.2	58.6	60.0	61.6	63.2	64.8	66.5	68.1	68.9
97.5°	96.5	97.5	98.6	99.7	100.7	101.9	103.1	104.3	105.4	106.5	107.5
100°	125.2	126.4	127.6	128.9	130.1	131.2	132.2	133.2	134.3	135.3	135.9
102.5°	158.3	159.1	159.8	160.5	161.3	162.3	163.7	165.0	166.4	167.7	168.3
105°	207.1	207.5	207.9	208.3	208.7	209.8	211.7	213.6	215.4	217.2	217.2
107.5°	263.8	264.0	264.3	264.5	264.7	265.3	266.0	266.7	267.4	268.2	268.9
110°	299.1	299.5	299.9	300.4	300.8	301.2	301.6	302.0	302.4	302.9	303.6



TEST NUMBER: P331908-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.0	336.2	336.4	336.7	336.9	337.1	337.2	337.2	337.3	337.4	338.4
115°	391.2	391.8	392.4	393.0	393.6	393.7	393.3	392.9	392.5	392.1	392.3
117.5°	446.8	447.2	447.6	448.0	448.4	448.4	447.8	447.3	446.8	446.2	446.2
120°	481.4	482.6	483.9	485.1	486.3	486.4	485.4	484.3	483.3	482.3	482.1
122.5°	517.5	518.3	519.3	520.1	521.1	521.3	520.7	520.1	519.7	519.1	518.6
125°	572.5	573.1	573.7	574.3	575.0	575.0	574.6	574.3	573.9	573.5	572.6
127.5°	623.3	624.6	625.9	627.2	628.5	629.0	628.5	628.0	627.6	627.2	626.1
130°	657.2	658.8	660.4	662.1	663.7	664.2	663.6	663.0	662.4	661.8	661.0
132.5°	691.0	692.7	694.3	695.9	697.6	698.2	697.8	697.3	696.8	696.4	695.4
135°	742.8	744.0	745.2	746.5	747.7	748.2	748.0	747.8	747.6	747.3	746.6
137.5°	790.7	791.6	792.7	793.7	794.7	795.5	796.1	796.5	797.1	797.6	796.8
140°	823.8	824.8	825.9	826.9	827.8	828.5	828.7	828.9	829.1	829.3	829.1
142.5°	854.0	855.0	856.0	857.1	858.1	858.7	859.1	859.5	859.8	860.2	860.0
145°	901.1	901.5	901.9	902.3	902.7	903.2	903.9	904.4	905.1	905.7	905.5
147.5°	942.3	943.1	943.8	944.5	945.3	945.9	946.5	947.1	947.6	948.2	948.2
150°	971.1	971.5	971.8	972.2	972.7	973.1	973.5	973.9	974.3	974.7	974.7
152.5°	994.6	995.2	995.8	996.3	996.9	997.3	997.5	997.8	998.1	998.3	998.6
155°	1031.8	1031.8	1031.8	1031.8	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6
157.5°	1063.4	1063.2	1063.0	1062.7	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0
160°	1083.3	1082.9	1082.5	1082.1	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5
162.5°	1101.0	1100.4	1099.9	1099.3	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2
165°	1123.9	1123.2	1122.6	1122.0	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3
167.5°	1142.1	1141.2	1140.4	1139.6	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3
170°	1152.4	1151.5	1150.7	1149.9	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1
172.5°	1160.5	1159.7	1158.8	1158.0	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1
175°	1168.9	1168.2	1167.3	1166.5	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5
177.5°	1172.4	1171.8	1171.2	1170.4	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P331908-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	427.6	428.3	429.0	429.3	429.2	429.1	429.0	429.0
5°	425.4	426.2	427.1	427.4	427.2	427.1	426.8	426.7
7.5°	420.9	421.6	422.3	422.6	422.6	422.5	422.4	422.2
10°	416.8	417.5	418.2	418.5	418.4	418.2	418.0	417.9
12.5°	412.2	412.7	413.3	413.5	413.4	413.3	413.2	413.1
15°	404.0	404.6	405.4	405.4	404.9	404.4	403.9	403.5
17.5°	393.6	394.1	394.6	394.7	394.5	394.3	394.2	394.0
20°	386.0	386.3	386.7	386.7	386.4	386.2	386.0	385.7
22.5°	377.9	378.2	378.4	378.4	378.1	377.8	377.5	377.2
25°	364.5	364.6	364.6	364.6	364.3	364.1	363.8	363.6
27.5°	350.2	350.3	350.3	350.2	349.9	349.6	349.3	349.0
30°	340.3	340.3	340.3	340.0	339.5	338.9	338.3	337.7
32.5°	329.9	329.5	329.1	328.7	328.4	328.0	327.7	327.4
35°	313.1	312.7	312.1	311.7	311.3	310.9	310.5	310.1
37.5°	295.7	295.2	294.5	294.1	293.9	293.6	293.3	293.1
40°	284.4	283.8	283.0	282.6	282.3	281.9	281.6	281.3
42.5°	272.6	271.9	271.2	270.8	270.5	270.1	269.8	269.4
45°	254.9	254.0	252.9	252.3	251.8	251.4	251.0	250.6
47.5°	236.4	235.4	234.4	233.8	233.4	233.1	232.7	232.3
50°	224.1	223.2	222.3	221.6	221.1	220.6	220.1	219.6
52.5°	211.7	210.9	210.1	209.5	209.0	208.5	208.0	207.6
55°	192.7	191.8	190.9	190.3	189.9	189.4	189.0	188.6
57.5°	174.1	173.3	172.5	171.8	171.3	170.9	170.4	169.9
60°	161.0	160.2	159.5	158.9	158.4	158.0	157.6	157.2
62.5°	148.2	147.5	146.8	146.2	146.0	145.7	145.4	145.1
65°	129.4	128.7	128.0	127.6	127.4	127.1	126.8	126.6
67.5°	110.6	110.0	109.5	109.0	108.7	108.3	108.0	107.7
70°	98.5	97.9	97.4	96.9	96.5	96.1	95.6	95.2
72.5°	86.3	85.7	85.2	84.8	84.7	84.4	84.2	84.0
75°	68.6	68.1	67.7	67.4	67.2	66.9	66.7	66.5
77.5°	52.0	51.8	51.5	51.4	51.4	51.4	51.4	51.4
80°	41.5	41.4	41.4	41.4	41.4	41.4	41.4	41.4
82.5°	32.0	31.8	31.7	31.5	31.5	31.4	31.4	31.3
85°	18.1	18.0	17.8	17.7	17.7	17.7	17.7	17.7
87.5°	11.1	11.2	11.3	11.4	11.5	11.6	11.6	11.7
90°	23.8	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	36.7	37.3	37.9	38.2	37.9	37.7	37.4	37.2
95°	69.7	70.6	71.4	71.8	71.8	71.8	71.8	71.8
97.5°	108.4	109.4	110.4	110.7	110.7	110.6	110.5	110.4
100°	136.5	137.1	137.8	138.2	138.7	139.1	139.5	139.9
102.5°	168.9	169.5	170.2	170.4	170.3	170.2	170.2	170.1
105°	217.2	217.2	217.2	217.5	217.9	218.2	218.6	219.0
107.5°	269.5	270.2	270.8	271.0	270.8	270.5	270.3	270.1
110°	304.4	305.3	306.1	306.3	305.9	305.5	305.1	304.7





TEST NUMBER: P331908-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	339.4	340.4	341.4	341.8	341.7	341.7	341.6	341.5
115°	392.5	392.7	392.9	392.9	392.7	392.5	392.3	392.1
117.5°	446.2	446.1	446.1	445.8	445.2	444.6	444.0	443.5
120°	481.9	481.7	481.5	481.2	480.8	480.4	480.0	479.5
122.5°	518.1	517.5	517.0	516.4	515.9	515.3	514.7	514.1
125°	571.8	571.0	570.1	569.3	568.5	567.7	566.9	566.1
127.5°	624.9	623.8	622.6	621.5	620.6	619.6	618.7	617.8
130°	660.1	659.3	658.5	657.4	655.9	654.5	653.1	651.6
132.5°	694.4	693.5	692.4	691.4	690.3	689.2	688.1	687.0
135°	745.8	744.9	744.1	743.5	743.1	742.7	742.3	741.9
137.5°	795.9	795.0	794.2	793.4	792.6	791.9	791.1	790.3
140°	828.9	828.7	828.5	827.7	826.2	824.8	823.4	822.0
142.5°	859.8	859.6	859.4	858.7	857.6	856.5	855.5	854.4
145°	905.3	905.1	904.9	904.4	903.6	902.7	901.9	901.1
147.5°	948.2	948.2	948.2	947.6	946.3	945.2	943.9	942.7
150°	974.7	974.7	974.7	974.1	972.9	971.7	970.4	969.2
152.5°	998.9	999.3	999.6	999.3	998.1	997.1	996.0	995.0
155°	1034.4	1035.1	1036.0	1035.7	1034.3	1032.8	1031.4	1029.9
157.5°	1064.8	1065.6	1066.5	1066.4	1065.2	1064.1	1063.0	1061.8
160°	1083.5	1084.6	1085.6	1085.7	1084.9	1084.0	1083.2	1082.4
162.5°	1101.2	1102.2	1103.3	1103.1	1101.8	1100.5	1099.2	1097.9
165°	1123.6	1124.7	1126.0	1125.8	1124.4	1123.0	1121.6	1120.1
167.5°	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1
170°	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7
172.5°	1159.4	1160.6	1161.9	1161.8	1160.3	1158.9	1157.5	1156.0
175°	1167.7	1168.9	1170.1	1170.1	1168.6	1167.2	1165.8	1164.3
177.5°	1171.5	1172.4	1173.4	1173.3	1172.2	1171.0	1169.9	1168.8
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7

(END OF REPORT)