

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331935-930

Luminaire Tested: **S123DIP-S560D805U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331935-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4140.6 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331935-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331935-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38				
2	88	81	75	69	81	74	69	64	62	58	55	51	48	46	40	39	37	32				
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	36	33	31	27				
4	73	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23				
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24	20				
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21	18				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13				
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7854	7747	7800
10°	7803	7679	7726
15°	7710	7592	7608
20°	7605	7468	7475
25°	7462	7321	7305
30°	7305	7157	7102
35°	7139	6984	6893
40°	6968	6792	6687
45°	6779	6616	6454
50°	6589	6400	6223
55°	6341	6176	5988
60°	6090	5916	5726
65°	5871	5631	5456
70°	5542	5306	5070
75°	5065	4882	4675
80°	4568	4376	4339
85°	4001	3853	3705



TEST NUMBER: P331935-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	1.7
10°-20°	193.2	4.7
20°-30°	285.4	6.9
30°-40°	333.3	8.1
40°-50°	335.1	8.1
50°-60°	294.4	7.1
60°-70°	219.3	5.3
70°-80°	124.9	3.0
80°-90°	38.3	0.9
90°-100°	52.9	1.3
100°-110°	158.2	3.8
110°-120°	269.1	6.5
120°-130°	354.0	8.5
130°-140°	397.9	9.6
140°-150°	391.1	9.4
150°-160°	329.2	8.0
160°-170°	219.2	5.3
170°-180°	76.7	1.9
0°-30°	547.0	13.2
0°-40°	880.3	21.3
0°-60°	1509.9	36.5
0°-90°	1892.4	45.7
90°-120°	480.2	11.6
90°-150°	1623.1	39.2
90°-180°	2248.0	54.3
0°-180°	4140.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	727	724	717	723	722	69
15°	692	689	681	686	683	195
25°	628	624	616	617	615	289
35°	543	539	532	528	525	340
45°	445	442	435	427	424	344
55°	338	337	329	322	319	303
65°	230	227	221	216	214	227
75°	122	119	117	114	112	130
85°	32	31	31	30	30	36
90°	1	7	15	18	19	4
95°	38	42	47	50	50	42
105°	143	145	150	150	152	154
115°	271	273	272	272	272	268
125°	396	398	397	395	392	353
135°	514	518	518	515	514	396
145°	624	625	627	626	624	390
155°	714	715	715	717	713	329
165°	778	776	776	780	776	219
175°	810	807	807	810	806	77
180°	812	812	812	812	812	



TEST NUMBER: P331935-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	728.8	728.4	728.0	727.5	727.1	726.2	725.0	723.7	722.6	721.4	722.4
5°	726.9	726.3	725.5	724.9	724.1	723.1	721.5	720.0	718.5	717.0	718.4
7.5°	719.8	719.2	718.4	717.8	717.1	715.9	714.4	712.7	711.2	709.6	710.9
10°	713.9	713.1	712.5	711.8	711.1	709.8	708.0	706.2	704.4	702.6	703.8
12.5°	705.9	705.2	704.7	704.1	703.5	702.4	700.7	699.0	697.3	695.6	696.5
15°	691.9	691.5	690.9	690.3	689.7	688.6	686.8	685.0	683.1	681.3	682.5
17.5°	675.9	675.1	674.4	673.7	672.9	671.7	669.9	668.1	666.3	664.5	665.3
20°	663.9	663.1	662.2	661.4	660.6	659.3	657.5	655.7	653.8	652.0	652.6
22.5°	650.4	649.5	648.7	647.9	647.0	645.7	643.9	642.1	640.3	638.5	639.0
25°	628.3	627.5	626.6	625.8	624.9	623.6	621.8	620.0	618.2	616.4	616.5
27.5°	604.7	603.9	603.1	602.3	601.4	600.1	598.1	596.2	594.3	592.3	592.4
30°	587.7	587.0	586.3	585.6	584.9	583.6	581.6	579.7	577.8	575.8	575.8
32.5°	570.7	569.8	568.8	567.9	567.0	565.8	564.4	562.8	561.3	559.9	559.1
35°	543.3	542.5	541.7	540.9	540.1	538.7	536.9	535.1	533.3	531.5	530.7
37.5°	515.4	514.3	513.2	512.2	511.1	509.7	507.8	506.1	504.2	502.4	501.4
40°	495.9	495.0	494.2	493.4	492.5	491.1	489.2	487.3	485.3	483.4	482.2
42.5°	476.4	475.5	474.5	473.5	472.6	471.2	469.2	467.3	465.4	463.4	462.3
45°	445.3	444.7	444.2	443.6	443.0	441.9	440.1	438.3	436.5	434.6	433.0
47.5°	414.4	413.6	412.9	412.1	411.2	409.9	408.3	406.6	404.9	403.2	401.5
50°	393.5	392.7	392.1	391.3	390.7	389.5	387.6	385.8	384.0	382.2	380.7
52.5°	371.5	371.0	370.6	370.1	369.6	368.4	366.5	364.6	362.6	360.8	359.5
55°	337.9	337.7	337.6	337.5	337.3	336.3	334.5	332.7	330.9	329.1	327.6
57.5°	305.9	305.4	304.9	304.5	304.0	303.0	301.6	300.2	298.7	297.3	296.0
60°	282.9	282.7	282.7	282.5	282.3	281.4	279.8	278.1	276.5	274.8	273.5
62.5°	262.4	262.0	261.7	261.4	261.0	260.0	258.3	256.7	254.9	253.3	252.1
65°	230.5	229.8	229.1	228.4	227.7	226.7	225.3	223.9	222.5	221.1	220.0
67.5°	196.6	196.0	195.3	194.8	194.1	193.3	192.2	191.2	190.1	189.1	188.2
70°	176.1	175.3	174.5	173.7	172.8	171.9	171.1	170.3	169.4	168.6	167.6
72.5°	154.7	154.0	153.4	152.8	152.2	151.4	150.5	149.5	148.5	147.7	146.8
75°	121.8	121.2	120.7	120.1	119.6	119.1	118.6	118.2	117.8	117.4	116.8
77.5°	92.7	92.4	92.0	91.8	91.5	91.1	90.6	90.1	89.5	89.0	88.6
80°	73.7	73.3	72.9	72.5	72.0	71.7	71.4	71.1	70.8	70.6	70.4
82.5°	55.2	55.1	55.0	55.0	54.9	54.8	54.8	54.7	54.6	54.6	54.3
85°	32.4	32.2	32.0	31.6	31.4	31.2	31.2	31.2	31.2	31.2	31.0
87.5°	13.1	13.0	13.0	13.0	12.9	13.0	13.3	13.5	13.8	14.0	14.0
90°	0.7	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	15.4	16.4	17.4	18.3	19.2	20.3	21.4	22.4	23.4	24.5	24.9
95°	37.6	38.6	39.6	40.6	41.6	42.6	43.8	44.9	46.1	47.2	47.8
97.5°	66.8	67.5	68.2	69.0	69.8	70.5	71.3	72.2	73.0	73.8	74.4
100°	86.7	87.6	88.4	89.3	90.1	90.9	91.6	92.3	93.0	93.7	94.2
102.5°	109.7	110.1	110.6	111.2	111.7	112.4	113.3	114.3	115.2	116.2	116.6
105°	143.4	143.7	144.0	144.3	144.6	145.4	146.6	147.9	149.2	150.4	150.4
107.5°	182.7	182.9	183.0	183.2	183.4	183.7	184.3	184.7	185.2	185.7	186.2
110°	207.2	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.5	209.7	210.3



TEST NUMBER: P331935-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	232.7	232.8	233.0	233.2	233.3	233.4	233.5	233.6	233.7	233.7	234.4
115°	270.9	271.3	271.7	272.1	272.6	272.7	272.4	272.1	271.8	271.6	271.7
117.5°	309.4	309.7	310.0	310.2	310.5	310.5	310.1	309.7	309.4	309.0	309.0
120°	333.4	334.2	335.1	335.9	336.8	336.9	336.1	335.4	334.8	334.0	333.9
122.5°	358.4	359.0	359.6	360.2	360.9	361.0	360.6	360.3	359.9	359.5	359.1
125°	396.5	396.9	397.3	397.8	398.2	398.3	397.9	397.7	397.4	397.1	396.6
127.5°	431.7	432.6	433.5	434.4	435.3	435.6	435.3	435.0	434.6	434.3	433.6
130°	455.1	456.2	457.4	458.5	459.7	460.0	459.6	459.2	458.8	458.3	457.7
132.5°	478.6	479.7	480.9	482.0	483.1	483.6	483.2	482.9	482.6	482.2	481.6
135°	514.4	515.3	516.1	517.0	517.8	518.2	518.0	517.9	517.7	517.6	517.1
137.5°	547.6	548.3	548.9	549.7	550.4	550.9	551.3	551.6	552.0	552.4	551.8
140°	570.5	571.2	571.9	572.7	573.3	573.7	573.9	574.1	574.2	574.3	574.2
142.5°	591.4	592.2	592.8	593.5	594.3	594.8	595.0	595.3	595.5	595.7	595.6
145°	624.0	624.4	624.6	624.9	625.2	625.5	626.0	626.4	626.8	627.2	627.1
147.5°	652.6	653.1	653.6	654.1	654.7	655.1	655.5	655.9	656.3	656.7	656.7
150°	672.5	672.8	673.0	673.4	673.6	673.9	674.2	674.5	674.7	675.1	675.1
152.5°	688.8	689.2	689.6	690.0	690.4	690.7	690.9	691.0	691.2	691.4	691.6
155°	714.5	714.5	714.5	714.5	714.5	714.6	714.8	714.9	715.1	715.2	715.8
157.5°	736.5	736.3	736.1	736.0	735.8	735.8	735.9	736.1	736.1	736.2	736.9
160°	750.2	750.0	749.7	749.4	749.1	749.0	749.0	749.0	749.0	749.0	749.7
162.5°	762.5	762.1	761.7	761.3	760.9	760.8	760.9	761.0	761.1	761.2	761.9
165°	778.3	777.9	777.5	777.1	776.6	776.4	776.4	776.4	776.4	776.4	777.2
167.5°	790.9	790.4	789.8	789.2	788.6	788.5	788.6	788.6	788.8	788.9	789.8
170°	798.1	797.5	797.0	796.4	795.8	795.5	795.5	795.5	795.5	795.5	796.5
172.5°	803.6	803.2	802.6	802.0	801.4	801.1	801.1	801.1	801.1	801.1	802.0
175°	809.5	808.9	808.5	807.9	807.3	807.0	807.0	807.0	807.0	807.0	807.9
177.5°	812.0	811.5	811.1	810.6	810.2	809.9	809.9	809.9	809.9	809.9	810.6
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P331935-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	723.6	724.6	725.8	726.3	726.2	726.0	725.9	725.9
5°	719.7	721.1	722.5	723.1	722.8	722.5	722.3	721.9
7.5°	712.1	713.3	714.6	715.1	714.9	714.8	714.6	714.4
10°	705.1	706.4	707.6	708.1	707.8	707.5	707.3	706.9
12.5°	697.4	698.4	699.3	699.6	699.4	699.3	699.1	699.0
15°	683.6	684.7	685.8	685.9	685.1	684.3	683.5	682.7
17.5°	666.1	666.8	667.6	667.8	667.6	667.2	666.9	666.6
20°	653.1	653.7	654.2	654.3	653.9	653.5	653.1	652.6
22.5°	639.4	639.8	640.3	640.3	639.8	639.2	638.7	638.1
25°	616.7	616.9	616.9	616.9	616.4	616.0	615.6	615.1
27.5°	592.6	592.6	592.7	592.6	592.0	591.5	590.9	590.4
30°	575.8	575.8	575.8	575.4	574.4	573.4	572.4	571.4
32.5°	558.3	557.5	556.7	556.0	555.5	555.1	554.5	554.0
35°	529.8	529.0	528.2	527.4	526.7	526.0	525.3	524.6
37.5°	500.3	499.4	498.4	497.7	497.3	496.8	496.4	495.9
40°	481.2	480.0	479.0	478.1	477.5	477.0	476.5	475.9
42.5°	461.2	460.1	458.9	458.1	457.5	457.1	456.5	455.9
45°	431.4	429.7	428.0	426.8	426.2	425.4	424.8	424.0
47.5°	399.9	398.3	396.6	395.5	394.9	394.3	393.7	393.1
50°	379.2	377.6	376.1	375.0	374.1	373.2	372.4	371.6
52.5°	358.2	356.9	355.6	354.4	353.6	352.8	352.0	351.1
55°	326.0	324.6	323.0	321.9	321.2	320.5	319.8	319.1
57.5°	294.6	293.2	291.9	290.7	289.9	289.2	288.4	287.6
60°	272.3	271.1	269.8	268.8	268.2	267.4	266.8	266.0
62.5°	250.8	249.6	248.3	247.4	247.0	246.5	246.1	245.6
65°	218.8	217.8	216.6	215.9	215.5	215.1	214.7	214.2
67.5°	187.2	186.2	185.2	184.4	183.8	183.3	182.7	182.1
70°	166.6	165.8	164.8	163.9	163.2	162.5	161.8	161.1
72.5°	145.9	145.0	144.2	143.6	143.2	142.8	142.5	142.1
75°	116.0	115.4	114.6	114.1	113.7	113.2	112.8	112.4
77.5°	88.1	87.6	87.2	86.9	86.9	86.9	86.9	86.9
80°	70.3	70.1	70.0	70.0	70.0	70.0	70.0	70.0
82.5°	54.1	53.8	53.6	53.4	53.3	53.2	53.1	53.0
85°	30.7	30.4	30.1	30.0	30.0	30.0	30.0	30.0
87.5°	14.0	14.0	14.0	14.1	14.2	14.2	14.3	14.3
90°	16.5	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	25.4	25.8	26.3	26.4	26.3	26.1	25.9	25.8
95°	48.3	48.8	49.4	49.7	49.7	49.7	49.7	49.7
97.5°	75.1	75.7	76.4	76.7	76.6	76.6	76.6	76.5
100°	94.6	95.0	95.4	95.8	96.0	96.3	96.6	96.9
102.5°	117.0	117.4	117.8	118.1	118.0	117.9	117.9	117.8
105°	150.4	150.4	150.4	150.6	150.8	151.2	151.4	151.7
107.5°	186.6	187.1	187.6	187.7	187.5	187.4	187.2	187.0
110°	210.8	211.4	212.0	212.1	211.8	211.6	211.2	211.0



TEST NUMBER: P331935-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.1	235.7	236.4	236.7	236.7	236.6	236.5	236.5
115°	271.8	272.0	272.1	272.1	272.0	271.8	271.7	271.6
117.5°	309.0	308.9	308.9	308.7	308.3	307.9	307.5	307.1
120°	333.7	333.6	333.5	333.2	333.0	332.6	332.4	332.1
122.5°	358.8	358.4	358.1	357.7	357.3	356.9	356.4	356.0
125°	396.0	395.4	394.8	394.3	393.7	393.1	392.6	392.0
127.5°	432.8	431.9	431.2	430.5	429.8	429.2	428.5	427.9
130°	457.2	456.6	456.1	455.3	454.3	453.3	452.3	451.3
132.5°	480.9	480.2	479.6	478.8	478.1	477.3	476.5	475.8
135°	516.5	515.9	515.4	514.9	514.6	514.4	514.0	513.8
137.5°	551.2	550.7	550.0	549.4	548.9	548.4	547.9	547.3
140°	574.1	573.9	573.7	573.2	572.2	571.2	570.2	569.2
142.5°	595.5	595.3	595.2	594.8	593.9	593.2	592.4	591.7
145°	627.0	626.8	626.6	626.3	625.7	625.2	624.6	624.0
147.5°	656.7	656.7	656.7	656.2	655.4	654.5	653.7	652.9
150°	675.1	675.1	675.1	674.7	673.8	672.9	672.1	671.2
152.5°	691.8	692.0	692.3	692.0	691.3	690.6	689.8	689.1
155°	716.3	716.9	717.5	717.2	716.2	715.3	714.3	713.3
157.5°	737.4	738.0	738.6	738.5	737.8	736.9	736.1	735.3
160°	750.4	751.1	751.8	751.9	751.3	750.7	750.2	749.6
162.5°	762.6	763.4	764.1	763.9	763.0	762.1	761.2	760.3
165°	778.1	778.9	779.8	779.8	778.8	777.7	776.7	775.8
167.5°	790.7	791.5	792.4	792.4	791.5	790.7	789.8	788.9
170°	797.5	798.5	799.5	799.5	798.5	797.5	796.5	795.5
172.5°	802.9	803.8	804.6	804.6	803.6	802.6	801.6	800.6
175°	808.7	809.5	810.4	810.3	809.3	808.4	807.3	806.3
177.5°	811.3	812.0	812.6	812.6	811.8	811.0	810.2	809.4
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5

(END OF REPORT)