

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831601

Luminaire Tested: S123DIP-S775D1025U930-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831601
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U930-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5764.5 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 51.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	49	49	43				
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37				
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32				
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28				
5	70	59	51	45	64	55	48	43	47	42	38	40	36	33	33	31	28	25				
6	65	53	45	40	60	49	43	37	43	37	33	37	32	29	31	28	25	22				
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23	20				
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	26	23	21	18				
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	24	21	19	17				
10	49	37	30	26	45	35	29	24	31	26	22	27	23	20	23	20	17	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	19362	19362	19362	19362	19362
5°	24487	23112	19535	15743	14467
10°	24725	25473	19406	12550	10966
15°	18622	23650	19274	10628	9274
20°	12975	19137	19027	9294	8424
25°	9894	14718	18608	8551	7902
30°	8559	11692	17938	8025	7480
35°	7941	9872	17165	7645	7184
40°	7519	8855	16080	7284	7085
45°	7269	8196	14702	7001	7039
50°	7142	7675	13070	6745	7003
55°	6876	7293	11466	6501	7034
60°	6631	6882	9883	6271	6919
65°	6230	6495	8525	6026	6783
70°	5753	6002	7251	5621	6382
75°	5207	5382	6213	5224	5831
80°	4296	4711	4916	4556	4916
85°	3396	3816	3606	3866	3915

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 16786 cd/sqm



TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.1	3.0
10°-20°	423.1	7.3
20°-30°	500.9	8.7
30°-40°	503.7	8.7
40°-50°	462.1	8.0
50°-60°	381.4	6.6
60°-70°	269.8	4.7
70°-80°	144.0	2.5
80°-90°	38.7	0.7
90°-100°	66.7	1.2
100°-110°	201.9	3.5
110°-120°	343.6	6.0
120°-130°	452.1	7.8
130°-140°	508.1	8.8
140°-150°	499.6	8.7
150°-160°	420.6	7.3
160°-170°	280.0	4.9
170°-180°	98.0	1.7
0°-30°	1094.1	19.0
0°-40°	1597.8	27.7
0°-60°	2441.3	42.4
0°-90°	2893.9	50.2
90°-120°	612.2	10.6
90°-150°	2072.0	35.9
90°-180°	2871.0	49.8
0°-180°	5764.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1799	1799	1799	1799	1799	
5°	2266	2139	1808	1457	1339	216
15°	1671	2122	1730	954	832	462
25°	833	1239	1567	720	665	393
35°	604	751	1306	582	547	380
45°	478	538	966	460	462	370
55°	366	389	611	346	375	328
65°	245	255	335	237	266	243
75°	125	129	149	126	140	132
85°	28	31	29	31	32	31
90°	24	20	1	20	24	13
95°	64	60	48	60	64	64
105°	194	192	183	192	194	205
115°	347	347	346	347	347	343
125°	500	507	506	507	500	448
135°	656	661	657	661	656	505
145°	797	801	797	801	797	498
155°	911	913	912	913	911	420
165°	990	991	994	991	990	279
175°	1030	1030	1034	1030	1030	98
180°	1036	1036	1036	1036	1036	



TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8
2.5°	2027.6	2025.5	2023.4	2012.9	2002.5	1997.5	1992.5	1977.5	1962.4	1945.7	1929.1
5°	2266.3	2272.1	2278.0	2271.3	2264.6	2244.2	2223.7	2196.6	2169.5	2139.0	2108.5
7.5°	2376.5	2379.8	2383.1	2379.0	2374.8	2369.4	2363.9	2339.7	2315.5	2284.2	2252.9
10°	2262.1	2269.6	2277.1	2293.4	2309.7	2328.1	2346.4	2343.1	2339.7	2330.6	2321.4
12.5°	2010.9	2020.0	2029.2	2061.8	2094.3	2136.1	2177.8	2213.7	2249.6	2274.6	2299.7
15°	1671.1	1696.6	1722.0	1751.7	1781.3	1842.7	1904.0	1979.6	2055.1	2122.3	2189.5
17.5°	1376.5	1386.1	1395.7	1427.4	1459.1	1536.3	1613.5	1700.8	1788.0	1899.4	2010.9
20°	1132.7	1141.5	1150.3	1192.0	1233.7	1294.2	1354.8	1452.8	1550.9	1670.7	1790.5
22.5°	951.6	965.4	979.1	1002.5	1025.9	1083.9	1141.9	1229.1	1316.4	1448.7	1581.0
25°	833.1	843.1	853.1	867.3	881.5	927.8	974.1	1045.9	1117.7	1239.2	1360.6
27.5°	752.1	756.3	760.4	774.6	788.8	818.9	848.9	910.7	972.5	1075.5	1178.6
30°	688.6	691.6	694.5	707.0	719.5	740.0	760.4	805.1	849.8	940.7	1031.7
32.5°	644.4	646.5	648.6	658.2	667.8	682.4	697.0	729.6	762.1	837.2	912.4
35°	604.3	605.6	606.8	613.9	621.0	631.9	642.7	667.4	692.0	751.3	810.5
37.5°	569.3	571.0	572.6	576.8	581.0	590.6	600.2	619.8	639.4	684.9	730.4
40°	535.1	538.0	540.9	543.8	546.7	554.7	562.6	577.6	592.7	630.2	667.8
42.5°	505.8	508.8	511.7	512.9	514.2	518.8	523.4	537.1	550.9	578.9	606.8
45°	477.5	478.7	480.0	481.2	482.5	486.2	490.0	502.1	514.2	538.4	562.6
47.5°	451.6	451.6	451.6	452.4	453.3	456.6	459.9	468.7	477.5	496.2	515.0
50°	426.5	426.5	426.5	425.3	424.0	426.1	428.2	434.9	441.6	458.3	475.0
52.5°	396.5	396.5	396.5	396.9	397.3	397.3	397.3	403.2	409.0	424.0	439.1
55°	366.4	368.1	369.8	368.5	367.3	368.1	368.9	372.7	376.5	388.6	400.7
57.5°	336.4	337.2	338.1	337.6	337.2	337.6	338.1	341.4	344.7	353.9	363.1
60°	308.0	308.0	308.0	307.2	306.3	307.2	308.0	309.7	311.4	319.7	328.0
62.5°	276.3	276.7	277.1	277.5	278.0	277.1	276.3	278.4	280.5	286.7	293.0
65°	244.6	245.0	245.4	246.7	247.9	247.1	246.2	248.3	250.4	255.0	259.6
67.5°	216.2	215.4	214.5	214.9	215.4	216.6	217.9	218.3	218.7	223.7	228.7
70°	182.8	183.6	184.5	184.1	183.6	184.1	184.5	185.7	187.0	190.7	194.5
72.5°	152.8	153.2	153.6	153.6	153.6	154.4	155.3	156.5	157.8	159.9	161.9
75°	125.2	125.2	125.2	126.0	126.9	127.3	127.7	127.7	127.7	129.4	131.1
77.5°	95.2	97.2	99.3	98.9	98.5	99.3	100.2	101.4	102.7	103.5	104.3
80°	69.3	69.3	69.3	69.7	70.1	71.4	72.6	73.5	74.3	76.0	77.6
82.5°	44.2	44.7	45.1	46.3	47.6	48.4	49.2	50.5	51.8	51.8	51.8
85°	27.5	26.7	25.9	26.7	27.5	28.4	29.2	29.6	30.1	30.9	31.7
87.5°	13.4	13.4	13.4	13.4	13.4	13.8	14.2	14.2	14.2	14.2	14.2
90°	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0	20.3	19.5	17.2
92.5°	35.0	35.4	35.7	36.1	36.4	36.4	35.8	35.3	34.7	34.2	33.1
95°	63.5	63.5	63.5	63.5	63.5	63.1	62.4	61.7	60.9	60.2	58.8
97.5°	91.1	91.3	91.5	91.7	91.9	91.5	90.6	89.7	88.8	87.9	86.8
100°	123.7	123.3	123.0	122.6	122.3	121.8	121.3	120.7	120.2	119.6	118.7
102.5°	157.1	157.3	157.4	157.6	157.8	157.6	157.1	156.5	156.0	155.4	154.2
105°	193.7	193.3	193.0	192.6	192.2	192.1	192.1	192.1	192.1	192.1	190.4
107.5°	231.1	231.3	231.5	231.7	231.9	231.7	231.1	230.6	230.0	229.5	228.8
110°	269.4	269.7	270.1	270.5	270.8	270.6	269.9	269.2	268.5	267.8	267.4



TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	310.1	310.1	310.1	310.1	310.1	309.6	308.7	307.8	306.9	306.0	306.0
115°	346.7	346.9	347.1	347.2	347.4	347.4	347.2	347.1	346.9	346.7	347.1
117.5°	384.1	384.7	385.2	385.8	386.3	386.6	386.6	386.6	386.6	386.6	386.9
120°	424.0	424.4	424.7	425.1	425.5	425.7	425.9	426.1	426.3	426.5	427.4
122.5°	462.3	462.8	463.3	463.9	464.4	465.0	465.5	466.1	466.6	467.1	467.5
125°	500.5	501.2	502.0	502.7	503.4	504.1	504.9	505.6	506.3	507.0	507.4
127.5°	538.8	539.5	540.2	540.9	541.7	542.6	543.6	544.7	545.8	546.9	547.3
130°	576.2	577.5	578.7	580.0	581.3	582.3	583.0	583.7	584.4	585.1	585.7
132.5°	615.3	616.2	617.1	618.0	618.9	619.8	620.7	621.6	622.5	623.4	623.8
135°	656.0	656.3	656.7	657.0	657.4	657.9	658.7	659.4	660.1	660.8	661.0
137.5°	691.8	692.3	692.8	693.4	693.9	694.7	695.6	696.5	697.4	698.3	697.7
140°	726.8	728.0	729.3	730.6	731.8	732.5	732.7	732.9	733.1	733.3	733.1
142.5°	762.6	763.5	764.4	765.3	766.2	766.7	766.9	767.1	767.3	767.4	767.1
145°	796.7	797.5	798.2	798.9	799.6	800.1	800.3	800.5	800.6	800.8	800.3
147.5°	827.7	828.8	829.8	830.9	832.0	832.6	832.6	832.6	832.6	832.6	832.0
150°	857.0	858.1	859.1	860.2	861.3	861.9	861.9	861.9	861.9	861.9	861.5
152.5°	885.5	886.4	887.3	888.2	889.1	889.3	889.0	888.6	888.3	887.9	887.7
155°	910.7	912.0	913.2	914.5	915.7	916.0	915.3	914.6	913.8	913.1	912.9
157.5°	934.3	935.4	936.5	937.5	938.6	938.8	938.1	937.4	936.6	935.9	935.7
160°	957.1	957.8	958.5	959.2	960.0	959.9	959.0	958.1	957.2	956.3	956.3
162.5°	974.2	975.4	976.7	978.0	979.2	979.4	978.5	977.6	976.7	975.8	975.6
165°	990.4	991.7	993.0	994.2	995.5	995.6	994.5	993.4	992.3	991.3	991.3
167.5°	1005.1	1006.2	1007.3	1008.3	1009.4	1009.4	1008.3	1007.3	1006.2	1005.1	1004.9
170°	1015.7	1016.9	1018.2	1019.5	1020.7	1020.7	1019.5	1018.2	1016.9	1015.7	1015.7
172.5°	1023.8	1025.1	1026.3	1027.6	1028.9	1029.0	1027.9	1026.8	1025.7	1024.6	1024.6
175°	1029.5	1030.8	1032.0	1033.3	1034.6	1034.7	1033.6	1032.5	1031.4	1030.3	1030.3
177.5°	1032.8	1034.0	1035.3	1036.6	1037.8	1037.9	1036.8	1035.7	1034.7	1033.6	1033.6
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8
2.5°	1924.0	1919.0	1900.7	1882.3	1861.4	1840.6	1825.1	1809.7	1786.7	1763.8	1745.0
5°	2085.1	2061.8	2023.0	1984.1	1931.6	1879.0	1843.5	1808.0	1760.4	1712.9	1674.9
7.5°	2212.9	2172.8	2118.5	2064.3	1995.4	1926.5	1861.4	1796.3	1723.7	1651.1	1591.8
10°	2294.2	2267.1	2204.5	2141.9	2049.7	1957.4	1866.4	1775.5	1682.0	1588.5	1510.0
12.5°	2302.2	2304.7	2247.1	2189.5	2085.1	1980.8	1870.2	1759.6	1641.9	1524.2	1432.8
15°	2232.5	2275.5	2243.7	2212.0	2106.8	2001.7	1865.6	1729.6	1593.9	1458.3	1352.7
17.5°	2103.1	2195.3	2199.9	2204.5	2099.3	1994.2	1843.5	1692.8	1539.2	1385.6	1274.6
20°	1926.5	2062.6	2109.4	2156.1	2070.5	1985.0	1823.0	1661.1	1489.2	1317.2	1200.8
22.5°	1746.2	1911.5	1997.1	2082.6	2019.2	1955.8	1783.4	1611.0	1429.5	1247.9	1129.8
25°	1540.9	1721.2	1852.7	1984.1	1945.3	1906.5	1736.6	1566.8	1373.5	1180.3	1059.7
27.5°	1361.9	1545.1	1703.7	1862.3	1853.9	1845.6	1677.0	1508.4	1310.5	1112.7	996.2
30°	1202.4	1373.1	1550.5	1727.9	1748.3	1768.8	1606.0	1443.2	1245.0	1046.7	934.5
32.5°	1061.4	1210.4	1400.7	1591.0	1631.1	1671.1	1524.2	1377.3	1181.1	985.0	876.9
35°	945.7	1081.0	1271.3	1461.6	1511.7	1561.8	1434.1	1306.3	1115.2	924.0	821.0
37.5°	843.5	956.6	1142.3	1328.1	1389.4	1450.8	1336.4	1222.0	1043.0	863.9	769.2
40°	758.8	849.8	1020.5	1191.2	1262.1	1333.1	1238.7	1144.4	974.5	804.7	717.4
42.5°	687.8	768.8	923.6	1078.5	1146.5	1214.5	1134.8	1055.1	904.0	752.9	673.2
45°	627.3	692.0	832.6	973.3	1038.0	1102.7	1034.2	965.8	832.6	699.5	625.2
47.5°	570.5	626.0	746.2	866.4	924.0	981.6	928.2	874.8	762.1	649.4	582.2
50°	519.6	564.3	669.5	774.6	824.7	874.8	827.6	780.5	687.8	595.2	536.7
52.5°	475.4	511.7	599.8	687.8	730.8	773.8	733.3	692.8	619.4	545.9	495.0
55°	431.6	462.4	538.8	615.2	644.4	673.6	642.3	611.0	551.8	492.5	449.5
57.5°	390.7	418.2	480.8	543.4	565.9	588.5	560.1	531.7	487.1	442.4	406.5
60°	350.6	373.1	425.3	477.5	491.2	505.0	482.1	459.1	427.8	396.5	364.4
62.5°	313.4	333.9	372.7	411.5	420.7	429.9	412.4	394.8	371.0	347.2	322.2
65°	275.0	290.5	322.2	353.9	359.8	365.6	350.2	334.7	316.8	298.8	280.5
67.5°	239.6	250.4	276.3	302.2	302.6	303.0	290.5	278.0	267.9	257.9	243.3
70°	204.9	215.4	232.5	249.6	250.0	250.4	240.4	230.4	222.9	215.4	204.5
72.5°	169.4	177.0	189.9	202.8	202.0	201.2	194.9	188.6	182.8	177.0	169.0
75°	137.3	143.6	152.3	161.1	158.6	156.1	152.8	149.4	144.4	139.4	134.4
77.5°	108.1	111.9	116.9	121.9	120.2	118.5	115.6	112.7	108.9	105.2	103.1
80°	79.3	81.0	84.3	87.6	86.8	86.0	82.6	79.3	78.5	77.6	74.7
82.5°	53.8	55.9	56.8	57.6	57.2	56.8	54.3	51.8	50.9	50.1	49.7
85°	32.1	32.6	33.0	33.4	32.1	30.9	30.1	29.2	29.2	29.2	28.8
87.5°	14.6	15.0	15.0	15.0	14.6	14.2	13.4	12.5	12.9	13.4	13.4
90°	14.8	12.5	10.1	8.0	6.2	4.4	2.6	0.8	2.6	4.4	6.2
92.5°	32.0	30.9	29.8	28.8	27.7	26.6	25.5	24.4	25.5	26.6	27.7
95°	57.3	55.9	54.4	53.1	51.8	50.5	49.3	48.0	49.3	50.5	51.8
97.5°	85.7	84.6	83.6	82.6	81.7	80.8	79.8	78.9	79.8	80.8	81.7
100°	117.8	116.9	116.0	115.0	113.9	112.9	111.8	110.7	111.8	112.9	113.9
102.5°	152.9	151.6	150.4	149.5	148.9	148.4	147.8	147.3	147.8	148.4	148.9
105°	188.8	187.2	185.6	184.6	184.2	183.8	183.5	183.1	183.5	183.8	184.2
107.5°	228.1	227.3	226.6	226.2	226.0	225.8	225.6	225.4	225.6	225.8	226.0
110°	267.0	266.7	266.3	265.9	265.6	265.2	264.9	264.5	264.9	265.2	265.6



TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	306.0	306.0	306.0	305.9	305.7	305.6	305.4	305.2	305.4	305.6	305.7
115°	347.4	347.8	348.1	348.1	347.5	347.0	346.4	345.9	346.4	347.0	347.5
117.5°	387.3	387.7	388.0	388.1	387.9	387.7	387.6	387.4	387.6	387.7	387.9
120°	428.3	429.2	430.1	430.0	428.9	427.8	426.7	425.6	426.7	427.8	428.9
122.5°	467.9	468.2	468.6	468.4	467.7	467.0	466.2	465.5	466.2	467.0	467.7
125°	507.7	508.1	508.5	508.4	507.8	507.3	506.7	506.2	506.7	507.3	507.8
127.5°	547.6	548.0	548.3	548.0	546.9	545.8	544.7	543.6	544.7	545.8	546.9
130°	586.2	586.8	587.3	586.9	585.4	584.0	582.5	581.1	582.5	584.0	585.4
132.5°	624.1	624.5	624.8	624.3	622.9	621.4	620.0	618.5	620.0	621.4	622.9
135°	661.2	661.4	661.6	661.1	660.0	658.9	657.9	656.8	657.9	658.9	660.0
137.5°	697.2	696.6	696.1	695.4	694.5	693.6	692.7	691.8	692.7	693.6	694.5
140°	732.9	732.7	732.5	732.0	731.1	730.2	729.3	728.4	729.3	730.2	731.1
142.5°	766.7	766.4	766.0	765.4	764.5	763.6	762.7	761.8	762.7	763.6	764.5
145°	799.7	799.2	798.6	798.2	797.8	797.5	797.1	796.7	797.1	797.5	797.8
147.5°	831.5	830.9	830.4	829.8	829.0	828.3	827.6	826.9	827.6	828.3	829.0
150°	861.1	860.8	860.4	860.0	859.7	859.3	859.0	858.6	859.0	859.3	859.7
152.5°	887.5	887.4	887.2	886.8	886.3	885.7	885.2	884.6	885.2	885.7	886.3
155°	912.8	912.6	912.4	912.3	912.3	912.3	912.3	912.3	912.3	912.3	912.3
157.5°	935.6	935.4	935.2	935.2	935.4	935.6	935.7	935.9	935.7	935.6	935.4
160°	956.3	956.3	956.3	956.4	956.8	957.2	957.5	957.9	957.5	957.2	956.8
162.5°	975.4	975.2	975.1	975.2	975.8	976.3	976.9	977.4	976.9	976.3	975.8
165°	991.3	991.3	991.3	991.5	992.1	992.6	993.2	993.7	993.2	992.6	992.1
167.5°	1004.7	1004.5	1004.4	1004.6	1005.4	1006.1	1006.8	1007.5	1006.8	1006.1	1005.4
170°	1015.7	1015.7	1015.7	1016.0	1016.8	1017.5	1018.2	1018.9	1018.2	1017.5	1016.8
172.5°	1024.6	1024.6	1024.6	1025.0	1025.7	1026.4	1027.2	1027.9	1027.2	1026.4	1025.7
175°	1030.3	1030.3	1030.3	1030.7	1031.4	1032.1	1032.9	1033.6	1032.9	1032.1	1031.4
177.5°	1033.6	1033.6	1033.6	1033.9	1034.7	1035.4	1036.1	1036.8	1036.1	1035.4	1034.7
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8
2.5°	1726.2	1709.9	1693.7	1681.1	1668.6	1647.3	1626.0	1621.0	1616.0	1608.9	1601.8
5°	1636.9	1596.8	1556.8	1520.9	1485.0	1457.0	1429.1	1410.7	1392.3	1379.0	1365.6
7.5°	1532.6	1472.5	1412.4	1369.8	1327.2	1286.7	1246.2	1233.3	1220.4	1202.8	1185.3
10°	1431.6	1365.2	1298.8	1243.3	1187.8	1148.2	1108.5	1092.7	1076.8	1054.7	1032.6
12.5°	1341.4	1268.8	1196.2	1140.2	1084.3	1045.9	1007.5	984.6	961.6	949.1	936.6
15°	1247.1	1169.5	1091.8	1040.1	988.3	953.7	919.0	899.0	879.0	866.9	854.8
17.5°	1163.6	1086.8	1010.0	960.4	910.7	879.0	847.2	829.7	812.2	803.0	793.8
20°	1084.3	1009.2	934.1	885.6	837.2	811.4	785.5	774.2	762.9	755.4	747.9
22.5°	1011.7	937.8	863.9	822.6	781.3	760.4	739.6	731.6	723.7	717.4	711.2
25°	939.1	873.1	807.2	772.1	737.1	720.0	702.8	694.9	687.0	680.7	674.5
27.5°	879.8	816.8	753.8	723.7	693.7	680.3	666.9	660.7	654.4	648.6	642.7
30°	822.2	765.9	709.5	683.6	657.8	645.7	633.6	627.3	621.0	615.6	610.2
32.5°	768.8	720.4	672.0	648.2	624.4	614.4	604.3	596.8	589.3	585.1	581.0
35°	717.9	674.5	631.1	611.4	591.8	581.8	571.8	565.5	559.3	555.9	552.6
37.5°	674.5	635.6	596.8	578.0	559.3	549.7	540.1	534.6	529.2	528.0	526.7
40°	630.2	596.8	563.4	545.1	526.7	518.4	510.0	506.7	503.3	502.5	501.7
42.5°	593.5	560.9	528.4	511.7	495.0	487.9	480.8	479.1	477.5	478.7	480.0
45°	550.9	523.8	496.7	481.2	465.8	459.9	454.1	452.8	451.6	454.1	456.6
47.5°	515.0	490.0	464.9	450.3	435.7	431.6	427.4	427.0	426.5	429.9	433.2
50°	478.3	454.1	429.9	418.2	406.5	402.8	399.0	400.3	401.5	406.9	412.4
52.5°	444.1	421.5	399.0	388.1	377.3	374.8	372.3	375.2	378.1	384.0	389.8
55°	406.5	386.1	365.6	357.3	348.9	346.4	343.9	349.8	355.6	361.0	366.4
57.5°	370.6	352.7	334.7	327.2	319.7	319.3	318.9	324.3	329.7	335.6	341.4
60°	332.2	317.2	302.2	296.3	290.5	291.3	292.2	298.4	304.7	309.3	313.9
62.5°	297.2	284.6	272.1	266.7	261.3	263.4	265.4	271.7	278.0	283.4	288.8
65°	262.1	251.7	241.2	237.5	233.7	236.6	239.6	245.0	250.4	254.2	257.9
67.5°	228.7	220.0	211.2	208.3	205.3	208.3	211.2	216.6	222.0	225.8	229.5
70°	193.7	186.6	179.5	177.4	175.3	178.6	182.0	186.6	191.2	194.9	198.7
72.5°	161.1	155.7	150.3	149.8	149.4	152.3	155.3	159.9	164.4	166.9	169.4
75°	129.4	126.5	123.5	123.1	122.7	125.6	128.5	131.1	133.6	135.6	137.7
77.5°	101.0	98.5	96.0	96.4	96.8	98.9	101.0	103.5	106.0	107.3	108.5
80°	71.8	71.0	70.1	71.0	71.8	73.5	75.1	76.8	78.5	79.3	80.1
82.5°	49.2	48.4	47.6	48.8	50.1	51.3	52.6	53.8	55.1	55.5	55.9
85°	28.4	29.6	30.9	30.9	30.9	31.3	31.7	32.1	32.6	32.1	31.7
87.5°	13.4	13.8	14.2	14.2	14.2	14.6	15.0	15.0	15.0	14.6	14.2
90°	8.0	10.1	12.5	14.8	17.2	19.5	20.3	21.0	21.7	22.4	23.0
92.5°	28.8	29.8	30.9	32.0	33.1	34.2	34.7	35.3	35.8	36.4	36.4
95°	53.1	54.4	55.9	57.3	58.8	60.2	60.9	61.7	62.4	63.1	63.5
97.5°	82.6	83.6	84.6	85.7	86.8	87.9	88.8	89.7	90.6	91.5	91.9
100°	115.0	116.0	116.9	117.8	118.7	119.6	120.2	120.7	121.3	121.8	122.3
102.5°	149.5	150.4	151.6	152.9	154.2	155.4	156.0	156.5	157.1	157.6	157.8
105°	184.6	185.6	187.2	188.8	190.4	192.1	192.1	192.1	192.1	192.1	192.2
107.5°	226.2	226.6	227.3	228.1	228.8	229.5	230.0	230.6	231.1	231.7	231.9
110°	265.9	266.3	266.7	267.0	267.4	267.8	268.5	269.2	269.9	270.6	270.8



TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	305.9	306.0	306.0	306.0	306.0	306.0	306.9	307.8	308.7	309.6	310.1
115°	348.1	348.1	347.8	347.4	347.1	346.7	346.9	347.1	347.2	347.4	347.4
117.5°	388.1	388.0	387.7	387.3	386.9	386.6	386.6	386.6	386.6	386.6	386.3
120°	430.0	430.1	429.2	428.3	427.4	426.5	426.3	426.1	425.9	425.7	425.5
122.5°	468.4	468.6	468.2	467.9	467.5	467.1	466.6	466.1	465.5	465.0	464.4
125°	508.4	508.5	508.1	507.7	507.4	507.0	506.3	505.6	504.9	504.1	503.4
127.5°	548.0	548.3	548.0	547.6	547.3	546.9	545.8	544.7	543.6	542.6	541.7
130°	586.9	587.3	586.8	586.2	585.7	585.1	584.4	583.7	583.0	582.3	581.3
132.5°	624.3	624.8	624.5	624.1	623.8	623.4	622.5	621.6	620.7	619.8	618.9
135°	661.1	661.6	661.4	661.2	661.0	660.8	660.1	659.4	658.7	657.9	657.4
137.5°	695.4	696.1	696.6	697.2	697.7	698.3	697.4	696.5	695.6	694.7	693.9
140°	732.0	732.5	732.7	732.9	733.1	733.3	733.1	732.9	732.7	732.5	731.8
142.5°	765.4	766.0	766.4	766.7	767.1	767.4	767.3	767.1	766.9	766.7	766.2
145°	798.2	798.6	799.2	799.7	800.3	800.8	800.6	800.5	800.3	800.1	799.6
147.5°	829.8	830.4	830.9	831.5	832.0	832.6	832.6	832.6	832.6	832.6	832.0
150°	860.0	860.4	860.8	861.1	861.5	861.9	861.9	861.9	861.9	861.9	861.3
152.5°	886.8	887.2	887.4	887.5	887.7	887.9	888.3	888.6	889.0	889.3	889.1
155°	912.3	912.4	912.6	912.8	912.9	913.1	913.8	914.6	915.3	916.0	915.7
157.5°	935.2	935.2	935.4	935.6	935.7	935.9	936.6	937.4	938.1	938.8	938.6
160°	956.4	956.3	956.3	956.3	956.3	956.3	957.2	958.1	959.0	959.9	960.0
162.5°	975.2	975.1	975.2	975.4	975.6	975.8	976.7	977.6	978.5	979.4	979.2
165°	991.5	991.3	991.3	991.3	991.3	991.3	992.3	993.4	994.5	995.6	995.5
167.5°	1004.6	1004.4	1004.5	1004.7	1004.9	1005.1	1006.2	1007.3	1008.3	1009.4	1009.4
170°	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9	1018.2	1019.5	1020.7	1020.7
172.5°	1025.0	1024.6	1024.6	1024.6	1024.6	1024.6	1025.7	1026.8	1027.9	1029.0	1028.9
175°	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4	1032.5	1033.6	1034.7	1034.6
177.5°	1033.9	1033.6	1033.6	1033.6	1033.6	1033.6	1034.7	1035.7	1036.8	1037.9	1037.8
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1798.8	1798.8	1798.8	1798.8
2.5°	1598.9	1596.0	1584.3	1572.6
5°	1355.6	1345.6	1342.2	1338.9
7.5°	1184.5	1183.6	1166.1	1148.6
10°	1033.8	1035.1	1019.2	1003.3
12.5°	926.1	915.7	914.4	913.2
15°	845.2	835.6	833.9	832.2
17.5°	788.0	782.1	780.5	778.8
20°	744.6	741.2	738.3	735.4
22.5°	707.0	702.8	700.3	697.8
25°	670.7	666.9	666.1	665.3
27.5°	638.1	633.6	633.6	633.6
30°	607.3	604.3	603.1	601.8
32.5°	578.5	576.0	576.0	576.0
35°	551.3	550.1	548.4	546.7
37.5°	526.7	526.7	525.9	525.0
40°	502.9	504.2	504.2	504.2
42.5°	481.2	482.5	482.5	482.5
45°	458.7	460.8	461.6	462.4
47.5°	436.6	439.9	440.7	441.6
50°	414.9	417.4	417.8	418.2
52.5°	392.7	395.7	397.7	399.8
55°	369.4	372.3	373.5	374.8
57.5°	344.3	347.2	347.7	348.1
60°	316.8	319.7	320.5	321.4
62.5°	290.5	292.2	293.0	293.8
65°	260.4	262.9	264.6	266.3
67.5°	231.6	233.7	233.7	233.7
70°	199.5	200.3	201.6	202.8
72.5°	169.9	170.3	170.3	170.3
75°	138.6	139.4	139.8	140.2
77.5°	108.9	109.3	109.3	109.3
80°	79.7	79.3	79.3	79.3
82.5°	54.7	53.4	53.4	53.4
85°	31.3	30.9	31.3	31.7
87.5°	14.2	14.2	14.2	14.2
90°	23.3	23.7	24.1	24.4
92.5°	36.1	35.7	35.4	35.0
95°	63.5	63.5	63.5	63.5
97.5°	91.7	91.5	91.3	91.1
100°	122.6	123.0	123.3	123.7
102.5°	157.6	157.4	157.3	157.1
105°	192.6	193.0	193.3	193.7
107.5°	231.7	231.5	231.3	231.1
110°	270.5	270.1	269.7	269.4



TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	310.1	310.1	310.1	310.1
115°	347.2	347.1	346.9	346.7
117.5°	385.8	385.2	384.7	384.1
120°	425.1	424.7	424.4	424.0
122.5°	463.9	463.3	462.8	462.3
125°	502.7	502.0	501.2	500.5
127.5°	540.9	540.2	539.5	538.8
130°	580.0	578.7	577.5	576.2
132.5°	618.0	617.1	616.2	615.3
135°	657.0	656.7	656.3	656.0
137.5°	693.4	692.8	692.3	691.8
140°	730.6	729.3	728.0	726.8
142.5°	765.3	764.4	763.5	762.6
145°	798.9	798.2	797.5	796.7
147.5°	830.9	829.8	828.8	827.7
150°	860.2	859.1	858.1	857.0
152.5°	888.2	887.3	886.4	885.5
155°	914.5	913.2	912.0	910.7
157.5°	937.5	936.5	935.4	934.3
160°	959.2	958.5	957.8	957.1
162.5°	978.0	976.7	975.4	974.2
165°	994.2	993.0	991.7	990.4
167.5°	1008.3	1007.3	1006.2	1005.1
170°	1019.5	1018.2	1016.9	1015.7
172.5°	1027.6	1026.3	1025.1	1023.8
175°	1033.3	1032.0	1030.8	1029.5
177.5°	1036.6	1035.3	1034.0	1032.8
180°	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P831601

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.88	14.71	14.84	15.68	16.95	16.12	16.95	17.08	17.92	19.19
	3H	15.53	16.27	16.50	17.25	18.54	17.54	18.28	18.51	19.26	20.56
	4H	16.10	16.80	17.09	17.79	19.09	17.99	18.69	18.98	19.68	20.98
	6H	16.47	17.12	17.47	18.11	19.42	18.26	18.91	19.26	19.90	21.21
	8H	16.57	17.18	17.57	18.19	19.50	18.33	18.94	19.33	19.95	21.26
	12H	16.61	17.19	17.62	18.19	19.53	18.34	18.93	19.35	19.93	21.26
4H	2H	14.45	15.15	15.45	16.14	17.44	16.28	16.98	17.27	17.96	19.27
	3H	16.28	16.86	17.28	17.88	19.19	17.89	18.48	18.90	19.49	20.81
	4H	16.98	17.51	17.99	18.52	19.86	18.48	19.01	19.49	20.02	21.36
	6H	17.45	17.91	18.47	18.94	20.27	18.88	19.34	19.90	20.37	21.71
	8H	17.59	18.01	18.61	19.04	20.39	18.99	19.42	20.01	20.44	21.79
	12H	17.65	18.04	18.69	19.08	20.43	19.03	19.42	20.07	20.46	21.81
8H	4H	17.24	17.67	18.26	18.69	20.04	18.58	19.01	19.60	20.03	21.38
	6H	17.83	18.18	18.87	19.25	20.59	19.08	19.43	20.13	20.50	21.85
	8H	18.03	18.34	19.09	19.40	20.76	19.26	19.57	20.31	20.62	21.99
	12H	18.16	18.43	19.21	19.47	20.89	19.36	19.63	20.42	20.68	22.09
12H	4H	17.24	17.62	18.28	18.66	20.02	18.55	18.94	19.59	19.98	21.33
	6H	17.88	18.19	18.93	19.24	20.61	19.09	19.41	20.15	20.46	21.82
	8H	18.11	18.38	19.17	19.43	20.84	19.29	19.57	20.35	20.61	22.02