

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331891-927

Luminaire Tested: **S123DIP-S340D805U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331891-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D805U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3421.3 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331891-927

CATALOG NUMBER: S123DIP-S340D805U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331891-927

CATALOG NUMBER: S123DIP-S340D805U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	82	84	81	78	75	64	62	60	49	48	47	35	35	34	27
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	28	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4621	4621	4621
5°	4643	4578	4611
10°	4611	4539	4568
15°	4558	4488	4496
20°	4495	4415	4418
25°	4410	4327	4318
30°	4318	4230	4197
35°	4221	4127	4075
40°	4118	4014	3953
45°	4007	3911	3815
50°	3893	3783	3677
55°	3748	3652	3539
60°	3599	3496	3384
65°	3469	3326	3224
70°	3276	3138	2996
75°	2994	2886	2766
80°	2703	2585	2566
85°	2371	2285	2186



TEST NUMBER: P331891-927

CATALOG NUMBER: S123DIP-S340D805U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	1.2
10°-20°	114.2	3.3
20°-30°	168.7	4.9
30°-40°	197.0	5.8
40°-50°	198.1	5.8
50°-60°	174.0	5.1
60°-70°	129.6	3.8
70°-80°	73.8	2.2
80°-90°	23.6	0.7
90°-100°	170.3	5.0
100°-110°	482.1	14.1
110°-120°	474.3	13.9
120°-130°	378.3	11.1
130°-140°	298.3	8.7
140°-150°	222.6	6.5
150°-160°	155.2	4.5
160°-170°	91.2	2.7
170°-180°	29.7	0.9
0°-30°	323.3	9.4
0°-40°	520.3	15.2
0°-60°	892.4	26.1
0°-90°	1119.4	32.7
90°-120°	1126.7	32.9
90°-150°	2025.9	59.2
90°-180°	2302.0	67.3
0°-180°	3421.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	429	429	429	429	429	
5°	430	428	424	427	427	41
15°	409	407	403	405	404	115
25°	371	369	364	365	364	171
35°	321	319	314	312	310	201
45°	263	262	257	253	251	203
55°	200	199	195	191	189	179
65°	136	134	131	128	127	134
75°	72	70	69	68	66	77
85°	19	18	18	18	18	21
90°	1	7	15	17	18	2
95°	21	68	367	107	72	23
105°	72	106	498	871	788	76
115°	127	158	381	835	958	126
125°	176	208	356	644	756	157
135°	207	247	350	530	612	160
145°	236	270	346	435	479	148
155°	268	289	335	381	397	123
165°	293	301	321	340	346	83
175°	305	306	308	312	312	29
180°	306	306	306	306	306	



TEST NUMBER: P331891-927

CATALOG NUMBER: S123DIP-S340D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	430.8	430.5	430.2	430.0	429.7	429.2	428.5	427.8	427.1	426.4	427.0
5°	429.7	429.2	428.8	428.4	428.0	427.4	426.4	425.6	424.6	423.7	424.5
7.5°	425.5	425.0	424.6	424.2	423.8	423.1	422.2	421.3	420.3	419.4	420.1
10°	421.9	421.5	421.0	420.6	420.3	419.5	418.4	417.4	416.3	415.3	416.0
12.5°	417.2	416.8	416.5	416.1	415.8	415.1	414.2	413.1	412.1	411.1	411.7
15°	409.0	408.7	408.3	408.0	407.7	406.9	405.9	404.8	403.8	402.7	403.4
17.5°	399.4	399.0	398.6	398.2	397.8	397.0	395.9	394.9	393.8	392.8	393.2
20°	392.4	391.9	391.4	390.9	390.4	389.6	388.6	387.5	386.4	385.4	385.7
22.5°	384.4	383.9	383.4	382.9	382.5	381.7	380.6	379.5	378.4	377.4	377.6
25°	371.3	370.8	370.3	369.9	369.4	368.6	367.5	366.5	365.4	364.3	364.4
27.5°	357.4	356.9	356.4	355.9	355.5	354.7	353.6	352.4	351.3	350.1	350.1
30°	347.4	346.9	346.5	346.1	345.7	344.9	343.8	342.6	341.5	340.3	340.3
32.5°	337.3	336.8	336.2	335.6	335.2	334.4	333.5	332.6	331.8	330.9	330.4
35°	321.2	320.7	320.1	319.6	319.2	318.4	317.3	316.2	315.2	314.1	313.6
37.5°	304.6	304.0	303.3	302.7	302.1	301.3	300.2	299.0	298.0	296.9	296.4
40°	293.1	292.6	292.1	291.6	291.1	290.3	289.1	288.0	286.8	285.7	285.0
42.5°	281.5	281.0	280.4	279.9	279.3	278.5	277.3	276.2	275.0	273.9	273.2
45°	263.2	262.8	262.5	262.2	261.9	261.2	260.1	259.0	257.9	256.9	256.0
47.5°	244.9	244.5	244.0	243.5	243.0	242.3	241.3	240.3	239.3	238.3	237.3
50°	232.5	232.1	231.7	231.3	230.9	230.1	229.1	228.1	227.0	225.9	225.0
52.5°	219.5	219.3	219.0	218.7	218.4	217.7	216.6	215.5	214.4	213.2	212.5
55°	199.7	199.6	199.6	199.5	199.4	198.8	197.7	196.6	195.6	194.6	193.6
57.5°	180.8	180.5	180.2	180.0	179.7	179.1	178.2	177.4	176.6	175.7	174.9
60°	167.2	167.2	167.1	167.0	166.9	166.4	165.3	164.4	163.4	162.4	161.7
62.5°	155.1	154.9	154.7	154.5	154.2	153.7	152.7	151.7	150.7	149.7	149.0
65°	136.2	135.8	135.4	135.0	134.6	134.0	133.2	132.3	131.5	130.6	130.0
67.5°	116.2	115.8	115.5	115.1	114.8	114.2	113.7	113.0	112.4	111.8	111.2
70°	104.1	103.6	103.1	102.6	102.1	101.6	101.2	100.6	100.1	99.7	99.1
72.5°	91.4	91.0	90.7	90.3	89.9	89.5	89.0	88.4	87.9	87.3	86.7
75°	72.0	71.6	71.3	71.0	70.7	70.3	70.1	69.9	69.6	69.4	69.0
77.5°	54.7	54.6	54.4	54.3	54.0	53.8	53.6	53.2	52.9	52.6	52.4
80°	43.6	43.3	43.1	42.9	42.5	42.4	42.2	42.1	41.9	41.7	41.6
82.5°	32.6	32.6	32.6	32.5	32.4	32.4	32.3	32.3	32.3	32.2	32.1
85°	19.2	19.0	18.9	18.7	18.5	18.5	18.5	18.5	18.5	18.5	18.3
87.5°	7.9	8.0	8.0	8.2	8.2	8.4	8.7	9.0	9.3	9.6	9.4
90°	1.3	2.5	3.7	5.5	6.8	8.1	9.9	11.8	13.6	15.4	14.9
92.5°	7.7	11.4	16.6	21.5	26.6	35.8	52.0	78.7	104.8	95.2	71.9
95°	21.1	22.9	29.7	40.2	56.3	80.5	133.2	225.5	327.0	367.3	297.9
97.5°	35.9	36.5	41.9	51.0	66.9	93.0	143.3	247.4	416.7	569.2	609.0
100°	45.9	46.4	50.8	59.5	74.3	98.5	141.8	233.5	396.4	586.5	708.5
102.5°	56.2	57.4	61.2	69.4	82.8	104.9	143.8	221.6	366.6	554.3	713.5
105°	71.9	73.7	77.4	84.8	96.6	115.8	149.2	213.0	330.1	498.0	675.7
107.5°	88.4	90.3	93.9	101.2	112.3	130.1	159.4	212.5	306.8	448.1	609.6
110°	100.4	102.2	105.3	112.1	122.6	140.0	167.9	214.9	297.9	419.9	567.9



TEST NUMBER: P331891-927

CATALOG NUMBER: S123DIP-S340D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.2	113.1	116.2	123.0	133.6	150.4	176.3	219.8	292.9	401.1	531.8
115°	127.0	129.4	133.2	139.3	149.9	166.6	190.1	227.9	291.1	380.9	488.1
117.5°	142.7	145.5	148.6	154.3	166.1	181.6	204.9	238.6	292.2	369.0	461.7
120°	153.6	155.4	158.5	164.8	176.5	192.0	214.3	246.5	294.2	363.5	447.8
122.5°	163.0	164.9	167.9	174.7	185.9	202.4	224.2	253.9	297.6	360.1	436.4
125°	176.5	177.8	181.5	188.3	200.0	216.7	238.4	265.7	302.9	355.5	421.8
127.5°	186.8	188.6	193.2	200.2	213.2	229.9	250.8	275.4	308.8	353.3	408.9
130°	193.2	195.1	200.7	208.1	221.1	237.8	258.3	281.8	312.8	351.8	402.0
132.5°	198.2	200.6	206.6	215.6	228.5	244.8	264.7	287.7	315.8	351.3	395.5
135°	206.8	209.4	216.2	225.5	238.4	255.2	274.3	295.4	320.2	350.5	387.1
137.5°	215.0	217.6	224.3	234.2	247.1	262.6	281.1	301.1	323.2	349.2	379.8
140°	220.5	223.6	229.8	239.7	252.1	267.5	285.5	304.1	325.2	348.7	375.3
142.5°	226.4	229.0	235.8	244.6	257.1	271.5	289.0	307.0	326.6	347.7	371.4
145°	236.0	237.8	243.4	252.7	263.2	277.5	293.6	310.3	327.6	346.2	366.1
147.5°	245.7	246.8	252.2	260.2	270.4	282.6	297.3	312.3	327.6	343.9	360.8
150°	252.1	252.7	257.6	265.7	274.3	285.5	299.8	312.8	327.6	341.9	357.4
152.5°	258.5	258.6	263.6	270.7	278.3	289.0	301.3	313.8	326.1	339.4	353.4
155°	268.2	268.2	271.9	278.1	284.9	293.6	304.1	314.0	324.6	335.1	347.5
157.5°	275.8	276.3	279.3	284.8	290.6	297.3	305.7	314.7	322.4	331.2	340.8
160°	281.8	281.8	284.3	289.2	293.6	299.8	307.2	314.7	321.5	328.3	336.3
162.5°	286.3	286.3	288.3	292.2	296.0	301.3	307.7	314.1	319.5	325.3	331.8
165°	292.9	292.3	293.6	296.7	299.1	303.5	308.4	312.8	316.5	320.8	325.7
167.5°	298.0	297.3	297.9	300.2	302.0	304.8	308.3	311.8	313.5	316.4	320.0
170°	301.0	299.8	300.4	302.2	303.5	304.8	307.8	310.3	311.6	313.4	316.5
172.5°	303.0	302.2	302.4	303.7	304.4	305.2	307.8	309.8	310.1	310.9	313.0
175°	305.3	304.8	304.1	305.3	305.3	305.9	307.2	308.4	307.8	307.8	309.0
177.5°	306.4	305.9	305.5	305.9	305.9	305.9	306.4	307.4	306.4	305.9	306.4
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P331891-927

CATALOG NUMBER: S123DIP-S340D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	427.6	428.3	429.0	429.3	429.2	429.1	429.0	429.0
5°	425.4	426.2	427.1	427.4	427.2	427.1	426.8	426.7
7.5°	420.9	421.6	422.3	422.6	422.6	422.5	422.4	422.2
10°	416.8	417.5	418.2	418.5	418.4	418.2	418.0	417.9
12.5°	412.2	412.7	413.3	413.5	413.4	413.3	413.2	413.1
15°	404.0	404.6	405.4	405.4	404.9	404.4	403.9	403.5
17.5°	393.6	394.1	394.6	394.7	394.5	394.3	394.2	394.0
20°	386.0	386.3	386.7	386.7	386.4	386.2	386.0	385.7
22.5°	377.9	378.2	378.4	378.4	378.1	377.8	377.5	377.2
25°	364.5	364.6	364.6	364.6	364.3	364.1	363.8	363.6
27.5°	350.2	350.3	350.3	350.2	349.9	349.6	349.3	349.0
30°	340.3	340.3	340.3	340.0	339.5	338.9	338.3	337.7
32.5°	329.9	329.5	329.1	328.7	328.4	328.0	327.7	327.4
35°	313.1	312.7	312.1	311.7	311.3	310.9	310.5	310.1
37.5°	295.7	295.2	294.5	294.1	293.9	293.6	293.3	293.1
40°	284.4	283.8	283.0	282.6	282.3	281.9	281.6	281.3
42.5°	272.6	271.9	271.2	270.8	270.5	270.1	269.8	269.4
45°	254.9	254.0	252.9	252.3	251.8	251.4	251.0	250.6
47.5°	236.4	235.4	234.4	233.8	233.4	233.1	232.7	232.3
50°	224.1	223.2	222.3	221.6	221.1	220.6	220.1	219.6
52.5°	211.7	210.9	210.1	209.5	209.0	208.5	208.0	207.6
55°	192.7	191.8	190.9	190.3	189.9	189.4	189.0	188.6
57.5°	174.1	173.3	172.5	171.8	171.3	170.9	170.4	169.9
60°	161.0	160.2	159.5	158.9	158.4	158.0	157.6	157.2
62.5°	148.2	147.5	146.8	146.2	146.0	145.7	145.4	145.1
65°	129.4	128.7	128.0	127.6	127.4	127.1	126.8	126.6
67.5°	110.6	110.0	109.5	109.0	108.7	108.3	108.0	107.7
70°	98.5	97.9	97.4	96.9	96.5	96.1	95.6	95.2
72.5°	86.3	85.7	85.2	84.8	84.7	84.4	84.2	84.0
75°	68.6	68.1	67.7	67.4	67.2	66.9	66.7	66.5
77.5°	52.0	51.8	51.5	51.4	51.4	51.4	51.4	51.4
80°	41.5	41.4	41.4	41.4	41.4	41.4	41.4	41.4
82.5°	32.0	31.8	31.7	31.5	31.5	31.4	31.4	31.3
85°	18.1	18.0	17.8	17.7	17.7	17.7	17.7	17.7
87.5°	9.4	9.5	9.6	9.8	9.7	9.8	9.9	9.8
90°	15.4	16.1	16.7	18.0	17.3	18.0	18.6	18.0
92.5°	52.1	41.4	36.5	33.4	32.2	30.3	31.0	29.9
95°	223.0	151.1	118.3	96.0	84.2	78.7	74.3	71.9
97.5°	555.8	445.2	365.3	291.2	245.5	217.6	200.9	195.6
100°	730.2	680.0	607.6	519.6	457.1	411.9	387.7	388.3
102.5°	788.1	786.6	744.3	688.6	639.9	604.1	583.9	569.7
105°	805.2	867.0	878.8	862.8	834.2	810.7	790.9	787.8
107.5°	756.4	856.9	911.2	933.2	933.7	925.8	919.1	913.4
110°	709.8	823.7	901.7	945.2	962.4	967.4	966.1	965.0



TEST NUMBER: P331891-927

CATALOG NUMBER: S123DIP-S340D805U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	663.7	780.1	867.6	923.3	955.1	970.4	975.1	975.3
115°	602.6	710.3	801.5	868.9	915.4	942.6	955.1	958.1
117.5°	558.4	651.4	733.2	801.7	850.1	881.3	899.1	903.4
120°	535.1	618.7	693.1	755.6	804.5	839.2	854.1	857.8
122.5°	516.8	592.5	661.3	719.5	762.9	794.1	810.5	815.2
125°	492.3	559.9	619.3	668.9	708.5	735.8	751.2	755.6
127.5°	471.1	531.2	584.9	630.0	665.3	688.6	702.6	706.5
130°	457.7	513.4	563.6	605.7	638.6	660.8	673.8	678.8
132.5°	445.3	496.6	543.3	583.4	614.3	636.6	648.1	651.6
135°	428.6	472.5	512.8	548.1	578.5	597.1	608.2	612.5
137.5°	413.4	449.4	484.1	514.7	540.2	559.0	568.5	571.3
140°	404.4	436.0	465.7	492.3	515.9	533.2	543.2	542.6
142.5°	396.0	423.1	448.9	472.1	492.1	507.5	516.4	515.8
145°	385.9	406.3	426.1	444.1	459.5	472.5	477.5	478.7
147.5°	377.6	393.8	409.8	422.6	434.3	443.1	447.8	448.3
150°	371.6	385.9	398.9	410.6	419.9	426.7	430.5	430.5
152.5°	366.1	378.4	389.9	399.7	407.0	413.4	415.6	415.6
155°	358.0	367.9	377.2	384.6	390.1	395.1	396.4	397.0
157.5°	349.3	357.6	364.8	370.6	375.4	379.1	380.2	380.0
160°	344.4	351.2	357.4	361.7	366.1	369.7	369.7	369.2
162.5°	338.4	344.2	349.9	353.8	356.6	359.8	359.8	359.3
165°	330.7	334.5	338.8	341.9	344.4	346.8	346.2	346.2
167.5°	324.0	326.9	329.4	331.6	332.7	334.5	333.8	333.8
170°	319.6	321.5	323.9	325.2	325.7	327.0	326.4	326.4
172.5°	315.6	317.0	318.9	319.7	319.8	321.1	320.0	319.5
175°	310.3	310.9	312.1	312.1	312.1	312.8	312.1	311.6
177.5°	307.0	307.4	307.9	307.9	307.4	307.9	307.0	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9

(END OF REPORT)