

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331952-927

Luminaire Tested: **S123DIP-S560D1195U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331952-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1195U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5617.7 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331952-927

CATALOG NUMBER: S123DIP-S560D1195U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331952-927

CATALOG NUMBER: S123DIP-S560D1195U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	82	84	81	78	75	64	62	60	49	48	47	35	35	34	27
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7597	7597	7597
5°	7632	7527	7580
10°	7581	7462	7508
15°	7492	7377	7392
20°	7389	7257	7263
25°	7251	7114	7099
30°	7097	6954	6901
35°	6937	6786	6699
40°	6770	6600	6497
45°	6587	6428	6272
50°	6402	6219	6047
55°	6161	6001	5819
60°	5918	5748	5565
65°	5703	5471	5300
70°	5385	5155	4925
75°	4924	4745	4541
80°	4438	4252	4215
85°	3890	3742	3606



TEST NUMBER: P331952-927

CATALOG NUMBER: S123DIP-S560D1195U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	1.2
10°-20°	187.7	3.3
20°-30°	277.3	4.9
30°-40°	323.9	5.8
40°-50°	325.6	5.8
50°-60°	286.0	5.1
60°-70°	213.1	3.8
70°-80°	121.4	2.2
80°-90°	38.3	0.7
90°-100°	45.0	0.8
100°-110°	214.7	3.8
110°-120°	515.6	9.2
120°-130°	656.6	11.7
130°-140°	701.5	12.5
140°-150°	656.0	11.7
150°-160°	529.2	9.4
160°-170°	341.5	6.1
170°-180°	117.7	2.1
0°-30°	531.5	9.5
0°-40°	855.4	15.2
0°-60°	1467.0	26.1
0°-90°	1839.9	32.8
90°-120°	775.3	13.8
90°-150°	2789.4	49.7
90°-180°	3778.0	67.3
0°-180°	5617.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	706	706	706	706	706	
5°	706	703	697	702	702	67
15°	672	670	662	666	663	189
25°	610	607	599	599	598	281
35°	528	524	516	513	510	330
45°	433	430	422	415	412	334
55°	328	327	320	313	310	294
65°	224	221	215	210	208	221
75°	118	116	114	111	109	127
85°	32	30	30	29	29	35
90°	1	10	22	26	28	4
95°	56	21	28	35	35	69
105°	274	279	202	48	40	291
115°	514	520	528	537	541	508
125°	725	732	736	738	740	647
135°	903	908	912	915	912	695
145°	1042	1048	1050	1052	1052	652
155°	1148	1146	1147	1151	1146	529
165°	1210	1208	1207	1213	1208	342
175°	1239	1234	1235	1241	1234	118
180°	1239	1239	1239	1239	1239	



TEST NUMBER: P331952-927

CATALOG NUMBER: S123DIP-S560D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8
2.5°	708.1	707.7	707.3	706.9	706.5	705.6	704.4	703.2	702.1	700.9	702.0
5°	706.3	705.7	705.0	704.3	703.6	702.6	701.1	699.6	698.2	696.6	698.0
7.5°	699.4	698.8	698.1	697.4	696.7	695.6	694.1	692.5	691.0	689.5	690.7
10°	693.6	692.9	692.3	691.6	690.9	689.7	687.9	686.2	684.4	682.7	683.9
12.5°	685.9	685.2	684.7	684.1	683.6	682.5	680.8	679.1	677.6	675.9	676.8
15°	672.3	671.8	671.3	670.7	670.2	669.1	667.3	665.6	663.8	662.0	663.1
17.5°	656.7	656.0	655.3	654.6	653.9	652.7	650.9	649.2	647.5	645.6	646.4
20°	645.1	644.3	643.4	642.6	641.8	640.6	638.8	637.1	635.3	633.5	634.1
22.5°	631.9	631.1	630.3	629.5	628.7	627.4	625.7	623.9	622.2	620.4	620.8
25°	610.5	609.7	608.9	608.1	607.2	605.9	604.2	602.5	600.7	599.0	599.0
27.5°	587.6	586.8	586.0	585.2	584.4	583.0	581.1	579.3	577.4	575.5	575.6
30°	571.0	570.4	569.7	569.0	568.3	567.0	565.1	563.2	561.4	559.5	559.5
32.5°	554.5	553.7	552.7	551.8	551.0	549.8	548.3	546.8	545.4	544.0	543.2
35°	527.9	527.1	526.3	525.5	524.7	523.4	521.7	519.9	518.2	516.4	515.6
37.5°	500.7	499.7	498.7	497.6	496.6	495.3	493.5	491.7	489.9	488.1	487.2
40°	481.8	481.0	480.2	479.4	478.6	477.2	475.3	473.5	471.6	469.7	468.6
42.5°	462.9	462.0	461.1	460.1	459.2	457.8	455.9	454.1	452.2	450.3	449.2
45°	432.7	432.1	431.6	431.0	430.5	429.4	427.6	425.9	424.1	422.3	420.7
47.5°	402.7	401.9	401.2	400.4	399.6	398.3	396.7	395.1	393.4	391.7	390.1
50°	382.3	381.6	381.0	380.2	379.6	378.4	376.6	374.9	373.1	371.4	369.9
52.5°	360.9	360.4	360.0	359.6	359.1	357.9	356.1	354.3	352.4	350.5	349.3
55°	328.3	328.1	328.0	327.9	327.7	326.8	325.0	323.3	321.5	319.8	318.3
57.5°	297.2	296.8	296.3	295.9	295.4	294.5	293.0	291.7	290.3	288.8	287.6
60°	274.9	274.7	274.6	274.5	274.3	273.5	271.9	270.2	268.6	267.0	265.8
62.5°	255.0	254.6	254.3	254.0	253.6	252.6	251.0	249.4	247.7	246.1	244.9
65°	223.9	223.2	222.6	221.9	221.3	220.2	218.9	217.5	216.2	214.8	213.7
67.5°	191.0	190.4	189.8	189.3	188.6	187.8	186.8	185.8	184.7	183.8	182.8
70°	171.1	170.3	169.5	168.7	167.9	167.1	166.3	165.5	164.6	163.8	162.9
72.5°	150.3	149.6	149.1	148.5	147.9	147.1	146.2	145.3	144.3	143.5	142.6
75°	118.4	117.8	117.2	116.7	116.2	115.7	115.3	114.9	114.5	114.1	113.4
77.5°	90.1	89.8	89.4	89.2	88.9	88.5	88.0	87.5	87.0	86.5	86.1
80°	71.6	71.2	70.8	70.4	69.9	69.6	69.4	69.1	68.8	68.6	68.4
82.5°	53.6	53.6	53.5	53.4	53.3	53.2	53.2	53.2	53.1	53.1	52.8
85°	31.5	31.3	31.1	30.7	30.5	30.3	30.3	30.3	30.3	30.3	30.1
87.5°	12.8	12.9	13.0	13.1	13.2	13.4	13.9	14.3	14.7	15.1	15.1
90°	1.0	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9
92.5°	17.1	16.6	16.0	15.4	14.8	15.5	17.6	19.6	21.5	23.5	24.9
95°	56.2	47.8	39.4	31.0	22.6	19.6	21.8	24.0	26.3	28.5	29.9
97.5°	112.8	109.1	105.3	101.6	97.8	88.6	73.8	59.1	44.4	29.6	31.3
100°	155.5	159.6	163.7	167.8	171.9	158.0	126.1	94.2	62.3	30.3	32.0
102.5°	204.1	207.1	210.0	212.9	215.9	199.9	165.1	130.2	95.4	60.5	55.5
105°	274.3	276.6	278.8	281.0	283.3	275.2	256.7	238.4	220.0	201.5	165.3
107.5°	348.2	350.1	351.9	353.6	355.5	357.8	360.8	363.6	366.5	369.5	342.9
110°	397.6	399.3	400.8	402.5	404.2	406.1	408.4	410.6	412.8	415.1	408.4



TEST NUMBER: P331952-927

CATALOG NUMBER: S123DIP-S560D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	444.7	446.2	447.7	449.2	450.6	452.5	454.7	457.0	459.2	461.4	461.6
115°	514.5	515.7	516.9	518.2	519.4	520.9	522.8	524.6	526.5	528.3	530.4
117.5°	582.0	583.5	585.0	586.6	588.1	589.3	590.3	591.2	592.2	593.1	594.7
120°	624.0	625.8	627.7	629.5	631.4	632.6	633.2	633.8	634.5	635.0	636.7
122.5°	666.7	668.2	669.7	671.2	672.8	673.9	674.7	675.5	676.2	677.0	678.2
125°	725.2	726.9	728.5	730.2	731.8	733.0	733.8	734.7	735.5	736.3	736.7
127.5°	782.0	783.5	785.2	786.9	788.5	789.8	790.8	791.8	792.7	793.7	794.4
130°	817.3	819.0	820.5	822.2	823.8	825.1	825.9	826.7	827.5	828.3	829.2
132.5°	851.1	852.8	854.4	856.0	857.7	858.8	859.5	860.2	860.8	861.5	862.3
135°	902.9	904.1	905.3	906.6	907.8	908.8	909.7	910.5	911.2	912.1	912.7
137.5°	947.1	948.6	950.1	951.7	953.3	954.3	954.7	955.2	955.6	956.1	957.0
140°	976.5	977.7	979.0	980.2	981.4	982.3	982.9	983.6	984.2	984.8	985.6
142.5°	1003.8	1005.0	1006.2	1007.4	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7
145°	1041.9	1043.3	1044.7	1046.2	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5
147.5°	1077.8	1078.7	1079.7	1080.5	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3
150°	1099.9	1100.4	1101.1	1101.7	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9
152.5°	1119.7	1120.0	1120.3	1120.5	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8
155°	1147.7	1147.3	1146.8	1146.4	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8
157.5°	1169.4	1169.3	1169.3	1169.3	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6
160°	1182.6	1182.5	1182.3	1182.1	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1
162.5°	1195.2	1194.7	1194.1	1193.6	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3
165°	1210.3	1209.7	1209.0	1208.5	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2
167.5°	1222.1	1221.2	1220.4	1219.6	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0
170°	1228.7	1227.9	1227.1	1226.2	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6
172.5°	1233.1	1232.2	1231.1	1230.2	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1
175°	1238.8	1237.8	1236.8	1235.7	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6
177.5°	1240.3	1239.4	1238.7	1237.9	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P331952-927

CATALOG NUMBER: S123DIP-S560D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8
2.5°	703.1	704.1	705.2	705.7	705.6	705.4	705.4	705.3
5°	699.3	700.7	702.0	702.6	702.3	702.0	701.8	701.5
7.5°	691.9	693.1	694.3	694.8	694.7	694.5	694.3	694.2
10°	685.1	686.3	687.5	688.0	687.8	687.5	687.2	686.9
12.5°	677.6	678.6	679.5	679.8	679.6	679.5	679.3	679.1
15°	664.2	665.3	666.4	666.5	665.7	664.9	664.1	663.3
17.5°	647.2	647.9	648.7	648.9	648.6	648.3	648.0	647.7
20°	634.6	635.2	635.6	635.7	635.3	634.9	634.5	634.1
22.5°	621.3	621.7	622.2	622.1	621.6	621.1	620.6	620.0
25°	599.2	599.4	599.4	599.4	599.0	598.6	598.1	597.7
27.5°	575.8	575.8	575.9	575.8	575.2	574.7	574.2	573.7
30°	559.5	559.5	559.5	559.0	558.1	557.1	556.2	555.2
32.5°	542.5	541.7	540.9	540.3	539.8	539.3	538.8	538.3
35°	514.8	514.0	513.2	512.5	511.7	511.1	510.4	509.8
37.5°	486.2	485.2	484.3	483.5	483.2	482.7	482.3	481.8
40°	467.5	466.4	465.4	464.5	464.0	463.5	463.0	462.4
42.5°	448.1	447.0	445.9	445.1	444.6	444.1	443.5	443.0
45°	419.1	417.5	415.9	414.7	414.1	413.4	412.7	412.0
47.5°	388.6	387.0	385.4	384.3	383.7	383.1	382.5	381.9
50°	368.4	366.9	365.4	364.3	363.5	362.7	361.9	361.1
52.5°	348.0	346.7	345.5	344.4	343.6	342.8	342.0	341.2
55°	316.8	315.4	313.9	312.8	312.1	311.4	310.8	310.1
57.5°	286.2	284.9	283.6	282.5	281.7	281.0	280.2	279.4
60°	264.6	263.4	262.1	261.2	260.5	259.8	259.2	258.5
62.5°	243.7	242.5	241.3	240.4	240.0	239.6	239.1	238.6
65°	212.6	211.6	210.5	209.8	209.4	209.0	208.6	208.1
67.5°	181.9	180.9	180.0	179.2	178.6	178.1	177.5	177.0
70°	161.9	161.1	160.1	159.2	158.6	157.9	157.2	156.5
72.5°	141.8	140.9	140.1	139.5	139.2	138.8	138.5	138.1
75°	112.7	112.1	111.4	110.8	110.4	110.0	109.6	109.2
77.5°	85.6	85.2	84.7	84.4	84.4	84.4	84.4	84.4
80°	68.3	68.1	68.0	68.0	68.0	68.0	68.0	68.0
82.5°	52.5	52.3	52.0	51.9	51.8	51.7	51.6	51.5
85°	29.8	29.5	29.2	29.2	29.2	29.2	29.2	29.2
87.5°	15.2	15.3	15.3	15.4	15.4	15.5	15.6	15.7
90°	23.7	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	26.1	27.5	28.8	29.5	29.8	30.1	30.3	30.6
95°	31.4	32.8	34.2	34.9	34.9	34.9	34.9	34.9
97.5°	32.9	34.5	36.2	37.1	37.3	37.5	37.7	37.9
100°	33.7	35.3	36.9	37.9	38.0	38.3	38.4	38.7
102.5°	50.4	45.3	40.2	37.9	38.3	38.7	39.1	39.4
105°	129.1	92.9	56.7	38.9	39.3	39.7	40.1	40.5
107.5°	316.3	289.8	263.2	236.3	209.1	181.7	154.5	127.2
110°	401.6	394.8	388.1	370.1	340.9	311.6	282.3	253.1



TEST NUMBER: P331952-927

CATALOG NUMBER: S123DIP-S560D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	461.7	461.8	462.0	458.9	452.7	446.6	440.4	434.2
115°	532.3	534.4	536.5	537.9	538.7	539.6	540.3	541.1
117.5°	596.4	598.0	599.6	600.6	600.7	600.9	601.0	601.2
120°	638.3	639.9	641.6	642.4	642.4	642.4	642.4	642.4
122.5°	679.3	680.5	681.6	682.2	682.4	682.5	682.8	682.9
125°	737.1	737.5	737.9	738.3	738.7	739.2	739.6	740.0
127.5°	795.0	795.7	796.3	796.5	796.1	795.7	795.3	794.8
130°	830.0	830.8	831.6	831.8	831.4	831.0	830.6	830.2
132.5°	863.1	864.0	864.7	864.8	864.3	863.7	863.2	862.5
135°	913.3	913.9	914.6	914.6	913.9	913.3	912.7	912.1
137.5°	958.1	959.0	960.0	960.3	959.9	959.5	959.1	958.6
140°	986.4	987.2	988.1	988.2	987.9	987.5	987.1	986.7
142.5°	1013.4	1014.0	1014.6	1014.7	1014.2	1013.5	1013.0	1012.4
145°	1051.0	1051.4	1051.8	1051.9	1051.9	1051.9	1051.9	1051.9
147.5°	1084.7	1085.1	1085.4	1085.2	1084.3	1083.3	1082.4	1081.4
150°	1105.3	1105.6	1106.0	1106.0	1105.3	1104.8	1104.1	1103.5
152.5°	1123.6	1124.3	1125.1	1125.0	1124.0	1123.1	1122.1	1121.2
155°	1148.8	1149.9	1150.9	1150.7	1149.5	1148.3	1147.1	1145.9
157.5°	1170.8	1172.0	1173.2	1173.1	1171.5	1169.8	1168.2	1166.6
160°	1183.3	1184.5	1185.7	1185.7	1184.2	1182.8	1181.3	1179.9
162.5°	1194.7	1196.0	1197.5	1197.5	1196.2	1194.9	1193.7	1192.4
165°	1209.9	1211.5	1213.1	1213.2	1211.8	1210.4	1208.9	1207.5
167.5°	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4
170°	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0
172.5°	1232.7	1234.3	1236.0	1235.9	1234.1	1232.3	1230.5	1228.7
175°	1238.0	1239.4	1240.9	1240.7	1239.1	1237.5	1235.9	1234.2
177.5°	1239.9	1241.3	1242.5	1242.4	1240.8	1239.1	1237.5	1235.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)