

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331998-930

Luminaire Tested: **S123DIP-S775D1195U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331998-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5928.1 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331998-930

CATALOG NUMBER: S123DIP-S775D1195U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331998-930

CATALOG NUMBER: S123DIP-S775D1195U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		64	64	64		50	50	50	44
1	96	92	88	85	88	84	81	78	70	67	65		57	55	53		44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54		50	47	45		39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45		44	40	38		35	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39		39	35	32		31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33		35	31	28		28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29		32	28	24		25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25		29	25	22		23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23		26	22	19		21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20		24	20	17		19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18		22	18	16		18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10687	10687	10687
5°	10737	10589	10662
10°	10665	10497	10563
15°	10541	10379	10398
20°	10394	10208	10219
25°	10200	10007	9987
30°	9984	9783	9708
35°	9759	9546	9423
40°	9524	9284	9140
45°	9266	9045	8824
50°	9008	8748	8505
55°	8668	8443	8188
60°	8325	8086	7830
65°	8023	7697	7457
70°	7578	7254	6930
75°	6924	6675	6392
80°	6248	5976	5926
85°	5483	5274	5064



TEST NUMBER: P331998-930

CATALOG NUMBER: S123DIP-S775D1195U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.6
10°-20°	264.1	4.5
20°-30°	390.1	6.6
30°-40°	455.7	7.7
40°-50°	458.1	7.7
50°-60°	402.4	6.8
60°-70°	299.8	5.1
70°-80°	170.8	2.9
80°-90°	52.6	0.9
90°-100°	78.6	1.3
100°-110°	235.1	4.0
110°-120°	399.9	6.7
120°-130°	526.0	8.9
130°-140°	591.2	10.0
140°-150°	581.2	9.8
150°-160°	489.3	8.3
160°-170°	325.7	5.5
170°-180°	114.0	1.9
0°-30°	747.7	12.6
0°-40°	1203.3	20.3
0°-60°	2063.8	34.8
0°-90°	2587.0	43.6
90°-120°	713.6	12.0
90°-150°	2412.1	40.7
90°-180°	3341.0	56.4
0°-180°	5928.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	994	989	980	988	987	94
15°	946	942	931	938	933	267
25°	859	853	843	843	841	395
35°	743	737	726	721	717	464
45°	609	605	594	584	580	470
55°	462	460	450	441	436	414
65°	315	310	302	296	293	311
75°	166	163	160	156	154	178
85°	44	43	43	41	41	49
90°	1	11	23	26	28	6
95°	56	63	70	74	74	63
105°	213	215	224	224	225	228
115°	403	405	404	404	404	398
125°	589	592	590	586	583	525
135°	764	770	769	766	764	589
145°	927	929	932	931	927	579
155°	1062	1062	1063	1066	1060	489
165°	1157	1154	1154	1159	1153	326
175°	1203	1199	1199	1204	1198	114
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P331998-930

CATALOG NUMBER: S123DIP-S775D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	996.2	995.6	995.1	994.4	993.8	992.7	991.0	989.4	987.7	986.0	987.5
5°	993.7	992.7	991.8	990.8	989.9	988.4	986.3	984.2	982.1	980.0	981.9
7.5°	984.0	983.0	982.0	981.1	980.2	978.6	976.4	974.3	972.1	970.0	971.7
10°	975.8	974.8	973.9	972.9	972.0	970.3	967.8	965.3	962.9	960.4	962.1
12.5°	964.8	964.0	963.3	962.5	961.6	960.1	957.8	955.4	953.2	950.8	952.1
15°	945.9	945.1	944.4	943.6	942.8	941.3	938.7	936.3	933.8	931.4	932.9
17.5°	923.8	922.8	921.9	920.9	919.9	918.2	915.7	913.2	910.8	908.3	909.4
20°	907.4	906.3	905.2	904.1	902.9	901.1	898.6	896.2	893.7	891.2	892.0
22.5°	889.0	887.9	886.7	885.6	884.4	882.6	880.2	877.8	875.3	872.8	873.4
25°	858.8	857.7	856.6	855.4	854.3	852.5	849.9	847.5	845.1	842.6	842.8
27.5°	826.6	825.4	824.3	823.2	822.1	820.3	817.6	815.0	812.3	809.6	809.8
30°	803.3	802.3	801.4	800.5	799.5	797.7	795.1	792.4	789.8	787.1	787.1
32.5°	780.1	778.9	777.6	776.3	775.1	773.5	771.4	769.3	767.3	765.2	764.2
35°	742.7	741.6	740.5	739.3	738.2	736.4	733.9	731.4	729.0	726.5	725.4
37.5°	704.4	703.0	701.6	700.1	698.7	696.8	694.2	691.7	689.2	686.7	685.3
40°	677.8	676.7	675.6	674.4	673.3	671.4	668.7	666.1	663.4	660.7	659.3
42.5°	651.2	649.9	648.6	647.3	646.0	644.1	641.4	638.7	636.1	633.4	631.9
45°	608.7	607.9	607.2	606.4	605.6	604.1	601.5	599.1	596.6	594.2	591.9
47.5°	566.5	565.4	564.3	563.2	562.1	560.4	558.1	555.8	553.4	551.1	548.9
50°	537.9	536.9	535.9	535.0	534.0	532.3	529.9	527.4	524.9	522.4	520.4
52.5°	507.8	507.1	506.5	505.8	505.2	503.5	500.9	498.3	495.7	493.1	491.3
55°	461.9	461.6	461.5	461.3	461.1	459.7	457.3	454.9	452.3	449.9	447.8
57.5°	418.2	417.5	416.9	416.2	415.6	414.3	412.3	410.3	408.3	406.3	404.5
60°	386.7	386.5	386.4	386.1	386.0	384.7	382.5	380.2	377.9	375.6	373.9
62.5°	358.7	358.2	357.8	357.3	356.8	355.4	353.1	350.8	348.5	346.3	344.5
65°	315.0	314.1	313.1	312.2	311.2	309.8	307.9	306.0	304.1	302.2	300.7
67.5°	268.7	267.9	267.1	266.2	265.4	264.2	262.9	261.4	259.9	258.5	257.1
70°	240.8	239.6	238.5	237.3	236.2	235.1	233.9	232.8	231.6	230.5	229.2
72.5°	211.4	210.5	209.7	208.9	208.1	207.0	205.7	204.4	203.1	201.8	200.6
75°	166.5	165.7	164.9	164.2	163.5	162.7	162.2	161.6	161.0	160.5	159.6
77.5°	126.7	126.3	125.9	125.5	125.0	124.5	123.8	123.1	122.5	121.7	121.1
80°	100.8	100.2	99.6	99.1	98.5	98.0	97.6	97.3	96.9	96.4	96.3
82.5°	75.5	75.3	75.3	75.1	75.0	74.9	74.8	74.8	74.7	74.6	74.3
85°	44.4	44.0	43.6	43.3	42.9	42.7	42.7	42.7	42.7	42.7	42.3
87.5°	17.9	17.9	17.9	17.9	17.8	18.0	18.4	18.8	19.2	19.6	19.6
90°	1.0	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6
92.5°	22.9	24.4	25.8	27.2	28.6	30.2	31.7	33.3	34.8	36.4	37.0
95°	55.9	57.4	58.9	60.3	61.8	63.3	65.1	66.7	68.4	70.1	70.9
97.5°	99.3	100.4	101.5	102.6	103.6	104.8	106.1	107.3	108.4	109.7	110.6
100°	128.8	130.1	131.3	132.6	133.9	135.0	136.1	137.1	138.2	139.3	139.9
102.5°	162.9	163.7	164.4	165.2	166.0	167.1	168.4	169.8	171.2	172.6	173.3
105°	213.1	213.5	214.0	214.4	214.8	216.0	217.8	219.8	221.7	223.6	223.6
107.5°	271.5	271.7	272.0	272.2	272.5	273.0	273.8	274.5	275.2	276.1	276.7
110°	307.9	308.3	308.7	309.2	309.6	310.0	310.4	310.8	311.2	311.7	312.5



TEST NUMBER: P331998-930

CATALOG NUMBER: S123DIP-S775D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	345.8	346.0	346.3	346.5	346.7	346.9	347.0	347.1	347.2	347.2	348.3
115°	402.6	403.2	403.8	404.5	405.1	405.2	404.8	404.4	404.0	403.6	403.7
117.5°	459.8	460.2	460.6	461.1	461.5	461.5	460.9	460.3	459.8	459.3	459.2
120°	495.5	496.7	498.0	499.2	500.5	500.6	499.5	498.5	497.4	496.4	496.2
122.5°	532.6	533.5	534.4	535.3	536.3	536.5	535.9	535.3	534.8	534.3	533.7
125°	589.2	589.9	590.4	591.1	591.7	591.8	591.4	591.0	590.6	590.2	589.3
127.5°	641.5	642.9	644.2	645.6	646.9	647.3	646.9	646.4	646.0	645.5	644.3
130°	676.4	678.0	679.7	681.4	683.1	683.6	683.0	682.3	681.8	681.1	680.3
132.5°	711.2	712.9	714.6	716.2	718.0	718.6	718.1	717.6	717.1	716.7	715.7
135°	764.4	765.7	767.0	768.3	769.5	770.1	769.8	769.6	769.4	769.2	768.3
137.5°	813.8	814.7	815.8	816.8	817.9	818.7	819.3	819.8	820.4	820.9	820.0
140°	847.8	848.9	849.9	851.0	852.0	852.6	852.9	853.0	853.3	853.5	853.3
142.5°	878.9	880.0	881.0	882.1	883.1	883.8	884.2	884.6	884.9	885.3	885.1
145°	927.4	927.8	928.2	928.6	929.0	929.6	930.3	930.8	931.5	932.1	931.9
147.5°	969.8	970.6	971.3	972.1	972.9	973.5	974.1	974.7	975.3	975.9	975.9
150°	999.4	999.8	1000.2	1000.6	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1
152.5°	1023.6	1024.3	1024.8	1025.4	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8
155°	1061.9	1061.9	1061.9	1061.9	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7
157.5°	1094.5	1094.2	1094.0	1093.7	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0
160°	1114.9	1114.5	1114.1	1113.7	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1
162.5°	1133.1	1132.5	1132.0	1131.4	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3
165°	1156.7	1156.0	1155.4	1154.7	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0
167.5°	1175.4	1174.5	1173.7	1172.9	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6
170°	1186.0	1185.1	1184.3	1183.5	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7
172.5°	1194.3	1193.5	1192.6	1191.8	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9
175°	1203.1	1202.2	1201.3	1200.5	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5
177.5°	1206.6	1206.0	1205.3	1204.6	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P331998-930

CATALOG NUMBER: S123DIP-S775D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	989.0	990.6	992.1	992.8	992.6	992.5	992.3	992.1
5°	983.8	985.7	987.7	988.4	988.0	987.7	987.2	986.8
7.5°	973.4	975.1	976.8	977.5	977.3	977.1	976.8	976.6
10°	963.8	965.5	967.2	967.9	967.5	967.1	966.8	966.4
12.5°	953.3	954.6	955.9	956.3	956.1	955.9	955.7	955.4
15°	934.4	935.9	937.4	937.6	936.5	935.3	934.3	933.1
17.5°	910.4	911.5	912.6	912.9	912.5	912.1	911.7	911.3
20°	892.8	893.5	894.3	894.4	893.8	893.2	892.7	892.1
22.5°	874.0	874.7	875.2	875.1	874.5	873.8	873.0	872.3
25°	842.9	843.2	843.3	843.2	842.6	842.0	841.5	840.9
27.5°	809.9	810.1	810.2	809.9	809.3	808.5	807.8	807.1
30°	787.1	787.1	787.1	786.4	785.1	783.7	782.4	781.1
32.5°	763.1	762.1	761.0	760.1	759.4	758.6	757.9	757.2
35°	724.2	723.1	721.9	720.9	719.9	719.0	718.0	717.1
37.5°	684.0	682.6	681.3	680.3	679.6	679.1	678.4	677.8
40°	657.7	656.2	654.7	653.5	652.8	652.0	651.3	650.5
42.5°	630.4	628.8	627.4	626.2	625.5	624.7	623.9	623.2
45°	589.6	587.3	585.1	583.4	582.5	581.6	580.6	579.7
47.5°	546.7	544.5	542.2	540.6	539.8	539.0	538.2	537.3
50°	518.3	516.2	514.1	512.5	511.4	510.2	509.1	507.9
52.5°	489.5	487.7	485.9	484.5	483.4	482.2	481.1	480.0
55°	445.7	443.6	441.6	440.0	439.0	438.1	437.2	436.3
57.5°	402.6	400.8	398.9	397.5	396.3	395.3	394.1	393.1
60°	372.2	370.5	368.8	367.5	366.5	365.6	364.6	363.7
62.5°	342.8	341.1	339.4	338.3	337.6	337.0	336.3	335.7
65°	299.1	297.7	296.1	295.1	294.5	293.9	293.3	292.8
67.5°	255.8	254.5	253.2	252.1	251.4	250.5	249.7	248.9
70°	227.9	226.5	225.2	224.0	223.1	222.2	221.2	220.2
72.5°	199.4	198.3	197.1	196.2	195.8	195.3	194.8	194.3
75°	158.6	157.7	156.7	156.0	155.4	154.8	154.3	153.7
77.5°	120.4	119.8	119.1	118.9	118.9	118.9	118.9	118.9
80°	96.1	95.9	95.7	95.6	95.6	95.6	95.6	95.6
82.5°	73.9	73.6	73.2	73.0	72.9	72.7	72.6	72.4
85°	41.9	41.6	41.2	41.0	41.0	41.0	41.0	41.0
87.5°	19.6	19.6	19.6	19.6	19.8	19.9	20.0	20.1
90°	24.5	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	37.7	38.4	39.1	39.3	39.1	38.8	38.5	38.2
95°	71.7	72.6	73.5	73.9	73.9	73.9	73.9	73.9
97.5°	111.6	112.6	113.6	114.0	113.9	113.8	113.7	113.7
100°	140.5	141.1	141.8	142.3	142.8	143.2	143.6	144.0
102.5°	173.8	174.5	175.1	175.4	175.3	175.2	175.1	175.0
105°	223.6	223.6	223.6	223.8	224.2	224.6	225.0	225.4
107.5°	277.4	278.1	278.8	278.9	278.7	278.4	278.2	277.9
110°	313.3	314.2	315.0	315.2	314.8	314.4	314.0	313.6



TEST NUMBER: P331998-930

CATALOG NUMBER: S123DIP-S775D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	349.3	350.3	351.3	351.8	351.7	351.6	351.6	351.5
115°	404.0	404.1	404.4	404.4	404.1	404.0	403.7	403.6
117.5°	459.2	459.1	459.1	458.8	458.2	457.5	457.0	456.4
120°	495.9	495.8	495.5	495.2	494.8	494.4	494.0	493.5
122.5°	533.2	532.6	532.1	531.5	530.9	530.4	529.7	529.1
125°	588.5	587.7	586.8	586.0	585.1	584.2	583.4	582.6
127.5°	643.1	642.0	640.7	639.7	638.7	637.7	636.7	635.9
130°	679.4	678.6	677.8	676.5	675.1	673.6	672.1	670.7
132.5°	714.7	713.7	712.7	711.6	710.5	709.3	708.2	707.0
135°	767.5	766.6	765.8	765.2	764.8	764.3	763.9	763.5
137.5°	819.1	818.2	817.3	816.5	815.7	815.0	814.2	813.3
140°	853.0	852.9	852.6	851.8	850.4	848.9	847.4	846.0
142.5°	884.9	884.7	884.5	883.8	882.6	881.5	880.4	879.3
145°	931.7	931.5	931.3	930.7	929.9	929.0	928.2	927.4
147.5°	975.9	975.9	975.9	975.3	974.0	972.7	971.4	970.2
150°	1003.1	1003.1	1003.1	1002.6	1001.3	1000.0	998.7	997.5
152.5°	1028.1	1028.4	1028.7	1028.4	1027.3	1026.2	1025.1	1024.0
155°	1064.5	1065.4	1066.2	1065.9	1064.5	1063.0	1061.5	1060.0
157.5°	1095.8	1096.7	1097.6	1097.5	1096.3	1095.1	1094.0	1092.7
160°	1115.2	1116.2	1117.3	1117.4	1116.6	1115.7	1114.8	1114.0
162.5°	1133.3	1134.4	1135.5	1135.3	1133.9	1132.6	1131.2	1129.9
165°	1156.3	1157.6	1158.9	1158.7	1157.2	1155.8	1154.3	1152.8
167.5°	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3
170°	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2
172.5°	1193.2	1194.5	1195.8	1195.7	1194.2	1192.7	1191.2	1189.8
175°	1201.8	1203.1	1204.3	1204.2	1202.7	1201.3	1199.8	1198.3
177.5°	1205.7	1206.6	1207.6	1207.5	1206.4	1205.2	1204.0	1202.9
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9

(END OF REPORT)