

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331970-930

Luminaire Tested: **S123DIP-S775D585U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331970-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D585U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4493.9 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331970-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331970-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	58	55	52	49	47	45	40
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	37	59	48	41	36	42	37	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10687	10687	10687
5°	10737	10589	10662
10°	10665	10497	10563
15°	10541	10379	10398
20°	10394	10208	10219
25°	10200	10007	9987
30°	9984	9783	9708
35°	9759	9546	9423
40°	9524	9284	9140
45°	9266	9045	8824
50°	9008	8748	8505
55°	8668	8443	8188
60°	8325	8086	7830
65°	8023	7697	7457
70°	7578	7254	6930
75°	6924	6675	6392
80°	6248	5976	5926
85°	5483	5274	5064



TEST NUMBER: P331970-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	2.1
10°-20°	264.1	5.9
20°-30°	390.1	8.7
30°-40°	455.7	10.1
40°-50°	458.1	10.2
50°-60°	402.4	9.0
60°-70°	299.8	6.7
70°-80°	170.8	3.8
80°-90°	50.8	1.1
90°-100°	22.8	0.5
100°-110°	108.4	2.4
110°-120°	260.5	5.8
120°-130°	331.7	7.4
130°-140°	354.4	7.9
140°-150°	331.4	7.4
150°-160°	267.4	5.9
160°-170°	172.6	3.8
170°-180°	59.5	1.3
0°-30°	747.7	16.6
0°-40°	1203.3	26.8
0°-60°	2063.8	45.9
0°-90°	2585.2	57.5
90°-120°	391.7	8.7
90°-150°	1409.3	31.4
90°-180°	1909.0	42.5
0°-180°	4493.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	994	989	980	988	987	94
15°	946	942	931	938	933	267
25°	859	853	843	843	841	395
35°	743	737	726	721	717	464
45°	609	605	594	584	580	470
55°	462	460	450	441	436	414
65°	315	310	302	296	293	311
75°	166	163	160	156	154	178
85°	44	43	43	41	41	49
90°	0	5	11	13	14	4
95°	28	11	14	18	18	35
105°	139	141	102	24	20	147
115°	260	263	267	271	274	257
125°	366	370	372	373	374	327
135°	456	459	461	462	461	351
145°	526	530	531	531	532	329
155°	580	579	579	581	579	267
165°	612	610	610	613	610	173
175°	626	624	624	627	624	60
180°	626	626	626	626	626	



TEST NUMBER: P331970-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	996.2	995.6	995.1	994.4	993.8	992.7	991.0	989.4	987.7	986.0	987.5
5°	993.7	992.7	991.8	990.8	989.9	988.4	986.3	984.2	982.1	980.0	981.9
7.5°	984.0	983.0	982.0	981.1	980.2	978.6	976.4	974.3	972.1	970.0	971.7
10°	975.8	974.8	973.9	972.9	972.0	970.3	967.8	965.3	962.9	960.4	962.1
12.5°	964.8	964.0	963.3	962.5	961.6	960.1	957.8	955.4	953.2	950.8	952.1
15°	945.9	945.1	944.4	943.6	942.8	941.3	938.7	936.3	933.8	931.4	932.9
17.5°	923.8	922.8	921.9	920.9	919.9	918.2	915.7	913.2	910.8	908.3	909.4
20°	907.4	906.3	905.2	904.1	902.9	901.1	898.6	896.2	893.7	891.2	892.0
22.5°	889.0	887.9	886.7	885.6	884.4	882.6	880.2	877.8	875.3	872.8	873.4
25°	858.8	857.7	856.6	855.4	854.3	852.5	849.9	847.5	845.1	842.6	842.8
27.5°	826.6	825.4	824.3	823.2	822.1	820.3	817.6	815.0	812.3	809.6	809.8
30°	803.3	802.3	801.4	800.5	799.5	797.7	795.1	792.4	789.8	787.1	787.1
32.5°	780.1	778.9	777.6	776.3	775.1	773.5	771.4	769.3	767.3	765.2	764.2
35°	742.7	741.6	740.5	739.3	738.2	736.4	733.9	731.4	729.0	726.5	725.4
37.5°	704.4	703.0	701.6	700.1	698.7	696.8	694.2	691.7	689.2	686.7	685.3
40°	677.8	676.7	675.6	674.4	673.3	671.4	668.7	666.1	663.4	660.7	659.3
42.5°	651.2	649.9	648.6	647.3	646.0	644.1	641.4	638.7	636.1	633.4	631.9
45°	608.7	607.9	607.2	606.4	605.6	604.1	601.5	599.1	596.6	594.2	591.9
47.5°	566.5	565.4	564.3	563.2	562.1	560.4	558.1	555.8	553.4	551.1	548.9
50°	537.9	536.9	535.9	535.0	534.0	532.3	529.9	527.4	524.9	522.4	520.4
52.5°	507.8	507.1	506.5	505.8	505.2	503.5	500.9	498.3	495.7	493.1	491.3
55°	461.9	461.6	461.5	461.3	461.1	459.7	457.3	454.9	452.3	449.9	447.8
57.5°	418.2	417.5	416.9	416.2	415.6	414.3	412.3	410.3	408.3	406.3	404.5
60°	386.7	386.5	386.4	386.1	386.0	384.7	382.5	380.2	377.9	375.6	373.9
62.5°	358.7	358.2	357.8	357.3	356.8	355.4	353.1	350.8	348.5	346.3	344.5
65°	315.0	314.1	313.1	312.2	311.2	309.8	307.9	306.0	304.1	302.2	300.7
67.5°	268.7	267.9	267.1	266.2	265.4	264.2	262.9	261.4	259.9	258.5	257.1
70°	240.8	239.6	238.5	237.3	236.2	235.1	233.9	232.8	231.6	230.5	229.2
72.5°	211.4	210.5	209.7	208.9	208.1	207.0	205.7	204.4	203.1	201.8	200.6
75°	166.5	165.7	164.9	164.2	163.5	162.7	162.2	161.6	161.0	160.5	159.6
77.5°	126.7	126.3	125.9	125.5	125.0	124.5	123.8	123.1	122.5	121.7	121.1
80°	100.8	100.2	99.6	99.1	98.5	98.0	97.6	97.3	96.9	96.4	96.3
82.5°	75.5	75.3	75.3	75.1	75.0	74.9	74.8	74.8	74.7	74.6	74.3
85°	44.4	44.0	43.6	43.3	42.9	42.7	42.7	42.7	42.7	42.7	42.3
87.5°	17.9	17.6	17.4	17.1	16.9	16.8	16.9	17.0	17.1	17.3	17.2
90°	0.5	1.5	2.5	3.6	4.6	5.8	7.1	8.5	9.8	11.2	11.6
92.5°	8.6	8.4	8.1	7.7	7.5	7.8	8.9	9.9	10.9	11.9	12.6
95°	28.4	24.1	19.9	15.7	11.4	9.9	11.0	12.1	13.3	14.4	15.2
97.5°	57.0	55.1	53.2	51.3	49.4	44.8	37.3	29.8	22.4	15.0	15.8
100°	78.6	80.6	82.8	84.8	86.8	79.8	63.7	47.6	31.5	15.3	16.1
102.5°	103.1	104.6	106.2	107.6	109.1	101.0	83.4	65.8	48.2	30.6	28.0
105°	138.6	139.7	140.9	141.9	143.1	139.0	129.7	120.4	111.1	101.8	83.6
107.5°	175.9	176.8	177.8	178.7	179.6	180.8	182.2	183.7	185.2	186.6	173.3
110°	200.9	201.7	202.5	203.3	204.2	205.2	206.3	207.4	208.6	209.7	206.3



TEST NUMBER: P331970-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	224.7	225.4	226.2	226.9	227.6	228.6	229.8	230.9	232.0	233.2	233.3
115°	259.9	260.6	261.1	261.8	262.4	263.2	264.2	265.1	266.0	266.9	268.0
117.5°	294.1	294.8	295.6	296.4	297.1	297.7	298.2	298.7	299.2	299.6	300.5
120°	315.3	316.2	317.2	318.0	319.0	319.6	319.9	320.2	320.6	320.8	321.7
122.5°	336.9	337.6	338.3	339.2	339.9	340.5	340.9	341.3	341.7	342.1	342.7
125°	366.4	367.3	368.1	368.9	369.7	370.4	370.8	371.2	371.6	372.0	372.2
127.5°	395.1	395.9	396.7	397.5	398.4	399.0	399.5	400.1	400.6	401.0	401.4
130°	412.9	413.8	414.6	415.4	416.2	416.9	417.3	417.7	418.1	418.5	418.9
132.5°	430.1	430.9	431.7	432.5	433.3	433.9	434.2	434.6	434.9	435.3	435.7
135°	456.2	456.8	457.4	458.0	458.7	459.2	459.6	460.0	460.4	460.8	461.1
137.5°	478.5	479.3	480.0	480.9	481.6	482.2	482.3	482.6	482.8	483.1	483.6
140°	493.3	494.0	494.6	495.2	495.9	496.4	496.6	496.9	497.3	497.6	498.0
142.5°	507.1	507.8	508.4	509.0	509.6	510.1	510.4	510.7	511.0	511.4	511.7
145°	526.4	527.1	527.8	528.6	529.3	529.8	529.9	530.2	530.4	530.6	530.8
147.5°	544.5	545.0	545.5	545.9	546.4	546.7	547.0	547.1	547.4	547.6	547.8
150°	555.7	556.0	556.3	556.6	556.9	557.2	557.4	557.6	557.8	558.0	558.2
152.5°	565.7	565.9	566.0	566.1	566.3	566.5	566.6	566.7	566.8	567.0	567.3
155°	579.8	579.7	579.4	579.3	579.0	579.0	579.1	579.2	579.3	579.4	579.9
157.5°	590.8	590.8	590.8	590.8	590.8	590.7	590.6	590.5	590.4	590.3	590.9
160°	597.5	597.5	597.4	597.2	597.1	597.0	596.9	596.8	596.7	596.6	597.2
162.5°	603.9	603.6	603.3	603.1	602.8	602.6	602.5	602.4	602.3	602.2	602.9
165°	611.5	611.1	610.9	610.6	610.3	610.0	609.9	609.8	609.8	609.6	610.5
167.5°	617.4	617.0	616.6	616.2	615.8	615.6	615.6	615.6	615.6	615.6	616.4
170°	620.8	620.4	620.0	619.5	619.1	618.9	618.9	618.9	618.9	618.9	619.8
172.5°	623.1	622.6	622.0	621.5	621.0	620.9	620.9	621.0	621.1	621.2	622.0
175°	625.9	625.4	624.8	624.4	623.9	623.6	623.7	623.9	623.9	624.0	624.8
177.5°	626.6	626.2	625.8	625.4	625.0	624.8	624.9	625.0	625.1	625.2	625.8
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9



TEST NUMBER: P331970-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	989.0	990.6	992.1	992.8	992.6	992.5	992.3	992.1
5°	983.8	985.7	987.7	988.4	988.0	987.7	987.2	986.8
7.5°	973.4	975.1	976.8	977.5	977.3	977.1	976.8	976.6
10°	963.8	965.5	967.2	967.9	967.5	967.1	966.8	966.4
12.5°	953.3	954.6	955.9	956.3	956.1	955.9	955.7	955.4
15°	934.4	935.9	937.4	937.6	936.5	935.3	934.3	933.1
17.5°	910.4	911.5	912.6	912.9	912.5	912.1	911.7	911.3
20°	892.8	893.5	894.3	894.4	893.8	893.2	892.7	892.1
22.5°	874.0	874.7	875.2	875.1	874.5	873.8	873.0	872.3
25°	842.9	843.2	843.3	843.2	842.6	842.0	841.5	840.9
27.5°	809.9	810.1	810.2	809.9	809.3	808.5	807.8	807.1
30°	787.1	787.1	787.1	786.4	785.1	783.7	782.4	781.1
32.5°	763.1	762.1	761.0	760.1	759.4	758.6	757.9	757.2
35°	724.2	723.1	721.9	720.9	719.9	719.0	718.0	717.1
37.5°	684.0	682.6	681.3	680.3	679.6	679.1	678.4	677.8
40°	657.7	656.2	654.7	653.5	652.8	652.0	651.3	650.5
42.5°	630.4	628.8	627.4	626.2	625.5	624.7	623.9	623.2
45°	589.6	587.3	585.1	583.4	582.5	581.6	580.6	579.7
47.5°	546.7	544.5	542.2	540.6	539.8	539.0	538.2	537.3
50°	518.3	516.2	514.1	512.5	511.4	510.2	509.1	507.9
52.5°	489.5	487.7	485.9	484.5	483.4	482.2	481.1	480.0
55°	445.7	443.6	441.6	440.0	439.0	438.1	437.2	436.3
57.5°	402.6	400.8	398.9	397.5	396.3	395.3	394.1	393.1
60°	372.2	370.5	368.8	367.5	366.5	365.6	364.6	363.7
62.5°	342.8	341.1	339.4	338.3	337.6	337.0	336.3	335.7
65°	299.1	297.7	296.1	295.1	294.5	293.9	293.3	292.8
67.5°	255.8	254.5	253.2	252.1	251.4	250.5	249.7	248.9
70°	227.9	226.5	225.2	224.0	223.1	222.2	221.2	220.2
72.5°	199.4	198.3	197.1	196.2	195.8	195.3	194.8	194.3
75°	158.6	157.7	156.7	156.0	155.4	154.8	154.3	153.7
77.5°	120.4	119.8	119.1	118.9	118.9	118.9	118.9	118.9
80°	96.1	95.9	95.7	95.6	95.6	95.6	95.6	95.6
82.5°	73.9	73.6	73.2	73.0	72.9	72.7	72.6	72.4
85°	41.9	41.6	41.2	41.0	41.0	41.0	41.0	41.0
87.5°	17.1	17.0	17.0	17.0	17.0	17.0	17.1	17.1
90°	12.0	12.4	12.8	13.1	13.4	13.5	13.8	13.9
92.5°	13.2	13.9	14.5	14.9	15.1	15.2	15.3	15.4
95°	15.9	16.6	17.3	17.7	17.7	17.7	17.7	17.7
97.5°	16.6	17.4	18.3	18.8	18.8	18.9	19.1	19.2
100°	17.0	17.9	18.7	19.1	19.2	19.3	19.4	19.6
102.5°	25.4	22.9	20.4	19.2	19.3	19.6	19.7	19.9
105°	65.2	47.0	28.7	19.6	19.8	20.1	20.2	20.5
107.5°	159.8	146.4	133.0	119.4	105.6	91.8	78.0	64.2
110°	202.9	199.5	196.1	186.9	172.2	157.4	142.7	127.8



TEST NUMBER: P331970-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	233.3	233.3	233.4	231.9	228.8	225.6	222.5	219.4
115°	269.0	270.0	271.1	271.7	272.1	272.6	273.0	273.5
117.5°	301.3	302.1	303.0	303.5	303.5	303.6	303.7	303.8
120°	322.5	323.3	324.2	324.6	324.6	324.6	324.6	324.6
122.5°	343.2	343.8	344.4	344.7	344.8	344.9	345.0	345.0
125°	372.4	372.6	372.8	373.1	373.2	373.5	373.7	373.9
127.5°	401.7	402.0	402.4	402.4	402.2	402.0	401.8	401.6
130°	419.3	419.7	420.1	420.3	420.0	419.9	419.6	419.5
132.5°	436.1	436.5	436.9	437.0	436.7	436.3	436.1	435.8
135°	461.5	461.8	462.0	462.0	461.8	461.5	461.1	460.8
137.5°	484.0	484.5	485.0	485.2	484.9	484.8	484.5	484.4
140°	498.4	498.8	499.2	499.3	499.1	498.9	498.7	498.5
142.5°	512.0	512.3	512.7	512.7	512.4	512.1	511.8	511.5
145°	531.0	531.2	531.4	531.5	531.5	531.5	531.5	531.5
147.5°	548.0	548.2	548.5	548.3	547.8	547.3	546.9	546.4
150°	558.4	558.6	558.8	558.8	558.5	558.2	557.8	557.6
152.5°	567.7	568.0	568.4	568.3	567.9	567.4	567.0	566.5
155°	580.4	581.0	581.5	581.4	580.8	580.2	579.6	578.9
157.5°	591.5	592.2	592.8	592.6	591.8	591.1	590.3	589.5
160°	597.9	598.4	599.1	599.0	598.3	597.6	596.9	596.1
162.5°	603.6	604.3	605.0	605.0	604.4	603.7	603.1	602.5
165°	611.3	612.1	612.9	613.0	612.3	611.6	610.8	610.1
167.5°	617.3	618.1	618.9	618.9	618.1	617.3	616.4	615.6
170°	620.6	621.4	622.2	622.2	621.4	620.6	619.8	618.9
172.5°	622.8	623.6	624.4	624.4	623.5	622.6	621.7	620.8
175°	625.5	626.2	627.0	626.9	626.1	625.3	624.4	623.5
177.5°	626.5	627.1	627.8	627.7	626.9	626.1	625.3	624.4
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9

(END OF REPORT)