

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331972-930

Luminaire Tested: **S123DIP-S775D585U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331972-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D585U930-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4313.6 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331972-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331972-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	58	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	47	42	38	40	37	34	31
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	30	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	31	27	23	27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10687	10687	10687
5°	10737	10589	10662
10°	10665	10497	10563
15°	10541	10379	10398
20°	10394	10208	10219
25°	10200	10007	9987
30°	9984	9783	9708
35°	9759	9546	9423
40°	9524	9284	9140
45°	9266	9045	8824
50°	9008	8748	8505
55°	8668	8443	8188
60°	8325	8086	7830
65°	8023	7697	7457
70°	7578	7254	6930
75°	6924	6675	6392
80°	6248	5976	5926
85°	5483	5274	5064



TEST NUMBER: P331972-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.5	2.2
10°-20°	264.1	6.1
20°-30°	390.1	9.0
30°-40°	455.7	10.6
40°-50°	458.1	10.6
50°-60°	402.4	9.3
60°-70°	299.8	6.9
70°-80°	170.8	4.0
80°-90°	50.8	1.2
90°-100°	127.8	3.0
100°-110°	362.0	8.4
110°-120°	356.1	8.3
120°-130°	284.0	6.6
130°-140°	224.0	5.2
140°-150°	167.1	3.9
150°-160°	116.5	2.7
160°-170°	68.4	1.6
170°-180°	22.3	0.5
0°-30°	747.7	17.3
0°-40°	1203.3	27.9
0°-60°	2063.8	47.8
0°-90°	2585.2	59.9
90°-120°	846.0	19.6
90°-150°	1521.1	35.3
90°-180°	1728.0	40.1
0°-180°	4313.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	994	989	980	988	987	94
15°	946	942	931	938	933	267
25°	859	853	843	843	841	395
35°	743	737	726	721	717	464
45°	609	605	594	584	580	470
55°	462	460	450	441	436	414
65°	315	310	302	296	293	311
75°	166	163	160	156	154	178
85°	44	43	43	41	41	49
90°	1	6	12	13	14	3
95°	16	51	276	80	54	17
105°	54	80	374	654	592	57
115°	95	119	286	627	719	94
125°	133	156	267	484	567	118
135°	155	185	263	398	460	120
145°	177	203	260	327	360	111
155°	201	217	252	286	298	93
165°	220	226	241	256	260	62
175°	229	230	231	234	234	22
180°	230	230	230	230	230	



TEST NUMBER: P331972-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	996.2	995.6	995.1	994.4	993.8	992.7	991.0	989.4	987.7	986.0	987.5
5°	993.7	992.7	991.8	990.8	989.9	988.4	986.3	984.2	982.1	980.0	981.9
7.5°	984.0	983.0	982.0	981.1	980.2	978.6	976.4	974.3	972.1	970.0	971.7
10°	975.8	974.8	973.9	972.9	972.0	970.3	967.8	965.3	962.9	960.4	962.1
12.5°	964.8	964.0	963.3	962.5	961.6	960.1	957.8	955.4	953.2	950.8	952.1
15°	945.9	945.1	944.4	943.6	942.8	941.3	938.7	936.3	933.8	931.4	932.9
17.5°	923.8	922.8	921.9	920.9	919.9	918.2	915.7	913.2	910.8	908.3	909.4
20°	907.4	906.3	905.2	904.1	902.9	901.1	898.6	896.2	893.7	891.2	892.0
22.5°	889.0	887.9	886.7	885.6	884.4	882.6	880.2	877.8	875.3	872.8	873.4
25°	858.8	857.7	856.6	855.4	854.3	852.5	849.9	847.5	845.1	842.6	842.8
27.5°	826.6	825.4	824.3	823.2	822.1	820.3	817.6	815.0	812.3	809.6	809.8
30°	803.3	802.3	801.4	800.5	799.5	797.7	795.1	792.4	789.8	787.1	787.1
32.5°	780.1	778.9	777.6	776.3	775.1	773.5	771.4	769.3	767.3	765.2	764.2
35°	742.7	741.6	740.5	739.3	738.2	736.4	733.9	731.4	729.0	726.5	725.4
37.5°	704.4	703.0	701.6	700.1	698.7	696.8	694.2	691.7	689.2	686.7	685.3
40°	677.8	676.7	675.6	674.4	673.3	671.4	668.7	666.1	663.4	660.7	659.3
42.5°	651.2	649.9	648.6	647.3	646.0	644.1	641.4	638.7	636.1	633.4	631.9
45°	608.7	607.9	607.2	606.4	605.6	604.1	601.5	599.1	596.6	594.2	591.9
47.5°	566.5	565.4	564.3	563.2	562.1	560.4	558.1	555.8	553.4	551.1	548.9
50°	537.9	536.9	535.9	535.0	534.0	532.3	529.9	527.4	524.9	522.4	520.4
52.5°	507.8	507.1	506.5	505.8	505.2	503.5	500.9	498.3	495.7	493.1	491.3
55°	461.9	461.6	461.5	461.3	461.1	459.7	457.3	454.9	452.3	449.9	447.8
57.5°	418.2	417.5	416.9	416.2	415.6	414.3	412.3	410.3	408.3	406.3	404.5
60°	386.7	386.5	386.4	386.1	386.0	384.7	382.5	380.2	377.9	375.6	373.9
62.5°	358.7	358.2	357.8	357.3	356.8	355.4	353.1	350.8	348.5	346.3	344.5
65°	315.0	314.1	313.1	312.2	311.2	309.8	307.9	306.0	304.1	302.2	300.7
67.5°	268.7	267.9	267.1	266.2	265.4	264.2	262.9	261.4	259.9	258.5	257.1
70°	240.8	239.6	238.5	237.3	236.2	235.1	233.9	232.8	231.6	230.5	229.2
72.5°	211.4	210.5	209.7	208.9	208.1	207.0	205.7	204.4	203.1	201.8	200.6
75°	166.5	165.7	164.9	164.2	163.5	162.7	162.2	161.6	161.0	160.5	159.6
77.5°	126.7	126.3	125.9	125.5	125.0	124.5	123.8	123.1	122.5	121.7	121.1
80°	100.8	100.2	99.6	99.1	98.5	98.0	97.6	97.3	96.9	96.4	96.3
82.5°	75.5	75.3	75.3	75.1	75.0	74.9	74.8	74.8	74.7	74.6	74.3
85°	44.4	44.0	43.6	43.3	42.9	42.7	42.7	42.7	42.7	42.7	42.3
87.5°	17.9	17.7	17.4	17.2	17.0	16.9	17.0	17.1	17.2	17.4	17.1
90°	0.9	1.9	2.8	4.2	5.1	6.0	7.4	8.8	10.2	11.7	11.2
92.5°	5.8	8.6	12.5	16.1	20.0	26.9	39.1	59.0	78.7	71.5	54.0
95°	15.8	17.2	22.3	30.2	42.3	60.4	100.0	169.3	245.6	275.7	223.6
97.5°	27.0	27.5	31.5	38.3	50.2	69.9	107.6	185.7	312.8	427.4	457.2
100°	34.4	34.9	38.2	44.7	55.8	73.9	106.5	175.3	297.6	440.3	532.0
102.5°	42.2	43.0	46.0	52.1	62.1	78.8	107.9	166.4	275.3	416.2	535.7
105°	54.0	55.4	58.1	63.7	72.6	87.0	112.1	160.0	247.9	373.9	507.4
107.5°	66.4	67.8	70.5	76.0	84.3	97.7	119.7	159.5	230.4	336.5	457.7
110°	75.3	76.7	79.1	84.1	92.0	105.1	126.0	161.3	223.6	315.3	426.4



TEST NUMBER: P331972-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	83.5	85.0	87.2	92.4	100.3	112.9	132.3	165.1	220.0	301.2	399.3
115°	95.3	97.2	100.0	104.6	112.5	125.1	142.8	171.1	218.6	286.0	366.5
117.5°	107.1	109.3	111.6	115.9	124.7	136.3	153.8	179.1	219.4	277.0	346.7
120°	115.4	116.8	119.0	123.7	132.6	144.1	160.9	185.1	220.9	273.0	336.2
122.5°	122.4	123.8	126.1	131.1	139.6	152.0	168.4	190.7	223.5	270.4	327.7
125°	132.6	133.5	136.2	141.4	150.2	162.7	179.0	199.5	227.4	266.9	316.7
127.5°	140.2	141.6	145.1	150.3	160.0	172.6	188.3	206.8	231.9	265.2	307.0
130°	145.1	146.5	150.7	156.2	166.0	178.6	193.9	211.6	234.8	264.2	301.8
132.5°	148.8	150.6	155.2	161.8	171.6	183.8	198.8	216.1	237.1	263.7	296.9
135°	155.3	157.2	162.3	169.3	179.0	191.6	206.0	221.8	240.4	263.2	290.7
137.5°	161.4	163.4	168.4	175.9	185.6	197.1	211.0	226.1	242.6	262.2	285.2
140°	165.6	167.9	172.5	179.9	189.2	200.9	214.3	228.4	244.1	261.8	281.8
142.5°	170.0	171.9	177.0	183.7	193.0	203.9	217.0	230.6	245.2	261.1	278.8
145°	177.2	178.6	182.8	189.7	197.6	208.3	220.5	233.0	246.0	259.9	274.8
147.5°	184.4	185.2	189.4	195.4	203.0	212.1	223.2	234.5	246.0	258.2	270.9
150°	189.2	189.7	193.5	199.5	206.0	214.3	225.1	234.8	246.0	256.7	268.3
152.5°	194.1	194.2	198.0	203.3	209.0	217.0	226.2	235.6	244.9	254.9	265.4
155°	201.4	201.4	204.2	208.8	213.9	220.5	228.4	235.8	243.7	251.6	260.9
157.5°	207.1	207.5	209.7	213.9	218.2	223.2	229.5	236.3	242.1	248.7	255.8
160°	211.6	211.6	213.4	217.2	220.5	225.1	230.6	236.3	241.3	246.5	252.5
162.5°	214.9	214.9	216.5	219.4	222.3	226.2	231.1	235.9	239.9	244.3	249.2
165°	220.0	219.5	220.5	222.7	224.6	227.9	231.5	234.8	237.7	240.9	244.6
167.5°	223.8	223.2	223.6	225.4	226.7	228.8	231.5	234.1	235.4	237.5	240.3
170°	226.0	225.1	225.5	226.9	227.9	228.8	231.1	233.0	233.9	235.3	237.7
172.5°	227.5	226.9	227.1	228.0	228.6	229.2	231.1	232.6	232.8	233.4	235.1
175°	229.3	228.8	228.4	229.3	229.3	229.8	230.6	231.5	231.1	231.1	232.0
177.5°	230.1	229.8	229.3	229.8	229.8	229.8	230.1	230.8	230.1	229.8	230.1
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331972-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	989.0	990.6	992.1	992.8	992.6	992.5	992.3	992.1
5°	983.8	985.7	987.7	988.4	988.0	987.7	987.2	986.8
7.5°	973.4	975.1	976.8	977.5	977.3	977.1	976.8	976.6
10°	963.8	965.5	967.2	967.9	967.5	967.1	966.8	966.4
12.5°	953.3	954.6	955.9	956.3	956.1	955.9	955.7	955.4
15°	934.4	935.9	937.4	937.6	936.5	935.3	934.3	933.1
17.5°	910.4	911.5	912.6	912.9	912.5	912.1	911.7	911.3
20°	892.8	893.5	894.3	894.4	893.8	893.2	892.7	892.1
22.5°	874.0	874.7	875.2	875.1	874.5	873.8	873.0	872.3
25°	842.9	843.2	843.3	843.2	842.6	842.0	841.5	840.9
27.5°	809.9	810.1	810.2	809.9	809.3	808.5	807.8	807.1
30°	787.1	787.1	787.1	786.4	785.1	783.7	782.4	781.1
32.5°	763.1	762.1	761.0	760.1	759.4	758.6	757.9	757.2
35°	724.2	723.1	721.9	720.9	719.9	719.0	718.0	717.1
37.5°	684.0	682.6	681.3	680.3	679.6	679.1	678.4	677.8
40°	657.7	656.2	654.7	653.5	652.8	652.0	651.3	650.5
42.5°	630.4	628.8	627.4	626.2	625.5	624.7	623.9	623.2
45°	589.6	587.3	585.1	583.4	582.5	581.6	580.6	579.7
47.5°	546.7	544.5	542.2	540.6	539.8	539.0	538.2	537.3
50°	518.3	516.2	514.1	512.5	511.4	510.2	509.1	507.9
52.5°	489.5	487.7	485.9	484.5	483.4	482.2	481.1	480.0
55°	445.7	443.6	441.6	440.0	439.0	438.1	437.2	436.3
57.5°	402.6	400.8	398.9	397.5	396.3	395.3	394.1	393.1
60°	372.2	370.5	368.8	367.5	366.5	365.6	364.6	363.7
62.5°	342.8	341.1	339.4	338.3	337.6	337.0	336.3	335.7
65°	299.1	297.7	296.1	295.1	294.5	293.9	293.3	292.8
67.5°	255.8	254.5	253.2	252.1	251.4	250.5	249.7	248.9
70°	227.9	226.5	225.2	224.0	223.1	222.2	221.2	220.2
72.5°	199.4	198.3	197.1	196.2	195.8	195.3	194.8	194.3
75°	158.6	157.7	156.7	156.0	155.4	154.8	154.3	153.7
77.5°	120.4	119.8	119.1	118.9	118.9	118.9	118.9	118.9
80°	96.1	95.9	95.7	95.6	95.6	95.6	95.6	95.6
82.5°	73.9	73.6	73.2	73.0	72.9	72.7	72.6	72.4
85°	41.9	41.6	41.2	41.0	41.0	41.0	41.0	41.0
87.5°	17.0	17.0	17.0	17.0	17.0	17.0	17.1	17.0
90°	11.7	12.1	12.6	13.5	13.0	13.5	13.9	13.5
92.5°	39.1	31.1	27.5	25.0	24.2	22.7	23.2	22.4
95°	167.4	113.5	88.8	72.1	63.3	59.0	55.8	54.0
97.5°	417.4	334.3	274.3	218.7	184.3	163.4	150.8	146.8
100°	548.3	510.6	456.2	390.1	343.2	309.2	291.1	291.6
102.5°	591.8	590.6	558.9	517.0	480.5	453.6	438.4	427.7
105°	604.5	651.0	659.9	647.8	626.4	608.7	593.9	591.5
107.5°	567.9	643.4	684.1	700.7	701.1	695.1	690.1	685.8
110°	532.9	618.5	677.1	709.6	722.7	726.4	725.5	724.5





TEST NUMBER: P331972-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	498.3	585.7	651.4	693.2	717.1	728.6	732.1	732.3
115°	452.5	533.4	601.8	652.4	687.3	707.8	717.1	719.4
117.5°	419.2	489.1	550.5	601.9	638.3	661.7	675.1	678.2
120°	401.8	464.6	520.3	567.4	604.1	630.1	641.2	644.1
122.5°	388.0	444.8	496.5	540.1	572.8	596.2	608.5	612.0
125°	369.7	420.4	465.0	502.2	532.0	552.4	564.1	567.4
127.5°	353.7	398.9	439.2	473.0	499.5	517.0	527.5	530.5
130°	343.6	385.5	423.1	454.8	479.5	496.2	506.0	509.6
132.5°	334.4	372.8	407.9	438.1	461.2	477.9	486.6	489.2
135°	321.8	354.8	385.1	411.6	434.3	448.3	456.6	459.9
137.5°	310.4	337.5	363.5	386.5	405.6	419.7	426.8	428.9
140°	303.7	327.3	349.7	369.7	387.3	400.4	407.8	407.3
142.5°	297.3	317.7	337.0	354.4	369.5	381.1	387.8	387.3
145°	289.7	305.1	319.9	333.5	345.0	354.8	358.6	359.5
147.5°	283.5	295.6	307.7	317.2	326.0	332.6	336.2	336.6
150°	279.0	289.7	299.5	308.3	315.3	320.4	323.2	323.2
152.5°	274.9	284.1	292.8	300.1	305.6	310.4	312.0	312.0
155°	268.8	276.2	283.2	288.8	292.9	296.7	297.6	298.1
157.5°	262.3	268.5	273.9	278.3	281.9	284.7	285.4	285.4
160°	258.5	263.7	268.3	271.6	274.8	277.6	277.6	277.1
162.5°	254.1	258.4	262.8	265.6	267.7	270.2	270.2	269.7
165°	248.3	251.1	254.4	256.7	258.5	260.4	259.9	259.9
167.5°	243.3	245.4	247.3	249.0	249.8	251.1	250.6	250.6
170°	239.9	241.3	243.2	244.1	244.6	245.6	245.1	245.1
172.5°	237.0	238.0	239.5	240.0	240.1	241.1	240.3	239.9
175°	233.0	233.4	234.4	234.4	234.4	234.8	234.4	233.9
177.5°	230.5	230.8	231.2	231.2	230.8	231.2	230.5	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8

(END OF REPORT)