

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331979-930

Luminaire Tested: **S123DIP-S775D805U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331979-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5202.2 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331979-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331979-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	42
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	40	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	34	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10687	10687	10687
5°	10737	10589	10662
10°	10665	10497	10563
15°	10541	10379	10398
20°	10394	10208	10219
25°	10200	10007	9987
30°	9984	9783	9708
35°	9759	9546	9423
40°	9524	9284	9140
45°	9266	9045	8824
50°	9008	8748	8505
55°	8668	8443	8188
60°	8325	8086	7830
65°	8023	7697	7457
70°	7578	7254	6930
75°	6924	6675	6392
80°	6248	5976	5926
85°	5483	5274	5064



TEST NUMBER: P331979-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.8
10°-20°	264.1	5.1
20°-30°	390.1	7.5
30°-40°	455.7	8.8
40°-50°	458.1	8.8
50°-60°	402.4	7.7
60°-70°	299.8	5.8
70°-80°	170.8	3.3
80°-90°	51.4	1.0
90°-100°	31.2	0.6
100°-110°	148.7	2.9
110°-120°	357.1	6.9
120°-130°	454.7	8.7
130°-140°	485.8	9.3
140°-150°	454.3	8.7
150°-160°	366.5	7.0
160°-170°	236.5	4.5
170°-180°	81.5	1.6
0°-30°	747.7	14.4
0°-40°	1203.3	23.1
0°-60°	2063.8	39.7
0°-90°	2585.9	49.7
90°-120°	536.9	10.3
90°-150°	1931.8	37.1
90°-180°	2616.0	50.3
0°-180°	5202.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	994	989	980	988	987	94
15°	946	942	931	938	933	267
25°	859	853	843	843	841	395
35°	743	737	726	721	717	464
45°	609	605	594	584	580	470
55°	462	460	450	441	436	414
65°	315	310	302	296	293	311
75°	166	163	160	156	154	178
85°	44	43	43	41	41	49
90°	1	7	15	18	19	4
95°	39	15	20	24	24	48
105°	190	193	140	33	28	201
115°	356	360	366	372	375	352
125°	502	507	510	511	512	448
135°	625	629	632	633	632	481
145°	722	726	727	728	729	451
155°	795	794	794	797	794	366
165°	838	836	836	840	836	237
175°	858	855	855	859	855	82
180°	858	858	858	858	858	



TEST NUMBER: P331979-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	996.2	995.6	995.1	994.4	993.8	992.7	991.0	989.4	987.7	986.0	987.5
5°	993.7	992.7	991.8	990.8	989.9	988.4	986.3	984.2	982.1	980.0	981.9
7.5°	984.0	983.0	982.0	981.1	980.2	978.6	976.4	974.3	972.1	970.0	971.7
10°	975.8	974.8	973.9	972.9	972.0	970.3	967.8	965.3	962.9	960.4	962.1
12.5°	964.8	964.0	963.3	962.5	961.6	960.1	957.8	955.4	953.2	950.8	952.1
15°	945.9	945.1	944.4	943.6	942.8	941.3	938.7	936.3	933.8	931.4	932.9
17.5°	923.8	922.8	921.9	920.9	919.9	918.2	915.7	913.2	910.8	908.3	909.4
20°	907.4	906.3	905.2	904.1	902.9	901.1	898.6	896.2	893.7	891.2	892.0
22.5°	889.0	887.9	886.7	885.6	884.4	882.6	880.2	877.8	875.3	872.8	873.4
25°	858.8	857.7	856.6	855.4	854.3	852.5	849.9	847.5	845.1	842.6	842.8
27.5°	826.6	825.4	824.3	823.2	822.1	820.3	817.6	815.0	812.3	809.6	809.8
30°	803.3	802.3	801.4	800.5	799.5	797.7	795.1	792.4	789.8	787.1	787.1
32.5°	780.1	778.9	777.6	776.3	775.1	773.5	771.4	769.3	767.3	765.2	764.2
35°	742.7	741.6	740.5	739.3	738.2	736.4	733.9	731.4	729.0	726.5	725.4
37.5°	704.4	703.0	701.6	700.1	698.7	696.8	694.2	691.7	689.2	686.7	685.3
40°	677.8	676.7	675.6	674.4	673.3	671.4	668.7	666.1	663.4	660.7	659.3
42.5°	651.2	649.9	648.6	647.3	646.0	644.1	641.4	638.7	636.1	633.4	631.9
45°	608.7	607.9	607.2	606.4	605.6	604.1	601.5	599.1	596.6	594.2	591.9
47.5°	566.5	565.4	564.3	563.2	562.1	560.4	558.1	555.8	553.4	551.1	548.9
50°	537.9	536.9	535.9	535.0	534.0	532.3	529.9	527.4	524.9	522.4	520.4
52.5°	507.8	507.1	506.5	505.8	505.2	503.5	500.9	498.3	495.7	493.1	491.3
55°	461.9	461.6	461.5	461.3	461.1	459.7	457.3	454.9	452.3	449.9	447.8
57.5°	418.2	417.5	416.9	416.2	415.6	414.3	412.3	410.3	408.3	406.3	404.5
60°	386.7	386.5	386.4	386.1	386.0	384.7	382.5	380.2	377.9	375.6	373.9
62.5°	358.7	358.2	357.8	357.3	356.8	355.4	353.1	350.8	348.5	346.3	344.5
65°	315.0	314.1	313.1	312.2	311.2	309.8	307.9	306.0	304.1	302.2	300.7
67.5°	268.7	267.9	267.1	266.2	265.4	264.2	262.9	261.4	259.9	258.5	257.1
70°	240.8	239.6	238.5	237.3	236.2	235.1	233.9	232.8	231.6	230.5	229.2
72.5°	211.4	210.5	209.7	208.9	208.1	207.0	205.7	204.4	203.1	201.8	200.6
75°	166.5	165.7	164.9	164.2	163.5	162.7	162.2	161.6	161.0	160.5	159.6
77.5°	126.7	126.3	125.9	125.5	125.0	124.5	123.8	123.1	122.5	121.7	121.1
80°	100.8	100.2	99.6	99.1	98.5	98.0	97.6	97.3	96.9	96.4	96.3
82.5°	75.5	75.3	75.3	75.1	75.0	74.9	74.8	74.8	74.7	74.6	74.3
85°	44.4	44.0	43.6	43.3	42.9	42.7	42.7	42.7	42.7	42.7	42.3
87.5°	17.9	17.7	17.5	17.4	17.2	17.2	17.4	17.7	17.9	18.1	18.0
90°	0.7	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	11.8	11.5	11.1	10.7	10.3	10.8	12.1	13.5	14.9	16.3	17.2
95°	38.9	33.1	27.2	21.4	15.7	13.5	15.1	16.6	18.2	19.7	20.8
97.5°	78.1	75.6	73.0	70.4	67.8	61.3	51.1	40.9	30.7	20.5	21.7
100°	107.7	110.6	113.4	116.2	119.0	109.4	87.3	65.2	43.1	21.0	22.2
102.5°	141.4	143.4	145.4	147.5	149.5	138.5	114.4	90.2	66.0	41.9	38.4
105°	190.0	191.5	193.1	194.6	196.2	190.6	177.8	165.1	152.3	139.6	114.5
107.5°	241.2	242.5	243.7	244.9	246.1	247.8	249.8	251.8	253.8	255.8	237.5
110°	275.3	276.5	277.6	278.8	279.9	281.2	282.8	284.4	285.9	287.5	282.8



TEST NUMBER: P331979-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.0	309.0	310.1	311.0	312.1	313.3	315.0	316.5	318.0	319.6	319.7
115°	356.3	357.2	358.0	358.9	359.7	360.8	362.1	363.3	364.6	365.9	367.3
117.5°	403.1	404.1	405.2	406.3	407.2	408.1	408.8	409.4	410.1	410.7	411.9
120°	432.2	433.4	434.7	435.9	437.2	438.1	438.5	439.0	439.4	439.8	440.9
122.5°	461.7	462.8	463.8	464.9	465.9	466.7	467.2	467.8	468.3	468.9	469.7
125°	502.3	503.4	504.5	505.6	506.8	507.7	508.3	508.7	509.3	509.9	510.2
127.5°	541.5	542.7	543.8	544.9	546.1	547.0	547.6	548.4	549.0	549.7	550.2
130°	566.0	567.1	568.3	569.4	570.5	571.4	571.9	572.5	573.1	573.6	574.2
132.5°	589.5	590.6	591.7	592.9	594.0	594.8	595.3	595.7	596.1	596.6	597.2
135°	625.3	626.1	627.0	627.9	628.7	629.4	630.0	630.6	631.1	631.7	632.1
137.5°	655.9	657.0	658.0	659.1	660.1	660.9	661.2	661.5	661.8	662.1	662.8
140°	676.3	677.1	678.0	678.8	679.7	680.3	680.8	681.2	681.6	682.0	682.6
142.5°	695.1	696.0	696.8	697.7	698.5	699.2	699.6	700.0	700.4	700.9	701.3
145°	721.5	722.5	723.5	724.5	725.5	726.1	726.4	726.7	727.0	727.2	727.6
147.5°	746.4	747.1	747.7	748.4	749.0	749.5	749.7	750.0	750.3	750.6	750.9
150°	761.7	762.1	762.5	763.0	763.4	763.8	764.0	764.3	764.6	764.9	765.2
152.5°	775.4	775.7	775.8	776.1	776.2	776.4	776.6	776.7	777.0	777.1	777.6
155°	794.8	794.6	794.3	794.0	793.7	793.6	793.8	793.9	794.0	794.2	794.9
157.5°	809.8	809.8	809.8	809.8	809.8	809.7	809.5	809.4	809.3	809.1	810.0
160°	819.0	818.9	818.8	818.6	818.5	818.3	818.2	818.1	817.9	817.7	818.6
162.5°	827.7	827.4	827.0	826.6	826.2	826.0	825.8	825.7	825.6	825.4	826.4
165°	838.2	837.7	837.3	836.9	836.5	836.2	836.1	835.9	835.8	835.6	836.7
167.5°	846.4	845.8	845.2	844.7	844.1	843.8	843.8	843.8	843.8	843.8	844.9
170°	850.9	850.4	849.8	849.2	848.6	848.4	848.4	848.4	848.4	848.4	849.5
172.5°	853.9	853.3	852.6	851.9	851.3	851.0	851.1	851.2	851.3	851.4	852.6
175°	857.9	857.2	856.6	855.8	855.1	854.8	854.9	855.1	855.2	855.4	856.4
177.5°	858.9	858.4	857.9	857.3	856.7	856.5	856.6	856.7	856.8	856.9	857.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P331979-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	989.0	990.6	992.1	992.8	992.6	992.5	992.3	992.1
5°	983.8	985.7	987.7	988.4	988.0	987.7	987.2	986.8
7.5°	973.4	975.1	976.8	977.5	977.3	977.1	976.8	976.6
10°	963.8	965.5	967.2	967.9	967.5	967.1	966.8	966.4
12.5°	953.3	954.6	955.9	956.3	956.1	955.9	955.7	955.4
15°	934.4	935.9	937.4	937.6	936.5	935.3	934.3	933.1
17.5°	910.4	911.5	912.6	912.9	912.5	912.1	911.7	911.3
20°	892.8	893.5	894.3	894.4	893.8	893.2	892.7	892.1
22.5°	874.0	874.7	875.2	875.1	874.5	873.8	873.0	872.3
25°	842.9	843.2	843.3	843.2	842.6	842.0	841.5	840.9
27.5°	809.9	810.1	810.2	809.9	809.3	808.5	807.8	807.1
30°	787.1	787.1	787.1	786.4	785.1	783.7	782.4	781.1
32.5°	763.1	762.1	761.0	760.1	759.4	758.6	757.9	757.2
35°	724.2	723.1	721.9	720.9	719.9	719.0	718.0	717.1
37.5°	684.0	682.6	681.3	680.3	679.6	679.1	678.4	677.8
40°	657.7	656.2	654.7	653.5	652.8	652.0	651.3	650.5
42.5°	630.4	628.8	627.4	626.2	625.5	624.7	623.9	623.2
45°	589.6	587.3	585.1	583.4	582.5	581.6	580.6	579.7
47.5°	546.7	544.5	542.2	540.6	539.8	539.0	538.2	537.3
50°	518.3	516.2	514.1	512.5	511.4	510.2	509.1	507.9
52.5°	489.5	487.7	485.9	484.5	483.4	482.2	481.1	480.0
55°	445.7	443.6	441.6	440.0	439.0	438.1	437.2	436.3
57.5°	402.6	400.8	398.9	397.5	396.3	395.3	394.1	393.1
60°	372.2	370.5	368.8	367.5	366.5	365.6	364.6	363.7
62.5°	342.8	341.1	339.4	338.3	337.6	337.0	336.3	335.7
65°	299.1	297.7	296.1	295.1	294.5	293.9	293.3	292.8
67.5°	255.8	254.5	253.2	252.1	251.4	250.5	249.7	248.9
70°	227.9	226.5	225.2	224.0	223.1	222.2	221.2	220.2
72.5°	199.4	198.3	197.1	196.2	195.8	195.3	194.8	194.3
75°	158.6	157.7	156.7	156.0	155.4	154.8	154.3	153.7
77.5°	120.4	119.8	119.1	118.9	118.9	118.9	118.9	118.9
80°	96.1	95.9	95.7	95.6	95.6	95.6	95.6	95.6
82.5°	73.9	73.6	73.2	73.0	72.9	72.7	72.6	72.4
85°	41.9	41.6	41.2	41.0	41.0	41.0	41.0	41.0
87.5°	18.0	17.9	17.9	17.9	18.0	18.0	18.1	18.2
90°	16.5	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	18.1	19.0	20.0	20.5	20.6	20.8	21.0	21.2
95°	21.8	22.7	23.7	24.2	24.2	24.2	24.2	24.2
97.5°	22.8	23.9	25.0	25.7	25.8	26.0	26.1	26.3
100°	23.3	24.5	25.6	26.2	26.3	26.5	26.7	26.7
102.5°	34.9	31.4	27.9	26.3	26.5	26.7	27.0	27.3
105°	89.4	64.4	39.3	26.9	27.2	27.5	27.8	28.0
107.5°	219.1	200.7	182.3	163.6	144.8	125.9	107.0	88.1
110°	278.1	273.5	268.8	256.3	236.0	215.8	195.5	175.3



TEST NUMBER: P331979-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	319.8	319.8	319.9	317.8	313.6	309.2	305.0	300.8
115°	368.7	370.1	371.5	372.5	373.1	373.7	374.2	374.8
117.5°	413.0	414.2	415.2	415.9	416.0	416.1	416.2	416.4
120°	442.1	443.2	444.3	444.9	444.9	444.9	444.9	444.9
122.5°	470.4	471.2	472.1	472.5	472.6	472.7	472.9	473.0
125°	510.5	510.8	511.0	511.4	511.6	511.9	512.2	512.5
127.5°	550.6	551.1	551.5	551.5	551.3	551.1	550.7	550.5
130°	574.8	575.4	575.9	576.1	575.8	575.5	575.2	574.9
132.5°	597.7	598.3	598.8	598.9	598.6	598.2	597.8	597.4
135°	632.5	632.9	633.3	633.3	632.9	632.5	632.1	631.7
137.5°	663.5	664.1	664.9	665.0	664.8	664.5	664.2	663.9
140°	683.1	683.7	684.3	684.4	684.1	683.9	683.5	683.3
142.5°	701.8	702.2	702.7	702.7	702.3	701.9	701.6	701.2
145°	727.8	728.1	728.4	728.6	728.6	728.6	728.6	728.6
147.5°	751.1	751.5	751.7	751.5	750.9	750.2	749.6	748.9
150°	765.4	765.7	766.0	766.0	765.5	765.1	764.7	764.3
152.5°	778.1	778.6	779.2	779.1	778.4	777.8	777.1	776.5
155°	795.7	796.3	797.0	797.0	796.1	795.2	794.4	793.5
157.5°	810.8	811.6	812.5	812.4	811.3	810.2	809.1	808.0
160°	819.5	820.4	821.2	821.1	820.1	819.1	818.2	817.2
162.5°	827.4	828.3	829.2	829.3	828.4	827.5	826.7	825.8
165°	837.9	839.0	840.2	840.2	839.3	838.2	837.2	836.3
167.5°	846.0	847.2	848.3	848.3	847.2	846.0	844.9	843.8
170°	850.6	851.7	852.9	852.9	851.7	850.6	849.5	848.4
172.5°	853.7	854.8	856.0	855.9	854.7	853.5	852.2	850.9
175°	857.4	858.3	859.3	859.2	858.2	857.0	855.9	854.8
177.5°	858.8	859.7	860.5	860.5	859.3	858.2	857.0	855.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9

(END OF REPORT)