

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331971-927

Luminaire Tested: **S123DIP-S775D585U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331971-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D585U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4105.6 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331971-927

CATALOG NUMBER: S123DIP-S775D585U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331971-927

CATALOG NUMBER: S123DIP-S775D585U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	78	76	73	68	66	64	59	57	56	51
2	91	84	77	72	85	78	73	68	69	64	61	60	57	54	52	49	47	43
3	83	73	66	60	78	69	62	57	61	55	51	53	49	45	46	43	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	64	52	44	38	60	49	42	36	44	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	27	24	21
8	55	43	35	29	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10384	10384	10384
5°	10432	10289	10361
10°	10363	10200	10263
15°	10242	10085	10104
20°	10100	9919	9929
25°	9911	9723	9704
30°	9701	9506	9434
35°	9483	9276	9155
40°	9254	9021	8882
45°	9003	8788	8573
50°	8751	8500	8264
55°	8422	8203	7955
60°	8088	7858	7608
65°	7796	7480	7246
70°	7361	7046	6735
75°	6729	6488	6209
80°	6069	5808	5759
85°	5323	5125	4915



TEST NUMBER: P331971-927

CATALOG NUMBER: S123DIP-S775D585U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	2.2
10°-20°	256.6	6.2
20°-30°	379.0	9.2
30°-40°	442.7	10.8
40°-50°	445.1	10.8
50°-60°	391.0	9.5
60°-70°	291.3	7.1
70°-80°	166.0	4.0
80°-90°	49.3	1.2
90°-100°	37.5	0.9
100°-110°	112.2	2.7
110°-120°	190.8	4.6
120°-130°	250.9	6.1
130°-140°	282.0	6.9
140°-150°	277.2	6.8
150°-160°	233.4	5.7
160°-170°	155.4	3.8
170°-180°	54.4	1.3
0°-30°	726.5	17.7
0°-40°	1169.2	28.5
0°-60°	2005.3	48.8
0°-90°	2511.9	61.2
90°-120°	340.4	8.3
90°-150°	1150.6	28.0
90°-180°	1594.0	38.8
0°-180°	4105.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	965	965	965	965	965	
5°	966	961	952	960	959	91
15°	919	915	905	911	907	259
25°	834	829	819	819	817	384
35°	722	716	706	701	697	451
45°	591	588	577	568	563	456
55°	449	447	437	428	424	402
65°	306	302	294	287	284	302
75°	162	158	156	152	149	173
85°	43	42	42	40	40	47
90°	0	5	11	13	14	4
95°	27	30	33	35	35	30
105°	102	103	107	107	108	109
115°	192	193	192	193	192	190
125°	281	282	282	280	278	251
135°	365	367	367	365	364	281
145°	442	443	445	444	442	276
155°	506	507	507	508	506	233
165°	552	550	550	553	550	155
175°	574	572	572	574	572	54
180°	575	575	575	575	575	



TEST NUMBER: P331971-927

CATALOG NUMBER: S123DIP-S775D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	968.0	967.4	966.9	966.2	965.7	964.6	962.9	961.3	959.6	958.1	959.5
5°	965.5	964.6	963.7	962.7	961.8	960.4	958.3	956.3	954.3	952.2	954.1
7.5°	956.1	955.1	954.2	953.3	952.4	950.9	948.7	946.7	944.5	942.5	944.1
10°	948.1	947.1	946.3	945.3	944.4	942.8	940.3	937.9	935.6	933.2	934.9
12.5°	937.5	936.7	936.0	935.2	934.4	932.9	930.7	928.4	926.1	923.8	925.1
15°	919.1	918.3	917.6	916.9	916.1	914.6	912.1	909.7	907.4	905.0	906.4
17.5°	897.6	896.7	895.7	894.8	893.8	892.2	889.8	887.3	884.9	882.6	883.6
20°	881.7	880.6	879.6	878.5	877.3	875.5	873.1	870.8	868.4	865.9	866.7
22.5°	863.8	862.7	861.6	860.5	859.4	857.6	855.2	852.9	850.5	848.0	848.7
25°	834.5	833.4	832.3	831.2	830.0	828.3	825.9	823.5	821.1	818.7	818.9
27.5°	803.1	802.0	801.0	799.9	798.8	797.0	794.4	791.9	789.3	786.6	786.8
30°	780.5	779.6	778.7	777.8	776.8	775.1	772.5	769.9	767.4	764.8	764.8
32.5°	758.0	756.8	755.5	754.3	753.1	751.5	749.5	747.5	745.5	743.5	742.5
35°	721.7	720.6	719.5	718.4	717.2	715.5	713.0	710.7	708.3	705.9	704.8
37.5°	684.4	683.1	681.7	680.2	678.9	677.0	674.5	672.1	669.6	667.3	665.9
40°	658.6	657.5	656.4	655.3	654.2	652.4	649.7	647.2	644.6	642.0	640.6
42.5°	632.7	631.4	630.2	629.0	627.7	625.8	623.2	620.6	618.1	615.4	614.0
45°	591.4	590.7	589.9	589.2	588.4	586.9	584.5	582.1	579.7	577.3	575.1
47.5°	550.4	549.4	548.3	547.2	546.1	544.5	542.2	540.0	537.7	535.5	533.3
50°	522.6	521.7	520.7	519.8	518.9	517.2	514.8	512.5	510.0	507.6	505.6
52.5°	493.4	492.7	492.1	491.5	490.8	489.3	486.7	484.2	481.6	479.1	477.4
55°	448.8	448.5	448.4	448.2	448.0	446.7	444.3	442.0	439.5	437.1	435.1
57.5°	406.3	405.7	405.0	404.4	403.8	402.5	400.6	398.6	396.7	394.8	393.0
60°	375.7	375.6	375.4	375.2	375.0	373.8	371.6	369.4	367.2	365.0	363.3
62.5°	348.6	348.1	347.6	347.1	346.7	345.3	343.1	340.9	338.7	336.4	334.8
65°	306.1	305.1	304.2	303.3	302.4	301.0	299.1	297.3	295.5	293.7	292.2
67.5°	261.1	260.3	259.5	258.6	257.9	256.7	255.4	254.0	252.5	251.2	249.9
70°	233.9	232.8	231.7	230.6	229.5	228.4	227.3	226.2	225.1	223.9	222.7
72.5°	205.4	204.5	203.7	203.0	202.2	201.1	199.9	198.6	197.3	196.1	195.0
75°	161.8	161.0	160.3	159.5	158.8	158.1	157.6	157.0	156.5	156.0	155.0
77.5°	123.1	122.7	122.3	121.9	121.4	121.0	120.3	119.6	119.0	118.3	117.6
80°	97.9	97.4	96.8	96.3	95.7	95.2	94.8	94.5	94.1	93.7	93.6
82.5°	73.4	73.2	73.1	73.0	72.9	72.8	72.7	72.6	72.6	72.5	72.2
85°	43.1	42.8	42.4	42.1	41.7	41.5	41.5	41.5	41.5	41.5	41.1
87.5°	17.3	17.1	16.9	16.6	16.4	16.3	16.4	16.6	16.6	16.8	16.7
90°	0.5	1.4	2.5	3.5	4.4	5.6	6.9	8.2	9.5	10.9	11.2
92.5°	10.9	11.6	12.3	13.0	13.7	14.4	15.1	15.8	16.6	17.3	17.7
95°	26.7	27.3	28.0	28.8	29.5	30.3	31.1	31.8	32.6	33.4	33.8
97.5°	47.4	47.8	48.4	49.0	49.4	50.0	50.5	51.2	51.7	52.4	52.8
100°	61.5	62.0	62.7	63.3	63.8	64.4	64.9	65.4	65.9	66.4	66.7
102.5°	77.7	78.1	78.4	78.8	79.1	79.7	80.3	81.0	81.7	82.3	82.6
105°	101.6	101.9	102.0	102.3	102.5	103.0	103.9	104.8	105.8	106.6	106.6
107.5°	129.5	129.6	129.8	129.8	130.0	130.2	130.6	130.9	131.3	131.7	132.0
110°	146.9	147.0	147.3	147.4	147.7	147.8	148.1	148.3	148.5	148.7	149.1



TEST NUMBER: P331971-927

CATALOG NUMBER: S123DIP-S775D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	164.9	165.0	165.2	165.2	165.4	165.5	165.6	165.6	165.6	165.6	166.1
115°	192.0	192.3	192.7	193.0	193.2	193.3	193.1	192.9	192.7	192.5	192.6
117.5°	219.4	219.5	219.8	219.9	220.1	220.1	219.8	219.6	219.4	219.0	219.0
120°	236.3	236.9	237.5	238.1	238.8	238.8	238.3	237.8	237.3	236.8	236.7
122.5°	254.1	254.4	254.9	255.3	255.8	255.9	255.6	255.4	255.1	254.8	254.6
125°	281.1	281.4	281.6	281.9	282.3	282.3	282.1	281.9	281.7	281.5	281.1
127.5°	306.0	306.7	307.3	307.9	308.6	308.8	308.6	308.3	308.1	307.9	307.4
130°	322.7	323.4	324.2	325.0	325.8	326.1	325.8	325.5	325.2	324.9	324.5
132.5°	339.2	340.1	340.9	341.7	342.5	342.8	342.5	342.3	342.1	341.9	341.4
135°	364.6	365.3	365.8	366.5	367.0	367.3	367.2	367.1	367.0	366.9	366.5
137.5°	388.2	388.6	389.1	389.7	390.1	390.5	390.8	391.0	391.3	391.6	391.2
140°	404.4	404.9	405.4	405.9	406.4	406.7	406.8	406.9	407.0	407.1	407.0
142.5°	419.2	419.7	420.3	420.7	421.2	421.6	421.8	421.9	422.2	422.3	422.2
145°	442.4	442.6	442.8	443.0	443.1	443.4	443.7	444.0	444.3	444.7	444.5
147.5°	462.6	463.0	463.3	463.7	464.1	464.4	464.7	464.9	465.2	465.5	465.5
150°	476.7	476.9	477.1	477.3	477.5	477.7	477.9	478.1	478.3	478.5	478.5
152.5°	488.3	488.5	488.9	489.1	489.4	489.6	489.7	489.8	490.0	490.0	490.2
155°	506.5	506.5	506.5	506.5	506.5	506.6	506.7	506.8	506.9	507.0	507.4
157.5°	522.0	522.0	521.8	521.7	521.6	521.6	521.7	521.7	521.8	521.9	522.3
160°	531.8	531.6	531.4	531.2	531.0	530.9	530.9	530.9	530.9	530.9	531.4
162.5°	540.5	540.2	540.0	539.6	539.4	539.3	539.4	539.5	539.6	539.6	540.1
165°	551.7	551.4	551.1	550.8	550.5	550.3	550.3	550.3	550.3	550.3	551.0
167.5°	560.6	560.2	559.8	559.4	559.0	558.9	559.0	559.0	559.1	559.2	559.8
170°	565.7	565.3	564.9	564.5	564.1	563.9	563.9	563.9	563.9	563.9	564.6
172.5°	569.7	569.3	568.9	568.5	568.1	567.9	567.9	567.9	567.9	567.9	568.5
175°	573.9	573.5	573.1	572.7	572.3	572.0	572.0	572.0	572.0	572.0	572.7
177.5°	575.6	575.3	575.0	574.6	574.3	574.1	574.1	574.1	574.1	574.1	574.6
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2



TEST NUMBER: P331971-927

CATALOG NUMBER: S123DIP-S775D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	961.0	962.5	963.9	964.6	964.5	964.3	964.2	964.0
5°	955.9	957.7	959.6	960.4	960.0	959.6	959.3	958.9
7.5°	945.8	947.5	949.1	949.8	949.6	949.4	949.1	949.0
10°	936.5	938.1	939.8	940.5	940.1	939.7	939.4	939.0
12.5°	926.3	927.5	928.8	929.2	929.0	928.8	928.6	928.4
15°	907.9	909.3	910.9	911.0	909.9	908.8	907.8	906.7
17.5°	884.6	885.7	886.7	887.0	886.6	886.2	885.8	885.4
20°	867.4	868.2	868.9	869.0	868.5	867.9	867.4	866.8
22.5°	849.2	849.9	850.4	850.3	849.7	849.0	848.3	847.6
25°	819.0	819.3	819.4	819.3	818.7	818.2	817.6	817.1
27.5°	787.0	787.1	787.3	787.0	786.3	785.6	784.9	784.2
30°	764.8	764.8	764.8	764.1	762.9	761.5	760.3	759.0
32.5°	741.5	740.5	739.4	738.6	737.8	737.1	736.4	735.8
35°	703.7	702.6	701.5	700.4	699.5	698.6	697.7	696.7
37.5°	664.6	663.2	661.9	661.0	660.4	659.8	659.2	658.6
40°	639.1	637.6	636.1	635.0	634.3	633.5	632.8	632.1
42.5°	612.5	611.0	609.6	608.5	607.8	607.0	606.3	605.5
45°	572.9	570.7	568.5	566.9	566.0	565.1	564.1	563.2
47.5°	531.2	529.0	526.8	525.3	524.5	523.7	522.9	522.0
50°	503.6	501.5	499.6	498.0	496.9	495.7	494.6	493.5
52.5°	475.6	473.9	472.1	470.8	469.7	468.6	467.5	466.4
55°	433.1	431.0	429.0	427.5	426.6	425.7	424.8	423.9
57.5°	391.2	389.4	387.6	386.2	385.1	384.0	382.9	381.9
60°	361.6	360.0	358.3	357.0	356.1	355.2	354.3	353.4
62.5°	333.1	331.4	329.8	328.7	328.0	327.4	326.8	326.1
65°	290.7	289.2	287.7	286.7	286.1	285.6	285.0	284.5
67.5°	248.6	247.3	246.0	244.9	244.2	243.4	242.6	241.9
70°	221.4	220.1	218.8	217.7	216.7	215.9	214.9	214.0
72.5°	193.8	192.7	191.5	190.7	190.2	189.7	189.3	188.8
75°	154.1	153.2	152.3	151.5	151.0	150.4	149.9	149.3
77.5°	117.0	116.4	115.7	115.5	115.5	115.5	115.5	115.5
80°	93.4	93.2	93.0	92.9	92.9	92.9	92.9	92.9
82.5°	71.9	71.5	71.1	70.9	70.8	70.7	70.5	70.3
85°	40.7	40.4	40.0	39.8	39.8	39.8	39.8	39.8
87.5°	16.6	16.6	16.5	16.5	16.6	16.6	16.6	16.6
90°	11.6	12.0	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	18.0	18.3	18.6	18.8	18.6	18.5	18.4	18.2
95°	34.2	34.6	35.0	35.3	35.3	35.3	35.3	35.3
97.5°	53.2	53.7	54.2	54.3	54.3	54.3	54.3	54.2
100°	67.0	67.3	67.7	67.9	68.0	68.3	68.4	68.7
102.5°	82.9	83.3	83.5	83.7	83.7	83.6	83.6	83.5
105°	106.6	106.6	106.6	106.7	106.9	107.1	107.3	107.6
107.5°	132.3	132.6	132.9	133.1	132.9	132.8	132.7	132.6
110°	149.5	149.9	150.3	150.4	150.2	150.0	149.8	149.6



TEST NUMBER: P331971-927

CATALOG NUMBER: S123DIP-S775D585U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	166.6	167.1	167.5	167.8	167.8	167.7	167.7	167.6
115°	192.7	192.8	192.9	192.9	192.8	192.7	192.6	192.5
117.5°	219.0	219.0	219.0	218.8	218.6	218.2	218.0	217.7
120°	236.5	236.5	236.4	236.2	236.0	235.8	235.6	235.4
122.5°	254.3	254.1	253.8	253.5	253.3	252.9	252.7	252.4
125°	280.7	280.3	279.9	279.5	279.1	278.7	278.3	277.9
127.5°	306.7	306.2	305.6	305.1	304.7	304.2	303.7	303.2
130°	324.1	323.7	323.3	322.7	322.0	321.3	320.6	319.9
132.5°	340.9	340.4	339.9	339.5	338.9	338.3	337.8	337.2
135°	366.1	365.7	365.3	365.0	364.8	364.6	364.4	364.2
137.5°	390.7	390.3	389.9	389.5	389.1	388.7	388.3	387.9
140°	406.9	406.8	406.7	406.3	405.6	404.9	404.2	403.5
142.5°	422.1	422.0	421.9	421.6	421.0	420.5	419.9	419.4
145°	444.4	444.3	444.3	443.9	443.5	443.1	442.8	442.4
147.5°	465.5	465.5	465.5	465.2	464.6	464.0	463.4	462.8
150°	478.5	478.5	478.5	478.2	477.6	477.0	476.4	475.8
152.5°	490.4	490.6	490.8	490.5	490.0	489.5	489.0	488.5
155°	507.8	508.2	508.6	508.4	507.7	507.0	506.4	505.6
157.5°	522.8	523.2	523.6	523.5	522.9	522.4	521.8	521.3
160°	532.0	532.4	532.9	533.0	532.6	532.2	531.8	531.4
162.5°	540.6	541.1	541.6	541.5	540.9	540.3	539.6	539.0
165°	551.6	552.2	552.8	552.7	552.0	551.3	550.6	549.9
167.5°	560.5	561.1	561.7	561.7	561.1	560.5	559.8	559.2
170°	565.3	566.0	566.7	566.7	566.0	565.3	564.6	563.9
172.5°	569.1	569.7	570.4	570.4	569.7	568.9	568.2	567.5
175°	573.2	573.9	574.5	574.4	573.7	573.0	572.3	571.6
177.5°	575.1	575.6	576.1	576.0	575.4	574.9	574.3	573.8
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2

(END OF REPORT)