

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332333-930

Luminaire Tested: **S123RDIP-S1000D365U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332333-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D365U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4274.5 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332333-930

CATALOG NUMBER: S123RDIP-S1000D365U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332333-930

CATALOG NUMBER: S123RDIP-S1000D365U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	69	67	66	62
2	94	87	81	76	89	83	77	73	75	71	67	68	64	61	61	58	56	53
3	86	77	70	64	82	73	67	61	67	61	57	60	56	52	54	51	48	45
4	79	68	60	54	75	65	58	53	59	54	49	54	49	45	49	45	42	39
5	73	61	53	47	69	59	51	46	54	47	43	49	44	40	44	40	37	34
6	68	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	33	30
7	63	50	42	36	59	48	41	35	44	38	33	40	35	31	37	33	29	27
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	34	30	26	24
9	55	42	34	29	52	40	33	28	37	31	27	34	29	25	32	27	24	22
10	51	39	31	27	49	37	30	26	34	29	24	32	27	23	29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14727	14727	14727
5°	14783	14579	14664
10°	14700	14397	14348
15°	14542	14060	13912
20°	14325	13639	13321
25°	14101	13166	12744
30°	13806	12621	11931
35°	13502	12073	11184
40°	13222	11428	10260
45°	12855	10794	9426
50°	12450	10071	8492
55°	12037	9246	7621
60°	11657	8361	6665
65°	11163	7404	5708
70°	10546	6216	4611
75°	9649	4891	4338
80°	8598	4333	3986
85°	7262	3841	3569



TEST NUMBER: P332333-930

CATALOG NUMBER: S123RDIP-S1000D365U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	3.0
10°-20°	357.5	8.4
20°-30°	514.7	12.0
30°-40°	579.8	13.6
40°-50°	554.7	13.0
50°-60°	454.2	10.6
60°-70°	306.5	7.2
70°-80°	154.2	3.6
80°-90°	41.9	1.0
90°-100°	14.1	0.3
100°-110°	67.2	1.6
110°-120°	161.4	3.8
120°-130°	205.5	4.8
130°-140°	219.6	5.1
140°-150°	205.4	4.8
150°-160°	165.6	3.9
160°-170°	106.9	2.5
170°-180°	36.8	0.9
0°-30°	1000.7	23.4
0°-40°	1580.5	37.0
0°-60°	2589.5	60.6
0°-90°	3092.0	72.3
90°-120°	242.7	5.7
90°-150°	873.2	20.4
90°-180°	1183.0	27.7
0°-180°	4274.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1368	1368	1368	1368	1368	
5°	1368	1362	1349	1359	1357	130
15°	1305	1292	1262	1256	1248	367
25°	1187	1158	1109	1086	1073	546
35°	1028	986	919	873	851	643
45°	844	793	709	648	619	651
55°	641	585	493	431	406	575
65°	438	376	291	239	224	434
75°	232	178	118	107	104	247
85°	59	36	31	29	29	66
90°	0	3	7	8	9	4
95°	18	7	9	11	11	22
105°	86	87	63	15	13	91
115°	161	163	165	168	169	159
125°	227	229	230	231	232	203
135°	283	284	286	286	286	217
145°	326	328	329	329	329	204
155°	359	359	359	360	359	165
165°	379	378	378	380	378	107
175°	388	386	387	388	386	37
180°	388	388	388	388	388	



TEST NUMBER: P332333-930

CATALOG NUMBER: S123RDIP-S1000D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1372.6	1371.8	1371.1	1370.3	1369.5	1367.9	1365.5	1363.2	1360.8	1358.5	1360.6
5°	1368.2	1366.9	1365.7	1364.5	1363.3	1361.1	1358.2	1355.3	1352.3	1349.3	1351.5
7.5°	1355.5	1354.2	1352.9	1351.5	1350.2	1347.6	1343.8	1339.9	1336.1	1332.3	1333.5
10°	1344.9	1343.2	1341.4	1339.7	1338.0	1334.9	1330.5	1326.0	1321.6	1317.2	1317.4
12.5°	1329.8	1327.9	1326.0	1324.0	1322.1	1318.4	1313.0	1307.6	1302.2	1296.7	1296.6
15°	1305.0	1302.3	1299.5	1296.8	1294.1	1289.3	1282.4	1275.5	1268.6	1261.7	1260.5
17.5°	1273.7	1270.5	1267.4	1264.2	1261.0	1255.1	1246.3	1237.5	1228.7	1219.9	1217.3
20°	1250.6	1246.7	1242.7	1238.8	1234.8	1228.2	1218.8	1209.4	1200.0	1190.7	1187.5
22.5°	1224.8	1220.3	1215.8	1211.2	1206.7	1199.5	1189.4	1179.5	1169.5	1159.6	1155.6
25°	1187.3	1181.2	1175.0	1168.8	1162.7	1153.9	1142.6	1131.2	1119.9	1108.6	1103.3
27.5°	1141.8	1135.1	1128.2	1121.4	1114.6	1104.9	1092.3	1079.6	1067.0	1054.4	1047.2
30°	1110.8	1103.3	1096.0	1088.6	1081.2	1070.6	1056.8	1042.9	1029.2	1015.4	1007.0
32.5°	1079.7	1071.3	1062.9	1054.5	1046.2	1034.7	1020.1	1005.5	990.8	976.2	967.1
35°	1027.5	1018.6	1009.7	1000.9	992.1	979.9	964.7	949.3	934.1	918.8	908.2
37.5°	974.7	964.8	955.0	945.1	935.2	922.2	905.9	889.5	873.2	856.9	844.8
40°	941.0	930.2	919.2	908.4	897.6	883.4	865.9	848.4	830.9	813.3	800.5
42.5°	902.8	891.9	881.1	870.3	859.4	845.0	826.9	808.8	790.7	772.6	758.6
45°	844.5	833.3	822.2	811.1	800.1	785.1	766.1	747.1	728.1	709.1	695.0
47.5°	786.1	773.9	761.7	749.5	737.4	721.8	702.8	683.8	664.8	645.8	630.6
50°	743.5	731.9	720.3	708.7	697.1	681.3	661.4	641.4	621.4	601.4	586.1
52.5°	705.3	692.8	680.1	667.6	655.0	638.8	619.1	599.2	579.5	559.7	543.8
55°	641.4	629.3	617.2	605.1	593.0	576.5	555.5	534.6	513.6	492.7	478.4
57.5°	582.4	569.2	556.0	542.8	529.7	512.6	491.5	470.4	449.4	428.4	414.8
60°	541.5	528.0	514.4	500.8	487.2	470.3	449.8	429.3	408.9	388.4	375.0
62.5°	500.7	487.1	473.5	460.0	446.5	429.4	409.0	388.5	368.0	347.6	335.0
65°	438.3	424.8	411.2	397.6	384.1	367.7	348.5	329.2	310.0	290.7	278.7
67.5°	375.9	362.2	348.5	334.8	321.1	305.0	286.6	268.2	249.7	231.2	222.3
70°	335.1	321.8	308.5	295.1	281.8	266.6	249.3	232.0	214.7	197.5	188.9
72.5°	294.2	281.2	268.1	254.9	241.8	227.4	211.7	196.1	180.3	164.7	157.6
75°	232.0	220.0	208.2	196.4	184.6	171.9	158.3	144.7	131.2	117.6	115.1
77.5°	175.1	164.4	153.7	143.0	132.3	122.5	113.8	105.1	96.4	87.6	86.3
80°	138.7	128.6	118.5	108.4	98.2	90.7	85.4	80.2	75.1	69.9	69.1
82.5°	104.1	95.4	86.7	77.9	69.1	63.6	61.1	58.8	56.3	53.9	53.2
85°	58.8	53.4	47.9	42.6	37.1	34.0	33.3	32.5	31.8	31.1	30.6
87.5°	21.4	19.3	17.3	15.2	13.2	12.2	12.4	12.6	12.7	13.0	12.8
90°	0.3	0.9	1.5	2.2	2.9	3.6	4.4	5.2	6.1	6.9	7.2
92.5°	5.4	5.2	5.0	4.8	4.6	4.9	5.5	6.1	6.8	7.3	7.7
95°	17.6	14.9	12.3	9.7	7.1	6.1	6.8	7.5	8.2	9.0	9.4
97.5°	35.3	34.2	32.9	31.8	30.6	27.7	23.1	18.5	13.9	9.3	9.8
100°	48.7	50.0	51.3	52.5	53.8	49.5	39.5	29.5	19.5	9.5	10.0
102.5°	63.9	64.8	65.7	66.7	67.6	62.6	51.7	40.8	29.8	19.0	17.4
105°	85.9	86.6	87.2	88.0	88.7	86.2	80.4	74.6	68.9	63.1	51.8
107.5°	109.0	109.6	110.1	110.7	111.3	112.0	112.9	113.8	114.7	115.6	107.3
110°	124.5	125.0	125.5	126.0	126.5	127.1	127.8	128.5	129.2	130.0	127.8



TEST NUMBER: P332333-930

CATALOG NUMBER: S123RDIP-S1000D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	139.2	139.7	140.1	140.6	141.0	141.6	142.4	143.1	143.7	144.5	144.5
115°	161.0	161.4	161.8	162.2	162.6	163.1	163.6	164.2	164.8	165.3	166.0
117.5°	182.2	182.7	183.1	183.6	184.1	184.5	184.7	185.1	185.4	185.6	186.1
120°	195.3	195.9	196.5	197.1	197.6	198.0	198.2	198.4	198.6	198.8	199.3
122.5°	208.7	209.2	209.6	210.1	210.6	210.9	211.2	211.4	211.7	211.9	212.3
125°	227.1	227.6	228.0	228.5	229.1	229.4	229.8	230.0	230.2	230.5	230.6
127.5°	244.8	245.3	245.8	246.3	246.8	247.2	247.5	247.9	248.2	248.4	248.7
130°	255.8	256.3	256.8	257.4	257.9	258.3	258.5	258.8	259.0	259.3	259.5
132.5°	266.4	266.9	267.5	268.0	268.5	268.8	269.0	269.3	269.5	269.7	269.9
135°	282.7	283.0	283.4	283.8	284.1	284.5	284.7	285.0	285.3	285.5	285.7
137.5°	296.4	296.9	297.4	297.9	298.4	298.7	298.9	299.0	299.1	299.3	299.6
140°	305.7	306.1	306.5	306.8	307.2	307.5	307.7	307.9	308.1	308.3	308.5
142.5°	314.2	314.6	315.0	315.4	315.8	316.0	316.3	316.4	316.6	316.8	317.0
145°	326.1	326.6	327.0	327.5	327.9	328.2	328.3	328.5	328.6	328.7	328.9
147.5°	337.4	337.7	337.9	338.3	338.5	338.8	338.9	339.0	339.2	339.2	339.4
150°	344.3	344.5	344.6	344.9	345.0	345.2	345.4	345.4	345.6	345.7	345.8
152.5°	350.5	350.6	350.7	350.7	350.8	351.0	351.0	351.1	351.1	351.2	351.5
155°	359.3	359.1	359.0	358.9	358.7	358.7	358.8	358.8	358.9	359.0	359.3
157.5°	366.1	366.1	366.1	366.0	366.0	366.0	365.9	365.8	365.7	365.7	366.1
160°	370.2	370.1	370.1	370.0	370.0	369.9	369.8	369.7	369.7	369.7	370.0
162.5°	374.1	374.0	373.8	373.7	373.5	373.3	373.2	373.2	373.2	373.1	373.5
165°	378.9	378.6	378.5	378.3	378.1	378.0	377.9	377.8	377.7	377.7	378.2
167.5°	382.5	382.3	382.0	381.8	381.5	381.4	381.4	381.4	381.4	381.4	381.9
170°	384.6	384.3	384.1	383.8	383.6	383.4	383.4	383.4	383.4	383.4	384.0
172.5°	386.0	385.7	385.4	385.1	384.7	384.7	384.7	384.7	384.8	384.8	385.4
175°	387.8	387.4	387.1	386.9	386.5	386.4	386.5	386.5	386.5	386.6	387.1
177.5°	388.2	388.0	387.8	387.5	387.2	387.1	387.2	387.2	387.3	387.3	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P332333-930

CATALOG NUMBER: S123RDIP-S1000D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1362.8	1365.0	1367.1	1368.0	1367.6	1367.3	1366.8	1366.4
5°	1353.8	1356.0	1358.2	1359.1	1358.6	1358.1	1357.6	1357.1
7.5°	1334.7	1335.9	1337.2	1337.4	1336.5	1335.7	1334.9	1334.0
10°	1317.7	1317.9	1318.2	1317.7	1316.4	1315.2	1313.9	1312.7
12.5°	1296.4	1296.3	1296.2	1295.3	1294.0	1292.5	1291.1	1289.6
15°	1259.2	1258.0	1256.8	1255.2	1253.5	1251.8	1250.1	1248.4
17.5°	1214.7	1212.1	1209.5	1206.9	1204.4	1201.8	1199.2	1196.6
20°	1184.2	1181.0	1177.9	1174.8	1171.8	1168.8	1165.9	1162.9
22.5°	1151.6	1147.6	1143.6	1140.2	1137.5	1134.7	1132.0	1129.2
25°	1098.2	1093.0	1087.9	1083.9	1081.2	1078.5	1075.8	1073.0
27.5°	1040.0	1032.8	1025.6	1019.9	1015.8	1011.6	1007.5	1003.4
30°	998.6	990.2	981.8	975.7	971.7	967.8	963.8	959.9
32.5°	957.9	948.8	939.6	932.9	928.8	924.6	920.5	916.3
35°	897.6	887.0	876.4	868.9	864.5	860.0	855.6	851.1
37.5°	832.8	820.8	808.8	800.0	794.5	789.0	783.6	778.1
40°	787.7	774.9	762.1	752.8	747.1	741.5	735.8	730.2
42.5°	744.5	730.5	716.5	706.9	701.9	696.8	691.7	686.6
45°	680.9	666.9	652.8	642.9	636.9	631.0	625.1	619.2
47.5°	615.2	600.0	584.7	574.4	569.1	563.9	558.6	553.3
50°	570.9	555.5	540.3	529.8	524.2	518.4	512.8	507.1
52.5°	528.0	512.1	496.2	485.7	480.6	475.6	470.5	465.4
55°	464.1	449.8	435.5	425.8	420.9	416.0	411.1	406.1
57.5°	401.3	387.8	374.3	365.4	361.3	357.0	352.9	348.6
60°	361.7	348.5	335.1	326.4	322.2	318.0	313.8	309.6
62.5°	322.5	310.0	297.4	288.9	284.6	280.2	275.8	271.4
65°	266.6	254.5	242.4	235.0	232.3	229.6	226.9	224.1
67.5°	213.2	204.2	195.2	189.1	186.3	183.4	180.4	177.6
70°	180.3	171.6	163.0	157.4	154.6	151.9	149.2	146.5
72.5°	150.6	143.5	136.5	132.4	131.3	130.1	129.0	127.8
75°	112.7	110.2	107.8	106.3	105.8	105.3	104.8	104.3
77.5°	85.0	83.6	82.3	81.4	81.0	80.5	80.0	79.5
80°	68.4	67.7	66.9	66.4	65.9	65.4	64.8	64.3
82.5°	52.4	51.7	51.0	50.5	50.5	50.4	50.2	50.1
85°	30.1	29.6	29.1	28.9	28.9	28.9	28.9	28.9
87.5°	12.6	12.5	12.3	12.1	12.0	11.8	11.7	11.5
90°	7.4	7.7	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	8.2	8.6	9.0	9.3	9.3	9.4	9.5	9.5
95°	9.9	10.3	10.8	10.9	10.9	10.9	10.9	10.9
97.5°	10.3	10.8	11.3	11.6	11.7	11.7	11.8	11.9
100°	10.5	11.0	11.6	11.8	11.9	12.0	12.1	12.1
102.5°	15.8	14.2	12.6	11.9	12.0	12.1	12.2	12.3
105°	40.4	29.1	17.8	12.1	12.3	12.4	12.6	12.6
107.5°	99.1	90.7	82.4	73.9	65.5	56.9	48.3	39.8
110°	125.7	123.6	121.5	115.9	106.7	97.5	88.4	79.2



TEST NUMBER: P332333-930

CATALOG NUMBER: S123RDIP-S1000D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	144.6	144.6	144.6	143.7	141.7	139.8	137.9	135.9
115°	166.6	167.3	168.0	168.4	168.6	168.9	169.2	169.4
117.5°	186.7	187.2	187.7	188.0	188.0	188.1	188.2	188.2
120°	199.8	200.3	200.8	201.1	201.1	201.1	201.1	201.1
122.5°	212.6	213.0	213.4	213.5	213.6	213.7	213.7	213.8
125°	230.7	230.9	231.0	231.1	231.2	231.4	231.5	231.6
127.5°	248.8	249.1	249.3	249.3	249.2	249.1	248.9	248.8
130°	259.8	260.1	260.3	260.4	260.2	260.2	260.0	259.8
132.5°	270.2	270.4	270.7	270.8	270.5	270.4	270.2	270.0
135°	285.9	286.1	286.3	286.3	286.1	285.9	285.7	285.5
137.5°	299.9	300.2	300.5	300.6	300.4	300.4	300.2	300.1
140°	308.8	309.0	309.3	309.3	309.2	309.1	309.0	308.8
142.5°	317.2	317.4	317.6	317.6	317.5	317.2	317.1	316.9
145°	329.0	329.1	329.2	329.3	329.3	329.3	329.3	329.3
147.5°	339.5	339.7	339.8	339.7	339.4	339.1	338.8	338.5
150°	346.0	346.1	346.3	346.2	346.0	345.8	345.6	345.4
152.5°	351.7	352.0	352.2	352.1	351.9	351.6	351.2	351.0
155°	359.6	360.0	360.3	360.2	359.9	359.5	359.1	358.7
157.5°	366.5	366.9	367.3	367.2	366.7	366.2	365.7	365.2
160°	370.4	370.8	371.2	371.1	370.7	370.2	369.8	369.3
162.5°	374.0	374.4	374.8	374.9	374.5	374.1	373.7	373.2
165°	378.7	379.3	379.8	379.8	379.4	378.9	378.5	378.0
167.5°	382.4	382.9	383.4	383.4	382.9	382.4	381.9	381.4
170°	384.5	385.0	385.5	385.5	385.0	384.5	384.0	383.4
172.5°	385.9	386.4	386.9	386.9	386.3	385.7	385.1	384.6
175°	387.5	388.0	388.4	388.4	387.9	387.3	386.9	386.4
177.5°	388.2	388.6	389.0	388.9	388.4	387.9	387.3	386.9
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)