

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831863

Luminaire Tested: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831863
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D585U930-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5237.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 50.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

Luminous Intensity Polar Plot



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	103	99	95	92	97	93	90	87	83	81	79	74	72	70	65	64	63	59				
2	94	87	82	77	89	83	78	73	74	70	67	66	63	61	59	56	55	51				
3	87	78	71	66	82	74	68	63	67	62	58	60	56	53	53	50	48	45				
4	80	70	63	57	76	67	60	55	60	55	50	54	50	46	48	45	42	39				
5	74	63	56	50	70	60	53	48	55	49	45	49	45	41	44	41	38	35				
6	69	57	50	44	65	55	48	43	50	44	40	45	41	37	41	37	34	32				
7	64	53	45	40	61	50	43	38	46	40	36	42	37	33	38	34	31	29				
8	60	48	41	36	57	46	39	35	42	37	33	39	34	30	35	31	28	26				
9	56	45	37	32	53	43	36	32	39	34	30	36	31	28	33	29	26	24				
10	53	41	34	30	50	40	33	29	37	31	27	34	29	26	31	27	24	22				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	28478	28478	28478	28478	28478
5°	33813	32736	28657	23166	21507
10°	30636	33250	28514	18560	15923
15°	21094	28509	28213	15170	12596
20°	14675	21950	27646	12791	11071
25°	11182	16728	26822	11370	10203
30°	9734	13375	25792	10556	9451
35°	8937	11282	24331	9871	8766
40°	8154	10075	22420	9198	8139
45°	7365	9214	20360	8561	7514
50°	6685	8502	17928	7937	6738
55°	6047	7807	15593	7328	5782
60°	5419	7100	13543	6654	5464
65°	5000	6299	11660	5980	5165
70°	4063	5445	10172	5410	4198
75°	3564	4329	8617	4487	3697
80°	3230	3663	7060	3763	3496
85°	2952	3211	5360	3421	3211

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 21482 cd/sqm



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.1	4.6
10°-20°	558.0	10.7
20°-30°	640.2	12.2
30°-40°	631.1	12.1
40°-50°	556.5	10.6
50°-60°	428.1	8.2
60°-70°	281.5	5.4
70°-80°	136.7	2.6
80°-90°	35.7	0.7
90°-100°	124.7	2.4
100°-110°	365.0	7.0
110°-120°	356.4	6.8
120°-130°	283.8	5.4
130°-140°	223.9	4.3
140°-150°	167.1	3.2
150°-160°	116.5	2.2
160°-170°	68.4	1.3
170°-180°	22.3	0.4
0°-30°	1439.4	27.5
0°-40°	2070.5	39.5
0°-60°	3055.1	58.3
0°-90°	3509.0	67.0
90°-120°	846.0	16.2
90°-150°	1520.8	29.0
90°-180°	1728.0	33.0
0°-180°	5237.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2646	2646	2646	2646	2646	
5°	3129	3030	2652	2144	1990	286
15°	1893	2558	2532	1361	1130	534
25°	942	1408	2258	957	859	445
35°	680	859	1852	751	667	424
45°	484	605	1338	562	494	376
55°	322	416	831	390	308	289
65°	196	247	458	235	203	192
75°	86	104	207	108	89	92
85°	24	26	43	28	26	25
90°	14	12	1	12	14	9
95°	54	276	16	276	54	88
105°	592	374	54	374	592	590
115°	719	286	95	286	719	702
125°	567	267	132	267	567	513
135°	460	263	155	263	460	357
145°	360	260	177	260	360	228
155°	298	252	201	252	298	139
165°	260	241	220	241	260	74
175°	234	231	229	231	234	23
180°	230	230	230	230	230	



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7
2.5°	2932.0	2922.8	2913.6	2910.9	2908.2	2899.5	2890.8	2871.3	2851.8	2831.7	2811.6
5°	3129.4	3130.5	3131.6	3128.9	3126.2	3114.8	3103.4	3079.6	3055.7	3029.7	3003.6
7.5°	3068.7	3086.1	3103.4	3106.7	3109.9	3118.6	3127.3	3121.9	3116.4	3106.7	3096.9
10°	2802.9	2801.9	2800.8	2820.3	2839.8	2897.9	2955.9	2985.7	3015.6	3042.1	3068.7
12.5°	2369.1	2370.7	2372.3	2436.3	2500.3	2555.1	2609.9	2685.8	2761.7	2843.6	2925.5
15°	1892.9	1919.4	1946.0	2003.0	2059.9	2142.3	2224.8	2326.7	2428.7	2558.3	2688.0
17.5°	1554.4	1565.8	1577.2	1632.0	1686.8	1764.9	1843.0	1958.5	2074.0	2241.1	2408.1
20°	1281.1	1291.4	1301.7	1341.3	1380.9	1455.7	1530.6	1640.7	1750.8	1916.2	2081.6
22.5°	1069.5	1089.6	1109.7	1136.3	1162.8	1217.1	1271.3	1383.6	1495.8	1646.6	1797.4
25°	941.5	950.8	960.0	982.8	1005.5	1057.6	1109.7	1184.0	1258.3	1408.5	1558.8
27.5°	854.8	857.5	860.2	877.0	893.8	927.4	961.1	1030.0	1098.8	1222.5	1346.2
30°	783.2	788.1	792.9	806.0	819.0	843.4	867.8	916.6	965.4	1076.1	1186.7
32.5°	727.9	730.6	733.3	744.1	755.0	772.9	790.8	829.3	867.8	952.4	1037.0
35°	680.1	680.7	681.2	689.3	697.5	714.8	732.2	764.2	796.2	858.6	920.9
37.5°	625.9	629.7	633.5	639.4	645.4	660.6	675.8	701.8	727.9	779.4	830.9
40°	580.3	583.6	586.8	593.9	600.9	612.9	624.8	648.7	672.5	717.0	761.5
42.5°	534.8	536.9	539.1	546.2	553.2	567.9	582.5	601.5	620.5	657.3	694.2
45°	483.8	489.2	494.6	502.2	509.8	522.3	534.8	554.3	573.8	605.3	636.7
47.5°	441.5	444.2	446.9	453.4	459.9	475.1	490.3	507.7	525.0	554.3	583.6
50°	399.2	400.3	401.4	407.3	413.3	426.8	440.4	460.5	480.5	507.7	534.8
52.5°	359.0	361.8	364.5	370.4	376.4	385.6	394.8	415.5	436.1	462.6	489.2
55°	322.2	323.8	325.4	329.8	334.1	344.9	355.8	373.7	391.6	416.0	440.4
57.5°	287.5	289.6	291.8	295.0	298.3	308.1	317.8	333.6	349.3	373.7	398.1
60°	251.7	254.4	257.1	260.9	264.7	272.3	279.9	294.0	308.1	329.8	351.5
62.5°	225.6	226.2	226.7	230.0	233.2	238.6	244.1	255.5	266.8	288.5	310.2
65°	196.3	198.0	199.6	201.2	202.8	207.2	211.5	221.3	231.0	247.3	263.6
67.5°	166.0	167.6	169.2	171.9	174.6	178.4	182.2	188.7	195.3	210.4	225.6
70°	129.1	129.1	129.1	133.4	137.8	144.3	150.8	155.7	160.5	173.0	185.5
72.5°	105.2	105.8	106.3	106.8	107.4	111.2	115.0	123.1	131.3	138.8	146.4
75°	85.7	86.2	86.8	87.3	87.9	88.9	90.0	92.7	95.5	104.1	112.8
77.5°	68.3	68.9	69.4	70.0	70.5	71.6	72.7	73.8	74.8	78.1	81.4
80°	52.1	52.6	53.2	53.7	54.2	54.8	55.3	56.4	57.5	59.1	60.7
82.5°	38.0	38.0	38.0	38.0	38.0	39.1	40.1	40.1	40.1	41.2	42.3
85°	23.9	23.9	23.9	24.4	24.9	24.9	24.9	25.5	26.0	26.0	26.0
87.5°	10.8	10.3	9.8	10.3	10.8	10.8	10.8	11.4	11.9	11.9	11.9
90°	13.5	14.0	13.5	13.0	13.5	12.6	12.1	11.6	11.2	11.6	10.2
92.5°	24.6	25.6	25.1	27.0	27.9	31.2	35.8	46.0	64.6	86.5	95.8
95°	53.9	55.8	59.1	63.2	72.1	88.8	113.5	167.4	223.7	275.8	245.5
97.5°	110.7	115.8	127.0	144.6	175.8	228.8	290.2	384.6	438.5	424.1	316.7
100°	291.6	291.1	309.2	343.2	390.2	456.2	510.6	548.3	532.0	440.4	297.6
102.5°	461.8	475.3	489.7	514.8	548.7	584.5	610.6	602.7	536.6	410.2	269.7
105°	591.5	593.8	608.7	626.4	647.8	659.9	651.0	604.5	507.3	373.9	247.9
107.5°	676.1	681.3	687.3	695.7	698.5	685.9	649.6	576.6	465.5	341.8	232.0
110°	724.5	725.4	726.4	722.6	709.6	677.1	618.5	532.9	426.4	315.3	223.7



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	734.3	733.8	729.2	715.7	689.2	645.0	577.6	489.7	392.5	297.6	219.0
115°	719.4	717.1	707.8	687.3	652.4	601.7	533.4	452.5	366.4	286.0	218.6
117.5°	686.8	683.6	669.6	646.8	610.6	558.0	495.3	423.6	349.2	278.1	219.0
120°	644.1	641.3	630.1	604.1	567.3	520.4	464.6	401.8	336.2	273.0	220.9
122.5°	604.1	600.3	587.8	565.0	533.4	490.6	439.9	384.6	325.5	269.7	224.1
125°	567.3	564.1	552.4	532.0	502.2	465.0	420.4	369.7	316.7	266.9	227.4
127.5°	535.7	532.9	522.2	504.6	477.6	443.2	402.2	356.2	308.3	265.5	231.1
130°	509.7	505.9	496.2	479.4	454.8	423.2	385.5	343.7	301.8	264.1	234.8
132.5°	484.1	481.8	473.4	456.7	433.9	404.1	369.7	332.0	295.8	263.7	237.6
135°	459.9	456.7	448.3	434.3	411.5	385.0	354.8	321.8	290.6	263.2	240.4
137.5°	434.3	431.5	424.6	410.2	390.6	366.9	339.9	312.0	286.0	262.3	242.3
140°	407.4	407.8	400.4	387.4	369.7	349.7	327.4	303.7	281.8	261.8	244.1
142.5°	382.3	382.7	376.2	365.0	350.6	333.9	315.3	295.8	278.1	260.9	245.5
145°	359.5	358.5	354.8	345.0	333.4	319.9	305.1	289.7	274.8	259.9	246.0
147.5°	339.9	339.5	335.7	328.8	319.5	309.7	297.2	284.6	271.6	258.6	246.0
150°	323.2	323.2	320.4	315.3	308.3	299.5	289.7	279.0	268.3	256.7	246.0
152.5°	309.2	309.2	307.8	303.2	298.1	291.1	282.7	273.9	264.6	254.4	244.6
155°	298.1	297.6	296.7	293.0	288.8	283.2	276.2	268.8	260.9	251.6	243.7
157.5°	287.4	287.4	286.5	283.7	279.9	275.3	269.7	263.2	256.7	249.3	242.3
160°	277.2	277.6	277.6	274.8	271.6	268.3	263.7	258.6	252.5	246.5	241.3
162.5°	267.9	268.3	268.3	266.0	264.1	261.3	257.2	253.0	248.3	243.7	239.5
165°	259.9	259.9	260.4	258.6	256.7	254.4	251.1	248.3	244.6	240.9	237.6
167.5°	252.0	252.0	252.5	251.1	250.2	248.3	246.5	244.1	240.9	238.1	235.8
170°	245.1	245.1	245.5	244.6	244.1	243.2	241.3	240.0	237.6	235.3	233.9
172.5°	238.6	239.0	240.0	239.0	239.0	238.6	237.2	236.2	234.4	233.0	232.5
175°	233.9	234.4	234.8	234.4	234.4	234.4	233.4	233.0	232.0	231.1	231.1
177.5°	230.7	230.7	231.6	231.1	231.6	231.6	231.1	230.7	230.2	229.7	230.2
180°	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7
2.5°	2808.9	2806.2	2780.2	2754.1	2728.6	2703.2	2684.2	2665.2	2633.2	2601.2	2581.1
5°	2983.0	2962.4	2921.2	2880.0	2818.1	2756.3	2704.2	2652.2	2586.0	2519.8	2464.5
7.5°	3080.1	3063.3	3013.4	2963.5	2881.6	2799.7	2718.3	2637.0	2539.4	2441.7	2358.2
10°	3082.8	3096.9	3055.7	3014.5	2922.3	2830.1	2719.4	2608.8	2477.5	2346.3	2238.3
12.5°	2986.3	3047.0	3038.3	3029.7	2935.8	2842.0	2707.5	2573.0	2411.9	2250.8	2115.8
15°	2805.7	2923.4	2958.1	2992.8	2915.2	2837.7	2684.7	2531.8	2342.5	2153.2	1998.1
17.5°	2573.0	2737.9	2829.5	2921.2	2864.8	2808.4	2640.8	2473.2	2260.0	2046.9	1878.2
20°	2297.5	2513.3	2657.0	2800.8	2780.2	2759.6	2586.5	2413.5	2183.6	1953.6	1770.8
22.5°	2025.2	2253.0	2451.5	2650.0	2671.2	2692.3	2517.7	2343.0	2091.4	1839.7	1653.7
25°	1790.3	2021.9	2258.4	2494.9	2542.6	2590.3	2424.4	2258.4	1997.5	1736.7	1551.7
27.5°	1566.4	1786.6	2046.9	2307.2	2394.0	2480.8	2328.9	2177.1	1905.3	1633.6	1449.2
30°	1383.6	1580.5	1846.2	2112.0	2232.9	2353.9	2214.5	2075.1	1805.5	1536.0	1355.4
32.5°	1213.3	1389.5	1656.4	1923.2	2063.7	2204.2	2083.8	1963.4	1704.1	1444.9	1266.4
35°	1078.8	1236.6	1485.5	1734.5	1891.8	2049.1	1950.3	1851.6	1598.4	1345.1	1176.4
37.5°	963.2	1095.6	1329.3	1563.1	1730.1	1897.2	1814.8	1732.3	1494.2	1256.1	1096.7
40°	867.8	974.1	1191.6	1409.1	1572.9	1736.7	1666.1	1595.6	1382.5	1169.3	1020.2
42.5°	785.9	877.5	1072.8	1268.1	1418.3	1568.5	1521.9	1475.2	1282.2	1089.1	950.8
45°	713.8	790.8	962.7	1134.6	1272.9	1411.2	1374.4	1337.5	1171.0	1004.5	877.5
47.5°	649.8	715.9	869.4	1022.9	1147.1	1271.3	1237.1	1203.0	1065.2	927.4	811.9
50°	591.2	647.6	775.6	903.6	1015.3	1127.0	1098.8	1070.6	956.7	842.8	743.0
52.5°	535.9	582.5	697.5	812.5	902.5	992.5	970.8	949.1	861.3	773.4	682.8
55°	483.2	526.1	623.2	720.3	797.3	874.3	852.6	830.9	762.6	694.2	614.5
57.5°	435.5	472.9	551.6	630.2	691.5	752.8	742.5	732.2	675.2	618.3	552.7
60°	385.1	418.7	486.5	554.3	603.7	653.0	641.1	629.1	588.5	547.8	491.4
62.5°	340.1	369.9	424.1	478.4	518.5	558.6	550.0	541.3	510.4	479.5	432.8
65°	292.9	322.2	366.1	410.0	441.5	472.9	465.3	457.8	434.4	411.1	373.7
67.5°	250.0	274.4	312.4	350.4	371.5	392.7	388.3	384.0	366.1	348.2	318.9
70°	206.6	227.8	259.3	290.7	305.4	320.0	321.6	323.2	307.0	290.7	269.0
72.5°	163.3	180.1	209.4	238.6	250.0	261.4	260.9	260.3	250.6	240.8	221.3
75°	125.3	137.8	160.5	183.3	193.1	202.8	205.0	207.2	198.0	188.7	177.9
77.5°	90.0	98.7	116.1	133.4	144.3	155.1	156.2	157.3	152.9	148.6	138.3
80°	63.5	66.2	77.0	87.9	99.3	110.6	112.3	113.9	109.6	105.2	98.7
82.5°	43.9	45.6	49.4	53.2	62.4	71.6	73.8	75.9	73.8	71.6	64.5
85°	26.6	27.1	28.7	30.4	34.7	39.1	41.2	43.4	42.3	41.2	37.4
87.5°	11.9	11.9	12.5	13.0	14.1	15.2	17.9	20.6	19.0	17.4	15.7
90°	8.8	7.4	6.0	5.1	4.2	2.8	1.9	0.9	1.9	2.8	4.2
92.5°	71.6	47.0	32.1	23.7	19.1	14.9	10.2	7.0	10.2	14.9	19.1
95°	169.3	100.0	60.5	42.3	30.2	22.3	17.2	15.8	17.2	22.3	30.2
97.5°	188.3	107.9	68.8	48.8	36.7	29.8	25.6	25.1	25.6	29.8	36.7
100°	175.3	106.5	73.9	55.8	44.6	38.1	34.9	34.4	34.9	38.1	44.6
102.5°	164.2	108.4	80.0	63.7	53.9	47.9	45.1	44.2	45.1	47.9	53.9
105°	160.0	112.1	87.0	72.5	63.7	58.1	55.3	53.9	55.3	58.1	63.7
107.5°	159.0	118.1	95.8	82.3	73.9	68.4	65.6	64.2	65.6	68.4	73.9
110°	161.4	126.0	105.1	92.1	84.2	79.1	76.7	75.3	76.7	79.1	84.2



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	166.0	133.9	114.9	102.3	94.4	89.3	87.0	85.6	87.0	89.3	94.4
115°	171.1	142.8	125.1	112.5	104.6	100.0	97.2	95.3	97.2	100.0	104.6
117.5°	177.6	152.1	134.4	122.8	113.9	109.7	107.4	105.1	107.4	109.7	113.9
120°	185.1	160.9	144.2	132.5	123.7	119.0	116.7	115.3	116.7	119.0	123.7
122.5°	192.1	170.2	153.9	141.4	133.0	127.9	125.6	124.2	125.6	127.9	133.0
125°	199.5	179.0	162.8	150.2	141.4	136.3	133.5	132.5	133.5	136.3	141.4
127.5°	205.5	186.9	171.1	158.6	148.8	143.7	140.4	139.0	140.4	143.7	148.8
130°	211.6	193.9	178.6	166.0	156.2	150.7	146.5	145.1	146.5	150.7	156.2
132.5°	217.2	200.0	185.1	173.0	163.2	156.2	151.6	149.7	151.6	156.2	163.2
135°	221.8	206.0	191.6	179.0	169.3	162.3	157.2	155.3	157.2	162.3	169.3
137.5°	225.5	210.2	196.2	184.6	174.8	167.4	162.3	160.4	162.3	167.4	174.8
140°	228.3	214.4	200.9	189.3	180.0	172.5	167.9	165.5	167.9	172.5	180.0
142.5°	231.1	217.6	204.6	193.9	184.6	178.1	173.0	171.1	173.0	178.1	184.6
145°	233.0	220.4	208.3	197.6	189.7	182.8	178.6	177.2	178.6	182.8	189.7
147.5°	234.4	222.7	211.6	202.3	194.4	188.3	184.1	183.2	184.1	188.3	194.4
150°	234.8	225.1	214.4	206.0	199.5	193.5	189.7	189.3	189.7	193.5	199.5
152.5°	235.8	226.5	217.6	209.7	204.1	199.0	195.3	195.3	195.3	199.0	204.1
155°	235.8	228.3	220.4	213.9	208.8	204.1	201.4	201.4	201.4	204.1	208.8
157.5°	236.2	229.3	222.7	217.6	213.0	208.8	206.5	206.0	206.5	208.8	213.0
160°	236.2	230.7	225.1	220.4	217.2	213.4	211.6	211.6	211.6	213.4	217.2
162.5°	235.8	231.1	226.5	222.7	220.0	217.2	215.8	215.8	215.8	217.2	220.0
165°	234.8	231.6	227.9	224.6	222.7	220.4	219.5	220.0	219.5	220.4	222.7
167.5°	234.4	231.6	228.8	226.5	225.1	223.2	222.7	223.2	222.7	223.2	225.1
170°	233.0	231.1	228.8	227.9	226.9	225.5	225.1	226.0	225.1	225.5	226.9
172.5°	232.5	231.1	229.3	228.8	228.3	227.4	227.4	227.9	227.4	227.4	228.3
175°	231.6	230.7	229.7	229.3	229.3	228.3	228.8	229.3	228.8	228.3	229.3
177.5°	231.1	230.2	229.7	229.7	229.7	229.3	229.7	230.2	229.7	229.3	229.7
180°	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7
2.5°	2561.1	2530.1	2499.2	2477.0	2454.7	2427.1	2399.4	2398.3	2397.3	2376.6	2356.0
5°	2409.2	2355.5	2301.8	2249.2	2196.6	2144.0	2091.4	2079.4	2067.5	2049.6	2031.7
7.5°	2274.7	2189.0	2103.3	2036.0	1968.8	1916.2	1863.6	1827.8	1792.0	1764.3	1736.7
10°	2130.4	2024.1	1917.8	1836.5	1755.1	1698.1	1641.2	1600.0	1558.8	1539.2	1519.7
12.5°	1980.7	1865.2	1749.7	1669.9	1590.2	1521.9	1453.5	1416.1	1378.7	1351.6	1324.5
15°	1843.0	1718.8	1594.6	1509.9	1425.3	1361.3	1297.3	1259.9	1222.5	1195.4	1168.3
17.5°	1709.5	1584.3	1459.0	1373.3	1287.6	1229.5	1171.5	1135.2	1098.8	1082.0	1065.2
20°	1588.0	1461.7	1335.3	1254.5	1173.7	1116.7	1059.8	1040.3	1020.7	1005.0	989.3
22.5°	1467.6	1346.2	1224.7	1147.1	1069.5	1028.3	987.1	971.4	955.6	943.7	931.8
25°	1366.8	1245.8	1124.9	1057.1	989.3	957.3	925.3	915.0	904.7	892.7	880.8
27.5°	1264.8	1149.8	1034.8	980.6	926.4	900.3	874.3	861.3	848.3	838.5	828.7
30°	1174.8	1068.5	962.2	917.1	872.1	849.3	826.6	812.5	798.4	789.1	779.9
32.5°	1088.0	993.6	899.2	860.7	822.2	800.0	777.8	764.2	750.6	739.8	728.9
35°	1007.7	925.8	843.9	808.7	773.4	751.2	728.9	715.4	701.8	691.0	680.1
37.5°	937.2	862.9	788.6	755.5	722.4	702.9	683.4	669.3	655.2	643.8	632.4
40°	871.0	805.4	739.8	707.8	675.8	654.6	633.5	621.0	608.5	598.2	587.9
42.5°	812.5	752.3	692.1	660.6	629.1	609.1	589.0	574.4	559.7	553.8	547.8
45°	750.6	697.5	644.3	614.0	583.6	562.4	541.3	528.8	516.3	510.9	505.5
47.5°	696.4	647.0	597.7	567.9	538.0	519.0	500.1	490.3	480.5	472.9	465.3
50°	643.2	595.5	547.8	519.0	490.3	474.0	457.8	445.8	433.9	428.5	423.0
52.5°	592.3	548.9	505.5	476.2	446.9	431.2	415.5	405.1	394.8	383.5	372.1
55°	534.8	496.8	458.8	432.8	406.8	390.5	374.2	362.3	350.4	338.4	326.5
57.5°	487.0	449.6	412.2	388.9	365.6	349.8	334.1	321.1	308.1	298.3	288.5
60°	435.0	402.4	369.9	347.1	324.3	309.1	294.0	281.5	269.0	264.1	259.3
62.5°	386.2	355.8	325.4	305.4	285.3	270.6	256.0	247.9	239.7	236.5	233.2
65°	336.3	310.2	284.2	265.8	247.3	234.8	222.4	218.6	214.8	212.1	209.4
67.5°	289.6	267.4	245.1	228.9	212.6	203.9	195.3	190.9	186.6	183.3	180.1
70°	247.3	227.8	208.3	194.2	180.1	171.9	163.8	160.0	156.2	150.2	144.3
72.5°	201.8	186.6	171.4	160.5	149.7	142.6	135.6	128.0	120.4	115.0	109.6
75°	167.0	151.9	136.7	126.4	116.1	107.9	99.8	97.1	94.4	92.7	91.1
77.5°	128.0	115.0	102.0	93.8	85.7	81.9	78.1	76.5	74.8	74.3	73.8
80°	92.2	81.4	70.5	66.2	61.8	60.7	59.7	58.6	57.5	56.9	56.4
82.5°	57.5	52.1	46.6	45.6	44.5	43.9	43.4	42.8	42.3	41.8	41.2
85°	33.6	31.5	29.3	28.7	28.2	27.7	27.1	27.1	27.1	27.1	27.1
87.5°	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	13.6	13.0
90°	5.1	6.0	7.4	8.8	10.2	11.6	11.2	11.6	12.1	12.6	13.5
92.5°	23.7	32.1	47.0	71.6	95.8	86.5	64.6	46.0	35.8	31.2	27.9
95°	42.3	60.5	100.0	169.3	245.5	275.8	223.7	167.4	113.5	88.8	72.1
97.5°	48.8	68.8	107.9	188.3	316.7	424.1	438.5	384.6	290.2	228.8	175.8
100°	55.8	73.9	106.5	175.3	297.6	440.4	532.0	548.3	510.6	456.2	390.2
102.5°	63.7	80.0	108.4	164.2	269.7	410.2	536.6	602.7	610.6	584.5	548.7
105°	72.5	87.0	112.1	160.0	247.9	373.9	507.3	604.5	651.0	659.9	647.8
107.5°	82.3	95.8	118.1	159.0	232.0	341.8	465.5	576.6	649.6	685.9	698.5
110°	92.1	105.1	126.0	161.4	223.7	315.3	426.4	532.9	618.5	677.1	709.6



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	102.3	114.9	133.9	166.0	219.0	297.6	392.5	489.7	577.6	645.0	689.2
115°	112.5	125.1	142.8	171.1	218.6	286.0	366.4	452.5	533.4	601.7	652.4
117.5°	122.8	134.4	152.1	177.6	219.0	278.1	349.2	423.6	495.3	558.0	610.6
120°	132.5	144.2	160.9	185.1	220.9	273.0	336.2	401.8	464.6	520.4	567.3
122.5°	141.4	153.9	170.2	192.1	224.1	269.7	325.5	384.6	439.9	490.6	533.4
125°	150.2	162.8	179.0	199.5	227.4	266.9	316.7	369.7	420.4	465.0	502.2
127.5°	158.6	171.1	186.9	205.5	231.1	265.5	308.3	356.2	402.2	443.2	477.6
130°	166.0	178.6	193.9	211.6	234.8	264.1	301.8	343.7	385.5	423.2	454.8
132.5°	173.0	185.1	200.0	217.2	237.6	263.7	295.8	332.0	369.7	404.1	433.9
135°	179.0	191.6	206.0	221.8	240.4	263.2	290.6	321.8	354.8	385.0	411.5
137.5°	184.6	196.2	210.2	225.5	242.3	262.3	286.0	312.0	339.9	366.9	390.6
140°	189.3	200.9	214.4	228.3	244.1	261.8	281.8	303.7	327.4	349.7	369.7
142.5°	193.9	204.6	217.6	231.1	245.5	260.9	278.1	295.8	315.3	333.9	350.6
145°	197.6	208.3	220.4	233.0	246.0	259.9	274.8	289.7	305.1	319.9	333.4
147.5°	202.3	211.6	222.7	234.4	246.0	258.6	271.6	284.6	297.2	309.7	319.5
150°	206.0	214.4	225.1	234.8	246.0	256.7	268.3	279.0	289.7	299.5	308.3
152.5°	209.7	217.6	226.5	235.8	244.6	254.4	264.6	273.9	282.7	291.1	298.1
155°	213.9	220.4	228.3	235.8	243.7	251.6	260.9	268.8	276.2	283.2	288.8
157.5°	217.6	222.7	229.3	236.2	242.3	249.3	256.7	263.2	269.7	275.3	279.9
160°	220.4	225.1	230.7	236.2	241.3	246.5	252.5	258.6	263.7	268.3	271.6
162.5°	222.7	226.5	231.1	235.8	239.5	243.7	248.3	253.0	257.2	261.3	264.1
165°	224.6	227.9	231.6	234.8	237.6	240.9	244.6	248.3	251.1	254.4	256.7
167.5°	226.5	228.8	231.6	234.4	235.8	238.1	240.9	244.1	246.5	248.3	250.2
170°	227.9	228.8	231.1	233.0	233.9	235.3	237.6	240.0	241.3	243.2	244.1
172.5°	228.8	229.3	231.1	232.5	232.5	233.0	234.4	236.2	237.2	238.6	239.0
175°	229.3	229.7	230.7	231.6	231.1	231.1	232.0	233.0	233.4	234.4	234.4
177.5°	229.7	229.7	230.2	231.1	230.2	229.7	230.2	230.7	231.1	231.6	231.6
180°	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7	229.7



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2645.7	2645.7	2645.7	2645.7
2.5°	2350.6	2345.2	2343.0	2340.9
5°	2014.9	1998.1	1994.3	1990.5
7.5°	1729.6	1722.6	1699.2	1675.9
10°	1498.0	1476.3	1466.6	1456.8
12.5°	1304.4	1284.3	1281.1	1277.8
15°	1154.2	1140.1	1135.2	1130.3
17.5°	1055.4	1045.7	1039.7	1033.7
20°	982.2	975.2	970.8	966.5
22.5°	926.4	920.9	917.7	914.4
25°	872.7	864.5	861.8	859.1
27.5°	821.7	814.6	811.9	809.2
30°	774.0	768.0	764.2	760.4
32.5°	721.9	714.8	712.7	710.5
35°	675.8	671.4	669.3	667.1
37.5°	627.0	621.6	618.3	615.0
40°	585.2	582.5	580.9	579.2
42.5°	542.9	538.0	537.5	536.9
45°	500.6	495.7	494.6	493.6
47.5°	461.0	456.7	456.1	455.6
50°	417.1	411.1	406.8	402.4
52.5°	366.6	361.2	357.4	353.6
55°	320.5	314.6	311.3	308.1
57.5°	285.8	283.1	281.5	279.9
60°	257.6	256.0	254.9	253.8
62.5°	231.6	230.0	230.0	230.0
65°	207.7	206.1	204.5	202.8
67.5°	176.8	173.6	173.0	172.5
70°	139.4	134.5	134.0	133.4
72.5°	109.0	108.5	107.4	106.3
75°	90.0	88.9	88.9	88.9
77.5°	72.7	71.6	71.6	71.6
80°	55.9	55.3	55.9	56.4
82.5°	41.2	41.2	40.7	40.1
85°	26.6	26.0	26.0	26.0
87.5°	13.0	13.0	13.0	13.0
90°	13.0	13.5	14.0	13.5
92.5°	27.0	25.1	25.6	24.6
95°	63.2	59.1	55.8	53.9
97.5°	144.6	127.0	115.8	110.7
100°	343.2	309.2	291.1	291.6
102.5°	514.8	489.7	475.3	461.8
105°	626.4	608.7	593.8	591.5
107.5°	695.7	687.3	681.3	676.1
110°	722.6	726.4	725.4	724.5



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	715.7	729.2	733.8	734.3
115°	687.3	707.8	717.1	719.4
117.5°	646.8	669.6	683.6	686.8
120°	604.1	630.1	641.3	644.1
122.5°	565.0	587.8	600.3	604.1
125°	532.0	552.4	564.1	567.3
127.5°	504.6	522.2	532.9	535.7
130°	479.4	496.2	505.9	509.7
132.5°	456.7	473.4	481.8	484.1
135°	434.3	448.3	456.7	459.9
137.5°	410.2	424.6	431.5	434.3
140°	387.4	400.4	407.8	407.4
142.5°	365.0	376.2	382.7	382.3
145°	345.0	354.8	358.5	359.5
147.5°	328.8	335.7	339.5	339.9
150°	315.3	320.4	323.2	323.2
152.5°	303.2	307.8	309.2	309.2
155°	293.0	296.7	297.6	298.1
157.5°	283.7	286.5	287.4	287.4
160°	274.8	277.6	277.6	277.2
162.5°	266.0	268.3	268.3	267.9
165°	258.6	260.4	259.9	259.9
167.5°	251.1	252.5	252.0	252.0
170°	244.6	245.5	245.1	245.1
172.5°	239.0	240.0	239.0	238.6
175°	234.4	234.8	234.4	233.9
177.5°	231.1	231.6	230.7	230.7
180°	229.7	229.7	229.7	229.7



TEST NUMBER: P831863

CATALOG NUMBER: S123RDIP-S1000D585U930-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.85	14.81	14.66	15.63	16.64	18.52	19.47	19.33	20.30	21.31
	3H	15.08	15.94	15.91	16.77	17.81	20.03	20.88	20.85	21.71	22.75
	4H	15.47	16.28	16.31	17.12	18.17	20.52	21.33	21.36	22.17	23.22
	6H	15.76	16.50	16.61	17.35	18.41	20.84	21.58	21.69	22.43	23.49
	8H	15.85	16.55	16.71	17.42	18.48	20.92	21.63	21.78	22.49	23.56
	12H	15.91	16.58	16.77	17.43	18.52	20.96	21.63	21.82	22.49	23.58
4H	2H	14.59	15.40	15.43	16.24	17.29	18.53	19.33	19.37	20.17	21.22
	3H	15.97	16.64	16.83	17.51	18.58	20.20	20.86	21.05	21.74	22.80
	4H	16.43	17.04	17.30	17.91	19.00	20.81	21.41	21.67	22.28	23.38
	6H	16.81	17.33	17.69	18.22	19.32	21.25	21.77	22.13	22.67	23.77
	8H	16.93	17.42	17.82	18.31	19.42	21.39	21.87	22.27	22.76	23.87
	12H	17.01	17.45	17.92	18.36	19.47	21.45	21.89	22.36	22.80	23.91
8H	4H	16.75	17.24	17.64	18.13	19.24	20.78	21.27	21.67	22.16	23.27
	6H	17.22	17.62	18.13	18.55	19.66	21.28	21.69	22.20	22.62	23.73
	8H	17.42	17.77	18.34	18.70	19.82	21.47	21.83	22.39	22.75	23.88
	12H	17.56	17.87	18.48	18.79	19.97	21.59	21.90	22.51	22.82	24.00
12H	4H	16.77	17.21	17.67	18.12	19.23	20.74	21.18	21.64	22.09	23.20
	6H	17.28	17.64	18.20	18.56	19.69	21.26	21.61	22.18	22.54	23.67
	8H	17.50	17.82	18.43	18.73	19.91	21.46	21.77	22.38	22.69	23.86