

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331973-927

Luminaire Tested: **S123DIP-S775D805U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331973-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D805U927-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5128.0 lumens  
Efficiency: N/A  
Efficacy: 111.7 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	57	57	57	50					50			
1	98	94	90	87	90	87	84	81	74	71	69	62	60	58	50	49	48	43					43			
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	45	43	41	36					36			
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31					31			
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	30	27					27			
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	23					23			
6	63	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	24	21					21			
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	23	21	18					18			
8	54	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	16					16			
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15					15			
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13					13			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9214	9214	9214	9214
5°	10988	9253	8200	9253
10°	13753	9206	7406	9206
15°	16868	9132	6896	9132
20°	20095	9016	6565	9016
25°	21338	8875	6492	8875
30°	18288	8772	6527	8772
35°	12720	8627	6594	8627
40°	9580	8455	6573	8455
45°	7954	8202	6491	8202
50°	7125	7681	6430	7681
55°	6662	7122	6351	7122
60°	6250	6536	6286	6536
65°	5873	5957	6082	5957
70°	5508	5297	5794	5297
75°	4932	4637	5311	4637
80°	4320	3806	4575	3806
85°	3384	2766	3075	2766



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.3	1.6
10°-20°	270.4	5.3
20°-30°	453.8	8.8
30°-40°	513.8	10.0
40°-50°	460.8	9.0
50°-60°	371.8	7.3
60°-70°	259.1	5.1
70°-80°	136.2	2.7
80°-90°	35.6	0.7
90°-100°	30.3	0.6
100°-110°	144.4	2.8
110°-120°	347.0	6.8
120°-130°	441.8	8.6
130°-140°	472.1	9.2
140°-150°	441.4	8.6
150°-160°	356.1	6.9
160°-170°	229.8	4.5
170°-180°	79.2	1.5
0°-30°	808.5	15.8
0°-40°	1322.3	25.8
0°-60°	2154.9	42.0
0°-90°	2585.9	50.4
90°-120°	521.7	10.2
90°-150°	1877.0	36.6
90°-180°	2542.0	49.6
0°-180°	5128.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	856	856	856	856	856	
5°	1017	856	759	856	1017	105
15°	1514	820	619	820	1514	437
25°	1797	747	547	747	1797	788
35°	968	656	502	656	968	629
45°	522	539	426	539	522	413
55°	355	380	338	380	355	319
65°	231	234	239	234	231	230
75°	119	112	128	112	119	127
85°	27	22	25	22	27	33
90°	19	1	19	1	19	10
95°	24	38	24	38	24	20
105°	27	185	27	185	27	62
115°	364	346	364	346	364	337
125°	498	488	498	488	498	445
135°	614	608	614	608	614	473
145°	708	701	708	701	708	442
155°	771	772	771	772	771	356
165°	812	814	812	814	812	229
175°	830	834	830	834	830	79
180°	834	834	834	834	834	



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	908.4	907.8	906.1	907.4	904.8	901.1	900.8	897.5	887.8	887.2	884.6
5°	1016.9	1013.6	1013.2	1012.7	1006.9	999.1	984.1	982.9	963.0	953.0	941.0
7.5°	1157.4	1159.1	1153.1	1147.8	1130.0	1118.3	1102.3	1081.8	1057.4	1032.6	1016.1
10°	1258.3	1271.9	1255.0	1243.3	1232.6	1212.2	1188.6	1159.1	1129.7	1095.3	1069.1
12.5°	1366.4	1373.2	1369.8	1358.8	1342.0	1311.1	1269.2	1236.8	1209.7	1152.3	1129.2
15°	1513.7	1539.1	1522.9	1485.5	1486.4	1456.9	1402.2	1342.0	1310.1	1259.9	1191.5
17.5°	1670.6	1673.8	1666.9	1635.9	1615.1	1574.6	1524.1	1466.5	1401.8	1341.0	1268.4
20°	1754.3	1751.8	1737.3	1721.1	1685.4	1653.9	1598.8	1534.5	1451.5	1391.8	1312.6
22.5°	1800.7	1796.6	1789.7	1776.2	1746.4	1712.6	1663.1	1592.8	1513.9	1431.6	1340.1
25°	1796.6	1802.0	1802.8	1799.0	1788.7	1768.4	1729.4	1673.4	1594.6	1488.8	1393.4
27.5°	1634.0	1641.6	1663.8	1683.5	1705.4	1727.8	1724.8	1697.0	1638.7	1547.4	1430.8
30°	1471.4	1454.8	1495.9	1547.8	1583.0	1645.2	1680.1	1682.1	1649.3	1571.0	1457.3
32.5°	1245.8	1264.1	1282.2	1346.0	1423.1	1492.9	1562.3	1618.1	1624.4	1572.3	1472.9
35°	968.0	990.8	1024.0	1057.1	1140.1	1211.4	1333.3	1439.5	1524.1	1535.3	1474.3
37.5°	780.0	791.3	812.3	845.5	899.8	984.4	1078.7	1212.9	1335.5	1426.6	1430.6
40°	681.8	685.2	708.8	734.0	778.0	847.7	932.7	1051.3	1198.1	1325.5	1378.6
42.5°	608.2	615.4	625.5	649.7	684.8	737.2	816.3	914.3	1048.8	1195.4	1299.3
45°	522.5	530.8	537.1	553.3	578.1	613.4	668.5	758.1	860.5	1011.9	1151.7
47.5°	466.0	466.7	471.3	483.5	500.4	526.9	565.9	623.4	717.5	840.2	983.7
50°	425.5	432.1	433.8	443.3	456.6	476.1	508.4	557.4	634.5	742.4	874.3
52.5°	397.0	398.9	403.6	410.5	422.1	437.3	465.3	503.7	564.2	656.1	777.4
55°	355.0	355.0	359.6	365.0	371.6	385.2	403.9	432.1	478.2	549.5	649.9
57.5°	316.2	318.2	321.5	323.1	328.8	337.9	353.4	374.9	409.2	464.1	543.8
60°	290.3	294.1	293.7	296.9	301.9	309.0	322.3	339.7	370.3	414.3	481.5
62.5°	267.8	267.5	267.4	271.4	276.4	283.1	291.7	306.8	332.9	371.9	429.0
65°	230.6	229.7	232.7	235.1	236.8	241.8	248.4	261.7	279.1	308.2	352.5
67.5°	197.6	195.2	196.8	197.6	200.4	204.3	210.5	218.7	232.6	255.9	289.3
70°	175.0	172.9	172.5	173.3	175.9	178.7	183.3	191.2	204.1	222.7	247.2
72.5°	151.8	150.4	150.3	152.1	153.3	155.2	158.4	165.6	175.9	189.9	212.7
75°	118.6	118.6	118.6	119.0	120.3	121.9	124.5	128.2	136.0	146.0	161.3
77.5°	88.9	88.8	88.3	88.2	90.1	90.9	91.4	94.9	99.3	106.0	117.2
80°	69.7	67.6	68.4	69.7	70.5	70.9	72.2	73.0	76.8	80.5	88.3
82.5°	51.7	50.0	50.1	52.1	52.3	52.7	53.9	55.1	56.5	59.9	64.1
85°	27.4	27.4	27.8	27.8	28.2	27.8	29.0	29.5	29.5	31.5	34.0
87.5°	13.7	12.9	13.2	13.5	13.2	13.4	13.6	13.8	14.0	14.3	14.3
90°	18.6	18.3	18.1	17.7	17.5	17.0	16.5	16.0	15.4	14.9	13.1
92.5°	20.6	20.4	20.2	20.0	19.9	19.4	18.5	17.6	16.7	15.8	14.5
95°	23.5	23.5	23.5	23.5	23.5	23.1	22.1	21.2	20.2	19.2	17.7
97.5°	25.5	25.3	25.3	25.1	25.0	24.3	23.2	22.2	21.1	20.0	29.9
100°	26.0	25.9	25.7	25.6	25.4	24.9	23.8	22.7	21.5	20.4	41.9
102.5°	26.5	26.2	26.0	25.7	25.5	27.1	30.5	33.9	37.3	40.7	64.2
105°	27.3	27.0	26.7	26.5	26.1	38.2	62.6	86.9	111.3	135.6	148.0
107.5°	85.6	103.9	122.3	140.7	159.0	177.1	195.0	212.9	230.8	248.6	246.6
110°	170.3	190.0	209.7	229.3	249.1	261.2	265.7	270.2	274.8	279.3	277.8



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.2	296.4	300.5	304.7	308.8	310.9	310.8	310.7	310.6	310.5	309.0
115°	364.2	363.6	363.1	362.5	361.9	361.0	359.7	358.2	356.9	355.5	354.3
117.5°	404.6	404.4	404.3	404.3	404.1	403.5	402.4	401.3	400.2	399.1	398.5
120°	432.3	432.3	432.3	432.3	432.3	431.7	430.6	429.5	428.4	427.3	426.9
122.5°	459.5	459.5	459.3	459.2	459.1	458.7	457.9	457.1	456.4	455.6	455.0
125°	498.0	497.6	497.4	497.1	496.9	496.5	496.3	496.0	495.7	495.4	494.9
127.5°	534.9	535.1	535.4	535.7	535.9	535.8	535.4	535.0	534.6	534.1	533.5
130°	558.6	558.9	559.2	559.4	559.8	559.6	559.0	558.5	557.9	557.4	556.8
132.5°	580.4	580.8	581.2	581.6	581.9	581.9	581.3	580.7	580.3	579.7	579.2
135°	613.8	614.2	614.6	615.0	615.4	615.4	615.0	614.6	614.2	613.8	613.2
137.5°	645.1	645.4	645.6	645.9	646.2	646.0	645.3	644.7	644.0	643.3	643.0
140°	663.9	664.2	664.5	664.7	665.0	664.9	664.3	663.8	663.2	662.7	662.3
142.5°	681.3	681.7	682.0	682.4	682.8	682.8	682.3	681.9	681.4	681.0	680.6
145°	707.9	707.9	707.9	707.9	707.9	707.7	707.5	707.2	706.9	706.6	706.4
147.5°	727.7	728.3	729.0	729.6	730.2	730.4	730.2	729.8	729.6	729.3	729.0
150°	742.6	743.0	743.4	743.8	744.3	744.3	744.0	743.7	743.5	743.2	742.9
152.5°	754.5	755.1	755.7	756.4	757.0	757.1	756.5	756.1	755.6	755.1	754.9
155°	771.0	771.9	772.7	773.6	774.4	774.4	773.7	773.1	772.4	771.7	771.5
157.5°	785.1	786.2	787.2	788.3	789.3	789.5	788.6	787.8	787.0	786.2	786.3
160°	794.0	795.0	795.9	796.9	797.8	797.9	797.1	796.2	795.4	794.6	794.7
162.5°	802.4	803.3	804.1	804.9	805.8	805.7	804.9	803.9	803.0	802.0	802.2
165°	812.5	813.5	814.4	815.5	816.4	816.3	815.2	814.1	813.0	811.9	812.1
167.5°	819.8	820.9	822.0	823.2	824.3	824.3	823.2	822.0	820.9	819.8	819.8
170°	824.3	825.5	826.5	827.6	828.7	828.7	827.6	826.5	825.5	824.3	824.3
172.5°	826.8	828.0	829.3	830.4	831.6	831.7	830.6	829.5	828.4	827.3	827.2
175°	830.5	831.6	832.7	833.9	834.9	835.0	834.0	833.1	832.1	831.2	831.0
177.5°	831.6	832.7	833.9	835.0	836.1	836.1	835.3	834.4	833.5	832.6	832.5
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	882.5	879.9	877.2	872.6	868.6	862.9	861.3	859.3	853.3	848.0	844.1
5°	936.4	926.5	912.0	898.7	888.0	873.4	865.1	856.4	844.0	832.7	823.6
7.5°	992.8	973.3	950.7	926.3	903.6	881.7	864.0	848.3	830.8	814.4	801.5
10°	1037.6	1009.4	977.9	943.9	914.9	886.7	863.0	842.3	819.9	800.4	784.3
12.5°	1088.7	1046.9	1003.5	962.2	927.8	888.7	860.1	833.7	808.3	784.8	766.7
15°	1149.2	1096.1	1044.7	987.9	935.6	886.7	852.7	819.5	790.0	766.0	742.8
17.5°	1204.3	1144.1	1076.3	1007.3	944.2	886.2	838.6	801.1	764.2	734.8	711.7
20°	1235.5	1167.0	1090.3	1018.6	948.9	884.2	831.9	787.1	747.3	716.2	690.1
22.5°	1262.3	1182.3	1102.9	1026.2	948.6	878.8	819.7	773.6	730.4	700.0	672.2
25°	1290.2	1194.4	1114.8	1024.8	938.1	865.9	799.5	747.3	704.2	668.5	639.9
27.5°	1314.1	1193.6	1099.1	1002.3	921.7	849.4	778.5	722.5	676.7	637.9	608.9
30°	1330.0	1195.2	1082.8	987.1	905.8	831.1	762.2	705.8	657.7	618.4	591.0
32.5°	1340.0	1194.2	1067.9	965.8	880.5	814.5	744.7	686.3	636.8	598.1	571.7
35°	1345.8	1186.9	1042.2	921.9	839.8	775.5	717.1	656.5	604.7	568.5	538.8
37.5°	1334.2	1171.6	1012.3	879.6	789.7	726.4	677.2	625.7	576.1	536.3	510.6
40°	1315.9	1161.7	989.1	849.8	755.2	694.3	652.4	601.7	552.8	515.1	491.0
42.5°	1281.0	1141.4	963.5	816.6	719.4	658.4	619.9	577.6	531.2	495.8	471.8
45°	1196.0	1097.3	925.3	766.8	666.5	603.4	569.4	538.8	496.9	462.4	441.6
47.5°	1078.1	1031.1	869.8	714.3	611.2	550.6	515.2	490.5	459.9	432.1	412.3
50°	996.2	976.7	832.3	678.5	574.4	515.1	481.1	458.7	436.7	408.9	390.7
52.5°	901.6	913.6	788.5	641.4	536.9	478.6	446.6	428.8	408.8	386.0	370.1
55°	768.5	812.0	712.9	578.9	481.1	425.5	395.2	379.5	367.9	350.9	337.2
57.5°	643.8	699.3	631.1	514.7	426.3	378.3	349.3	332.1	324.6	315.8	305.0
60°	569.8	624.6	572.7	471.5	389.4	343.8	318.1	303.6	296.1	289.9	280.7
62.5°	503.8	559.2	515.6	427.8	353.2	310.9	288.6	274.4	268.5	265.3	257.5
65°	413.0	460.7	431.7	359.6	301.5	264.2	243.8	233.9	228.5	227.3	222.3
67.5°	336.2	372.5	351.3	298.3	252.5	220.3	203.0	194.6	190.4	190.0	186.3
70°	285.7	319.7	303.6	255.5	216.1	190.8	175.9	168.3	165.9	165.5	163.4
72.5°	246.6	270.3	257.5	217.3	186.9	163.9	153.0	145.1	142.4	142.9	141.5
75°	182.4	200.3	192.8	165.1	140.6	125.6	116.5	111.5	109.1	110.4	108.7
77.5°	131.3	142.6	135.9	116.6	101.6	90.7	84.1	81.0	78.7	78.7	77.9
80°	99.1	105.8	102.0	90.4	78.0	68.8	63.5	61.4	60.1	59.7	59.3
82.5°	70.6	76.2	71.9	63.8	55.4	49.9	46.9	44.1	43.3	43.5	43.0
85°	35.6	37.7	36.0	31.1	27.8	25.3	23.6	22.4	21.5	21.9	21.2
87.5°	14.5	14.5	13.2	11.5	10.5	9.3	9.0	8.1	7.7	8.0	7.9
90°	11.2	9.5	7.7	6.1	4.8	3.4	2.0	0.6	2.0	3.4	4.8
92.5°	13.2	11.8	10.5	10.0	10.4	10.8	11.2	11.5	11.2	10.8	10.4
95°	16.2	14.7	13.2	15.2	20.8	26.5	32.2	37.8	32.2	26.5	20.8
97.5°	39.8	49.7	59.6	65.8	68.4	70.9	73.4	75.9	73.4	70.9	68.4
100°	63.4	84.8	106.3	115.7	112.9	110.2	107.4	104.6	107.4	110.2	112.9
102.5°	87.6	111.1	134.6	145.3	143.3	141.3	139.3	137.4	139.3	141.3	143.3
105°	160.4	172.8	185.2	190.6	189.1	187.6	186.1	184.6	186.1	187.6	189.1
107.5°	244.7	242.7	240.7	239.2	238.0	236.8	235.6	234.3	235.6	236.8	238.0
110°	276.3	274.8	273.2	272.0	270.8	269.7	268.6	267.5	268.6	269.7	270.8





TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	307.5	306.0	304.4	303.2	302.2	301.3	300.2	299.3	300.2	301.3	302.2
115°	353.0	351.8	350.5	349.5	348.7	347.8	347.1	346.2	347.1	347.8	348.7
117.5°	397.8	397.2	396.6	395.7	394.7	393.7	392.7	391.7	392.7	393.7	394.7
120°	426.5	426.1	425.7	424.8	423.6	422.4	421.1	419.9	421.1	422.4	423.6
122.5°	454.6	454.0	453.4	452.7	451.7	450.7	449.6	448.6	449.6	450.7	451.7
125°	494.3	493.8	493.3	492.4	491.3	490.2	489.1	488.1	489.1	490.2	491.3
127.5°	532.8	532.1	531.5	530.6	529.5	528.4	527.3	526.2	527.3	528.4	529.5
130°	556.3	555.7	555.2	554.4	553.3	552.2	551.0	549.9	551.0	552.2	553.3
132.5°	578.8	578.4	577.9	577.2	576.1	575.0	573.9	572.7	573.9	575.0	576.1
135°	612.7	612.1	611.6	610.9	610.1	609.2	608.4	607.5	608.4	609.2	610.1
137.5°	642.8	642.5	642.1	641.4	640.4	639.4	638.3	637.3	638.3	639.4	640.4
140°	661.9	661.5	661.0	660.4	659.6	658.8	657.9	657.1	657.9	658.8	659.6
142.5°	680.2	679.8	679.4	678.7	677.9	677.1	676.3	675.4	676.3	677.1	677.9
145°	706.1	705.8	705.5	705.0	703.9	703.0	702.0	701.1	702.0	703.0	703.9
147.5°	728.7	728.5	728.3	727.8	727.1	726.5	725.9	725.2	725.9	726.5	727.1
150°	742.7	742.4	742.1	741.7	741.3	740.9	740.5	740.1	740.5	740.9	741.3
152.5°	754.7	754.6	754.4	754.2	754.1	753.8	753.7	753.4	753.7	753.8	754.1
155°	771.4	771.3	771.1	771.2	771.5	771.7	772.1	772.3	772.1	771.7	771.5
157.5°	786.5	786.6	786.7	786.8	786.8	786.9	786.9	786.9	786.9	786.9	786.8
160°	794.9	795.0	795.1	795.3	795.4	795.6	795.7	795.8	795.7	795.6	795.4
162.5°	802.3	802.4	802.6	802.8	803.2	803.5	803.9	804.2	803.9	803.5	803.2
165°	812.2	812.4	812.5	812.8	813.2	813.6	814.0	814.4	814.0	813.6	813.2
167.5°	819.8	819.8	819.8	820.1	820.7	821.3	821.8	822.4	821.8	821.3	820.7
170°	824.3	824.3	824.3	824.6	825.1	825.7	826.2	826.8	826.2	825.7	825.1
172.5°	827.0	827.0	826.9	827.1	827.8	828.5	829.1	829.7	829.1	828.5	827.8
175°	830.8	830.7	830.6	830.8	831.6	832.3	832.9	833.6	832.9	832.3	831.6
177.5°	832.4	832.3	832.2	832.4	833.0	833.5	834.1	834.6	834.1	833.5	833.0
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	841.7	839.4	836.1	831.1	827.1	820.8	820.8	821.8	821.8	821.5	820.8
5°	816.2	809.9	802.5	793.8	784.7	775.5	773.9	770.6	768.1	766.4	764.3
7.5°	789.3	778.2	767.3	755.1	744.0	734.8	728.4	723.1	719.7	716.1	713.4
10°	771.0	757.2	744.4	731.6	717.5	706.3	699.3	694.3	690.5	687.2	685.6
12.5°	749.4	733.7	719.5	707.3	691.9	680.4	673.7	671.4	666.9	660.0	656.3
15°	717.9	703.4	686.3	667.7	660.2	646.1	638.3	634.5	632.0	626.6	625.0
17.5°	690.9	671.9	652.8	638.9	625.0	613.6	609.2	604.6	601.3	596.8	595.6
20°	669.4	652.4	634.9	620.0	605.5	593.0	589.3	586.0	582.7	580.6	578.9
22.5°	647.5	630.5	616.0	602.1	586.6	578.5	574.4	570.8	568.4	567.0	565.4
25°	616.7	601.7	585.6	573.1	560.7	555.3	552.8	550.7	549.1	547.0	546.6
27.5°	589.1	572.9	559.8	548.2	539.2	534.7	532.3	531.3	531.7	532.4	532.9
30°	568.5	553.7	542.9	532.9	524.7	520.5	520.1	520.1	521.7	522.1	523.0
32.5°	549.7	537.4	526.6	517.0	510.7	507.9	509.5	509.5	510.8	511.8	513.3
35°	522.1	511.4	503.0	494.8	489.4	490.6	491.5	492.3	494.3	496.9	498.5
37.5°	495.8	486.5	477.8	471.3	468.9	471.1	473.1	474.8	477.3	479.2	480.9
40°	476.9	469.8	461.6	455.7	456.6	457.9	459.5	461.6	463.7	464.9	466.6
42.5°	459.3	451.9	445.7	440.8	442.0	443.6	444.6	445.7	448.1	450.3	451.3
45°	432.5	426.7	421.0	418.0	418.9	419.7	420.5	421.8	423.8	425.5	426.0
47.5°	402.4	398.4	394.5	391.7	393.0	392.7	393.7	396.4	397.0	398.1	400.4
50°	383.2	379.5	374.9	374.1	374.1	374.1	374.5	377.8	377.8	379.5	381.1
52.5°	361.9	359.6	356.6	355.1	354.5	354.5	356.2	357.9	358.5	360.9	362.6
55°	330.5	328.0	325.6	324.3	323.4	324.3	327.6	328.4	330.5	331.8	333.0
57.5°	297.8	295.9	293.9	293.2	293.0	294.1	296.0	298.4	299.0	302.8	304.7
60°	276.2	273.3	271.6	271.6	270.8	274.6	273.7	277.9	278.7	281.1	284.1
62.5°	254.0	250.1	249.4	249.4	250.6	251.7	252.8	254.6	256.8	259.9	262.2
65°	218.2	216.1	219.0	218.6	217.7	220.2	220.2	222.3	224.7	227.7	232.3
67.5°	184.2	183.2	183.4	183.4	184.7	186.1	187.2	189.0	192.0	195.1	198.0
70°	161.3	162.6	160.5	162.2	163.4	163.8	164.6	167.2	170.5	172.5	175.9
72.5°	139.1	139.0	139.3	139.9	141.2	141.9	142.8	145.6	149.2	151.0	153.6
75°	107.0	106.5	107.8	107.8	109.9	110.7	111.5	112.8	116.1	118.6	120.6
77.5°	78.1	78.7	78.3	79.8	79.2	79.4	81.9	83.2	83.5	88.4	89.5
80°	58.9	59.7	60.1	60.5	61.0	60.1	63.1	64.2	64.2	67.2	69.2
82.5°	42.3	42.8	43.9	44.3	44.4	45.2	45.5	46.3	47.4	48.6	51.3
85°	21.2	22.4	22.8	22.4	22.8	21.9	23.2	23.6	24.1	24.1	24.1
87.5°	7.8	8.5	8.6	9.2	9.3	9.9	10.1	9.5	9.6	10.7	9.5
90°	6.1	7.7	9.5	11.2	13.1	14.9	15.4	16.0	16.5	17.0	17.5
92.5°	10.0	10.5	11.8	13.2	14.5	15.8	16.7	17.6	18.5	19.4	19.9
95°	15.2	13.2	14.7	16.2	17.7	19.2	20.2	21.2	22.1	23.1	23.5
97.5°	65.8	59.6	49.7	39.8	29.9	20.0	21.1	22.2	23.2	24.3	25.0
100°	115.7	106.3	84.8	63.4	41.9	20.4	21.5	22.7	23.8	24.9	25.4
102.5°	145.3	134.6	111.1	87.6	64.2	40.7	37.3	33.9	30.5	27.1	25.5
105°	190.6	185.2	172.8	160.4	148.0	135.6	111.3	86.9	62.6	38.2	26.1
107.5°	239.2	240.7	242.7	244.7	246.6	248.6	230.8	212.9	195.0	177.1	159.0
110°	272.0	273.2	274.8	276.3	277.8	279.3	274.8	270.2	265.7	261.2	249.1



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	303.2	304.4	306.0	307.5	309.0	310.5	310.6	310.7	310.8	310.9	308.8
115°	349.5	350.5	351.8	353.0	354.3	355.5	356.9	358.2	359.7	361.0	361.9
117.5°	395.7	396.6	397.2	397.8	398.5	399.1	400.2	401.3	402.4	403.5	404.1
120°	424.8	425.7	426.1	426.5	426.9	427.3	428.4	429.5	430.6	431.7	432.3
122.5°	452.7	453.4	454.0	454.6	455.0	455.6	456.4	457.1	457.9	458.7	459.1
125°	492.4	493.3	493.8	494.3	494.9	495.4	495.7	496.0	496.3	496.5	496.9
127.5°	530.6	531.5	532.1	532.8	533.5	534.1	534.6	535.0	535.4	535.8	535.9
130°	554.4	555.2	555.7	556.3	556.8	557.4	557.9	558.5	559.0	559.6	559.8
132.5°	577.2	577.9	578.4	578.8	579.2	579.7	580.3	580.7	581.3	581.9	581.9
135°	610.9	611.6	612.1	612.7	613.2	613.8	614.2	614.6	615.0	615.4	615.4
137.5°	641.4	642.1	642.5	642.8	643.0	643.3	644.0	644.7	645.3	646.0	646.2
140°	660.4	661.0	661.5	661.9	662.3	662.7	663.2	663.8	664.3	664.9	665.0
142.5°	678.7	679.4	679.8	680.2	680.6	681.0	681.4	681.9	682.3	682.8	682.8
145°	705.0	705.5	705.8	706.1	706.4	706.6	706.9	707.2	707.5	707.7	707.9
147.5°	727.8	728.3	728.5	728.7	729.0	729.3	729.6	729.8	730.2	730.4	730.2
150°	741.7	742.1	742.4	742.7	742.9	743.2	743.5	743.7	744.0	744.3	744.3
152.5°	754.2	754.4	754.6	754.7	754.9	755.1	755.6	756.1	756.5	757.1	757.0
155°	771.2	771.1	771.3	771.4	771.5	771.7	772.4	773.1	773.7	774.4	774.4
157.5°	786.8	786.7	786.6	786.5	786.3	786.2	787.0	787.8	788.6	789.5	789.3
160°	795.3	795.1	795.0	794.9	794.7	794.6	795.4	796.2	797.1	797.9	797.8
162.5°	802.8	802.6	802.4	802.3	802.2	802.0	803.0	803.9	804.9	805.7	805.8
165°	812.8	812.5	812.4	812.2	812.1	811.9	813.0	814.1	815.2	816.3	816.4
167.5°	820.1	819.8	819.8	819.8	819.8	819.8	820.9	822.0	823.2	824.3	824.3
170°	824.6	824.3	824.3	824.3	824.3	824.3	825.5	826.5	827.6	828.7	828.7
172.5°	827.1	826.9	827.0	827.0	827.2	827.3	828.4	829.5	830.6	831.7	831.6
175°	830.8	830.6	830.7	830.8	831.0	831.2	832.1	833.1	834.0	835.0	834.9
177.5°	832.4	832.2	832.3	832.4	832.5	832.6	833.5	834.4	835.3	836.1	836.1
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	818.5	818.2	820.5	818.8	820.5	818.2	818.5	820.8	821.5	821.8	821.8
5°	761.8	763.1	758.9	758.9	758.9	763.1	761.8	764.3	766.4	768.1	770.6
7.5°	711.4	709.6	709.7	707.5	709.7	709.6	711.4	713.4	716.1	719.7	723.1
10°	680.6	678.1	677.2	677.6	677.2	678.1	680.6	685.6	687.2	690.5	694.3
12.5°	655.0	654.5	649.0	649.1	649.0	654.5	655.0	656.3	660.0	666.9	671.4
15°	625.0	617.1	616.2	618.8	616.2	617.1	625.0	625.0	626.6	632.0	634.5
17.5°	594.8	590.7	591.0	589.7	591.0	590.7	594.8	595.6	596.8	601.3	604.6
20°	578.9	576.5	576.1	573.1	576.1	576.5	578.9	578.9	580.6	582.7	586.0
22.5°	564.4	563.6	563.8	560.5	563.8	563.6	564.4	565.4	567.0	568.4	570.8
25°	546.2	548.3	546.6	546.6	546.6	548.3	546.2	546.6	547.0	549.1	550.7
27.5°	533.9	533.9	533.0	533.0	533.0	533.9	533.9	532.9	532.4	531.7	531.3
30°	524.7	524.2	525.1	525.1	525.1	524.2	524.7	523.0	522.1	521.7	520.1
32.5°	515.3	515.9	516.1	516.4	516.1	515.9	515.3	513.3	511.8	510.8	509.5
35°	501.0	501.4	502.6	501.8	502.6	501.4	501.0	498.5	496.9	494.3	492.3
37.5°	481.6	483.5	483.1	483.7	483.1	483.5	481.6	480.9	479.2	477.3	474.8
40°	467.0	468.3	467.8	467.8	467.8	468.3	467.0	466.6	464.9	463.7	461.6
42.5°	452.0	453.0	451.9	451.2	451.9	453.0	452.0	451.3	450.3	448.1	445.7
45°	427.5	426.7	428.0	426.4	428.0	426.7	427.5	426.0	425.5	423.8	421.8
47.5°	400.2	401.0	401.4	402.6	401.4	401.0	400.2	400.4	398.1	397.0	396.4
50°	382.0	384.4	384.4	384.0	384.4	384.4	382.0	381.1	379.5	377.8	377.8
52.5°	364.0	365.2	366.9	366.8	366.9	365.2	364.0	362.6	360.9	358.5	357.9
55°	336.4	337.2	338.0	338.4	338.0	337.2	336.4	333.0	331.8	330.5	328.4
57.5°	307.6	307.3	309.3	309.9	309.3	307.3	307.6	304.7	302.8	299.0	298.4
60°	287.4	287.4	290.7	292.0	290.7	287.4	287.4	284.1	281.1	278.7	277.9
62.5°	265.9	267.2	270.5	268.7	270.5	267.2	265.9	262.2	259.9	256.8	254.6
65°	234.3	237.7	237.3	238.8	237.3	237.7	234.3	232.3	227.7	224.7	222.3
67.5°	201.4	203.4	206.4	206.7	206.4	203.4	201.4	198.0	195.1	192.0	189.0
70°	179.2	181.3	182.9	184.1	182.9	181.3	179.2	175.9	172.5	170.5	167.2
72.5°	157.6	158.7	162.6	160.9	162.6	158.7	157.6	153.6	151.0	149.2	145.6
75°	123.6	126.5	129.0	127.7	129.0	126.5	123.6	120.6	118.6	116.1	112.8
77.5°	91.4	94.3	95.5	94.4	95.5	94.3	91.4	89.5	88.4	83.5	83.2
80°	72.2	71.8	74.2	73.8	74.2	71.8	72.2	69.2	67.2	64.2	64.2
82.5°	52.9	52.5	53.6	53.9	53.6	52.5	52.9	51.3	48.6	47.4	46.3
85°	25.7	26.9	25.3	24.9	25.3	26.9	25.7	24.1	24.1	24.1	23.6
87.5°	9.5	9.6	9.3	9.0	9.3	9.6	9.5	9.5	10.7	9.6	9.5
90°	17.7	18.1	18.3	18.6	18.3	18.1	17.7	17.5	17.0	16.5	16.0
92.5°	20.0	20.2	20.4	20.6	20.4	20.2	20.0	19.9	19.4	18.5	17.6
95°	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.1	22.1	21.2
97.5°	25.1	25.3	25.3	25.5	25.3	25.3	25.1	25.0	24.3	23.2	22.2
100°	25.6	25.7	25.9	26.0	25.9	25.7	25.6	25.4	24.9	23.8	22.7
102.5°	25.7	26.0	26.2	26.5	26.2	26.0	25.7	25.5	27.1	30.5	33.9
105°	26.5	26.7	27.0	27.3	27.0	26.7	26.5	26.1	38.2	62.6	86.9
107.5°	140.7	122.3	103.9	85.6	103.9	122.3	140.7	159.0	177.1	195.0	212.9
110°	229.3	209.7	190.0	170.3	190.0	209.7	229.3	249.1	261.2	265.7	270.2



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	304.7	300.5	296.4	292.2	296.4	300.5	304.7	308.8	310.9	310.8	310.7
115°	362.5	363.1	363.6	364.2	363.6	363.1	362.5	361.9	361.0	359.7	358.2
117.5°	404.3	404.3	404.4	404.6	404.4	404.3	404.3	404.1	403.5	402.4	401.3
120°	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	431.7	430.6	429.5
122.5°	459.2	459.3	459.5	459.5	459.5	459.3	459.2	459.1	458.7	457.9	457.1
125°	497.1	497.4	497.6	498.0	497.6	497.4	497.1	496.9	496.5	496.3	496.0
127.5°	535.7	535.4	535.1	534.9	535.1	535.4	535.7	535.9	535.8	535.4	535.0
130°	559.4	559.2	558.9	558.6	558.9	559.2	559.4	559.8	559.6	559.0	558.5
132.5°	581.6	581.2	580.8	580.4	580.8	581.2	581.6	581.9	581.9	581.3	580.7
135°	615.0	614.6	614.2	613.8	614.2	614.6	615.0	615.4	615.4	615.0	614.6
137.5°	645.9	645.6	645.4	645.1	645.4	645.6	645.9	646.2	646.0	645.3	644.7
140°	664.7	664.5	664.2	663.9	664.2	664.5	664.7	665.0	664.9	664.3	663.8
142.5°	682.4	682.0	681.7	681.3	681.7	682.0	682.4	682.8	682.8	682.3	681.9
145°	707.9	707.9	707.9	707.9	707.9	707.9	707.9	707.9	707.7	707.5	707.2
147.5°	729.6	729.0	728.3	727.7	728.3	729.0	729.6	730.2	730.4	730.2	729.8
150°	743.8	743.4	743.0	742.6	743.0	743.4	743.8	744.3	744.3	744.0	743.7
152.5°	756.4	755.7	755.1	754.5	755.1	755.7	756.4	757.0	757.1	756.5	756.1
155°	773.6	772.7	771.9	771.0	771.9	772.7	773.6	774.4	774.4	773.7	773.1
157.5°	788.3	787.2	786.2	785.1	786.2	787.2	788.3	789.3	789.5	788.6	787.8
160°	796.9	795.9	795.0	794.0	795.0	795.9	796.9	797.8	797.9	797.1	796.2
162.5°	804.9	804.1	803.3	802.4	803.3	804.1	804.9	805.8	805.7	804.9	803.9
165°	815.5	814.4	813.5	812.5	813.5	814.4	815.5	816.4	816.3	815.2	814.1
167.5°	823.2	822.0	820.9	819.8	820.9	822.0	823.2	824.3	824.3	823.2	822.0
170°	827.6	826.5	825.5	824.3	825.5	826.5	827.6	828.7	828.7	827.6	826.5
172.5°	830.4	829.3	828.0	826.8	828.0	829.3	830.4	831.6	831.7	830.6	829.5
175°	833.9	832.7	831.6	830.5	831.6	832.7	833.9	834.9	835.0	834.0	833.1
177.5°	835.0	833.9	832.7	831.6	832.7	833.9	835.0	836.1	836.1	835.3	834.4
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	820.8	820.8	827.1	831.1	836.1	839.4	841.7	844.1	848.0	853.3	859.3
5°	773.9	775.5	784.7	793.8	802.5	809.9	816.2	823.6	832.7	844.0	856.4
7.5°	728.4	734.8	744.0	755.1	767.3	778.2	789.3	801.5	814.4	830.8	848.3
10°	699.3	706.3	717.5	731.6	744.4	757.2	771.0	784.3	800.4	819.9	842.3
12.5°	673.7	680.4	691.9	707.3	719.5	733.7	749.4	766.7	784.8	808.3	833.7
15°	638.3	646.1	660.2	667.7	686.3	703.4	717.9	742.8	766.0	790.0	819.5
17.5°	609.2	613.6	625.0	638.9	652.8	671.9	690.9	711.7	734.8	764.2	801.1
20°	589.3	593.0	605.5	620.0	634.9	652.4	669.4	690.1	716.2	747.3	787.1
22.5°	574.4	578.5	586.6	602.1	616.0	630.5	647.5	672.2	700.0	730.4	773.6
25°	552.8	555.3	560.7	573.1	585.6	601.7	616.7	639.9	668.5	704.2	747.3
27.5°	532.3	534.7	539.2	548.2	559.8	572.9	589.1	608.9	637.9	676.7	722.5
30°	520.1	520.5	524.7	532.9	542.9	553.7	568.5	591.0	618.4	657.7	705.8
32.5°	509.5	507.9	510.7	517.0	526.6	537.4	549.7	571.7	598.1	636.8	686.3
35°	491.5	490.6	489.4	494.8	503.0	511.4	522.1	538.8	568.5	604.7	656.5
37.5°	473.1	471.1	468.9	471.3	477.8	486.5	495.8	510.6	536.3	576.1	625.7
40°	459.5	457.9	456.6	455.7	461.6	469.8	476.9	491.0	515.1	552.8	601.7
42.5°	444.6	443.6	442.0	440.8	445.7	451.9	459.3	471.8	495.8	531.2	577.6
45°	420.5	419.7	418.9	418.0	421.0	426.7	432.5	441.6	462.4	496.9	538.8
47.5°	393.7	392.7	393.0	391.7	394.5	398.4	402.4	412.3	432.1	459.9	490.5
50°	374.5	374.1	374.1	374.1	374.9	379.5	383.2	390.7	408.9	436.7	458.7
52.5°	356.2	354.5	354.5	355.1	356.6	359.6	361.9	370.1	386.0	408.8	428.8
55°	327.6	324.3	323.4	324.3	325.6	328.0	330.5	337.2	350.9	367.9	379.5
57.5°	296.0	294.1	293.0	293.2	293.9	295.9	297.8	305.0	315.8	324.6	332.1
60°	273.7	274.6	270.8	271.6	271.6	273.3	276.2	280.7	289.9	296.1	303.6
62.5°	252.8	251.7	250.6	249.4	249.4	250.1	254.0	257.5	265.3	268.5	274.4
65°	220.2	220.2	217.7	218.6	219.0	216.1	218.2	222.3	227.3	228.5	233.9
67.5°	187.2	186.1	184.7	183.4	183.4	183.2	184.2	186.3	190.0	190.4	194.6
70°	164.6	163.8	163.4	162.2	160.5	162.6	161.3	163.4	165.5	165.9	168.3
72.5°	142.8	141.9	141.2	139.9	139.3	139.0	139.1	141.5	142.9	142.4	145.1
75°	111.5	110.7	109.9	107.8	107.8	106.5	107.0	108.7	110.4	109.1	111.5
77.5°	81.9	79.4	79.2	79.8	78.3	78.7	78.1	77.9	78.7	78.7	81.0
80°	63.1	60.1	61.0	60.5	60.1	59.7	58.9	59.3	59.7	60.1	61.4
82.5°	45.5	45.2	44.4	44.3	43.9	42.8	42.3	43.0	43.5	43.3	44.1
85°	23.2	21.9	22.8	22.4	22.8	22.4	21.2	21.2	21.9	21.5	22.4
87.5°	10.1	9.9	9.3	9.2	8.6	8.5	7.8	7.9	8.0	7.7	8.1
90°	15.4	14.9	13.1	11.2	9.5	7.7	6.1	4.8	3.4	2.0	0.6
92.5°	16.7	15.8	14.5	13.2	11.8	10.5	10.0	10.4	10.8	11.2	11.5
95°	20.2	19.2	17.7	16.2	14.7	13.2	15.2	20.8	26.5	32.2	37.8
97.5°	21.1	20.0	29.9	39.8	49.7	59.6	65.8	68.4	70.9	73.4	75.9
100°	21.5	20.4	41.9	63.4	84.8	106.3	115.7	112.9	110.2	107.4	104.6
102.5°	37.3	40.7	64.2	87.6	111.1	134.6	145.3	143.3	141.3	139.3	137.4
105°	111.3	135.6	148.0	160.4	172.8	185.2	190.6	189.1	187.6	186.1	184.6
107.5°	230.8	248.6	246.6	244.7	242.7	240.7	239.2	238.0	236.8	235.6	234.3
110°	274.8	279.3	277.8	276.3	274.8	273.2	272.0	270.8	269.7	268.6	267.5



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	310.6	310.5	309.0	307.5	306.0	304.4	303.2	302.2	301.3	300.2	299.3
115°	356.9	355.5	354.3	353.0	351.8	350.5	349.5	348.7	347.8	347.1	346.2
117.5°	400.2	399.1	398.5	397.8	397.2	396.6	395.7	394.7	393.7	392.7	391.7
120°	428.4	427.3	426.9	426.5	426.1	425.7	424.8	423.6	422.4	421.1	419.9
122.5°	456.4	455.6	455.0	454.6	454.0	453.4	452.7	451.7	450.7	449.6	448.6
125°	495.7	495.4	494.9	494.3	493.8	493.3	492.4	491.3	490.2	489.1	488.1
127.5°	534.6	534.1	533.5	532.8	532.1	531.5	530.6	529.5	528.4	527.3	526.2
130°	557.9	557.4	556.8	556.3	555.7	555.2	554.4	553.3	552.2	551.0	549.9
132.5°	580.3	579.7	579.2	578.8	578.4	577.9	577.2	576.1	575.0	573.9	572.7
135°	614.2	613.8	613.2	612.7	612.1	611.6	610.9	610.1	609.2	608.4	607.5
137.5°	644.0	643.3	643.0	642.8	642.5	642.1	641.4	640.4	639.4	638.3	637.3
140°	663.2	662.7	662.3	661.9	661.5	661.0	660.4	659.6	658.8	657.9	657.1
142.5°	681.4	681.0	680.6	680.2	679.8	679.4	678.7	677.9	677.1	676.3	675.4
145°	706.9	706.6	706.4	706.1	705.8	705.5	705.0	703.9	703.0	702.0	701.1
147.5°	729.6	729.3	729.0	728.7	728.5	728.3	727.8	727.1	726.5	725.9	725.2
150°	743.5	743.2	742.9	742.7	742.4	742.1	741.7	741.3	740.9	740.5	740.1
152.5°	755.6	755.1	754.9	754.7	754.6	754.4	754.2	754.1	753.8	753.7	753.4
155°	772.4	771.7	771.5	771.4	771.3	771.1	771.2	771.5	771.7	772.1	772.3
157.5°	787.0	786.2	786.3	786.5	786.6	786.7	786.8	786.8	786.9	786.9	786.9
160°	795.4	794.6	794.7	794.9	795.0	795.1	795.3	795.4	795.6	795.7	795.8
162.5°	803.0	802.0	802.2	802.3	802.4	802.6	802.8	803.2	803.5	803.9	804.2
165°	813.0	811.9	812.1	812.2	812.4	812.5	812.8	813.2	813.6	814.0	814.4
167.5°	820.9	819.8	819.8	819.8	819.8	819.8	820.1	820.7	821.3	821.8	822.4
170°	825.5	824.3	824.3	824.3	824.3	824.3	824.6	825.1	825.7	826.2	826.8
172.5°	828.4	827.3	827.2	827.0	827.0	826.9	827.1	827.8	828.5	829.1	829.7
175°	832.1	831.2	831.0	830.8	830.7	830.6	830.8	831.6	832.3	832.9	833.6
177.5°	833.5	832.6	832.5	832.4	832.3	832.2	832.4	833.0	833.5	834.1	834.6
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	861.3	862.9	868.6	872.6	877.2	879.9	882.5	884.6	887.2	887.8	897.5
5°	865.1	873.4	888.0	898.7	912.0	926.5	936.4	941.0	953.0	963.0	982.9
7.5°	864.0	881.7	903.6	926.3	950.7	973.3	992.8	1016.1	1032.6	1057.4	1081.8
10°	863.0	886.7	914.9	943.9	977.9	1009.4	1037.6	1069.1	1095.3	1129.7	1159.1
12.5°	860.1	888.7	927.8	962.2	1003.5	1046.9	1088.7	1129.2	1152.3	1209.7	1236.8
15°	852.7	886.7	935.6	987.9	1044.7	1096.1	1149.2	1191.5	1259.9	1310.1	1342.0
17.5°	838.6	886.2	944.2	1007.3	1076.3	1144.1	1204.3	1268.4	1341.0	1401.8	1466.5
20°	831.9	884.2	948.9	1018.6	1090.3	1167.0	1235.5	1312.6	1391.8	1451.5	1534.5
22.5°	819.7	878.8	948.6	1026.2	1102.9	1182.3	1262.3	1340.1	1431.6	1513.9	1592.8
25°	799.5	865.9	938.1	1024.8	1114.8	1194.4	1290.2	1393.4	1488.8	1594.6	1673.4
27.5°	778.5	849.4	921.7	1002.3	1099.1	1193.6	1314.1	1430.8	1547.4	1638.7	1697.0
30°	762.2	831.1	905.8	987.1	1082.8	1195.2	1330.0	1457.3	1571.0	1649.3	1682.1
32.5°	744.7	814.5	880.5	965.8	1067.9	1194.2	1340.0	1472.9	1572.3	1624.4	1618.1
35°	717.1	775.5	839.8	921.9	1042.2	1186.9	1345.8	1474.3	1535.3	1524.1	1439.5
37.5°	677.2	726.4	789.7	879.6	1012.3	1171.6	1334.2	1430.6	1426.6	1335.5	1212.9
40°	652.4	694.3	755.2	849.8	989.1	1161.7	1315.9	1378.6	1325.5	1198.1	1051.3
42.5°	619.9	658.4	719.4	816.6	963.5	1141.4	1281.0	1299.3	1195.4	1048.8	914.3
45°	569.4	603.4	666.5	766.8	925.3	1097.3	1196.0	1151.7	1011.9	860.5	758.1
47.5°	515.2	550.6	611.2	714.3	869.8	1031.1	1078.1	983.7	840.2	717.5	623.4
50°	481.1	515.1	574.4	678.5	832.3	976.7	996.2	874.3	742.4	634.5	557.4
52.5°	446.6	478.6	536.9	641.4	788.5	913.6	901.6	777.4	656.1	564.2	503.7
55°	395.2	425.5	481.1	578.9	712.9	812.0	768.5	649.9	549.5	478.2	432.1
57.5°	349.3	378.3	426.3	514.7	631.1	699.3	643.8	543.8	464.1	409.2	374.9
60°	318.1	343.8	389.4	471.5	572.7	624.6	569.8	481.5	414.3	370.3	339.7
62.5°	288.6	310.9	353.2	427.8	515.6	559.2	503.8	429.0	371.9	332.9	306.8
65°	243.8	264.2	301.5	359.6	431.7	460.7	413.0	352.5	308.2	279.1	261.7
67.5°	203.0	220.3	252.5	298.3	351.3	372.5	336.2	289.3	255.9	232.6	218.7
70°	175.9	190.8	216.1	255.5	303.6	319.7	285.7	247.2	222.7	204.1	191.2
72.5°	153.0	163.9	186.9	217.3	257.5	270.3	246.6	212.7	189.9	175.9	165.6
75°	116.5	125.6	140.6	165.1	192.8	200.3	182.4	161.3	146.0	136.0	128.2
77.5°	84.1	90.7	101.6	116.6	135.9	142.6	131.3	117.2	106.0	99.3	94.9
80°	63.5	68.8	78.0	90.4	102.0	105.8	99.1	88.3	80.5	76.8	73.0
82.5°	46.9	49.9	55.4	63.8	71.9	76.2	70.6	64.1	59.9	56.5	55.1
85°	23.6	25.3	27.8	31.1	36.0	37.7	35.6	34.0	31.5	29.5	29.5
87.5°	9.0	9.3	10.5	11.5	13.2	14.5	14.5	14.3	14.3	14.0	13.8
90°	2.0	3.4	4.8	6.1	7.7	9.5	11.2	13.1	14.9	15.4	16.0
92.5°	11.2	10.8	10.4	10.0	10.5	11.8	13.2	14.5	15.8	16.7	17.6
95°	32.2	26.5	20.8	15.2	13.2	14.7	16.2	17.7	19.2	20.2	21.2
97.5°	73.4	70.9	68.4	65.8	59.6	49.7	39.8	29.9	20.0	21.1	22.2
100°	107.4	110.2	112.9	115.7	106.3	84.8	63.4	41.9	20.4	21.5	22.7
102.5°	139.3	141.3	143.3	145.3	134.6	111.1	87.6	64.2	40.7	37.3	33.9
105°	186.1	187.6	189.1	190.6	185.2	172.8	160.4	148.0	135.6	111.3	86.9
107.5°	235.6	236.8	238.0	239.2	240.7	242.7	244.7	246.6	248.6	230.8	212.9
110°	268.6	269.7	270.8	272.0	273.2	274.8	276.3	277.8	279.3	274.8	270.2





TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	300.2	301.3	302.2	303.2	304.4	306.0	307.5	309.0	310.5	310.6	310.7
115°	347.1	347.8	348.7	349.5	350.5	351.8	353.0	354.3	355.5	356.9	358.2
117.5°	392.7	393.7	394.7	395.7	396.6	397.2	397.8	398.5	399.1	400.2	401.3
120°	421.1	422.4	423.6	424.8	425.7	426.1	426.5	426.9	427.3	428.4	429.5
122.5°	449.6	450.7	451.7	452.7	453.4	454.0	454.6	455.0	455.6	456.4	457.1
125°	489.1	490.2	491.3	492.4	493.3	493.8	494.3	494.9	495.4	495.7	496.0
127.5°	527.3	528.4	529.5	530.6	531.5	532.1	532.8	533.5	534.1	534.6	535.0
130°	551.0	552.2	553.3	554.4	555.2	555.7	556.3	556.8	557.4	557.9	558.5
132.5°	573.9	575.0	576.1	577.2	577.9	578.4	578.8	579.2	579.7	580.3	580.7
135°	608.4	609.2	610.1	610.9	611.6	612.1	612.7	613.2	613.8	614.2	614.6
137.5°	638.3	639.4	640.4	641.4	642.1	642.5	642.8	643.0	643.3	644.0	644.7
140°	657.9	658.8	659.6	660.4	661.0	661.5	661.9	662.3	662.7	663.2	663.8
142.5°	676.3	677.1	677.9	678.7	679.4	679.8	680.2	680.6	681.0	681.4	681.9
145°	702.0	703.0	703.9	705.0	705.5	705.8	706.1	706.4	706.6	706.9	707.2
147.5°	725.9	726.5	727.1	727.8	728.3	728.5	728.7	729.0	729.3	729.6	729.8
150°	740.5	740.9	741.3	741.7	742.1	742.4	742.7	742.9	743.2	743.5	743.7
152.5°	753.7	753.8	754.1	754.2	754.4	754.6	754.7	754.9	755.1	755.6	756.1
155°	772.1	771.7	771.5	771.2	771.1	771.3	771.4	771.5	771.7	772.4	773.1
157.5°	786.9	786.9	786.8	786.8	786.7	786.6	786.5	786.3	786.2	787.0	787.8
160°	795.7	795.6	795.4	795.3	795.1	795.0	794.9	794.7	794.6	795.4	796.2
162.5°	803.9	803.5	803.2	802.8	802.6	802.4	802.3	802.2	802.0	803.0	803.9
165°	814.0	813.6	813.2	812.8	812.5	812.4	812.2	812.1	811.9	813.0	814.1
167.5°	821.8	821.3	820.7	820.1	819.8	819.8	819.8	819.8	819.8	820.9	822.0
170°	826.2	825.7	825.1	824.6	824.3	824.3	824.3	824.3	824.3	825.5	826.5
172.5°	829.1	828.5	827.8	827.1	826.9	827.0	827.0	827.2	827.3	828.4	829.5
175°	832.9	832.3	831.6	830.8	830.6	830.7	830.8	831.0	831.2	832.1	833.1
177.5°	834.1	833.5	833.0	832.4	832.2	832.3	832.4	832.5	832.6	833.5	834.4
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	900.8	901.1	904.8	907.4	906.1	907.8	908.4
5°	984.1	999.1	1006.9	1012.7	1013.2	1013.6	1016.9
7.5°	1102.3	1118.3	1130.0	1147.8	1153.1	1159.1	1157.4
10°	1188.6	1212.2	1232.6	1243.3	1255.0	1271.9	1258.3
12.5°	1269.2	1311.1	1342.0	1358.8	1369.8	1373.2	1366.4
15°	1402.2	1456.9	1486.4	1485.5	1522.9	1539.1	1513.7
17.5°	1524.1	1574.6	1615.1	1635.9	1666.9	1673.8	1670.6
20°	1598.8	1653.9	1685.4	1721.1	1737.3	1751.8	1754.3
22.5°	1663.1	1712.6	1746.4	1776.2	1789.7	1796.6	1800.7
25°	1729.4	1768.4	1788.7	1799.0	1802.8	1802.0	1796.6
27.5°	1724.8	1727.8	1705.4	1683.5	1663.8	1641.6	1634.0
30°	1680.1	1645.2	1583.0	1547.8	1495.9	1454.8	1471.4
32.5°	1562.3	1492.9	1423.1	1346.0	1282.2	1264.1	1245.8
35°	1333.3	1211.4	1140.1	1057.1	1024.0	990.8	968.0
37.5°	1078.7	984.4	899.8	845.5	812.3	791.3	780.0
40°	932.7	847.7	778.0	734.0	708.8	685.2	681.8
42.5°	816.3	737.2	684.8	649.7	625.5	615.4	608.2
45°	668.5	613.4	578.1	553.3	537.1	530.8	522.5
47.5°	565.9	526.9	500.4	483.5	471.3	466.7	466.0
50°	508.4	476.1	456.6	443.3	433.8	432.1	425.5
52.5°	465.3	437.3	422.1	410.5	403.6	398.9	397.0
55°	403.9	385.2	371.6	365.0	359.6	355.0	355.0
57.5°	353.4	337.9	328.8	323.1	321.5	318.2	316.2
60°	322.3	309.0	301.9	296.9	293.7	294.1	290.3
62.5°	291.7	283.1	276.4	271.4	267.4	267.5	267.8
65°	248.4	241.8	236.8	235.1	232.7	229.7	230.6
67.5°	210.5	204.3	200.4	197.6	196.8	195.2	197.6
70°	183.3	178.7	175.9	173.3	172.5	172.9	175.0
72.5°	158.4	155.2	153.3	152.1	150.3	150.4	151.8
75°	124.5	121.9	120.3	119.0	118.6	118.6	118.6
77.5°	91.4	90.9	90.1	88.2	88.3	88.8	88.9
80°	72.2	70.9	70.5	69.7	68.4	67.6	69.7
82.5°	53.9	52.7	52.3	52.1	50.1	50.0	51.7
85°	29.0	27.8	28.2	27.8	27.8	27.4	27.4
87.5°	13.6	13.4	13.2	13.5	13.2	12.9	13.7
90°	16.5	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	18.5	19.4	19.9	20.0	20.2	20.4	20.6
95°	22.1	23.1	23.5	23.5	23.5	23.5	23.5
97.5°	23.2	24.3	25.0	25.1	25.3	25.3	25.5
100°	23.8	24.9	25.4	25.6	25.7	25.9	26.0
102.5°	30.5	27.1	25.5	25.7	26.0	26.2	26.5
105°	62.6	38.2	26.1	26.5	26.7	27.0	27.3
107.5°	195.0	177.1	159.0	140.7	122.3	103.9	85.6
110°	265.7	261.2	249.1	229.3	209.7	190.0	170.3



TEST NUMBER: P331973-927

CATALOG NUMBER: S123DIP-S775D805U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	310.8	310.9	308.8	304.7	300.5	296.4	292.2
115°	359.7	361.0	361.9	362.5	363.1	363.6	364.2
117.5°	402.4	403.5	404.1	404.3	404.3	404.4	404.6
120°	430.6	431.7	432.3	432.3	432.3	432.3	432.3
122.5°	457.9	458.7	459.1	459.2	459.3	459.5	459.5
125°	496.3	496.5	496.9	497.1	497.4	497.6	498.0
127.5°	535.4	535.8	535.9	535.7	535.4	535.1	534.9
130°	559.0	559.6	559.8	559.4	559.2	558.9	558.6
132.5°	581.3	581.9	581.9	581.6	581.2	580.8	580.4
135°	615.0	615.4	615.4	615.0	614.6	614.2	613.8
137.5°	645.3	646.0	646.2	645.9	645.6	645.4	645.1
140°	664.3	664.9	665.0	664.7	664.5	664.2	663.9
142.5°	682.3	682.8	682.8	682.4	682.0	681.7	681.3
145°	707.5	707.7	707.9	707.9	707.9	707.9	707.9
147.5°	730.2	730.4	730.2	729.6	729.0	728.3	727.7
150°	744.0	744.3	744.3	743.8	743.4	743.0	742.6
152.5°	756.5	757.1	757.0	756.4	755.7	755.1	754.5
155°	773.7	774.4	774.4	773.6	772.7	771.9	771.0
157.5°	788.6	789.5	789.3	788.3	787.2	786.2	785.1
160°	797.1	797.9	797.8	796.9	795.9	795.0	794.0
162.5°	804.9	805.7	805.8	804.9	804.1	803.3	802.4
165°	815.2	816.3	816.4	815.5	814.4	813.5	812.5
167.5°	823.2	824.3	824.3	823.2	822.0	820.9	819.8
170°	827.6	828.7	828.7	827.6	826.5	825.5	824.3
172.5°	830.6	831.7	831.6	830.4	829.3	828.0	826.8
175°	834.0	835.0	834.9	833.9	832.7	831.6	830.5
177.5°	835.3	836.1	836.1	835.0	833.9	832.7	831.6
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6

(END OF REPORT)