

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332344-930

Luminaire Tested: **S123RDIP-S1000D805U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332344-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5598.5 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	90	87	84	78	76	73	67	65	64	57	56	55	50
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47	43
3	84	75	68	62	78	70	64	59	61	57	53	53	50	47	46	43	41	37
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	41	38	36	32
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	37	34	32	29
6	66	54	46	40	61	51	44	39	45	39	35	39	35	32	34	31	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	31	28	25	23
8	57	45	37	32	53	42	35	31	38	32	28	33	29	25	29	25	23	20
9	53	41	34	29	49	39	32	27	35	29	25	31	26	23	27	23	21	19
10	50	38	31	26	46	36	29	25	32	27	23	28	24	21	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13951	13951	13951	13951
5°	16630	14011	12337	14011
10°	20764	13930	11146	13930
15°	24373	13788	10165	13788
20°	27202	13575	9330	13575
25°	26766	13351	8817	13351
30°	19240	13144	8289	13144
35°	12846	12875	7947	12875
40°	9465	12552	7593	12552
45°	7939	11985	7247	11985
50°	7005	11241	6764	11241
55°	6142	10393	6101	10393
60°	5470	9580	5591	9580
65°	4806	8706	5201	8706
70°	3770	7928	4749	7928
75°	3323	6924	4338	6924
80°	2889	5883	4265	5883
85°	2322	4730	4520	4730



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.5	2.3
10°-20°	398.2	7.1
20°-30°	625.6	11.2
30°-40°	652.7	11.7
40°-50°	558.6	10.0
50°-60°	425.7	7.6
60°-70°	272.9	4.9
70°-80°	131.3	2.3
80°-90°	37.2	0.7
90°-100°	175.2	3.1
100°-110°	496.2	8.9
110°-120°	488.1	8.7
120°-130°	389.3	7.0
130°-140°	307.0	5.5
140°-150°	229.1	4.1
150°-160°	159.7	2.9
160°-170°	93.8	1.7
170°-180°	30.5	0.5
0°-30°	1151.2	20.6
0°-40°	1803.9	32.2
0°-60°	2788.2	49.8
0°-90°	3229.5	57.7
90°-120°	1159.6	20.7
90°-150°	2085.0	37.2
90°-180°	2369.0	42.3
0°-180°	5598.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1296	1296	1296	1296	1296	
5°	1539	1297	1142	1297	1539	159
15°	2187	1237	912	1237	2187	620
25°	2254	1124	742	1124	2254	969
35°	978	980	605	980	978	641
45°	522	787	476	787	522	410
55°	327	554	325	554	327	296
65°	189	342	204	342	189	186
75°	80	166	104	166	80	86
85°	19	38	37	38	19	22
90°	18	1	18	1	18	10
95°	74	22	74	22	74	133
105°	811	74	811	74	811	800
115°	986	131	986	131	986	958
125°	778	182	778	182	778	705
135°	630	213	630	213	630	489
145°	493	243	493	243	493	313
155°	408	276	408	276	408	191
165°	356	302	356	302	356	102
175°	321	314	321	314	321	31
180°	315	315	315	315	315	



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1380.5	1382.2	1376.5	1375.6	1368.9	1367.1	1367.1	1357.8	1352.0	1344.5	1340.0
5°	1539.1	1548.0	1543.5	1533.6	1516.9	1513.0	1502.5	1485.9	1467.0	1443.7	1432.6
7.5°	1737.3	1749.4	1744.7	1729.3	1711.9	1697.8	1668.1	1640.5	1601.7	1567.7	1538.7
10°	1899.7	1887.0	1877.0	1862.1	1845.9	1819.8	1788.8	1746.0	1696.7	1657.8	1614.6
12.5°	2021.4	2019.3	2006.6	1991.2	1968.5	1943.7	1905.5	1853.5	1796.1	1740.0	1690.4
15°	2187.2	2190.5	2182.1	2166.1	2133.9	2090.1	2032.4	2010.8	1928.6	1867.6	1806.5
17.5°	2301.9	2301.3	2300.1	2277.9	2245.0	2213.8	2160.3	2103.4	2029.0	1943.0	1860.8
20°	2374.7	2369.2	2370.2	2345.3	2320.9	2284.8	2232.7	2150.0	2089.0	1989.7	1904.8
22.5°	2372.9	2371.8	2376.0	2367.5	2349.8	2322.1	2281.0	2211.3	2133.3	2033.1	1937.6
25°	2253.7	2249.3	2275.4	2282.6	2310.9	2315.9	2303.7	2265.4	2191.6	2088.4	1970.3
27.5°	1886.2	1883.7	1932.2	1992.8	2069.6	2129.2	2187.0	2214.8	2191.6	2117.7	1999.3
30°	1548.0	1600.2	1624.6	1712.2	1809.9	1926.4	2028.5	2125.6	2149.5	2117.3	2020.1
32.5°	1285.2	1330.7	1351.1	1426.4	1517.4	1653.8	1807.0	1944.5	2041.6	2066.2	2007.8
35°	977.6	978.2	1024.7	1058.1	1142.4	1282.8	1431.5	1615.7	1798.8	1937.5	1951.9
37.5°	780.1	782.9	811.1	844.2	907.5	981.7	1112.6	1265.8	1477.3	1690.3	1815.1
40°	673.6	678.6	699.7	732.4	777.9	833.9	936.0	1080.3	1256.7	1493.6	1687.3
42.5°	605.2	613.3	624.2	649.4	677.6	730.0	812.6	924.1	1084.5	1308.6	1531.9
45°	521.5	525.9	534.3	545.9	571.4	608.1	663.6	738.5	871.6	1052.0	1275.5
47.5°	460.1	457.7	466.5	476.0	492.9	517.9	555.1	616.2	711.2	855.9	1045.5
50°	418.3	417.8	423.9	431.1	447.2	465.5	496.0	542.1	617.5	737.4	911.0
52.5°	379.3	381.4	385.7	394.7	406.3	421.1	448.5	481.7	546.5	650.0	794.8
55°	327.3	329.1	335.1	340.1	348.5	363.4	380.6	408.4	452.7	524.9	644.2
57.5°	283.4	282.7	288.5	289.8	299.1	311.4	324.7	346.3	378.4	432.0	512.3
60°	254.1	252.4	257.5	261.3	266.4	276.3	287.4	308.5	334.0	373.4	442.2
62.5°	227.5	226.7	230.4	234.2	238.4	247.4	256.8	273.0	293.2	326.4	381.0
65°	188.7	190.3	192.0	193.6	195.8	201.4	210.3	221.4	235.2	258.5	297.9
67.5°	148.2	149.9	150.5	153.9	158.7	162.2	167.5	177.4	187.1	206.8	229.2
70°	119.8	119.3	119.8	121.5	127.6	133.7	141.0	148.1	154.3	168.1	186.9
72.5°	103.0	102.0	103.5	103.8	106.7	108.4	113.0	119.8	127.6	137.1	150.6
75°	79.9	79.9	79.9	79.9	82.1	83.2	84.9	86.6	89.4	93.8	103.8
77.5°	59.0	59.1	59.9	60.5	60.9	61.6	62.6	64.2	65.2	67.6	71.9
80°	46.6	47.1	46.6	47.1	47.1	48.3	48.8	50.5	51.0	53.8	55.5
82.5°	35.1	34.7	35.1	35.6	35.6	36.8	36.9	38.1	38.2	39.6	41.3
85°	18.8	17.8	18.8	18.3	19.4	18.3	18.8	20.0	20.0	20.5	22.7
87.5°	8.2	9.1	8.2	8.5	8.6	8.8	8.6	8.5	9.3	9.0	9.0
90°	18.5	19.2	18.5	17.9	18.5	17.2	16.6	15.9	15.3	15.9	14.0
92.5°	30.7	31.9	31.2	33.2	34.3	37.6	42.6	53.6	73.9	98.0	107.9
95°	73.9	76.5	81.0	86.7	98.8	121.7	155.6	229.5	306.6	378.0	336.6
97.5°	201.3	206.8	224.0	252.7	299.7	375.9	458.2	572.0	626.7	585.8	428.8
100°	399.7	399.0	423.9	470.4	534.8	625.3	699.9	751.5	729.2	603.6	408.0
102.5°	586.3	601.0	621.7	658.6	708.7	766.1	809.5	811.1	734.3	570.5	377.3
105°	810.8	814.0	834.4	858.6	887.9	904.5	892.3	828.7	695.5	512.5	339.7
107.5°	940.0	945.9	952.8	961.0	960.4	937.8	881.9	778.4	627.4	461.2	315.8
110°	993.1	994.3	995.6	990.5	972.7	928.1	847.7	730.5	584.5	432.2	306.6



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1003.8	1003.6	998.7	982.9	950.2	892.9	802.9	683.1	547.3	412.8	301.5
115°	986.1	982.9	970.1	942.1	894.3	824.8	731.1	620.2	502.3	392.0	299.6
117.5°	929.8	925.4	907.0	874.9	825.1	754.6	670.4	574.7	475.2	379.8	300.8
120°	882.8	879.0	863.7	828.0	777.6	713.3	636.7	550.7	460.9	374.1	302.8
122.5°	838.9	834.1	817.3	785.1	740.5	680.6	609.8	531.9	449.1	370.6	306.3
125°	777.6	773.1	757.2	729.2	688.4	637.4	576.3	506.7	434.1	365.9	311.7
127.5°	727.2	723.1	708.7	684.7	648.4	602.0	546.7	484.9	420.9	363.6	317.8
130°	698.6	693.5	680.1	657.2	623.4	580.1	528.4	471.1	413.7	362.1	321.9
132.5°	670.6	667.0	655.2	632.2	600.5	559.1	511.1	458.3	407.1	361.5	325.0
135°	630.4	625.9	614.5	595.3	564.1	527.7	486.3	441.1	398.4	360.8	329.5
137.5°	588.0	585.1	575.4	556.0	529.7	498.2	462.5	425.4	390.9	359.4	332.6
140°	558.4	559.1	548.8	531.0	506.7	479.3	448.7	416.2	386.3	358.9	334.7
142.5°	530.8	531.5	522.3	506.5	485.8	462.0	435.5	407.6	382.2	357.8	336.1
145°	492.7	491.5	486.3	473.0	457.1	438.5	418.2	397.1	376.7	356.3	337.2
147.5°	461.4	460.9	456.0	446.9	434.9	421.8	405.3	388.6	371.4	353.9	337.2
150°	443.0	443.0	439.2	432.2	422.6	410.5	397.1	382.5	367.8	351.9	337.2
152.5°	427.7	427.7	425.4	418.9	411.4	401.3	389.5	376.8	363.7	349.3	335.7
155°	408.5	408.0	406.7	401.5	395.8	388.2	378.6	368.4	357.6	344.9	334.0
157.5°	391.1	391.3	390.2	386.4	381.4	375.4	368.0	359.5	350.7	340.9	331.8
160°	379.9	380.5	380.5	376.7	372.3	367.8	361.4	354.4	346.1	337.9	330.8
162.5°	369.7	370.3	370.3	367.0	364.1	360.1	354.2	348.3	341.5	334.8	328.8
165°	356.3	356.3	356.9	354.4	351.9	348.7	344.2	340.4	335.3	330.2	325.7
167.5°	343.6	343.6	344.2	342.4	341.3	339.0	336.4	333.5	329.3	325.6	322.7
170°	335.9	335.9	336.6	335.3	334.7	333.4	330.8	328.9	325.7	322.5	320.7
172.5°	328.8	329.3	330.4	329.1	329.1	328.2	326.2	324.8	322.1	320.0	319.1
175°	320.7	321.2	321.9	321.2	321.2	321.2	320.0	319.4	318.0	316.8	316.8
177.5°	315.9	315.9	316.9	316.4	316.9	316.9	316.4	315.9	315.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1338.2	1336.9	1330.7	1323.6	1314.3	1308.1	1303.2	1300.6	1292.6	1282.8	1276.1
5°	1420.9	1404.3	1386.6	1364.9	1344.9	1324.4	1311.7	1296.7	1278.3	1257.8	1243.4
7.5°	1509.5	1476.8	1441.7	1405.4	1369.5	1337.4	1309.0	1284.7	1255.5	1226.0	1205.4
10°	1577.4	1529.7	1480.3	1429.8	1383.7	1340.5	1307.2	1274.5	1239.5	1205.7	1180.1
12.5°	1639.1	1576.3	1519.4	1457.3	1398.4	1346.7	1298.8	1260.3	1218.2	1182.1	1153.1
15°	1717.2	1652.9	1584.0	1489.7	1411.5	1346.1	1287.8	1237.3	1186.3	1141.8	1113.5
17.5°	1790.2	1693.4	1600.9	1522.2	1420.6	1338.8	1267.7	1207.3	1151.3	1104.2	1069.4
20°	1820.4	1726.6	1626.2	1525.8	1426.0	1334.4	1251.7	1185.1	1126.9	1073.6	1041.5
22.5°	1838.6	1732.4	1626.7	1518.7	1412.6	1317.5	1235.7	1162.5	1099.3	1048.7	1009.0
25°	1859.8	1733.3	1616.8	1510.3	1402.1	1298.9	1201.8	1124.1	1055.9	1002.0	959.9
27.5°	1873.8	1725.0	1587.3	1468.8	1359.1	1256.4	1167.3	1085.0	1015.8	958.9	913.6
30°	1876.5	1718.3	1564.6	1436.5	1324.9	1230.6	1136.3	1057.5	984.3	923.8	881.7
32.5°	1880.0	1701.9	1534.0	1397.8	1283.7	1190.3	1104.8	1029.6	954.6	895.0	851.9
35°	1865.4	1692.8	1487.5	1331.1	1216.8	1126.3	1049.2	979.8	906.0	848.3	804.5
37.5°	1802.3	1656.8	1439.3	1255.8	1136.3	1052.6	989.7	929.3	861.5	799.3	758.0
40°	1738.9	1621.2	1402.1	1210.1	1085.2	999.2	942.6	893.3	827.9	769.6	725.2
42.5°	1644.3	1572.9	1366.6	1162.1	1027.5	944.7	896.9	850.7	793.2	734.0	692.4
45°	1470.9	1480.3	1293.9	1085.8	947.6	864.5	819.5	787.3	736.3	687.5	644.7
47.5°	1253.4	1341.6	1208.5	1004.4	863.4	785.3	746.0	718.0	683.5	635.6	596.6
50°	1111.3	1237.3	1140.2	949.9	810.7	733.0	694.1	671.3	641.4	603.6	566.5
52.5°	980.4	1115.7	1057.6	889.1	753.3	682.3	644.4	625.7	601.9	566.4	532.7
55°	799.5	936.5	923.2	797.3	667.5	603.6	574.8	553.8	537.6	511.0	484.4
57.5°	646.7	776.7	783.5	695.2	591.8	528.7	503.9	488.0	477.5	457.4	432.8
60°	550.4	669.7	693.0	626.4	537.6	482.2	457.7	445.0	436.7	420.5	401.7
62.5°	470.5	572.0	598.4	550.5	485.7	433.7	414.7	402.4	396.7	382.9	366.2
65°	360.1	444.4	469.9	443.3	409.4	367.9	352.3	341.8	336.8	329.1	316.8
67.5°	270.8	332.2	360.2	341.4	329.2	303.0	293.1	287.4	283.0	277.6	267.4
70°	217.5	263.0	291.9	286.8	276.9	263.0	255.8	251.9	247.4	243.0	234.2
72.5°	174.9	206.2	233.3	235.8	227.6	224.9	218.5	216.9	214.2	208.9	204.0
75°	115.9	137.6	156.5	163.7	167.0	169.7	167.0	166.5	165.9	161.4	158.7
77.5°	76.0	87.6	99.5	111.9	117.1	120.8	121.7	123.8	122.3	119.9	118.6
80°	58.3	61.1	69.4	79.9	88.2	91.6	93.8	94.9	94.3	93.8	91.6
82.5°	42.3	44.6	48.5	55.9	62.9	68.5	69.8	69.5	70.8	71.1	69.4
85°	22.7	23.3	24.4	25.5	29.4	35.5	37.2	38.3	39.4	39.4	36.0
87.5°	9.5	8.7	9.2	9.0	10.0	10.1	12.5	14.4	15.2	13.6	14.0
90°	12.1	10.2	8.3	7.0	5.7	3.8	2.5	1.3	2.5	3.8	5.7
92.5°	81.0	53.6	36.9	27.4	22.1	17.1	11.7	7.9	11.7	17.1	22.1
95°	232.0	137.1	82.8	58.0	41.4	30.6	23.6	21.7	23.6	30.6	41.4
97.5°	254.6	147.5	95.7	68.8	52.5	43.1	37.6	36.9	37.6	43.1	52.5
100°	240.3	145.9	101.3	76.5	61.2	52.3	47.8	47.2	47.8	52.3	61.2
102.5°	228.0	148.0	107.9	85.2	71.4	62.9	59.0	57.9	59.0	62.9	71.4
105°	219.2	153.6	119.2	99.5	87.3	79.7	75.8	73.9	75.8	79.7	87.3
107.5°	218.7	164.0	133.9	115.5	104.1	96.6	92.9	91.0	92.9	96.6	104.1
110°	221.2	172.8	144.1	126.2	115.4	108.4	105.2	103.3	105.2	108.4	115.4



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	226.2	181.4	154.7	137.5	126.6	119.6	116.4	114.5	116.4	119.6	126.6
115°	234.6	195.7	171.5	154.3	143.4	137.1	133.2	130.7	133.2	137.1	143.4
117.5°	245.6	210.8	186.9	171.0	158.8	153.0	149.8	146.8	149.8	153.0	158.8
120°	253.7	220.5	197.6	181.6	169.6	163.1	160.0	158.1	160.0	163.1	169.6
122.5°	261.3	230.7	208.3	191.4	179.8	172.8	169.7	167.8	169.7	172.8	179.8
125°	273.5	245.4	223.1	205.9	193.8	186.8	183.0	181.6	183.0	186.8	193.8
127.5°	283.4	258.1	236.6	219.4	206.0	198.9	194.1	192.2	194.1	198.9	206.0
130°	290.0	265.8	244.8	227.6	214.2	206.5	200.8	198.9	200.8	206.5	214.2
132.5°	296.1	272.4	251.9	235.2	221.8	212.6	206.4	204.0	206.4	212.6	221.8
135°	304.0	282.3	262.6	245.4	232.0	222.5	215.5	212.9	215.5	222.5	232.0
137.5°	309.9	289.3	270.3	254.3	241.1	230.9	224.0	221.3	224.0	230.9	241.1
140°	313.0	293.8	275.3	259.4	246.7	236.5	230.1	226.9	230.1	236.5	246.7
142.5°	316.0	297.4	279.4	264.6	251.8	242.6	235.7	233.0	235.7	242.6	251.8
145°	319.4	302.1	285.6	270.9	260.1	250.5	244.8	242.9	244.8	250.5	260.1
147.5°	321.4	306.0	290.8	278.3	267.8	259.6	254.0	252.8	254.0	259.6	267.8
150°	321.9	308.5	293.8	282.3	273.5	265.1	260.1	259.4	260.1	265.1	273.5
152.5°	322.9	310.1	297.4	286.4	278.6	271.3	266.2	266.0	266.2	271.3	278.6
155°	323.2	313.0	302.1	293.2	286.2	279.8	276.0	276.0	276.0	279.8	286.2
157.5°	323.8	314.6	306.0	299.1	293.1	287.5	284.4	283.9	284.4	287.5	293.1
160°	323.8	316.2	308.5	302.1	297.7	292.6	290.0	290.0	290.0	292.6	297.7
162.5°	323.3	316.7	310.1	304.7	300.8	296.7	294.6	294.6	294.6	296.7	300.8
165°	321.9	317.4	312.3	307.9	305.3	302.1	300.8	301.5	300.8	302.1	305.3
167.5°	320.9	317.3	313.6	310.8	309.0	306.6	306.0	306.7	306.0	306.6	309.0
170°	319.4	316.8	313.6	312.3	311.0	309.2	308.5	309.8	308.5	309.2	311.0
172.5°	318.9	316.8	314.1	313.3	312.6	311.2	311.0	311.9	311.0	311.2	312.6
175°	317.4	316.2	314.9	314.2	314.2	313.0	313.6	314.2	313.6	313.0	314.2
177.5°	316.4	315.4	314.9	314.9	314.9	314.4	314.9	315.4	314.9	314.4	314.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1273.9	1268.1	1264.1	1255.2	1249.5	1243.2	1237.1	1241.0	1240.6	1240.2	1240.2
5°	1231.2	1218.4	1206.8	1191.8	1182.3	1170.7	1161.8	1160.7	1162.9	1155.2	1150.7
7.5°	1188.8	1171.3	1154.9	1138.3	1120.8	1106.8	1098.0	1093.9	1088.3	1083.5	1078.5
10°	1159.0	1138.6	1122.4	1101.9	1083.0	1066.4	1055.9	1048.6	1044.7	1040.9	1033.6
12.5°	1128.5	1108.3	1087.9	1064.6	1046.7	1027.4	1019.5	1011.4	1004.0	999.6	989.7
15°	1083.6	1057.5	1035.9	1011.5	991.5	972.7	961.6	945.4	943.2	937.7	927.7
17.5°	1038.7	1010.3	980.5	962.5	939.9	920.2	903.4	898.0	882.1	876.1	867.4
20°	1003.1	977.1	954.3	930.5	897.7	879.4	866.1	858.9	846.1	838.4	832.8
22.5°	972.5	946.0	919.7	891.9	864.9	844.3	834.6	823.4	816.4	805.5	799.5
25°	928.8	899.9	868.3	838.4	819.0	803.4	787.9	777.9	767.9	762.9	751.8
27.5°	878.0	847.8	818.2	795.5	771.7	756.4	742.2	733.4	721.4	713.0	706.9
30°	850.0	814.5	789.0	768.4	737.9	723.5	713.0	701.9	693.0	684.1	678.0
32.5°	817.6	785.2	761.0	735.6	712.2	696.4	682.8	673.0	665.4	657.0	650.9
35°	766.8	739.6	714.6	689.1	671.9	655.8	639.8	631.4	624.2	616.4	610.9
37.5°	720.8	695.5	671.7	647.5	626.1	613.1	600.1	593.8	584.0	578.8	573.2
40°	692.4	667.5	642.0	618.6	596.5	586.4	574.8	565.4	556.5	552.6	546.5
42.5°	661.4	636.4	614.9	589.8	571.6	558.1	547.3	537.0	530.4	524.6	521.2
45°	615.3	593.1	572.0	547.1	529.9	518.2	506.0	496.6	490.5	486.6	480.5
47.5°	570.6	548.4	527.0	505.2	488.6	475.2	463.1	456.5	448.4	443.7	439.5
50°	538.2	518.2	495.5	475.5	458.9	445.6	435.5	427.2	420.0	413.9	411.2
52.5°	508.4	487.1	467.5	448.9	431.3	416.2	407.2	398.4	393.0	386.0	382.7
55°	459.4	438.9	422.2	403.9	386.7	374.0	362.9	355.1	349.5	341.8	337.4
57.5°	413.4	394.9	375.0	359.2	341.4	330.7	321.5	311.0	304.2	298.1	293.8
60°	382.3	361.2	344.0	329.1	313.5	299.6	291.3	283.0	275.7	269.6	265.8
62.5°	349.8	331.5	315.1	298.8	284.6	272.6	262.9	255.9	249.6	245.6	241.8
65°	300.2	285.8	269.1	255.8	242.5	233.6	225.8	219.7	215.2	212.5	209.2
67.5°	254.5	240.4	225.9	212.9	204.0	197.2	192.1	186.9	184.7	181.1	178.9
70°	224.7	210.3	197.5	187.5	178.6	173.7	170.3	166.5	164.2	159.8	157.6
72.5°	192.3	181.9	172.7	164.4	157.4	152.8	148.5	143.8	140.2	135.3	133.1
75°	151.5	142.0	134.9	129.3	124.8	118.7	112.6	107.6	106.0	104.3	103.8
77.5°	112.2	106.2	101.0	96.3	90.7	86.3	85.0	83.9	83.6	82.7	82.7
80°	88.2	82.7	78.8	73.2	69.9	69.9	69.9	68.8	69.4	69.4	69.4
82.5°	65.6	60.5	58.4	56.3	55.7	56.2	56.2	56.3	56.0	56.9	56.5
85°	33.8	34.4	35.5	35.0	35.5	35.5	36.6	36.0	36.6	35.5	36.6
87.5°	13.9	15.4	16.2	17.0	17.9	17.9	18.2	18.3	18.8	19.0	19.2
90°	7.0	8.3	10.2	12.1	14.0	15.9	15.3	15.9	16.6	17.2	18.5
92.5°	27.4	36.9	53.6	81.0	107.9	98.0	73.9	53.6	42.6	37.6	34.3
95°	58.0	82.8	137.1	232.0	336.6	378.0	306.6	229.5	155.6	121.7	98.8
97.5°	68.8	95.7	147.5	254.6	428.8	585.8	626.7	572.0	458.2	375.9	299.7
100°	76.5	101.3	145.9	240.3	408.0	603.6	729.2	751.5	699.9	625.3	534.8
102.5°	85.2	107.9	148.0	228.0	377.3	570.5	734.3	811.1	809.5	766.1	708.7
105°	99.5	119.2	153.6	219.2	339.7	512.5	695.5	828.7	892.3	904.5	887.9
107.5°	115.5	133.9	164.0	218.7	315.8	461.2	627.4	778.4	881.9	937.8	960.4
110°	126.2	144.1	172.8	221.2	306.6	432.2	584.5	730.5	847.7	928.1	972.7



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	137.5	154.7	181.4	226.2	301.5	412.8	547.3	683.1	802.9	892.9	950.2
115°	154.3	171.5	195.7	234.6	299.6	392.0	502.3	620.2	731.1	824.8	894.3
117.5°	171.0	186.9	210.8	245.6	300.8	379.8	475.2	574.7	670.4	754.6	825.1
120°	181.6	197.6	220.5	253.7	302.8	374.1	460.9	550.7	636.7	713.3	777.6
122.5°	191.4	208.3	230.7	261.3	306.3	370.6	449.1	531.9	609.8	680.6	740.5
125°	205.9	223.1	245.4	273.5	311.7	365.9	434.1	506.7	576.3	637.4	688.4
127.5°	219.4	236.6	258.1	283.4	317.8	363.6	420.9	484.9	546.7	602.0	648.4
130°	227.6	244.8	265.8	290.0	321.9	362.1	413.7	471.1	528.4	580.1	623.4
132.5°	235.2	251.9	272.4	296.1	325.0	361.5	407.1	458.3	511.1	559.1	600.5
135°	245.4	262.6	282.3	304.0	329.5	360.8	398.4	441.1	486.3	527.7	564.1
137.5°	254.3	270.3	289.3	309.9	332.6	359.4	390.9	425.4	462.5	498.2	529.7
140°	259.4	275.3	293.8	313.0	334.7	358.9	386.3	416.2	448.7	479.3	506.7
142.5°	264.6	279.4	297.4	316.0	336.1	357.8	382.2	407.6	435.5	462.0	485.8
145°	270.9	285.6	302.1	319.4	337.2	356.3	376.7	397.1	418.2	438.5	457.1
147.5°	278.3	290.8	306.0	321.4	337.2	353.9	371.4	388.6	405.3	421.8	434.9
150°	282.3	293.8	308.5	321.9	337.2	351.9	367.8	382.5	397.1	410.5	422.6
152.5°	286.4	297.4	310.1	322.9	335.7	349.3	363.7	376.8	389.5	401.3	411.4
155°	293.2	302.1	313.0	323.2	334.0	344.9	357.6	368.4	378.6	388.2	395.8
157.5°	299.1	306.0	314.6	323.8	331.8	340.9	350.7	359.5	368.0	375.4	381.4
160°	302.1	308.5	316.2	323.8	330.8	337.9	346.1	354.4	361.4	367.8	372.3
162.5°	304.7	310.1	316.7	323.3	328.8	334.8	341.5	348.3	354.2	360.1	364.1
165°	307.9	312.3	317.4	321.9	325.7	330.2	335.3	340.4	344.2	348.7	351.9
167.5°	310.8	313.6	317.3	320.9	322.7	325.6	329.3	333.5	336.4	339.0	341.3
170°	312.3	313.6	316.8	319.4	320.7	322.5	325.7	328.9	330.8	333.4	334.7
172.5°	313.3	314.1	316.8	318.9	319.1	320.0	322.1	324.8	326.2	328.2	329.1
175°	314.2	314.9	316.2	317.4	316.8	316.8	318.0	319.4	320.0	321.2	321.2
177.5°	314.9	314.9	315.4	316.4	315.4	314.9	315.4	315.9	316.4	316.9	316.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1234.9	1234.4	1234.9	1233.1	1234.9	1234.4	1234.9	1240.2	1240.2	1240.6	1241.0
5°	1149.1	1148.5	1146.9	1141.8	1146.9	1148.5	1149.1	1150.7	1155.2	1162.9	1160.7
7.5°	1074.2	1073.4	1068.5	1068.6	1068.5	1073.4	1074.2	1078.5	1083.5	1088.3	1093.9
10°	1029.8	1030.3	1023.7	1019.8	1023.7	1030.3	1029.8	1033.6	1040.9	1044.7	1048.6
12.5°	986.8	984.1	978.8	974.5	978.8	984.1	986.8	989.7	999.6	1004.0	1011.4
15°	929.9	924.4	911.0	912.2	911.0	924.4	929.9	927.7	937.7	943.2	945.4
17.5°	863.0	858.9	858.7	850.9	858.7	858.9	863.0	867.4	876.1	882.1	898.0
20°	823.9	821.2	822.2	814.5	822.2	821.2	823.9	832.8	838.4	846.1	858.9
22.5°	793.3	790.5	785.9	783.4	785.9	790.5	793.3	799.5	805.5	816.4	823.4
25°	748.4	744.0	739.6	742.4	739.6	744.0	748.4	751.8	762.9	767.9	777.9
27.5°	703.7	700.3	695.9	695.3	695.9	700.3	703.7	706.9	713.0	721.4	733.4
30°	675.2	671.9	669.7	666.9	669.7	671.9	675.2	678.0	684.1	693.0	701.9
32.5°	646.4	645.7	641.7	641.2	641.7	645.7	646.4	650.9	657.0	665.4	673.0
35°	608.6	605.4	604.2	604.8	604.2	605.4	608.6	610.9	616.4	624.2	631.4
37.5°	572.8	568.3	566.4	564.4	566.4	568.3	572.8	573.2	578.8	584.0	593.8
40°	547.1	542.7	541.5	540.4	541.5	542.7	547.1	546.5	552.6	556.5	565.4
42.5°	518.2	516.4	515.8	513.8	515.8	516.4	518.2	521.2	524.6	530.4	537.0
45°	478.8	478.3	474.9	476.1	474.9	478.3	478.8	480.5	486.6	490.5	496.6
47.5°	437.3	434.9	432.5	434.1	432.5	434.9	437.3	439.5	443.7	448.4	456.5
50°	409.0	407.8	402.8	403.9	402.8	407.8	409.0	411.2	413.9	420.0	427.2
52.5°	380.5	376.3	374.4	373.7	374.4	376.3	380.5	382.7	386.0	393.0	398.4
55°	333.5	328.5	326.3	325.1	326.3	328.5	333.5	337.4	341.8	349.5	355.1
57.5°	287.3	285.9	284.2	285.4	284.2	285.9	287.3	293.8	298.1	304.2	311.0
60°	260.2	260.2	260.2	259.7	260.2	260.2	260.2	265.8	269.6	275.7	283.0
62.5°	239.4	238.0	237.6	238.4	237.6	238.0	239.4	241.8	245.6	249.6	255.9
65°	207.5	206.9	204.7	204.2	204.7	206.9	207.5	209.2	212.5	215.2	219.7
67.5°	177.4	175.5	174.8	174.0	174.8	175.5	177.4	178.9	181.1	184.7	186.9
70°	154.8	153.7	150.3	150.9	150.3	153.7	154.8	157.6	159.8	164.2	166.5
72.5°	130.4	129.3	128.6	127.8	128.6	129.3	130.4	133.1	135.3	140.2	143.8
75°	103.2	102.6	102.1	104.3	102.1	102.6	103.2	103.8	104.3	106.0	107.6
77.5°	82.7	82.7	83.0	82.1	83.0	82.7	82.7	82.7	82.7	83.6	83.9
80°	69.4	69.4	68.8	68.8	68.8	69.4	69.4	69.4	69.4	69.4	68.8
82.5°	55.6	56.0	56.3	55.5	56.3	56.0	55.6	56.5	56.9	56.0	56.3
85°	36.6	36.0	37.2	36.6	37.2	36.0	36.6	36.6	35.5	36.6	36.0
87.5°	20.0	19.2	19.3	19.6	19.3	19.2	20.0	19.2	19.0	18.8	18.3
90°	17.9	18.5	19.2	18.5	19.2	18.5	17.9	18.5	17.2	16.6	15.9
92.5°	33.2	31.2	31.9	30.7	31.9	31.2	33.2	34.3	37.6	42.6	53.6
95°	86.7	81.0	76.5	73.9	76.5	81.0	86.7	98.8	121.7	155.6	229.5
97.5°	252.7	224.0	206.8	201.3	206.8	224.0	252.7	299.7	375.9	458.2	572.0
100°	470.4	423.9	399.0	399.7	399.0	423.9	470.4	534.8	625.3	699.9	751.5
102.5°	658.6	621.7	601.0	586.3	601.0	621.7	658.6	708.7	766.1	809.5	811.1
105°	858.6	834.4	814.0	810.8	814.0	834.4	858.6	887.9	904.5	892.3	828.7
107.5°	961.0	952.8	945.9	940.0	945.9	952.8	961.0	960.4	937.8	881.9	778.4
110°	990.5	995.6	994.3	993.1	994.3	995.6	990.5	972.7	928.1	847.7	730.5



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	982.9	998.7	1003.6	1003.8	1003.6	998.7	982.9	950.2	892.9	802.9	683.1
115°	942.1	970.1	982.9	986.1	982.9	970.1	942.1	894.3	824.8	731.1	620.2
117.5°	874.9	907.0	925.4	929.8	925.4	907.0	874.9	825.1	754.6	670.4	574.7
120°	828.0	863.7	879.0	882.8	879.0	863.7	828.0	777.6	713.3	636.7	550.7
122.5°	785.1	817.3	834.1	838.9	834.1	817.3	785.1	740.5	680.6	609.8	531.9
125°	729.2	757.2	773.1	777.6	773.1	757.2	729.2	688.4	637.4	576.3	506.7
127.5°	684.7	708.7	723.1	727.2	723.1	708.7	684.7	648.4	602.0	546.7	484.9
130°	657.2	680.1	693.5	698.6	693.5	680.1	657.2	623.4	580.1	528.4	471.1
132.5°	632.2	655.2	667.0	670.6	667.0	655.2	632.2	600.5	559.1	511.1	458.3
135°	595.3	614.5	625.9	630.4	625.9	614.5	595.3	564.1	527.7	486.3	441.1
137.5°	556.0	575.4	585.1	588.0	585.1	575.4	556.0	529.7	498.2	462.5	425.4
140°	531.0	548.8	559.1	558.4	559.1	548.8	531.0	506.7	479.3	448.7	416.2
142.5°	506.5	522.3	531.5	530.8	531.5	522.3	506.5	485.8	462.0	435.5	407.6
145°	473.0	486.3	491.5	492.7	491.5	486.3	473.0	457.1	438.5	418.2	397.1
147.5°	446.9	456.0	460.9	461.4	460.9	456.0	446.9	434.9	421.8	405.3	388.6
150°	432.2	439.2	443.0	443.0	443.0	439.2	432.2	422.6	410.5	397.1	382.5
152.5°	418.9	425.4	427.7	427.7	427.7	425.4	418.9	411.4	401.3	389.5	376.8
155°	401.5	406.7	408.0	408.5	408.0	406.7	401.5	395.8	388.2	378.6	368.4
157.5°	386.4	390.2	391.3	391.1	391.3	390.2	386.4	381.4	375.4	368.0	359.5
160°	376.7	380.5	380.5	379.9	380.5	380.5	376.7	372.3	367.8	361.4	354.4
162.5°	367.0	370.3	370.3	369.7	370.3	370.3	367.0	364.1	360.1	354.2	348.3
165°	354.4	356.9	356.3	356.3	356.3	356.9	354.4	351.9	348.7	344.2	340.4
167.5°	342.4	344.2	343.6	343.6	343.6	344.2	342.4	341.3	339.0	336.4	333.5
170°	335.3	336.6	335.9	335.9	335.9	336.6	335.3	334.7	333.4	330.8	328.9
172.5°	329.1	330.4	329.3	328.8	329.3	330.4	329.1	329.1	328.2	326.2	324.8
175°	321.2	321.9	321.2	320.7	321.2	321.9	321.2	321.2	321.2	320.0	319.4
177.5°	316.4	316.9	315.9	315.9	315.9	316.9	316.4	316.9	316.9	316.4	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1237.1	1243.2	1249.5	1255.2	1264.1	1268.1	1273.9	1276.1	1282.8	1292.6	1300.6
5°	1161.8	1170.7	1182.3	1191.8	1206.8	1218.4	1231.2	1243.4	1257.8	1278.3	1296.7
7.5°	1098.0	1106.8	1120.8	1138.3	1154.9	1171.3	1188.8	1205.4	1226.0	1255.5	1284.7
10°	1055.9	1066.4	1083.0	1101.9	1122.4	1138.6	1159.0	1180.1	1205.7	1239.5	1274.5
12.5°	1019.5	1027.4	1046.7	1064.6	1087.9	1108.3	1128.5	1153.1	1182.1	1218.2	1260.3
15°	961.6	972.7	991.5	1011.5	1035.9	1057.5	1083.6	1113.5	1141.8	1186.3	1237.3
17.5°	903.4	920.2	939.9	962.5	980.5	1010.3	1038.7	1069.4	1104.2	1151.3	1207.3
20°	866.1	879.4	897.7	930.5	954.3	977.1	1003.1	1041.5	1073.6	1126.9	1185.1
22.5°	834.6	844.3	864.9	891.9	919.7	946.0	972.5	1009.0	1048.7	1099.3	1162.5
25°	787.9	803.4	819.0	838.4	868.3	899.9	928.8	959.9	1002.0	1055.9	1124.1
27.5°	742.2	756.4	771.7	795.5	818.2	847.8	878.0	913.6	958.9	1015.8	1085.0
30°	713.0	723.5	737.9	768.4	789.0	814.5	850.0	881.7	923.8	984.3	1057.5
32.5°	682.8	696.4	712.2	735.6	761.0	785.2	817.6	851.9	895.0	954.6	1029.6
35°	639.8	655.8	671.9	689.1	714.6	739.6	766.8	804.5	848.3	906.0	979.8
37.5°	600.1	613.1	626.1	647.5	671.7	695.5	720.8	758.0	799.3	861.5	929.3
40°	574.8	586.4	596.5	618.6	642.0	667.5	692.4	725.2	769.6	827.9	893.3
42.5°	547.3	558.1	571.6	589.8	614.9	636.4	661.4	692.4	734.0	793.2	850.7
45°	506.0	518.2	529.9	547.1	572.0	593.1	615.3	644.7	687.5	736.3	787.3
47.5°	463.1	475.2	488.6	505.2	527.0	548.4	570.6	596.6	635.6	683.5	718.0
50°	435.5	445.6	458.9	475.5	495.5	518.2	538.2	566.5	603.6	641.4	671.3
52.5°	407.2	416.2	431.3	448.9	467.5	487.1	508.4	532.7	566.4	601.9	625.7
55°	362.9	374.0	386.7	403.9	422.2	438.9	459.4	484.4	511.0	537.6	553.8
57.5°	321.5	330.7	341.4	359.2	375.0	394.9	413.4	432.8	457.4	477.5	488.0
60°	291.3	299.6	313.5	329.1	344.0	361.2	382.3	401.7	420.5	436.7	445.0
62.5°	262.9	272.6	284.6	298.8	315.1	331.5	349.8	366.2	382.9	396.7	402.4
65°	225.8	233.6	242.5	255.8	269.1	285.8	300.2	316.8	329.1	336.8	341.8
67.5°	192.1	197.2	204.0	212.9	225.9	240.4	254.5	267.4	277.6	283.0	287.4
70°	170.3	173.7	178.6	187.5	197.5	210.3	224.7	234.2	243.0	247.4	251.9
72.5°	148.5	152.8	157.4	164.4	172.7	181.9	192.3	204.0	208.9	214.2	216.9
75°	112.6	118.7	124.8	129.3	134.9	142.0	151.5	158.7	161.4	165.9	166.5
77.5°	85.0	86.3	90.7	96.3	101.0	106.2	112.2	118.6	119.9	122.3	123.8
80°	69.9	69.9	69.9	73.2	78.8	82.7	88.2	91.6	93.8	94.3	94.9
82.5°	56.2	56.2	55.7	56.3	58.4	60.5	65.6	69.4	71.1	70.8	69.5
85°	36.6	35.5	35.5	35.0	35.5	34.4	33.8	36.0	39.4	39.4	38.3
87.5°	18.2	17.9	17.9	17.0	16.2	15.4	13.9	14.0	13.6	15.2	14.4
90°	15.3	15.9	14.0	12.1	10.2	8.3	7.0	5.7	3.8	2.5	1.3
92.5°	73.9	98.0	107.9	81.0	53.6	36.9	27.4	22.1	17.1	11.7	7.9
95°	306.6	378.0	336.6	232.0	137.1	82.8	58.0	41.4	30.6	23.6	21.7
97.5°	626.7	585.8	428.8	254.6	147.5	95.7	68.8	52.5	43.1	37.6	36.9
100°	729.2	603.6	408.0	240.3	145.9	101.3	76.5	61.2	52.3	47.8	47.2
102.5°	734.3	570.5	377.3	228.0	148.0	107.9	85.2	71.4	62.9	59.0	57.9
105°	695.5	512.5	339.7	219.2	153.6	119.2	99.5	87.3	79.7	75.8	73.9
107.5°	627.4	461.2	315.8	218.7	164.0	133.9	115.5	104.1	96.6	92.9	91.0
110°	584.5	432.2	306.6	221.2	172.8	144.1	126.2	115.4	108.4	105.2	103.3



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	547.3	412.8	301.5	226.2	181.4	154.7	137.5	126.6	119.6	116.4	114.5
115°	502.3	392.0	299.6	234.6	195.7	171.5	154.3	143.4	137.1	133.2	130.7
117.5°	475.2	379.8	300.8	245.6	210.8	186.9	171.0	158.8	153.0	149.8	146.8
120°	460.9	374.1	302.8	253.7	220.5	197.6	181.6	169.6	163.1	160.0	158.1
122.5°	449.1	370.6	306.3	261.3	230.7	208.3	191.4	179.8	172.8	169.7	167.8
125°	434.1	365.9	311.7	273.5	245.4	223.1	205.9	193.8	186.8	183.0	181.6
127.5°	420.9	363.6	317.8	283.4	258.1	236.6	219.4	206.0	198.9	194.1	192.2
130°	413.7	362.1	321.9	290.0	265.8	244.8	227.6	214.2	206.5	200.8	198.9
132.5°	407.1	361.5	325.0	296.1	272.4	251.9	235.2	221.8	212.6	206.4	204.0
135°	398.4	360.8	329.5	304.0	282.3	262.6	245.4	232.0	222.5	215.5	212.9
137.5°	390.9	359.4	332.6	309.9	289.3	270.3	254.3	241.1	230.9	224.0	221.3
140°	386.3	358.9	334.7	313.0	293.8	275.3	259.4	246.7	236.5	230.1	226.9
142.5°	382.2	357.8	336.1	316.0	297.4	279.4	264.6	251.8	242.6	235.7	233.0
145°	376.7	356.3	337.2	319.4	302.1	285.6	270.9	260.1	250.5	244.8	242.9
147.5°	371.4	353.9	337.2	321.4	306.0	290.8	278.3	267.8	259.6	254.0	252.8
150°	367.8	351.9	337.2	321.9	308.5	293.8	282.3	273.5	265.1	260.1	259.4
152.5°	363.7	349.3	335.7	322.9	310.1	297.4	286.4	278.6	271.3	266.2	266.0
155°	357.6	344.9	334.0	323.2	313.0	302.1	293.2	286.2	279.8	276.0	276.0
157.5°	350.7	340.9	331.8	323.8	314.6	306.0	299.1	293.1	287.5	284.4	283.9
160°	346.1	337.9	330.8	323.8	316.2	308.5	302.1	297.7	292.6	290.0	290.0
162.5°	341.5	334.8	328.8	323.3	316.7	310.1	304.7	300.8	296.7	294.6	294.6
165°	335.3	330.2	325.7	321.9	317.4	312.3	307.9	305.3	302.1	300.8	301.5
167.5°	329.3	325.6	322.7	320.9	317.3	313.6	310.8	309.0	306.6	306.0	306.7
170°	325.7	322.5	320.7	319.4	316.8	313.6	312.3	311.0	309.2	308.5	309.8
172.5°	322.1	320.0	319.1	318.9	316.8	314.1	313.3	312.6	311.2	311.0	311.9
175°	318.0	316.8	316.8	317.4	316.2	314.9	314.2	314.2	313.0	313.6	314.2
177.5°	315.4	314.9	315.4	316.4	315.4	314.9	314.9	314.9	314.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1303.2	1308.1	1314.3	1323.6	1330.7	1336.9	1338.2	1340.0	1344.5	1352.0	1357.8
5°	1311.7	1324.4	1344.9	1364.9	1386.6	1404.3	1420.9	1432.6	1443.7	1467.0	1485.9
7.5°	1309.0	1337.4	1369.5	1405.4	1441.7	1476.8	1509.5	1538.7	1567.7	1601.7	1640.5
10°	1307.2	1340.5	1383.7	1429.8	1480.3	1529.7	1577.4	1614.6	1657.8	1696.7	1746.0
12.5°	1298.8	1346.7	1398.4	1457.3	1519.4	1576.3	1639.1	1690.4	1740.0	1796.1	1853.5
15°	1287.8	1346.1	1411.5	1489.7	1584.0	1652.9	1717.2	1806.5	1867.6	1928.6	2010.8
17.5°	1267.7	1338.8	1420.6	1522.2	1600.9	1693.4	1790.2	1860.8	1943.0	2029.0	2103.4
20°	1251.7	1334.4	1426.0	1525.8	1626.2	1726.6	1820.4	1904.8	1989.7	2089.0	2150.0
22.5°	1235.7	1317.5	1412.6	1518.7	1626.7	1732.4	1838.6	1937.6	2033.1	2133.3	2211.3
25°	1201.8	1298.9	1402.1	1510.3	1616.8	1733.3	1859.8	1970.3	2088.4	2191.6	2265.4
27.5°	1167.3	1256.4	1359.1	1468.8	1587.3	1725.0	1873.8	1999.3	2117.7	2191.6	2214.8
30°	1136.3	1230.6	1324.9	1436.5	1564.6	1718.3	1876.5	2020.1	2117.3	2149.5	2125.6
32.5°	1104.8	1190.3	1283.7	1397.8	1534.0	1701.9	1880.0	2007.8	2066.2	2041.6	1944.5
35°	1049.2	1126.3	1216.8	1331.1	1487.5	1692.8	1865.4	1951.9	1937.5	1798.8	1615.7
37.5°	989.7	1052.6	1136.3	1255.8	1439.3	1656.8	1802.3	1815.1	1690.3	1477.3	1265.8
40°	942.6	999.2	1085.2	1210.1	1402.1	1621.2	1738.9	1687.3	1493.6	1256.7	1080.3
42.5°	896.9	944.7	1027.5	1162.1	1366.6	1572.9	1644.3	1531.9	1308.6	1084.5	924.1
45°	819.5	864.5	947.6	1085.8	1293.9	1480.3	1470.9	1275.5	1052.0	871.6	738.5
47.5°	746.0	785.3	863.4	1004.4	1208.5	1341.6	1253.4	1045.5	855.9	711.2	616.2
50°	694.1	733.0	810.7	949.9	1140.2	1237.3	1111.3	911.0	737.4	617.5	542.1
52.5°	644.4	682.3	753.3	889.1	1057.6	1115.7	980.4	794.8	650.0	546.5	481.7
55°	574.8	603.6	667.5	797.3	923.2	936.5	799.5	644.2	524.9	452.7	408.4
57.5°	503.9	528.7	591.8	695.2	783.5	776.7	646.7	512.3	432.0	378.4	346.3
60°	457.7	482.2	537.6	626.4	693.0	669.7	550.4	442.2	373.4	334.0	308.5
62.5°	414.7	433.7	485.7	550.5	598.4	572.0	470.5	381.0	326.4	293.2	273.0
65°	352.3	367.9	409.4	443.3	469.9	444.4	360.1	297.9	258.5	235.2	221.4
67.5°	293.1	303.0	329.2	341.4	360.2	332.2	270.8	229.2	206.8	187.1	177.4
70°	255.8	263.0	276.9	286.8	291.9	263.0	217.5	186.9	168.1	154.3	148.1
72.5°	218.5	224.9	227.6	235.8	233.3	206.2	174.9	150.6	137.1	127.6	119.8
75°	167.0	169.7	167.0	163.7	156.5	137.6	115.9	103.8	93.8	89.4	86.6
77.5°	121.7	120.8	117.1	111.9	99.5	87.6	76.0	71.9	67.6	65.2	64.2
80°	93.8	91.6	88.2	79.9	69.4	61.1	58.3	55.5	53.8	51.0	50.5
82.5°	69.8	68.5	62.9	55.9	48.5	44.6	42.3	41.3	39.6	38.2	38.1
85°	37.2	35.5	29.4	25.5	24.4	23.3	22.7	22.7	20.5	20.0	20.0
87.5°	12.5	10.1	10.0	9.0	9.2	8.7	9.5	9.0	9.0	9.3	8.5
90°	2.5	3.8	5.7	7.0	8.3	10.2	12.1	14.0	15.9	15.3	15.9
92.5°	11.7	17.1	22.1	27.4	36.9	53.6	81.0	107.9	98.0	73.9	53.6
95°	23.6	30.6	41.4	58.0	82.8	137.1	232.0	336.6	378.0	306.6	229.5
97.5°	37.6	43.1	52.5	68.8	95.7	147.5	254.6	428.8	585.8	626.7	572.0
100°	47.8	52.3	61.2	76.5	101.3	145.9	240.3	408.0	603.6	729.2	751.5
102.5°	59.0	62.9	71.4	85.2	107.9	148.0	228.0	377.3	570.5	734.3	811.1
105°	75.8	79.7	87.3	99.5	119.2	153.6	219.2	339.7	512.5	695.5	828.7
107.5°	92.9	96.6	104.1	115.5	133.9	164.0	218.7	315.8	461.2	627.4	778.4
110°	105.2	108.4	115.4	126.2	144.1	172.8	221.2	306.6	432.2	584.5	730.5



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	116.4	119.6	126.6	137.5	154.7	181.4	226.2	301.5	412.8	547.3	683.1
115°	133.2	137.1	143.4	154.3	171.5	195.7	234.6	299.6	392.0	502.3	620.2
117.5°	149.8	153.0	158.8	171.0	186.9	210.8	245.6	300.8	379.8	475.2	574.7
120°	160.0	163.1	169.6	181.6	197.6	220.5	253.7	302.8	374.1	460.9	550.7
122.5°	169.7	172.8	179.8	191.4	208.3	230.7	261.3	306.3	370.6	449.1	531.9
125°	183.0	186.8	193.8	205.9	223.1	245.4	273.5	311.7	365.9	434.1	506.7
127.5°	194.1	198.9	206.0	219.4	236.6	258.1	283.4	317.8	363.6	420.9	484.9
130°	200.8	206.5	214.2	227.6	244.8	265.8	290.0	321.9	362.1	413.7	471.1
132.5°	206.4	212.6	221.8	235.2	251.9	272.4	296.1	325.0	361.5	407.1	458.3
135°	215.5	222.5	232.0	245.4	262.6	282.3	304.0	329.5	360.8	398.4	441.1
137.5°	224.0	230.9	241.1	254.3	270.3	289.3	309.9	332.6	359.4	390.9	425.4
140°	230.1	236.5	246.7	259.4	275.3	293.8	313.0	334.7	358.9	386.3	416.2
142.5°	235.7	242.6	251.8	264.6	279.4	297.4	316.0	336.1	357.8	382.2	407.6
145°	244.8	250.5	260.1	270.9	285.6	302.1	319.4	337.2	356.3	376.7	397.1
147.5°	254.0	259.6	267.8	278.3	290.8	306.0	321.4	337.2	353.9	371.4	388.6
150°	260.1	265.1	273.5	282.3	293.8	308.5	321.9	337.2	351.9	367.8	382.5
152.5°	266.2	271.3	278.6	286.4	297.4	310.1	322.9	335.7	349.3	363.7	376.8
155°	276.0	279.8	286.2	293.2	302.1	313.0	323.2	334.0	344.9	357.6	368.4
157.5°	284.4	287.5	293.1	299.1	306.0	314.6	323.8	331.8	340.9	350.7	359.5
160°	290.0	292.6	297.7	302.1	308.5	316.2	323.8	330.8	337.9	346.1	354.4
162.5°	294.6	296.7	300.8	304.7	310.1	316.7	323.3	328.8	334.8	341.5	348.3
165°	300.8	302.1	305.3	307.9	312.3	317.4	321.9	325.7	330.2	335.3	340.4
167.5°	306.0	306.6	309.0	310.8	313.6	317.3	320.9	322.7	325.6	329.3	333.5
170°	308.5	309.2	311.0	312.3	313.6	316.8	319.4	320.7	322.5	325.7	328.9
172.5°	311.0	311.2	312.6	313.3	314.1	316.8	318.9	319.1	320.0	322.1	324.8
175°	313.6	313.0	314.2	314.2	314.9	316.2	317.4	316.8	316.8	318.0	319.4
177.5°	314.9	314.4	314.9	314.9	314.9	315.4	316.4	315.4	314.9	315.4	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1367.1	1367.1	1368.9	1375.6	1376.5	1382.2	1380.5
5°	1502.5	1513.0	1516.9	1533.6	1543.5	1548.0	1539.1
7.5°	1668.1	1697.8	1711.9	1729.3	1744.7	1749.4	1737.3
10°	1788.8	1819.8	1845.9	1862.1	1877.0	1887.0	1899.7
12.5°	1905.5	1943.7	1968.5	1991.2	2006.6	2019.3	2021.4
15°	2032.4	2090.1	2133.9	2166.1	2182.1	2190.5	2187.2
17.5°	2160.3	2213.8	2245.0	2277.9	2300.1	2301.3	2301.9
20°	2232.7	2284.8	2320.9	2345.3	2370.2	2369.2	2374.7
22.5°	2281.0	2322.1	2349.8	2367.5	2376.0	2371.8	2372.9
25°	2303.7	2315.9	2310.9	2282.6	2275.4	2249.3	2253.7
27.5°	2187.0	2129.2	2069.6	1992.8	1932.2	1883.7	1886.2
30°	2028.5	1926.4	1809.9	1712.2	1624.6	1600.2	1548.0
32.5°	1807.0	1653.8	1517.4	1426.4	1351.1	1330.7	1285.2
35°	1431.5	1282.8	1142.4	1058.1	1024.7	978.2	977.6
37.5°	1112.6	981.7	907.5	844.2	811.1	782.9	780.1
40°	936.0	833.9	777.9	732.4	699.7	678.6	673.6
42.5°	812.6	730.0	677.6	649.4	624.2	613.3	605.2
45°	663.6	608.1	571.4	545.9	534.3	525.9	521.5
47.5°	555.1	517.9	492.9	476.0	466.5	457.7	460.1
50°	496.0	465.5	447.2	431.1	423.9	417.8	418.3
52.5°	448.5	421.1	406.3	394.7	385.7	381.4	379.3
55°	380.6	363.4	348.5	340.1	335.1	329.1	327.3
57.5°	324.7	311.4	299.1	289.8	288.5	282.7	283.4
60°	287.4	276.3	266.4	261.3	257.5	252.4	254.1
62.5°	256.8	247.4	238.4	234.2	230.4	226.7	227.5
65°	210.3	201.4	195.8	193.6	192.0	190.3	188.7
67.5°	167.5	162.2	158.7	153.9	150.5	149.9	148.2
70°	141.0	133.7	127.6	121.5	119.8	119.3	119.8
72.5°	113.0	108.4	106.7	103.8	103.5	102.0	103.0
75°	84.9	83.2	82.1	79.9	79.9	79.9	79.9
77.5°	62.6	61.6	60.9	60.5	59.9	59.1	59.0
80°	48.8	48.3	47.1	47.1	46.6	47.1	46.6
82.5°	36.9	36.8	35.6	35.6	35.1	34.7	35.1
85°	18.8	18.3	19.4	18.3	18.8	17.8	18.8
87.5°	8.6	8.8	8.6	8.5	8.2	9.1	8.2
90°	16.6	17.2	18.5	17.9	18.5	19.2	18.5
92.5°	42.6	37.6	34.3	33.2	31.2	31.9	30.7
95°	155.6	121.7	98.8	86.7	81.0	76.5	73.9
97.5°	458.2	375.9	299.7	252.7	224.0	206.8	201.3
100°	699.9	625.3	534.8	470.4	423.9	399.0	399.7
102.5°	809.5	766.1	708.7	658.6	621.7	601.0	586.3
105°	892.3	904.5	887.9	858.6	834.4	814.0	810.8
107.5°	881.9	937.8	960.4	961.0	952.8	945.9	940.0
110°	847.7	928.1	972.7	990.5	995.6	994.3	993.1



TEST NUMBER: P332344-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	802.9	892.9	950.2	982.9	998.7	1003.6	1003.8
115°	731.1	824.8	894.3	942.1	970.1	982.9	986.1
117.5°	670.4	754.6	825.1	874.9	907.0	925.4	929.8
120°	636.7	713.3	777.6	828.0	863.7	879.0	882.8
122.5°	609.8	680.6	740.5	785.1	817.3	834.1	838.9
125°	576.3	637.4	688.4	729.2	757.2	773.1	777.6
127.5°	546.7	602.0	648.4	684.7	708.7	723.1	727.2
130°	528.4	580.1	623.4	657.2	680.1	693.5	698.6
132.5°	511.1	559.1	600.5	632.2	655.2	667.0	670.6
135°	486.3	527.7	564.1	595.3	614.5	625.9	630.4
137.5°	462.5	498.2	529.7	556.0	575.4	585.1	588.0
140°	448.7	479.3	506.7	531.0	548.8	559.1	558.4
142.5°	435.5	462.0	485.8	506.5	522.3	531.5	530.8
145°	418.2	438.5	457.1	473.0	486.3	491.5	492.7
147.5°	405.3	421.8	434.9	446.9	456.0	460.9	461.4
150°	397.1	410.5	422.6	432.2	439.2	443.0	443.0
152.5°	389.5	401.3	411.4	418.9	425.4	427.7	427.7
155°	378.6	388.2	395.8	401.5	406.7	408.0	408.5
157.5°	368.0	375.4	381.4	386.4	390.2	391.3	391.1
160°	361.4	367.8	372.3	376.7	380.5	380.5	379.9
162.5°	354.2	360.1	364.1	367.0	370.3	370.3	369.7
165°	344.2	348.7	351.9	354.4	356.9	356.3	356.3
167.5°	336.4	339.0	341.3	342.4	344.2	343.6	343.6
170°	330.8	333.4	334.7	335.3	336.6	335.9	335.9
172.5°	326.2	328.2	329.1	329.1	330.4	329.3	328.8
175°	320.0	321.2	321.2	321.2	321.9	321.2	320.7
177.5°	316.4	316.9	316.9	316.4	316.9	315.9	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9

(END OF REPORT)