

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332387-930

Luminaire Tested: **S123RDIP-S1165D1195U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332387-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1195U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7461.4 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332387-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332387-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48		
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41	41	41	41		
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35	35	35	35	35	35	35		
3	81	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30	30	30	30	30		
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	32	29	26	26	26	26	26	26	26		
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23	23	23	23	23	23	23		
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20	20	20	20	20		
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18	18	18	18	18	18	18		
8	54	42	35	29	50	39	33	28	34	28	25	29	25	21	24	21	18	16	16	16	16	16	16	16		
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	15	15	15	15	15	15	15		
10	47	35	28	24	44	33	27	22	29	24	20	24	20	18	20	17	15	13	13	13	13	13	13	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17009	17009	17009
5°	17074	16839	16935
10°	16978	16628	16571
15°	16796	16238	16067
20°	16544	15753	15385
25°	16286	15206	14719
30°	15945	14574	13779
35°	15594	13943	12917
40°	15271	13200	11849
45°	14846	12466	10886
50°	14380	11632	9808
55°	13902	10678	8801
60°	13464	9657	7698
65°	12893	8550	6594
70°	12180	7179	5325
75°	11137	5648	5011
80°	9930	5002	4612
85°	8386	4434	4113



TEST NUMBER: P332387-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.4	2.0
10°-20°	412.9	5.5
20°-30°	594.5	8.0
30°-40°	669.6	9.0
40°-50°	640.6	8.6
50°-60°	524.6	7.0
60°-70°	354.0	4.7
70°-80°	178.1	2.4
80°-90°	50.7	0.7
90°-100°	46.4	0.6
100°-110°	220.9	3.0
110°-120°	530.6	7.1
120°-130°	675.7	9.1
130°-140°	722.0	9.7
140°-150°	675.1	9.0
150°-160°	544.6	7.3
160°-170°	351.5	4.7
170°-180°	121.1	1.6
0°-30°	1155.7	15.5
0°-40°	1825.4	24.5
0°-60°	2990.6	40.1
0°-90°	3573.3	47.9
90°-120°	797.9	10.7
90°-150°	2870.8	38.5
90°-180°	3888.0	52.1
0°-180°	7461.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1580	1573	1558	1569	1567	150
15°	1507	1492	1457	1451	1442	424
25°	1371	1338	1280	1254	1239	630
35°	1187	1139	1061	1008	983	742
45°	975	915	819	748	715	752
55°	741	675	569	497	469	664
65°	506	434	336	276	259	501
75°	268	206	136	124	120	286
85°	68	41	36	33	33	76
90°	1	11	23	26	28	6
95°	58	22	29	36	36	71
105°	282	287	207	49	42	299
115°	530	535	544	553	557	522
125°	746	754	758	760	762	666
135°	929	935	939	941	939	715
145°	1072	1079	1081	1083	1083	671
155°	1181	1179	1180	1184	1179	544
165°	1246	1243	1242	1249	1243	352
175°	1275	1270	1271	1277	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P332387-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1585.3	1584.4	1583.5	1582.6	1581.7	1579.8	1577.1	1574.3	1571.7	1568.9	1571.4
5°	1580.2	1578.7	1577.4	1575.9	1574.5	1572.1	1568.6	1565.2	1561.8	1558.4	1561.0
7.5°	1565.5	1564.1	1562.5	1561.0	1559.4	1556.4	1552.0	1547.5	1543.1	1538.6	1540.1
10°	1553.3	1551.3	1549.3	1547.3	1545.3	1541.7	1536.6	1531.5	1526.3	1521.3	1521.5
12.5°	1535.9	1533.7	1531.4	1529.2	1527.0	1522.7	1516.5	1510.2	1503.9	1497.6	1497.5
15°	1507.2	1504.0	1500.9	1497.7	1494.6	1489.1	1481.1	1473.1	1465.1	1457.2	1455.7
17.5°	1471.0	1467.4	1463.7	1460.0	1456.5	1449.5	1439.4	1429.2	1419.1	1409.0	1406.0
20°	1444.3	1439.8	1435.3	1430.7	1426.1	1418.5	1407.6	1396.8	1385.9	1375.2	1371.4
22.5°	1414.6	1409.3	1404.1	1398.9	1393.7	1385.3	1373.8	1362.3	1350.8	1339.2	1334.6
25°	1371.3	1364.2	1357.1	1349.9	1342.8	1332.7	1319.6	1306.5	1293.4	1280.3	1274.3
27.5°	1318.7	1310.9	1303.0	1295.2	1287.3	1276.1	1261.5	1246.9	1232.3	1217.7	1209.4
30°	1282.9	1274.3	1265.8	1257.2	1248.7	1236.4	1220.5	1204.5	1188.6	1172.6	1162.9
32.5°	1247.0	1237.3	1227.6	1217.9	1208.3	1195.0	1178.1	1161.2	1144.4	1127.6	1117.0
35°	1186.7	1176.5	1166.2	1156.0	1145.7	1131.8	1114.1	1096.5	1078.8	1061.1	1048.9
37.5°	1125.8	1114.4	1102.9	1091.5	1080.2	1065.0	1046.2	1027.4	1008.5	989.6	975.8
40°	1086.8	1074.2	1061.7	1049.2	1036.7	1020.3	1000.0	979.8	959.6	939.4	924.5
42.5°	1042.7	1030.1	1017.7	1005.1	992.5	975.8	955.0	934.0	913.1	892.3	876.0
45°	975.3	962.5	949.7	936.9	924.0	906.6	884.7	862.7	840.8	818.9	802.7
47.5°	907.8	893.8	879.7	865.7	851.6	833.6	811.6	789.7	767.8	745.9	728.2
50°	858.7	845.3	831.8	818.5	805.1	786.9	763.9	740.8	717.7	694.6	676.9
52.5°	814.6	800.1	785.5	771.0	756.4	737.8	714.9	692.1	669.3	646.5	628.1
55°	740.8	726.8	712.8	698.9	684.9	665.9	641.6	617.4	593.2	569.0	552.5
57.5°	672.5	657.4	642.1	627.0	611.7	592.0	567.7	543.3	519.0	494.7	479.1
60°	625.4	609.8	594.1	578.5	562.7	543.1	519.4	495.9	472.2	448.6	433.2
62.5°	578.2	562.6	546.9	531.2	515.6	495.9	472.3	448.7	425.0	401.4	386.9
65°	506.2	490.6	474.9	459.3	443.6	424.6	402.4	380.2	358.0	335.7	321.8
67.5°	434.2	418.3	402.5	386.7	370.9	352.3	331.0	309.7	288.4	267.1	256.7
70°	387.0	371.7	356.3	340.9	325.5	307.9	288.0	268.0	248.1	228.1	218.2
72.5°	339.9	324.7	309.6	294.4	279.2	262.6	244.5	226.4	208.3	190.2	182.1
75°	267.8	254.2	240.5	226.8	213.2	198.5	182.9	167.1	151.5	135.8	133.0
77.5°	202.2	189.9	177.5	165.2	152.8	141.5	131.5	121.4	111.3	101.3	99.7
80°	160.2	148.5	136.8	125.1	113.5	104.7	98.7	92.7	86.7	80.7	79.9
82.5°	120.2	110.1	100.0	89.9	79.9	73.5	70.7	67.8	65.1	62.3	61.4
85°	67.9	61.6	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.8	22.7	20.6	18.5	16.5	15.7	16.2	16.8	17.4	17.9	17.9
90°	1.0	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6
92.5°	17.6	17.0	16.5	15.8	15.2	16.0	18.1	20.1	22.2	24.2	25.6
95°	57.8	49.2	40.5	31.9	23.2	20.1	22.4	24.7	27.1	29.4	30.8
97.5°	116.1	112.3	108.4	104.5	100.6	91.2	76.0	60.8	45.7	30.5	32.2
100°	160.0	164.3	168.5	172.7	176.9	162.6	129.8	96.9	64.1	31.2	32.9
102.5°	210.1	213.1	216.1	219.2	222.3	205.8	169.9	134.0	98.2	62.3	57.1
105°	282.3	284.6	286.9	289.2	291.6	283.2	264.2	245.3	226.4	207.4	170.2
107.5°	358.4	360.3	362.2	363.9	365.8	368.3	371.3	374.2	377.2	380.3	352.9
110°	409.2	410.9	412.5	414.3	416.0	417.9	420.3	422.6	424.9	427.2	420.3



TEST NUMBER: P332387-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.7	459.2	460.7	462.3	463.7	465.7	468.0	470.3	472.6	474.9	475.1
115°	529.5	530.8	532.0	533.3	534.5	536.1	538.0	539.9	541.8	543.7	545.8
117.5°	599.0	600.5	602.1	603.7	605.3	606.5	607.5	608.5	609.4	610.4	612.0
120°	642.2	644.1	646.0	647.9	649.8	651.1	651.7	652.3	653.0	653.5	655.3
122.5°	686.2	687.7	689.3	690.8	692.4	693.6	694.4	695.2	695.9	696.8	698.0
125°	746.4	748.1	749.7	751.5	753.2	754.4	755.2	756.1	756.9	757.7	758.2
127.5°	804.8	806.4	808.1	809.8	811.5	812.9	813.8	814.9	815.9	816.8	817.6
130°	841.1	842.9	844.5	846.2	847.8	849.1	849.9	850.8	851.7	852.5	853.4
132.5°	876.0	877.7	879.4	881.0	882.7	883.9	884.6	885.3	885.9	886.6	887.5
135°	929.2	930.5	931.7	933.0	934.3	935.3	936.2	937.0	937.8	938.7	939.3
137.5°	974.7	976.3	977.9	979.5	981.1	982.1	982.6	983.1	983.5	984.0	985.0
140°	1005.0	1006.2	1007.5	1008.8	1010.1	1011.0	1011.6	1012.3	1012.9	1013.5	1014.4
142.5°	1033.1	1034.3	1035.6	1036.8	1038.1	1039.0	1039.7	1040.3	1041.0	1041.5	1042.3
145°	1072.3	1073.7	1075.2	1076.7	1078.2	1079.1	1079.5	1079.9	1080.4	1080.8	1081.2
147.5°	1109.2	1110.2	1111.2	1112.1	1113.0	1113.8	1114.2	1114.6	1115.0	1115.4	1115.9
150°	1132.0	1132.5	1133.2	1133.8	1134.5	1135.0	1135.4	1135.8	1136.3	1136.7	1137.1
152.5°	1152.4	1152.7	1153.0	1153.2	1153.6	1153.8	1154.1	1154.4	1154.6	1154.9	1155.6
155°	1181.2	1180.8	1180.3	1179.9	1179.5	1179.4	1179.6	1179.8	1180.1	1180.2	1181.3
157.5°	1203.5	1203.5	1203.5	1203.4	1203.4	1203.2	1203.1	1202.8	1202.6	1202.4	1203.7
160°	1217.2	1217.0	1216.8	1216.6	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1216.6
162.5°	1230.0	1229.6	1229.0	1228.4	1227.8	1227.5	1227.3	1227.1	1226.9	1226.6	1228.1
165°	1245.6	1245.0	1244.3	1243.7	1243.1	1242.7	1242.4	1242.2	1242.0	1241.8	1243.5
167.5°	1257.8	1256.9	1256.1	1255.2	1254.3	1253.9	1253.9	1253.9	1253.9	1253.9	1255.6
170°	1264.5	1263.7	1262.9	1262.0	1261.2	1260.8	1260.8	1260.8	1260.8	1260.8	1262.4
172.5°	1269.1	1268.1	1267.1	1266.1	1265.0	1264.6	1264.8	1264.9	1265.1	1265.3	1267.0
175°	1275.0	1273.9	1272.8	1271.8	1270.7	1270.3	1270.6	1270.7	1271.0	1271.1	1272.7
177.5°	1276.5	1275.6	1274.8	1274.0	1273.1	1272.8	1272.9	1273.1	1273.3	1273.4	1274.8
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332387-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1573.9	1576.5	1578.9	1580.0	1579.5	1579.1	1578.6	1578.1
5°	1563.5	1566.1	1568.6	1569.6	1569.0	1568.5	1567.9	1567.3
7.5°	1541.5	1543.0	1544.3	1544.6	1543.6	1542.6	1541.6	1540.7
10°	1521.8	1522.1	1522.4	1521.8	1520.4	1519.0	1517.5	1516.1
12.5°	1497.3	1497.1	1497.0	1496.1	1494.4	1492.7	1491.1	1489.5
15°	1454.3	1452.9	1451.5	1449.8	1447.7	1445.8	1443.7	1441.8
17.5°	1403.0	1399.9	1396.9	1393.9	1390.9	1388.0	1385.0	1382.0
20°	1367.7	1364.0	1360.3	1356.7	1353.3	1349.9	1346.5	1343.1
22.5°	1330.0	1325.4	1320.8	1316.9	1313.7	1310.5	1307.3	1304.2
25°	1268.4	1262.3	1256.4	1251.8	1248.7	1245.5	1242.4	1239.3
27.5°	1201.1	1192.8	1184.5	1177.9	1173.1	1168.4	1163.6	1158.8
30°	1153.2	1143.6	1133.9	1126.8	1122.3	1117.7	1113.1	1108.6
32.5°	1106.4	1095.8	1085.2	1077.5	1072.7	1067.9	1063.2	1058.3
35°	1036.7	1024.4	1012.2	1003.5	998.3	993.2	988.1	983.0
37.5°	961.8	947.9	934.0	923.9	917.6	911.3	905.0	898.6
40°	909.8	895.0	880.2	869.5	862.9	856.4	849.9	843.3
42.5°	859.9	843.7	827.5	816.5	810.7	804.8	798.9	793.0
45°	786.4	770.2	754.0	742.5	735.6	728.8	721.9	715.1
47.5°	710.5	692.9	675.2	663.4	657.3	651.2	645.1	639.0
50°	659.3	641.6	623.9	611.9	605.4	598.8	592.2	585.7
52.5°	609.8	591.4	573.1	560.9	555.1	549.3	543.4	537.5
55°	536.0	519.4	503.0	491.9	486.2	480.5	474.7	469.0
57.5°	463.5	447.8	432.3	422.0	417.2	412.4	407.5	402.7
60°	417.8	402.4	387.0	376.9	372.1	367.2	362.4	357.6
62.5°	372.4	358.0	343.5	333.8	328.6	323.6	318.5	313.5
65°	307.9	293.9	280.0	271.4	268.3	265.1	262.0	258.9
67.5°	246.2	235.8	225.3	218.5	215.2	211.7	208.4	205.0
70°	208.1	198.2	188.3	181.7	178.6	175.5	172.3	169.2
72.5°	173.9	165.8	157.6	152.9	151.6	150.3	149.0	147.7
75°	130.1	127.3	124.4	122.8	122.2	121.6	121.1	120.5
77.5°	98.2	96.6	95.1	94.0	93.4	92.9	92.3	91.7
80°	79.0	78.2	77.3	76.6	76.1	75.5	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.1	58.0	58.0
85°	34.7	34.2	33.6	33.3	33.3	33.3	33.3	33.3
87.5°	17.8	17.7	17.6	17.5	17.4	17.3	17.1	17.0
90°	24.4	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	26.9	28.3	29.7	30.4	30.7	31.0	31.2	31.5
95°	32.3	33.8	35.2	36.0	36.0	36.0	36.0	36.0
97.5°	33.8	35.5	37.3	38.2	38.4	38.6	38.8	39.1
100°	34.7	36.3	38.0	39.0	39.1	39.4	39.5	39.8
102.5°	51.9	46.6	41.4	39.1	39.4	39.8	40.2	40.5
105°	132.9	95.6	58.4	40.0	40.4	40.8	41.3	41.7
107.5°	325.5	298.2	270.9	243.2	215.2	187.0	159.0	130.9
110°	413.3	406.3	399.4	380.9	350.8	320.7	290.6	260.5



TEST NUMBER: P332387-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	475.2	475.3	475.5	472.3	465.9	459.6	453.2	446.9
115°	547.9	550.0	552.1	553.6	554.4	555.3	556.1	556.9
117.5°	613.8	615.5	617.1	618.1	618.2	618.4	618.6	618.7
120°	657.0	658.6	660.3	661.1	661.1	661.1	661.1	661.1
122.5°	699.1	700.3	701.5	702.1	702.3	702.5	702.7	702.9
125°	758.6	759.0	759.5	759.9	760.3	760.8	761.2	761.6
127.5°	818.2	818.9	819.5	819.7	819.3	818.9	818.5	818.0
130°	854.2	855.0	855.9	856.1	855.7	855.2	854.8	854.4
132.5°	888.3	889.2	890.0	890.1	889.5	888.9	888.4	887.7
135°	940.0	940.6	941.3	941.3	940.6	940.0	939.3	938.7
137.5°	986.0	987.0	988.0	988.3	987.9	987.5	987.1	986.6
140°	1015.2	1016.0	1016.9	1017.1	1016.7	1016.3	1015.9	1015.5
142.5°	1042.9	1043.6	1044.2	1044.3	1043.7	1043.1	1042.5	1042.0
145°	1081.7	1082.1	1082.5	1082.6	1082.6	1082.6	1082.6	1082.6
147.5°	1116.3	1116.7	1117.1	1116.9	1115.9	1114.9	1113.9	1113.0
150°	1137.5	1137.9	1138.3	1138.2	1137.6	1137.0	1136.4	1135.7
152.5°	1156.3	1157.2	1157.9	1157.8	1156.8	1155.8	1154.9	1153.9
155°	1182.3	1183.4	1184.5	1184.3	1183.1	1181.9	1180.6	1179.3
157.5°	1204.9	1206.2	1207.5	1207.3	1205.7	1204.0	1202.3	1200.7
160°	1217.8	1219.0	1220.3	1220.3	1218.8	1217.3	1215.8	1214.3
162.5°	1229.6	1230.9	1232.4	1232.4	1231.1	1229.8	1228.5	1227.2
165°	1245.2	1246.8	1248.5	1248.6	1247.2	1245.7	1244.2	1242.8
167.5°	1257.3	1259.0	1260.7	1260.7	1259.0	1257.3	1255.6	1253.9
170°	1264.1	1265.8	1267.5	1267.5	1265.8	1264.1	1262.4	1260.8
172.5°	1268.7	1270.3	1272.0	1271.9	1270.1	1268.3	1266.4	1264.5
175°	1274.1	1275.6	1277.1	1276.9	1275.3	1273.6	1271.9	1270.2
177.5°	1276.1	1277.5	1278.8	1278.6	1277.0	1275.3	1273.6	1271.9
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0

(END OF REPORT)