

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332354-927

Luminaire Tested: **S123RDIP-S1000D1195U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332354-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U927-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6916.8 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	90	86	89	86	83	80	72	69	67	59	57	56	47	46	45	39
2	89	82	76	71	81	75	70	66	63	60	57	52	50	47	42	40	39	34
3	82	72	66	60	75	67	61	56	56	52	48	47	43	41	37	35	33	29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	22
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	24	21	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13555	13555	13555	13555
5°	16159	13613	11988	13613
10°	20176	13535	10831	13535
15°	23682	13397	9877	13397
20°	26431	13190	9065	13190
25°	26008	12973	8568	12973
30°	18695	12771	8054	12771
35°	12482	12510	7721	12510
40°	9197	12197	7378	12197
45°	7715	11645	7042	11645
50°	6807	10923	6571	10923
55°	5970	10098	5928	10098
60°	5315	9309	5431	9309
65°	4669	8458	5053	8458
70°	3666	7704	4614	7704
75°	3227	6729	4213	6729
80°	2808	5715	4147	5715
85°	2260	4594	4397	4594



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	1.8
10°-20°	386.9	5.6
20°-30°	607.8	8.8
30°-40°	634.2	9.2
40°-50°	542.7	7.8
50°-60°	413.6	6.0
60°-70°	265.1	3.8
70°-80°	127.5	1.8
80°-90°	37.2	0.5
90°-100°	45.0	0.7
100°-110°	214.7	3.1
110°-120°	515.6	7.5
120°-130°	656.6	9.5
130°-140°	701.5	10.1
140°-150°	656.0	9.5
150°-160°	529.2	7.7
160°-170°	341.5	4.9
170°-180°	117.7	1.7
0°-30°	1118.6	16.2
0°-40°	1752.8	25.3
0°-60°	2709.1	39.2
0°-90°	3139.0	45.4
90°-120°	775.3	11.2
90°-150°	2789.4	40.3
90°-180°	3778.0	54.6
0°-180°	6916.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1259	1259	1259	1259	1259	
5°	1496	1260	1110	1260	1496	154
15°	2125	1202	886	1202	2125	603
25°	2190	1092	721	1092	2190	941
35°	950	952	588	952	950	623
45°	507	765	463	765	507	398
55°	318	538	316	538	318	288
65°	183	332	198	332	183	180
75°	78	162	101	162	78	83
85°	18	37	36	37	18	22
90°	28	1	28	1	28	13
95°	35	56	35	56	35	29
105°	40	274	40	274	40	93
115°	541	514	541	514	541	500
125°	740	725	740	725	740	661
135°	912	903	912	903	912	703
145°	1052	1042	1052	1042	1052	657
155°	1146	1148	1146	1148	1146	528
165°	1208	1210	1208	1210	1208	341
175°	1234	1239	1234	1239	1234	117
180°	1239	1239	1239	1239	1239	



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1341.3	1343.0	1337.4	1336.6	1330.1	1328.3	1328.3	1319.3	1313.7	1306.4	1302.0
5°	1495.5	1504.1	1499.8	1490.1	1473.9	1470.1	1459.9	1443.8	1425.4	1402.7	1391.9
7.5°	1688.1	1699.8	1695.3	1680.3	1663.3	1649.6	1620.8	1593.9	1556.3	1523.3	1495.1
10°	1845.9	1833.5	1823.8	1809.3	1793.6	1768.2	1738.0	1696.5	1648.6	1610.8	1568.8
12.5°	1964.1	1962.0	1949.7	1934.7	1912.6	1888.6	1851.5	1800.9	1745.2	1690.7	1642.5
15°	2125.2	2128.4	2120.3	2104.7	2073.4	2030.8	1974.8	1953.8	1873.9	1814.7	1755.3
17.5°	2236.6	2236.0	2234.9	2213.3	2181.4	2151.0	2099.0	2043.8	1971.5	1887.9	1808.1
20°	2307.4	2302.0	2303.0	2278.8	2255.1	2220.0	2169.4	2089.1	2029.7	1933.2	1850.8
22.5°	2305.6	2304.5	2308.7	2300.3	2283.1	2256.3	2216.4	2148.6	2072.8	1975.5	1882.7
25°	2189.8	2185.6	2210.9	2217.9	2245.4	2250.2	2238.4	2201.2	2129.5	2029.2	1914.4
27.5°	1832.7	1830.3	1877.4	1936.3	2010.9	2068.9	2124.9	2152.0	2129.5	2057.7	1942.6
30°	1504.1	1554.8	1578.5	1663.7	1758.6	1871.8	1970.9	2065.3	2088.5	2057.2	1962.9
32.5°	1248.8	1293.0	1312.8	1385.9	1474.3	1606.9	1755.8	1889.4	1983.7	2007.6	1950.8
35°	949.9	950.5	995.7	1028.1	1110.0	1246.4	1390.9	1569.9	1747.8	1882.5	1896.6
37.5°	758.0	760.7	788.1	820.3	881.8	953.9	1081.1	1229.9	1435.4	1642.4	1763.6
40°	654.5	659.3	679.9	711.6	755.8	810.2	909.5	1049.6	1221.1	1451.3	1639.4
42.5°	588.0	596.0	606.5	631.0	658.4	709.3	789.6	897.9	1053.8	1271.5	1488.5
45°	506.8	511.0	519.2	530.4	555.2	590.9	644.8	717.6	846.9	1022.2	1239.4
47.5°	447.0	444.7	453.3	462.5	479.0	503.2	539.3	598.7	691.0	831.6	1015.9
50°	406.5	405.9	411.9	418.9	434.5	452.3	482.0	526.7	600.0	716.4	885.2
52.5°	368.5	370.6	374.8	383.5	394.8	409.2	435.8	468.0	531.0	631.5	772.2
55°	318.1	319.7	325.6	330.5	338.6	353.1	369.8	396.8	439.9	510.0	625.9
57.5°	275.4	274.6	280.4	281.5	290.7	302.5	315.4	336.4	367.7	419.8	497.8
60°	246.9	245.3	250.2	253.9	258.8	268.5	279.2	299.8	324.6	362.8	429.7
62.5°	221.0	220.3	223.9	227.6	231.6	240.4	249.5	265.2	284.9	317.1	370.2
65°	183.3	184.9	186.6	188.1	190.3	195.7	204.3	215.1	228.5	251.2	289.5
67.5°	144.0	145.7	146.2	149.6	154.2	157.6	162.8	172.4	181.8	200.9	222.7
70°	116.5	115.9	116.5	118.0	124.0	129.9	137.0	143.9	149.9	163.3	181.6
72.5°	100.1	99.1	100.5	100.8	103.7	105.4	109.8	116.4	124.0	133.2	146.3
75°	77.6	77.6	77.6	77.6	79.8	80.9	82.5	84.1	86.8	91.1	100.8
77.5°	57.4	57.4	58.2	58.8	59.2	59.8	60.8	62.4	63.4	65.7	69.9
80°	45.3	45.8	45.3	45.8	45.8	46.9	47.5	49.0	49.6	52.3	53.9
82.5°	34.1	33.7	34.1	34.6	34.6	35.7	35.8	37.0	37.1	38.5	40.1
85°	18.3	17.3	18.3	17.8	18.9	17.8	18.3	19.4	19.4	20.0	22.1
87.5°	9.8	10.6	9.7	10.0	9.9	10.2	10.1	9.9	10.6	10.1	9.9
90°	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.7	22.9	22.1	19.4
92.5°	30.6	30.3	30.1	29.8	29.5	28.8	27.5	26.1	24.9	23.5	21.5
95°	34.9	34.9	34.9	34.9	34.9	34.2	32.8	31.4	29.9	28.5	26.3
97.5°	37.9	37.7	37.5	37.3	37.1	36.2	34.5	32.9	31.3	29.6	44.4
100°	38.7	38.4	38.3	38.0	37.9	36.9	35.3	33.7	32.0	30.3	62.3
102.5°	39.4	39.1	38.7	38.3	37.9	40.2	45.3	50.4	55.5	60.5	95.4
105°	40.5	40.1	39.7	39.3	38.9	56.7	92.9	129.1	165.3	201.5	220.0
107.5°	127.2	154.5	181.7	209.1	236.3	263.2	289.8	316.3	342.9	369.5	366.5
110°	253.1	282.3	311.6	340.9	370.1	388.1	394.8	401.6	408.4	415.1	412.8



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.2	440.4	446.6	452.7	458.9	462.0	461.8	461.7	461.6	461.4	459.2
115°	541.1	540.3	539.6	538.7	537.9	536.5	534.4	532.3	530.4	528.3	526.5
117.5°	601.2	601.0	600.9	600.7	600.6	599.6	598.0	596.4	594.7	593.1	592.2
120°	642.4	642.4	642.4	642.4	642.4	641.6	639.9	638.3	636.7	635.0	634.5
122.5°	682.9	682.8	682.5	682.4	682.2	681.6	680.5	679.3	678.2	677.0	676.2
125°	740.0	739.6	739.2	738.7	738.3	737.9	737.5	737.1	736.7	736.3	735.5
127.5°	794.8	795.3	795.7	796.1	796.5	796.3	795.7	795.0	794.4	793.7	792.7
130°	830.2	830.6	831.0	831.4	831.8	831.6	830.8	830.0	829.2	828.3	827.5
132.5°	862.5	863.2	863.7	864.3	864.8	864.7	864.0	863.1	862.3	861.5	860.8
135°	912.1	912.7	913.3	913.9	914.6	914.6	913.9	913.3	912.7	912.1	911.2
137.5°	958.6	959.1	959.5	959.9	960.3	960.0	959.0	958.1	957.0	956.1	955.6
140°	986.7	987.1	987.5	987.9	988.2	988.1	987.2	986.4	985.6	984.8	984.2
142.5°	1012.4	1013.0	1013.5	1014.2	1014.7	1014.6	1014.0	1013.4	1012.7	1012.0	1011.5
145°	1051.9	1051.9	1051.9	1051.9	1051.9	1051.8	1051.4	1051.0	1050.5	1050.1	1049.7
147.5°	1081.4	1082.4	1083.3	1084.3	1085.2	1085.4	1085.1	1084.7	1084.3	1083.8	1083.4
150°	1103.5	1104.1	1104.8	1105.3	1106.0	1106.0	1105.6	1105.3	1104.9	1104.5	1104.1
152.5°	1121.2	1122.1	1123.1	1124.0	1125.0	1125.1	1124.3	1123.6	1122.8	1122.1	1121.9
155°	1145.9	1147.1	1148.3	1149.5	1150.7	1150.9	1149.9	1148.8	1147.8	1146.8	1146.6
157.5°	1166.6	1168.2	1169.8	1171.5	1173.1	1173.2	1172.0	1170.8	1169.6	1168.3	1168.5
160°	1179.9	1181.3	1182.8	1184.2	1185.7	1185.7	1184.5	1183.3	1182.1	1180.8	1181.1
162.5°	1192.4	1193.7	1194.9	1196.2	1197.5	1197.5	1196.0	1194.7	1193.3	1191.8	1192.1
165°	1207.5	1208.9	1210.4	1211.8	1213.2	1213.1	1211.5	1209.9	1208.2	1206.6	1206.8
167.5°	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4	1218.4
170°	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0	1225.0
172.5°	1228.7	1230.5	1232.3	1234.1	1235.9	1236.0	1234.3	1232.7	1231.1	1229.4	1229.2
175°	1234.2	1235.9	1237.5	1239.1	1240.7	1240.9	1239.4	1238.0	1236.6	1235.1	1234.9
177.5°	1235.9	1237.5	1239.1	1240.8	1242.4	1242.5	1241.3	1239.9	1238.7	1237.3	1237.2
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1300.3	1299.0	1293.0	1286.1	1277.0	1271.0	1266.2	1263.7	1255.9	1246.4	1239.9
5°	1380.6	1364.5	1347.3	1326.2	1306.8	1286.8	1274.5	1259.9	1242.1	1222.2	1208.2
7.5°	1466.7	1435.0	1400.8	1365.6	1330.7	1299.5	1271.8	1248.2	1219.9	1191.3	1171.2
10°	1532.7	1486.3	1438.4	1389.3	1344.5	1302.5	1270.1	1238.3	1204.4	1171.5	1146.7
12.5°	1592.6	1531.6	1476.3	1416.0	1358.8	1308.5	1261.9	1224.6	1183.7	1148.6	1120.4
15°	1668.5	1606.0	1539.1	1447.5	1371.5	1307.9	1251.3	1202.2	1152.6	1109.5	1082.0
17.5°	1739.5	1645.4	1555.5	1479.1	1380.3	1300.8	1231.8	1173.1	1118.6	1072.9	1039.1
20°	1768.8	1677.7	1580.1	1482.6	1385.5	1296.6	1216.2	1151.5	1095.0	1043.1	1011.9
22.5°	1786.5	1683.3	1580.6	1475.7	1372.5	1280.2	1200.7	1129.6	1068.2	1019.0	980.4
25°	1807.0	1684.2	1571.0	1467.4	1362.3	1262.0	1167.7	1092.3	1026.0	973.6	932.6
27.5°	1820.7	1676.1	1542.3	1427.2	1320.6	1220.8	1134.2	1054.2	987.0	931.7	887.7
30°	1823.3	1669.6	1520.3	1395.7	1287.4	1195.7	1104.1	1027.5	956.4	897.6	856.7
32.5°	1826.7	1653.7	1490.5	1358.2	1247.3	1156.5	1073.5	1000.4	927.5	869.6	827.8
35°	1812.5	1644.8	1445.3	1293.3	1182.3	1094.4	1019.5	952.0	880.4	824.3	781.7
37.5°	1751.2	1609.8	1398.5	1220.2	1104.1	1022.7	961.6	902.9	837.1	776.7	736.5
40°	1689.6	1575.3	1362.3	1175.8	1054.5	970.9	915.9	868.0	804.4	747.7	704.6
42.5°	1597.7	1528.3	1327.9	1129.2	998.4	917.9	871.5	826.6	770.7	713.2	672.7
45°	1429.2	1438.4	1257.2	1055.0	920.8	840.0	796.2	765.0	715.4	668.0	626.5
47.5°	1217.8	1303.5	1174.3	976.0	838.9	763.0	724.8	697.6	664.2	617.6	579.7
50°	1079.8	1202.2	1107.9	923.0	787.7	712.2	674.4	652.3	623.2	586.5	550.4
52.5°	952.6	1084.0	1027.6	863.9	732.0	663.0	626.1	607.9	584.8	550.3	517.6
55°	776.8	910.0	897.1	774.7	648.6	586.5	558.5	538.1	522.4	496.5	470.6
57.5°	628.4	754.6	761.3	675.5	575.0	513.7	489.6	474.2	464.0	444.4	420.5
60°	534.8	650.7	673.4	608.6	522.4	468.5	444.7	432.4	424.3	408.6	390.3
62.5°	457.2	555.8	581.5	534.9	471.9	421.4	402.9	390.9	385.5	372.0	355.8
65°	349.9	431.8	456.6	430.7	397.8	357.4	342.3	332.1	327.3	319.7	307.8
67.5°	263.1	322.8	350.0	331.8	319.9	294.4	284.8	279.2	275.0	269.7	259.8
70°	211.4	255.6	283.6	278.7	269.0	255.6	248.5	244.8	240.4	236.1	227.5
72.5°	169.9	200.3	226.6	229.1	221.2	218.5	212.3	210.7	208.1	203.0	198.2
75°	112.6	133.7	152.0	159.1	162.2	164.9	162.2	161.8	161.2	156.9	154.2
77.5°	73.8	85.2	96.7	108.7	113.8	117.4	118.3	120.3	118.8	116.5	115.3
80°	56.6	59.3	67.4	77.6	85.7	89.0	91.1	92.2	91.7	91.1	89.0
82.5°	41.1	43.3	47.1	54.3	61.2	66.5	67.8	67.6	68.8	69.1	67.4
85°	22.1	22.7	23.7	24.8	28.6	34.5	36.1	37.2	38.3	38.3	35.0
87.5°	10.2	9.3	9.6	9.2	10.1	10.1	12.2	14.0	14.8	13.5	13.9
90°	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0	2.9	5.0	7.1
92.5°	19.6	17.6	15.5	14.8	15.4	16.0	16.6	17.1	16.6	16.0	15.4
95°	24.0	21.8	19.6	22.6	31.0	39.4	47.8	56.2	47.8	39.4	31.0
97.5°	59.1	73.8	88.6	97.8	101.6	105.3	109.1	112.8	109.1	105.3	101.6
100°	94.2	126.1	158.0	171.9	167.8	163.7	159.6	155.5	159.6	163.7	167.8
102.5°	130.2	165.1	199.9	215.9	212.9	210.0	207.1	204.1	207.1	210.0	212.9
105°	238.4	256.7	275.2	283.3	281.0	278.8	276.6	274.3	276.6	278.8	281.0
107.5°	363.6	360.8	357.8	355.5	353.6	351.9	350.1	348.2	350.1	351.9	353.6
110°	410.6	408.4	406.1	404.2	402.5	400.8	399.3	397.6	399.3	400.8	402.5



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.0	454.7	452.5	450.6	449.2	447.7	446.2	444.7	446.2	447.7	449.2
115°	524.6	522.8	520.9	519.4	518.2	516.9	515.7	514.5	515.7	516.9	518.2
117.5°	591.2	590.3	589.3	588.1	586.6	585.0	583.5	582.0	583.5	585.0	586.6
120°	633.8	633.2	632.6	631.4	629.5	627.7	625.8	624.0	625.8	627.7	629.5
122.5°	675.5	674.7	673.9	672.8	671.2	669.7	668.2	666.7	668.2	669.7	671.2
125°	734.7	733.8	733.0	731.8	730.2	728.5	726.9	725.2	726.9	728.5	730.2
127.5°	791.8	790.8	789.8	788.5	786.9	785.2	783.5	782.0	783.5	785.2	786.9
130°	826.7	825.9	825.1	823.8	822.2	820.5	819.0	817.3	819.0	820.5	822.2
132.5°	860.2	859.5	858.8	857.7	856.0	854.4	852.8	851.1	852.8	854.4	856.0
135°	910.5	909.7	908.8	907.8	906.6	905.3	904.1	902.9	904.1	905.3	906.6
137.5°	955.2	954.7	954.3	953.3	951.7	950.1	948.6	947.1	948.6	950.1	951.7
140°	983.6	982.9	982.3	981.4	980.2	979.0	977.7	976.5	977.7	979.0	980.2
142.5°	1010.8	1010.2	1009.6	1008.7	1007.4	1006.2	1005.0	1003.8	1005.0	1006.2	1007.4
145°	1049.3	1048.9	1048.5	1047.6	1046.2	1044.7	1043.3	1041.9	1043.3	1044.7	1046.2
147.5°	1083.0	1082.6	1082.2	1081.5	1080.5	1079.7	1078.7	1077.8	1078.7	1079.7	1080.5
150°	1103.6	1103.2	1102.8	1102.3	1101.7	1101.1	1100.4	1099.9	1100.4	1101.1	1101.7
152.5°	1121.7	1121.3	1121.1	1120.9	1120.5	1120.3	1120.0	1119.7	1120.0	1120.3	1120.5
155°	1146.4	1146.1	1146.0	1146.1	1146.4	1146.8	1147.3	1147.7	1147.3	1146.8	1146.4
157.5°	1168.7	1168.9	1169.1	1169.3	1169.3	1169.3	1169.3	1169.4	1169.3	1169.3	1169.3
160°	1181.2	1181.5	1181.6	1181.9	1182.1	1182.3	1182.5	1182.6	1182.5	1182.3	1182.1
162.5°	1192.3	1192.5	1192.7	1193.0	1193.6	1194.1	1194.7	1195.2	1194.7	1194.1	1193.6
165°	1207.0	1207.2	1207.4	1207.8	1208.5	1209.0	1209.7	1210.3	1209.7	1209.0	1208.5
167.5°	1218.4	1218.4	1218.4	1218.8	1219.6	1220.4	1221.2	1222.1	1221.2	1220.4	1219.6
170°	1225.0	1225.0	1225.0	1225.4	1226.2	1227.1	1227.9	1228.7	1227.9	1227.1	1226.2
172.5°	1229.1	1228.9	1228.8	1229.2	1230.2	1231.1	1232.2	1233.1	1232.2	1231.1	1230.2
175°	1234.7	1234.5	1234.3	1234.7	1235.7	1236.8	1237.8	1238.8	1237.8	1236.8	1235.7
177.5°	1237.0	1236.8	1236.7	1237.0	1237.9	1238.7	1239.4	1240.3	1239.4	1238.7	1237.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1237.8	1232.2	1228.3	1219.6	1214.1	1208.0	1202.0	1205.9	1205.5	1205.0	1205.0
5°	1196.3	1183.8	1172.6	1158.0	1148.8	1137.5	1128.9	1127.8	1130.0	1122.4	1118.1
7.5°	1155.1	1138.1	1122.1	1106.0	1089.0	1075.4	1066.9	1062.9	1057.4	1052.7	1047.9
10°	1126.2	1106.3	1090.6	1070.6	1052.3	1036.2	1026.0	1018.9	1015.1	1011.4	1004.3
12.5°	1096.5	1076.9	1057.0	1034.4	1017.0	998.2	990.5	982.7	975.5	971.2	961.6
15°	1052.9	1027.5	1006.5	982.8	963.4	945.1	934.3	918.6	916.5	911.1	901.4
17.5°	1009.2	981.7	952.7	935.2	913.2	894.1	877.7	872.5	857.1	851.3	842.8
20°	974.7	949.4	927.2	904.1	872.3	854.4	841.5	834.6	822.1	814.6	809.2
22.5°	944.9	919.2	893.7	866.6	840.3	820.4	811.0	800.0	793.2	782.7	776.8
25°	902.5	874.4	843.7	814.6	795.7	780.6	765.6	755.8	746.2	741.2	730.5
27.5°	853.1	823.8	795.0	772.9	749.8	734.9	721.2	712.6	700.9	692.8	686.8
30°	825.9	791.4	766.6	746.6	717.0	703.0	692.8	682.0	673.4	664.7	658.8
32.5°	794.4	763.0	739.4	714.8	692.0	676.7	663.5	653.9	646.6	638.4	632.5
35°	745.0	718.7	694.3	669.6	652.8	637.2	621.6	613.5	606.5	599.0	593.6
37.5°	700.4	675.7	652.7	629.2	608.4	595.7	583.1	576.9	567.4	562.4	556.9
40°	672.8	648.6	623.8	601.1	579.6	569.8	558.5	549.4	540.7	536.9	531.0
42.5°	642.6	618.4	597.5	573.1	555.4	542.2	531.8	521.7	515.3	509.8	506.4
45°	597.9	576.3	555.8	531.6	514.8	503.5	491.6	482.5	476.6	472.8	466.8
47.5°	554.4	532.8	512.1	490.9	474.8	461.8	450.0	443.5	435.7	431.1	427.1
50°	522.9	503.5	481.4	462.0	445.8	432.9	423.2	415.1	408.1	402.2	399.5
52.5°	494.0	473.3	454.2	436.2	419.1	404.4	395.6	387.1	381.8	375.0	371.9
55°	446.4	426.4	410.3	392.4	375.7	363.4	352.6	345.0	339.6	332.1	327.8
57.5°	401.6	383.7	364.4	349.0	331.8	321.3	312.4	302.1	295.6	289.6	285.4
60°	371.5	350.9	334.2	319.7	304.6	291.1	283.0	275.0	267.9	262.0	258.3
62.5°	339.9	322.1	306.2	290.3	276.6	264.8	255.4	248.7	242.5	238.7	235.0
65°	291.7	277.7	261.5	248.5	235.6	227.0	219.4	213.5	209.1	206.4	203.3
67.5°	247.2	233.6	219.5	206.8	198.2	191.6	186.6	181.6	179.4	175.9	173.8
70°	218.3	204.3	191.9	182.2	173.6	168.7	165.5	161.8	159.5	155.3	153.1
72.5°	186.9	176.7	167.8	159.8	152.9	148.5	144.3	139.7	136.3	131.5	129.4
75°	147.2	138.0	131.0	125.6	121.3	115.3	109.4	104.6	103.0	101.3	100.8
77.5°	109.0	103.2	98.2	93.6	88.2	83.9	82.6	81.5	81.2	80.3	80.3
80°	85.7	80.3	76.5	71.1	67.9	67.9	67.9	66.9	67.4	67.4	67.4
82.5°	63.7	58.8	56.7	54.7	54.1	54.6	54.6	54.7	54.4	55.3	54.9
85°	32.9	33.4	34.5	34.0	34.5	34.5	35.6	35.0	35.6	34.5	35.6
87.5°	13.9	15.7	16.6	17.6	18.5	18.6	19.3	19.4	20.0	20.2	20.3
90°	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.7	24.6	25.3	26.0
92.5°	14.8	15.5	17.6	19.6	21.5	23.5	24.9	26.1	27.5	28.8	29.5
95°	22.6	19.6	21.8	24.0	26.3	28.5	29.9	31.4	32.8	34.2	34.9
97.5°	97.8	88.6	73.8	59.1	44.4	29.6	31.3	32.9	34.5	36.2	37.1
100°	171.9	158.0	126.1	94.2	62.3	30.3	32.0	33.7	35.3	36.9	37.9
102.5°	215.9	199.9	165.1	130.2	95.4	60.5	55.5	50.4	45.3	40.2	37.9
105°	283.3	275.2	256.7	238.4	220.0	201.5	165.3	129.1	92.9	56.7	38.9
107.5°	355.5	357.8	360.8	363.6	366.5	369.5	342.9	316.3	289.8	263.2	236.3
110°	404.2	406.1	408.4	410.6	412.8	415.1	408.4	401.6	394.8	388.1	370.1



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	450.6	452.5	454.7	457.0	459.2	461.4	461.6	461.7	461.8	462.0	458.9
115°	519.4	520.9	522.8	524.6	526.5	528.3	530.4	532.3	534.4	536.5	537.9
117.5°	588.1	589.3	590.3	591.2	592.2	593.1	594.7	596.4	598.0	599.6	600.6
120°	631.4	632.6	633.2	633.8	634.5	635.0	636.7	638.3	639.9	641.6	642.4
122.5°	672.8	673.9	674.7	675.5	676.2	677.0	678.2	679.3	680.5	681.6	682.2
125°	731.8	733.0	733.8	734.7	735.5	736.3	736.7	737.1	737.5	737.9	738.3
127.5°	788.5	789.8	790.8	791.8	792.7	793.7	794.4	795.0	795.7	796.3	796.5
130°	823.8	825.1	825.9	826.7	827.5	828.3	829.2	830.0	830.8	831.6	831.8
132.5°	857.7	858.8	859.5	860.2	860.8	861.5	862.3	863.1	864.0	864.7	864.8
135°	907.8	908.8	909.7	910.5	911.2	912.1	912.7	913.3	913.9	914.6	914.6
137.5°	953.3	954.3	954.7	955.2	955.6	956.1	957.0	958.1	959.0	960.0	960.3
140°	981.4	982.3	982.9	983.6	984.2	984.8	985.6	986.4	987.2	988.1	988.2
142.5°	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7	1013.4	1014.0	1014.6	1014.7
145°	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5	1051.0	1051.4	1051.8	1051.9
147.5°	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3	1084.7	1085.1	1085.4	1085.2
150°	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9	1105.3	1105.6	1106.0	1106.0
152.5°	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8	1123.6	1124.3	1125.1	1125.0
155°	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8	1148.8	1149.9	1150.9	1150.7
157.5°	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6	1170.8	1172.0	1173.2	1173.1
160°	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1	1183.3	1184.5	1185.7	1185.7
162.5°	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3	1194.7	1196.0	1197.5	1197.5
165°	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2	1209.9	1211.5	1213.1	1213.2
167.5°	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0
170°	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5
172.5°	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1	1232.7	1234.3	1236.0	1235.9
175°	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6	1238.0	1239.4	1240.9	1240.7
177.5°	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7	1239.9	1241.3	1242.5	1242.4
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1199.8	1199.4	1199.8	1198.1	1199.8	1199.4	1199.8	1205.0	1205.0	1205.5	1205.9
5°	1116.5	1115.9	1114.4	1109.5	1114.4	1115.9	1116.5	1118.1	1122.4	1130.0	1127.8
7.5°	1043.7	1043.0	1038.2	1038.3	1038.2	1043.0	1043.7	1047.9	1052.7	1057.4	1062.9
10°	1000.6	1001.1	994.7	990.9	994.7	1001.1	1000.6	1004.3	1011.4	1015.1	1018.9
12.5°	958.8	956.2	951.1	946.9	951.1	956.2	958.8	961.6	971.2	975.5	982.7
15°	903.6	898.2	885.2	886.3	885.2	898.2	903.6	901.4	911.1	916.5	918.6
17.5°	838.5	834.6	834.3	826.8	834.3	834.6	838.5	842.8	851.3	857.1	872.5
20°	800.6	797.9	798.9	791.4	798.9	797.9	800.6	809.2	814.6	822.1	834.6
22.5°	770.8	768.1	763.6	761.2	763.6	768.1	770.8	776.8	782.7	793.2	800.0
25°	727.2	722.9	718.7	721.4	718.7	722.9	727.2	730.5	741.2	746.2	755.8
27.5°	683.7	680.5	676.1	675.6	676.1	680.5	683.7	686.8	692.8	700.9	712.6
30°	656.1	652.8	650.7	648.0	650.7	652.8	656.1	658.8	664.7	673.4	682.0
32.5°	628.0	627.4	623.5	623.0	623.5	627.4	628.0	632.5	638.4	646.6	653.9
35°	591.4	588.2	587.1	587.6	587.1	588.2	591.4	593.6	599.0	606.5	613.5
37.5°	556.6	552.2	550.3	548.3	550.3	552.2	556.6	556.9	562.4	567.4	576.9
40°	531.6	527.3	526.2	525.1	526.2	527.3	531.6	531.0	536.9	540.7	549.4
42.5°	503.5	501.8	501.1	499.2	501.1	501.8	503.5	506.4	509.8	515.3	521.7
45°	465.2	464.7	461.4	462.6	461.4	464.7	465.2	466.8	472.8	476.6	482.5
47.5°	424.9	422.6	420.3	421.8	420.3	422.6	424.9	427.1	431.1	435.7	443.5
50°	397.4	396.2	391.4	392.4	391.4	396.2	397.4	399.5	402.2	408.1	415.1
52.5°	369.7	365.6	363.8	363.1	363.8	365.6	369.7	371.9	375.0	381.8	387.1
55°	324.0	319.2	317.0	315.9	317.0	319.2	324.0	327.8	332.1	339.6	345.0
57.5°	279.2	277.8	276.2	277.3	276.2	277.8	279.2	285.4	289.6	295.6	302.1
60°	252.9	252.9	252.9	252.3	252.9	252.9	252.9	258.3	262.0	267.9	275.0
62.5°	232.6	231.2	230.8	231.6	230.8	231.2	232.6	235.0	238.7	242.5	248.7
65°	201.6	201.1	198.9	198.4	198.9	201.1	201.6	203.3	206.4	209.1	213.5
67.5°	172.4	170.5	169.8	169.1	169.8	170.5	172.4	173.8	175.9	179.4	181.6
70°	150.4	149.3	146.1	146.6	146.1	149.3	150.4	153.1	155.3	159.5	161.8
72.5°	126.7	125.6	124.9	124.2	124.9	125.6	126.7	129.4	131.5	136.3	139.7
75°	100.3	99.7	99.2	101.3	99.2	99.7	100.3	100.8	101.3	103.0	104.6
77.5°	80.3	80.3	80.6	79.8	80.6	80.3	80.3	80.3	80.3	81.2	81.5
80°	67.4	67.4	66.9	66.9	66.9	67.4	67.4	67.4	67.4	67.4	66.9
82.5°	54.0	54.4	54.7	53.9	54.7	54.4	54.0	54.9	55.3	54.4	54.7
85°	35.6	35.0	36.1	35.6	36.1	35.0	35.6	35.6	34.5	35.6	35.0
87.5°	21.2	20.4	20.5	21.1	20.5	20.4	21.2	20.3	20.2	20.0	19.4
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.7
92.5°	29.8	30.1	30.3	30.6	30.3	30.1	29.8	29.5	28.8	27.5	26.1
95°	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.2	32.8	31.4
97.5°	37.3	37.5	37.7	37.9	37.7	37.5	37.3	37.1	36.2	34.5	32.9
100°	38.0	38.3	38.4	38.7	38.4	38.3	38.0	37.9	36.9	35.3	33.7
102.5°	38.3	38.7	39.1	39.4	39.1	38.7	38.3	37.9	40.2	45.3	50.4
105°	39.3	39.7	40.1	40.5	40.1	39.7	39.3	38.9	56.7	92.9	129.1
107.5°	209.1	181.7	154.5	127.2	154.5	181.7	209.1	236.3	263.2	289.8	316.3
110°	340.9	311.6	282.3	253.1	282.3	311.6	340.9	370.1	388.1	394.8	401.6



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	452.7	446.6	440.4	434.2	440.4	446.6	452.7	458.9	462.0	461.8	461.7
115°	538.7	539.6	540.3	541.1	540.3	539.6	538.7	537.9	536.5	534.4	532.3
117.5°	600.7	600.9	601.0	601.2	601.0	600.9	600.7	600.6	599.6	598.0	596.4
120°	642.4	642.4	642.4	642.4	642.4	642.4	642.4	642.4	641.6	639.9	638.3
122.5°	682.4	682.5	682.8	682.9	682.8	682.5	682.4	682.2	681.6	680.5	679.3
125°	738.7	739.2	739.6	740.0	739.6	739.2	738.7	738.3	737.9	737.5	737.1
127.5°	796.1	795.7	795.3	794.8	795.3	795.7	796.1	796.5	796.3	795.7	795.0
130°	831.4	831.0	830.6	830.2	830.6	831.0	831.4	831.8	831.6	830.8	830.0
132.5°	864.3	863.7	863.2	862.5	863.2	863.7	864.3	864.8	864.7	864.0	863.1
135°	913.9	913.3	912.7	912.1	912.7	913.3	913.9	914.6	914.6	913.9	913.3
137.5°	959.9	959.5	959.1	958.6	959.1	959.5	959.9	960.3	960.0	959.0	958.1
140°	987.9	987.5	987.1	986.7	987.1	987.5	987.9	988.2	988.1	987.2	986.4
142.5°	1014.2	1013.5	1013.0	1012.4	1013.0	1013.5	1014.2	1014.7	1014.6	1014.0	1013.4
145°	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.8	1051.4	1051.0
147.5°	1084.3	1083.3	1082.4	1081.4	1082.4	1083.3	1084.3	1085.2	1085.4	1085.1	1084.7
150°	1105.3	1104.8	1104.1	1103.5	1104.1	1104.8	1105.3	1106.0	1106.0	1105.6	1105.3
152.5°	1124.0	1123.1	1122.1	1121.2	1122.1	1123.1	1124.0	1125.0	1125.1	1124.3	1123.6
155°	1149.5	1148.3	1147.1	1145.9	1147.1	1148.3	1149.5	1150.7	1150.9	1149.9	1148.8
157.5°	1171.5	1169.8	1168.2	1166.6	1168.2	1169.8	1171.5	1173.1	1173.2	1172.0	1170.8
160°	1184.2	1182.8	1181.3	1179.9	1181.3	1182.8	1184.2	1185.7	1185.7	1184.5	1183.3
162.5°	1196.2	1194.9	1193.7	1192.4	1193.7	1194.9	1196.2	1197.5	1197.5	1196.0	1194.7
165°	1211.8	1210.4	1208.9	1207.5	1208.9	1210.4	1211.8	1213.2	1213.1	1211.5	1209.9
167.5°	1223.3	1221.6	1220.0	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6
170°	1229.9	1228.3	1226.6	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3
172.5°	1234.1	1232.3	1230.5	1228.7	1230.5	1232.3	1234.1	1235.9	1236.0	1234.3	1232.7
175°	1239.1	1237.5	1235.9	1234.2	1235.9	1237.5	1239.1	1240.7	1240.9	1239.4	1238.0
177.5°	1240.8	1239.1	1237.5	1235.9	1237.5	1239.1	1240.8	1242.4	1242.5	1241.3	1239.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1202.0	1208.0	1214.1	1219.6	1228.3	1232.2	1237.8	1239.9	1246.4	1255.9	1263.7
5°	1128.9	1137.5	1148.8	1158.0	1172.6	1183.8	1196.3	1208.2	1222.2	1242.1	1259.9
7.5°	1066.9	1075.4	1089.0	1106.0	1122.1	1138.1	1155.1	1171.2	1191.3	1219.9	1248.2
10°	1026.0	1036.2	1052.3	1070.6	1090.6	1106.3	1126.2	1146.7	1171.5	1204.4	1238.3
12.5°	990.5	998.2	1017.0	1034.4	1057.0	1076.9	1096.5	1120.4	1148.6	1183.7	1224.6
15°	934.3	945.1	963.4	982.8	1006.5	1027.5	1052.9	1082.0	1109.5	1152.6	1202.2
17.5°	877.7	894.1	913.2	935.2	952.7	981.7	1009.2	1039.1	1072.9	1118.6	1173.1
20°	841.5	854.4	872.3	904.1	927.2	949.4	974.7	1011.9	1043.1	1095.0	1151.5
22.5°	811.0	820.4	840.3	866.6	893.7	919.2	944.9	980.4	1019.0	1068.2	1129.6
25°	765.6	780.6	795.7	814.6	843.7	874.4	902.5	932.6	973.6	1026.0	1092.3
27.5°	721.2	734.9	749.8	772.9	795.0	823.8	853.1	887.7	931.7	987.0	1054.2
30°	692.8	703.0	717.0	746.6	766.6	791.4	825.9	856.7	897.6	956.4	1027.5
32.5°	663.5	676.7	692.0	714.8	739.4	763.0	794.4	827.8	869.6	927.5	1000.4
35°	621.6	637.2	652.8	669.6	694.3	718.7	745.0	781.7	824.3	880.4	952.0
37.5°	583.1	595.7	608.4	629.2	652.7	675.7	700.4	736.5	776.7	837.1	902.9
40°	558.5	569.8	579.6	601.1	623.8	648.6	672.8	704.6	747.7	804.4	868.0
42.5°	531.8	542.2	555.4	573.1	597.5	618.4	642.6	672.7	713.2	770.7	826.6
45°	491.6	503.5	514.8	531.6	555.8	576.3	597.9	626.5	668.0	715.4	765.0
47.5°	450.0	461.8	474.8	490.9	512.1	532.8	554.4	579.7	617.6	664.2	697.6
50°	423.2	432.9	445.8	462.0	481.4	503.5	522.9	550.4	586.5	623.2	652.3
52.5°	395.6	404.4	419.1	436.2	454.2	473.3	494.0	517.6	550.3	584.8	607.9
55°	352.6	363.4	375.7	392.4	410.3	426.4	446.4	470.6	496.5	522.4	538.1
57.5°	312.4	321.3	331.8	349.0	364.4	383.7	401.6	420.5	444.4	464.0	474.2
60°	283.0	291.1	304.6	319.7	334.2	350.9	371.5	390.3	408.6	424.3	432.4
62.5°	255.4	264.8	276.6	290.3	306.2	322.1	339.9	355.8	372.0	385.5	390.9
65°	219.4	227.0	235.6	248.5	261.5	277.7	291.7	307.8	319.7	327.3	332.1
67.5°	186.6	191.6	198.2	206.8	219.5	233.6	247.2	259.8	269.7	275.0	279.2
70°	165.5	168.7	173.6	182.2	191.9	204.3	218.3	227.5	236.1	240.4	244.8
72.5°	144.3	148.5	152.9	159.8	167.8	176.7	186.9	198.2	203.0	208.1	210.7
75°	109.4	115.3	121.3	125.6	131.0	138.0	147.2	154.2	156.9	161.2	161.8
77.5°	82.6	83.9	88.2	93.6	98.2	103.2	109.0	115.3	116.5	118.8	120.3
80°	67.9	67.9	67.9	71.1	76.5	80.3	85.7	89.0	91.1	91.7	92.2
82.5°	54.6	54.6	54.1	54.7	56.7	58.8	63.7	67.4	69.1	68.8	67.6
85°	35.6	34.5	34.5	34.0	34.5	33.4	32.9	35.0	38.3	38.3	37.2
87.5°	19.3	18.6	18.5	17.6	16.6	15.7	13.9	13.9	13.5	14.8	14.0
90°	22.9	22.1	19.4	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0
92.5°	24.9	23.5	21.5	19.6	17.6	15.5	14.8	15.4	16.0	16.6	17.1
95°	29.9	28.5	26.3	24.0	21.8	19.6	22.6	31.0	39.4	47.8	56.2
97.5°	31.3	29.6	44.4	59.1	73.8	88.6	97.8	101.6	105.3	109.1	112.8
100°	32.0	30.3	62.3	94.2	126.1	158.0	171.9	167.8	163.7	159.6	155.5
102.5°	55.5	60.5	95.4	130.2	165.1	199.9	215.9	212.9	210.0	207.1	204.1
105°	165.3	201.5	220.0	238.4	256.7	275.2	283.3	281.0	278.8	276.6	274.3
107.5°	342.9	369.5	366.5	363.6	360.8	357.8	355.5	353.6	351.9	350.1	348.2
110°	408.4	415.1	412.8	410.6	408.4	406.1	404.2	402.5	400.8	399.3	397.6



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	461.6	461.4	459.2	457.0	454.7	452.5	450.6	449.2	447.7	446.2	444.7
115°	530.4	528.3	526.5	524.6	522.8	520.9	519.4	518.2	516.9	515.7	514.5
117.5°	594.7	593.1	592.2	591.2	590.3	589.3	588.1	586.6	585.0	583.5	582.0
120°	636.7	635.0	634.5	633.8	633.2	632.6	631.4	629.5	627.7	625.8	624.0
122.5°	678.2	677.0	676.2	675.5	674.7	673.9	672.8	671.2	669.7	668.2	666.7
125°	736.7	736.3	735.5	734.7	733.8	733.0	731.8	730.2	728.5	726.9	725.2
127.5°	794.4	793.7	792.7	791.8	790.8	789.8	788.5	786.9	785.2	783.5	782.0
130°	829.2	828.3	827.5	826.7	825.9	825.1	823.8	822.2	820.5	819.0	817.3
132.5°	862.3	861.5	860.8	860.2	859.5	858.8	857.7	856.0	854.4	852.8	851.1
135°	912.7	912.1	911.2	910.5	909.7	908.8	907.8	906.6	905.3	904.1	902.9
137.5°	957.0	956.1	955.6	955.2	954.7	954.3	953.3	951.7	950.1	948.6	947.1
140°	985.6	984.8	984.2	983.6	982.9	982.3	981.4	980.2	979.0	977.7	976.5
142.5°	1012.7	1012.0	1011.5	1010.8	1010.2	1009.6	1008.7	1007.4	1006.2	1005.0	1003.8
145°	1050.5	1050.1	1049.7	1049.3	1048.9	1048.5	1047.6	1046.2	1044.7	1043.3	1041.9
147.5°	1084.3	1083.8	1083.4	1083.0	1082.6	1082.2	1081.5	1080.5	1079.7	1078.7	1077.8
150°	1104.9	1104.5	1104.1	1103.6	1103.2	1102.8	1102.3	1101.7	1101.1	1100.4	1099.9
152.5°	1122.8	1122.1	1121.9	1121.7	1121.3	1121.1	1120.9	1120.5	1120.3	1120.0	1119.7
155°	1147.8	1146.8	1146.6	1146.4	1146.1	1146.0	1146.1	1146.4	1146.8	1147.3	1147.7
157.5°	1169.6	1168.3	1168.5	1168.7	1168.9	1169.1	1169.3	1169.3	1169.3	1169.3	1169.4
160°	1182.1	1180.8	1181.1	1181.2	1181.5	1181.6	1181.9	1182.1	1182.3	1182.5	1182.6
162.5°	1193.3	1191.8	1192.1	1192.3	1192.5	1192.7	1193.0	1193.6	1194.1	1194.7	1195.2
165°	1208.2	1206.6	1206.8	1207.0	1207.2	1207.4	1207.8	1208.5	1209.0	1209.7	1210.3
167.5°	1220.0	1218.4	1218.4	1218.4	1218.4	1218.4	1218.8	1219.6	1220.4	1221.2	1222.1
170°	1226.6	1225.0	1225.0	1225.0	1225.0	1225.0	1225.4	1226.2	1227.1	1227.9	1228.7
172.5°	1231.1	1229.4	1229.2	1229.1	1228.9	1228.8	1229.2	1230.2	1231.1	1232.2	1233.1
175°	1236.6	1235.1	1234.9	1234.7	1234.5	1234.3	1234.7	1235.7	1236.8	1237.8	1238.8
177.5°	1238.7	1237.3	1237.2	1237.0	1236.8	1236.7	1237.0	1237.9	1238.7	1239.4	1240.3
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1266.2	1271.0	1277.0	1286.1	1293.0	1299.0	1300.3	1302.0	1306.4	1313.7	1319.3
5°	1274.5	1286.8	1306.8	1326.2	1347.3	1364.5	1380.6	1391.9	1402.7	1425.4	1443.8
7.5°	1271.8	1299.5	1330.7	1365.6	1400.8	1435.0	1466.7	1495.1	1523.3	1556.3	1593.9
10°	1270.1	1302.5	1344.5	1389.3	1438.4	1486.3	1532.7	1568.8	1610.8	1648.6	1696.5
12.5°	1261.9	1308.5	1358.8	1416.0	1476.3	1531.6	1592.6	1642.5	1690.7	1745.2	1800.9
15°	1251.3	1307.9	1371.5	1447.5	1539.1	1606.0	1668.5	1755.3	1814.7	1873.9	1953.8
17.5°	1231.8	1300.8	1380.3	1479.1	1555.5	1645.4	1739.5	1808.1	1887.9	1971.5	2043.8
20°	1216.2	1296.6	1385.5	1482.6	1580.1	1677.7	1768.8	1850.8	1933.2	2029.7	2089.1
22.5°	1200.7	1280.2	1372.5	1475.7	1580.6	1683.3	1786.5	1882.7	1975.5	2072.8	2148.6
25°	1167.7	1262.0	1362.3	1467.4	1571.0	1684.2	1807.0	1914.4	2029.2	2129.5	2201.2
27.5°	1134.2	1220.8	1320.6	1427.2	1542.3	1676.1	1820.7	1942.6	2057.7	2129.5	2152.0
30°	1104.1	1195.7	1287.4	1395.7	1520.3	1669.6	1823.3	1962.9	2057.2	2088.5	2065.3
32.5°	1073.5	1156.5	1247.3	1358.2	1490.5	1653.7	1826.7	1950.8	2007.6	1983.7	1889.4
35°	1019.5	1094.4	1182.3	1293.3	1445.3	1644.8	1812.5	1896.6	1882.5	1747.8	1569.9
37.5°	961.6	1022.7	1104.1	1220.2	1398.5	1609.8	1751.2	1763.6	1642.4	1435.4	1229.9
40°	915.9	970.9	1054.5	1175.8	1362.3	1575.3	1689.6	1639.4	1451.3	1221.1	1049.6
42.5°	871.5	917.9	998.4	1129.2	1327.9	1528.3	1597.7	1488.5	1271.5	1053.8	897.9
45°	796.2	840.0	920.8	1055.0	1257.2	1438.4	1429.2	1239.4	1022.2	846.9	717.6
47.5°	724.8	763.0	838.9	976.0	1174.3	1303.5	1217.8	1015.9	831.6	691.0	598.7
50°	674.4	712.2	787.7	923.0	1107.9	1202.2	1079.8	885.2	716.4	600.0	526.7
52.5°	626.1	663.0	732.0	863.9	1027.6	1084.0	952.6	772.2	631.5	531.0	468.0
55°	558.5	586.5	648.6	774.7	897.1	910.0	776.8	625.9	510.0	439.9	396.8
57.5°	489.6	513.7	575.0	675.5	761.3	754.6	628.4	497.8	419.8	367.7	336.4
60°	444.7	468.5	522.4	608.6	673.4	650.7	534.8	429.7	362.8	324.6	299.8
62.5°	402.9	421.4	471.9	534.9	581.5	555.8	457.2	370.2	317.1	284.9	265.2
65°	342.3	357.4	397.8	430.7	456.6	431.8	349.9	289.5	251.2	228.5	215.1
67.5°	284.8	294.4	319.9	331.8	350.0	322.8	263.1	222.7	200.9	181.8	172.4
70°	248.5	255.6	269.0	278.7	283.6	255.6	211.4	181.6	163.3	149.9	143.9
72.5°	212.3	218.5	221.2	229.1	226.6	200.3	169.9	146.3	133.2	124.0	116.4
75°	162.2	164.9	162.2	159.1	152.0	133.7	112.6	100.8	91.1	86.8	84.1
77.5°	118.3	117.4	113.8	108.7	96.7	85.2	73.8	69.9	65.7	63.4	62.4
80°	91.1	89.0	85.7	77.6	67.4	59.3	56.6	53.9	52.3	49.6	49.0
82.5°	67.8	66.5	61.2	54.3	47.1	43.3	41.1	40.1	38.5	37.1	37.0
85°	36.1	34.5	28.6	24.8	23.7	22.7	22.1	22.1	20.0	19.4	19.4
87.5°	12.2	10.1	10.1	9.2	9.6	9.3	10.2	9.9	10.1	10.6	9.9
90°	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.7
92.5°	16.6	16.0	15.4	14.8	15.5	17.6	19.6	21.5	23.5	24.9	26.1
95°	47.8	39.4	31.0	22.6	19.6	21.8	24.0	26.3	28.5	29.9	31.4
97.5°	109.1	105.3	101.6	97.8	88.6	73.8	59.1	44.4	29.6	31.3	32.9
100°	159.6	163.7	167.8	171.9	158.0	126.1	94.2	62.3	30.3	32.0	33.7
102.5°	207.1	210.0	212.9	215.9	199.9	165.1	130.2	95.4	60.5	55.5	50.4
105°	276.6	278.8	281.0	283.3	275.2	256.7	238.4	220.0	201.5	165.3	129.1
107.5°	350.1	351.9	353.6	355.5	357.8	360.8	363.6	366.5	369.5	342.9	316.3
110°	399.3	400.8	402.5	404.2	406.1	408.4	410.6	412.8	415.1	408.4	401.6



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	446.2	447.7	449.2	450.6	452.5	454.7	457.0	459.2	461.4	461.6	461.7
115°	515.7	516.9	518.2	519.4	520.9	522.8	524.6	526.5	528.3	530.4	532.3
117.5°	583.5	585.0	586.6	588.1	589.3	590.3	591.2	592.2	593.1	594.7	596.4
120°	625.8	627.7	629.5	631.4	632.6	633.2	633.8	634.5	635.0	636.7	638.3
122.5°	668.2	669.7	671.2	672.8	673.9	674.7	675.5	676.2	677.0	678.2	679.3
125°	726.9	728.5	730.2	731.8	733.0	733.8	734.7	735.5	736.3	736.7	737.1
127.5°	783.5	785.2	786.9	788.5	789.8	790.8	791.8	792.7	793.7	794.4	795.0
130°	819.0	820.5	822.2	823.8	825.1	825.9	826.7	827.5	828.3	829.2	830.0
132.5°	852.8	854.4	856.0	857.7	858.8	859.5	860.2	860.8	861.5	862.3	863.1
135°	904.1	905.3	906.6	907.8	908.8	909.7	910.5	911.2	912.1	912.7	913.3
137.5°	948.6	950.1	951.7	953.3	954.3	954.7	955.2	955.6	956.1	957.0	958.1
140°	977.7	979.0	980.2	981.4	982.3	982.9	983.6	984.2	984.8	985.6	986.4
142.5°	1005.0	1006.2	1007.4	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7	1013.4
145°	1043.3	1044.7	1046.2	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5	1051.0
147.5°	1078.7	1079.7	1080.5	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3	1084.7
150°	1100.4	1101.1	1101.7	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9	1105.3
152.5°	1120.0	1120.3	1120.5	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8	1123.6
155°	1147.3	1146.8	1146.4	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8	1148.8
157.5°	1169.3	1169.3	1169.3	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6	1170.8
160°	1182.5	1182.3	1182.1	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1	1183.3
162.5°	1194.7	1194.1	1193.6	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3	1194.7
165°	1209.7	1209.0	1208.5	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2	1209.9
167.5°	1221.2	1220.4	1219.6	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0	1221.6
170°	1227.9	1227.1	1226.2	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6	1228.3
172.5°	1232.2	1231.1	1230.2	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1	1232.7
175°	1237.8	1236.8	1235.7	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6	1238.0
177.5°	1239.4	1238.7	1237.9	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7	1239.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1328.3	1328.3	1330.1	1336.6	1337.4	1343.0	1341.3
5°	1459.9	1470.1	1473.9	1490.1	1499.8	1504.1	1495.5
7.5°	1620.8	1649.6	1663.3	1680.3	1695.3	1699.8	1688.1
10°	1738.0	1768.2	1793.6	1809.3	1823.8	1833.5	1845.9
12.5°	1851.5	1888.6	1912.6	1934.7	1949.7	1962.0	1964.1
15°	1974.8	2030.8	2073.4	2104.7	2120.3	2128.4	2125.2
17.5°	2099.0	2151.0	2181.4	2213.3	2234.9	2236.0	2236.6
20°	2169.4	2220.0	2255.1	2278.8	2303.0	2302.0	2307.4
22.5°	2216.4	2256.3	2283.1	2300.3	2308.7	2304.5	2305.6
25°	2238.4	2250.2	2245.4	2217.9	2210.9	2185.6	2189.8
27.5°	2124.9	2068.9	2010.9	1936.3	1877.4	1830.3	1832.7
30°	1970.9	1871.8	1758.6	1663.7	1578.5	1554.8	1504.1
32.5°	1755.8	1606.9	1474.3	1385.9	1312.8	1293.0	1248.8
35°	1390.9	1246.4	1110.0	1028.1	995.7	950.5	949.9
37.5°	1081.1	953.9	881.8	820.3	788.1	760.7	758.0
40°	909.5	810.2	755.8	711.6	679.9	659.3	654.5
42.5°	789.6	709.3	658.4	631.0	606.5	596.0	588.0
45°	644.8	590.9	555.2	530.4	519.2	511.0	506.8
47.5°	539.3	503.2	479.0	462.5	453.3	444.7	447.0
50°	482.0	452.3	434.5	418.9	411.9	405.9	406.5
52.5°	435.8	409.2	394.8	383.5	374.8	370.6	368.5
55°	369.8	353.1	338.6	330.5	325.6	319.7	318.1
57.5°	315.4	302.5	290.7	281.5	280.4	274.6	275.4
60°	279.2	268.5	258.8	253.9	250.2	245.3	246.9
62.5°	249.5	240.4	231.6	227.6	223.9	220.3	221.0
65°	204.3	195.7	190.3	188.1	186.6	184.9	183.3
67.5°	162.8	157.6	154.2	149.6	146.2	145.7	144.0
70°	137.0	129.9	124.0	118.0	116.5	115.9	116.5
72.5°	109.8	105.4	103.7	100.8	100.5	99.1	100.1
75°	82.5	80.9	79.8	77.6	77.6	77.6	77.6
77.5°	60.8	59.8	59.2	58.8	58.2	57.4	57.4
80°	47.5	46.9	45.8	45.8	45.3	45.8	45.3
82.5°	35.8	35.7	34.6	34.6	34.1	33.7	34.1
85°	18.3	17.8	18.9	17.8	18.3	17.3	18.3
87.5°	10.1	10.2	9.9	10.0	9.7	10.6	9.8
90°	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	27.5	28.8	29.5	29.8	30.1	30.3	30.6
95°	32.8	34.2	34.9	34.9	34.9	34.9	34.9
97.5°	34.5	36.2	37.1	37.3	37.5	37.7	37.9
100°	35.3	36.9	37.9	38.0	38.3	38.4	38.7
102.5°	45.3	40.2	37.9	38.3	38.7	39.1	39.4
105°	92.9	56.7	38.9	39.3	39.7	40.1	40.5
107.5°	289.8	263.2	236.3	209.1	181.7	154.5	127.2
110°	394.8	388.1	370.1	340.9	311.6	282.3	253.1



TEST NUMBER: P332354-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	461.8	462.0	458.9	452.7	446.6	440.4	434.2
115°	534.4	536.5	537.9	538.7	539.6	540.3	541.1
117.5°	598.0	599.6	600.6	600.7	600.9	601.0	601.2
120°	639.9	641.6	642.4	642.4	642.4	642.4	642.4
122.5°	680.5	681.6	682.2	682.4	682.5	682.8	682.9
125°	737.5	737.9	738.3	738.7	739.2	739.6	740.0
127.5°	795.7	796.3	796.5	796.1	795.7	795.3	794.8
130°	830.8	831.6	831.8	831.4	831.0	830.6	830.2
132.5°	864.0	864.7	864.8	864.3	863.7	863.2	862.5
135°	913.9	914.6	914.6	913.9	913.3	912.7	912.1
137.5°	959.0	960.0	960.3	959.9	959.5	959.1	958.6
140°	987.2	988.1	988.2	987.9	987.5	987.1	986.7
142.5°	1014.0	1014.6	1014.7	1014.2	1013.5	1013.0	1012.4
145°	1051.4	1051.8	1051.9	1051.9	1051.9	1051.9	1051.9
147.5°	1085.1	1085.4	1085.2	1084.3	1083.3	1082.4	1081.4
150°	1105.6	1106.0	1106.0	1105.3	1104.8	1104.1	1103.5
152.5°	1124.3	1125.1	1125.0	1124.0	1123.1	1122.1	1121.2
155°	1149.9	1150.9	1150.7	1149.5	1148.3	1147.1	1145.9
157.5°	1172.0	1173.2	1173.1	1171.5	1169.8	1168.2	1166.6
160°	1184.5	1185.7	1185.7	1184.2	1182.8	1181.3	1179.9
162.5°	1196.0	1197.5	1197.5	1196.2	1194.9	1193.7	1192.4
165°	1211.5	1213.1	1213.2	1211.8	1210.4	1208.9	1207.5
167.5°	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4
170°	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0
172.5°	1234.3	1236.0	1235.9	1234.1	1232.3	1230.5	1228.7
175°	1239.4	1240.9	1240.7	1239.1	1237.5	1235.9	1234.2
177.5°	1241.3	1242.5	1242.4	1240.8	1239.1	1237.5	1235.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)